

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for  
Cooper Lighting Solutions  
(formerly Eaton)

Brand: NEO-RAY

Report Number: P331609-935

Luminaire Tested: **S122DIW-S1005D1440U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331609-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D1440U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 8751.4 lumens  
Efficiency: N/A  
Efficacy: 105.6 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 82.9  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	88	85	82	79	70	68	66	57	56	54	45	44	43	37
2	88	81	75	71	81	75	70	65	62	59	55	51	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	28
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	27	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17
8	54	42	35	30	49	39	32	28	33	28	24	28	24	21	23	20	18	15
9	50	39	31	26	46	36	29	25	31	25	22	26	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	163.5	1.9
10°-20°	475.3	5.4
20°-30°	689.9	7.9
30°-40°	728.0	8.3
40°-50°	644.6	7.4
50°-60°	514.4	5.9
60°-70°	349.6	4.0
70°-80°	179.3	2.0
80°-90°	47.4	0.5
90°-100°	56.5	0.6
100°-110°	207.0	2.4
110°-120°	553.4	6.3
120°-130°	913.5	10.4
130°-140°	971.4	11.1
140°-150°	902.9	10.3
150°-160°	726.0	8.3
160°-170°	467.8	5.3
170°-180°	161.0	1.8
0°-30°	1328.7	15.2
0°-40°	2056.7	23.5
0°-60°	3215.7	36.7
0°-90°	3791.9	43.3
90°-120°	816.8	9.3
90°-150°	3604.6	41.2
90°-180°	4959.0	56.7
0°-180°	8751.4	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	40
90°	33	1	33	1	33	16
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	704	100	704	100	251
125°	1047	996	1047	996	1047	906
135°	1272	1232	1272	1232	1272	981
145°	1451	1429	1451	1429	1451	907
155°	1575	1574	1575	1574	1575	727
165°	1654	1658	1654	1658	1654	467
175°	1686	1696	1686	1696	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	20.3	20.2	20.7	20.0	19.9	20.2	20.0	19.2	19.5	19.7	19.8
90°	33.1	32.5	31.9	31.4	30.9	30.0	28.6	27.2	25.8	24.5	22.3
92.5°	33.1	32.7	32.4	32.1	31.8	31.3	30.6	29.8	29.1	28.4	27.3
95°	52.7	53.0	53.2	53.5	53.7	53.2	51.8	50.5	49.1	47.8	45.9
97.5°	70.3	70.0	69.7	69.3	69.0	68.3	67.2	66.1	65.0	63.9	59.5
100°	82.1	81.5	80.9	80.4	79.9	78.5	76.4	74.1	72.0	69.8	65.2
102.5°	87.9	87.1	86.4	85.7	84.9	83.1	80.2	77.4	74.6	71.7	110.5
105°	93.1	92.0	90.9	89.8	88.7	86.7	83.7	80.7	77.7	74.7	149.0
107.5°	95.7	94.7	93.6	92.5	91.4	92.4	95.4	98.5	101.5	104.6	193.6
110°	96.8	95.7	94.5	93.5	92.4	105.5	132.7	159.9	187.1	214.3	292.9



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.7	96.9	96.0	95.1	94.2	143.4	242.7	342.0	441.3	540.5	559.9
115°	100.4	120.0	139.6	159.2	178.7	251.6	377.5	503.6	629.6	755.5	748.7
117.5°	410.0	474.3	538.7	603.1	667.5	715.0	745.5	775.9	806.4	836.9	832.2
120°	747.0	783.7	820.4	857.2	893.9	910.7	907.4	904.1	900.9	897.6	892.7
122.5°	932.1	939.3	946.4	953.5	960.6	963.2	961.3	959.3	957.3	955.4	950.0
125°	1047.0	1046.2	1045.3	1044.6	1043.7	1042.3	1040.4	1038.5	1036.6	1034.7	1029.6
127.5°	1119.5	1119.3	1119.1	1119.0	1118.9	1117.3	1114.6	1111.8	1109.1	1106.3	1102.4
130°	1164.5	1164.8	1165.1	1165.4	1165.6	1164.2	1161.3	1158.3	1155.3	1152.3	1149.3
132.5°	1208.6	1208.9	1209.2	1209.4	1209.7	1208.6	1206.0	1203.4	1200.9	1198.3	1195.3
135°	1272.3	1272.8	1273.4	1273.9	1274.5	1273.4	1270.7	1267.9	1265.2	1262.5	1260.1
137.5°	1330.3	1331.3	1332.2	1333.1	1334.0	1333.2	1330.5	1327.8	1325.2	1322.5	1319.7
140°	1366.6	1368.0	1369.3	1370.7	1372.0	1371.5	1369.1	1366.6	1364.2	1361.7	1358.7
142.5°	1401.9	1403.3	1404.5	1405.9	1407.3	1406.9	1404.6	1402.4	1400.2	1397.9	1394.5
145°	1451.1	1452.4	1453.8	1455.2	1456.6	1456.3	1454.3	1452.4	1450.5	1448.6	1444.0
147.5°	1494.4	1495.6	1496.8	1497.9	1499.0	1498.9	1497.5	1496.1	1494.6	1493.2	1488.7
150°	1520.9	1522.2	1523.6	1525.0	1526.3	1526.2	1524.6	1522.9	1521.3	1519.7	1515.3
152.5°	1543.4	1545.2	1547.0	1548.8	1550.6	1550.7	1549.0	1547.4	1545.8	1544.1	1540.0
155°	1574.8	1576.9	1579.2	1581.3	1583.5	1583.7	1582.1	1580.5	1578.8	1577.2	1574.0
157.5°	1603.4	1605.5	1607.7	1609.8	1611.9	1612.1	1610.2	1608.3	1606.5	1604.6	1602.3
160°	1620.1	1622.0	1623.8	1625.8	1627.7	1627.8	1626.2	1624.5	1622.9	1621.3	1619.6
162.5°	1633.8	1636.2	1638.5	1640.8	1643.1	1643.4	1641.6	1639.7	1637.9	1636.0	1634.6
165°	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3	1653.6
167.5°	1667.3	1669.8	1672.2	1674.7	1677.1	1677.4	1675.5	1673.6	1671.7	1669.8	1669.0
170°	1675.2	1677.7	1680.1	1682.6	1685.0	1685.2	1683.3	1681.4	1679.6	1677.7	1677.1
172.5°	1681.0	1683.5	1685.9	1688.4	1690.8	1691.1	1689.2	1687.3	1685.4	1683.5	1683.0
175°	1686.2	1688.9	1691.6	1694.4	1697.1	1697.5	1695.6	1693.7	1691.8	1689.9	1689.4
177.5°	1689.4	1691.3	1693.3	1695.2	1697.2	1697.5	1695.9	1694.4	1692.9	1691.3	1691.1
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	19.9	19.5	19.0	19.5	17.3	16.8	14.0	11.9	12.0	12.0	11.5
90°	20.1	18.0	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.3	25.1	24.0	23.7	23.9	24.2	24.5	24.7	24.5	24.2	23.9
95°	43.9	42.0	40.1	43.7	52.7	61.6	70.6	79.6	70.6	61.6	52.7
97.5°	55.1	50.7	46.3	56.7	82.1	107.4	132.7	158.0	132.7	107.4	82.1
100°	60.5	55.9	51.3	67.6	104.9	142.2	179.4	216.7	179.4	142.2	104.9
102.5°	149.1	187.9	226.5	249.9	257.7	265.6	273.5	281.4	273.5	265.6	257.7
105°	223.3	297.6	371.9	404.9	396.7	388.6	380.4	372.3	380.4	388.6	396.7
107.5°	282.8	371.9	461.0	502.2	495.6	489.0	482.4	475.9	482.4	489.0	495.6
110°	371.6	450.2	528.8	565.3	559.6	553.9	548.2	542.5	548.2	553.9	559.6





TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	579.4	598.8	618.2	625.4	620.4	615.3	610.2	605.2	610.2	615.3	620.4
115°	741.9	735.1	728.3	722.6	718.0	713.3	708.8	704.1	708.8	713.3	718.0
117.5°	827.5	822.8	818.1	813.2	808.0	802.9	797.7	792.6	797.7	802.9	808.0
120°	887.8	882.9	878.0	873.5	869.4	865.3	861.3	857.2	861.3	865.3	869.4
122.5°	944.7	939.4	934.1	929.3	925.0	920.7	916.4	912.1	916.4	920.7	925.0
125°	1024.4	1019.3	1014.1	1009.7	1006.2	1002.6	999.1	995.6	999.1	1002.6	1006.2
127.5°	1098.5	1094.7	1090.8	1086.9	1083.0	1079.1	1075.1	1071.3	1075.1	1079.1	1083.0
130°	1146.3	1143.3	1140.3	1136.7	1132.3	1127.9	1123.6	1119.2	1123.6	1127.9	1132.3
132.5°	1192.3	1189.4	1186.4	1183.0	1179.3	1175.6	1171.9	1168.2	1171.9	1175.6	1179.3
135°	1257.6	1255.2	1252.7	1249.3	1244.9	1240.6	1236.2	1231.9	1236.2	1240.6	1244.9
137.5°	1317.0	1314.1	1311.4	1308.5	1305.4	1302.4	1299.3	1296.3	1299.3	1302.4	1305.4
140°	1355.7	1352.7	1349.7	1347.1	1345.0	1342.8	1340.6	1338.4	1340.6	1342.8	1345.0
142.5°	1391.1	1387.7	1384.2	1381.6	1379.6	1377.6	1375.6	1373.7	1375.6	1377.6	1379.6
145°	1439.4	1434.8	1430.1	1428.0	1428.2	1428.5	1428.7	1429.1	1428.7	1428.5	1428.2
147.5°	1484.1	1479.5	1474.9	1473.2	1474.2	1475.2	1476.3	1477.3	1476.3	1475.2	1474.2
150°	1511.0	1506.6	1502.3	1501.0	1503.0	1504.9	1506.8	1508.6	1506.8	1504.9	1503.0
152.5°	1535.9	1531.7	1527.6	1526.6	1528.7	1530.9	1533.0	1535.1	1533.0	1530.9	1528.7
155°	1570.7	1567.5	1564.2	1563.7	1566.2	1568.7	1571.1	1573.6	1571.1	1568.7	1566.2
157.5°	1600.1	1597.8	1595.5	1595.4	1597.5	1599.6	1601.6	1603.7	1601.6	1599.6	1597.5
160°	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1619.6	1618.1	1616.4
162.5°	1633.1	1631.8	1630.3	1630.5	1632.1	1633.7	1635.4	1636.9	1635.4	1633.7	1632.1
165°	1652.7	1651.9	1651.1	1651.5	1653.1	1654.8	1656.4	1658.0	1656.4	1654.8	1653.1
167.5°	1668.3	1667.5	1666.7	1667.2	1668.8	1670.4	1672.1	1673.7	1672.1	1670.4	1668.8
170°	1676.5	1676.0	1675.4	1676.0	1677.7	1679.3	1680.9	1682.6	1680.9	1679.3	1677.7
172.5°	1682.4	1681.9	1681.4	1681.9	1683.5	1685.1	1686.8	1688.4	1686.8	1685.1	1683.5
175°	1688.8	1688.2	1687.7	1688.4	1690.3	1692.2	1694.1	1696.0	1694.1	1692.2	1690.3
177.5°	1690.9	1690.7	1690.5	1691.1	1692.6	1694.2	1695.7	1697.2	1695.7	1694.2	1692.6
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	11.6	11.6	11.5	12.0	11.9	11.8	11.5	11.8	12.1	11.3	11.5
90°	13.2	15.8	18.0	20.1	22.3	24.5	25.8	27.2	28.6	30.0	30.9
92.5°	23.7	24.0	25.1	26.3	27.3	28.4	29.1	29.8	30.6	31.3	31.8
95°	43.7	40.1	42.0	43.9	45.9	47.8	49.1	50.5	51.8	53.2	53.7
97.5°	56.7	46.3	50.7	55.1	59.5	63.9	65.0	66.1	67.2	68.3	69.0
100°	67.6	51.3	55.9	60.5	65.2	69.8	72.0	74.1	76.4	78.5	79.9
102.5°	249.9	226.5	187.9	149.1	110.5	71.7	74.6	77.4	80.2	83.1	84.9
105°	404.9	371.9	297.6	223.3	149.0	74.7	77.7	80.7	83.7	86.7	88.7
107.5°	502.2	461.0	371.9	282.8	193.6	104.6	101.5	98.5	95.4	92.4	91.4
110°	565.3	528.8	450.2	371.6	292.9	214.3	187.1	159.9	132.7	105.5	92.4



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	625.4	618.2	598.8	579.4	559.9	540.5	441.3	342.0	242.7	143.4	94.2
115°	722.6	728.3	735.1	741.9	748.7	755.5	629.6	503.6	377.5	251.6	178.7
117.5°	813.2	818.1	822.8	827.5	832.2	836.9	806.4	775.9	745.5	715.0	667.5
120°	873.5	878.0	882.9	887.8	892.7	897.6	900.9	904.1	907.4	910.7	893.9
122.5°	929.3	934.1	939.4	944.7	950.0	955.4	957.3	959.3	961.3	963.2	960.6
125°	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6	1038.5	1040.4	1042.3	1043.7
127.5°	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1	1111.8	1114.6	1117.3	1118.9
130°	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3	1158.3	1161.3	1164.2	1165.6
132.5°	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9	1203.4	1206.0	1208.6	1209.7
135°	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2	1267.9	1270.7	1273.4	1274.5
137.5°	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2	1327.8	1330.5	1333.2	1334.0
140°	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2	1366.6	1369.1	1371.5	1372.0
142.5°	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2	1402.4	1404.6	1406.9	1407.3
145°	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5	1452.4	1454.3	1456.3	1456.6
147.5°	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6	1496.1	1497.5	1498.9	1499.0
150°	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3	1522.9	1524.6	1526.2	1526.3
152.5°	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8	1547.4	1549.0	1550.7	1550.6
155°	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8	1580.5	1582.1	1583.7	1583.5
157.5°	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5	1608.3	1610.2	1612.1	1611.9
160°	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9	1624.5	1626.2	1627.8	1627.7
162.5°	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9	1639.7	1641.6	1643.4	1643.1
165°	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0
167.5°	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7	1673.6	1675.5	1677.4	1677.1
170°	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6	1681.4	1683.3	1685.2	1685.0
172.5°	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4	1687.3	1689.2	1691.1	1690.8
175°	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8	1693.7	1695.6	1697.5	1697.1
177.5°	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9	1694.4	1695.9	1697.5	1697.2
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	11.5	11.1	11.3	10.8	11.3	11.1	11.5	11.5	11.3	12.1	11.8
90°	31.4	31.9	32.5	33.1	32.5	31.9	31.4	30.9	30.0	28.6	27.2
92.5°	32.1	32.4	32.7	33.1	32.7	32.4	32.1	31.8	31.3	30.6	29.8
95°	53.5	53.2	53.0	52.7	53.0	53.2	53.5	53.7	53.2	51.8	50.5
97.5°	69.3	69.7	70.0	70.3	70.0	69.7	69.3	69.0	68.3	67.2	66.1
100°	80.4	80.9	81.5	82.1	81.5	80.9	80.4	79.9	78.5	76.4	74.1
102.5°	85.7	86.4	87.1	87.9	87.1	86.4	85.7	84.9	83.1	80.2	77.4
105°	89.8	90.9	92.0	93.1	92.0	90.9	89.8	88.7	86.7	83.7	80.7
107.5°	92.5	93.6	94.7	95.7	94.7	93.6	92.5	91.4	92.4	95.4	98.5
110°	93.5	94.5	95.7	96.8	95.7	94.5	93.5	92.4	105.5	132.7	159.9



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.1	96.0	96.9	97.7	96.9	96.0	95.1	94.2	143.4	242.7	342.0
115°	159.2	139.6	120.0	100.4	120.0	139.6	159.2	178.7	251.6	377.5	503.6
117.5°	603.1	538.7	474.3	410.0	474.3	538.7	603.1	667.5	715.0	745.5	775.9
120°	857.2	820.4	783.7	747.0	783.7	820.4	857.2	893.9	910.7	907.4	904.1
122.5°	953.5	946.4	939.3	932.1	939.3	946.4	953.5	960.6	963.2	961.3	959.3
125°	1044.6	1045.3	1046.2	1047.0	1046.2	1045.3	1044.6	1043.7	1042.3	1040.4	1038.5
127.5°	1119.0	1119.1	1119.3	1119.5	1119.3	1119.1	1119.0	1118.9	1117.3	1114.6	1111.8
130°	1165.4	1165.1	1164.8	1164.5	1164.8	1165.1	1165.4	1165.6	1164.2	1161.3	1158.3
132.5°	1209.4	1209.2	1208.9	1208.6	1208.9	1209.2	1209.4	1209.7	1208.6	1206.0	1203.4
135°	1273.9	1273.4	1272.8	1272.3	1272.8	1273.4	1273.9	1274.5	1273.4	1270.7	1267.9
137.5°	1333.1	1332.2	1331.3	1330.3	1331.3	1332.2	1333.1	1334.0	1333.2	1330.5	1327.8
140°	1370.7	1369.3	1368.0	1366.6	1368.0	1369.3	1370.7	1372.0	1371.5	1369.1	1366.6
142.5°	1405.9	1404.5	1403.3	1401.9	1403.3	1404.5	1405.9	1407.3	1406.9	1404.6	1402.4
145°	1455.2	1453.8	1452.4	1451.1	1452.4	1453.8	1455.2	1456.6	1456.3	1454.3	1452.4
147.5°	1497.9	1496.8	1495.6	1494.4	1495.6	1496.8	1497.9	1499.0	1498.9	1497.5	1496.1
150°	1525.0	1523.6	1522.2	1520.9	1522.2	1523.6	1525.0	1526.3	1526.2	1524.6	1522.9
152.5°	1548.8	1547.0	1545.2	1543.4	1545.2	1547.0	1548.8	1550.6	1550.7	1549.0	1547.4
155°	1581.3	1579.2	1576.9	1574.8	1576.9	1579.2	1581.3	1583.5	1583.7	1582.1	1580.5
157.5°	1609.8	1607.7	1605.5	1603.4	1605.5	1607.7	1609.8	1611.9	1612.1	1610.2	1608.3
160°	1625.8	1623.8	1622.0	1620.1	1622.0	1623.8	1625.8	1627.7	1627.8	1626.2	1624.5
162.5°	1640.8	1638.5	1636.2	1633.8	1636.2	1638.5	1640.8	1643.1	1643.4	1641.6	1639.7
165°	1660.1	1658.2	1656.3	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2
167.5°	1674.7	1672.2	1669.8	1667.3	1669.8	1672.2	1674.7	1677.1	1677.4	1675.5	1673.6
170°	1682.6	1680.1	1677.7	1675.2	1677.7	1680.1	1682.6	1685.0	1685.2	1683.3	1681.4
172.5°	1688.4	1685.9	1683.5	1681.0	1683.5	1685.9	1688.4	1690.8	1691.1	1689.2	1687.3
175°	1694.4	1691.6	1688.9	1686.2	1688.9	1691.6	1694.4	1697.1	1697.5	1695.6	1693.7
177.5°	1695.2	1693.3	1691.3	1689.4	1691.3	1693.3	1695.2	1697.2	1697.5	1695.9	1694.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	11.5	11.8	11.9	12.0	11.5	11.6	11.6	11.5	12.0	12.0	11.9
90°	25.8	24.5	22.3	20.1	18.0	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.3	25.1	24.0	23.7	23.9	24.2	24.5	24.7
95°	49.1	47.8	45.9	43.9	42.0	40.1	43.7	52.7	61.6	70.6	79.6
97.5°	65.0	63.9	59.5	55.1	50.7	46.3	56.7	82.1	107.4	132.7	158.0
100°	72.0	69.8	65.2	60.5	55.9	51.3	67.6	104.9	142.2	179.4	216.7
102.5°	74.6	71.7	110.5	149.1	187.9	226.5	249.9	257.7	265.6	273.5	281.4
105°	77.7	74.7	149.0	223.3	297.6	371.9	404.9	396.7	388.6	380.4	372.3
107.5°	101.5	104.6	193.6	282.8	371.9	461.0	502.2	495.6	489.0	482.4	475.9
110°	187.1	214.3	292.9	371.6	450.2	528.8	565.3	559.6	553.9	548.2	542.5



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	441.3	540.5	559.9	579.4	598.8	618.2	625.4	620.4	615.3	610.2	605.2
115°	629.6	755.5	748.7	741.9	735.1	728.3	722.6	718.0	713.3	708.8	704.1
117.5°	806.4	836.9	832.2	827.5	822.8	818.1	813.2	808.0	802.9	797.7	792.6
120°	900.9	897.6	892.7	887.8	882.9	878.0	873.5	869.4	865.3	861.3	857.2
122.5°	957.3	955.4	950.0	944.7	939.4	934.1	929.3	925.0	920.7	916.4	912.1
125°	1036.6	1034.7	1029.6	1024.4	1019.3	1014.1	1009.7	1006.2	1002.6	999.1	995.6
127.5°	1109.1	1106.3	1102.4	1098.5	1094.7	1090.8	1086.9	1083.0	1079.1	1075.1	1071.3
130°	1155.3	1152.3	1149.3	1146.3	1143.3	1140.3	1136.7	1132.3	1127.9	1123.6	1119.2
132.5°	1200.9	1198.3	1195.3	1192.3	1189.4	1186.4	1183.0	1179.3	1175.6	1171.9	1168.2
135°	1265.2	1262.5	1260.1	1257.6	1255.2	1252.7	1249.3	1244.9	1240.6	1236.2	1231.9
137.5°	1325.2	1322.5	1319.7	1317.0	1314.1	1311.4	1308.5	1305.4	1302.4	1299.3	1296.3
140°	1364.2	1361.7	1358.7	1355.7	1352.7	1349.7	1347.1	1345.0	1342.8	1340.6	1338.4
142.5°	1400.2	1397.9	1394.5	1391.1	1387.7	1384.2	1381.6	1379.6	1377.6	1375.6	1373.7
145°	1450.5	1448.6	1444.0	1439.4	1434.8	1430.1	1428.0	1428.2	1428.5	1428.7	1429.1
147.5°	1494.6	1493.2	1488.7	1484.1	1479.5	1474.9	1473.2	1474.2	1475.2	1476.3	1477.3
150°	1521.3	1519.7	1515.3	1511.0	1506.6	1502.3	1501.0	1503.0	1504.9	1506.8	1508.6
152.5°	1545.8	1544.1	1540.0	1535.9	1531.7	1527.6	1526.6	1528.7	1530.9	1533.0	1535.1
155°	1578.8	1577.2	1574.0	1570.7	1567.5	1564.2	1563.7	1566.2	1568.7	1571.1	1573.6
157.5°	1606.5	1604.6	1602.3	1600.1	1597.8	1595.5	1595.4	1597.5	1599.6	1601.6	1603.7
160°	1622.9	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3
162.5°	1637.9	1636.0	1634.6	1633.1	1631.8	1630.3	1630.5	1632.1	1633.7	1635.4	1636.9
165°	1656.3	1654.3	1653.6	1652.7	1651.9	1651.1	1651.5	1653.1	1654.8	1656.4	1658.0
167.5°	1671.7	1669.8	1669.0	1668.3	1667.5	1666.7	1667.2	1668.8	1670.4	1672.1	1673.7
170°	1679.6	1677.7	1677.1	1676.5	1676.0	1675.4	1676.0	1677.7	1679.3	1680.9	1682.6
172.5°	1685.4	1683.5	1683.0	1682.4	1681.9	1681.4	1681.9	1683.5	1685.1	1686.8	1688.4
175°	1691.8	1689.9	1689.4	1688.8	1688.2	1687.7	1688.4	1690.3	1692.2	1694.1	1696.0
177.5°	1692.9	1691.3	1691.1	1690.9	1690.7	1690.5	1691.1	1692.6	1694.2	1695.7	1697.2
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	14.0	16.8	17.3	19.5	19.0	19.5	19.9	19.8	19.7	19.5	19.2
90°	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8	27.2
92.5°	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1	29.8
95°	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1	50.5
97.5°	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0	66.1
100°	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0	74.1
102.5°	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6	77.4
105°	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7	80.7
107.5°	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5	98.5
110°	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1	159.9





TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3	342.0
115°	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6	503.6
117.5°	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4	775.9
120°	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9	904.1
122.5°	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3	959.3
125°	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6	1038.5
127.5°	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1	1111.8
130°	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3	1158.3
132.5°	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9	1203.4
135°	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2	1267.9
137.5°	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2	1327.8
140°	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2	1366.6
142.5°	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2	1402.4
145°	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5	1452.4
147.5°	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6	1496.1
150°	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3	1522.9
152.5°	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8	1547.4
155°	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8	1580.5
157.5°	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5	1608.3
160°	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9	1624.5
162.5°	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9	1639.7
165°	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3	1658.2
167.5°	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7	1673.6
170°	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6	1681.4
172.5°	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4	1687.3
175°	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8	1693.7
177.5°	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9	1694.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	20.0	20.2	19.9	20.0	20.7	20.2	20.3
90°	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	132.7	105.5	92.4	93.5	94.5	95.7	96.8



TEST NUMBER: P331609-935

CATALOG NUMBER: S122DIW-S1005D1440U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)