

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331823-830

Luminaire Tested: **S122RDIW-S675D1440U830-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331823-830
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S675D1440U830-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7620.4 lumens
Efficiency: N/A
Efficacy: 111.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 68.1
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	91	91	91	91	72	72	72	53	53	53	37	37	37	29				
1	93	89	86	82	83	80	77	74	63	61	59	47	46	45	33	32	31	25				
2	85	78	72	68	76	70	65	61	55	52	49	42	40	38	29	28	27	21				
3	78	69	62	57	69	62	56	51	49	45	42	37	34	32	26	24	23	18				
4	71	61	54	48	64	55	49	44	44	39	36	33	30	28	23	22	20	16				
5	65	54	47	41	58	49	43	38	39	34	31	30	27	24	21	19	18	14				
6	60	49	41	36	54	44	37	33	35	30	27	27	24	21	19	17	16	12				
7	56	44	36	31	50	40	33	29	32	27	24	25	21	19	18	16	14	11				
8	52	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	13	10				
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11	9				
10	45	33	26	22	40	30	24	20	24	20	17	19	16	14	14	12	10	8				

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	17166	17166	17166
5°	17232	16951	17045
10°	17100	16674	16531
15°	16904	16181	15714
20°	16632	15474	14698
25°	16352	14672	13714
30°	15966	13848	12450
35°	15589	12952	11341
40°	15209	12026	10058
45°	14764	10985	8896
50°	14307	9934	7759
55°	13841	8802	6663
60°	13298	7611	5532
65°	12684	6395	5039
70°	11948	5268	4631
75°	11042	4803	4323
80°	9754	4296	3933
85°	7669	3390	3390



TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	99.5	1.3
10°-20°	273.3	3.6
20°-30°	383.7	5.0
30°-40°	418.4	5.5
40°-50°	384.7	5.0
50°-60°	302.2	4.0
60°-70°	197.0	2.6
70°-80°	101.6	1.3
80°-90°	30.9	0.4
90°-100°	61.8	0.8
100°-110°	226.6	3.0
110°-120°	605.8	7.9
120°-130°	1000.0	13.1
130°-140°	1063.4	14.0
140°-150°	988.4	13.0
150°-160°	794.7	10.4
160°-170°	512.1	6.7
170°-180°	176.3	2.3
0°-30°	756.5	9.9
0°-40°	1174.9	15.4
0°-60°	1861.8	24.4
0°-90°	2191.3	28.8
90°-120°	894.2	11.7
90°-150°	3946.0	51.8
90°-180°	5429.0	71.2
0°-180°	7620.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1063	1063	1063	1063	1063	
5°	1063	1058	1046	1054	1052	101
15°	1011	999	968	950	940	285
25°	918	885	824	786	770	422
35°	791	740	657	599	575	495
45°	647	580	481	415	390	499
55°	492	415	313	257	237	439
65°	332	254	167	136	132	329
75°	177	112	77	71	69	187
85°	41	22	18	18	18	49
90°	1	16	27	33	36	6
95°	87	46	52	58	58	107
105°	408	425	82	96	102	435
115°	771	794	827	236	110	759
125°	1090	1108	1133	1142	1146	971
135°	1349	1369	1382	1395	1393	1041
145°	1564	1564	1586	1594	1589	978
155°	1723	1712	1726	1734	1724	793
165°	1815	1808	1811	1819	1811	513
175°	1857	1848	1850	1858	1846	177
180°	1853	1853	1853	1853	1853	



TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1067.1	1066.2	1065.4	1064.5	1063.7	1062.2	1060.4	1058.5	1056.7	1054.8	1056.5
5°	1063.2	1062.2	1061.1	1060.0	1058.9	1057.1	1054.2	1051.5	1048.7	1045.9	1047.8
7.5°	1052.3	1050.9	1049.6	1048.3	1047.0	1044.6	1041.4	1038.2	1034.9	1031.7	1032.2
10°	1043.0	1041.5	1040.0	1038.5	1037.0	1034.2	1029.8	1025.6	1021.3	1017.0	1016.4
12.5°	1031.4	1029.6	1027.7	1026.0	1024.1	1020.5	1015.0	1009.6	1004.0	998.5	997.4
15°	1011.3	1008.9	1006.5	1004.2	1001.8	997.0	989.8	982.5	975.2	968.0	963.9
17.5°	986.5	982.9	979.3	975.6	972.0	965.6	956.3	947.0	937.6	928.3	923.5
20°	968.0	963.7	959.4	955.2	950.8	943.4	932.6	922.0	911.3	900.6	895.2
22.5°	947.9	943.2	938.4	933.6	928.8	920.4	908.3	896.3	884.2	872.1	865.3
25°	917.9	911.1	904.3	897.4	890.6	880.1	866.0	851.9	837.7	823.6	814.8
27.5°	881.7	874.3	866.9	859.4	852.0	840.3	824.4	808.5	792.6	776.7	766.5
30°	856.4	848.2	840.1	832.0	823.9	811.2	794.1	777.0	759.9	742.8	731.9
32.5°	831.7	822.2	812.8	803.2	793.7	780.2	762.8	745.4	727.9	710.5	698.0
35°	790.9	780.0	769.1	758.2	747.3	732.4	713.6	694.8	676.0	657.1	643.7
37.5°	750.2	738.1	726.1	714.2	702.2	686.2	666.2	646.1	626.0	606.0	591.2
40°	721.6	708.8	696.0	683.2	670.3	653.6	632.8	612.1	591.4	570.6	555.4
42.5°	692.4	678.9	665.3	651.9	638.4	620.9	599.5	578.1	556.6	535.2	519.4
45°	646.6	632.3	617.9	603.6	589.3	570.9	548.5	526.0	503.5	481.1	465.9
47.5°	601.9	586.7	571.6	556.4	541.2	522.1	498.9	475.7	452.5	429.3	414.2
50°	569.6	554.4	539.2	524.1	508.9	489.6	466.0	442.5	419.0	395.5	380.7
52.5°	538.1	522.2	506.3	490.5	474.6	455.2	432.2	409.2	386.2	363.2	348.9
55°	491.7	475.0	458.4	441.7	425.0	405.1	382.0	358.9	335.8	312.7	299.9
57.5°	444.1	427.1	409.9	392.9	375.7	356.1	333.8	311.7	289.5	267.3	255.5
60°	411.8	394.7	377.6	360.5	343.4	323.9	301.8	279.7	257.8	235.7	224.8
62.5°	380.2	363.2	346.0	328.9	311.8	292.8	271.8	250.8	229.8	208.8	198.4
65°	332.0	314.6	297.3	280.0	262.7	244.4	225.2	205.9	186.6	167.4	160.1
67.5°	285.4	268.2	251.0	233.8	216.6	199.3	182.0	164.8	147.4	130.1	126.8
70°	253.1	236.4	219.7	203.0	186.3	170.6	155.9	141.1	126.4	111.6	109.4
72.5°	222.3	206.2	190.3	174.3	158.3	144.4	132.5	120.6	108.9	97.0	95.2
75°	177.0	162.1	147.1	132.1	117.2	106.0	98.8	91.5	84.3	77.0	75.5
77.5°	132.6	119.4	106.3	93.2	80.1	71.7	68.2	64.8	61.3	57.8	56.8
80°	104.9	94.0	83.0	72.2	61.3	54.8	52.6	50.4	48.4	46.2	45.3
82.5°	79.5	71.0	62.5	53.9	45.4	40.4	39.0	37.5	36.1	34.7	34.1
85°	41.4	36.9	32.4	27.9	23.4	20.8	20.2	19.6	18.9	18.3	18.3
87.5°	12.6	11.9	11.1	10.5	9.7	9.6	10.1	10.6	11.0	11.5	11.7
90°	1.3	4.6	7.9	11.2	14.4	17.2	19.7	22.1	24.4	26.8	28.3
92.5°	27.1	26.8	26.5	26.2	25.9	26.3	27.5	28.7	29.9	31.1	31.9
95°	87.1	77.3	67.5	57.7	47.8	43.9	46.0	48.1	50.2	52.3	53.7
97.5°	173.0	145.2	117.5	89.8	62.1	50.7	55.5	60.3	65.1	69.9	71.2
100°	237.2	196.4	155.6	114.8	74.0	56.2	61.2	66.3	71.4	76.4	78.8
102.5°	308.0	299.4	290.8	282.1	273.5	248.0	205.7	163.2	120.9	78.5	81.6
105°	407.6	416.4	425.4	434.3	443.3	407.1	325.7	244.4	163.1	81.8	85.0
107.5°	520.9	528.1	535.4	542.5	549.8	504.6	407.1	309.5	212.0	114.5	111.1
110°	593.9	600.1	606.3	612.7	618.9	578.9	492.9	406.8	320.7	234.6	204.8



TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	662.5	668.0	673.5	679.1	684.7	676.7	655.5	634.2	612.9	591.7	483.1
115°	770.8	775.9	780.9	786.0	791.1	797.3	804.7	812.2	819.6	827.1	689.2
117.5°	867.6	873.3	878.9	884.6	890.2	895.6	900.7	905.9	911.0	916.2	882.8
120°	938.4	942.8	947.3	951.8	956.2	961.1	966.5	971.9	977.2	982.6	986.2
122.5°	998.4	1003.1	1007.9	1012.6	1017.3	1022.6	1028.3	1034.2	1040.0	1045.8	1048.0
125°	1089.9	1093.7	1097.6	1101.5	1105.3	1110.1	1115.8	1121.4	1127.1	1132.7	1134.8
127.5°	1172.7	1177.0	1181.3	1185.5	1189.9	1194.1	1198.3	1202.6	1206.8	1211.1	1214.1
130°	1225.2	1230.0	1234.7	1239.5	1244.3	1248.3	1251.6	1254.9	1258.1	1261.4	1264.7
132.5°	1278.8	1282.9	1286.9	1291.0	1295.1	1298.7	1302.0	1305.2	1308.5	1311.8	1314.7
135°	1348.6	1353.3	1358.1	1362.8	1367.6	1371.3	1374.0	1376.7	1379.4	1382.1	1385.1
137.5°	1419.1	1422.4	1425.8	1429.1	1432.4	1435.6	1438.6	1441.7	1444.7	1447.7	1450.7
140°	1465.2	1467.5	1470.0	1472.3	1474.7	1477.5	1480.8	1484.1	1487.4	1490.6	1493.4
142.5°	1503.8	1505.9	1508.1	1510.2	1512.4	1515.3	1519.1	1522.9	1526.5	1530.3	1532.8
145°	1564.4	1564.1	1563.8	1563.5	1563.2	1565.6	1570.7	1575.7	1580.7	1585.8	1587.9
147.5°	1617.2	1616.1	1615.0	1613.8	1612.7	1614.6	1619.6	1624.7	1629.7	1634.7	1636.2
150°	1651.5	1649.4	1647.4	1645.3	1643.1	1644.5	1649.3	1654.1	1658.8	1663.6	1665.4
152.5°	1680.5	1678.2	1675.8	1673.5	1671.2	1672.3	1676.8	1681.3	1685.8	1690.4	1692.1
155°	1722.6	1719.9	1717.2	1714.5	1711.8	1712.3	1715.9	1719.5	1723.1	1726.5	1728.3
157.5°	1755.6	1753.3	1751.1	1748.8	1746.5	1746.6	1749.1	1751.6	1754.1	1756.6	1758.7
160°	1774.8	1773.0	1771.3	1769.5	1767.7	1767.7	1769.5	1771.3	1773.0	1774.8	1776.6
162.5°	1792.0	1790.3	1788.5	1786.7	1784.9	1784.7	1786.3	1787.8	1789.4	1790.9	1793.0
165°	1815.1	1813.3	1811.5	1809.7	1807.9	1807.5	1808.4	1809.2	1810.2	1811.0	1813.2
167.5°	1832.2	1830.4	1828.6	1826.8	1825.0	1824.6	1825.4	1826.3	1827.1	1828.0	1830.0
170°	1841.9	1840.1	1838.3	1836.5	1834.8	1834.1	1834.8	1835.3	1835.9	1836.5	1838.6
172.5°	1848.3	1846.5	1844.7	1843.0	1841.2	1840.6	1841.2	1841.7	1842.4	1843.0	1845.0
175°	1856.6	1854.5	1852.5	1850.4	1848.3	1847.6	1848.1	1848.7	1849.4	1849.9	1852.0
177.5°	1857.9	1856.3	1854.6	1852.9	1851.2	1850.6	1850.8	1851.1	1851.2	1851.5	1853.2
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6



TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2	1063.2
2.5°	1058.2	1059.9	1061.6	1062.2	1062.0	1061.6	1061.3	1060.9
5°	1049.7	1051.7	1053.6	1054.2	1053.6	1052.9	1052.3	1051.7
7.5°	1032.7	1033.3	1033.9	1033.6	1032.5	1031.4	1030.3	1029.2
10°	1015.8	1015.1	1014.5	1013.5	1012.2	1011.0	1009.7	1008.3
12.5°	996.3	995.1	993.9	992.3	990.1	988.1	985.9	983.7
15°	959.9	955.7	951.7	948.6	946.5	944.3	942.2	940.1
17.5°	918.7	913.8	909.0	904.7	901.1	897.4	893.7	890.0
20°	889.9	884.6	879.2	874.2	869.5	864.8	860.1	855.4
22.5°	858.4	851.5	844.6	839.4	835.8	832.4	828.9	825.4
25°	806.1	797.3	788.5	782.6	779.4	776.2	773.0	769.8
27.5°	756.2	746.0	735.8	728.1	723.0	717.9	712.8	707.8
30°	721.0	710.1	699.2	690.9	685.0	679.3	673.5	667.8
32.5°	685.6	673.2	660.7	651.8	646.3	640.9	635.5	630.1
35°	630.3	616.8	603.3	594.2	589.5	584.8	580.1	575.4
37.5°	576.3	561.5	546.7	536.5	531.1	525.8	520.4	515.0
40°	540.2	525.0	509.8	499.5	493.9	488.3	482.8	477.2
42.5°	503.8	488.0	472.4	461.8	456.5	451.1	445.7	440.3
45°	450.7	435.5	420.4	410.2	405.1	399.9	394.8	389.6
47.5°	399.2	384.1	368.9	359.1	354.4	349.8	345.1	340.4
50°	366.0	351.2	336.5	326.8	322.3	317.8	313.4	308.9
52.5°	334.7	320.4	306.1	297.0	292.8	288.7	284.6	280.4
55°	287.1	274.2	261.4	253.0	248.9	244.8	240.7	236.7
57.5°	243.7	232.1	220.3	212.6	209.2	205.9	202.4	199.0
60°	214.0	203.0	192.1	184.9	181.5	178.1	174.7	171.3
62.5°	188.0	177.6	167.2	161.0	158.9	156.9	154.9	152.8
65°	152.9	145.6	138.4	134.4	133.7	133.1	132.4	131.9
67.5°	123.4	120.1	116.8	114.7	114.0	113.4	112.7	112.0
70°	107.4	105.2	103.0	101.6	100.7	99.8	99.0	98.1
72.5°	93.4	91.6	89.8	88.7	88.1	87.7	87.1	86.6
75°	74.0	72.5	71.0	70.1	69.9	69.7	69.5	69.3
77.5°	56.0	55.1	54.3	53.7	53.3	53.1	52.7	52.3
80°	44.5	43.6	42.8	42.3	42.3	42.3	42.3	42.3
82.5°	33.6	33.1	32.6	32.3	32.3	32.3	32.3	32.3
85°	18.3	18.3	18.3	18.3	18.3	18.3	18.3	18.3
87.5°	11.8	11.9	12.1	12.2	12.3	12.3	12.5	12.6
90°	29.8	31.3	32.8	33.8	34.4	35.0	35.6	36.2
92.5°	32.6	33.5	34.2	34.8	35.2	35.4	35.8	36.2
95°	55.2	56.7	58.2	58.8	58.5	58.2	58.0	57.7
97.5°	72.4	73.5	74.7	75.5	75.9	76.3	76.6	76.9
100°	81.2	83.6	86.0	87.5	88.0	88.6	89.3	89.8
102.5°	84.7	87.8	91.0	92.9	93.8	94.5	95.4	96.2
105°	88.3	91.6	94.9	97.1	98.3	99.5	100.7	101.9
107.5°	107.8	104.4	101.1	100.1	101.2	102.5	103.7	104.8
110°	175.0	145.2	115.5	101.1	102.4	103.5	104.7	105.9



TEST NUMBER: P331823-830

CATALOG NUMBER: S122RDIW-S675D1440U830-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	374.4	265.7	157.0	103.1	104.2	105.1	106.0	107.0
115°	551.3	413.3	275.4	195.7	174.3	152.8	131.4	109.9
117.5°	849.4	816.1	782.7	730.8	660.3	589.7	519.2	448.8
120°	989.8	993.3	996.9	978.5	938.4	898.1	857.9	817.7
122.5°	1050.2	1052.3	1054.4	1051.6	1043.8	1036.0	1028.2	1020.4
125°	1136.9	1139.0	1141.0	1142.6	1143.5	1144.3	1145.3	1146.1
127.5°	1217.1	1220.1	1223.1	1224.8	1224.9	1225.1	1225.3	1225.5
130°	1268.0	1271.3	1274.5	1276.0	1275.7	1275.4	1275.2	1274.8
132.5°	1317.4	1320.2	1323.0	1324.3	1324.0	1323.7	1323.4	1323.0
135°	1388.0	1391.0	1394.0	1395.2	1394.6	1394.0	1393.4	1392.8
137.5°	1453.6	1456.5	1459.4	1460.4	1459.3	1458.4	1457.4	1456.3
140°	1496.0	1498.7	1501.4	1501.9	1500.5	1499.0	1497.5	1496.0
142.5°	1535.2	1537.7	1540.1	1540.6	1539.1	1537.6	1536.2	1534.6
145°	1590.0	1592.0	1594.2	1594.5	1593.0	1591.5	1590.0	1588.6
147.5°	1637.8	1639.3	1640.9	1641.0	1639.7	1638.5	1637.2	1636.0
150°	1667.2	1669.0	1670.8	1670.8	1669.4	1667.9	1666.4	1664.9
152.5°	1693.9	1695.7	1697.5	1697.4	1695.4	1693.6	1691.6	1689.6
155°	1730.1	1731.9	1733.7	1733.4	1731.1	1728.7	1726.3	1723.9
157.5°	1760.7	1762.6	1764.7	1764.5	1762.3	1759.9	1757.6	1755.3
160°	1778.4	1780.2	1782.0	1781.9	1779.8	1777.6	1775.6	1773.5
162.5°	1795.0	1797.1	1799.0	1798.7	1796.2	1793.7	1791.1	1788.6
165°	1815.2	1817.3	1819.4	1819.4	1817.3	1815.2	1813.2	1811.0
167.5°	1832.1	1834.2	1836.3	1836.0	1833.3	1830.6	1828.0	1825.2
170°	1840.7	1842.8	1844.8	1844.6	1841.9	1839.2	1836.5	1833.8
172.5°	1847.1	1849.2	1851.2	1851.0	1848.3	1845.6	1843.0	1840.2
175°	1854.1	1856.1	1858.2	1857.8	1854.8	1851.8	1848.9	1845.9
177.5°	1854.8	1856.5	1858.2	1857.9	1855.8	1853.7	1851.5	1849.4
180°	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6	1852.6

(END OF REPORT)