

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331586-935

Luminaire Tested: **S122DIW-S1005D435U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331586-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5082.1 lumens
Efficiency: N/A
Efficacy: 97.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	97	97	97	87	87	87	79	79	79	75
1	104	100	96	93	99	95	92	89	86	84	81	78	76	74	71	69	68	64
2	95	88	82	77	90	84	79	74	76	72	69	70	66	63	63	61	58	55
3	87	78	71	65	83	75	68	63	68	63	59	62	58	54	57	53	50	47
4	80	70	62	56	76	67	60	54	61	55	51	56	51	47	51	47	44	41
5	74	63	55	49	70	60	53	47	55	49	44	51	46	42	46	42	39	36
6	69	57	49	43	65	54	47	42	50	44	39	46	41	37	42	38	35	32
7	64	52	44	38	61	50	42	37	46	40	35	42	37	33	39	35	31	29
8	60	47	39	34	57	45	38	33	42	36	31	39	34	30	36	32	28	26
9	56	43	36	31	53	42	35	30	39	33	29	36	31	27	33	29	26	24
10	52	40	33	28	50	39	32	27	36	30	26	33	28	25	31	27	24	22

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	27719	27719	27719	27719
5°	31076	27901	24725	27901
10°	35611	27671	21397	27671
15°	39397	27164	18903	27164
20°	38797	26620	17234	26620
25°	34983	25896	16174	25896
30°	28909	24738	15401	24738
35°	21068	23526	14852	23526
40°	16828	22097	14547	22097
45°	14705	20445	14132	20445
50°	13823	18844	13855	18844
55°	12740	17219	13486	17219
60°	11677	15490	12910	15490
65°	10636	13941	12351	13941
70°	9659	12430	11528	12430
75°	8559	10742	10212	10742
80°	7364	8898	8219	8898
85°	6595	6595	4891	6595



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	163.5	3.2
10°-20°	475.3	9.4
20°-30°	689.9	13.6
30°-40°	728.0	14.3
40°-50°	644.6	12.7
50°-60°	514.4	10.1
60°-70°	349.6	6.9
70°-80°	179.3	3.5
80°-90°	45.1	0.9
90°-100°	29.3	0.6
100°-110°	91.0	1.8
110°-120°	155.5	3.1
120°-130°	204.5	4.0
130°-140°	229.5	4.5
140°-150°	225.0	4.4
150°-160°	188.8	3.7
160°-170°	125.2	2.5
170°-180°	43.8	0.9
0°-30°	1328.7	26.1
0°-40°	2056.7	40.5
0°-60°	3215.7	63.3
0°-90°	3789.6	74.6
90°-120°	275.7	5.4
90°-150°	934.8	18.4
90°-180°	1293.0	25.4
0°-180°	5082.1	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1717	1717	1717	1717	1717	
5°	1917	1722	1526	1722	1917	191
15°	2357	1625	1131	1625	2357	650
25°	1964	1454	908	1454	1964	888
35°	1069	1194	754	1194	1069	695
45°	644	895	619	895	644	506
55°	453	612	479	612	453	406
65°	278	365	323	365	278	277
75°	137	172	164	172	137	147
85°	36	36	26	36	36	39
90°	13	0	13	0	13	8
95°	24	20	24	20	24	27
105°	87	84	87	84	87	91
115°	156	156	156	156	156	154
125°	228	227	228	227	228	203
135°	297	294	297	294	297	229
145°	360	356	360	356	360	225
155°	411	408	411	408	411	189
165°	444	444	444	444	444	125
175°	460	462	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1796.0	1796.6	1797.6	1789.2	1788.1	1788.1	1780.7	1774.4	1767.0	1757.0	1758.1
5°	1917.4	1924.7	1927.3	1919.4	1907.5	1906.3	1895.1	1876.5	1859.4	1845.6	1835.7
7.5°	2062.4	2065.3	2058.8	2048.4	2039.5	2023.7	2002.9	1982.4	1953.8	1927.5	1908.0
10°	2172.1	2176.1	2164.9	2149.7	2137.2	2118.7	2088.4	2057.4	2019.7	1983.5	1954.4
12.5°	2255.6	2265.3	2250.9	2248.9	2227.5	2202.1	2165.9	2150.3	2097.3	2046.8	2015.7
15°	2356.9	2356.2	2357.6	2345.0	2329.2	2325.2	2287.0	2245.4	2170.8	2141.1	2089.6
17.5°	2327.6	2337.6	2342.3	2342.1	2341.7	2339.3	2326.9	2300.7	2263.3	2215.2	2155.8
20°	2258.0	2271.1	2273.1	2288.3	2296.9	2308.1	2312.7	2305.4	2282.3	2242.1	2190.6
22.5°	2150.3	2154.0	2160.2	2183.8	2202.4	2230.5	2245.1	2269.5	2260.7	2241.0	2198.0
25°	1963.7	1957.1	1980.1	1992.0	2034.9	2079.7	2112.1	2147.8	2179.4	2198.6	2186.0
27.5°	1739.6	1729.7	1764.3	1795.8	1830.7	1879.2	1929.6	1989.1	2038.6	2100.5	2121.8
30°	1550.6	1556.5	1589.5	1623.2	1675.9	1744.6	1801.3	1866.6	1937.2	2006.6	2054.7
32.5°	1346.9	1369.7	1390.5	1442.1	1488.6	1565.1	1648.2	1729.9	1818.0	1896.8	1971.3
35°	1068.9	1095.3	1124.4	1161.9	1227.3	1303.1	1384.3	1494.5	1614.6	1722.2	1810.6
37.5°	899.7	895.5	912.1	939.4	992.2	1053.5	1146.9	1255.8	1397.1	1523.5	1648.2
40°	798.4	795.7	807.6	832.7	873.0	917.8	999.6	1095.3	1226.6	1381.0	1529.5
42.5°	728.8	730.3	736.9	754.6	782.1	819.1	880.4	961.7	1082.0	1227.4	1387.0
45°	644.0	648.6	655.9	664.4	680.3	710.7	744.9	803.1	898.0	1019.4	1176.5
47.5°	583.0	583.2	590.6	598.1	607.4	624.6	652.6	689.0	756.0	854.9	989.9
50°	550.3	545.7	551.0	556.9	566.8	578.7	597.1	631.5	676.3	756.1	869.0
52.5°	510.1	510.3	515.1	517.3	526.2	538.0	554.9	578.7	619.3	681.7	774.5
55°	452.6	455.9	458.6	462.5	470.5	479.1	492.2	508.1	539.8	586.6	655.2
57.5°	398.6	399.6	402.3	409.7	414.7	422.7	435.2	449.6	470.2	504.9	556.5
60°	361.6	361.6	366.9	370.1	376.8	384.7	394.6	408.5	426.9	455.3	496.9
62.5°	327.8	327.3	329.4	334.8	339.8	347.2	357.1	368.9	386.2	411.5	445.7
65°	278.4	277.2	281.1	282.4	287.7	295.0	302.9	315.4	329.2	347.8	378.1
67.5°	230.9	232.6	234.6	237.1	240.0	247.7	253.0	261.8	273.5	288.9	309.4
70°	204.6	204.6	204.6	206.6	210.5	214.5	219.7	227.0	238.2	251.4	269.8
72.5°	175.0	177.1	179.2	178.1	183.0	185.4	191.7	195.9	206.6	215.0	231.4
75°	137.2	137.2	137.2	140.5	142.5	144.5	148.4	152.4	157.7	168.2	176.8
77.5°	102.4	102.1	102.8	103.6	105.7	108.1	109.3	112.8	117.7	122.6	129.8
80°	79.2	80.5	81.2	82.5	82.5	83.8	84.5	89.1	92.4	95.7	100.3
82.5°	61.2	61.5	61.6	61.9	62.4	63.2	64.9	66.4	67.6	70.3	73.9
85°	35.6	35.0	35.0	36.2	35.6	35.6	36.9	38.2	38.2	38.9	40.9
87.5°	16.4	16.4	16.9	16.4	16.3	16.9	16.9	16.4	17.0	17.5	17.7
90°	13.3	13.2	13.1	13.0	12.9	13.0	13.2	13.3	13.5	13.7	11.7
92.5°	12.7	12.7	12.6	12.6	12.6	12.6	12.5	12.5	12.4	12.4	12.0
95°	24.2	24.4	24.5	24.7	24.9	25.0	25.0	25.0	25.0	25.0	24.8
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.7
100°	53.5	53.6	53.6	53.7	53.8	53.8	53.8	53.8	53.8	53.8	53.6
102.5°	66.6	66.6	66.7	66.8	66.9	66.9	66.8	66.7	66.7	66.6	66.3
105°	86.6	86.6	86.6	86.6	86.6	86.5	86.4	86.2	86.0	85.8	85.7
107.5°	105.5	105.9	106.2	106.7	107.1	107.3	107.2	107.1	107.0	106.9	106.9
110°	120.1	120.4	120.6	120.9	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.2	134.4	134.6	134.7	134.9	135.2	135.3	135.6	135.8	136.0	136.0
115°	156.0	156.3	156.5	156.8	157.0	157.2	157.3	157.4	157.5	157.6	157.7
117.5°	176.8	177.1	177.4	177.6	177.9	178.1	178.3	178.6	178.7	179.0	179.4
120°	191.6	191.8	192.1	192.3	192.6	192.7	192.7	192.7	192.7	192.7	193.4
122.5°	205.9	206.0	206.3	206.5	206.6	206.8	207.1	207.2	207.5	207.7	208.2
125°	227.8	227.9	228.0	228.1	228.2	228.3	228.6	228.9	229.1	229.4	229.6
127.5°	247.8	248.1	248.3	248.6	248.9	249.2	249.5	249.8	250.1	250.5	250.7
130°	262.2	262.5	262.9	263.2	263.6	263.8	264.0	264.2	264.3	264.5	264.7
132.5°	275.9	276.1	276.4	276.7	277.0	277.3	277.7	278.1	278.4	278.8	278.8
135°	297.2	297.5	297.7	298.0	298.3	298.4	298.5	298.6	298.7	298.8	298.6
137.5°	316.6	316.9	317.3	317.6	318.0	318.2	318.2	318.3	318.4	318.5	318.2
140°	330.0	330.4	330.7	331.1	331.4	331.6	331.6	331.6	331.6	331.6	331.1
142.5°	342.2	342.5	342.9	343.2	343.5	343.7	343.6	343.5	343.5	343.5	343.1
145°	360.4	360.8	361.1	361.4	361.8	362.0	361.9	361.8	361.7	361.6	361.1
147.5°	376.8	377.0	377.4	377.7	378.1	378.2	378.0	377.7	377.5	377.4	377.0
150°	387.4	387.6	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4	387.0
152.5°	397.4	397.7	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4	396.9
155°	410.8	411.0	411.3	411.6	411.8	411.7	411.3	410.9	410.4	410.0	409.7
157.5°	422.3	422.8	423.1	423.5	424.0	423.9	423.3	422.7	422.1	421.5	421.4
160°	429.5	429.8	430.2	430.5	430.8	430.8	430.2	429.7	429.2	428.7	428.6
162.5°	435.8	436.1	436.5	437.0	437.4	437.3	436.7	436.1	435.5	435.0	434.9
165°	443.9	444.4	444.8	445.2	445.7	445.6	445.0	444.4	443.8	443.2	443.2
167.5°	450.6	451.1	451.5	451.9	452.5	452.4	451.8	451.2	450.6	450.0	450.0
170°	454.1	454.6	455.1	455.6	456.2	456.1	455.5	454.9	454.3	453.7	453.7
172.5°	456.8	457.4	457.9	458.4	458.9	458.9	458.3	457.7	457.1	456.5	456.6
175°	459.9	460.5	461.0	461.5	462.0	461.9	461.3	460.7	460.1	459.5	459.7
177.5°	461.3	461.8	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3	461.4
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1761.8	1757.6	1754.9	1745.4	1736.9	1728.5	1725.9	1726.9	1715.3	1704.2	1699.4
5°	1830.4	1817.1	1804.7	1786.8	1765.7	1742.6	1730.7	1721.5	1698.4	1673.4	1658.8
7.5°	1891.9	1873.0	1848.8	1815.3	1784.6	1748.3	1725.2	1704.7	1670.9	1635.6	1613.9
10°	1929.3	1903.6	1872.6	1831.7	1794.1	1749.9	1718.8	1687.8	1648.2	1606.0	1579.6
12.5°	1961.5	1926.8	1896.4	1843.8	1799.3	1744.0	1707.3	1663.5	1621.9	1571.7	1545.8
15°	2038.2	1974.2	1916.2	1856.7	1802.0	1724.8	1683.9	1625.1	1570.4	1508.4	1478.7
17.5°	2097.5	2025.5	1934.1	1858.6	1794.8	1709.3	1649.2	1578.8	1514.1	1443.2	1402.8
20°	2131.2	2048.7	1950.4	1860.7	1784.2	1686.5	1621.2	1549.3	1473.4	1393.5	1350.0
22.5°	2151.3	2064.6	1967.4	1852.8	1763.1	1668.0	1585.8	1507.0	1430.1	1343.9	1298.3
25°	2157.7	2078.5	1975.6	1846.2	1736.6	1629.1	1530.2	1453.6	1360.6	1280.0	1213.4
27.5°	2126.2	2069.5	1970.5	1833.8	1706.2	1580.5	1470.1	1383.4	1285.2	1197.8	1130.8
30°	2087.7	2054.7	1958.3	1821.1	1681.9	1546.6	1425.2	1326.9	1229.2	1140.8	1072.2
32.5°	2028.1	2020.9	1936.2	1803.2	1656.0	1503.9	1378.3	1278.8	1170.7	1083.8	1018.4
35°	1910.9	1942.5	1889.1	1763.1	1607.3	1443.0	1307.1	1193.6	1081.5	998.3	936.9
37.5°	1753.9	1832.5	1818.5	1704.3	1541.6	1376.8	1226.8	1108.1	1001.3	917.3	857.1
40°	1645.6	1745.9	1760.4	1659.5	1495.2	1325.6	1166.6	1048.4	944.2	867.7	806.9
42.5°	1529.5	1646.7	1686.5	1605.6	1444.5	1271.8	1112.8	990.4	887.2	812.8	759.0
45°	1334.8	1489.9	1561.9	1515.6	1359.9	1183.1	1019.4	895.4	801.7	731.8	690.2
47.5°	1152.9	1322.3	1419.0	1402.7	1265.8	1090.7	928.9	809.9	718.7	662.9	625.7
50°	1024.1	1198.3	1315.0	1320.3	1198.3	1024.7	862.4	750.2	666.4	614.3	583.9
52.5°	912.1	1078.4	1205.7	1233.7	1122.7	956.1	802.7	691.1	617.3	569.5	542.3
55°	766.0	906.6	1047.8	1099.2	1010.2	851.9	710.0	611.7	542.3	509.4	485.6
57.5°	636.9	754.1	884.4	941.3	886.4	750.9	617.9	532.4	476.3	447.4	429.1
60°	568.8	661.2	777.3	845.2	797.7	677.0	560.9	479.7	433.5	407.8	390.6
62.5°	505.4	587.3	685.4	747.6	721.7	607.9	503.9	432.2	392.4	368.2	355.8
65°	417.0	481.6	557.6	614.9	597.8	511.3	426.3	364.9	333.2	314.1	304.2
67.5°	343.4	390.1	442.7	493.0	479.1	417.9	349.6	301.8	278.2	261.7	255.7
70°	297.0	332.5	379.4	419.7	408.5	358.3	304.2	263.3	242.8	228.9	223.0
72.5°	252.6	281.9	317.6	350.5	342.9	301.3	256.1	225.2	209.6	196.7	191.9
75°	190.7	213.1	234.9	256.7	254.7	222.4	196.0	172.2	159.7	149.8	147.8
77.5°	140.8	153.3	168.2	181.1	177.5	159.0	138.3	124.7	115.5	108.8	107.8
80°	107.5	114.8	125.4	134.6	130.0	122.1	105.6	95.7	89.1	82.5	79.8
82.5°	78.0	85.2	91.6	96.6	93.1	85.7	75.5	68.8	64.8	60.3	59.2
85°	40.9	44.9	47.5	48.8	47.5	42.9	38.2	35.6	32.4	30.4	29.7
87.5°	17.8	17.4	17.0	17.8	16.0	15.8	13.5	11.7	11.4	11.0	10.2
90°	9.8	7.9	6.0	4.6	3.5	2.5	1.5	0.4	1.5	2.5	3.5
92.5°	11.5	11.0	10.6	10.0	9.2	8.4	7.7	7.0	7.7	8.4	9.2
95°	24.6	24.5	24.3	23.8	22.9	22.0	21.2	20.3	21.2	22.0	22.9
97.5°	41.3	41.0	40.6	40.1	39.3	38.6	37.8	37.0	37.8	38.6	39.3
100°	53.3	53.0	52.8	52.3	51.7	50.9	50.2	49.5	50.2	50.9	51.7
102.5°	66.0	65.6	65.3	64.8	64.3	63.7	63.2	62.7	63.2	63.7	64.3
105°	85.5	85.3	85.2	84.9	84.6	84.4	84.1	83.9	84.1	84.4	84.6
107.5°	106.9	106.9	106.9	106.8	106.4	106.0	105.6	105.2	105.6	106.0	106.4
110°	121.3	121.3	121.3	121.1	120.5	120.0	119.5	119.0	119.5	120.0	120.5



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	136.1	136.2	136.3	136.0	135.5	135.0	134.5	134.0	134.5	135.0	135.5
115°	157.9	158.1	158.3	158.1	157.6	157.0	156.5	156.0	156.5	157.0	157.6
117.5°	179.9	180.5	180.9	180.8	180.1	179.4	178.7	178.1	178.7	179.4	180.1
120°	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	193.4	194.1	194.8
122.5°	208.6	209.1	209.7	209.5	208.6	207.8	207.0	206.1	207.0	207.8	208.6
125°	229.9	230.1	230.4	230.1	229.4	228.6	227.8	227.0	227.8	228.6	229.4
127.5°	251.1	251.4	251.7	251.3	250.4	249.3	248.4	247.4	248.4	249.3	250.4
130°	264.8	265.0	265.2	264.7	263.6	262.4	261.3	260.2	261.3	262.4	263.6
132.5°	278.8	278.7	278.7	278.2	277.3	276.4	275.4	274.6	275.4	276.4	277.3
135°	298.4	298.3	298.1	297.6	296.6	295.7	294.7	293.8	294.7	295.7	296.6
137.5°	318.1	317.8	317.5	317.0	316.2	315.5	314.7	313.9	314.7	315.5	316.2
140°	330.7	330.3	329.8	329.2	328.5	327.7	326.9	326.1	326.9	327.7	328.5
142.5°	342.9	342.5	342.2	341.7	341.0	340.2	339.4	338.6	339.4	340.2	341.0
145°	360.6	360.1	359.6	359.0	358.3	357.7	357.1	356.5	357.1	357.7	358.3
147.5°	376.7	376.3	376.0	375.5	374.7	374.0	373.2	372.6	373.2	374.0	374.7
150°	386.7	386.3	386.0	385.6	385.0	384.5	384.0	383.5	384.0	384.5	385.0
152.5°	396.5	396.1	395.7	395.2	394.7	394.2	393.6	393.1	393.6	394.2	394.7
155°	409.5	409.2	409.0	408.7	408.5	408.1	407.9	407.6	407.9	408.1	408.5
157.5°	421.2	421.0	420.9	420.8	420.6	420.4	420.3	420.1	420.3	420.4	420.6
160°	428.5	428.4	428.3	428.3	428.1	427.9	427.7	427.6	427.7	427.9	428.1
162.5°	434.8	434.7	434.6	434.5	434.5	434.5	434.5	434.4	434.5	434.5	434.5
165°	443.2	443.2	443.2	443.2	443.2	443.3	443.4	443.5	443.4	443.3	443.2
167.5°	450.0	450.0	450.0	450.1	450.4	450.6	450.9	451.2	450.9	450.6	450.4
170°	453.8	453.9	454.0	454.2	454.4	454.7	455.0	455.2	455.0	454.7	454.4
172.5°	456.7	456.8	456.8	457.0	457.3	457.5	457.8	458.1	457.8	457.5	457.3
175°	459.9	460.0	460.2	460.5	460.7	461.0	461.2	461.5	461.2	461.0	460.7
177.5°	461.6	461.8	461.8	462.0	462.3	462.4	462.7	462.9	462.7	462.4	462.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1694.2	1691.0	1679.9	1674.1	1664.7	1655.6	1649.8	1652.5	1654.6	1653.6	1651.9
5°	1645.6	1633.1	1613.9	1597.4	1585.5	1563.8	1554.5	1550.0	1546.0	1541.4	1536.7
7.5°	1587.8	1568.1	1540.6	1517.1	1494.9	1467.8	1452.4	1443.2	1433.7	1423.2	1414.0
10°	1546.6	1518.9	1489.9	1456.9	1430.6	1406.1	1384.3	1369.8	1356.6	1344.1	1334.8
12.5°	1503.4	1471.4	1435.5	1390.4	1361.3	1326.4	1323.1	1297.5	1276.9	1269.1	1258.3
15°	1434.4	1389.6	1344.1	1290.6	1267.6	1235.9	1216.1	1196.3	1178.5	1165.9	1162.6
17.5°	1356.2	1298.1	1252.8	1214.4	1176.6	1144.2	1125.9	1110.1	1095.5	1078.7	1076.4
20°	1296.6	1246.4	1197.0	1163.3	1124.4	1091.3	1068.9	1053.1	1040.5	1030.6	1022.1
22.5°	1240.1	1185.2	1139.9	1103.1	1064.7	1038.0	1020.4	1005.0	994.6	983.7	975.6
25°	1149.4	1106.6	1057.0	1015.5	983.8	966.6	952.1	938.9	932.4	925.1	915.8
27.5°	1070.1	1022.4	976.1	943.9	916.1	901.0	890.6	881.7	875.5	871.2	866.0
30°	1014.2	966.0	929.7	898.0	874.9	859.8	853.2	847.9	840.6	838.0	835.3
32.5°	960.3	916.9	885.9	858.4	836.4	826.5	820.4	815.7	810.0	807.4	802.1
35°	884.2	847.9	817.5	802.4	784.5	775.9	771.4	764.7	759.5	756.8	756.1
37.5°	812.5	781.0	761.0	741.5	734.0	728.8	722.4	717.9	716.4	715.9	715.2
40°	766.0	740.3	722.6	706.7	703.4	695.4	690.2	686.2	686.2	686.9	686.2
42.5°	723.8	700.8	685.0	671.3	667.4	662.7	657.5	657.2	658.2	660.5	658.2
45°	659.9	643.3	632.1	625.5	618.3	613.6	612.9	614.9	615.6	616.3	618.3
47.5°	601.0	590.0	579.9	572.6	569.5	568.6	567.8	571.3	574.5	575.7	578.7
50°	566.1	553.6	545.0	540.4	537.8	536.4	537.8	541.7	544.3	547.7	549.7
52.5°	527.1	518.2	512.3	508.8	507.6	508.5	508.8	513.2	517.5	518.7	519.5
55°	473.1	466.5	465.2	459.3	461.8	461.2	464.5	467.2	471.1	475.1	475.7
57.5°	419.2	414.0	410.4	411.0	411.7	414.7	417.4	422.1	426.3	430.5	430.8
60°	383.4	380.7	378.8	378.8	380.0	384.0	387.3	391.9	394.6	397.2	399.2
62.5°	350.6	348.0	346.0	347.1	350.5	352.8	356.7	359.2	361.9	364.5	365.4
65°	298.9	297.6	299.5	300.9	301.5	304.9	309.4	311.4	314.1	315.4	320.0
67.5°	251.2	251.5	251.2	253.1	256.9	257.7	262.1	266.7	267.3	269.8	272.8
70°	219.0	220.4	221.7	223.0	226.4	227.6	230.9	232.9	235.6	237.5	239.5
72.5°	189.5	189.8	191.1	190.8	193.6	196.5	199.2	201.2	203.9	206.4	208.4
75°	145.9	145.9	147.1	147.8	151.1	154.4	153.8	155.1	157.7	160.3	161.7
77.5°	106.5	105.0	106.5	107.2	108.2	111.0	111.5	113.4	116.4	115.5	116.9
80°	81.2	79.2	81.2	81.8	81.8	85.2	85.2	86.4	88.4	86.4	88.4
82.5°	57.9	57.0	58.5	58.6	59.7	59.8	60.9	61.1	63.1	62.2	63.1
85°	29.0	28.4	29.0	28.4	29.0	29.7	29.7	29.0	29.0	30.4	28.4
87.5°	9.9	9.6	9.5	9.9	9.7	9.6	9.0	9.0	9.0	7.8	7.8
90°	4.6	6.0	7.9	9.8	11.7	13.7	13.5	13.3	13.2	13.0	12.9
92.5°	10.0	10.6	11.0	11.5	12.0	12.4	12.4	12.5	12.5	12.6	12.6
95°	23.8	24.3	24.5	24.6	24.8	25.0	25.0	25.0	25.0	25.0	24.9
97.5°	40.1	40.6	41.0	41.3	41.7	41.9	41.9	41.9	41.9	41.9	41.9
100°	52.3	52.8	53.0	53.3	53.6	53.8	53.8	53.8	53.8	53.8	53.8
102.5°	64.8	65.3	65.6	66.0	66.3	66.6	66.7	66.7	66.8	66.9	66.9
105°	84.9	85.2	85.3	85.5	85.7	85.8	86.0	86.2	86.4	86.5	86.6
107.5°	106.8	106.9	106.9	106.9	106.9	106.9	107.0	107.1	107.2	107.3	107.1
110°	121.1	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.1



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	136.0	136.3	136.2	136.1	136.0	136.0	135.8	135.6	135.3	135.2	134.9
115°	158.1	158.3	158.1	157.9	157.7	157.6	157.5	157.4	157.3	157.2	157.0
117.5°	180.8	180.9	180.5	179.9	179.4	179.0	178.7	178.6	178.3	178.1	177.9
120°	195.4	195.4	194.8	194.1	193.4	192.7	192.7	192.7	192.7	192.7	192.6
122.5°	209.5	209.7	209.1	208.6	208.2	207.7	207.5	207.2	207.1	206.8	206.6
125°	230.1	230.4	230.1	229.9	229.6	229.4	229.1	228.9	228.6	228.3	228.2
127.5°	251.3	251.7	251.4	251.1	250.7	250.5	250.1	249.8	249.5	249.2	248.9
130°	264.7	265.2	265.0	264.8	264.7	264.5	264.3	264.2	264.0	263.8	263.6
132.5°	278.2	278.7	278.7	278.8	278.8	278.8	278.4	278.1	277.7	277.3	277.0
135°	297.6	298.1	298.3	298.4	298.6	298.8	298.7	298.6	298.5	298.4	298.3
137.5°	317.0	317.5	317.8	318.1	318.2	318.5	318.4	318.3	318.2	318.2	318.0
140°	329.2	329.8	330.3	330.7	331.1	331.6	331.6	331.6	331.6	331.6	331.4
142.5°	341.7	342.2	342.5	342.9	343.1	343.5	343.5	343.5	343.6	343.7	343.5
145°	359.0	359.6	360.1	360.6	361.1	361.6	361.7	361.8	361.9	362.0	361.8
147.5°	375.5	376.0	376.3	376.7	377.0	377.4	377.5	377.7	378.0	378.2	378.1
150°	385.6	386.0	386.3	386.7	387.0	387.4	387.6	387.9	388.1	388.4	388.4
152.5°	395.2	395.7	396.1	396.5	396.9	397.4	397.7	398.0	398.3	398.6	398.6
155°	408.7	409.0	409.2	409.5	409.7	410.0	410.4	410.9	411.3	411.7	411.8
157.5°	420.8	420.9	421.0	421.2	421.4	421.5	422.1	422.7	423.3	423.9	424.0
160°	428.3	428.3	428.4	428.5	428.6	428.7	429.2	429.7	430.2	430.8	430.8
162.5°	434.5	434.6	434.7	434.8	434.9	435.0	435.5	436.1	436.7	437.3	437.4
165°	443.2	443.2	443.2	443.2	443.2	443.2	443.8	444.4	445.0	445.6	445.7
167.5°	450.1	450.0	450.0	450.0	450.0	450.0	450.6	451.2	451.8	452.4	452.5
170°	454.2	454.0	453.9	453.8	453.7	453.7	454.3	454.9	455.5	456.1	456.2
172.5°	457.0	456.8	456.8	456.7	456.6	456.5	457.1	457.7	458.3	458.9	458.9
175°	460.5	460.2	460.0	459.9	459.7	459.5	460.1	460.7	461.3	461.9	462.0
177.5°	462.0	461.8	461.8	461.6	461.4	461.3	461.8	462.2	462.5	463.0	463.0
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1646.7	1645.6	1645.6	1640.9	1645.6	1645.6	1646.7	1651.9	1653.6	1654.6	1652.5
5°	1527.5	1525.5	1522.2	1525.5	1522.2	1525.5	1527.5	1536.7	1541.4	1546.0	1550.0
7.5°	1409.6	1401.7	1400.6	1392.8	1400.6	1401.7	1409.6	1414.0	1423.2	1433.7	1443.2
10°	1323.6	1318.4	1317.7	1305.1	1317.7	1318.4	1323.6	1334.8	1344.1	1356.6	1369.8
12.5°	1258.2	1245.5	1248.0	1240.7	1248.0	1245.5	1258.2	1258.3	1269.1	1276.9	1297.5
15°	1144.8	1144.8	1142.2	1130.9	1142.2	1144.8	1144.8	1162.6	1165.9	1178.5	1196.3
17.5°	1063.4	1062.0	1055.8	1058.9	1055.8	1062.0	1063.4	1076.4	1078.7	1095.5	1110.1
20°	1014.8	1010.9	1003.0	1003.0	1003.0	1010.9	1014.8	1022.1	1030.6	1040.5	1053.1
22.5°	968.9	968.6	960.2	962.9	960.2	968.6	968.9	975.6	983.7	994.6	1005.0
25°	915.2	909.9	905.9	907.9	905.9	909.9	915.2	915.8	925.1	932.4	938.9
27.5°	864.3	861.3	861.1	855.7	861.1	861.3	864.3	866.0	871.2	875.5	881.7
30°	834.7	828.1	829.4	826.1	829.4	828.1	834.7	835.3	838.0	840.6	847.9
32.5°	800.9	798.5	797.2	794.4	797.2	798.5	800.9	802.1	807.4	810.0	815.7
35°	754.8	755.5	752.2	753.5	752.2	755.5	754.8	756.1	756.8	759.5	764.7
37.5°	714.6	716.7	715.1	715.5	715.1	716.7	714.6	715.2	715.9	716.4	717.9
40°	688.2	688.2	688.2	690.2	688.2	688.2	688.2	686.2	686.9	686.2	686.2
42.5°	662.9	661.9	660.7	660.6	660.7	661.9	662.9	658.2	660.5	658.2	657.2
45°	619.6	621.6	622.2	618.9	622.2	621.6	619.6	618.3	616.3	615.6	614.9
47.5°	580.4	580.7	580.4	583.3	580.4	580.7	580.4	578.7	575.7	574.5	571.3
50°	552.9	551.6	552.9	551.6	552.9	551.6	552.9	549.7	547.7	544.3	541.7
52.5°	523.9	524.2	523.4	523.1	523.4	524.2	523.9	519.5	518.7	517.5	513.2
55°	478.4	479.7	479.1	479.1	479.1	479.7	478.4	475.7	475.1	471.1	467.2
57.5°	431.3	432.5	433.3	430.5	433.3	432.5	431.3	430.8	430.5	426.3	422.1
60°	398.6	401.8	401.1	399.8	401.1	401.8	398.6	399.2	397.2	394.6	391.9
62.5°	368.4	369.6	369.5	369.3	369.5	369.6	368.4	365.4	364.5	361.9	359.2
65°	322.0	323.3	321.3	323.3	321.3	323.3	322.0	320.0	315.4	314.1	311.4
67.5°	272.0	272.4	273.8	274.7	273.8	272.4	272.0	272.8	269.8	267.3	266.7
70°	240.8	240.2	242.2	244.2	242.2	240.2	240.8	239.5	237.5	235.6	232.9
72.5°	208.1	209.6	208.9	210.3	208.9	209.6	208.1	208.4	206.4	203.9	201.2
75°	160.3	162.3	161.7	163.7	161.7	162.3	160.3	161.7	160.3	157.7	155.1
77.5°	115.9	116.1	115.9	116.9	115.9	116.1	115.9	116.9	115.5	116.4	113.4
80°	88.4	87.1	85.8	88.4	85.8	87.1	88.4	88.4	86.4	88.4	86.4
82.5°	61.5	62.3	61.0	61.0	61.0	62.3	61.5	63.1	62.2	63.1	61.1
85°	28.4	27.7	26.4	26.4	26.4	27.7	28.4	28.4	30.4	29.0	29.0
87.5°	7.9	7.4	7.4	6.9	7.4	7.4	7.9	7.8	7.8	9.0	9.0
90°	13.0	13.1	13.2	13.3	13.2	13.1	13.0	12.9	13.0	13.2	13.3
92.5°	12.6	12.6	12.7	12.7	12.7	12.6	12.6	12.6	12.6	12.5	12.5
95°	24.7	24.5	24.4	24.2	24.4	24.5	24.7	24.9	25.0	25.0	25.0
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.7	53.6	53.6	53.5	53.6	53.6	53.7	53.8	53.8	53.8	53.8
102.5°	66.8	66.7	66.6	66.6	66.6	66.7	66.8	66.9	66.9	66.8	66.7
105°	86.6	86.6	86.6	86.6	86.6	86.6	86.6	86.6	86.5	86.4	86.2
107.5°	106.7	106.2	105.9	105.5	105.9	106.2	106.7	107.1	107.3	107.2	107.1
110°	120.9	120.6	120.4	120.1	120.4	120.6	120.9	121.1	121.3	121.3	121.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	134.7	134.6	134.4	134.2	134.4	134.6	134.7	134.9	135.2	135.3	135.6
115°	156.8	156.5	156.3	156.0	156.3	156.5	156.8	157.0	157.2	157.3	157.4
117.5°	177.6	177.4	177.1	176.8	177.1	177.4	177.6	177.9	178.1	178.3	178.6
120°	192.3	192.1	191.8	191.6	191.8	192.1	192.3	192.6	192.7	192.7	192.7
122.5°	206.5	206.3	206.0	205.9	206.0	206.3	206.5	206.6	206.8	207.1	207.2
125°	228.1	228.0	227.9	227.8	227.9	228.0	228.1	228.2	228.3	228.6	228.9
127.5°	248.6	248.3	248.1	247.8	248.1	248.3	248.6	248.9	249.2	249.5	249.8
130°	263.2	262.9	262.5	262.2	262.5	262.9	263.2	263.6	263.8	264.0	264.2
132.5°	276.7	276.4	276.1	275.9	276.1	276.4	276.7	277.0	277.3	277.7	278.1
135°	298.0	297.7	297.5	297.2	297.5	297.7	298.0	298.3	298.4	298.5	298.6
137.5°	317.6	317.3	316.9	316.6	316.9	317.3	317.6	318.0	318.2	318.2	318.3
140°	331.1	330.7	330.4	330.0	330.4	330.7	331.1	331.4	331.6	331.6	331.6
142.5°	343.2	342.9	342.5	342.2	342.5	342.9	343.2	343.5	343.7	343.6	343.5
145°	361.4	361.1	360.8	360.4	360.8	361.1	361.4	361.8	362.0	361.9	361.8
147.5°	377.7	377.4	377.0	376.8	377.0	377.4	377.7	378.1	378.2	378.0	377.7
150°	388.1	387.9	387.6	387.4	387.6	387.9	388.1	388.4	388.4	388.1	387.9
152.5°	398.3	398.0	397.7	397.4	397.7	398.0	398.3	398.6	398.6	398.3	398.0
155°	411.6	411.3	411.0	410.8	411.0	411.3	411.6	411.8	411.7	411.3	410.9
157.5°	423.5	423.1	422.8	422.3	422.8	423.1	423.5	424.0	423.9	423.3	422.7
160°	430.5	430.2	429.8	429.5	429.8	430.2	430.5	430.8	430.8	430.2	429.7
162.5°	437.0	436.5	436.1	435.8	436.1	436.5	437.0	437.4	437.3	436.7	436.1
165°	445.2	444.8	444.4	443.9	444.4	444.8	445.2	445.7	445.6	445.0	444.4
167.5°	451.9	451.5	451.1	450.6	451.1	451.5	451.9	452.5	452.4	451.8	451.2
170°	455.6	455.1	454.6	454.1	454.6	455.1	455.6	456.2	456.1	455.5	454.9
172.5°	458.4	457.9	457.4	456.8	457.4	457.9	458.4	458.9	458.9	458.3	457.7
175°	461.5	461.0	460.5	459.9	460.5	461.0	461.5	462.0	461.9	461.3	460.7
177.5°	462.5	462.2	461.8	461.3	461.8	462.2	462.5	463.0	463.0	462.5	462.2
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1649.8	1655.6	1664.7	1674.1	1679.9	1691.0	1694.2	1699.4	1704.2	1715.3	1726.9
5°	1554.5	1563.8	1585.5	1597.4	1613.9	1633.1	1645.6	1658.8	1673.4	1698.4	1721.5
7.5°	1452.4	1467.8	1494.9	1517.1	1540.6	1568.1	1587.8	1613.9	1635.6	1670.9	1704.7
10°	1384.3	1406.1	1430.6	1456.9	1489.9	1518.9	1546.6	1579.6	1606.0	1648.2	1687.8
12.5°	1323.1	1326.4	1361.3	1390.4	1435.5	1471.4	1503.4	1545.8	1571.7	1621.9	1663.5
15°	1216.1	1235.9	1267.6	1290.6	1344.1	1389.6	1434.4	1478.7	1508.4	1570.4	1625.1
17.5°	1125.9	1144.2	1176.6	1214.4	1252.8	1298.1	1356.2	1402.8	1443.2	1514.1	1578.8
20°	1068.9	1091.3	1124.4	1163.3	1197.0	1246.4	1296.6	1350.0	1393.5	1473.4	1549.3
22.5°	1020.4	1038.0	1064.7	1103.1	1139.9	1185.2	1240.1	1298.3	1343.9	1430.1	1507.0
25°	952.1	966.6	983.8	1015.5	1057.0	1106.6	1149.4	1213.4	1280.0	1360.6	1453.6
27.5°	890.6	901.0	916.1	943.9	976.1	1022.4	1070.1	1130.8	1197.8	1285.2	1383.4
30°	853.2	859.8	874.9	898.0	929.7	966.0	1014.2	1072.2	1140.8	1229.2	1326.9
32.5°	820.4	826.5	836.4	858.4	885.9	916.9	960.3	1018.4	1083.8	1170.7	1278.8
35°	771.4	775.9	784.5	802.4	817.5	847.9	884.2	936.9	998.3	1081.5	1193.6
37.5°	722.4	728.8	734.0	741.5	761.0	781.0	812.5	857.1	917.3	1001.3	1108.1
40°	690.2	695.4	703.4	706.7	722.6	740.3	766.0	806.9	867.7	944.2	1048.4
42.5°	657.5	662.7	667.4	671.3	685.0	700.8	723.8	759.0	812.8	887.2	990.4
45°	612.9	613.6	618.3	625.5	632.1	643.3	659.9	690.2	731.8	801.7	895.4
47.5°	567.8	568.6	569.5	572.6	579.9	590.0	601.0	625.7	662.9	718.7	809.9
50°	537.8	536.4	537.8	540.4	545.0	553.6	566.1	583.9	614.3	666.4	750.2
52.5°	508.8	508.5	507.6	508.8	512.3	518.2	527.1	542.3	569.5	617.3	691.1
55°	464.5	461.2	461.8	459.3	465.2	466.5	473.1	485.6	509.4	542.3	611.7
57.5°	417.4	414.7	411.7	411.0	410.4	414.0	419.2	429.1	447.4	476.3	532.4
60°	387.3	384.0	380.0	378.8	378.8	380.7	383.4	390.6	407.8	433.5	479.7
62.5°	356.7	352.8	350.5	347.1	346.0	348.0	350.6	355.8	368.2	392.4	432.2
65°	309.4	304.9	301.5	300.9	299.5	297.6	298.9	304.2	314.1	333.2	364.9
67.5°	262.1	257.7	256.9	253.1	251.2	251.5	251.2	255.7	261.7	278.2	301.8
70°	230.9	227.6	226.4	223.0	221.7	220.4	219.0	223.0	228.9	242.8	263.3
72.5°	199.2	196.5	193.6	190.8	191.1	189.8	189.5	191.9	196.7	209.6	225.2
75°	153.8	154.4	151.1	147.8	147.1	145.9	145.9	147.8	149.8	159.7	172.2
77.5°	111.5	111.0	108.2	107.2	106.5	105.0	106.5	107.8	108.8	115.5	124.7
80°	85.2	85.2	81.8	81.8	81.2	79.2	81.2	79.8	82.5	89.1	95.7
82.5°	60.9	59.8	59.7	58.6	58.5	57.0	57.9	59.2	60.3	64.8	68.8
85°	29.7	29.7	29.0	28.4	29.0	28.4	29.0	29.7	30.4	32.4	35.6
87.5°	9.0	9.6	9.7	9.9	9.5	9.6	9.9	10.2	11.0	11.4	11.7
90°	13.5	13.7	11.7	9.8	7.9	6.0	4.6	3.5	2.5	1.5	0.4
92.5°	12.4	12.4	12.0	11.5	11.0	10.6	10.0	9.2	8.4	7.7	7.0
95°	25.0	25.0	24.8	24.6	24.5	24.3	23.8	22.9	22.0	21.2	20.3
97.5°	41.9	41.9	41.7	41.3	41.0	40.6	40.1	39.3	38.6	37.8	37.0
100°	53.8	53.8	53.6	53.3	53.0	52.8	52.3	51.7	50.9	50.2	49.5
102.5°	66.7	66.6	66.3	66.0	65.6	65.3	64.8	64.3	63.7	63.2	62.7
105°	86.0	85.8	85.7	85.5	85.3	85.2	84.9	84.6	84.4	84.1	83.9
107.5°	107.0	106.9	106.9	106.9	106.9	106.9	106.8	106.4	106.0	105.6	105.2
110°	121.3	121.3	121.3	121.3	121.3	121.3	121.1	120.5	120.0	119.5	119.0



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	135.8	136.0	136.0	136.1	136.2	136.3	136.0	135.5	135.0	134.5	134.0
115°	157.5	157.6	157.7	157.9	158.1	158.3	158.1	157.6	157.0	156.5	156.0
117.5°	178.7	179.0	179.4	179.9	180.5	180.9	180.8	180.1	179.4	178.7	178.1
120°	192.7	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7
122.5°	207.5	207.7	208.2	208.6	209.1	209.7	209.5	208.6	207.8	207.0	206.1
125°	229.1	229.4	229.6	229.9	230.1	230.4	230.1	229.4	228.6	227.8	227.0
127.5°	250.1	250.5	250.7	251.1	251.4	251.7	251.3	250.4	249.3	248.4	247.4
130°	264.3	264.5	264.7	264.8	265.0	265.2	264.7	263.6	262.4	261.3	260.2
132.5°	278.4	278.8	278.8	278.8	278.7	278.7	278.2	277.3	276.4	275.4	274.6
135°	298.7	298.8	298.6	298.4	298.3	298.1	297.6	296.6	295.7	294.7	293.8
137.5°	318.4	318.5	318.2	318.1	317.8	317.5	317.0	316.2	315.5	314.7	313.9
140°	331.6	331.6	331.1	330.7	330.3	329.8	329.2	328.5	327.7	326.9	326.1
142.5°	343.5	343.5	343.1	342.9	342.5	342.2	341.7	341.0	340.2	339.4	338.6
145°	361.7	361.6	361.1	360.6	360.1	359.6	359.0	358.3	357.7	357.1	356.5
147.5°	377.5	377.4	377.0	376.7	376.3	376.0	375.5	374.7	374.0	373.2	372.6
150°	387.6	387.4	387.0	386.7	386.3	386.0	385.6	385.0	384.5	384.0	383.5
152.5°	397.7	397.4	396.9	396.5	396.1	395.7	395.2	394.7	394.2	393.6	393.1
155°	410.4	410.0	409.7	409.5	409.2	409.0	408.7	408.5	408.1	407.9	407.6
157.5°	422.1	421.5	421.4	421.2	421.0	420.9	420.8	420.6	420.4	420.3	420.1
160°	429.2	428.7	428.6	428.5	428.4	428.3	428.3	428.1	427.9	427.7	427.6
162.5°	435.5	435.0	434.9	434.8	434.7	434.6	434.5	434.5	434.5	434.5	434.4
165°	443.8	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.3	443.4	443.5
167.5°	450.6	450.0	450.0	450.0	450.0	450.0	450.1	450.4	450.6	450.9	451.2
170°	454.3	453.7	453.7	453.8	453.9	454.0	454.2	454.4	454.7	455.0	455.2
172.5°	457.1	456.5	456.6	456.7	456.8	456.8	457.0	457.3	457.5	457.8	458.1
175°	460.1	459.5	459.7	459.9	460.0	460.2	460.5	460.7	461.0	461.2	461.5
177.5°	461.8	461.3	461.4	461.6	461.8	461.8	462.0	462.3	462.4	462.7	462.9
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1725.9	1728.5	1736.9	1745.4	1754.9	1757.6	1761.8	1758.1	1757.0	1767.0	1774.4
5°	1730.7	1742.6	1765.7	1786.8	1804.7	1817.1	1830.4	1835.7	1845.6	1859.4	1876.5
7.5°	1725.2	1748.3	1784.6	1815.3	1848.8	1873.0	1891.9	1908.0	1927.5	1953.8	1982.4
10°	1718.8	1749.9	1794.1	1831.7	1872.6	1903.6	1929.3	1954.4	1983.5	2019.7	2057.4
12.5°	1707.3	1744.0	1799.3	1843.8	1896.4	1926.8	1961.5	2015.7	2046.8	2097.3	2150.3
15°	1683.9	1724.8	1802.0	1856.7	1916.2	1974.2	2038.2	2089.6	2141.1	2170.8	2245.4
17.5°	1649.2	1709.3	1794.8	1858.6	1934.1	2025.5	2097.5	2155.8	2215.2	2263.3	2300.7
20°	1621.2	1686.5	1784.2	1860.7	1950.4	2048.7	2131.2	2190.6	2242.1	2282.3	2305.4
22.5°	1585.8	1668.0	1763.1	1852.8	1967.4	2064.6	2151.3	2198.0	2241.0	2260.7	2269.5
25°	1530.2	1629.1	1736.6	1846.2	1975.6	2078.5	2157.7	2186.0	2198.6	2179.4	2147.8
27.5°	1470.1	1580.5	1706.2	1833.8	1970.5	2069.5	2126.2	2121.8	2100.5	2038.6	1989.1
30°	1425.2	1546.6	1681.9	1821.1	1958.3	2054.7	2087.7	2054.7	2006.6	1937.2	1866.6
32.5°	1378.3	1503.9	1656.0	1803.2	1936.2	2020.9	2028.1	1971.3	1896.8	1818.0	1729.9
35°	1307.1	1443.0	1607.3	1763.1	1889.1	1942.5	1910.9	1810.6	1722.2	1614.6	1494.5
37.5°	1226.8	1376.8	1541.6	1704.3	1818.5	1832.5	1753.9	1648.2	1523.5	1397.1	1255.8
40°	1166.6	1325.6	1495.2	1659.5	1760.4	1745.9	1645.6	1529.5	1381.0	1226.6	1095.3
42.5°	1112.8	1271.8	1444.5	1605.6	1686.5	1646.7	1529.5	1387.0	1227.4	1082.0	961.7
45°	1019.4	1183.1	1359.9	1515.6	1561.9	1489.9	1334.8	1176.5	1019.4	898.0	803.1
47.5°	928.9	1090.7	1265.8	1402.7	1419.0	1322.3	1152.9	989.9	854.9	756.0	689.0
50°	862.4	1024.7	1198.3	1320.3	1315.0	1198.3	1024.1	869.0	756.1	676.3	631.5
52.5°	802.7	956.1	1122.7	1233.7	1205.7	1078.4	912.1	774.5	681.7	619.3	578.7
55°	710.0	851.9	1010.2	1099.2	1047.8	906.6	766.0	655.2	586.6	539.8	508.1
57.5°	617.9	750.9	886.4	941.3	884.4	754.1	636.9	556.5	504.9	470.2	449.6
60°	560.9	677.0	797.7	845.2	777.3	661.2	568.8	496.9	455.3	426.9	408.5
62.5°	503.9	607.9	721.7	747.6	685.4	587.3	505.4	445.7	411.5	386.2	368.9
65°	426.3	511.3	597.8	614.9	557.6	481.6	417.0	378.1	347.8	329.2	315.4
67.5°	349.6	417.9	479.1	493.0	442.7	390.1	343.4	309.4	288.9	273.5	261.8
70°	304.2	358.3	408.5	419.7	379.4	332.5	297.0	269.8	251.4	238.2	227.0
72.5°	256.1	301.3	342.9	350.5	317.6	281.9	252.6	231.4	215.0	206.6	195.9
75°	196.0	222.4	254.7	256.7	234.9	213.1	190.7	176.8	168.2	157.7	152.4
77.5°	138.3	159.0	177.5	181.1	168.2	153.3	140.8	129.8	122.6	117.7	112.8
80°	105.6	122.1	130.0	134.6	125.4	114.8	107.5	100.3	95.7	92.4	89.1
82.5°	75.5	85.7	93.1	96.6	91.6	85.2	78.0	73.9	70.3	67.6	66.4
85°	38.2	42.9	47.5	48.8	47.5	44.9	40.9	40.9	38.9	38.2	38.2
87.5°	13.5	15.8	16.0	17.8	17.0	17.4	17.8	17.7	17.5	17.0	16.4
90°	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5	13.3
92.5°	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4	12.5
95°	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0	25.0
97.5°	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9	41.9
100°	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8	53.8
102.5°	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7	66.7
105°	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0	86.2
107.5°	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0	107.1
110°	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8	135.6
115°	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5	157.4
117.5°	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7	178.6
120°	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7	192.7
122.5°	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5	207.2
125°	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1	228.9
127.5°	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1	249.8
130°	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3	264.2
132.5°	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4	278.1
135°	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7	298.6
137.5°	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4	318.3
140°	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6	331.6
142.5°	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5	343.5
145°	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7	361.8
147.5°	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5	377.7
150°	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6	387.9
152.5°	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7	398.0
155°	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4	410.9
157.5°	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1	422.7
160°	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2	429.7
162.5°	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5	436.1
165°	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8	444.4
167.5°	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6	451.2
170°	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3	454.9
172.5°	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1	457.7
175°	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1	460.7
177.5°	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8	462.2
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8	1716.8
2.5°	1780.7	1788.1	1788.1	1789.2	1797.6	1796.6	1796.0
5°	1895.1	1906.3	1907.5	1919.4	1927.3	1924.7	1917.4
7.5°	2002.9	2023.7	2039.5	2048.4	2058.8	2065.3	2062.4
10°	2088.4	2118.7	2137.2	2149.7	2164.9	2176.1	2172.1
12.5°	2165.9	2202.1	2227.5	2248.9	2250.9	2265.3	2255.6
15°	2287.0	2325.2	2329.2	2345.0	2357.6	2356.2	2356.9
17.5°	2326.9	2339.3	2341.7	2342.1	2342.3	2337.6	2327.6
20°	2312.7	2308.1	2296.9	2288.3	2273.1	2271.1	2258.0
22.5°	2245.1	2230.5	2202.4	2183.8	2160.2	2154.0	2150.3
25°	2112.1	2079.7	2034.9	1992.0	1980.1	1957.1	1963.7
27.5°	1929.6	1879.2	1830.7	1795.8	1764.3	1729.7	1739.6
30°	1801.3	1744.6	1675.9	1623.2	1589.5	1556.5	1550.6
32.5°	1648.2	1565.1	1488.6	1442.1	1390.5	1369.7	1346.9
35°	1384.3	1303.1	1227.3	1161.9	1124.4	1095.3	1068.9
37.5°	1146.9	1053.5	992.2	939.4	912.1	895.5	899.7
40°	999.6	917.8	873.0	832.7	807.6	795.7	798.4
42.5°	880.4	819.1	782.1	754.6	736.9	730.3	728.8
45°	744.9	710.7	680.3	664.4	655.9	648.6	644.0
47.5°	652.6	624.6	607.4	598.1	590.6	583.2	583.0
50°	597.1	578.7	566.8	556.9	551.0	545.7	550.3
52.5°	554.9	538.0	526.2	517.3	515.1	510.3	510.1
55°	492.2	479.1	470.5	462.5	458.6	455.9	452.6
57.5°	435.2	422.7	414.7	409.7	402.3	399.6	398.6
60°	394.6	384.7	376.8	370.1	366.9	361.6	361.6
62.5°	357.1	347.2	339.8	334.8	329.4	327.3	327.8
65°	302.9	295.0	287.7	282.4	281.1	277.2	278.4
67.5°	253.0	247.7	240.0	237.1	234.6	232.6	230.9
70°	219.7	214.5	210.5	206.6	204.6	204.6	204.6
72.5°	191.7	185.4	183.0	178.1	179.2	177.1	175.0
75°	148.4	144.5	142.5	140.5	137.2	137.2	137.2
77.5°	109.3	108.1	105.7	103.6	102.8	102.1	102.4
80°	84.5	83.8	82.5	82.5	81.2	80.5	79.2
82.5°	64.9	63.2	62.4	61.9	61.6	61.5	61.2
85°	36.9	35.6	35.6	36.2	35.0	35.0	35.6
87.5°	16.9	16.9	16.3	16.4	16.9	16.4	16.4
90°	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.1	120.9	120.6	120.4	120.1



TEST NUMBER: P331586-935

CATALOG NUMBER: S122DIW-S1005D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)