

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331489-935

Luminaire Tested: **S122DIW-S290D1440U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331489-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D1440U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6086.4 lumens
Efficiency: N/A
Efficacy: 114.0 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot



— 0°-180° - - 45°-225° - - - 90°-270° - - - 135°-315°



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19				
1	91	87	83	80	80	77	74	71	58	56	54	40	39	38	24	24	23	16				
2	83	76	70	65	73	67	62	58	51	48	45	36	34	32	22	21	20	14				
3	76	67	60	55	66	59	54	49	45	41	38	32	29	27	19	18	17	12				
4	69	59	52	46	61	52	46	41	40	36	32	28	26	23	17	16	15	10				
5	63	53	45	39	56	47	40	35	36	31	28	25	22	20	16	14	13	9				
6	58	47	39	34	51	42	35	31	32	27	24	23	20	18	14	13	11	8				
7	54	42	35	30	47	38	31	27	29	24	21	21	18	16	13	11	10	7				
8	50	38	31	26	44	34	28	24	26	22	19	19	16	14	12	10	9	6				
9	46	35	28	23	41	31	25	21	24	20	17	17	14	12	11	9	8	6				
10	43	32	25	20	38	28	22	19	22	18	15	16	13	11	10	9	7	5				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	0.8
10°-20°	140.9	2.3
20°-30°	204.5	3.4
30°-40°	215.8	3.5
40°-50°	191.1	3.1
50°-60°	152.5	2.5
60°-70°	103.6	1.7
70°-80°	53.1	0.9
80°-90°	17.0	0.3
90°-100°	56.5	0.9
100°-110°	207.0	3.4
110°-120°	553.4	9.1
120°-130°	913.5	15.0
130°-140°	971.4	16.0
140°-150°	902.9	14.8
150°-160°	726.0	11.9
160°-170°	467.8	7.7
170°-180°	161.0	2.6
0°-30°	393.9	6.5
0°-40°	609.7	10.0
0°-60°	953.2	15.7
0°-90°	1127.0	18.5
90°-120°	816.8	13.4
90°-150°	3604.6	59.2
90°-180°	4959.0	81.5
0°-180°	6086.4	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	33	1	33	1	33	15
95°	53	80	53	80	53	49
105°	93	372	93	372	93	97
115°	100	704	100	704	100	251
125°	1047	996	1047	996	1047	906
135°	1272	1232	1272	1232	1272	981
145°	1451	1429	1451	1429	1451	907
155°	1575	1574	1575	1574	1575	727
165°	1654	1658	1654	1658	1654	467
175°	1686	1696	1686	1696	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	10.7	10.6	10.6	10.3	10.2	10.2	9.9	9.5	9.4	9.3	9.0
90°	33.1	32.5	31.9	31.4	30.9	30.0	28.6	27.2	25.8	24.5	22.3
92.5°	33.1	32.7	32.4	32.1	31.8	31.3	30.6	29.8	29.1	28.4	27.3
95°	52.7	53.0	53.2	53.5	53.7	53.2	51.8	50.5	49.1	47.8	45.9
97.5°	70.3	70.0	69.7	69.3	69.0	68.3	67.2	66.1	65.0	63.9	59.5
100°	82.1	81.5	80.9	80.4	79.9	78.5	76.4	74.1	72.0	69.8	65.2
102.5°	87.9	87.1	86.4	85.7	84.9	83.1	80.2	77.4	74.6	71.7	110.5
105°	93.1	92.0	90.9	89.8	88.7	86.7	83.7	80.7	77.7	74.7	149.0
107.5°	95.7	94.7	93.6	92.5	91.4	92.4	95.4	98.5	101.5	104.6	193.6
110°	96.8	95.7	94.5	93.5	92.4	105.5	132.7	159.9	187.1	214.3	292.9



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	97.7	96.9	96.0	95.1	94.2	143.4	242.7	342.0	441.3	540.5	559.9
115°	100.4	120.0	139.6	159.2	178.7	251.6	377.5	503.6	629.6	755.5	748.7
117.5°	410.0	474.3	538.7	603.1	667.5	715.0	745.5	775.9	806.4	836.9	832.2
120°	747.0	783.7	820.4	857.2	893.9	910.7	907.4	904.1	900.9	897.6	892.7
122.5°	932.1	939.3	946.4	953.5	960.6	963.2	961.3	959.3	957.3	955.4	950.0
125°	1047.0	1046.2	1045.3	1044.6	1043.7	1042.3	1040.4	1038.5	1036.6	1034.7	1029.6
127.5°	1119.5	1119.3	1119.1	1119.0	1118.9	1117.3	1114.6	1111.8	1109.1	1106.3	1102.4
130°	1164.5	1164.8	1165.1	1165.4	1165.6	1164.2	1161.3	1158.3	1155.3	1152.3	1149.3
132.5°	1208.6	1208.9	1209.2	1209.4	1209.7	1208.6	1206.0	1203.4	1200.9	1198.3	1195.3
135°	1272.3	1272.8	1273.4	1273.9	1274.5	1273.4	1270.7	1267.9	1265.2	1262.5	1260.1
137.5°	1330.3	1331.3	1332.2	1333.1	1334.0	1333.2	1330.5	1327.8	1325.2	1322.5	1319.7
140°	1366.6	1368.0	1369.3	1370.7	1372.0	1371.5	1369.1	1366.6	1364.2	1361.7	1358.7
142.5°	1401.9	1403.3	1404.5	1405.9	1407.3	1406.9	1404.6	1402.4	1400.2	1397.9	1394.5
145°	1451.1	1452.4	1453.8	1455.2	1456.6	1456.3	1454.3	1452.4	1450.5	1448.6	1444.0
147.5°	1494.4	1495.6	1496.8	1497.9	1499.0	1498.9	1497.5	1496.1	1494.6	1493.2	1488.7
150°	1520.9	1522.2	1523.6	1525.0	1526.3	1526.2	1524.6	1522.9	1521.3	1519.7	1515.3
152.5°	1543.4	1545.2	1547.0	1548.8	1550.6	1550.7	1549.0	1547.4	1545.8	1544.1	1540.0
155°	1574.8	1576.9	1579.2	1581.3	1583.5	1583.7	1582.1	1580.5	1578.8	1577.2	1574.0
157.5°	1603.4	1605.5	1607.7	1609.8	1611.9	1612.1	1610.2	1608.3	1606.5	1604.6	1602.3
160°	1620.1	1622.0	1623.8	1625.8	1627.7	1627.8	1626.2	1624.5	1622.9	1621.3	1619.6
162.5°	1633.8	1636.2	1638.5	1640.8	1643.1	1643.4	1641.6	1639.7	1637.9	1636.0	1634.6
165°	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3	1653.6
167.5°	1667.3	1669.8	1672.2	1674.7	1677.1	1677.4	1675.5	1673.6	1671.7	1669.8	1669.0
170°	1675.2	1677.7	1680.1	1682.6	1685.0	1685.2	1683.3	1681.4	1679.6	1677.7	1677.1
172.5°	1681.0	1683.5	1685.9	1688.4	1690.8	1691.1	1689.2	1687.3	1685.4	1683.5	1683.0
175°	1686.2	1688.9	1691.6	1694.4	1697.1	1697.5	1695.6	1693.7	1691.8	1689.9	1689.4
177.5°	1689.4	1691.3	1693.3	1695.2	1697.2	1697.5	1695.9	1694.4	1692.9	1691.3	1691.1
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	8.7	8.3	7.8	7.7	6.5	5.9	4.7	3.7	4.1	4.6	4.8
90°	20.1	18.0	15.8	13.2	10.2	7.2	4.2	1.2	4.2	7.2	10.2
92.5°	26.3	25.1	24.0	23.7	23.9	24.2	24.5	24.7	24.5	24.2	23.9
95°	43.9	42.0	40.1	43.7	52.7	61.6	70.6	79.6	70.6	61.6	52.7
97.5°	55.1	50.7	46.3	56.7	82.1	107.4	132.7	158.0	132.7	107.4	82.1
100°	60.5	55.9	51.3	67.6	104.9	142.2	179.4	216.7	179.4	142.2	104.9
102.5°	149.1	187.9	226.5	249.9	257.7	265.6	273.5	281.4	273.5	265.6	257.7
105°	223.3	297.6	371.9	404.9	396.7	388.6	380.4	372.3	380.4	388.6	396.7
107.5°	282.8	371.9	461.0	502.2	495.6	489.0	482.4	475.9	482.4	489.0	495.6
110°	371.6	450.2	528.8	565.3	559.6	553.9	548.2	542.5	548.2	553.9	559.6



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	579.4	598.8	618.2	625.4	620.4	615.3	610.2	605.2	610.2	615.3	620.4
115°	741.9	735.1	728.3	722.6	718.0	713.3	708.8	704.1	708.8	713.3	718.0
117.5°	827.5	822.8	818.1	813.2	808.0	802.9	797.7	792.6	797.7	802.9	808.0
120°	887.8	882.9	878.0	873.5	869.4	865.3	861.3	857.2	861.3	865.3	869.4
122.5°	944.7	939.4	934.1	929.3	925.0	920.7	916.4	912.1	916.4	920.7	925.0
125°	1024.4	1019.3	1014.1	1009.7	1006.2	1002.6	999.1	995.6	999.1	1002.6	1006.2
127.5°	1098.5	1094.7	1090.8	1086.9	1083.0	1079.1	1075.1	1071.3	1075.1	1079.1	1083.0
130°	1146.3	1143.3	1140.3	1136.7	1132.3	1127.9	1123.6	1119.2	1123.6	1127.9	1132.3
132.5°	1192.3	1189.4	1186.4	1183.0	1179.3	1175.6	1171.9	1168.2	1171.9	1175.6	1179.3
135°	1257.6	1255.2	1252.7	1249.3	1244.9	1240.6	1236.2	1231.9	1236.2	1240.6	1244.9
137.5°	1317.0	1314.1	1311.4	1308.5	1305.4	1302.4	1299.3	1296.3	1299.3	1302.4	1305.4
140°	1355.7	1352.7	1349.7	1347.1	1345.0	1342.8	1340.6	1338.4	1340.6	1342.8	1345.0
142.5°	1391.1	1387.7	1384.2	1381.6	1379.6	1377.6	1375.6	1373.7	1375.6	1377.6	1379.6
145°	1439.4	1434.8	1430.1	1428.0	1428.2	1428.5	1428.7	1429.1	1428.7	1428.5	1428.2
147.5°	1484.1	1479.5	1474.9	1473.2	1474.2	1475.2	1476.3	1477.3	1476.3	1475.2	1474.2
150°	1511.0	1506.6	1502.3	1501.0	1503.0	1504.9	1506.8	1508.6	1506.8	1504.9	1503.0
152.5°	1535.9	1531.7	1527.6	1526.6	1528.7	1530.9	1533.0	1535.1	1533.0	1530.9	1528.7
155°	1570.7	1567.5	1564.2	1563.7	1566.2	1568.7	1571.1	1573.6	1571.1	1568.7	1566.2
157.5°	1600.1	1597.8	1595.5	1595.4	1597.5	1599.6	1601.6	1603.7	1601.6	1599.6	1597.5
160°	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1619.6	1618.1	1616.4
162.5°	1633.1	1631.8	1630.3	1630.5	1632.1	1633.7	1635.4	1636.9	1635.4	1633.7	1632.1
165°	1652.7	1651.9	1651.1	1651.5	1653.1	1654.8	1656.4	1658.0	1656.4	1654.8	1653.1
167.5°	1668.3	1667.5	1666.7	1667.2	1668.8	1670.4	1672.1	1673.7	1672.1	1670.4	1668.8
170°	1676.5	1676.0	1675.4	1676.0	1677.7	1679.3	1680.9	1682.6	1680.9	1679.3	1677.7
172.5°	1682.4	1681.9	1681.4	1681.9	1683.5	1685.1	1686.8	1688.4	1686.8	1685.1	1683.5
175°	1688.8	1688.2	1687.7	1688.4	1690.3	1692.2	1694.1	1696.0	1694.1	1692.2	1690.3
177.5°	1690.9	1690.7	1690.5	1691.1	1692.6	1694.2	1695.7	1697.2	1695.7	1694.2	1692.6
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	5.3	5.7	5.9	6.4	6.6	7.0	7.1	7.3	7.6	7.6	7.7
90°	13.2	15.8	18.0	20.1	22.3	24.5	25.8	27.2	28.6	30.0	30.9
92.5°	23.7	24.0	25.1	26.3	27.3	28.4	29.1	29.8	30.6	31.3	31.8
95°	43.7	40.1	42.0	43.9	45.9	47.8	49.1	50.5	51.8	53.2	53.7
97.5°	56.7	46.3	50.7	55.1	59.5	63.9	65.0	66.1	67.2	68.3	69.0
100°	67.6	51.3	55.9	60.5	65.2	69.8	72.0	74.1	76.4	78.5	79.9
102.5°	249.9	226.5	187.9	149.1	110.5	71.7	74.6	77.4	80.2	83.1	84.9
105°	404.9	371.9	297.6	223.3	149.0	74.7	77.7	80.7	83.7	86.7	88.7
107.5°	502.2	461.0	371.9	282.8	193.6	104.6	101.5	98.5	95.4	92.4	91.4
110°	565.3	528.8	450.2	371.6	292.9	214.3	187.1	159.9	132.7	105.5	92.4



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	625.4	618.2	598.8	579.4	559.9	540.5	441.3	342.0	242.7	143.4	94.2
115°	722.6	728.3	735.1	741.9	748.7	755.5	629.6	503.6	377.5	251.6	178.7
117.5°	813.2	818.1	822.8	827.5	832.2	836.9	806.4	775.9	745.5	715.0	667.5
120°	873.5	878.0	882.9	887.8	892.7	897.6	900.9	904.1	907.4	910.7	893.9
122.5°	929.3	934.1	939.4	944.7	950.0	955.4	957.3	959.3	961.3	963.2	960.6
125°	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6	1038.5	1040.4	1042.3	1043.7
127.5°	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1	1111.8	1114.6	1117.3	1118.9
130°	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3	1158.3	1161.3	1164.2	1165.6
132.5°	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9	1203.4	1206.0	1208.6	1209.7
135°	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2	1267.9	1270.7	1273.4	1274.5
137.5°	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2	1327.8	1330.5	1333.2	1334.0
140°	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2	1366.6	1369.1	1371.5	1372.0
142.5°	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2	1402.4	1404.6	1406.9	1407.3
145°	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5	1452.4	1454.3	1456.3	1456.6
147.5°	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6	1496.1	1497.5	1498.9	1499.0
150°	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3	1522.9	1524.6	1526.2	1526.3
152.5°	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8	1547.4	1549.0	1550.7	1550.6
155°	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8	1580.5	1582.1	1583.7	1583.5
157.5°	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5	1608.3	1610.2	1612.1	1611.9
160°	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9	1624.5	1626.2	1627.8	1627.7
162.5°	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9	1639.7	1641.6	1643.4	1643.1
165°	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0
167.5°	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7	1673.6	1675.5	1677.4	1677.1
170°	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6	1681.4	1683.3	1685.2	1685.0
172.5°	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4	1687.3	1689.2	1691.1	1690.8
175°	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8	1693.7	1695.6	1697.5	1697.1
177.5°	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9	1694.4	1695.9	1697.5	1697.2
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	7.8	7.8	7.9	7.8	7.9	7.8	7.8	7.7	7.6	7.6	7.3
90°	31.4	31.9	32.5	33.1	32.5	31.9	31.4	30.9	30.0	28.6	27.2
92.5°	32.1	32.4	32.7	33.1	32.7	32.4	32.1	31.8	31.3	30.6	29.8
95°	53.5	53.2	53.0	52.7	53.0	53.2	53.5	53.7	53.2	51.8	50.5
97.5°	69.3	69.7	70.0	70.3	70.0	69.7	69.3	69.0	68.3	67.2	66.1
100°	80.4	80.9	81.5	82.1	81.5	80.9	80.4	79.9	78.5	76.4	74.1
102.5°	85.7	86.4	87.1	87.9	87.1	86.4	85.7	84.9	83.1	80.2	77.4
105°	89.8	90.9	92.0	93.1	92.0	90.9	89.8	88.7	86.7	83.7	80.7
107.5°	92.5	93.6	94.7	95.7	94.7	93.6	92.5	91.4	92.4	95.4	98.5
110°	93.5	94.5	95.7	96.8	95.7	94.5	93.5	92.4	105.5	132.7	159.9



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	95.1	96.0	96.9	97.7	96.9	96.0	95.1	94.2	143.4	242.7	342.0
115°	159.2	139.6	120.0	100.4	120.0	139.6	159.2	178.7	251.6	377.5	503.6
117.5°	603.1	538.7	474.3	410.0	474.3	538.7	603.1	667.5	715.0	745.5	775.9
120°	857.2	820.4	783.7	747.0	783.7	820.4	857.2	893.9	910.7	907.4	904.1
122.5°	953.5	946.4	939.3	932.1	939.3	946.4	953.5	960.6	963.2	961.3	959.3
125°	1044.6	1045.3	1046.2	1047.0	1046.2	1045.3	1044.6	1043.7	1042.3	1040.4	1038.5
127.5°	1119.0	1119.1	1119.3	1119.5	1119.3	1119.1	1119.0	1118.9	1117.3	1114.6	1111.8
130°	1165.4	1165.1	1164.8	1164.5	1164.8	1165.1	1165.4	1165.6	1164.2	1161.3	1158.3
132.5°	1209.4	1209.2	1208.9	1208.6	1208.9	1209.2	1209.4	1209.7	1208.6	1206.0	1203.4
135°	1273.9	1273.4	1272.8	1272.3	1272.8	1273.4	1273.9	1274.5	1273.4	1270.7	1267.9
137.5°	1333.1	1332.2	1331.3	1330.3	1331.3	1332.2	1333.1	1334.0	1333.2	1330.5	1327.8
140°	1370.7	1369.3	1368.0	1366.6	1368.0	1369.3	1370.7	1372.0	1371.5	1369.1	1366.6
142.5°	1405.9	1404.5	1403.3	1401.9	1403.3	1404.5	1405.9	1407.3	1406.9	1404.6	1402.4
145°	1455.2	1453.8	1452.4	1451.1	1452.4	1453.8	1455.2	1456.6	1456.3	1454.3	1452.4
147.5°	1497.9	1496.8	1495.6	1494.4	1495.6	1496.8	1497.9	1499.0	1498.9	1497.5	1496.1
150°	1525.0	1523.6	1522.2	1520.9	1522.2	1523.6	1525.0	1526.3	1526.2	1524.6	1522.9
152.5°	1548.8	1547.0	1545.2	1543.4	1545.2	1547.0	1548.8	1550.6	1550.7	1549.0	1547.4
155°	1581.3	1579.2	1576.9	1574.8	1576.9	1579.2	1581.3	1583.5	1583.7	1582.1	1580.5
157.5°	1609.8	1607.7	1605.5	1603.4	1605.5	1607.7	1609.8	1611.9	1612.1	1610.2	1608.3
160°	1625.8	1623.8	1622.0	1620.1	1622.0	1623.8	1625.8	1627.7	1627.8	1626.2	1624.5
162.5°	1640.8	1638.5	1636.2	1633.8	1636.2	1638.5	1640.8	1643.1	1643.4	1641.6	1639.7
165°	1660.1	1658.2	1656.3	1654.3	1656.3	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2
167.5°	1674.7	1672.2	1669.8	1667.3	1669.8	1672.2	1674.7	1677.1	1677.4	1675.5	1673.6
170°	1682.6	1680.1	1677.7	1675.2	1677.7	1680.1	1682.6	1685.0	1685.2	1683.3	1681.4
172.5°	1688.4	1685.9	1683.5	1681.0	1683.5	1685.9	1688.4	1690.8	1691.1	1689.2	1687.3
175°	1694.4	1691.6	1688.9	1686.2	1688.9	1691.6	1694.4	1697.1	1697.5	1695.6	1693.7
177.5°	1695.2	1693.3	1691.3	1689.4	1691.3	1693.3	1695.2	1697.2	1697.5	1695.9	1694.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	7.1	7.0	6.6	6.4	5.9	5.7	5.3	4.8	4.6	4.1	3.7
90°	25.8	24.5	22.3	20.1	18.0	15.8	13.2	10.2	7.2	4.2	1.2
92.5°	29.1	28.4	27.3	26.3	25.1	24.0	23.7	23.9	24.2	24.5	24.7
95°	49.1	47.8	45.9	43.9	42.0	40.1	43.7	52.7	61.6	70.6	79.6
97.5°	65.0	63.9	59.5	55.1	50.7	46.3	56.7	82.1	107.4	132.7	158.0
100°	72.0	69.8	65.2	60.5	55.9	51.3	67.6	104.9	142.2	179.4	216.7
102.5°	74.6	71.7	110.5	149.1	187.9	226.5	249.9	257.7	265.6	273.5	281.4
105°	77.7	74.7	149.0	223.3	297.6	371.9	404.9	396.7	388.6	380.4	372.3
107.5°	101.5	104.6	193.6	282.8	371.9	461.0	502.2	495.6	489.0	482.4	475.9
110°	187.1	214.3	292.9	371.6	450.2	528.8	565.3	559.6	553.9	548.2	542.5



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	441.3	540.5	559.9	579.4	598.8	618.2	625.4	620.4	615.3	610.2	605.2
115°	629.6	755.5	748.7	741.9	735.1	728.3	722.6	718.0	713.3	708.8	704.1
117.5°	806.4	836.9	832.2	827.5	822.8	818.1	813.2	808.0	802.9	797.7	792.6
120°	900.9	897.6	892.7	887.8	882.9	878.0	873.5	869.4	865.3	861.3	857.2
122.5°	957.3	955.4	950.0	944.7	939.4	934.1	929.3	925.0	920.7	916.4	912.1
125°	1036.6	1034.7	1029.6	1024.4	1019.3	1014.1	1009.7	1006.2	1002.6	999.1	995.6
127.5°	1109.1	1106.3	1102.4	1098.5	1094.7	1090.8	1086.9	1083.0	1079.1	1075.1	1071.3
130°	1155.3	1152.3	1149.3	1146.3	1143.3	1140.3	1136.7	1132.3	1127.9	1123.6	1119.2
132.5°	1200.9	1198.3	1195.3	1192.3	1189.4	1186.4	1183.0	1179.3	1175.6	1171.9	1168.2
135°	1265.2	1262.5	1260.1	1257.6	1255.2	1252.7	1249.3	1244.9	1240.6	1236.2	1231.9
137.5°	1325.2	1322.5	1319.7	1317.0	1314.1	1311.4	1308.5	1305.4	1302.4	1299.3	1296.3
140°	1364.2	1361.7	1358.7	1355.7	1352.7	1349.7	1347.1	1345.0	1342.8	1340.6	1338.4
142.5°	1400.2	1397.9	1394.5	1391.1	1387.7	1384.2	1381.6	1379.6	1377.6	1375.6	1373.7
145°	1450.5	1448.6	1444.0	1439.4	1434.8	1430.1	1428.0	1428.2	1428.5	1428.7	1429.1
147.5°	1494.6	1493.2	1488.7	1484.1	1479.5	1474.9	1473.2	1474.2	1475.2	1476.3	1477.3
150°	1521.3	1519.7	1515.3	1511.0	1506.6	1502.3	1501.0	1503.0	1504.9	1506.8	1508.6
152.5°	1545.8	1544.1	1540.0	1535.9	1531.7	1527.6	1526.6	1528.7	1530.9	1533.0	1535.1
155°	1578.8	1577.2	1574.0	1570.7	1567.5	1564.2	1563.7	1566.2	1568.7	1571.1	1573.6
157.5°	1606.5	1604.6	1602.3	1600.1	1597.8	1595.5	1595.4	1597.5	1599.6	1601.6	1603.7
160°	1622.9	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3
162.5°	1637.9	1636.0	1634.6	1633.1	1631.8	1630.3	1630.5	1632.1	1633.7	1635.4	1636.9
165°	1656.3	1654.3	1653.6	1652.7	1651.9	1651.1	1651.5	1653.1	1654.8	1656.4	1658.0
167.5°	1671.7	1669.8	1669.0	1668.3	1667.5	1666.7	1667.2	1668.8	1670.4	1672.1	1673.7
170°	1679.6	1677.7	1677.1	1676.5	1676.0	1675.4	1676.0	1677.7	1679.3	1680.9	1682.6
172.5°	1685.4	1683.5	1683.0	1682.4	1681.9	1681.4	1681.9	1683.5	1685.1	1686.8	1688.4
175°	1691.8	1689.9	1689.4	1688.8	1688.2	1687.7	1688.4	1690.3	1692.2	1694.1	1696.0
177.5°	1692.9	1691.3	1691.1	1690.9	1690.7	1690.5	1691.1	1692.6	1694.2	1695.7	1697.2
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.7	5.9	6.5	7.7	7.8	8.3	8.7	9.0	9.3	9.4	9.5
90°	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8	27.2
92.5°	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1	29.8
95°	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1	50.5
97.5°	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0	66.1
100°	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0	74.1
102.5°	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6	77.4
105°	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7	80.7
107.5°	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5	98.5
110°	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1	159.9



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3	342.0
115°	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6	503.6
117.5°	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4	775.9
120°	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9	904.1
122.5°	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3	959.3
125°	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6	1038.5
127.5°	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1	1111.8
130°	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3	1158.3
132.5°	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9	1203.4
135°	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2	1267.9
137.5°	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2	1327.8
140°	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2	1366.6
142.5°	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2	1402.4
145°	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5	1452.4
147.5°	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6	1496.1
150°	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3	1522.9
152.5°	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8	1547.4
155°	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8	1580.5
157.5°	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5	1608.3
160°	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9	1624.5
162.5°	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9	1639.7
165°	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3	1658.2
167.5°	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7	1673.6
170°	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6	1681.4
172.5°	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4	1687.3
175°	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8	1693.7
177.5°	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9	1694.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	9.9	10.2	10.2	10.3	10.6	10.6	10.7
90°	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	132.7	105.5	92.4	93.5	94.5	95.7	96.8



TEST NUMBER: P331489-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)