

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331493-935

Luminaire Tested: **S122DIW-S290D1440U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331493-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D1440U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 1440 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5998.5 lumens  
Efficiency: N/A  
Efficacy: 112.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 53.4  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	90	86	83	79	79	76	73	70	57	55	53	39	38	37	23	22	22	15
2	82	75	70	65	72	66	62	58	50	47	44	34	33	31	20	19	18	12
3	75	66	59	54	66	58	53	48	44	40	37	30	28	26	18	17	16	10
4	68	58	51	45	60	52	45	40	39	35	31	27	24	22	16	15	13	9
5	63	52	44	38	55	46	39	34	35	30	27	24	21	19	14	13	12	8
6	58	46	39	33	50	41	34	30	31	26	23	22	19	17	13	11	10	7
7	53	41	34	29	47	37	30	26	28	23	20	20	17	15	12	10	9	6
8	49	37	30	25	43	33	27	23	25	21	18	18	15	13	11	9	8	5
9	46	34	27	22	40	30	24	20	23	19	16	16	13	11	10	8	7	5
10	42	31	24	20	37	28	22	18	21	17	14	15	12	10	9	8	7	4

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	0.6
10°-20°	107.6	1.8
20°-30°	158.2	2.6
30°-40°	183.8	3.1
40°-50°	183.6	3.1
50°-60°	160.1	2.7
60°-70°	118.4	2.0
70°-80°	67.0	1.1
80°-90°	22.2	0.4
90°-100°	56.5	0.9
100°-110°	207.0	3.5
110°-120°	553.4	9.2
120°-130°	913.5	15.2
130°-140°	971.4	16.2
140°-150°	902.9	15.1
150°-160°	726.0	12.1
160°-170°	467.8	7.8
170°-180°	161.0	2.7
0°-30°	304.1	5.1
0°-40°	487.8	8.1
0°-60°	831.5	13.9
0°-90°	1039.0	17.3
90°-120°	816.8	13.6
90°-150°	3604.6	60.1
90°-180°	4959.0	82.7
0°-180°	5998.5	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	14	24	30	33	5
95°	80	42	48	53	53	97
105°	372	388	75	88	93	398
115°	704	725	756	215	100	693
125°	996	1012	1035	1043	1047	887
135°	1232	1251	1262	1274	1272	951
145°	1429	1429	1449	1456	1451	893
155°	1574	1564	1577	1584	1575	725
165°	1658	1651	1654	1662	1654	468
175°	1696	1688	1690	1697	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.9	6.4	6.8	7.2	7.7	8.1	8.4	8.7	9.0	9.3	9.4
90°	1.2	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8
92.5°	24.7	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1
95°	79.6	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1
97.5°	158.0	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0
100°	216.7	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0
102.5°	281.4	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6
105°	372.3	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7
107.5°	475.9	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5
110°	542.5	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1



TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	605.2	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3
115°	704.1	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6
117.5°	792.6	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4
120°	857.2	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9
122.5°	912.1	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3
125°	995.6	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6
127.5°	1071.3	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1
130°	1119.2	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3
132.5°	1168.2	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9
135°	1231.9	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2
137.5°	1296.3	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2
140°	1338.4	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2
142.5°	1373.7	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2
145°	1429.1	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5
147.5°	1477.3	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6
150°	1508.6	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3
152.5°	1535.1	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8
155°	1573.6	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8
157.5°	1603.7	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5
160°	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9
162.5°	1636.9	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9
165°	1658.0	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3
167.5°	1673.7	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7
170°	1682.6	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6
172.5°	1688.4	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4
175°	1696.0	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8
177.5°	1697.2	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	9.4	9.5	9.6	9.6	9.6	9.6	9.7	9.7
90°	27.2	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	29.8	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	50.5	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	66.1	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	74.1	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	77.4	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	80.7	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	98.5	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	159.9	132.7	105.5	92.4	93.5	94.5	95.7	96.8





TEST NUMBER: P331493-935

CATALOG NUMBER: S122DIW-S290D1440U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.0	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	503.6	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	775.9	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	904.1	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	959.3	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1038.5	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1111.8	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1158.3	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1203.4	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1267.9	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1327.8	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1366.6	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1402.4	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1452.4	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1496.1	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1522.9	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1547.4	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1580.5	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1608.3	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1624.5	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1639.7	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1673.6	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1681.4	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1687.3	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1693.7	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1694.4	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)