

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331465-935

Luminaire Tested: **S122DIW-S290D435U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331465-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D435U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2614.5 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	96	96	96	96	79	79	79	64	64	64	50	50	50	43
1	97	92	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	33	32	27
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	26	24	22	19
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	21	19	17
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	17	15
9	50	38	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	14	13

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	1.9
10°-20°	140.9	5.4
20°-30°	204.5	7.8
30°-40°	215.8	8.3
40°-50°	191.1	7.3
50°-60°	152.5	5.8
60°-70°	103.6	4.0
70°-80°	53.1	2.0
80°-90°	14.1	0.5
90°-100°	17.0	0.6
100°-110°	62.2	2.4
110°-120°	166.3	6.4
120°-130°	274.5	10.5
130°-140°	291.9	11.2
140°-150°	271.3	10.4
150°-160°	218.2	8.3
160°-170°	140.6	5.4
170°-180°	48.4	1.9
0°-30°	393.9	15.1
0°-40°	609.7	23.3
0°-60°	953.2	36.5
0°-90°	1124.0	43.0
90°-120°	245.5	9.4
90°-150°	1083.3	41.4
90°-180°	1490.0	57.0
0°-180°	2614.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	10	0	10	0	10	5
95°	16	24	16	24	16	15
105°	28	112	28	112	28	29
115°	30	212	30	212	30	76
125°	315	299	315	299	315	272
135°	382	370	382	370	382	295
145°	436	430	436	430	436	273
155°	473	473	473	473	473	218
165°	497	498	497	498	497	140
175°	507	510	507	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	6.0	6.0	6.1	5.9	5.9	6.0	5.9	5.7	5.8	5.9	5.9
90°	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2	7.7	7.3	6.7
92.5°	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0	8.8	8.5	8.2
95°	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2	14.7	14.4	13.8
97.5°	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9	19.5	19.2	17.9
100°	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3	21.6	21.0	19.5
102.5°	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2	22.4	21.5	33.2
105°	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3	23.3	22.5	44.8
107.5°	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6	30.5	31.4	58.2
110°	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0	56.2	64.4	88.0



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8	132.6	162.5	168.2
115°	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4	189.2	227.0	225.0
117.5°	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2	242.4	251.5	250.1
120°	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7	270.7	269.8	268.3
122.5°	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3	287.7	287.1	285.5
125°	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1	311.5	311.0	309.4
127.5°	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2	333.3	332.4	331.3
130°	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1	347.2	346.3	345.4
132.5°	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7	360.9	360.2	359.2
135°	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1	380.2	379.4	378.7
137.5°	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1	398.2	397.4	396.6
140°	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7	409.9	409.2	408.3
142.5°	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5	420.8	420.1	419.0
145°	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5	435.9	435.3	433.9
147.5°	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6	449.2	448.8	447.4
150°	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7	457.2	456.7	455.4
152.5°	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0	464.5	464.1	462.8
155°	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0	474.5	474.0	473.0
157.5°	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4	482.8	482.2	481.6
160°	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2	487.8	487.2	486.7
162.5°	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8	492.2	491.6	491.2
165°	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1	497.0
167.5°	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0	502.4	501.8	501.6
170°	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3	504.7	504.2	504.0
172.5°	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0	506.5	505.9	505.8
175°	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0	508.4	507.8	507.6
177.5°	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2	508.8	508.2	508.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	5.9	5.8	5.7	5.8	5.2	5.0	4.1	3.5	3.5	3.5	3.4
90°	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3	1.3	2.2	3.1
92.5°	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4	7.3	7.2	7.1
95°	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9	21.2	18.5	15.8
97.5°	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4	39.9	32.3	24.6
100°	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2	53.9	42.7	31.5
102.5°	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6	82.2	79.8	77.5
105°	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8	114.3	116.8	119.2
107.5°	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0	145.0	147.0	149.0
110°	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0	164.7	166.4	168.2



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8	183.4	184.9	186.4
115°	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6	213.0	214.4	215.8
117.5°	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2	239.7	241.3	242.8
120°	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6	258.8	260.0	261.3
122.5°	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1	275.3	276.6	277.9
125°	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2	300.2	301.4	302.4
127.5°	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9	323.1	324.3	325.5
130°	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4	337.7	339.0	340.3
132.5°	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1	352.1	353.3	354.4
135°	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2	371.5	372.8	374.1
137.5°	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6	390.5	391.4	392.4
140°	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3	402.9	403.6	404.2
142.5°	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8	413.5	414.0	414.6
145°	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5	429.4	429.3	429.2
147.5°	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9	443.7	443.3	443.1
150°	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4	452.8	452.2	451.7
152.5°	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3	460.7	460.0	459.4
155°	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9	472.2	471.4	470.7
157.5°	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9	481.3	480.7	480.1
160°	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	486.7	486.3	485.8
162.5°	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0	491.5	490.9	490.5
165°	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3	497.8	497.3	496.8
167.5°	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0	502.5	502.0	501.5
170°	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7	505.1	504.6	504.2
172.5°	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4	507.0	506.4	505.9
175°	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7	509.1	508.5	508.0
177.5°	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1	509.6	509.1	508.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	3.4	3.4	3.4	3.5	3.5	3.5	3.4	3.5	3.6	3.4	3.4
90°	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2	8.6	9.0	9.3
92.5°	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0	9.2	9.4	9.6
95°	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2	15.6	16.0	16.2
97.5°	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9	20.2	20.5	20.8
100°	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3	22.9	23.6	24.0
102.5°	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2	24.1	25.0	25.5
105°	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3	25.1	26.1	26.7
107.5°	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6	28.7	27.7	27.5
110°	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0	39.9	31.7	27.7



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8	72.9	43.1	28.3
115°	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4	113.5	75.6	53.7
117.5°	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2	224.0	214.8	200.6
120°	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7	272.7	273.7	268.6
122.5°	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3	288.9	289.5	288.7
125°	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1	312.7	313.2	313.7
127.5°	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2	334.9	335.8	336.2
130°	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1	349.0	349.9	350.3
132.5°	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7	362.4	363.2	363.5
135°	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1	381.9	382.7	383.0
137.5°	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1	399.8	400.6	400.9
140°	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7	411.5	412.2	412.3
142.5°	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5	422.1	422.8	422.9
145°	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5	437.0	437.6	437.7
147.5°	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6	450.0	450.5	450.5
150°	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7	458.1	458.7	458.7
152.5°	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0	465.5	466.1	466.0
155°	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0	475.4	476.0	475.9
157.5°	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4	483.9	484.5	484.4
160°	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2	488.7	489.2	489.1
162.5°	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8	493.4	493.9	493.8
165°	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3	498.9	499.5	499.5
167.5°	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0	503.5	504.1	504.0
170°	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3	505.9	506.4	506.4
172.5°	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0	507.6	508.2	508.2
175°	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0	509.5	510.1	510.1
177.5°	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2	509.6	510.1	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	3.4	3.4	3.4	3.3	3.4	3.4	3.4	3.4	3.4	3.6	3.5
90°	9.5	9.6	9.8	9.9	9.8	9.6	9.5	9.3	9.0	8.6	8.2
92.5°	9.6	9.7	9.8	9.9	9.8	9.7	9.6	9.6	9.4	9.2	9.0
95°	16.1	16.0	15.9	15.8	15.9	16.0	16.1	16.2	16.0	15.6	15.2
97.5°	20.8	20.9	21.0	21.1	21.0	20.9	20.8	20.8	20.5	20.2	19.9
100°	24.2	24.4	24.5	24.6	24.5	24.4	24.2	24.0	23.6	22.9	22.3
102.5°	25.7	26.0	26.2	26.4	26.2	26.0	25.7	25.5	25.0	24.1	23.2
105°	26.9	27.3	27.6	28.0	27.6	27.3	26.9	26.7	26.1	25.1	24.3
107.5°	27.8	28.2	28.4	28.8	28.4	28.2	27.8	27.5	27.7	28.7	29.6
110°	28.1	28.4	28.8	29.1	28.8	28.4	28.1	27.7	31.7	39.9	48.0



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	28.6	28.8	29.1	29.4	29.1	28.8	28.6	28.3	43.1	72.9	102.8
115°	47.9	41.9	36.1	30.1	36.1	41.9	47.9	53.7	75.6	113.5	151.4
117.5°	181.2	161.9	142.6	123.2	142.6	161.9	181.2	200.6	214.8	224.0	233.2
120°	257.6	246.6	235.5	224.5	235.5	246.6	257.6	268.6	273.7	272.7	271.7
122.5°	286.5	284.4	282.2	280.1	282.2	284.4	286.5	288.7	289.5	288.9	288.3
125°	313.9	314.2	314.4	314.6	314.4	314.2	313.9	313.7	313.2	312.7	312.1
127.5°	336.3	336.3	336.4	336.4	336.4	336.3	336.3	336.2	335.8	334.9	334.2
130°	350.3	350.2	350.1	350.0	350.1	350.2	350.3	350.3	349.9	349.0	348.1
132.5°	363.4	363.3	363.3	363.3	363.3	363.3	363.4	363.5	363.2	362.4	361.7
135°	382.9	382.7	382.5	382.4	382.5	382.7	382.9	383.0	382.7	381.9	381.1
137.5°	400.6	400.4	400.1	399.8	400.1	400.4	400.6	400.9	400.6	399.8	399.1
140°	411.9	411.5	411.1	410.7	411.1	411.5	411.9	412.3	412.2	411.5	410.7
142.5°	422.5	422.1	421.7	421.3	421.7	422.1	422.5	422.9	422.8	422.1	421.5
145°	437.3	436.9	436.5	436.1	436.5	436.9	437.3	437.7	437.6	437.0	436.5
147.5°	450.1	449.8	449.4	449.1	449.4	449.8	450.1	450.5	450.5	450.0	449.6
150°	458.3	457.9	457.4	457.1	457.4	457.9	458.3	458.7	458.7	458.1	457.7
152.5°	465.5	464.9	464.3	463.8	464.3	464.9	465.5	466.0	466.1	465.5	465.0
155°	475.2	474.6	473.9	473.3	473.9	474.6	475.2	475.9	476.0	475.4	475.0
157.5°	483.8	483.1	482.5	481.9	482.5	483.1	483.8	484.4	484.5	483.9	483.4
160°	488.6	488.0	487.4	486.9	487.4	488.0	488.6	489.1	489.2	488.7	488.2
162.5°	493.1	492.4	491.7	491.0	491.7	492.4	493.1	493.8	493.9	493.4	492.8
165°	498.9	498.3	497.7	497.1	497.7	498.3	498.9	499.5	499.5	498.9	498.3
167.5°	503.3	502.6	501.8	501.1	501.8	502.6	503.3	504.0	504.1	503.5	503.0
170°	505.7	504.9	504.2	503.4	504.2	504.9	505.7	506.4	506.4	505.9	505.3
172.5°	507.4	506.7	505.9	505.2	505.9	506.7	507.4	508.2	508.2	507.6	507.0
175°	509.2	508.4	507.6	506.8	507.6	508.4	509.2	510.1	510.1	509.5	509.0
177.5°	509.5	508.9	508.2	507.7	508.2	508.9	509.5	510.1	510.1	509.6	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	3.4	3.5	3.5	3.5	3.4	3.4	3.4	3.4	3.5	3.5	3.5
90°	7.7	7.3	6.7	6.0	5.4	4.7	4.0	3.1	2.2	1.3	0.3
92.5°	8.8	8.5	8.2	7.9	7.6	7.2	7.1	7.1	7.2	7.3	7.4
95°	14.7	14.4	13.8	13.2	12.7	12.1	13.1	15.8	18.5	21.2	23.9
97.5°	19.5	19.2	17.9	16.5	15.2	13.9	17.0	24.6	32.3	39.9	47.4
100°	21.6	21.0	19.5	18.2	16.8	15.4	20.3	31.5	42.7	53.9	65.2
102.5°	22.4	21.5	33.2	44.9	56.5	68.1	75.1	77.5	79.8	82.2	84.6
105°	23.3	22.5	44.8	67.1	89.5	111.8	121.7	119.2	116.8	114.3	111.8
107.5°	30.5	31.4	58.2	85.0	111.8	138.5	150.9	149.0	147.0	145.0	143.0
110°	56.2	64.4	88.0	111.7	135.3	158.9	169.9	168.2	166.4	164.7	163.0



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	132.6	162.5	168.2	174.1	179.9	185.8	188.0	186.4	184.9	183.4	181.8
115°	189.2	227.0	225.0	223.0	220.9	218.9	217.1	215.8	214.4	213.0	211.6
117.5°	242.4	251.5	250.1	248.7	247.3	245.9	244.4	242.8	241.3	239.7	238.2
120°	270.7	269.8	268.3	266.8	265.4	263.9	262.5	261.3	260.0	258.8	257.6
122.5°	287.7	287.1	285.5	283.9	282.3	280.7	279.2	277.9	276.6	275.3	274.1
125°	311.5	311.0	309.4	307.9	306.3	304.7	303.4	302.4	301.4	300.2	299.2
127.5°	333.3	332.4	331.3	330.1	329.0	327.8	326.7	325.5	324.3	323.1	321.9
130°	347.2	346.3	345.4	344.5	343.6	342.7	341.6	340.3	339.0	337.7	336.4
132.5°	360.9	360.2	359.2	358.3	357.4	356.5	355.5	354.4	353.3	352.1	351.1
135°	380.2	379.4	378.7	378.0	377.2	376.4	375.5	374.1	372.8	371.5	370.2
137.5°	398.2	397.4	396.6	395.8	394.9	394.1	393.2	392.4	391.4	390.5	389.6
140°	409.9	409.2	408.3	407.4	406.6	405.6	404.8	404.2	403.6	402.9	402.3
142.5°	420.8	420.1	419.0	418.0	417.0	416.0	415.2	414.6	414.0	413.5	412.8
145°	435.9	435.3	433.9	432.6	431.2	429.8	429.1	429.2	429.3	429.4	429.5
147.5°	449.2	448.8	447.4	446.0	444.6	443.2	442.7	443.1	443.3	443.7	443.9
150°	457.2	456.7	455.4	454.1	452.8	451.4	451.1	451.7	452.2	452.8	453.4
152.5°	464.5	464.1	462.8	461.6	460.3	459.1	458.7	459.4	460.0	460.7	461.3
155°	474.5	474.0	473.0	472.0	471.1	470.1	469.9	470.7	471.4	472.2	472.9
157.5°	482.8	482.2	481.6	480.9	480.2	479.5	479.5	480.1	480.7	481.3	481.9
160°	487.8	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2
162.5°	492.2	491.6	491.2	490.8	490.3	490.0	490.0	490.5	490.9	491.5	492.0
165°	497.7	497.1	497.0	496.7	496.5	496.2	496.3	496.8	497.3	497.8	498.3
167.5°	502.4	501.8	501.6	501.4	501.1	500.9	501.0	501.5	502.0	502.5	503.0
170°	504.7	504.2	504.0	503.9	503.7	503.5	503.7	504.2	504.6	505.1	505.7
172.5°	506.5	505.9	505.8	505.6	505.4	505.3	505.4	505.9	506.4	507.0	507.4
175°	508.4	507.8	507.6	507.6	507.4	507.2	507.4	508.0	508.5	509.1	509.7
177.5°	508.8	508.2	508.2	508.2	508.1	508.0	508.2	508.7	509.1	509.6	510.1
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.1	5.0	5.2	5.8	5.7	5.8	5.9	5.9	5.9	5.8	5.7
90°	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7	8.2
92.5°	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8	9.0
95°	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7	15.2
97.5°	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5	19.9
100°	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6	22.3
102.5°	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4	23.2
105°	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3	24.3
107.5°	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5	29.6
110°	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2	48.0



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6	102.8
115°	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2	151.4
117.5°	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4	233.2
120°	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7	271.7
122.5°	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7	288.3
125°	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5	312.1
127.5°	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3	334.2
130°	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2	348.1
132.5°	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9	361.7
135°	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2	381.1
137.5°	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2	399.1
140°	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9	410.7
142.5°	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8	421.5
145°	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9	436.5
147.5°	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2	449.6
150°	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2	457.7
152.5°	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5	465.0
155°	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5	475.0
157.5°	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8	483.4
160°	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8	488.2
162.5°	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2	492.8
165°	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7	498.3
167.5°	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4	503.0
170°	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7	505.3
172.5°	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5	507.0
175°	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4	509.0
177.5°	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8	509.2
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	5.9	6.0	5.9	5.9	6.1	6.0	6.0
90°	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331465-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)