

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331466-935

Luminaire Tested: **S122DIW-S290D435U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331466-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D435U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2417.2 lumens
Efficiency: N/A
Efficacy: 105.1 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 23
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	47	46	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	82	72	65	60	75	67	61	56	56	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	50	45	41	42	38	35	34	32	29	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	15	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	8217	8217	8217	8217
5°	9211	8271	7329	8271
10°	10557	8202	6342	8202
15°	11677	8052	5605	8052
20°	11500	7892	5108	7892
25°	10368	7675	4794	7675
30°	8569	7333	4566	7333
35°	6244	6974	4401	6974
40°	4989	6551	4312	6551
45°	4359	6060	4190	6060
50°	4099	5586	4107	5586
55°	3775	5103	3997	5103
60°	3462	4592	3830	4592
65°	3156	4130	3660	4130
70°	2861	3682	3418	3682
75°	2539	3188	3026	3188
80°	2185	2631	2436	2631
85°	1964	1964	1445	1964



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	48.5	2.0
10°-20°	140.9	5.8
20°-30°	204.5	8.5
30°-40°	215.8	8.9
40°-50°	191.1	7.9
50°-60°	152.5	6.3
60°-70°	103.6	4.3
70°-80°	53.1	2.2
80°-90°	14.7	0.6
90°-100°	29.3	1.2
100°-110°	91.0	3.8
110°-120°	155.5	6.4
120°-130°	204.5	8.5
130°-140°	229.5	9.5
140°-150°	225.0	9.3
150°-160°	188.8	7.8
160°-170°	125.2	5.2
170°-180°	43.8	1.8
0°-30°	393.9	16.3
0°-40°	609.7	25.2
0°-60°	953.2	39.4
0°-90°	1124.6	46.5
90°-120°	275.7	11.4
90°-150°	934.8	38.7
90°-180°	1293.0	53.5
0°-180°	2417.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	509	509	509	509	509	
5°	568	510	452	510	568	57
15°	699	482	335	482	699	193
25°	582	431	269	431	582	263
35°	317	354	223	354	317	206
45°	191	265	184	265	191	150
55°	134	181	142	181	134	120
65°	83	108	96	108	83	82
75°	41	51	48	51	41	43
85°	11	11	8	11	11	12
90°	13	0	13	0	13	6
95°	24	20	24	20	24	27
105°	87	84	87	84	87	91
115°	156	156	156	156	156	154
125°	228	227	228	227	228	203
135°	297	294	297	294	297	229
145°	360	356	360	356	360	225
155°	411	408	411	408	411	189
165°	444	444	444	444	444	125
175°	460	462	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	532.4	532.5	532.9	530.4	530.0	530.0	527.9	526.0	523.7	520.8	521.2
5°	568.3	570.5	571.3	568.9	565.4	565.1	561.7	556.3	551.1	547.1	544.2
7.5°	611.3	612.2	610.3	607.2	604.6	599.9	593.7	587.6	579.1	571.4	565.6
10°	643.9	645.1	641.7	637.2	633.5	628.0	619.1	609.8	598.7	588.0	579.4
12.5°	668.6	671.5	667.2	666.7	660.3	652.7	642.0	637.4	621.7	606.7	597.4
15°	698.6	698.4	698.9	695.1	690.4	689.2	678.0	665.6	643.5	634.6	619.4
17.5°	689.9	692.9	694.3	694.2	694.1	693.4	689.7	682.0	670.9	656.6	639.0
20°	669.3	673.2	673.8	678.3	680.9	684.2	685.5	683.4	676.6	664.6	649.4
22.5°	637.4	638.5	640.3	647.3	652.8	661.2	665.5	672.8	670.1	664.3	651.5
25°	582.0	580.1	586.9	590.5	603.2	616.5	626.1	636.6	646.0	651.7	648.0
27.5°	515.7	512.7	523.0	532.4	542.6	557.1	572.0	589.6	604.2	622.7	629.0
30°	459.6	461.4	471.1	481.1	496.8	517.1	534.0	553.3	574.3	594.8	609.1
32.5°	399.2	406.0	412.2	427.5	441.3	463.9	488.6	512.8	538.9	562.2	584.4
35°	316.8	324.7	333.3	344.4	363.8	386.2	410.4	443.0	478.6	510.5	536.7
37.5°	266.7	265.4	270.4	278.4	294.1	312.3	340.0	372.2	414.1	451.6	488.6
40°	236.7	235.9	239.4	246.8	258.7	272.1	296.4	324.7	363.6	409.4	453.4
42.5°	216.0	216.5	218.4	223.7	231.9	242.8	261.0	285.1	320.7	363.9	411.1
45°	190.9	192.3	194.4	197.0	201.6	210.7	220.8	238.1	266.2	302.2	348.7
47.5°	172.8	172.9	175.0	177.3	180.0	185.1	193.5	204.2	224.1	253.4	293.4
50°	163.2	161.8	163.3	165.1	168.0	171.5	177.0	187.2	200.4	224.1	257.6
52.5°	151.2	151.3	152.7	153.3	155.9	159.5	164.5	171.5	183.6	202.1	229.5
55°	134.1	135.2	136.0	137.1	139.5	142.0	145.9	150.6	160.0	173.8	194.2
57.5°	118.1	118.5	119.2	121.5	123.0	125.3	129.0	133.3	139.4	149.6	165.0
60°	107.2	107.2	108.7	109.7	111.7	114.0	116.9	121.1	126.6	134.9	147.3
62.5°	97.2	97.0	97.6	99.3	100.7	102.9	105.8	109.3	114.5	122.0	132.1
65°	82.6	82.1	83.3	83.7	85.2	87.4	89.8	93.5	97.6	103.1	112.1
67.5°	68.4	69.0	69.6	70.3	71.1	73.4	75.0	77.6	81.1	85.7	91.7
70°	60.6	60.6	60.6	61.2	62.4	63.5	65.1	67.2	70.6	74.5	80.0
72.5°	51.8	52.5	53.1	52.8	54.2	54.9	56.8	58.0	61.2	63.7	68.5
75°	40.7	40.7	40.7	41.7	42.3	42.8	44.0	45.2	46.8	49.9	52.4
77.5°	30.4	30.3	30.5	30.7	31.3	32.0	32.4	33.4	34.9	36.3	38.5
80°	23.5	23.8	24.0	24.5	24.5	24.8	25.1	26.4	27.4	28.3	29.7
82.5°	18.2	18.3	18.3	18.3	18.5	18.8	19.3	19.7	20.1	20.8	21.9
85°	10.6	10.3	10.3	10.8	10.6	10.6	10.9	11.4	11.4	11.5	12.1
87.5°	6.7	6.7	6.8	6.6	6.6	6.8	6.9	6.7	6.9	7.1	6.9
90°	13.3	13.2	13.1	13.0	12.9	13.0	13.2	13.3	13.5	13.7	11.7
92.5°	12.7	12.7	12.6	12.6	12.6	12.6	12.5	12.5	12.4	12.4	12.0
95°	24.2	24.4	24.5	24.7	24.9	25.0	25.0	25.0	25.0	25.0	24.8
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.7
100°	53.5	53.6	53.6	53.7	53.8	53.8	53.8	53.8	53.8	53.8	53.6
102.5°	66.6	66.6	66.7	66.8	66.9	66.9	66.8	66.7	66.7	66.6	66.3
105°	86.6	86.6	86.6	86.6	86.6	86.5	86.4	86.2	86.0	85.8	85.7
107.5°	105.5	105.9	106.2	106.7	107.1	107.3	107.2	107.1	107.0	106.9	106.9
110°	120.1	120.4	120.6	120.9	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.2	134.4	134.6	134.7	134.9	135.2	135.3	135.6	135.8	136.0	136.0
115°	156.0	156.3	156.5	156.8	157.0	157.2	157.3	157.4	157.5	157.6	157.7
117.5°	176.8	177.1	177.4	177.6	177.9	178.1	178.3	178.6	178.7	179.0	179.4
120°	191.6	191.8	192.1	192.3	192.6	192.7	192.7	192.7	192.7	192.7	193.4
122.5°	205.9	206.0	206.3	206.5	206.6	206.8	207.1	207.2	207.5	207.7	208.2
125°	227.8	227.9	228.0	228.1	228.2	228.3	228.6	228.9	229.1	229.4	229.6
127.5°	247.8	248.1	248.3	248.6	248.9	249.2	249.5	249.8	250.1	250.5	250.7
130°	262.2	262.5	262.9	263.2	263.6	263.8	264.0	264.2	264.3	264.5	264.7
132.5°	275.9	276.1	276.4	276.7	277.0	277.3	277.7	278.1	278.4	278.8	278.8
135°	297.2	297.5	297.7	298.0	298.3	298.4	298.5	298.6	298.7	298.8	298.6
137.5°	316.6	316.9	317.3	317.6	318.0	318.2	318.2	318.3	318.4	318.5	318.2
140°	330.0	330.4	330.7	331.1	331.4	331.6	331.6	331.6	331.6	331.6	331.1
142.5°	342.2	342.5	342.9	343.2	343.5	343.7	343.6	343.5	343.5	343.5	343.1
145°	360.4	360.8	361.1	361.4	361.8	362.0	361.9	361.8	361.7	361.6	361.1
147.5°	376.8	377.0	377.4	377.7	378.1	378.2	378.0	377.7	377.5	377.4	377.0
150°	387.4	387.6	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4	387.0
152.5°	397.4	397.7	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4	396.9
155°	410.8	411.0	411.3	411.6	411.8	411.7	411.3	410.9	410.4	410.0	409.7
157.5°	422.3	422.8	423.1	423.5	424.0	423.9	423.3	422.7	422.1	421.5	421.4
160°	429.5	429.8	430.2	430.5	430.8	430.8	430.2	429.7	429.2	428.7	428.6
162.5°	435.8	436.1	436.5	437.0	437.4	437.3	436.7	436.1	435.5	435.0	434.9
165°	443.9	444.4	444.8	445.2	445.7	445.6	445.0	444.4	443.8	443.2	443.2
167.5°	450.6	451.1	451.5	451.9	452.5	452.4	451.8	451.2	450.6	450.0	450.0
170°	454.1	454.6	455.1	455.6	456.2	456.1	455.5	454.9	454.3	453.7	453.7
172.5°	456.8	457.4	457.9	458.4	458.9	458.9	458.3	457.7	457.1	456.5	456.6
175°	459.9	460.5	461.0	461.5	462.0	461.9	461.3	460.7	460.1	459.5	459.7
177.5°	461.3	461.8	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3	461.4
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	522.2	521.0	520.2	517.4	514.9	512.4	511.6	511.9	508.4	505.1	503.8
5°	542.6	538.6	534.9	529.7	523.4	516.5	513.1	510.3	503.4	496.0	491.7
7.5°	560.8	555.2	548.0	538.1	529.0	518.2	511.3	505.3	495.3	484.8	478.4
10°	571.9	564.3	555.1	542.9	531.8	518.7	509.5	500.3	488.6	476.0	468.2
12.5°	581.4	571.2	562.1	546.6	533.4	516.9	506.1	493.1	480.8	465.9	458.2
15°	604.2	585.2	568.0	550.4	534.2	511.3	499.1	481.7	465.5	447.1	438.3
17.5°	621.7	600.4	573.3	551.0	532.0	506.6	488.9	468.0	448.8	427.8	415.9
20°	631.7	607.3	578.2	551.6	528.9	499.9	480.5	459.3	436.8	413.1	400.2
22.5°	637.7	612.0	583.2	549.2	522.6	494.5	470.1	446.7	424.0	398.4	384.9
25°	639.6	616.1	585.6	547.3	514.8	482.9	453.6	430.8	403.3	379.4	359.7
27.5°	630.3	613.5	584.1	543.5	505.8	468.5	435.8	410.1	381.0	355.1	335.2
30°	618.8	609.1	580.5	539.8	498.5	458.5	422.5	393.3	364.4	338.2	317.8
32.5°	601.2	599.1	573.9	534.5	490.9	445.8	408.5	379.1	347.0	321.2	301.9
35°	566.5	575.8	560.0	522.6	476.5	427.7	387.4	353.8	320.6	295.9	277.8
37.5°	519.9	543.2	539.1	505.2	456.9	408.1	363.6	328.5	296.8	271.9	254.1
40°	487.8	517.5	521.9	491.9	443.2	393.0	345.8	310.8	279.9	257.2	239.2
42.5°	453.4	488.1	499.9	476.0	428.2	376.9	329.8	293.6	262.9	240.9	225.0
45°	395.7	441.6	463.0	449.3	403.1	350.7	302.2	265.4	237.6	216.9	204.6
47.5°	341.7	391.9	420.6	415.8	375.2	323.3	275.3	240.0	213.0	196.5	185.5
50°	303.6	355.2	389.8	391.4	355.2	303.8	255.6	222.4	197.5	182.1	173.1
52.5°	270.4	319.7	357.4	365.8	332.8	283.4	238.0	204.8	183.0	168.8	160.7
55°	227.0	268.7	310.6	325.9	299.5	252.5	210.4	181.3	160.7	151.0	144.0
57.5°	188.8	223.5	262.2	279.1	262.8	222.6	183.1	157.8	141.2	132.6	127.2
60°	168.6	196.0	230.4	250.6	236.4	200.7	166.3	142.2	128.5	120.9	115.8
62.5°	149.8	174.1	203.2	221.6	214.0	180.2	149.4	128.1	116.3	109.2	105.5
65°	123.6	142.8	165.3	182.3	177.2	151.6	126.3	108.1	98.8	93.1	90.1
67.5°	101.8	115.6	131.2	146.1	142.1	123.9	103.7	89.5	82.5	77.6	75.8
70°	88.0	98.6	112.4	124.4	121.1	106.2	90.1	78.0	72.0	67.8	66.1
72.5°	74.9	83.5	94.2	103.9	101.7	89.3	75.9	66.8	62.1	58.3	56.9
75°	56.6	63.2	69.7	76.1	75.5	66.0	58.1	51.1	47.4	44.4	43.8
77.5°	41.8	45.5	49.9	53.6	52.6	47.1	41.0	36.9	34.3	32.3	31.9
80°	31.9	34.0	37.2	39.9	38.6	36.2	31.3	28.3	26.4	24.5	23.7
82.5°	23.2	25.2	27.1	28.7	27.6	25.4	22.4	20.4	19.2	17.9	17.6
85°	12.1	13.3	14.1	14.5	14.1	12.7	11.4	10.6	9.6	9.0	8.8
87.5°	6.6	6.3	5.9	5.9	5.3	5.0	4.2	3.5	3.5	3.6	3.5
90°	9.8	7.9	6.0	4.6	3.5	2.5	1.5	0.4	1.5	2.5	3.5
92.5°	11.5	11.0	10.6	10.0	9.2	8.4	7.7	7.0	7.7	8.4	9.2
95°	24.6	24.5	24.3	23.8	22.9	22.0	21.2	20.3	21.2	22.0	22.9
97.5°	41.3	41.0	40.6	40.1	39.3	38.6	37.8	37.0	37.8	38.6	39.3
100°	53.3	53.0	52.8	52.3	51.7	50.9	50.2	49.5	50.2	50.9	51.7
102.5°	66.0	65.6	65.3	64.8	64.3	63.7	63.2	62.7	63.2	63.7	64.3
105°	85.5	85.3	85.2	84.9	84.6	84.4	84.1	83.9	84.1	84.4	84.6
107.5°	106.9	106.9	106.9	106.8	106.4	106.0	105.6	105.2	105.6	106.0	106.4
110°	121.3	121.3	121.3	121.1	120.5	120.0	119.5	119.0	119.5	120.0	120.5



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	136.1	136.2	136.3	136.0	135.5	135.0	134.5	134.0	134.5	135.0	135.5
115°	157.9	158.1	158.3	158.1	157.6	157.0	156.5	156.0	156.5	157.0	157.6
117.5°	179.9	180.5	180.9	180.8	180.1	179.4	178.7	178.1	178.7	179.4	180.1
120°	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	193.4	194.1	194.8
122.5°	208.6	209.1	209.7	209.5	208.6	207.8	207.0	206.1	207.0	207.8	208.6
125°	229.9	230.1	230.4	230.1	229.4	228.6	227.8	227.0	227.8	228.6	229.4
127.5°	251.1	251.4	251.7	251.3	250.4	249.3	248.4	247.4	248.4	249.3	250.4
130°	264.8	265.0	265.2	264.7	263.6	262.4	261.3	260.2	261.3	262.4	263.6
132.5°	278.8	278.7	278.7	278.2	277.3	276.4	275.4	274.6	275.4	276.4	277.3
135°	298.4	298.3	298.1	297.6	296.6	295.7	294.7	293.8	294.7	295.7	296.6
137.5°	318.1	317.8	317.5	317.0	316.2	315.5	314.7	313.9	314.7	315.5	316.2
140°	330.7	330.3	329.8	329.2	328.5	327.7	326.9	326.1	326.9	327.7	328.5
142.5°	342.9	342.5	342.2	341.7	341.0	340.2	339.4	338.6	339.4	340.2	341.0
145°	360.6	360.1	359.6	359.0	358.3	357.7	357.1	356.5	357.1	357.7	358.3
147.5°	376.7	376.3	376.0	375.5	374.7	374.0	373.2	372.6	373.2	374.0	374.7
150°	386.7	386.3	386.0	385.6	385.0	384.5	384.0	383.5	384.0	384.5	385.0
152.5°	396.5	396.1	395.7	395.2	394.7	394.2	393.6	393.1	393.6	394.2	394.7
155°	409.5	409.2	409.0	408.7	408.5	408.1	407.9	407.6	407.9	408.1	408.5
157.5°	421.2	421.0	420.9	420.8	420.6	420.4	420.3	420.1	420.3	420.4	420.6
160°	428.5	428.4	428.3	428.3	428.1	427.9	427.7	427.6	427.7	427.9	428.1
162.5°	434.8	434.7	434.6	434.5	434.5	434.5	434.5	434.4	434.5	434.5	434.5
165°	443.2	443.2	443.2	443.2	443.2	443.3	443.4	443.5	443.4	443.3	443.2
167.5°	450.0	450.0	450.0	450.1	450.4	450.6	450.9	451.2	450.9	450.6	450.4
170°	453.8	453.9	454.0	454.2	454.4	454.7	455.0	455.2	455.0	454.7	454.4
172.5°	456.7	456.8	456.8	457.0	457.3	457.5	457.8	458.1	457.8	457.5	457.3
175°	459.9	460.0	460.2	460.5	460.7	461.0	461.2	461.5	461.2	461.0	460.7
177.5°	461.6	461.8	461.8	462.0	462.3	462.4	462.7	462.9	462.7	462.4	462.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	502.2	501.3	498.0	496.3	493.4	490.8	489.0	489.8	490.4	490.2	489.7
5°	487.8	484.1	478.4	473.6	470.0	463.6	460.8	459.4	458.2	456.9	455.6
7.5°	470.6	464.8	456.7	449.7	443.2	435.1	430.5	427.8	425.0	421.9	419.1
10°	458.5	450.2	441.6	431.9	424.0	416.8	410.4	406.0	402.1	398.4	395.7
12.5°	445.7	436.2	425.5	412.2	403.6	393.1	392.2	384.6	378.5	376.2	373.0
15°	425.2	411.9	398.4	382.5	375.7	366.4	360.5	354.6	349.3	345.6	344.7
17.5°	402.0	384.8	371.3	360.0	348.8	339.1	333.7	329.1	324.7	319.8	319.1
20°	384.4	369.5	354.8	344.8	333.3	323.5	316.8	312.2	308.4	305.5	303.0
22.5°	367.6	351.3	337.9	327.0	315.6	307.7	302.5	297.9	294.8	291.6	289.2
25°	340.7	328.0	313.3	301.0	291.6	286.5	282.2	278.4	276.4	274.2	271.5
27.5°	317.2	303.1	289.4	279.8	271.6	267.1	264.0	261.3	259.5	258.2	256.7
30°	300.7	286.4	275.6	266.2	259.3	254.9	252.9	251.3	249.2	248.4	247.6
32.5°	284.6	271.8	262.6	254.4	248.0	245.0	243.2	241.8	240.1	239.4	237.7
35°	262.1	251.3	242.4	237.8	232.6	230.0	228.7	226.7	225.2	224.4	224.1
37.5°	240.8	231.5	225.6	219.8	217.6	216.0	214.1	212.8	212.3	212.2	212.0
40°	227.0	219.5	214.1	209.5	208.5	206.1	204.6	203.5	203.5	203.6	203.5
42.5°	214.6	207.7	203.0	199.0	197.9	196.5	194.8	194.8	195.1	195.8	195.1
45°	195.6	190.7	187.4	185.5	183.3	181.9	181.7	182.3	182.4	182.7	183.3
47.5°	178.1	174.9	171.9	169.7	168.8	168.6	168.3	169.4	170.3	170.7	171.5
50°	167.8	164.1	161.5	160.1	159.4	159.0	159.4	160.6	161.4	162.3	162.9
52.5°	156.3	153.6	151.9	150.8	150.5	150.8	150.8	152.1	153.3	153.8	154.0
55°	140.3	138.3	137.9	136.1	136.9	136.7	137.7	138.4	139.7	140.9	141.0
57.5°	124.2	122.7	121.7	121.8	122.1	123.0	123.7	125.1	126.3	127.6	127.7
60°	113.7	112.9	112.3	112.3	112.6	113.8	114.8	116.1	116.9	117.8	118.3
62.5°	103.9	103.1	102.5	102.9	103.9	104.6	105.7	106.5	107.3	108.1	108.3
65°	88.6	88.3	88.8	89.2	89.4	90.3	91.7	92.3	93.1	93.5	94.9
67.5°	74.5	74.6	74.5	75.0	76.2	76.4	77.7	79.0	79.2	80.0	80.8
70°	64.9	65.3	65.7	66.1	67.1	67.5	68.4	69.1	69.8	70.4	71.0
72.5°	56.1	56.2	56.7	56.6	57.4	58.2	59.1	59.7	60.4	61.2	61.7
75°	43.2	43.2	43.7	43.8	44.8	45.8	45.5	46.0	46.8	47.5	48.0
77.5°	31.6	31.2	31.6	31.8	32.1	32.9	33.1	33.6	34.5	34.3	34.7
80°	24.0	23.5	24.0	24.3	24.3	25.2	25.2	25.7	26.2	25.7	26.2
82.5°	17.1	16.9	17.3	17.4	17.7	17.7	18.0	18.1	18.7	18.4	18.7
85°	8.6	8.4	8.6	8.4	8.6	8.8	8.8	8.6	8.6	9.0	8.4
87.5°	3.5	3.7	4.0	4.3	4.6	4.7	4.6	4.6	4.5	4.1	4.1
90°	4.6	6.0	7.9	9.8	11.7	13.7	13.5	13.3	13.2	13.0	12.9
92.5°	10.0	10.6	11.0	11.5	12.0	12.4	12.4	12.5	12.5	12.6	12.6
95°	23.8	24.3	24.5	24.6	24.8	25.0	25.0	25.0	25.0	25.0	24.9
97.5°	40.1	40.6	41.0	41.3	41.7	41.9	41.9	41.9	41.9	41.9	41.9
100°	52.3	52.8	53.0	53.3	53.6	53.8	53.8	53.8	53.8	53.8	53.8
102.5°	64.8	65.3	65.6	66.0	66.3	66.6	66.7	66.7	66.8	66.9	66.9
105°	84.9	85.2	85.3	85.5	85.7	85.8	86.0	86.2	86.4	86.5	86.6
107.5°	106.8	106.9	106.9	106.9	106.9	106.9	107.0	107.1	107.2	107.3	107.1
110°	121.1	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.3	121.1



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	136.0	136.3	136.2	136.1	136.0	136.0	135.8	135.6	135.3	135.2	134.9
115°	158.1	158.3	158.1	157.9	157.7	157.6	157.5	157.4	157.3	157.2	157.0
117.5°	180.8	180.9	180.5	179.9	179.4	179.0	178.7	178.6	178.3	178.1	177.9
120°	195.4	195.4	194.8	194.1	193.4	192.7	192.7	192.7	192.7	192.7	192.6
122.5°	209.5	209.7	209.1	208.6	208.2	207.7	207.5	207.2	207.1	206.8	206.6
125°	230.1	230.4	230.1	229.9	229.6	229.4	229.1	228.9	228.6	228.3	228.2
127.5°	251.3	251.7	251.4	251.1	250.7	250.5	250.1	249.8	249.5	249.2	248.9
130°	264.7	265.2	265.0	264.8	264.7	264.5	264.3	264.2	264.0	263.8	263.6
132.5°	278.2	278.7	278.7	278.8	278.8	278.8	278.4	278.1	277.7	277.3	277.0
135°	297.6	298.1	298.3	298.4	298.6	298.8	298.7	298.6	298.5	298.4	298.3
137.5°	317.0	317.5	317.8	318.1	318.2	318.5	318.4	318.3	318.2	318.2	318.0
140°	329.2	329.8	330.3	330.7	331.1	331.6	331.6	331.6	331.6	331.6	331.4
142.5°	341.7	342.2	342.5	342.9	343.1	343.5	343.5	343.5	343.6	343.7	343.5
145°	359.0	359.6	360.1	360.6	361.1	361.6	361.7	361.8	361.9	362.0	361.8
147.5°	375.5	376.0	376.3	376.7	377.0	377.4	377.5	377.7	378.0	378.2	378.1
150°	385.6	386.0	386.3	386.7	387.0	387.4	387.6	387.9	388.1	388.4	388.4
152.5°	395.2	395.7	396.1	396.5	396.9	397.4	397.7	398.0	398.3	398.6	398.6
155°	408.7	409.0	409.2	409.5	409.7	410.0	410.4	410.9	411.3	411.7	411.8
157.5°	420.8	420.9	421.0	421.2	421.4	421.5	422.1	422.7	423.3	423.9	424.0
160°	428.3	428.3	428.4	428.5	428.6	428.7	429.2	429.7	430.2	430.8	430.8
162.5°	434.5	434.6	434.7	434.8	434.9	435.0	435.5	436.1	436.7	437.3	437.4
165°	443.2	443.2	443.2	443.2	443.2	443.2	443.8	444.4	445.0	445.6	445.7
167.5°	450.1	450.0	450.0	450.0	450.0	450.0	450.6	451.2	451.8	452.4	452.5
170°	454.2	454.0	453.9	453.8	453.7	453.7	454.3	454.9	455.5	456.1	456.2
172.5°	457.0	456.8	456.8	456.7	456.6	456.5	457.1	457.7	458.3	458.9	458.9
175°	460.5	460.2	460.0	459.9	459.7	459.5	460.1	460.7	461.3	461.9	462.0
177.5°	462.0	461.8	461.8	461.6	461.4	461.3	461.8	462.2	462.5	463.0	463.0
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	488.1	487.8	487.8	486.4	487.8	487.8	488.1	489.7	490.2	490.4	489.8
5°	452.8	452.2	451.3	452.2	451.3	452.2	452.8	455.6	456.9	458.2	459.4
7.5°	417.8	415.5	415.2	412.8	415.2	415.5	417.8	419.1	421.9	425.0	427.8
10°	392.4	390.8	390.5	386.8	390.5	390.8	392.4	395.7	398.4	402.1	406.0
12.5°	373.0	369.2	370.0	367.8	370.0	369.2	373.0	373.0	376.2	378.5	384.6
15°	339.3	339.3	338.5	335.3	338.5	339.3	339.3	344.7	345.6	349.3	354.6
17.5°	315.2	314.8	313.0	313.9	313.0	314.8	315.2	319.1	319.8	324.7	329.1
20°	300.8	299.6	297.3	297.3	297.3	299.6	300.8	303.0	305.5	308.4	312.2
22.5°	287.2	287.1	284.6	285.4	284.6	287.1	287.2	289.2	291.6	294.8	297.9
25°	271.3	269.8	268.5	269.1	268.5	269.8	271.3	271.5	274.2	276.4	278.4
27.5°	256.1	255.3	255.2	253.7	255.2	255.3	256.1	256.7	258.2	259.5	261.3
30°	247.5	245.5	245.8	244.9	245.8	245.5	247.5	247.6	248.4	249.2	251.3
32.5°	237.4	236.7	236.3	235.5	236.3	236.7	237.4	237.7	239.4	240.1	241.8
35°	223.8	223.9	223.0	223.3	223.0	223.9	223.8	224.1	224.4	225.2	226.7
37.5°	211.8	212.4	212.0	212.1	212.0	212.4	211.8	212.0	212.2	212.3	212.8
40°	204.0	204.0	204.0	204.6	204.0	204.0	204.0	203.5	203.6	203.5	203.5
42.5°	196.5	196.1	195.9	195.8	195.9	196.1	196.5	195.1	195.8	195.1	194.8
45°	183.7	184.3	184.4	183.5	184.4	184.3	183.7	183.3	182.7	182.4	182.3
47.5°	172.0	172.1	172.0	172.9	172.0	172.1	172.0	171.5	170.7	170.3	169.4
50°	163.9	163.5	163.9	163.5	163.9	163.5	163.9	162.9	162.3	161.4	160.6
52.5°	155.3	155.4	155.2	155.1	155.2	155.4	155.3	154.0	153.8	153.3	152.1
55°	141.8	142.2	142.0	142.0	142.0	142.2	141.8	141.0	140.9	139.7	138.4
57.5°	127.9	128.2	128.5	127.6	128.5	128.2	127.9	127.7	127.6	126.3	125.1
60°	118.1	119.1	118.9	118.6	118.9	119.1	118.1	118.3	117.8	116.9	116.1
62.5°	109.2	109.6	109.5	109.4	109.5	109.6	109.2	108.3	108.1	107.3	106.5
65°	95.5	95.8	95.2	95.8	95.2	95.8	95.5	94.9	93.5	93.1	92.3
67.5°	80.6	80.8	81.2	81.5	81.2	80.8	80.6	80.8	80.0	79.2	79.0
70°	71.4	71.2	71.8	72.4	71.8	71.2	71.4	71.0	70.4	69.8	69.1
72.5°	61.6	62.1	61.9	62.3	61.9	62.1	61.6	61.7	61.2	60.4	59.7
75°	47.5	48.1	48.0	48.5	48.0	48.1	47.5	48.0	47.5	46.8	46.0
77.5°	34.4	34.4	34.4	34.7	34.4	34.4	34.4	34.7	34.3	34.5	33.6
80°	26.2	25.8	25.4	26.2	25.4	25.8	26.2	26.2	25.7	26.2	25.7
82.5°	18.3	18.4	18.1	18.1	18.1	18.4	18.3	18.7	18.4	18.7	18.1
85°	8.4	8.2	7.8	7.8	7.8	8.2	8.4	8.4	9.0	8.6	8.6
87.5°	4.1	4.0	4.0	3.9	4.0	4.0	4.1	4.1	4.1	4.5	4.6
90°	13.0	13.1	13.2	13.3	13.2	13.1	13.0	12.9	13.0	13.2	13.3
92.5°	12.6	12.6	12.7	12.7	12.7	12.6	12.6	12.6	12.6	12.5	12.5
95°	24.7	24.5	24.4	24.2	24.4	24.5	24.7	24.9	25.0	25.0	25.0
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.7	53.6	53.6	53.5	53.6	53.6	53.7	53.8	53.8	53.8	53.8
102.5°	66.8	66.7	66.6	66.6	66.6	66.7	66.8	66.9	66.9	66.8	66.7
105°	86.6	86.6	86.6	86.6	86.6	86.6	86.6	86.6	86.5	86.4	86.2
107.5°	106.7	106.2	105.9	105.5	105.9	106.2	106.7	107.1	107.3	107.2	107.1
110°	120.9	120.6	120.4	120.1	120.4	120.6	120.9	121.1	121.3	121.3	121.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	134.7	134.6	134.4	134.2	134.4	134.6	134.7	134.9	135.2	135.3	135.6
115°	156.8	156.5	156.3	156.0	156.3	156.5	156.8	157.0	157.2	157.3	157.4
117.5°	177.6	177.4	177.1	176.8	177.1	177.4	177.6	177.9	178.1	178.3	178.6
120°	192.3	192.1	191.8	191.6	191.8	192.1	192.3	192.6	192.7	192.7	192.7
122.5°	206.5	206.3	206.0	205.9	206.0	206.3	206.5	206.6	206.8	207.1	207.2
125°	228.1	228.0	227.9	227.8	227.9	228.0	228.1	228.2	228.3	228.6	228.9
127.5°	248.6	248.3	248.1	247.8	248.1	248.3	248.6	248.9	249.2	249.5	249.8
130°	263.2	262.9	262.5	262.2	262.5	262.9	263.2	263.6	263.8	264.0	264.2
132.5°	276.7	276.4	276.1	275.9	276.1	276.4	276.7	277.0	277.3	277.7	278.1
135°	298.0	297.7	297.5	297.2	297.5	297.7	298.0	298.3	298.4	298.5	298.6
137.5°	317.6	317.3	316.9	316.6	316.9	317.3	317.6	318.0	318.2	318.2	318.3
140°	331.1	330.7	330.4	330.0	330.4	330.7	331.1	331.4	331.6	331.6	331.6
142.5°	343.2	342.9	342.5	342.2	342.5	342.9	343.2	343.5	343.7	343.6	343.5
145°	361.4	361.1	360.8	360.4	360.8	361.1	361.4	361.8	362.0	361.9	361.8
147.5°	377.7	377.4	377.0	376.8	377.0	377.4	377.7	378.1	378.2	378.0	377.7
150°	388.1	387.9	387.6	387.4	387.6	387.9	388.1	388.4	388.4	388.1	387.9
152.5°	398.3	398.0	397.7	397.4	397.7	398.0	398.3	398.6	398.6	398.3	398.0
155°	411.6	411.3	411.0	410.8	411.0	411.3	411.6	411.8	411.7	411.3	410.9
157.5°	423.5	423.1	422.8	422.3	422.8	423.1	423.5	424.0	423.9	423.3	422.7
160°	430.5	430.2	429.8	429.5	429.8	430.2	430.5	430.8	430.8	430.2	429.7
162.5°	437.0	436.5	436.1	435.8	436.1	436.5	437.0	437.4	437.3	436.7	436.1
165°	445.2	444.8	444.4	443.9	444.4	444.8	445.2	445.7	445.6	445.0	444.4
167.5°	451.9	451.5	451.1	450.6	451.1	451.5	451.9	452.5	452.4	451.8	451.2
170°	455.6	455.1	454.6	454.1	454.6	455.1	455.6	456.2	456.1	455.5	454.9
172.5°	458.4	457.9	457.4	456.8	457.4	457.9	458.4	458.9	458.9	458.3	457.7
175°	461.5	461.0	460.5	459.9	460.5	461.0	461.5	462.0	461.9	461.3	460.7
177.5°	462.5	462.2	461.8	461.3	461.8	462.2	462.5	463.0	463.0	462.5	462.2
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	489.0	490.8	493.4	496.3	498.0	501.3	502.2	503.8	505.1	508.4	511.9
5°	460.8	463.6	470.0	473.6	478.4	484.1	487.8	491.7	496.0	503.4	510.3
7.5°	430.5	435.1	443.2	449.7	456.7	464.8	470.6	478.4	484.8	495.3	505.3
10°	410.4	416.8	424.0	431.9	441.6	450.2	458.5	468.2	476.0	488.6	500.3
12.5°	392.2	393.1	403.6	412.2	425.5	436.2	445.7	458.2	465.9	480.8	493.1
15°	360.5	366.4	375.7	382.5	398.4	411.9	425.2	438.3	447.1	465.5	481.7
17.5°	333.7	339.1	348.8	360.0	371.3	384.8	402.0	415.9	427.8	448.8	468.0
20°	316.8	323.5	333.3	344.8	354.8	369.5	384.4	400.2	413.1	436.8	459.3
22.5°	302.5	307.7	315.6	327.0	337.9	351.3	367.6	384.9	398.4	424.0	446.7
25°	282.2	286.5	291.6	301.0	313.3	328.0	340.7	359.7	379.4	403.3	430.8
27.5°	264.0	267.1	271.6	279.8	289.4	303.1	317.2	335.2	355.1	381.0	410.1
30°	252.9	254.9	259.3	266.2	275.6	286.4	300.7	317.8	338.2	364.4	393.3
32.5°	243.2	245.0	248.0	254.4	262.6	271.8	284.6	301.9	321.2	347.0	379.1
35°	228.7	230.0	232.6	237.8	242.4	251.3	262.1	277.8	295.9	320.6	353.8
37.5°	214.1	216.0	217.6	219.8	225.6	231.5	240.8	254.1	271.9	296.8	328.5
40°	204.6	206.1	208.5	209.5	214.1	219.5	227.0	239.2	257.2	279.9	310.8
42.5°	194.8	196.5	197.9	199.0	203.0	207.7	214.6	225.0	240.9	262.9	293.6
45°	181.7	181.9	183.3	185.5	187.4	190.7	195.6	204.6	216.9	237.6	265.4
47.5°	168.3	168.6	168.8	169.7	171.9	174.9	178.1	185.5	196.5	213.0	240.0
50°	159.4	159.0	159.4	160.1	161.5	164.1	167.8	173.1	182.1	197.5	222.4
52.5°	150.8	150.8	150.5	150.8	151.9	153.6	156.3	160.7	168.8	183.0	204.8
55°	137.7	136.7	136.9	136.1	137.9	138.3	140.3	144.0	151.0	160.7	181.3
57.5°	123.7	123.0	122.1	121.8	121.7	122.7	124.2	127.2	132.6	141.2	157.8
60°	114.8	113.8	112.6	112.3	112.3	112.9	113.7	115.8	120.9	128.5	142.2
62.5°	105.7	104.6	103.9	102.9	102.5	103.1	103.9	105.5	109.2	116.3	128.1
65°	91.7	90.3	89.4	89.2	88.8	88.3	88.6	90.1	93.1	98.8	108.1
67.5°	77.7	76.4	76.2	75.0	74.5	74.6	74.5	75.8	77.6	82.5	89.5
70°	68.4	67.5	67.1	66.1	65.7	65.3	64.9	66.1	67.8	72.0	78.0
72.5°	59.1	58.2	57.4	56.6	56.7	56.2	56.1	56.9	58.3	62.1	66.8
75°	45.5	45.8	44.8	43.8	43.7	43.2	43.2	43.8	44.4	47.4	51.1
77.5°	33.1	32.9	32.1	31.8	31.6	31.2	31.6	31.9	32.3	34.3	36.9
80°	25.2	25.2	24.3	24.3	24.0	23.5	24.0	23.7	24.5	26.4	28.3
82.5°	18.0	17.7	17.7	17.4	17.3	16.9	17.1	17.6	17.9	19.2	20.4
85°	8.8	8.8	8.6	8.4	8.6	8.4	8.6	8.8	9.0	9.6	10.6
87.5°	4.6	4.7	4.6	4.3	4.0	3.7	3.5	3.5	3.6	3.5	3.5
90°	13.5	13.7	11.7	9.8	7.9	6.0	4.6	3.5	2.5	1.5	0.4
92.5°	12.4	12.4	12.0	11.5	11.0	10.6	10.0	9.2	8.4	7.7	7.0
95°	25.0	25.0	24.8	24.6	24.5	24.3	23.8	22.9	22.0	21.2	20.3
97.5°	41.9	41.9	41.7	41.3	41.0	40.6	40.1	39.3	38.6	37.8	37.0
100°	53.8	53.8	53.6	53.3	53.0	52.8	52.3	51.7	50.9	50.2	49.5
102.5°	66.7	66.6	66.3	66.0	65.6	65.3	64.8	64.3	63.7	63.2	62.7
105°	86.0	85.8	85.7	85.5	85.3	85.2	84.9	84.6	84.4	84.1	83.9
107.5°	107.0	106.9	106.9	106.9	106.9	106.9	106.8	106.4	106.0	105.6	105.2
110°	121.3	121.3	121.3	121.3	121.3	121.3	121.1	120.5	120.0	119.5	119.0



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	135.8	136.0	136.0	136.1	136.2	136.3	136.0	135.5	135.0	134.5	134.0
115°	157.5	157.6	157.7	157.9	158.1	158.3	158.1	157.6	157.0	156.5	156.0
117.5°	178.7	179.0	179.4	179.9	180.5	180.9	180.8	180.1	179.4	178.7	178.1
120°	192.7	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7
122.5°	207.5	207.7	208.2	208.6	209.1	209.7	209.5	208.6	207.8	207.0	206.1
125°	229.1	229.4	229.6	229.9	230.1	230.4	230.1	229.4	228.6	227.8	227.0
127.5°	250.1	250.5	250.7	251.1	251.4	251.7	251.3	250.4	249.3	248.4	247.4
130°	264.3	264.5	264.7	264.8	265.0	265.2	264.7	263.6	262.4	261.3	260.2
132.5°	278.4	278.8	278.8	278.8	278.7	278.7	278.2	277.3	276.4	275.4	274.6
135°	298.7	298.8	298.6	298.4	298.3	298.1	297.6	296.6	295.7	294.7	293.8
137.5°	318.4	318.5	318.2	318.1	317.8	317.5	317.0	316.2	315.5	314.7	313.9
140°	331.6	331.6	331.1	330.7	330.3	329.8	329.2	328.5	327.7	326.9	326.1
142.5°	343.5	343.5	343.1	342.9	342.5	342.2	341.7	341.0	340.2	339.4	338.6
145°	361.7	361.6	361.1	360.6	360.1	359.6	359.0	358.3	357.7	357.1	356.5
147.5°	377.5	377.4	377.0	376.7	376.3	376.0	375.5	374.7	374.0	373.2	372.6
150°	387.6	387.4	387.0	386.7	386.3	386.0	385.6	385.0	384.5	384.0	383.5
152.5°	397.7	397.4	396.9	396.5	396.1	395.7	395.2	394.7	394.2	393.6	393.1
155°	410.4	410.0	409.7	409.5	409.2	409.0	408.7	408.5	408.1	407.9	407.6
157.5°	422.1	421.5	421.4	421.2	421.0	420.9	420.8	420.6	420.4	420.3	420.1
160°	429.2	428.7	428.6	428.5	428.4	428.3	428.3	428.1	427.9	427.7	427.6
162.5°	435.5	435.0	434.9	434.8	434.7	434.6	434.5	434.5	434.5	434.5	434.4
165°	443.8	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.3	443.4	443.5
167.5°	450.6	450.0	450.0	450.0	450.0	450.0	450.1	450.4	450.6	450.9	451.2
170°	454.3	453.7	453.7	453.8	453.9	454.0	454.2	454.4	454.7	455.0	455.2
172.5°	457.1	456.5	456.6	456.7	456.8	456.8	457.0	457.3	457.5	457.8	458.1
175°	460.1	459.5	459.7	459.9	460.0	460.2	460.5	460.7	461.0	461.2	461.5
177.5°	461.8	461.3	461.4	461.6	461.8	461.8	462.0	462.3	462.4	462.7	462.9
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	511.6	512.4	514.9	517.4	520.2	521.0	522.2	521.2	520.8	523.7	526.0
5°	513.1	516.5	523.4	529.7	534.9	538.6	542.6	544.2	547.1	551.1	556.3
7.5°	511.3	518.2	529.0	538.1	548.0	555.2	560.8	565.6	571.4	579.1	587.6
10°	509.5	518.7	531.8	542.9	555.1	564.3	571.9	579.4	588.0	598.7	609.8
12.5°	506.1	516.9	533.4	546.6	562.1	571.2	581.4	597.4	606.7	621.7	637.4
15°	499.1	511.3	534.2	550.4	568.0	585.2	604.2	619.4	634.6	643.5	665.6
17.5°	488.9	506.6	532.0	551.0	573.3	600.4	621.7	639.0	656.6	670.9	682.0
20°	480.5	499.9	528.9	551.6	578.2	607.3	631.7	649.4	664.6	676.6	683.4
22.5°	470.1	494.5	522.6	549.2	583.2	612.0	637.7	651.5	664.3	670.1	672.8
25°	453.6	482.9	514.8	547.3	585.6	616.1	639.6	648.0	651.7	646.0	636.6
27.5°	435.8	468.5	505.8	543.5	584.1	613.5	630.3	629.0	622.7	604.2	589.6
30°	422.5	458.5	498.5	539.8	580.5	609.1	618.8	609.1	594.8	574.3	553.3
32.5°	408.5	445.8	490.9	534.5	573.9	599.1	601.2	584.4	562.2	538.9	512.8
35°	387.4	427.7	476.5	522.6	560.0	575.8	566.5	536.7	510.5	478.6	443.0
37.5°	363.6	408.1	456.9	505.2	539.1	543.2	519.9	488.6	451.6	414.1	372.2
40°	345.8	393.0	443.2	491.9	521.9	517.5	487.8	453.4	409.4	363.6	324.7
42.5°	329.8	376.9	428.2	476.0	499.9	488.1	453.4	411.1	363.9	320.7	285.1
45°	302.2	350.7	403.1	449.3	463.0	441.6	395.7	348.7	302.2	266.2	238.1
47.5°	275.3	323.3	375.2	415.8	420.6	391.9	341.7	293.4	253.4	224.1	204.2
50°	255.6	303.8	355.2	391.4	389.8	355.2	303.6	257.6	224.1	200.4	187.2
52.5°	238.0	283.4	332.8	365.8	357.4	319.7	270.4	229.5	202.1	183.6	171.5
55°	210.4	252.5	299.5	325.9	310.6	268.7	227.0	194.2	173.8	160.0	150.6
57.5°	183.1	222.6	262.8	279.1	262.2	223.5	188.8	165.0	149.6	139.4	133.3
60°	166.3	200.7	236.4	250.6	230.4	196.0	168.6	147.3	134.9	126.6	121.1
62.5°	149.4	180.2	214.0	221.6	203.2	174.1	149.8	132.1	122.0	114.5	109.3
65°	126.3	151.6	177.2	182.3	165.3	142.8	123.6	112.1	103.1	97.6	93.5
67.5°	103.7	123.9	142.1	146.1	131.2	115.6	101.8	91.7	85.7	81.1	77.6
70°	90.1	106.2	121.1	124.4	112.4	98.6	88.0	80.0	74.5	70.6	67.2
72.5°	75.9	89.3	101.7	103.9	94.2	83.5	74.9	68.5	63.7	61.2	58.0
75°	58.1	66.0	75.5	76.1	69.7	63.2	56.6	52.4	49.9	46.8	45.2
77.5°	41.0	47.1	52.6	53.6	49.9	45.5	41.8	38.5	36.3	34.9	33.4
80°	31.3	36.2	38.6	39.9	37.2	34.0	31.9	29.7	28.3	27.4	26.4
82.5°	22.4	25.4	27.6	28.7	27.1	25.2	23.2	21.9	20.8	20.1	19.7
85°	11.4	12.7	14.1	14.5	14.1	13.3	12.1	12.1	11.5	11.4	11.4
87.5°	4.2	5.0	5.3	5.9	5.9	6.3	6.6	6.9	7.1	6.9	6.7
90°	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5	13.3
92.5°	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4	12.5
95°	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0	25.0
97.5°	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9	41.9
100°	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8	53.8
102.5°	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7	66.7
105°	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0	86.2
107.5°	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0	107.1
110°	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8	135.6
115°	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5	157.4
117.5°	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7	178.6
120°	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7	192.7
122.5°	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5	207.2
125°	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1	228.9
127.5°	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1	249.8
130°	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3	264.2
132.5°	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4	278.1
135°	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7	298.6
137.5°	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4	318.3
140°	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6	331.6
142.5°	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5	343.5
145°	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7	361.8
147.5°	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5	377.7
150°	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6	387.9
152.5°	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7	398.0
155°	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4	410.9
157.5°	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1	422.7
160°	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2	429.7
162.5°	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5	436.1
165°	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8	444.4
167.5°	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6	451.2
170°	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3	454.9
172.5°	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1	457.7
175°	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1	460.7
177.5°	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8	462.2
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	508.9	508.9	508.9	508.9	508.9	508.9	508.9
2.5°	527.9	530.0	530.0	530.4	532.9	532.5	532.4
5°	561.7	565.1	565.4	568.9	571.3	570.5	568.3
7.5°	593.7	599.9	604.6	607.2	610.3	612.2	611.3
10°	619.1	628.0	633.5	637.2	641.7	645.1	643.9
12.5°	642.0	652.7	660.3	666.7	667.2	671.5	668.6
15°	678.0	689.2	690.4	695.1	698.9	698.4	698.6
17.5°	689.7	693.4	694.1	694.2	694.3	692.9	689.9
20°	685.5	684.2	680.9	678.3	673.8	673.2	669.3
22.5°	665.5	661.2	652.8	647.3	640.3	638.5	637.4
25°	626.1	616.5	603.2	590.5	586.9	580.1	582.0
27.5°	572.0	557.1	542.6	532.4	523.0	512.7	515.7
30°	534.0	517.1	496.8	481.1	471.1	461.4	459.6
32.5°	488.6	463.9	441.3	427.5	412.2	406.0	399.2
35°	410.4	386.2	363.8	344.4	333.3	324.7	316.8
37.5°	340.0	312.3	294.1	278.4	270.4	265.4	266.7
40°	296.4	272.1	258.7	246.8	239.4	235.9	236.7
42.5°	261.0	242.8	231.9	223.7	218.4	216.5	216.0
45°	220.8	210.7	201.6	197.0	194.4	192.3	190.9
47.5°	193.5	185.1	180.0	177.3	175.0	172.9	172.8
50°	177.0	171.5	168.0	165.1	163.3	161.8	163.2
52.5°	164.5	159.5	155.9	153.3	152.7	151.3	151.2
55°	145.9	142.0	139.5	137.1	136.0	135.2	134.1
57.5°	129.0	125.3	123.0	121.5	119.2	118.5	118.1
60°	116.9	114.0	111.7	109.7	108.7	107.2	107.2
62.5°	105.8	102.9	100.7	99.3	97.6	97.0	97.2
65°	89.8	87.4	85.2	83.7	83.3	82.1	82.6
67.5°	75.0	73.4	71.1	70.3	69.6	69.0	68.4
70°	65.1	63.5	62.4	61.2	60.6	60.6	60.6
72.5°	56.8	54.9	54.2	52.8	53.1	52.5	51.8
75°	44.0	42.8	42.3	41.7	40.7	40.7	40.7
77.5°	32.4	32.0	31.3	30.7	30.5	30.3	30.4
80°	25.1	24.8	24.5	24.5	24.0	23.8	23.5
82.5°	19.3	18.8	18.5	18.3	18.3	18.3	18.2
85°	10.9	10.6	10.6	10.8	10.3	10.3	10.6
87.5°	6.9	6.8	6.6	6.6	6.8	6.7	6.7
90°	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.1	120.9	120.6	120.4	120.1



TEST NUMBER: P331466-935

CATALOG NUMBER: S122DIW-S290D435U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)