

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331482-935

Luminaire Tested: **S122DIW-S290D970U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331482-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S290D970U935-4F0-1E-UDD-F1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 3928.6 lumens  
Efficiency: N/A  
Efficacy: 103.4 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 38  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

### Luminous Intensity Polar Plot





TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29	22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6567	6567	6567
5°	6592	6498	6536
10°	6555	6432	6465
15°	6472	6349	6342
20°	6357	6223	6216
25°	6242	6070	6070
30°	6096	5929	5876
35°	5960	5757	5673
40°	5788	5590	5482
45°	5617	5421	5286
50°	5433	5247	5061
55°	5239	5044	4856
60°	5028	4799	4624
65°	4795	4558	4348
70°	4504	4263	4060
75°	4099	3924	3830
80°	3636	3533	3347
85°	2964	2816	2538



TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	38.3	1.0
10°-20°	107.6	2.7
20°-30°	158.2	4.0
30°-40°	183.8	4.7
40°-50°	183.6	4.7
50°-60°	160.1	4.1
60°-70°	118.4	3.0
70°-80°	67.0	1.7
80°-90°	22.1	0.6
90°-100°	65.5	1.7
100°-110°	203.4	5.2
110°-120°	347.6	8.8
120°-130°	457.2	11.6
130°-140°	513.1	13.1
140°-150°	503.1	12.8
150°-160°	422.0	10.7
160°-170°	279.9	7.1
170°-180°	97.8	2.5
0°-30°	304.1	7.7
0°-40°	487.8	12.4
0°-60°	831.5	21.2
0°-90°	1039.0	26.4
90°-120°	616.5	15.7
90°-150°	2089.9	53.2
90°-180°	2890.0	73.6
0°-180°	3928.6	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	407	407	407	407	407	
5°	407	405	401	404	403	39
15°	387	385	380	381	379	109
25°	350	347	341	341	341	161
35°	302	298	292	290	288	189
45°	246	243	237	233	232	190
55°	186	184	179	175	172	166
65°	126	123	119	116	114	124
75°	66	65	63	61	61	70
85°	16	16	15	14	14	18
90°	1	12	30	29	30	3
95°	45	54	56	56	54	52
105°	188	190	192	194	194	198
115°	349	354	352	351	349	345
125°	508	515	513	510	509	453
135°	657	666	668	667	664	507
145°	797	803	808	809	806	498
155°	911	914	916	920	918	419
165°	992	991	991	996	992	280
175°	1032	1029	1027	1033	1028	98
180°	1033	1033	1033	1033	1033	



TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	408.6	408.3	407.9	407.6	407.3	406.7	406.0	405.2	404.4	403.6	404.3
5°	406.7	406.4	406.0	405.7	405.4	404.8	403.8	402.9	401.8	400.9	401.6
7.5°	403.2	402.6	402.1	401.6	401.1	400.3	399.3	398.3	397.4	396.4	397.1
10°	399.8	399.2	398.6	398.0	397.3	396.5	395.5	394.4	393.4	392.3	393.0
12.5°	395.0	394.5	394.0	393.4	392.9	392.1	391.1	390.0	389.0	388.0	388.4
15°	387.2	386.7	386.2	385.6	385.1	384.4	383.1	382.0	380.9	379.8	380.1
17.5°	377.2	376.7	376.2	375.7	375.1	374.3	373.2	372.0	370.8	369.7	370.1
20°	370.0	369.5	368.9	368.4	367.9	367.0	365.8	364.6	363.4	362.2	362.5
22.5°	362.8	362.1	361.4	360.6	359.9	359.0	357.8	356.6	355.5	354.4	354.4
25°	350.4	349.7	349.0	348.4	347.7	346.6	345.1	343.6	342.2	340.7	340.9
27.5°	336.4	335.8	335.1	334.5	333.9	332.9	331.8	330.6	329.5	328.3	328.0
30°	327.0	326.3	325.6	324.9	324.2	323.2	321.9	320.6	319.3	318.0	317.7
32.5°	316.9	316.4	315.9	315.3	314.8	313.7	312.4	311.1	309.7	308.3	307.8
35°	302.4	301.4	300.6	299.7	298.9	297.7	296.4	295.0	293.6	292.1	291.6
37.5°	285.9	285.1	284.3	283.5	282.8	281.7	280.3	279.0	277.5	276.1	275.5
40°	274.6	273.9	273.2	272.5	271.8	270.8	269.3	267.9	266.6	265.2	264.4
42.5°	263.6	262.9	262.3	261.6	260.9	259.8	258.4	257.0	255.6	254.3	253.4
45°	246.0	245.4	244.8	244.2	243.6	242.6	241.3	240.0	238.8	237.4	236.4
47.5°	228.5	227.9	227.4	226.8	226.2	225.2	223.9	222.6	221.2	219.8	218.8
50°	216.3	215.9	215.4	215.0	214.6	213.7	212.5	211.3	210.1	208.9	207.7
52.5°	204.4	203.8	203.3	202.7	202.1	201.2	200.1	199.0	197.8	196.7	195.6
55°	186.1	185.6	185.1	184.6	184.1	183.3	182.3	181.2	180.2	179.2	178.1
57.5°	167.9	167.5	167.0	166.6	166.2	165.4	164.3	163.2	162.0	160.8	159.8
60°	155.7	155.3	155.0	154.6	154.3	153.5	152.3	151.1	149.8	148.6	147.7
62.5°	143.8	143.2	142.7	142.2	141.5	140.8	139.8	139.0	138.0	137.1	136.1
65°	125.5	125.0	124.5	124.0	123.5	122.8	121.9	121.1	120.2	119.3	118.5
67.5°	107.0	106.6	106.2	105.7	105.4	104.8	103.9	103.1	102.4	101.6	101.0
70°	95.4	95.1	94.7	94.4	94.0	93.5	92.7	92.0	91.1	90.3	89.7
72.5°	83.5	83.2	82.8	82.5	82.1	81.7	81.2	80.8	80.2	79.7	79.1
75°	65.7	65.5	65.3	65.2	65.0	64.7	64.3	63.8	63.4	62.9	62.4
77.5°	49.8	49.4	49.2	48.9	48.6	48.3	48.1	48.0	47.8	47.6	47.4
80°	39.1	39.0	38.9	38.8	38.7	38.7	38.5	38.3	38.1	38.0	37.7
82.5°	29.1	29.1	29.1	29.0	29.0	28.9	28.8	28.8	28.7	28.6	28.2
85°	16.0	15.9	15.8	15.8	15.7	15.6	15.5	15.4	15.3	15.2	15.0
87.5°	5.8	6.1	6.5	6.8	7.1	7.7	8.4	9.0	9.7	10.5	10.2
90°	0.9	3.2	5.5	7.8	10.2	13.4	17.7	22.0	26.3	30.5	30.1
92.5°	15.5	17.2	18.9	20.7	22.4	23.7	24.7	25.7	26.7	27.7	27.8
95°	45.4	47.3	49.2	51.1	53.1	54.2	54.7	55.0	55.4	55.8	55.8
97.5°	82.8	84.6	86.3	88.0	89.6	90.9	91.6	92.4	93.1	93.8	93.8
100°	110.7	112.3	113.8	115.4	116.9	118.0	118.6	119.2	119.8	120.4	120.4
102.5°	140.1	141.3	142.5	143.8	145.0	146.0	146.7	147.5	148.2	149.0	149.1
105°	187.5	188.0	188.6	189.2	189.9	190.3	190.7	191.1	191.5	191.8	192.3
107.5°	235.3	236.2	236.9	237.8	238.7	239.1	239.1	239.1	239.1	239.1	239.3
110°	266.0	267.2	268.3	269.5	270.6	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.5	300.7	301.8	303.0	304.1	304.6	304.4	304.3	304.2	304.0	303.5
115°	348.8	350.0	351.1	352.3	353.4	353.9	353.4	353.1	352.7	352.3	352.1
117.5°	398.0	399.6	401.1	402.7	404.2	404.4	403.4	402.3	401.2	400.1	399.7
120°	430.8	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	430.8
122.5°	460.8	462.7	464.5	466.4	468.2	468.6	467.5	466.5	465.4	464.3	463.8
125°	507.6	509.3	511.0	512.8	514.5	515.1	514.5	513.9	513.3	512.8	512.2
127.5°	553.1	555.3	557.5	559.7	561.9	562.7	562.0	561.3	560.6	559.9	559.1
130°	581.7	584.2	586.7	589.3	591.8	592.8	592.5	592.0	591.7	591.2	590.9
132.5°	613.7	615.8	617.9	619.9	622.0	623.0	623.1	623.2	623.3	623.4	622.5
135°	656.7	658.8	660.9	663.1	665.2	666.4	666.8	667.2	667.6	668.0	667.8
137.5°	701.8	703.6	705.3	707.1	708.8	710.0	710.4	710.9	711.4	712.0	711.8
140°	729.0	730.8	732.5	734.3	736.0	737.4	738.4	739.3	740.3	741.2	741.2
142.5°	757.0	758.7	760.4	762.2	764.0	765.2	765.8	766.5	767.2	767.8	767.9
145°	797.0	798.4	799.8	801.2	802.5	803.7	804.9	806.1	807.3	808.4	808.6
147.5°	832.8	834.5	836.1	837.7	839.3	840.5	841.3	842.1	842.8	843.6	844.0
150°	857.2	858.4	859.5	860.7	861.9	862.9	863.7	864.4	865.2	866.0	866.5
152.5°	878.9	880.0	881.2	882.4	883.6	884.6	885.5	886.4	887.3	888.3	889.0
155°	911.3	911.9	912.5	913.1	913.6	914.2	914.8	915.4	915.9	916.5	917.5
157.5°	939.0	939.4	939.8	940.2	940.6	941.0	941.3	941.7	942.0	942.4	943.7
160°	955.8	956.1	956.6	956.9	957.3	957.6	957.9	958.0	958.2	958.4	959.6
162.5°	971.1	971.2	971.3	971.4	971.5	971.6	971.8	972.0	972.2	972.3	973.7
165°	991.5	991.4	991.2	990.9	990.8	990.7	990.7	990.7	990.7	990.7	992.0
167.5°	1008.7	1008.1	1007.5	1006.9	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2
170°	1017.7	1017.1	1016.6	1016.0	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5
172.5°	1024.0	1023.4	1022.8	1022.3	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8
175°	1031.7	1031.0	1030.5	1029.9	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6
177.5°	1034.8	1034.3	1033.9	1033.4	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	406.7	406.7	406.7	406.7	406.7	406.7	406.7	406.7
2.5°	405.0	405.7	406.4	406.7	406.6	406.4	406.3	406.1
5°	402.3	403.0	403.7	404.0	403.8	403.6	403.5	403.3
7.5°	397.8	398.5	399.2	399.4	399.2	399.0	398.8	398.6
10°	393.7	394.4	395.1	395.3	395.0	394.8	394.5	394.3
12.5°	388.9	389.3	389.9	390.0	389.9	389.6	389.4	389.3
15°	380.5	380.8	381.2	381.2	380.7	380.3	379.9	379.4
17.5°	370.5	370.9	371.3	371.3	370.8	370.5	370.1	369.6
20°	362.7	363.0	363.3	363.2	362.8	362.5	362.1	361.8
22.5°	354.5	354.6	354.6	354.5	354.3	354.0	353.9	353.7
25°	341.0	341.2	341.4	341.4	341.2	341.0	340.9	340.7
27.5°	327.8	327.5	327.3	326.9	326.5	326.1	325.7	325.3
30°	317.5	317.2	316.9	316.7	316.3	316.0	315.6	315.2
32.5°	307.4	306.9	306.4	306.0	305.7	305.3	305.0	304.6
35°	291.1	290.6	290.1	289.6	289.2	288.8	288.3	287.8
37.5°	274.8	274.2	273.5	273.0	272.6	272.2	271.8	271.4
40°	263.6	262.9	262.1	261.5	261.1	260.8	260.5	260.1
42.5°	252.5	251.7	250.8	250.1	249.7	249.2	248.7	248.2
45°	235.5	234.5	233.6	232.9	232.6	232.2	231.9	231.5
47.5°	217.8	216.8	215.8	215.0	214.6	214.0	213.5	213.0
50°	206.5	205.2	204.0	203.2	202.8	202.3	201.9	201.5
52.5°	194.7	193.6	192.6	191.8	191.2	190.7	190.1	189.5
55°	177.0	176.0	175.0	174.3	173.8	173.3	172.9	172.5
57.5°	158.8	157.7	156.7	156.0	155.8	155.4	155.1	154.7
60°	146.7	145.8	144.8	144.2	144.0	143.7	143.4	143.2
62.5°	135.3	134.4	133.5	132.9	132.6	132.2	131.9	131.6
65°	117.7	116.9	116.1	115.5	115.1	114.7	114.3	113.8
67.5°	100.4	99.8	99.2	98.7	98.3	98.0	97.6	97.3
70°	89.1	88.5	87.9	87.5	87.1	86.7	86.4	86.0
72.5°	78.5	77.9	77.3	76.8	76.5	76.3	76.0	75.7
75°	61.9	61.4	60.9	60.7	60.9	61.0	61.2	61.4
77.5°	47.1	46.8	46.6	46.3	46.1	45.9	45.6	45.4
80°	37.5	37.2	36.9	36.7	36.5	36.3	36.2	36.0
82.5°	27.9	27.6	27.2	27.0	27.0	26.9	26.9	26.9
85°	14.7	14.5	14.2	14.0	13.9	13.9	13.8	13.7
87.5°	9.9	9.6	9.3	9.2	9.1	9.1	9.1	9.0
90°	29.7	29.4	28.9	28.8	29.1	29.3	29.4	29.6
92.5°	27.9	28.0	28.1	28.1	28.2	28.2	28.2	28.2
95°	55.8	55.8	55.8	55.6	55.2	54.8	54.4	54.1
97.5°	93.8	93.8	93.8	93.8	93.8	93.8	93.7	93.7
100°	120.4	120.4	120.4	120.3	120.0	119.9	119.7	119.5
102.5°	149.3	149.4	149.6	149.6	149.4	149.1	149.0	148.8
105°	192.6	193.0	193.4	193.6	193.6	193.6	193.6	193.6
107.5°	239.4	239.6	239.7	239.4	238.5	237.5	236.7	235.8
110°	271.2	271.2	271.2	271.0	270.4	269.8	269.1	268.6





TEST NUMBER: P331482-935

CATALOG NUMBER: S122DIW-S290D970U935-4F0-1E-UDD-F1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	303.1	302.6	302.1	301.7	301.3	300.8	300.4	300.0
115°	351.9	351.7	351.5	351.1	350.6	350.0	349.4	348.8
117.5°	399.2	398.7	398.2	397.7	397.2	396.6	396.0	395.4
120°	430.8	430.8	430.8	430.5	429.9	429.4	428.8	428.2
122.5°	463.4	462.9	462.4	462.0	461.6	461.2	460.7	460.3
125°	511.6	511.0	510.5	510.1	509.9	509.7	509.5	509.3
127.5°	558.4	557.8	557.1	556.4	555.8	555.2	554.6	554.0
130°	590.5	590.1	589.7	589.1	588.3	587.5	586.8	586.0
132.5°	621.6	620.8	619.9	619.2	618.6	617.9	617.3	616.7
135°	667.6	667.4	667.2	666.8	666.2	665.6	665.1	664.5
137.5°	711.6	711.5	711.4	710.8	710.1	709.3	708.5	707.7
140°	741.2	741.2	741.2	740.9	740.1	739.3	738.6	737.8
142.5°	768.1	768.3	768.4	768.1	767.3	766.5	765.8	765.0
145°	808.8	809.0	809.2	808.9	808.1	807.4	806.6	805.8
147.5°	844.5	844.9	845.3	845.2	844.5	843.7	843.0	842.2
150°	867.1	867.7	868.3	868.3	867.7	867.1	866.5	866.0
152.5°	889.8	890.5	891.2	891.2	890.5	889.8	889.0	888.3
155°	918.5	919.5	920.4	920.6	920.1	919.5	918.9	918.3
157.5°	945.0	946.3	947.6	947.8	946.9	946.0	945.0	944.1
160°	960.7	961.9	963.0	963.3	962.5	961.7	961.0	960.2
162.5°	975.0	976.3	977.7	977.8	976.9	975.9	975.0	974.1
165°	993.4	994.7	996.1	996.3	995.3	994.4	993.4	992.4
167.5°	1008.6	1010.0	1011.2	1011.4	1010.5	1009.4	1008.4	1007.5
170°	1016.9	1018.3	1019.7	1019.8	1018.6	1017.4	1016.2	1015.1
172.5°	1023.2	1024.6	1025.9	1026.1	1024.8	1023.7	1022.5	1021.4
175°	1030.0	1031.4	1032.7	1032.9	1031.7	1030.5	1029.3	1028.2
177.5°	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4

(END OF REPORT)