

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331830-830

Luminaire Tested: **S122RDIW-S865D710U830-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331830-830  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S865D710U830-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5431.3 lumens  
Efficiency: N/A  
Efficacy: 101.3 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 53.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43
3	85	76	69	63	79	71	65	60	62	58	54	54	50	48	46	44	42	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	33
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	29061	29061	29061	29061
5°	32456	29242	25929	29242
10°	36008	29037	22474	29037
15°	37778	28612	17708	28612
20°	32752	27981	15323	27981
25°	21480	27118	13682	27118
30°	14458	26071	12381	26071
35°	11710	24750	11168	24750
40°	10414	23317	10334	23317
45°	9423	21633	9225	21633
50°	8578	19964	8545	19964
55°	8062	18117	7958	18117
60°	6746	16417	6665	16417
65°	5685	14907	6449	14907
70°	5254	13312	6080	13312
75°	4916	11591	5614	11591
80°	4537	9530	5002	9530
85°	4168	7521	4409	7521



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.6	3.1
10°-20°	475.4	8.8
20°-30°	612.6	11.3
30°-40°	582.2	10.7
40°-50°	498.7	9.2
50°-60°	379.8	7.0
60°-70°	240.1	4.4
70°-80°	119.9	2.2
80°-90°	34.5	0.6
90°-100°	52.5	1.0
100°-110°	163.1	3.0
110°-120°	278.8	5.1
120°-130°	366.6	6.8
130°-140°	411.5	7.6
140°-150°	403.5	7.4
150°-160°	338.4	6.2
160°-170°	224.5	4.1
170°-180°	78.5	1.4
0°-30°	1258.6	23.2
0°-40°	1840.8	33.9
0°-60°	2719.4	50.1
0°-90°	3113.9	57.3
90°-120°	494.4	9.1
90°-150°	1676.1	30.9
90°-180°	2317.0	42.7
0°-180°	5431.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1800	1800	1800	1800	1800	
5°	2002	1804	1600	1804	2002	198
15°	2260	1712	1059	1712	2260	610
25°	1206	1522	768	1522	1206	572
35°	594	1256	567	1256	594	380
45°	413	947	404	947	413	319
55°	286	644	283	644	286	251
65°	149	390	169	390	149	152
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	24	1	24	1	24	11
95°	43	36	43	36	43	48
105°	155	150	155	150	155	163
115°	280	280	280	280	280	276
125°	408	407	408	407	408	364
135°	533	527	533	527	533	410
145°	646	639	646	639	646	404
155°	736	731	736	731	736	339
165°	796	795	796	795	796	224
175°	825	827	825	827	825	78
180°	829	829	829	829	829	



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1872.9	1874.4	1875.9	1872.4	1872.4	1869.4	1862.9	1857.9	1843.9	1841.9	1841.9
5°	2002.5	2001.2	2003.8	1995.6	1984.3	1981.9	1970.0	1954.4	1938.1	1920.0	1916.2
7.5°	2131.3	2129.4	2124.4	2123.1	2114.4	2095.6	2076.4	2056.1	2029.0	2002.6	1989.3
10°	2196.3	2217.0	2204.5	2182.6	2187.0	2157.6	2141.9	2115.1	2092.5	2053.1	2044.4
12.5°	2260.4	2268.5	2264.6	2252.1	2246.6	2226.1	2205.0	2181.6	2140.0	2104.7	2073.9
15°	2260.1	2272.0	2275.1	2271.4	2274.5	2273.3	2262.0	2242.6	2206.4	2167.6	2133.8
17.5°	2093.3	2101.6	2122.0	2135.9	2153.4	2190.5	2208.8	2215.8	2210.5	2188.3	2164.5
20°	1906.2	1892.4	1949.9	1979.3	2004.3	2066.9	2120.7	2141.4	2174.4	2173.9	2167.6
22.5°	1641.0	1644.3	1698.8	1733.7	1806.8	1869.3	1930.6	2008.3	2072.4	2114.8	2139.6
25°	1205.7	1229.5	1283.9	1331.4	1412.8	1529.1	1634.7	1757.4	1873.0	1964.4	2051.3
27.5°	905.6	907.3	950.5	994.4	1042.6	1137.9	1271.0	1417.4	1582.3	1718.4	1875.0
30°	775.5	771.8	789.9	816.7	858.0	931.8	1031.9	1175.7	1340.2	1545.3	1728.0
32.5°	683.4	683.6	697.3	717.2	751.5	801.3	869.8	986.7	1142.1	1343.7	1557.8
35°	594.1	593.5	603.5	617.8	632.3	664.1	711.1	772.3	879.3	1067.5	1286.4
37.5°	530.1	532.8	537.7	546.7	562.6	580.3	608.5	649.7	725.9	837.2	1021.2
40°	494.1	495.3	502.2	509.7	519.1	532.8	556.0	589.1	644.8	733.6	868.0
42.5°	461.0	462.3	467.1	474.2	481.5	495.3	514.4	543.1	588.2	657.5	768.5
45°	412.7	412.7	417.2	420.3	428.4	440.9	456.6	480.3	511.5	562.9	636.7
47.5°	367.5	367.6	370.5	375.9	381.0	390.8	406.1	425.6	448.3	488.0	551.0
50°	341.5	342.0	343.9	348.4	351.5	360.2	372.1	389.0	412.7	443.4	496.0
52.5°	320.5	320.1	322.4	324.3	326.5	332.7	341.6	356.5	377.8	404.4	447.9
55°	286.4	283.9	287.7	290.8	292.7	295.2	300.2	309.5	327.7	350.2	382.8
57.5°	243.9	242.9	245.5	248.4	254.3	261.0	265.3	271.3	280.7	296.8	329.0
60°	208.9	208.9	214.5	216.4	223.3	232.1	240.8	245.8	255.1	265.8	289.5
62.5°	177.9	178.3	181.0	182.9	186.7	197.5	209.7	220.7	229.6	239.8	255.5
65°	148.8	150.1	150.1	151.4	153.8	156.4	161.4	170.1	185.8	200.1	212.0
67.5°	126.3	126.7	127.1	128.4	128.9	131.7	133.7	137.6	141.2	154.9	169.6
70°	111.3	113.2	112.5	113.9	114.4	115.6	118.2	120.1	125.7	128.8	137.6
72.5°	97.3	98.7	98.6	99.3	100.9	101.2	103.2	105.1	108.7	111.3	116.0
75°	78.8	78.1	78.8	80.0	80.7	81.3	81.3	83.8	85.7	88.2	91.3
77.5°	60.8	61.5	61.3	61.5	61.5	62.7	62.6	63.6	65.5	66.8	68.3
80°	48.8	49.4	48.8	49.4	50.0	50.6	50.0	50.6	52.5	53.8	53.8
82.5°	37.8	37.9	38.3	38.4	38.5	38.6	39.5	39.7	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.1	22.5	22.5	23.1	23.1	23.1
87.5°	12.7	13.2	13.2	13.2	13.1	13.2	13.2	13.8	13.4	13.9	12.7
90°	23.8	23.7	23.5	23.3	23.2	23.3	23.6	23.8	24.1	24.5	21.0
92.5°	22.6	22.6	22.6	22.5	22.5	22.5	22.4	22.3	22.3	22.2	21.4
95°	43.4	43.6	44.0	44.3	44.6	44.8	44.8	44.8	44.8	44.8	44.5
97.5°	75.1	75.1	75.2	75.2	75.2	75.2	75.2	75.2	75.2	75.2	74.6
100°	95.9	96.0	96.1	96.3	96.4	96.5	96.5	96.5	96.5	96.5	96.0
102.5°	119.3	119.5	119.6	119.8	120.0	120.0	119.8	119.7	119.6	119.4	118.9
105°	155.2	155.2	155.2	155.2	155.2	155.1	154.8	154.5	154.2	153.9	153.5
107.5°	189.2	189.8	190.6	191.2	192.0	192.3	192.2	192.0	191.9	191.8	191.8
110°	215.5	215.8	216.3	216.8	217.3	217.5	217.5	217.5	217.5	217.5	217.5



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	240.6	240.9	241.3	241.7	242.0	242.3	242.7	243.1	243.5	243.8	243.9
115°	279.7	280.2	280.7	281.2	281.6	281.9	282.1	282.3	282.4	282.6	282.9
117.5°	317.1	317.5	318.0	318.5	319.0	319.4	319.8	320.2	320.6	320.9	321.8
120°	343.4	343.8	344.3	344.8	345.3	345.5	345.5	345.5	345.5	345.5	346.8
122.5°	369.2	369.5	369.9	370.1	370.5	370.9	371.3	371.6	372.0	372.4	373.2
125°	408.5	408.6	408.8	409.0	409.1	409.3	409.8	410.3	410.8	411.2	411.7
127.5°	444.3	444.8	445.3	445.7	446.3	446.8	447.3	447.9	448.5	449.0	449.6
130°	470.0	470.6	471.3	471.8	472.5	473.0	473.3	473.6	473.9	474.2	474.5
132.5°	494.6	495.1	495.6	496.2	496.6	497.2	497.9	498.6	499.3	499.9	499.9
135°	532.9	533.4	533.9	534.3	534.8	535.2	535.3	535.5	535.6	535.7	535.5
137.5°	567.6	568.3	568.9	569.5	570.1	570.5	570.6	570.7	570.9	571.0	570.6
140°	591.7	592.3	593.0	593.6	594.2	594.5	594.5	594.5	594.5	594.5	593.7
142.5°	613.5	614.2	614.7	615.4	616.0	616.2	616.1	616.0	615.9	615.8	615.2
145°	646.3	646.9	647.5	648.1	648.8	648.9	648.8	648.7	648.5	648.4	647.4
147.5°	675.5	676.1	676.7	677.3	677.9	678.0	677.6	677.3	676.9	676.7	676.0
150°	694.6	695.0	695.4	695.9	696.4	696.4	695.9	695.4	695.0	694.6	693.9
152.5°	712.5	713.0	713.6	714.2	714.8	714.8	714.2	713.6	713.0	712.5	711.7
155°	736.5	737.0	737.4	737.9	738.4	738.2	737.4	736.6	735.8	735.1	734.6
157.5°	757.1	757.9	758.7	759.4	760.2	760.0	758.9	757.9	756.9	755.8	755.5
160°	770.1	770.7	771.3	771.9	772.5	772.4	771.5	770.5	769.6	768.6	768.5
162.5°	781.3	782.0	782.8	783.4	784.2	784.1	783.1	781.9	780.9	779.9	779.7
165°	796.0	796.7	797.5	798.2	799.1	798.9	797.8	796.7	795.6	794.6	794.6
167.5°	807.9	808.8	809.5	810.4	811.2	811.1	809.9	808.9	807.8	806.7	806.7
170°	814.1	815.0	816.0	816.9	817.8	817.7	816.7	815.6	814.5	813.4	813.6
172.5°	819.2	820.1	821.0	822.0	822.8	822.8	821.7	820.7	819.5	818.4	818.6
175°	824.6	825.6	826.5	827.4	828.3	828.3	827.2	826.0	825.0	823.9	824.3
177.5°	827.1	827.8	828.6	829.3	830.1	830.1	829.3	828.6	827.8	827.1	827.4
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1842.9	1838.9	1835.4	1826.4	1821.8	1811.8	1810.3	1809.9	1796.9	1784.3	1780.8
5°	1906.2	1896.2	1881.1	1863.7	1845.5	1826.7	1814.2	1804.2	1779.2	1755.5	1741.7
7.5°	1970.0	1948.4	1922.6	1889.4	1861.8	1830.8	1807.7	1787.1	1751.6	1717.6	1694.7
10°	2017.5	1982.4	1948.0	1902.4	1866.8	1831.7	1799.2	1771.1	1731.1	1686.0	1654.2
12.5°	2047.0	2008.5	1961.1	1916.5	1870.3	1825.7	1782.3	1746.1	1699.0	1652.6	1614.6
15°	2086.9	2045.6	1988.1	1924.3	1864.9	1806.8	1756.7	1711.7	1650.4	1594.7	1548.4
17.5°	2119.6	2062.8	2001.0	1927.2	1858.4	1784.5	1720.0	1662.6	1594.3	1527.2	1472.6
20°	2130.1	2073.8	2002.5	1928.7	1847.4	1760.5	1691.0	1628.5	1555.3	1482.1	1419.7
22.5°	2123.5	2079.8	2000.5	1912.1	1828.9	1738.0	1659.5	1587.0	1505.8	1431.2	1358.6
25°	2079.4	2064.4	1989.3	1893.0	1798.0	1692.3	1601.6	1522.2	1429.6	1349.6	1270.7
27.5°	1976.5	2008.8	1962.4	1859.7	1754.1	1640.8	1538.8	1448.4	1352.4	1262.3	1183.7
30°	1877.5	1951.8	1931.8	1836.7	1718.5	1607.2	1492.8	1398.4	1295.8	1203.2	1125.7
32.5°	1741.8	1864.7	1884.3	1804.8	1682.5	1560.2	1440.3	1346.3	1239.3	1141.7	1066.1
35°	1526.0	1709.8	1794.2	1743.6	1621.0	1489.0	1365.2	1255.7	1148.2	1051.9	976.9
37.5°	1268.4	1518.8	1659.5	1663.1	1550.6	1413.3	1278.6	1169.9	1059.8	965.3	884.0
40°	1101.3	1372.7	1555.9	1596.6	1501.6	1353.3	1217.0	1106.3	998.7	906.2	813.0
42.5°	951.2	1221.6	1446.9	1517.6	1442.0	1294.8	1158.0	1042.3	937.7	850.2	755.0
45°	769.2	1005.6	1253.9	1380.3	1338.3	1202.0	1057.5	947.4	849.2	773.6	682.3
47.5°	648.9	815.5	1055.7	1226.6	1225.9	1101.5	959.3	853.9	762.8	691.9	618.0
50°	580.3	725.5	928.7	1122.6	1138.8	1034.3	899.3	794.8	709.8	635.4	576.0
52.5°	518.8	638.4	821.1	1007.0	1053.3	962.8	831.8	735.4	652.8	584.4	533.5
55°	438.4	530.9	669.8	843.7	913.7	849.9	733.6	643.6	576.6	519.1	475.3
57.5°	370.9	440.3	551.7	691.6	773.3	733.1	637.2	564.0	506.7	454.7	420.1
60°	328.3	385.2	479.7	596.6	686.6	658.6	576.6	508.4	459.7	414.6	382.1
62.5°	288.3	337.2	418.1	513.0	595.6	584.0	517.1	459.9	417.2	376.1	348.6
65°	232.1	267.7	330.8	405.3	471.6	477.2	429.0	390.2	352.1	319.6	295.2
67.5°	184.7	208.0	252.5	315.2	364.9	382.6	353.2	323.6	293.3	268.2	247.0
70°	155.7	174.5	207.0	257.7	303.3	322.1	305.2	282.0	255.8	235.2	217.0
72.5°	126.2	144.5	168.4	205.7	244.8	265.0	259.2	242.5	221.2	204.2	187.0
75°	95.1	100.7	117.0	141.9	172.6	190.1	194.5	185.8	168.8	155.7	145.7
77.5°	70.3	73.7	81.4	94.5	114.6	130.2	136.6	135.5	123.9	116.3	107.0
80°	56.3	58.2	61.9	67.6	82.6	98.2	102.5	102.5	94.4	91.3	81.9
82.5°	42.8	44.1	46.4	49.5	56.6	70.1	75.0	76.1	70.9	66.8	59.4
85°	24.4	23.8	25.0	26.9	28.2	31.9	39.4	40.6	39.4	34.4	32.5
87.5°	12.1	11.9	11.1	10.2	10.3	10.4	12.5	14.6	13.0	11.9	11.3
90°	17.6	14.2	10.8	8.2	6.3	4.4	2.5	0.7	2.5	4.4	6.3
92.5°	20.6	19.8	19.0	17.9	16.6	15.2	13.9	12.4	13.9	15.2	16.6
95°	44.1	43.8	43.5	42.6	41.0	39.5	37.9	36.4	37.9	39.5	41.0
97.5°	74.1	73.5	72.9	71.9	70.5	69.2	67.8	66.4	67.8	69.2	70.5
100°	95.6	95.1	94.6	93.8	92.6	91.3	90.1	88.8	90.1	91.3	92.6
102.5°	118.3	117.7	117.1	116.3	115.3	114.3	113.3	112.4	113.3	114.3	115.3
105°	153.3	153.0	152.6	152.2	151.7	151.3	150.8	150.3	150.8	151.3	151.7
107.5°	191.8	191.8	191.8	191.4	190.8	190.1	189.4	188.7	189.4	190.1	190.8
110°	217.5	217.5	217.5	217.1	216.1	215.2	214.2	213.3	214.2	215.2	216.1





TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	244.0	244.2	244.3	243.9	243.0	242.0	241.1	240.2	241.1	242.0	243.0
115°	283.1	283.5	283.8	283.5	282.6	281.6	280.7	279.7	280.7	281.6	282.6
117.5°	322.6	323.5	324.3	324.1	322.9	321.7	320.5	319.2	320.5	321.7	322.9
120°	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5	346.8	348.0	349.2
122.5°	374.1	374.9	375.9	375.5	374.0	372.6	371.1	369.6	371.1	372.6	374.0
125°	412.2	412.6	413.1	412.6	411.2	409.8	408.5	407.1	408.5	409.8	411.2
127.5°	450.2	450.7	451.3	450.6	448.8	447.1	445.4	443.6	445.4	447.1	448.8
130°	474.9	475.1	475.4	474.6	472.6	470.5	468.5	466.5	468.5	470.5	472.6
132.5°	499.8	499.7	499.7	498.8	497.2	495.6	493.9	492.3	493.9	495.6	497.2
135°	535.2	534.8	534.5	533.5	531.8	530.1	528.4	526.7	528.4	530.1	531.8
137.5°	570.2	569.8	569.4	568.4	567.1	565.7	564.3	562.9	564.3	565.7	567.1
140°	593.0	592.2	591.4	590.3	588.9	587.5	586.1	584.8	586.1	587.5	588.9
142.5°	614.7	614.2	613.7	612.7	611.3	609.9	608.5	607.1	608.5	609.9	611.3
145°	646.5	645.5	644.6	643.7	642.5	641.4	640.4	639.2	640.4	641.4	642.5
147.5°	675.3	674.8	674.1	673.2	671.8	670.5	669.2	668.0	669.2	670.5	671.8
150°	693.2	692.7	692.0	691.3	690.3	689.4	688.4	687.5	688.4	689.4	690.3
152.5°	711.0	710.2	709.5	708.6	707.7	706.7	705.8	704.8	705.8	706.7	707.7
155°	734.1	733.7	733.2	732.7	732.3	731.8	731.3	730.8	731.3	731.8	732.3
157.5°	755.3	755.0	754.7	754.4	754.0	753.8	753.5	753.1	753.5	753.8	754.0
160°	768.4	768.2	768.1	767.8	767.5	767.1	766.9	766.6	766.9	767.1	767.5
162.5°	779.6	779.4	779.2	779.1	779.0	779.0	778.9	778.8	778.9	779.0	779.0
165°	794.6	794.6	794.6	794.7	794.8	794.9	795.0	795.2	795.0	794.9	794.8
167.5°	806.7	806.8	806.8	807.1	807.6	808.0	808.5	809.0	808.5	808.0	807.6
170°	813.7	813.9	814.1	814.4	814.8	815.3	815.8	816.2	815.8	815.3	814.8
172.5°	818.8	818.9	819.1	819.4	819.8	820.3	820.8	821.2	820.8	820.3	819.8
175°	824.5	824.8	825.2	825.6	826.0	826.5	827.0	827.4	827.0	826.5	826.0
177.5°	827.6	827.8	828.1	828.4	828.8	829.2	829.5	829.9	829.5	829.2	828.8
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1774.3	1770.8	1764.3	1754.4	1748.3	1737.9	1730.8	1734.8	1735.8	1734.8	1733.8
5°	1726.6	1713.5	1695.4	1677.9	1661.6	1644.2	1634.1	1629.8	1621.0	1616.0	1613.5
7.5°	1669.1	1646.4	1620.7	1590.3	1564.3	1537.2	1523.3	1516.5	1498.5	1488.7	1480.3
10°	1626.0	1590.4	1564.7	1524.7	1500.3	1464.6	1440.3	1440.9	1416.5	1402.7	1392.7
12.5°	1578.5	1539.4	1496.7	1460.7	1426.7	1398.1	1368.8	1356.8	1331.0	1317.7	1290.6
15°	1499.7	1454.1	1409.0	1360.2	1325.8	1281.4	1238.9	1186.9	1145.1	1108.8	1098.8
17.5°	1413.6	1357.1	1311.9	1254.6	1195.7	1121.1	1071.8	1041.6	1016.3	997.2	983.0
20°	1354.6	1297.0	1248.9	1162.6	1083.2	1032.6	996.3	973.1	946.9	926.2	914.9
22.5°	1292.5	1232.5	1166.9	1070.5	1008.6	968.0	935.7	909.1	891.3	875.2	864.9
25°	1204.5	1138.8	1030.7	964.3	914.3	871.8	849.2	833.0	814.3	792.4	782.3
27.5°	1111.4	1007.0	929.3	880.1	832.3	804.6	784.4	760.1	743.3	733.5	723.0
30°	1041.9	937.5	876.8	823.0	789.2	758.6	734.8	721.0	704.8	688.0	681.1
32.5°	964.3	880.9	822.7	778.0	743.7	717.6	698.8	676.6	664.8	654.4	640.0
35°	868.0	804.8	751.7	715.5	683.0	661.7	639.8	626.6	605.4	596.6	591.0
37.5°	786.5	731.7	692.0	653.7	628.0	604.5	591.1	570.2	561.0	548.8	537.0
40°	740.5	686.6	648.6	617.3	588.5	571.0	554.1	537.2	523.5	517.8	503.4
42.5°	693.4	649.7	611.5	577.2	558.0	539.4	518.1	505.7	491.4	482.3	473.4
45°	628.5	589.7	557.2	529.0	507.8	488.4	474.7	454.0	445.9	427.7	420.3
47.5°	571.5	535.5	504.4	477.7	456.9	444.3	424.1	408.0	395.0	383.9	374.2
50°	530.9	501.0	470.9	447.1	428.4	410.3	389.6	381.4	361.5	355.8	350.2
52.5°	493.9	465.4	437.9	414.6	395.9	378.2	360.1	349.5	335.9	330.4	326.2
55°	442.1	414.6	388.3	367.7	348.9	330.8	319.6	306.4	300.2	295.8	290.8
57.5°	390.1	365.3	345.3	324.3	305.5	291.1	278.1	270.1	263.6	257.9	251.9
60°	357.1	333.3	315.2	295.8	276.4	264.6	254.5	245.2	237.6	228.8	226.4
62.5°	322.1	301.3	284.6	265.8	248.9	238.0	228.5	219.6	210.7	197.8	194.4
65°	273.9	257.7	240.2	224.5	209.5	198.9	185.1	175.1	171.4	170.1	169.5
67.5°	230.4	215.0	200.0	184.0	170.3	160.5	153.4	151.9	149.3	148.5	146.8
70°	201.3	187.0	172.0	156.9	143.8	141.9	139.5	137.0	133.8	132.6	131.3
72.5°	175.3	160.5	145.4	133.5	127.8	125.5	122.9	120.5	118.3	117.1	116.3
75°	134.5	120.7	110.7	106.3	103.2	101.3	97.6	95.7	94.4	92.6	91.9
77.5°	96.8	89.1	84.5	81.7	78.4	76.4	74.3	72.4	71.1	70.7	69.7
80°	73.8	70.0	66.9	63.2	61.9	59.4	58.8	56.9	57.5	55.7	55.7
82.5°	57.3	52.5	49.9	48.2	46.9	44.9	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.2	26.9	25.6	25.6	23.8	24.4	23.8	23.8	22.5	21.9
87.5°	11.1	11.1	10.8	11.5	12.3	12.4	12.3	11.8	11.7	11.7	11.1
90°	8.2	10.8	14.2	17.6	21.0	24.5	24.1	23.8	23.6	23.3	23.2
92.5°	17.9	19.0	19.8	20.6	21.4	22.2	22.3	22.3	22.4	22.5	22.5
95°	42.6	43.5	43.8	44.1	44.5	44.8	44.8	44.8	44.8	44.8	44.6
97.5°	71.9	72.9	73.5	74.1	74.6	75.2	75.2	75.2	75.2	75.2	75.2
100°	93.8	94.6	95.1	95.6	96.0	96.5	96.5	96.5	96.5	96.5	96.4
102.5°	116.3	117.1	117.7	118.3	118.9	119.4	119.6	119.7	119.8	120.0	120.0
105°	152.2	152.6	153.0	153.3	153.5	153.9	154.2	154.5	154.8	155.1	155.2
107.5°	191.4	191.8	191.8	191.8	191.8	191.8	191.9	192.0	192.2	192.3	192.0
110°	217.1	217.5	217.5	217.5	217.5	217.5	217.5	217.5	217.5	217.5	217.3



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	243.9	244.3	244.2	244.0	243.9	243.8	243.5	243.1	242.7	242.3	242.0
115°	283.5	283.8	283.5	283.1	282.9	282.6	282.4	282.3	282.1	281.9	281.6
117.5°	324.1	324.3	323.5	322.6	321.8	320.9	320.6	320.2	319.8	319.4	319.0
120°	350.4	350.4	349.2	348.0	346.8	345.5	345.5	345.5	345.5	345.5	345.3
122.5°	375.5	375.9	374.9	374.1	373.2	372.4	372.0	371.6	371.3	370.9	370.5
125°	412.6	413.1	412.6	412.2	411.7	411.2	410.8	410.3	409.8	409.3	409.1
127.5°	450.6	451.3	450.7	450.2	449.6	449.0	448.5	447.9	447.3	446.8	446.3
130°	474.6	475.4	475.1	474.9	474.5	474.2	473.9	473.6	473.3	473.0	472.5
132.5°	498.8	499.7	499.7	499.8	499.9	499.9	499.3	498.6	497.9	497.2	496.6
135°	533.5	534.5	534.8	535.2	535.5	535.7	535.6	535.5	535.3	535.2	534.8
137.5°	568.4	569.4	569.8	570.2	570.6	571.0	570.9	570.7	570.6	570.5	570.1
140°	590.3	591.4	592.2	593.0	593.7	594.5	594.5	594.5	594.5	594.5	594.2
142.5°	612.7	613.7	614.2	614.7	615.2	615.8	615.9	616.0	616.1	616.2	616.0
145°	643.7	644.6	645.5	646.5	647.4	648.4	648.5	648.7	648.8	648.9	648.8
147.5°	673.2	674.1	674.8	675.3	676.0	676.7	676.9	677.3	677.6	678.0	677.9
150°	691.3	692.0	692.7	693.2	693.9	694.6	695.0	695.4	695.9	696.4	696.4
152.5°	708.6	709.5	710.2	711.0	711.7	712.5	713.0	713.6	714.2	714.8	714.8
155°	732.7	733.2	733.7	734.1	734.6	735.1	735.8	736.6	737.4	738.2	738.4
157.5°	754.4	754.7	755.0	755.3	755.5	755.8	756.9	757.9	758.9	760.0	760.2
160°	767.8	768.1	768.2	768.4	768.5	768.6	769.6	770.5	771.5	772.4	772.5
162.5°	779.1	779.2	779.4	779.6	779.7	779.9	780.9	781.9	783.1	784.1	784.2
165°	794.7	794.6	794.6	794.6	794.6	794.6	795.6	796.7	797.8	798.9	799.1
167.5°	807.1	806.8	806.8	806.7	806.7	806.7	807.8	808.9	809.9	811.1	811.2
170°	814.4	814.1	813.9	813.7	813.6	813.4	814.5	815.6	816.7	817.7	817.8
172.5°	819.4	819.1	818.9	818.8	818.6	818.4	819.5	820.7	821.7	822.8	822.8
175°	825.6	825.2	824.8	824.5	824.3	823.9	825.0	826.0	827.2	828.3	828.3
177.5°	828.4	828.1	827.8	827.6	827.4	827.1	827.8	828.6	829.3	830.1	830.1
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1728.3	1729.3	1727.8	1728.8	1727.8	1729.3	1728.3	1733.8	1734.8	1735.8	1734.8
5°	1610.3	1602.9	1601.6	1599.8	1601.6	1602.9	1610.3	1613.5	1616.0	1621.0	1629.8
7.5°	1469.5	1468.4	1465.3	1460.9	1465.3	1468.4	1469.5	1480.3	1488.7	1498.5	1516.5
10°	1378.9	1375.8	1375.3	1370.8	1375.3	1375.8	1378.9	1392.7	1402.7	1416.5	1440.9
12.5°	1272.9	1252.7	1250.7	1239.7	1250.7	1252.7	1272.9	1290.6	1317.7	1331.0	1356.8
15°	1083.8	1080.1	1067.5	1059.4	1067.5	1080.1	1083.8	1098.8	1108.8	1145.1	1186.9
17.5°	975.7	963.5	959.6	957.8	959.6	963.5	975.7	983.0	997.2	1016.3	1041.6
20°	906.2	894.9	893.1	891.8	893.1	894.9	906.2	914.9	926.2	946.9	973.1
22.5°	858.2	846.4	841.5	837.7	841.5	846.4	858.2	864.9	875.2	891.3	909.1
25°	776.1	771.8	769.2	768.0	769.2	771.8	776.1	782.3	792.4	814.3	833.0
27.5°	711.9	702.3	700.4	697.2	700.4	702.3	711.9	723.0	733.5	743.3	760.1
30°	675.4	672.3	667.9	664.1	667.9	672.3	675.4	681.1	688.0	704.8	721.0
32.5°	632.4	629.8	625.8	624.2	625.8	629.8	632.4	640.0	654.4	664.8	676.6
35°	584.8	576.0	572.2	566.6	572.2	576.0	584.8	591.0	596.6	605.4	626.6
37.5°	534.3	529.7	524.4	526.3	524.4	529.7	534.3	537.0	548.8	561.0	570.2
40°	495.3	492.2	491.0	490.3	491.0	492.2	495.3	503.4	517.8	523.5	537.2
42.5°	464.3	455.6	452.4	452.2	452.4	455.6	464.3	473.4	482.3	491.4	505.7
45°	417.2	409.0	403.4	404.0	403.4	409.0	417.2	420.3	427.7	445.9	454.0
47.5°	368.8	368.6	365.1	366.3	365.1	368.6	368.8	374.2	383.9	395.0	408.0
50°	345.8	342.0	339.6	340.2	339.6	342.0	345.8	350.2	355.8	361.5	381.4
52.5°	323.9	320.6	318.6	321.2	318.6	320.6	323.9	326.2	330.4	335.9	349.5
55°	287.7	283.9	283.3	282.7	283.3	283.9	287.7	290.8	295.8	300.2	306.4
57.5°	247.3	244.8	241.0	239.4	241.0	244.8	247.3	251.9	257.9	263.6	270.1
60°	218.3	213.3	207.0	206.4	207.0	213.3	218.3	226.4	228.8	237.6	245.2
62.5°	191.7	190.8	189.5	189.4	189.5	190.8	191.7	194.4	197.8	210.7	219.6
65°	168.2	167.6	168.2	168.8	168.2	167.6	168.2	169.5	170.1	171.4	175.1
67.5°	146.6	145.4	144.3	144.9	144.3	145.4	146.6	146.8	148.5	149.3	151.9
70°	130.1	129.4	128.8	128.8	128.8	129.4	130.1	131.3	132.6	133.8	137.0
72.5°	114.0	114.0	113.3	112.8	113.3	114.0	114.0	116.3	117.1	118.3	120.5
75°	91.3	90.0	90.0	90.0	90.0	90.0	91.3	91.9	92.6	94.4	95.7
77.5°	69.6	68.9	68.3	67.8	68.3	68.9	69.6	69.7	70.7	71.1	72.4
80°	55.0	54.4	53.8	53.8	53.8	54.4	55.0	55.7	55.7	57.5	56.9
82.5°	42.0	41.4	41.3	40.8	41.3	41.4	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.1	22.5	23.8	22.5	23.1	22.5	21.9	22.5	23.8	23.8
87.5°	11.1	10.7	11.2	10.7	11.2	10.7	11.1	11.1	11.7	11.7	11.8
90°	23.3	23.5	23.7	23.8	23.7	23.5	23.3	23.2	23.3	23.6	23.8
92.5°	22.5	22.6	22.6	22.6	22.6	22.6	22.5	22.5	22.5	22.4	22.3
95°	44.3	44.0	43.6	43.4	43.6	44.0	44.3	44.6	44.8	44.8	44.8
97.5°	75.2	75.2	75.1	75.1	75.1	75.2	75.2	75.2	75.2	75.2	75.2
100°	96.3	96.1	96.0	95.9	96.0	96.1	96.3	96.4	96.5	96.5	96.5
102.5°	119.8	119.6	119.5	119.3	119.5	119.6	119.8	120.0	120.0	119.8	119.7
105°	155.2	155.2	155.2	155.2	155.2	155.2	155.2	155.2	155.1	154.8	154.5
107.5°	191.2	190.6	189.8	189.2	189.8	190.6	191.2	192.0	192.3	192.2	192.0
110°	216.8	216.3	215.8	215.5	215.8	216.3	216.8	217.3	217.5	217.5	217.5



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	241.7	241.3	240.9	240.6	240.9	241.3	241.7	242.0	242.3	242.7	243.1
115°	281.2	280.7	280.2	279.7	280.2	280.7	281.2	281.6	281.9	282.1	282.3
117.5°	318.5	318.0	317.5	317.1	317.5	318.0	318.5	319.0	319.4	319.8	320.2
120°	344.8	344.3	343.8	343.4	343.8	344.3	344.8	345.3	345.5	345.5	345.5
122.5°	370.1	369.9	369.5	369.2	369.5	369.9	370.1	370.5	370.9	371.3	371.6
125°	409.0	408.8	408.6	408.5	408.6	408.8	409.0	409.1	409.3	409.8	410.3
127.5°	445.7	445.3	444.8	444.3	444.8	445.3	445.7	446.3	446.8	447.3	447.9
130°	471.8	471.3	470.6	470.0	470.6	471.3	471.8	472.5	473.0	473.3	473.6
132.5°	496.2	495.6	495.1	494.6	495.1	495.6	496.2	496.6	497.2	497.9	498.6
135°	534.3	533.9	533.4	532.9	533.4	533.9	534.3	534.8	535.2	535.3	535.5
137.5°	569.5	568.9	568.3	567.6	568.3	568.9	569.5	570.1	570.5	570.6	570.7
140°	593.6	593.0	592.3	591.7	592.3	593.0	593.6	594.2	594.5	594.5	594.5
142.5°	615.4	614.7	614.2	613.5	614.2	614.7	615.4	616.0	616.2	616.1	616.0
145°	648.1	647.5	646.9	646.3	646.9	647.5	648.1	648.8	648.9	648.8	648.7
147.5°	677.3	676.7	676.1	675.5	676.1	676.7	677.3	677.9	678.0	677.6	677.3
150°	695.9	695.4	695.0	694.6	695.0	695.4	695.9	696.4	696.4	695.9	695.4
152.5°	714.2	713.6	713.0	712.5	713.0	713.6	714.2	714.8	714.8	714.2	713.6
155°	737.9	737.4	737.0	736.5	737.0	737.4	737.9	738.4	738.2	737.4	736.6
157.5°	759.4	758.7	757.9	757.1	757.9	758.7	759.4	760.2	760.0	758.9	757.9
160°	771.9	771.3	770.7	770.1	770.7	771.3	771.9	772.5	772.4	771.5	770.5
162.5°	783.4	782.8	782.0	781.3	782.0	782.8	783.4	784.2	784.1	783.1	781.9
165°	798.2	797.5	796.7	796.0	796.7	797.5	798.2	799.1	798.9	797.8	796.7
167.5°	810.4	809.5	808.8	807.9	808.8	809.5	810.4	811.2	811.1	809.9	808.9
170°	816.9	816.0	815.0	814.1	815.0	816.0	816.9	817.8	817.7	816.7	815.6
172.5°	822.0	821.0	820.1	819.2	820.1	821.0	822.0	822.8	822.8	821.7	820.7
175°	827.4	826.5	825.6	824.6	825.6	826.5	827.4	828.3	828.3	827.2	826.0
177.5°	829.3	828.6	827.8	827.1	827.8	828.6	829.3	830.1	830.1	829.3	828.6
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1730.8	1737.9	1748.3	1754.4	1764.3	1770.8	1774.3	1780.8	1784.3	1796.9	1809.9
5°	1634.1	1644.2	1661.6	1677.9	1695.4	1713.5	1726.6	1741.7	1755.5	1779.2	1804.2
7.5°	1523.3	1537.2	1564.3	1590.3	1620.7	1646.4	1669.1	1694.7	1717.6	1751.6	1787.1
10°	1440.3	1464.6	1500.3	1524.7	1564.7	1590.4	1626.0	1654.2	1686.0	1731.1	1771.1
12.5°	1368.8	1398.1	1426.7	1460.7	1496.7	1539.4	1578.5	1614.6	1652.6	1699.0	1746.1
15°	1238.9	1281.4	1325.8	1360.2	1409.0	1454.1	1499.7	1548.4	1594.7	1650.4	1711.7
17.5°	1071.8	1121.1	1195.7	1254.6	1311.9	1357.1	1413.6	1472.6	1527.2	1594.3	1662.6
20°	996.3	1032.6	1083.2	1162.6	1248.9	1297.0	1354.6	1419.7	1482.1	1555.3	1628.5
22.5°	935.7	968.0	1008.6	1070.5	1166.9	1232.5	1292.5	1358.6	1431.2	1505.8	1587.0
25°	849.2	871.8	914.3	964.3	1030.7	1138.8	1204.5	1270.7	1349.6	1429.6	1522.2
27.5°	784.4	804.6	832.3	880.1	929.3	1007.0	1111.4	1183.7	1262.3	1352.4	1448.4
30°	734.8	758.6	789.2	823.0	876.8	937.5	1041.9	1125.7	1203.2	1295.8	1398.4
32.5°	698.8	717.6	743.7	778.0	822.7	880.9	964.3	1066.1	1141.7	1239.3	1346.3
35°	639.8	661.7	683.0	715.5	751.7	804.8	868.0	976.9	1051.9	1148.2	1255.7
37.5°	591.1	604.5	628.0	653.7	692.0	731.7	786.5	884.0	965.3	1059.8	1169.9
40°	554.1	571.0	588.5	617.3	648.6	686.6	740.5	813.0	906.2	998.7	1106.3
42.5°	518.1	539.4	558.0	577.2	611.5	649.7	693.4	755.0	850.2	937.7	1042.3
45°	474.7	488.4	507.8	529.0	557.2	589.7	628.5	682.3	773.6	849.2	947.4
47.5°	424.1	444.3	456.9	477.7	504.4	535.5	571.5	618.0	691.9	762.8	853.9
50°	389.6	410.3	428.4	447.1	470.9	501.0	530.9	576.0	635.4	709.8	794.8
52.5°	360.1	378.2	395.9	414.6	437.9	465.4	493.9	533.5	584.4	652.8	735.4
55°	319.6	330.8	348.9	367.7	388.3	414.6	442.1	475.3	519.1	576.6	643.6
57.5°	278.1	291.1	305.5	324.3	345.3	365.3	390.1	420.1	454.7	506.7	564.0
60°	254.5	264.6	276.4	295.8	315.2	333.3	357.1	382.1	414.6	459.7	508.4
62.5°	228.5	238.0	248.9	265.8	284.6	301.3	322.1	348.6	376.1	417.2	459.9
65°	185.1	198.9	209.5	224.5	240.2	257.7	273.9	295.2	319.6	352.1	390.2
67.5°	153.4	160.5	170.3	184.0	200.0	215.0	230.4	247.0	268.2	293.3	323.6
70°	139.5	141.9	143.8	156.9	172.0	187.0	201.3	217.0	235.2	255.8	282.0
72.5°	122.9	125.5	127.8	133.5	145.4	160.5	175.3	187.0	204.2	221.2	242.5
75°	97.6	101.3	103.2	106.3	110.7	120.7	134.5	145.7	155.7	168.8	185.8
77.5°	74.3	76.4	78.4	81.7	84.5	89.1	96.8	107.0	116.3	123.9	135.5
80°	58.8	59.4	61.9	63.2	66.9	70.0	73.8	81.9	91.3	94.4	102.5
82.5°	44.3	44.9	46.9	48.2	49.9	52.5	57.3	59.4	66.8	70.9	76.1
85°	24.4	23.8	25.6	25.6	26.9	28.2	29.4	32.5	34.4	39.4	40.6
87.5°	12.3	12.4	12.3	11.5	10.8	11.1	11.1	11.3	11.9	13.0	14.6
90°	24.1	24.5	21.0	17.6	14.2	10.8	8.2	6.3	4.4	2.5	0.7
92.5°	22.3	22.2	21.4	20.6	19.8	19.0	17.9	16.6	15.2	13.9	12.4
95°	44.8	44.8	44.5	44.1	43.8	43.5	42.6	41.0	39.5	37.9	36.4
97.5°	75.2	75.2	74.6	74.1	73.5	72.9	71.9	70.5	69.2	67.8	66.4
100°	96.5	96.5	96.0	95.6	95.1	94.6	93.8	92.6	91.3	90.1	88.8
102.5°	119.6	119.4	118.9	118.3	117.7	117.1	116.3	115.3	114.3	113.3	112.4
105°	154.2	153.9	153.5	153.3	153.0	152.6	152.2	151.7	151.3	150.8	150.3
107.5°	191.9	191.8	191.8	191.8	191.8	191.8	191.4	190.8	190.1	189.4	188.7
110°	217.5	217.5	217.5	217.5	217.5	217.5	217.1	216.1	215.2	214.2	213.3



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	243.5	243.8	243.9	244.0	244.2	244.3	243.9	243.0	242.0	241.1	240.2
115°	282.4	282.6	282.9	283.1	283.5	283.8	283.5	282.6	281.6	280.7	279.7
117.5°	320.6	320.9	321.8	322.6	323.5	324.3	324.1	322.9	321.7	320.5	319.2
120°	345.5	345.5	346.8	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5
122.5°	372.0	372.4	373.2	374.1	374.9	375.9	375.5	374.0	372.6	371.1	369.6
125°	410.8	411.2	411.7	412.2	412.6	413.1	412.6	411.2	409.8	408.5	407.1
127.5°	448.5	449.0	449.6	450.2	450.7	451.3	450.6	448.8	447.1	445.4	443.6
130°	473.9	474.2	474.5	474.9	475.1	475.4	474.6	472.6	470.5	468.5	466.5
132.5°	499.3	499.9	499.9	499.8	499.7	499.7	498.8	497.2	495.6	493.9	492.3
135°	535.6	535.7	535.5	535.2	534.8	534.5	533.5	531.8	530.1	528.4	526.7
137.5°	570.9	571.0	570.6	570.2	569.8	569.4	568.4	567.1	565.7	564.3	562.9
140°	594.5	594.5	593.7	593.0	592.2	591.4	590.3	588.9	587.5	586.1	584.8
142.5°	615.9	615.8	615.2	614.7	614.2	613.7	612.7	611.3	609.9	608.5	607.1
145°	648.5	648.4	647.4	646.5	645.5	644.6	643.7	642.5	641.4	640.4	639.2
147.5°	676.9	676.7	676.0	675.3	674.8	674.1	673.2	671.8	670.5	669.2	668.0
150°	695.0	694.6	693.9	693.2	692.7	692.0	691.3	690.3	689.4	688.4	687.5
152.5°	713.0	712.5	711.7	711.0	710.2	709.5	708.6	707.7	706.7	705.8	704.8
155°	735.8	735.1	734.6	734.1	733.7	733.2	732.7	732.3	731.8	731.3	730.8
157.5°	756.9	755.8	755.5	755.3	755.0	754.7	754.4	754.0	753.8	753.5	753.1
160°	769.6	768.6	768.5	768.4	768.2	768.1	767.8	767.5	767.1	766.9	766.6
162.5°	780.9	779.9	779.7	779.6	779.4	779.2	779.1	779.0	779.0	778.9	778.8
165°	795.6	794.6	794.6	794.6	794.6	794.6	794.7	794.8	794.9	795.0	795.2
167.5°	807.8	806.7	806.7	806.7	806.8	806.8	807.1	807.6	808.0	808.5	809.0
170°	814.5	813.4	813.6	813.7	813.9	814.1	814.4	814.8	815.3	815.8	816.2
172.5°	819.5	818.4	818.6	818.8	818.9	819.1	819.4	819.8	820.3	820.8	821.2
175°	825.0	823.9	824.3	824.5	824.8	825.2	825.6	826.0	826.5	827.0	827.4
177.5°	827.8	827.1	827.4	827.6	827.8	828.1	828.4	828.8	829.2	829.5	829.9
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1810.3	1811.8	1821.8	1826.4	1835.4	1838.9	1842.9	1841.9	1841.9	1843.9	1857.9
5°	1814.2	1826.7	1845.5	1863.7	1881.1	1896.2	1906.2	1916.2	1920.0	1938.1	1954.4
7.5°	1807.7	1830.8	1861.8	1889.4	1922.6	1948.4	1970.0	1989.3	2002.6	2029.0	2056.1
10°	1799.2	1831.7	1866.8	1902.4	1948.0	1982.4	2017.5	2044.4	2053.1	2092.5	2115.1
12.5°	1782.3	1825.7	1870.3	1916.5	1961.1	2008.5	2047.0	2073.9	2104.7	2140.0	2181.6
15°	1756.7	1806.8	1864.9	1924.3	1988.1	2045.6	2086.9	2133.8	2167.6	2206.4	2242.6
17.5°	1720.0	1784.5	1858.4	1927.2	2001.0	2062.8	2119.6	2164.5	2188.3	2210.5	2215.8
20°	1691.0	1760.5	1847.4	1928.7	2002.5	2073.8	2130.1	2167.6	2173.9	2174.4	2141.4
22.5°	1659.5	1738.0	1828.9	1912.1	2000.5	2079.8	2123.5	2139.6	2114.8	2072.4	2008.3
25°	1601.6	1692.3	1798.0	1893.0	1989.3	2064.4	2079.4	2051.3	1964.4	1873.0	1757.4
27.5°	1538.8	1640.8	1754.1	1859.7	1962.4	2008.8	1976.5	1875.0	1718.4	1582.3	1417.4
30°	1492.8	1607.2	1718.5	1836.7	1931.8	1951.8	1877.5	1728.0	1545.3	1340.2	1175.7
32.5°	1440.3	1560.2	1682.5	1804.8	1884.3	1864.7	1741.8	1557.8	1343.7	1142.1	986.7
35°	1365.2	1489.0	1621.0	1743.6	1794.2	1709.8	1526.0	1286.4	1067.5	879.3	772.3
37.5°	1278.6	1413.3	1550.6	1663.1	1659.5	1518.8	1268.4	1021.2	837.2	725.9	649.7
40°	1217.0	1353.3	1501.6	1596.6	1555.9	1372.7	1101.3	868.0	733.6	644.8	589.1
42.5°	1158.0	1294.8	1442.0	1517.6	1446.9	1221.6	951.2	768.5	657.5	588.2	543.1
45°	1057.5	1202.0	1338.3	1380.3	1253.9	1005.6	769.2	636.7	562.9	511.5	480.3
47.5°	959.3	1101.5	1225.9	1226.6	1055.7	815.5	648.9	551.0	488.0	448.3	425.6
50°	899.3	1034.3	1138.8	1122.6	928.7	725.5	580.3	496.0	443.4	412.7	389.0
52.5°	831.8	962.8	1053.3	1007.0	821.1	638.4	518.8	447.9	404.4	377.8	356.5
55°	733.6	849.9	913.7	843.7	669.8	530.9	438.4	382.8	350.2	327.7	309.5
57.5°	637.2	733.1	773.3	691.6	551.7	440.3	370.9	329.0	296.8	280.7	271.3
60°	576.6	658.6	686.6	596.6	479.7	385.2	328.3	289.5	265.8	255.1	245.8
62.5°	517.1	584.0	595.6	513.0	418.1	337.2	288.3	255.5	239.8	229.6	220.7
65°	429.0	477.2	471.6	405.3	330.8	267.7	232.1	212.0	200.1	185.8	170.1
67.5°	353.2	382.6	364.9	315.2	252.5	208.0	184.7	169.6	154.9	141.2	137.6
70°	305.2	322.1	303.3	257.7	207.0	174.5	155.7	137.6	128.8	125.7	120.1
72.5°	259.2	265.0	244.8	205.7	168.4	144.5	126.2	116.0	111.3	108.7	105.1
75°	194.5	190.1	172.6	141.9	117.0	100.7	95.1	91.3	88.2	85.7	83.8
77.5°	136.6	130.2	114.6	94.5	81.4	73.7	70.3	68.3	66.8	65.5	63.6
80°	102.5	98.2	82.6	67.6	61.9	58.2	56.3	53.8	53.8	52.5	50.6
82.5°	75.0	70.1	56.6	49.5	46.4	44.1	42.8	41.3	40.8	41.0	39.7
85°	39.4	31.9	28.2	26.9	25.0	23.8	24.4	23.1	23.1	23.1	22.5
87.5°	12.5	10.4	10.3	10.2	11.1	11.9	12.1	12.7	13.9	13.4	13.8
90°	2.5	4.4	6.3	8.2	10.8	14.2	17.6	21.0	24.5	24.1	23.8
92.5°	13.9	15.2	16.6	17.9	19.0	19.8	20.6	21.4	22.2	22.3	22.3
95°	37.9	39.5	41.0	42.6	43.5	43.8	44.1	44.5	44.8	44.8	44.8
97.5°	67.8	69.2	70.5	71.9	72.9	73.5	74.1	74.6	75.2	75.2	75.2
100°	90.1	91.3	92.6	93.8	94.6	95.1	95.6	96.0	96.5	96.5	96.5
102.5°	113.3	114.3	115.3	116.3	117.1	117.7	118.3	118.9	119.4	119.6	119.7
105°	150.8	151.3	151.7	152.2	152.6	153.0	153.3	153.5	153.9	154.2	154.5
107.5°	189.4	190.1	190.8	191.4	191.8	191.8	191.8	191.8	191.8	191.9	192.0
110°	214.2	215.2	216.1	217.1	217.5	217.5	217.5	217.5	217.5	217.5	217.5





TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	241.1	242.0	243.0	243.9	244.3	244.2	244.0	243.9	243.8	243.5	243.1
115°	280.7	281.6	282.6	283.5	283.8	283.5	283.1	282.9	282.6	282.4	282.3
117.5°	320.5	321.7	322.9	324.1	324.3	323.5	322.6	321.8	320.9	320.6	320.2
120°	346.8	348.0	349.2	350.4	350.4	349.2	348.0	346.8	345.5	345.5	345.5
122.5°	371.1	372.6	374.0	375.5	375.9	374.9	374.1	373.2	372.4	372.0	371.6
125°	408.5	409.8	411.2	412.6	413.1	412.6	412.2	411.7	411.2	410.8	410.3
127.5°	445.4	447.1	448.8	450.6	451.3	450.7	450.2	449.6	449.0	448.5	447.9
130°	468.5	470.5	472.6	474.6	475.4	475.1	474.9	474.5	474.2	473.9	473.6
132.5°	493.9	495.6	497.2	498.8	499.7	499.7	499.8	499.9	499.9	499.3	498.6
135°	528.4	530.1	531.8	533.5	534.5	534.8	535.2	535.5	535.7	535.6	535.5
137.5°	564.3	565.7	567.1	568.4	569.4	569.8	570.2	570.6	571.0	570.9	570.7
140°	586.1	587.5	588.9	590.3	591.4	592.2	593.0	593.7	594.5	594.5	594.5
142.5°	608.5	609.9	611.3	612.7	613.7	614.2	614.7	615.2	615.8	615.9	616.0
145°	640.4	641.4	642.5	643.7	644.6	645.5	646.5	647.4	648.4	648.5	648.7
147.5°	669.2	670.5	671.8	673.2	674.1	674.8	675.3	676.0	676.7	676.9	677.3
150°	688.4	689.4	690.3	691.3	692.0	692.7	693.2	693.9	694.6	695.0	695.4
152.5°	705.8	706.7	707.7	708.6	709.5	710.2	711.0	711.7	712.5	713.0	713.6
155°	731.3	731.8	732.3	732.7	733.2	733.7	734.1	734.6	735.1	735.8	736.6
157.5°	753.5	753.8	754.0	754.4	754.7	755.0	755.3	755.5	755.8	756.9	757.9
160°	766.9	767.1	767.5	767.8	768.1	768.2	768.4	768.5	768.6	769.6	770.5
162.5°	778.9	779.0	779.0	779.1	779.2	779.4	779.6	779.7	779.9	780.9	781.9
165°	795.0	794.9	794.8	794.7	794.6	794.6	794.6	794.6	794.6	795.6	796.7
167.5°	808.5	808.0	807.6	807.1	806.8	806.8	806.7	806.7	806.7	807.8	808.9
170°	815.8	815.3	814.8	814.4	814.1	813.9	813.7	813.6	813.4	814.5	815.6
172.5°	820.8	820.3	819.8	819.4	819.1	818.9	818.8	818.6	818.4	819.5	820.7
175°	827.0	826.5	826.0	825.6	825.2	824.8	824.5	824.3	823.9	825.0	826.0
177.5°	829.5	829.2	828.8	828.4	828.1	827.8	827.6	827.4	827.1	827.8	828.6
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8	828.8



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9	1799.9
2.5°	1862.9	1869.4	1872.4	1872.4	1875.9	1874.4	1872.9
5°	1970.0	1981.9	1984.3	1995.6	2003.8	2001.2	2002.5
7.5°	2076.4	2095.6	2114.4	2123.1	2124.4	2129.4	2131.3
10°	2141.9	2157.6	2187.0	2182.6	2204.5	2217.0	2196.3
12.5°	2205.0	2226.1	2246.6	2252.1	2264.6	2268.5	2260.4
15°	2262.0	2273.3	2274.5	2271.4	2275.1	2272.0	2260.1
17.5°	2208.8	2190.5	2153.4	2135.9	2122.0	2101.6	2093.3
20°	2120.7	2066.9	2004.3	1979.3	1949.9	1892.4	1906.2
22.5°	1930.6	1869.3	1806.8	1733.7	1698.8	1644.3	1641.0
25°	1634.7	1529.1	1412.8	1331.4	1283.9	1229.5	1205.7
27.5°	1271.0	1137.9	1042.6	994.4	950.5	907.3	905.6
30°	1031.9	931.8	858.0	816.7	789.9	771.8	775.5
32.5°	869.8	801.3	751.5	717.2	697.3	683.6	683.4
35°	711.1	664.1	632.3	617.8	603.5	593.5	594.1
37.5°	608.5	580.3	562.6	546.7	537.7	532.8	530.1
40°	556.0	532.8	519.1	509.7	502.2	495.3	494.1
42.5°	514.4	495.3	481.5	474.2	467.1	462.3	461.0
45°	456.6	440.9	428.4	420.3	417.2	412.7	412.7
47.5°	406.1	390.8	381.0	375.9	370.5	367.6	367.5
50°	372.1	360.2	351.5	348.4	343.9	342.0	341.5
52.5°	341.6	332.7	326.5	324.3	322.4	320.1	320.5
55°	300.2	295.2	292.7	290.8	287.7	283.9	286.4
57.5°	265.3	261.0	254.3	248.4	245.5	242.9	243.9
60°	240.8	232.1	223.3	216.4	214.5	208.9	208.9
62.5°	209.7	197.5	186.7	182.9	181.0	178.3	177.9
65°	161.4	156.4	153.8	151.4	150.1	150.1	148.8
67.5°	133.7	131.7	128.9	128.4	127.1	126.7	126.3
70°	118.2	115.6	114.4	113.9	112.5	113.2	111.3
72.5°	103.2	101.2	100.9	99.3	98.6	98.7	97.3
75°	81.3	81.3	80.7	80.0	78.8	78.1	78.8
77.5°	62.6	62.7	61.5	61.5	61.3	61.5	60.8
80°	50.0	50.6	50.0	49.4	48.8	49.4	48.8
82.5°	39.5	38.6	38.5	38.4	38.3	37.9	37.8
85°	22.5	23.1	22.5	21.9	21.9	21.9	22.5
87.5°	13.2	13.2	13.1	13.2	13.2	13.2	12.7
90°	23.6	23.3	23.2	23.3	23.5	23.7	23.8
92.5°	22.4	22.5	22.5	22.5	22.6	22.6	22.6
95°	44.8	44.8	44.6	44.3	44.0	43.6	43.4
97.5°	75.2	75.2	75.2	75.2	75.2	75.1	75.1
100°	96.5	96.5	96.4	96.3	96.1	96.0	95.9
102.5°	119.8	120.0	120.0	119.8	119.6	119.5	119.3
105°	154.8	155.1	155.2	155.2	155.2	155.2	155.2
107.5°	192.2	192.3	192.0	191.2	190.6	189.8	189.2
110°	217.5	217.5	217.3	216.8	216.3	215.8	215.5



TEST NUMBER: P331830-830

CATALOG NUMBER: S122RDIW-S865D710U830-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	242.7	242.3	242.0	241.7	241.3	240.9	240.6
115°	282.1	281.9	281.6	281.2	280.7	280.2	279.7
117.5°	319.8	319.4	319.0	318.5	318.0	317.5	317.1
120°	345.5	345.5	345.3	344.8	344.3	343.8	343.4
122.5°	371.3	370.9	370.5	370.1	369.9	369.5	369.2
125°	409.8	409.3	409.1	409.0	408.8	408.6	408.5
127.5°	447.3	446.8	446.3	445.7	445.3	444.8	444.3
130°	473.3	473.0	472.5	471.8	471.3	470.6	470.0
132.5°	497.9	497.2	496.6	496.2	495.6	495.1	494.6
135°	535.3	535.2	534.8	534.3	533.9	533.4	532.9
137.5°	570.6	570.5	570.1	569.5	568.9	568.3	567.6
140°	594.5	594.5	594.2	593.6	593.0	592.3	591.7
142.5°	616.1	616.2	616.0	615.4	614.7	614.2	613.5
145°	648.8	648.9	648.8	648.1	647.5	646.9	646.3
147.5°	677.6	678.0	677.9	677.3	676.7	676.1	675.5
150°	695.9	696.4	696.4	695.9	695.4	695.0	694.6
152.5°	714.2	714.8	714.8	714.2	713.6	713.0	712.5
155°	737.4	738.2	738.4	737.9	737.4	737.0	736.5
157.5°	758.9	760.0	760.2	759.4	758.7	757.9	757.1
160°	771.5	772.4	772.5	771.9	771.3	770.7	770.1
162.5°	783.1	784.1	784.2	783.4	782.8	782.0	781.3
165°	797.8	798.9	799.1	798.2	797.5	796.7	796.0
167.5°	809.9	811.1	811.2	810.4	809.5	808.8	807.9
170°	816.7	817.7	817.8	816.9	816.0	815.0	814.1
172.5°	821.7	822.8	822.8	822.0	821.0	820.1	819.2
175°	827.2	828.3	828.3	827.4	826.5	825.6	824.6
177.5°	829.3	830.1	830.1	829.3	828.6	827.8	827.1
180°	828.8	828.8	828.8	828.8	828.8	828.8	828.8

(END OF REPORT)