

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331513-935

Luminaire Tested: **S122DIW-S485D1240U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331513-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6115.0 lumens
Efficiency: N/A
Efficacy: 113.7 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30
1	94	90	86	83	84	81	77	75	64	62	60	48	47	46	34	33	33	26
2	85	78	73	68	77	71	66	62	56	53	50	43	41	39	30	29	28	22
3	78	69	62	57	70	62	57	52	50	46	42	38	35	33	27	25	24	19
4	72	61	54	48	64	55	49	44	44	40	36	34	31	28	24	22	21	17
5	66	55	47	41	59	49	43	38	40	35	31	31	27	25	22	20	18	15
6	60	49	41	36	54	44	38	33	36	31	27	28	24	22	20	18	16	13
7	56	44	37	31	50	40	34	29	32	28	24	25	22	19	18	16	15	12
8	52	40	33	28	46	36	30	26	30	25	21	23	20	17	17	15	13	11
9	48	37	29	25	43	33	27	23	27	22	19	21	18	15	16	13	12	10
10	45	33	27	22	40	30	24	20	25	20	17	20	16	14	15	12	11	9

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	1.3
10°-20°	231.6	3.8
20°-30°	336.2	5.5
30°-40°	354.8	5.8
40°-50°	314.1	5.1
50°-60°	250.7	4.1
60°-70°	170.4	2.8
70°-80°	87.4	1.4
80°-90°	24.6	0.4
90°-100°	48.6	0.8
100°-110°	178.1	2.9
110°-120°	476.0	7.8
120°-130°	785.7	12.8
130°-140°	835.5	13.7
140°-150°	776.6	12.7
150°-160°	624.4	10.2
160°-170°	402.3	6.6
170°-180°	138.5	2.3
0°-30°	647.5	10.6
0°-40°	1002.3	16.4
0°-60°	1567.1	25.6
0°-90°	1849.5	30.2
90°-120°	702.6	11.5
90°-150°	3100.4	50.7
90°-180°	4266.0	69.8
0°-180°	6115.0	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	28	1	28	1	28	13
95°	45	68	45	68	45	42
105°	80	320	80	320	80	83
115°	86	606	86	606	86	216
125°	900	856	900	856	900	779
135°	1094	1060	1094	1060	1094	843
145°	1248	1229	1248	1229	1248	781
155°	1354	1353	1354	1353	1354	625
165°	1423	1426	1423	1426	1423	402
175°	1450	1459	1450	1459	1450	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	12.4	12.3	12.5	12.1	12.0	12.1	11.9	11.4	11.4	11.5	11.3
90°	28.4	28.0	27.5	27.0	26.6	25.7	24.5	23.4	22.2	21.1	19.2
92.5°	28.4	28.2	27.9	27.6	27.3	26.9	26.3	25.7	25.1	24.5	23.5
95°	45.3	45.5	45.7	46.0	46.2	45.7	44.6	43.4	42.3	41.1	39.4
97.5°	60.4	60.2	59.9	59.6	59.3	58.7	57.8	56.8	55.9	55.0	51.2
100°	70.6	70.1	69.7	69.1	68.7	67.5	65.6	63.8	61.9	60.0	56.1
102.5°	75.6	75.0	74.3	73.6	73.0	71.5	69.1	66.6	64.1	61.7	59.0
105°	80.1	79.1	78.2	77.2	76.3	74.6	72.0	69.4	66.8	64.2	61.1
107.5°	82.4	81.5	80.5	79.6	78.6	79.5	82.1	84.7	87.3	90.0	92.1
110°	83.2	82.3	81.4	80.4	79.5	90.7	114.1	137.5	160.9	184.3	215.9



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	84.0	83.3	82.6	81.8	81.0	123.4	208.8	294.1	379.5	464.9	481.6
115°	86.4	103.2	120.1	136.9	153.8	216.4	324.8	433.1	541.5	649.9	644.0
117.5°	352.6	408.0	463.4	518.8	574.1	614.9	641.1	667.4	693.5	719.8	715.7
120°	642.5	674.1	705.7	737.3	768.9	783.3	780.4	777.7	774.8	772.0	767.8
122.5°	801.7	807.9	814.0	820.1	826.2	828.5	826.8	825.1	823.4	821.7	817.2
125°	900.5	899.8	899.1	898.4	897.7	896.6	894.9	893.3	891.7	890.0	885.5
127.5°	962.9	962.7	962.6	962.4	962.3	961.0	958.6	956.2	953.9	951.5	948.1
130°	1001.6	1001.9	1002.1	1002.3	1002.5	1001.3	998.8	996.3	993.7	991.1	988.5
132.5°	1039.6	1039.7	1040.0	1040.3	1040.4	1039.5	1037.2	1035.1	1032.9	1030.7	1028.1
135°	1094.3	1094.8	1095.3	1095.7	1096.1	1095.3	1092.9	1090.5	1088.2	1085.9	1083.7
137.5°	1144.2	1145.0	1145.8	1146.6	1147.4	1146.7	1144.4	1142.0	1139.8	1137.5	1135.1
140°	1175.4	1176.6	1177.8	1178.9	1180.1	1179.7	1177.5	1175.4	1173.3	1171.2	1168.6
142.5°	1205.7	1206.9	1208.1	1209.3	1210.4	1210.0	1208.2	1206.2	1204.3	1202.4	1199.4
145°	1248.1	1249.2	1250.4	1251.5	1252.8	1252.5	1250.9	1249.2	1247.6	1246.0	1242.0
147.5°	1285.4	1286.3	1287.3	1288.3	1289.3	1289.2	1288.0	1286.8	1285.6	1284.3	1280.4
150°	1308.1	1309.2	1310.4	1311.6	1312.8	1312.7	1311.3	1309.8	1308.5	1307.1	1303.3
152.5°	1327.5	1329.0	1330.6	1332.1	1333.7	1333.8	1332.3	1330.9	1329.6	1328.1	1324.6
155°	1354.4	1356.3	1358.2	1360.0	1361.9	1362.2	1360.8	1359.3	1358.0	1356.6	1353.8
157.5°	1379.1	1381.0	1382.8	1384.6	1386.4	1386.6	1384.9	1383.4	1381.7	1380.2	1378.2
160°	1393.4	1395.1	1396.7	1398.4	1400.0	1400.1	1398.7	1397.3	1395.9	1394.5	1393.1
162.5°	1405.2	1407.2	1409.2	1411.3	1413.2	1413.5	1411.9	1410.3	1408.7	1407.1	1405.9
165°	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9	1422.2
167.5°	1434.1	1436.1	1438.3	1440.4	1442.5	1442.7	1441.1	1439.4	1437.8	1436.1	1435.5
170°	1440.8	1442.9	1445.0	1447.2	1449.2	1449.5	1447.9	1446.2	1444.6	1442.9	1442.4
172.5°	1445.9	1447.9	1450.1	1452.2	1454.3	1454.5	1452.9	1451.2	1449.6	1447.9	1447.5
175°	1450.3	1452.6	1455.0	1457.3	1459.7	1460.0	1458.4	1456.7	1455.1	1453.5	1453.0
177.5°	1453.0	1454.7	1456.4	1458.1	1459.7	1460.0	1458.6	1457.3	1456.0	1454.7	1454.5
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	11.2	10.8	10.4	10.5	9.2	8.7	7.1	5.9	6.1	6.4	6.4
90°	17.3	15.4	13.6	11.4	8.8	6.2	3.6	1.0	3.6	6.2	8.8
92.5°	22.6	21.6	20.7	20.3	20.6	20.8	21.0	21.3	21.0	20.8	20.6
95°	37.8	36.2	34.5	37.5	45.3	53.0	60.7	68.4	60.7	53.0	45.3
97.5°	47.4	43.6	39.8	48.8	70.6	92.3	114.1	135.9	114.1	92.3	70.6
100°	52.1	48.1	44.1	58.2	90.2	122.3	154.4	186.4	154.4	122.3	90.2
102.5°	128.3	161.5	194.8	214.9	221.7	228.4	235.2	242.0	235.2	228.4	221.7
105°	192.0	256.0	319.9	348.3	341.2	334.2	327.2	320.2	327.2	334.2	341.2
107.5°	243.2	319.9	396.5	432.0	426.3	420.6	414.9	409.3	414.9	420.6	426.3
110°	319.6	387.3	454.9	486.2	481.3	476.4	471.5	466.6	471.5	476.4	481.3



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	498.3	515.1	531.8	538.0	533.6	529.2	524.9	520.5	524.9	529.2	533.6
115°	638.2	632.3	626.5	621.6	617.5	613.5	609.6	605.6	609.6	613.5	617.5
117.5°	711.7	707.7	703.7	699.5	695.0	690.5	686.1	681.7	686.1	690.5	695.0
120°	763.6	759.4	755.2	751.3	747.8	744.2	740.8	737.3	740.8	744.2	747.8
122.5°	812.5	808.0	803.4	799.3	795.6	791.9	788.2	784.5	788.2	791.9	795.6
125°	881.1	876.7	872.2	868.4	865.4	862.4	859.3	856.3	859.3	862.4	865.4
127.5°	944.9	941.5	938.2	934.9	931.5	928.1	924.7	921.4	924.7	928.1	931.5
130°	985.9	983.3	980.8	977.7	973.9	970.2	966.4	962.7	966.4	970.2	973.9
132.5°	1025.5	1023.0	1020.4	1017.5	1014.3	1011.2	1008.0	1004.8	1008.0	1011.2	1014.3
135°	1081.7	1079.5	1077.5	1074.5	1070.7	1067.0	1063.2	1059.5	1063.2	1067.0	1070.7
137.5°	1132.7	1130.3	1127.9	1125.4	1122.8	1120.2	1117.6	1114.9	1117.6	1120.2	1122.8
140°	1166.1	1163.5	1160.9	1158.6	1156.8	1154.9	1153.1	1151.2	1153.1	1154.9	1156.8
142.5°	1196.4	1193.5	1190.6	1188.3	1186.5	1184.9	1183.2	1181.6	1183.2	1184.9	1186.5
145°	1238.0	1234.1	1230.0	1228.2	1228.4	1228.6	1228.9	1229.1	1228.9	1228.6	1228.4
147.5°	1276.4	1272.5	1268.6	1267.0	1267.9	1268.9	1269.7	1270.6	1269.7	1268.9	1267.9
150°	1299.6	1295.8	1292.1	1291.0	1292.6	1294.3	1296.0	1297.6	1296.0	1294.3	1292.6
152.5°	1321.0	1317.4	1313.9	1313.0	1314.8	1316.6	1318.5	1320.3	1318.5	1316.6	1314.8
155°	1350.9	1348.2	1345.3	1345.0	1347.0	1349.2	1351.3	1353.4	1351.3	1349.2	1347.0
157.5°	1376.2	1374.2	1372.3	1372.2	1374.0	1375.7	1377.5	1379.3	1377.5	1375.7	1374.0
160°	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1393.1	1391.6	1390.3
162.5°	1404.6	1403.4	1402.2	1402.3	1403.8	1405.2	1406.5	1408.0	1406.5	1405.2	1403.8
165°	1421.5	1420.8	1420.1	1420.5	1421.9	1423.2	1424.7	1426.1	1424.7	1423.2	1421.9
167.5°	1434.9	1434.3	1433.6	1433.9	1435.4	1436.8	1438.1	1439.6	1438.1	1436.8	1435.4
170°	1442.0	1441.5	1441.1	1441.5	1442.9	1444.3	1445.7	1447.2	1445.7	1444.3	1442.9
172.5°	1447.0	1446.6	1446.1	1446.6	1447.9	1449.4	1450.8	1452.2	1450.8	1449.4	1447.9
175°	1452.5	1452.1	1451.6	1452.2	1453.8	1455.4	1457.1	1458.7	1457.1	1455.4	1453.8
177.5°	1454.3	1454.1	1454.0	1454.5	1455.9	1457.2	1458.4	1459.7	1458.4	1457.2	1455.9
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	6.6	6.8	7.0	7.3	7.4	7.6	7.6	7.7	8.0	7.7	7.9
90°	11.4	13.6	15.4	17.3	19.2	21.1	22.2	23.4	24.5	25.7	26.6
92.5°	20.3	20.7	21.6	22.6	23.5	24.5	25.1	25.7	26.3	26.9	27.3
95°	37.5	34.5	36.2	37.8	39.4	41.1	42.3	43.4	44.6	45.7	46.2
97.5°	48.8	39.8	43.6	47.4	51.2	55.0	55.9	56.8	57.8	58.7	59.3
100°	58.2	44.1	48.1	52.1	56.1	60.0	61.9	63.8	65.6	67.5	68.7
102.5°	214.9	194.8	161.5	128.3	95.0	61.7	64.1	66.6	69.1	71.5	73.0
105°	348.3	319.9	256.0	192.0	128.1	64.2	66.8	69.4	72.0	74.6	76.3
107.5°	432.0	396.5	319.9	243.2	166.6	90.0	87.3	84.7	82.1	79.5	78.6
110°	486.2	454.9	387.3	319.6	251.9	184.3	160.9	137.5	114.1	90.7	79.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	538.0	531.8	515.1	498.3	481.6	464.9	379.5	294.1	208.8	123.4	81.0
115°	621.6	626.5	632.3	638.2	644.0	649.9	541.5	433.1	324.8	216.4	153.8
117.5°	699.5	703.7	707.7	711.7	715.7	719.8	693.5	667.4	641.1	614.9	574.1
120°	751.3	755.2	759.4	763.6	767.8	772.0	774.8	777.7	780.4	783.3	768.9
122.5°	799.3	803.4	808.0	812.5	817.2	821.7	823.4	825.1	826.8	828.5	826.2
125°	868.4	872.2	876.7	881.1	885.5	890.0	891.7	893.3	894.9	896.6	897.7
127.5°	934.9	938.2	941.5	944.9	948.1	951.5	953.9	956.2	958.6	961.0	962.3
130°	977.7	980.8	983.3	985.9	988.5	991.1	993.7	996.3	998.8	1001.3	1002.5
132.5°	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9	1035.1	1037.2	1039.5	1040.4
135°	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2	1090.5	1092.9	1095.3	1096.1
137.5°	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8	1142.0	1144.4	1146.7	1147.4
140°	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3	1175.4	1177.5	1179.7	1180.1
142.5°	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3	1206.2	1208.2	1210.0	1210.4
145°	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6	1249.2	1250.9	1252.5	1252.8
147.5°	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6	1286.8	1288.0	1289.2	1289.3
150°	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5	1309.8	1311.3	1312.7	1312.8
152.5°	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6	1330.9	1332.3	1333.8	1333.7
155°	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0	1359.3	1360.8	1362.2	1361.9
157.5°	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7	1383.4	1384.9	1386.6	1386.4
160°	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9	1397.3	1398.7	1400.1	1400.0
162.5°	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7	1410.3	1411.9	1413.5	1413.2
165°	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4
167.5°	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8	1439.4	1441.1	1442.7	1442.5
170°	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6	1446.2	1447.9	1449.5	1449.2
172.5°	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6	1451.2	1452.9	1454.5	1454.3
175°	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1	1456.7	1458.4	1460.0	1459.7
177.5°	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0	1457.3	1458.6	1460.0	1459.7
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	8.0	7.8	7.9	7.7	7.9	7.8	8.0	7.9	7.7	8.0	7.7
90°	27.0	27.5	28.0	28.4	28.0	27.5	27.0	26.6	25.7	24.5	23.4
92.5°	27.6	27.9	28.2	28.4	28.2	27.9	27.6	27.3	26.9	26.3	25.7
95°	46.0	45.7	45.5	45.3	45.5	45.7	46.0	46.2	45.7	44.6	43.4
97.5°	59.6	59.9	60.2	60.4	60.2	59.9	59.6	59.3	58.7	57.8	56.8
100°	69.1	69.7	70.1	70.6	70.1	69.7	69.1	68.7	67.5	65.6	63.8
102.5°	73.6	74.3	75.0	75.6	75.0	74.3	73.6	73.0	71.5	69.1	66.6
105°	77.2	78.2	79.1	80.1	79.1	78.2	77.2	76.3	74.6	72.0	69.4
107.5°	79.6	80.5	81.5	82.4	81.5	80.5	79.6	78.6	79.5	82.1	84.7
110°	80.4	81.4	82.3	83.2	82.3	81.4	80.4	79.5	90.7	114.1	137.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	81.8	82.6	83.3	84.0	83.3	82.6	81.8	81.0	123.4	208.8	294.1
115°	136.9	120.1	103.2	86.4	103.2	120.1	136.9	153.8	216.4	324.8	433.1
117.5°	518.8	463.4	408.0	352.6	408.0	463.4	518.8	574.1	614.9	641.1	667.4
120°	737.3	705.7	674.1	642.5	674.1	705.7	737.3	768.9	783.3	780.4	777.7
122.5°	820.1	814.0	807.9	801.7	807.9	814.0	820.1	826.2	828.5	826.8	825.1
125°	898.4	899.1	899.8	900.5	899.8	899.1	898.4	897.7	896.6	894.9	893.3
127.5°	962.4	962.6	962.7	962.9	962.7	962.6	962.4	962.3	961.0	958.6	956.2
130°	1002.3	1002.1	1001.9	1001.6	1001.9	1002.1	1002.3	1002.5	1001.3	998.8	996.3
132.5°	1040.3	1040.0	1039.7	1039.6	1039.7	1040.0	1040.3	1040.4	1039.5	1037.2	1035.1
135°	1095.7	1095.3	1094.8	1094.3	1094.8	1095.3	1095.7	1096.1	1095.3	1092.9	1090.5
137.5°	1146.6	1145.8	1145.0	1144.2	1145.0	1145.8	1146.6	1147.4	1146.7	1144.4	1142.0
140°	1178.9	1177.8	1176.6	1175.4	1176.6	1177.8	1178.9	1180.1	1179.7	1177.5	1175.4
142.5°	1209.3	1208.1	1206.9	1205.7	1206.9	1208.1	1209.3	1210.4	1210.0	1208.2	1206.2
145°	1251.5	1250.4	1249.2	1248.1	1249.2	1250.4	1251.5	1252.8	1252.5	1250.9	1249.2
147.5°	1288.3	1287.3	1286.3	1285.4	1286.3	1287.3	1288.3	1289.3	1289.2	1288.0	1286.8
150°	1311.6	1310.4	1309.2	1308.1	1309.2	1310.4	1311.6	1312.8	1312.7	1311.3	1309.8
152.5°	1332.1	1330.6	1329.0	1327.5	1329.0	1330.6	1332.1	1333.7	1333.8	1332.3	1330.9
155°	1360.0	1358.2	1356.3	1354.4	1356.3	1358.2	1360.0	1361.9	1362.2	1360.8	1359.3
157.5°	1384.6	1382.8	1381.0	1379.1	1381.0	1382.8	1384.6	1386.4	1386.6	1384.9	1383.4
160°	1398.4	1396.7	1395.1	1393.4	1395.1	1396.7	1398.4	1400.0	1400.1	1398.7	1397.3
162.5°	1411.3	1409.2	1407.2	1405.2	1407.2	1409.2	1411.3	1413.2	1413.5	1411.9	1410.3
165°	1427.8	1426.2	1424.5	1422.9	1424.5	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2
167.5°	1440.4	1438.3	1436.1	1434.1	1436.1	1438.3	1440.4	1442.5	1442.7	1441.1	1439.4
170°	1447.2	1445.0	1442.9	1440.8	1442.9	1445.0	1447.2	1449.2	1449.5	1447.9	1446.2
172.5°	1452.2	1450.1	1447.9	1445.9	1447.9	1450.1	1452.2	1454.3	1454.5	1452.9	1451.2
175°	1457.3	1455.0	1452.6	1450.3	1452.6	1455.0	1457.3	1459.7	1460.0	1458.4	1456.7
177.5°	1458.1	1456.4	1454.7	1453.0	1454.7	1456.4	1458.1	1459.7	1460.0	1458.6	1457.3
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	7.6	7.6	7.4	7.3	7.0	6.8	6.6	6.4	6.4	6.1	5.9
90°	22.2	21.1	19.2	17.3	15.4	13.6	11.4	8.8	6.2	3.6	1.0
92.5°	25.1	24.5	23.5	22.6	21.6	20.7	20.3	20.6	20.8	21.0	21.3
95°	42.3	41.1	39.4	37.8	36.2	34.5	37.5	45.3	53.0	60.7	68.4
97.5°	55.9	55.0	51.2	47.4	43.6	39.8	48.8	70.6	92.3	114.1	135.9
100°	61.9	60.0	56.1	52.1	48.1	44.1	58.2	90.2	122.3	154.4	186.4
102.5°	64.1	61.7	95.0	128.3	161.5	194.8	214.9	221.7	228.4	235.2	242.0
105°	66.8	64.2	128.1	192.0	256.0	319.9	348.3	341.2	334.2	327.2	320.2
107.5°	87.3	90.0	166.6	243.2	319.9	396.5	432.0	426.3	420.6	414.9	409.3
110°	160.9	184.3	251.9	319.6	387.3	454.9	486.2	481.3	476.4	471.5	466.6



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	379.5	464.9	481.6	498.3	515.1	531.8	538.0	533.6	529.2	524.9	520.5
115°	541.5	649.9	644.0	638.2	632.3	626.5	621.6	617.5	613.5	609.6	605.6
117.5°	693.5	719.8	715.7	711.7	707.7	703.7	699.5	695.0	690.5	686.1	681.7
120°	774.8	772.0	767.8	763.6	759.4	755.2	751.3	747.8	744.2	740.8	737.3
122.5°	823.4	821.7	817.2	812.5	808.0	803.4	799.3	795.6	791.9	788.2	784.5
125°	891.7	890.0	885.5	881.1	876.7	872.2	868.4	865.4	862.4	859.3	856.3
127.5°	953.9	951.5	948.1	944.9	941.5	938.2	934.9	931.5	928.1	924.7	921.4
130°	993.7	991.1	988.5	985.9	983.3	980.8	977.7	973.9	970.2	966.4	962.7
132.5°	1032.9	1030.7	1028.1	1025.5	1023.0	1020.4	1017.5	1014.3	1011.2	1008.0	1004.8
135°	1088.2	1085.9	1083.7	1081.7	1079.5	1077.5	1074.5	1070.7	1067.0	1063.2	1059.5
137.5°	1139.8	1137.5	1135.1	1132.7	1130.3	1127.9	1125.4	1122.8	1120.2	1117.6	1114.9
140°	1173.3	1171.2	1168.6	1166.1	1163.5	1160.9	1158.6	1156.8	1154.9	1153.1	1151.2
142.5°	1204.3	1202.4	1199.4	1196.4	1193.5	1190.6	1188.3	1186.5	1184.9	1183.2	1181.6
145°	1247.6	1246.0	1242.0	1238.0	1234.1	1230.0	1228.2	1228.4	1228.6	1228.9	1229.1
147.5°	1285.6	1284.3	1280.4	1276.4	1272.5	1268.6	1267.0	1267.9	1268.9	1269.7	1270.6
150°	1308.5	1307.1	1303.3	1299.6	1295.8	1292.1	1291.0	1292.6	1294.3	1296.0	1297.6
152.5°	1329.6	1328.1	1324.6	1321.0	1317.4	1313.9	1313.0	1314.8	1316.6	1318.5	1320.3
155°	1358.0	1356.6	1353.8	1350.9	1348.2	1345.3	1345.0	1347.0	1349.2	1351.3	1353.4
157.5°	1381.7	1380.2	1378.2	1376.2	1374.2	1372.3	1372.2	1374.0	1375.7	1377.5	1379.3
160°	1395.9	1394.5	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5
162.5°	1408.7	1407.1	1405.9	1404.6	1403.4	1402.2	1402.3	1403.8	1405.2	1406.5	1408.0
165°	1424.5	1422.9	1422.2	1421.5	1420.8	1420.1	1420.5	1421.9	1423.2	1424.7	1426.1
167.5°	1437.8	1436.1	1435.5	1434.9	1434.3	1433.6	1433.9	1435.4	1436.8	1438.1	1439.6
170°	1444.6	1442.9	1442.4	1442.0	1441.5	1441.1	1441.5	1442.9	1444.3	1445.7	1447.2
172.5°	1449.6	1447.9	1447.5	1447.0	1446.6	1446.1	1446.6	1447.9	1449.4	1450.8	1452.2
175°	1455.1	1453.5	1453.0	1452.5	1452.1	1451.6	1452.2	1453.8	1455.4	1457.1	1458.7
177.5°	1456.0	1454.7	1454.5	1454.3	1454.1	1454.0	1454.5	1455.9	1457.2	1458.4	1459.7
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	7.1	8.7	9.2	10.5	10.4	10.8	11.2	11.3	11.5	11.4	11.4
90°	3.6	6.2	8.8	11.4	13.6	15.4	17.3	19.2	21.1	22.2	23.4
92.5°	21.0	20.8	20.6	20.3	20.7	21.6	22.6	23.5	24.5	25.1	25.7
95°	60.7	53.0	45.3	37.5	34.5	36.2	37.8	39.4	41.1	42.3	43.4
97.5°	114.1	92.3	70.6	48.8	39.8	43.6	47.4	51.2	55.0	55.9	56.8
100°	154.4	122.3	90.2	58.2	44.1	48.1	52.1	56.1	60.0	61.9	63.8
102.5°	235.2	228.4	221.7	214.9	194.8	161.5	128.3	95.0	61.7	64.1	66.6
105°	327.2	334.2	341.2	348.3	319.9	256.0	192.0	128.1	64.2	66.8	69.4
107.5°	414.9	420.6	426.3	432.0	396.5	319.9	243.2	166.6	90.0	87.3	84.7
110°	471.5	476.4	481.3	486.2	454.9	387.3	319.6	251.9	184.3	160.9	137.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	524.9	529.2	533.6	538.0	531.8	515.1	498.3	481.6	464.9	379.5	294.1
115°	609.6	613.5	617.5	621.6	626.5	632.3	638.2	644.0	649.9	541.5	433.1
117.5°	686.1	690.5	695.0	699.5	703.7	707.7	711.7	715.7	719.8	693.5	667.4
120°	740.8	744.2	747.8	751.3	755.2	759.4	763.6	767.8	772.0	774.8	777.7
122.5°	788.2	791.9	795.6	799.3	803.4	808.0	812.5	817.2	821.7	823.4	825.1
125°	859.3	862.4	865.4	868.4	872.2	876.7	881.1	885.5	890.0	891.7	893.3
127.5°	924.7	928.1	931.5	934.9	938.2	941.5	944.9	948.1	951.5	953.9	956.2
130°	966.4	970.2	973.9	977.7	980.8	983.3	985.9	988.5	991.1	993.7	996.3
132.5°	1008.0	1011.2	1014.3	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9	1035.1
135°	1063.2	1067.0	1070.7	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2	1090.5
137.5°	1117.6	1120.2	1122.8	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8	1142.0
140°	1153.1	1154.9	1156.8	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3	1175.4
142.5°	1183.2	1184.9	1186.5	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3	1206.2
145°	1228.9	1228.6	1228.4	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6	1249.2
147.5°	1269.7	1268.9	1267.9	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6	1286.8
150°	1296.0	1294.3	1292.6	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5	1309.8
152.5°	1318.5	1316.6	1314.8	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6	1330.9
155°	1351.3	1349.2	1347.0	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0	1359.3
157.5°	1377.5	1375.7	1374.0	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7	1383.4
160°	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9	1397.3
162.5°	1406.5	1405.2	1403.8	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7	1410.3
165°	1424.7	1423.2	1421.9	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5	1426.2
167.5°	1438.1	1436.8	1435.4	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8	1439.4
170°	1445.7	1444.3	1442.9	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6	1446.2
172.5°	1450.8	1449.4	1447.9	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6	1451.2
175°	1457.1	1455.4	1453.8	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1	1456.7
177.5°	1458.4	1457.2	1455.9	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0	1457.3
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	11.9	12.1	12.0	12.1	12.5	12.3	12.4
90°	24.5	25.7	26.6	27.0	27.5	28.0	28.4
92.5°	26.3	26.9	27.3	27.6	27.9	28.2	28.4
95°	44.6	45.7	46.2	46.0	45.7	45.5	45.3
97.5°	57.8	58.7	59.3	59.6	59.9	60.2	60.4
100°	65.6	67.5	68.7	69.1	69.7	70.1	70.6
102.5°	69.1	71.5	73.0	73.6	74.3	75.0	75.6
105°	72.0	74.6	76.3	77.2	78.2	79.1	80.1
107.5°	82.1	79.5	78.6	79.6	80.5	81.5	82.4
110°	114.1	90.7	79.5	80.4	81.4	82.3	83.2



TEST NUMBER: P331513-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	208.8	123.4	81.0	81.8	82.6	83.3	84.0
115°	324.8	216.4	153.8	136.9	120.1	103.2	86.4
117.5°	641.1	614.9	574.1	518.8	463.4	408.0	352.6
120°	780.4	783.3	768.9	737.3	705.7	674.1	642.5
122.5°	826.8	828.5	826.2	820.1	814.0	807.9	801.7
125°	894.9	896.6	897.7	898.4	899.1	899.8	900.5
127.5°	958.6	961.0	962.3	962.4	962.6	962.7	962.9
130°	998.8	1001.3	1002.5	1002.3	1002.1	1001.9	1001.6
132.5°	1037.2	1039.5	1040.4	1040.3	1040.0	1039.7	1039.6
135°	1092.9	1095.3	1096.1	1095.7	1095.3	1094.8	1094.3
137.5°	1144.4	1146.7	1147.4	1146.6	1145.8	1145.0	1144.2
140°	1177.5	1179.7	1180.1	1178.9	1177.8	1176.6	1175.4
142.5°	1208.2	1210.0	1210.4	1209.3	1208.1	1206.9	1205.7
145°	1250.9	1252.5	1252.8	1251.5	1250.4	1249.2	1248.1
147.5°	1288.0	1289.2	1289.3	1288.3	1287.3	1286.3	1285.4
150°	1311.3	1312.7	1312.8	1311.6	1310.4	1309.2	1308.1
152.5°	1332.3	1333.8	1333.7	1332.1	1330.6	1329.0	1327.5
155°	1360.8	1362.2	1361.9	1360.0	1358.2	1356.3	1354.4
157.5°	1384.9	1386.6	1386.4	1384.6	1382.8	1381.0	1379.1
160°	1398.7	1400.1	1400.0	1398.4	1396.7	1395.1	1393.4
162.5°	1411.9	1413.5	1413.2	1411.3	1409.2	1407.2	1405.2
165°	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9
167.5°	1441.1	1442.7	1442.5	1440.4	1438.3	1436.1	1434.1
170°	1447.9	1449.5	1449.2	1447.2	1445.0	1442.9	1440.8
172.5°	1452.9	1454.5	1454.3	1452.2	1450.1	1447.9	1445.9
175°	1458.4	1460.0	1459.7	1457.3	1455.0	1452.6	1450.3
177.5°	1458.6	1460.0	1459.7	1458.1	1456.4	1454.7	1453.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5

(END OF REPORT)