

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331614-930

Luminaire Tested: **S122DIW-S1005D1440U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331614-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D1440U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7384.4 lumens
Efficiency: N/A
Efficacy: 89.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	32
3	80	71	64	58	73	65	59	54	54	50	46	45	41	38	35	33	31	27
4	73	63	55	49	67	58	51	46	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	21	18
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	21	18	16
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	21	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	19	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	1.7
10°-20°	343.8	4.7
20°-30°	505.4	6.8
30°-40°	587.0	7.9
40°-50°	586.4	7.9
50°-60°	511.4	6.9
60°-70°	378.1	5.1
70°-80°	214.2	2.9
80°-90°	63.4	0.9
90°-100°	92.3	1.2
100°-110°	286.6	3.9
110°-120°	490.0	6.6
120°-130°	644.3	8.7
130°-140°	723.2	9.8
140°-150°	709.1	9.6
150°-160°	594.8	8.1
160°-170°	394.5	5.3
170°-180°	137.9	1.9
0°-30°	971.4	13.2
0°-40°	1558.4	21.1
0°-60°	2656.1	36.0
0°-90°	3311.8	44.8
90°-120°	868.9	11.8
90°-150°	2945.5	39.9
90°-180°	4073.0	55.2
0°-180°	7384.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	17	43	41	42	6
95°	64	76	79	79	76	73
105°	264	268	270	273	273	279
115°	492	498	497	495	492	486
125°	715	726	723	719	718	639
135°	926	938	942	940	937	715
145°	1123	1132	1139	1140	1136	702
155°	1284	1288	1292	1297	1294	591
165°	1398	1396	1396	1404	1399	394
175°	1454	1450	1448	1456	1449	138
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.3	18.4	18.7	18.8	19.1	19.6	20.3	21.1	21.9	22.6	21.9
90°	1.2	4.5	7.7	11.1	14.3	19.0	25.0	31.0	37.0	43.0	42.5
92.5°	21.9	24.3	26.7	29.1	31.5	33.4	34.8	36.3	37.7	39.1	39.2
95°	63.9	66.6	69.4	72.1	74.8	76.5	77.0	77.5	78.1	78.7	78.7
97.5°	116.8	119.2	121.6	124.0	126.4	128.1	129.1	130.2	131.2	132.2	132.2
100°	156.1	158.2	160.5	162.7	164.9	166.3	167.1	168.0	168.8	169.6	169.6
102.5°	197.4	199.2	200.9	202.6	204.4	205.8	206.8	207.8	208.9	209.9	210.2
105°	264.2	265.1	265.9	266.7	267.5	268.2	268.8	269.3	269.9	270.4	270.9
107.5°	331.6	332.8	334.0	335.3	336.4	337.0	337.0	337.0	337.0	337.0	337.2
110°	374.9	376.5	378.1	379.8	381.4	382.3	382.3	382.3	382.3	382.3	382.3



TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	422.1	423.7	425.3	427.0	428.6	429.3	429.1	428.9	428.7	428.4	427.8
115°	491.6	493.3	494.9	496.6	498.2	498.7	498.2	497.7	497.1	496.6	496.3
117.5°	561.0	563.1	565.3	567.5	569.7	570.1	568.5	567.0	565.4	563.9	563.3
120°	607.2	609.4	611.6	613.8	616.0	616.0	613.8	611.6	609.4	607.2	607.2
122.5°	649.5	652.1	654.7	657.3	660.0	660.5	659.0	657.5	655.9	654.4	653.7
125°	715.3	717.8	720.2	722.7	725.2	726.0	725.2	724.4	723.6	722.7	721.9
127.5°	779.5	782.6	785.7	788.9	792.0	793.0	792.1	791.1	790.1	789.1	788.1
130°	819.8	823.4	827.0	830.5	834.1	835.5	834.9	834.5	833.9	833.3	832.8
132.5°	865.0	868.0	870.8	873.8	876.6	878.2	878.2	878.3	878.5	878.6	877.3
135°	925.5	928.5	931.6	934.5	937.5	939.3	939.9	940.4	940.9	941.5	941.3
137.5°	989.2	991.6	994.1	996.5	999.0	1000.6	1001.4	1002.0	1002.7	1003.5	1003.2
140°	1027.5	1030.0	1032.5	1034.9	1037.4	1039.3	1040.6	1042.0	1043.4	1044.7	1044.7
142.5°	1066.9	1069.3	1071.8	1074.2	1076.7	1078.4	1079.3	1080.3	1081.2	1082.1	1082.3
145°	1123.4	1125.4	1127.2	1129.1	1131.1	1132.9	1134.5	1136.1	1137.8	1139.4	1139.6
147.5°	1173.8	1176.1	1178.4	1180.7	1183.0	1184.7	1185.8	1186.8	1188.0	1189.0	1189.7
150°	1208.2	1209.8	1211.5	1213.2	1214.8	1216.1	1217.2	1218.3	1219.4	1220.5	1221.3
152.5°	1238.7	1240.3	1241.9	1243.6	1245.3	1246.8	1248.1	1249.4	1250.7	1252.0	1253.0
155°	1284.4	1285.2	1286.1	1286.9	1287.7	1288.5	1289.3	1290.1	1290.9	1291.8	1293.1
157.5°	1323.5	1324.0	1324.6	1325.2	1325.7	1326.2	1326.7	1327.2	1327.7	1328.2	1330.0
160°	1347.1	1347.7	1348.2	1348.7	1349.3	1349.7	1350.0	1350.2	1350.5	1350.8	1352.4
162.5°	1368.7	1368.9	1369.0	1369.1	1369.2	1369.4	1369.6	1369.9	1370.2	1370.4	1372.3
165°	1397.5	1397.3	1396.9	1396.7	1396.4	1396.3	1396.3	1396.3	1396.3	1396.3	1398.2
167.5°	1421.6	1420.7	1419.9	1419.1	1418.3	1417.9	1417.8	1417.8	1417.7	1417.6	1419.6
170°	1434.4	1433.5	1432.7	1431.9	1431.1	1430.5	1430.3	1430.0	1429.7	1429.5	1431.3
172.5°	1443.2	1442.4	1441.6	1440.8	1440.0	1439.4	1439.2	1438.8	1438.6	1438.3	1440.2
175°	1454.0	1453.2	1452.4	1451.6	1450.7	1450.1	1449.5	1448.9	1448.5	1447.9	1449.8
177.5°	1458.5	1457.8	1457.2	1456.5	1455.9	1455.3	1454.8	1454.4	1454.0	1453.5	1454.8
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5



TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	21.0	20.3	19.5	19.0	18.8	18.7	18.5	18.3
90°	41.9	41.4	40.8	40.7	41.0	41.3	41.5	41.8
92.5°	39.3	39.4	39.5	39.6	39.6	39.7	39.8	39.8
95°	78.7	78.7	78.7	78.4	77.9	77.3	76.7	76.2
97.5°	132.2	132.2	132.2	132.2	132.2	132.1	132.1	132.0
100°	169.6	169.6	169.6	169.5	169.2	168.9	168.7	168.4
102.5°	210.3	210.6	210.8	210.8	210.5	210.3	209.9	209.7
105°	271.5	272.1	272.6	272.9	272.9	272.9	272.9	272.9
107.5°	337.5	337.7	337.9	337.4	336.1	334.8	333.6	332.3
110°	382.3	382.3	382.3	381.8	381.0	380.2	379.4	378.5



TEST NUMBER: P331614-930

CATALOG NUMBER: S122DIW-S1005D1440U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	427.1	426.5	425.8	425.2	424.6	424.0	423.4	422.8
115°	496.0	495.7	495.5	494.9	494.1	493.3	492.4	491.6
117.5°	562.6	562.0	561.3	560.5	559.7	558.9	558.1	557.3
120°	607.2	607.2	607.2	606.7	605.9	605.1	604.3	603.5
122.5°	653.1	652.4	651.8	651.1	650.5	650.0	649.3	648.7
125°	721.1	720.2	719.4	718.9	718.6	718.4	718.1	717.8
127.5°	787.1	786.1	785.1	784.2	783.3	782.4	781.6	780.7
130°	832.3	831.7	831.1	830.3	829.2	828.2	827.0	826.0
132.5°	876.2	875.0	873.8	872.7	871.9	871.0	870.1	869.2
135°	940.9	940.7	940.4	939.9	939.1	938.2	937.4	936.6
137.5°	1003.0	1002.8	1002.6	1001.9	1000.9	999.7	998.7	997.5
140°	1044.7	1044.7	1044.7	1044.2	1043.1	1042.0	1040.9	1039.8
142.5°	1082.6	1082.8	1083.0	1082.6	1081.5	1080.4	1079.3	1078.2
145°	1140.0	1140.2	1140.4	1140.0	1139.0	1137.9	1136.8	1135.7
147.5°	1190.3	1190.8	1191.5	1191.2	1190.2	1189.1	1188.1	1187.1
150°	1222.1	1222.9	1223.8	1223.8	1222.9	1222.1	1221.3	1220.5
152.5°	1254.0	1255.1	1256.1	1256.1	1255.1	1254.0	1253.0	1252.0
155°	1294.5	1295.9	1297.2	1297.5	1296.7	1295.9	1295.1	1294.3
157.5°	1331.9	1333.7	1335.6	1335.9	1334.6	1333.3	1332.0	1330.6
160°	1354.0	1355.7	1357.3	1357.6	1356.5	1355.4	1354.4	1353.2
162.5°	1374.2	1376.1	1377.9	1378.2	1376.9	1375.6	1374.3	1372.9
165°	1400.1	1402.0	1403.9	1404.2	1402.8	1401.5	1400.1	1398.7
167.5°	1421.5	1423.4	1425.3	1425.6	1424.2	1422.7	1421.3	1419.8
170°	1433.3	1435.2	1437.1	1437.2	1435.6	1433.9	1432.3	1430.7
172.5°	1442.1	1444.1	1445.9	1446.1	1444.5	1442.8	1441.2	1439.6
175°	1451.7	1453.6	1455.6	1455.7	1454.0	1452.4	1450.7	1449.1
177.5°	1456.2	1457.5	1458.8	1458.8	1457.5	1456.2	1454.8	1453.5
180°	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5	1456.5

(END OF REPORT)