

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331518-935

Luminaire Tested: **S122DIW-S485D1240U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331518-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D1240U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5405.9 lumens
Efficiency: N/A
Efficacy: 100.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	103	103	103	103	92	92	92	92	73	73	73	55	55	55	39	39	39	32								
1	94	89	86	82	84	81	77	74	64	62	60	49	47	46	35	34	33	27								
2	85	78	72	67	76	70	65	61	56	52	49	43	40	38	30	29	28	22								
3	78	69	61	56	70	62	56	51	49	45	42	38	35	32	27	25	24	19								
4	71	61	53	47	64	55	48	43	44	39	35	34	30	28	24	22	20	16								
5	65	54	46	40	58	49	42	37	39	34	30	30	27	24	22	19	18	14								
6	60	48	40	35	54	44	37	32	35	30	26	27	24	21	20	17	16	12								
7	55	43	36	30	50	39	33	28	32	27	23	25	21	18	18	16	14	11								
8	51	39	32	27	46	36	29	25	29	24	20	22	19	16	16	14	12	10								
9	48	36	28	24	43	33	26	22	26	22	18	21	17	15	15	13	11	9								
10	44	33	26	21	40	30	24	19	24	20	16	19	16	13	14	12	10	8								

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10797	10797	10797
5°	10838	10682	10746
10°	10775	10575	10627
15°	10641	10437	10425
20°	10452	10232	10220
25°	10265	9978	9978
30°	10023	9747	9661
35°	9798	9469	9329
40°	9514	9190	9012
45°	9236	8912	8690
50°	8932	8626	8317
55°	8617	8290	7983
60°	8263	7892	7598
65°	7885	7492	7148
70°	7407	7010	6680
75°	6744	6457	6301
80°	5979	5793	5504
85°	4872	4650	4168



TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	1.2
10°-20°	176.9	3.3
20°-30°	260.1	4.8
30°-40°	302.1	5.6
40°-50°	301.8	5.6
50°-60°	263.2	4.9
60°-70°	194.6	3.6
70°-80°	110.2	2.0
80°-90°	34.9	0.6
90°-100°	83.8	1.6
100°-110°	260.4	4.8
110°-120°	445.0	8.2
120°-130°	585.3	10.8
130°-140°	656.9	12.2
140°-150°	644.1	11.9
150°-160°	540.2	10.0
160°-170°	358.3	6.6
170°-180°	125.2	2.3
0°-30°	499.9	9.2
0°-40°	802.0	14.8
0°-60°	1366.9	25.3
0°-90°	1706.7	31.6
90°-120°	789.2	14.6
90°-150°	2675.4	49.5
90°-180°	3699.0	68.4
0°-180°	5405.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	669	669	669	669	669	
5°	669	666	659	664	663	63
15°	637	632	624	627	624	179
25°	576	571	560	561	560	265
35°	497	490	480	476	473	310
45°	404	400	390	384	381	312
55°	306	302	294	287	284	274
65°	206	202	196	190	187	204
75°	108	107	104	100	101	115
85°	26	26	25	23	22	30
90°	1	15	39	37	38	4
95°	58	69	72	71	69	67
105°	240	243	246	248	248	253
115°	447	453	451	450	447	442
125°	650	659	656	653	652	580
135°	841	852	855	854	851	649
145°	1020	1028	1035	1036	1032	637
155°	1167	1170	1173	1178	1176	537
165°	1269	1268	1268	1275	1270	358
175°	1321	1318	1315	1322	1316	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	671.8	671.2	670.7	670.1	669.5	668.7	667.4	666.2	664.9	663.6	664.8
5°	668.7	668.1	667.6	667.0	666.5	665.4	663.8	662.3	660.6	659.1	660.2
7.5°	662.8	661.9	661.1	660.1	659.3	658.1	656.4	654.9	653.2	651.6	652.8
10°	657.2	656.2	655.1	654.2	653.2	651.8	650.1	648.4	646.7	645.0	646.1
12.5°	649.5	648.6	647.6	646.8	645.9	644.6	642.9	641.2	639.5	637.7	638.5
15°	636.6	635.8	634.9	634.0	633.2	631.8	629.9	628.1	626.2	624.4	624.9
17.5°	620.1	619.3	618.5	617.6	616.7	615.4	613.5	611.6	609.7	607.8	608.5
20°	608.3	607.4	606.6	605.7	604.9	603.5	601.4	599.4	597.4	595.5	595.9
22.5°	596.5	595.3	594.1	592.9	591.7	590.1	588.2	586.3	584.4	582.6	582.6
25°	576.2	575.0	573.9	572.7	571.6	569.8	567.4	564.9	562.5	560.1	560.3
27.5°	553.0	552.0	551.0	549.9	548.9	547.4	545.5	543.5	541.7	539.8	539.3
30°	537.6	536.4	535.3	534.2	533.0	531.3	529.2	527.1	525.0	522.8	522.4
32.5°	521.1	520.2	519.3	518.3	517.5	515.8	513.6	511.3	509.1	506.9	506.1
35°	497.1	495.6	494.2	492.8	491.4	489.5	487.2	484.9	482.6	480.4	479.5
37.5°	469.9	468.6	467.4	466.1	464.9	463.1	460.8	458.6	456.2	454.0	452.9
40°	451.4	450.2	449.1	448.0	446.9	445.1	442.8	440.6	438.2	436.0	434.7
42.5°	433.4	432.2	431.1	430.0	428.9	427.1	424.8	422.6	420.3	417.9	416.6
45°	404.5	403.5	402.4	401.5	400.5	398.9	396.7	394.6	392.4	390.3	388.7
47.5°	375.7	374.7	373.8	372.8	371.9	370.3	368.1	365.8	363.6	361.4	359.7
50°	355.6	354.9	354.1	353.4	352.8	351.4	349.4	347.4	345.3	343.4	341.4
52.5°	336.0	335.1	334.2	333.2	332.3	330.9	329.0	327.1	325.2	323.3	321.7
55°	306.1	305.2	304.4	303.5	302.6	301.4	299.6	297.9	296.2	294.5	292.8
57.5°	276.0	275.3	274.6	274.0	273.3	272.0	270.1	268.2	266.3	264.4	262.7
60°	255.9	255.4	254.8	254.2	253.7	252.4	250.4	248.3	246.3	244.4	242.8
62.5°	236.3	235.5	234.5	233.6	232.7	231.5	230.0	228.4	226.9	225.3	223.9
65°	206.4	205.5	204.7	203.8	203.0	201.8	200.4	199.0	197.5	196.1	194.8
67.5°	175.9	175.2	174.5	173.8	173.1	172.2	170.9	169.6	168.3	167.0	166.1
70°	156.9	156.4	155.8	155.2	154.6	153.7	152.4	151.1	149.8	148.5	147.6
72.5°	137.3	136.8	136.2	135.6	135.1	134.4	133.5	132.7	131.9	131.0	130.0
75°	108.1	107.7	107.5	107.2	106.9	106.4	105.6	105.0	104.3	103.5	102.6
77.5°	81.8	81.3	80.8	80.3	79.8	79.5	79.2	78.9	78.6	78.4	77.9
80°	64.3	64.1	64.1	63.9	63.7	63.5	63.2	62.9	62.7	62.3	61.9
82.5°	47.9	47.8	47.8	47.8	47.7	47.6	47.4	47.3	47.1	46.9	46.4
85°	26.3	26.3	26.1	25.9	25.8	25.7	25.5	25.4	25.2	25.1	24.6
87.5°	9.5	9.8	10.2	10.6	10.9	11.5	12.4	13.3	14.1	15.0	14.6
90°	1.1	4.1	7.1	10.1	13.0	17.2	22.7	28.2	33.6	39.1	38.6
92.5°	19.9	22.0	24.3	26.4	28.6	30.3	31.6	32.9	34.2	35.5	35.6
95°	58.0	60.5	63.0	65.5	68.0	69.5	70.0	70.4	70.9	71.5	71.5
97.5°	106.1	108.2	110.5	112.6	114.8	116.3	117.3	118.2	119.2	120.1	120.1
100°	141.8	143.8	145.8	147.7	149.7	151.1	151.8	152.6	153.3	154.0	154.0
102.5°	179.3	180.9	182.4	184.1	185.6	186.9	187.9	188.8	189.8	190.7	190.9
105°	240.0	240.7	241.5	242.3	243.0	243.7	244.1	244.6	245.1	245.6	246.1
107.5°	301.2	302.3	303.4	304.4	305.6	306.1	306.1	306.1	306.1	306.1	306.3
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.4	384.9	386.3	387.9	389.3	389.9	389.8	389.6	389.3	389.2	388.6
115°	446.6	448.1	449.5	451.0	452.5	453.0	452.5	452.0	451.5	451.0	450.8
117.5°	509.5	511.5	513.5	515.5	517.5	517.8	516.3	515.0	513.6	512.2	511.6
120°	551.5	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	551.5
122.5°	589.9	592.3	594.7	597.0	599.4	599.9	598.6	597.2	595.7	594.3	593.7
125°	649.7	651.9	654.2	656.4	658.7	659.4	658.7	658.0	657.2	656.4	655.7
127.5°	708.0	710.8	713.7	716.5	719.4	720.3	719.5	718.5	717.6	716.7	715.8
130°	744.7	747.9	751.1	754.3	757.5	758.9	758.5	757.9	757.4	756.9	756.4
132.5°	785.7	788.3	791.0	793.6	796.3	797.6	797.7	797.8	797.9	798.0	796.9
135°	840.7	843.3	846.1	848.9	851.6	853.2	853.7	854.2	854.7	855.1	854.9
137.5°	898.5	900.7	902.9	905.2	907.4	908.9	909.5	910.2	910.8	911.5	911.3
140°	933.3	935.6	937.8	940.0	942.3	944.0	945.2	946.5	947.7	948.9	948.9
142.5°	969.1	971.3	973.5	975.8	978.0	979.5	980.3	981.2	982.1	982.9	983.1
145°	1020.4	1022.2	1023.9	1025.6	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2
147.5°	1066.2	1068.2	1070.3	1072.5	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6
150°	1097.4	1098.9	1100.4	1101.9	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3
152.5°	1125.2	1126.6	1128.1	1129.5	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2
155°	1166.7	1167.4	1168.1	1168.9	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6
157.5°	1202.1	1202.6	1203.2	1203.7	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1
160°	1223.6	1224.1	1224.6	1225.1	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4
162.5°	1243.2	1243.4	1243.5	1243.5	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5
165°	1269.4	1269.1	1268.9	1268.6	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0
167.5°	1291.2	1290.5	1289.8	1289.0	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4
170°	1302.9	1302.1	1301.4	1300.6	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1
172.5°	1310.9	1310.2	1309.4	1308.6	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2
175°	1320.7	1320.0	1319.2	1318.4	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9
177.5°	1324.7	1324.1	1323.5	1322.9	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	665.9	667.0	668.1	668.7	668.4	668.1	668.0	667.7
5°	661.4	662.5	663.7	664.1	663.8	663.5	663.2	663.0
7.5°	653.9	655.0	656.3	656.6	656.3	656.0	655.7	655.4
10°	647.2	648.4	649.5	649.9	649.5	649.0	648.6	648.2
12.5°	639.4	640.2	640.9	641.2	640.8	640.6	640.2	639.9
15°	625.5	626.1	626.6	626.5	625.9	625.2	624.5	623.7
17.5°	609.1	609.8	610.4	610.4	609.7	609.1	608.4	607.7
20°	596.3	596.8	597.2	597.1	596.5	595.9	595.4	594.8
22.5°	582.7	582.8	582.9	582.8	582.5	582.1	581.8	581.4
25°	560.7	560.9	561.2	561.2	560.9	560.7	560.3	560.1
27.5°	538.9	538.5	538.0	537.5	536.8	536.1	535.5	534.8
30°	521.9	521.5	521.1	520.6	520.0	519.4	518.8	518.2
32.5°	505.3	504.5	503.8	503.1	502.5	502.0	501.4	500.8
35°	478.6	477.8	476.9	476.1	475.4	474.7	474.0	473.3
37.5°	451.9	450.8	449.8	448.8	448.2	447.5	446.8	446.2
40°	433.4	432.1	430.8	429.9	429.3	428.8	428.2	427.6
42.5°	415.2	413.8	412.3	411.3	410.4	409.7	408.9	408.0
45°	387.2	385.6	384.0	383.0	382.4	381.9	381.3	380.6
47.5°	358.1	356.4	354.7	353.5	352.7	351.9	351.0	350.2
50°	339.4	337.3	335.4	334.0	333.3	332.6	331.8	331.1
52.5°	320.0	318.3	316.7	315.4	314.4	313.5	312.5	311.6
55°	291.1	289.4	287.7	286.5	285.7	285.0	284.3	283.6
57.5°	261.1	259.3	257.7	256.6	256.0	255.5	254.9	254.3
60°	241.2	239.6	238.1	237.0	236.6	236.2	235.7	235.3
62.5°	222.4	220.9	219.5	218.5	217.9	217.4	216.9	216.3
65°	193.6	192.3	191.0	189.9	189.2	188.6	187.9	187.1
67.5°	165.1	164.0	163.1	162.3	161.7	161.1	160.6	160.0
70°	146.5	145.5	144.6	143.8	143.2	142.6	142.1	141.5
72.5°	129.1	128.0	127.1	126.3	125.9	125.4	124.9	124.5
75°	101.8	101.0	100.1	99.8	100.1	100.4	100.7	101.0
77.5°	77.5	77.1	76.6	76.2	75.8	75.4	75.0	74.6
80°	61.5	61.0	60.7	60.3	60.0	59.8	59.4	59.2
82.5°	45.9	45.3	44.8	44.4	44.4	44.3	44.3	44.3
85°	24.2	23.8	23.3	23.1	22.9	22.8	22.6	22.5
87.5°	14.1	13.7	13.3	13.0	12.9	12.8	12.8	12.7
90°	38.1	37.6	37.1	36.9	37.2	37.5	37.7	38.0
92.5°	35.7	35.8	35.9	36.0	36.0	36.1	36.2	36.2
95°	71.5	71.5	71.5	71.2	70.7	70.2	69.7	69.2
97.5°	120.1	120.1	120.1	120.1	120.0	120.0	119.9	119.9
100°	154.0	154.0	154.0	153.9	153.7	153.4	153.2	152.9
102.5°	191.1	191.3	191.5	191.5	191.2	191.0	190.7	190.5
105°	246.6	247.1	247.6	247.9	247.9	247.9	247.9	247.9
107.5°	306.5	306.7	306.9	306.4	305.3	304.2	303.0	301.9
110°	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.9



TEST NUMBER: P331518-935

CATALOG NUMBER: S122DIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.0	387.4	386.8	386.2	385.6	385.1	384.6	384.0
115°	450.6	450.3	450.0	449.5	448.8	448.1	447.3	446.6
117.5°	511.0	510.4	509.8	509.2	508.4	507.6	507.0	506.2
120°	551.5	551.5	551.5	551.1	550.4	549.7	548.9	548.2
122.5°	593.2	592.6	592.0	591.4	590.9	590.3	589.8	589.3
125°	655.0	654.2	653.5	653.0	652.7	652.5	652.2	651.9
127.5°	715.0	714.0	713.2	712.3	711.5	710.8	710.0	709.1
130°	756.0	755.4	754.9	754.2	753.2	752.3	751.2	750.2
132.5°	795.8	794.7	793.7	792.7	791.9	791.1	790.3	789.5
135°	854.7	854.5	854.2	853.7	852.9	852.2	851.4	850.7
137.5°	911.0	910.9	910.7	910.1	909.0	908.1	907.1	906.1
140°	948.9	948.9	948.9	948.5	947.4	946.5	945.5	944.5
142.5°	983.3	983.5	983.7	983.3	982.3	981.3	980.3	979.3
145°	1035.4	1035.7	1035.9	1035.5	1034.6	1033.5	1032.6	1031.6
147.5°	1081.1	1081.7	1082.2	1082.0	1081.1	1080.1	1079.2	1078.2
150°	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6
152.5°	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2
155°	1175.9	1177.1	1178.3	1178.5	1177.8	1177.1	1176.3	1175.6
157.5°	1209.8	1211.4	1213.1	1213.4	1212.2	1211.0	1209.8	1208.6
160°	1229.9	1231.4	1232.9	1233.1	1232.2	1231.1	1230.2	1229.2
162.5°	1248.2	1249.8	1251.5	1251.8	1250.6	1249.4	1248.2	1247.1
165°	1271.7	1273.4	1275.2	1275.4	1274.2	1273.0	1271.7	1270.5
167.5°	1291.2	1292.9	1294.6	1294.9	1293.6	1292.3	1291.0	1289.7
170°	1301.8	1303.6	1305.4	1305.4	1304.0	1302.5	1301.0	1299.5
172.5°	1309.9	1311.6	1313.4	1313.5	1312.0	1310.5	1309.1	1307.5
175°	1318.6	1320.3	1322.1	1322.2	1320.7	1319.2	1317.8	1316.2
177.5°	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)