

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331585-930

Luminaire Tested: **S122DIW-S1005D435U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331585-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4999.2 lumens
Efficiency: N/A
Efficacy: 95.4 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	95	95	95	85	85	85	76	76	76	72
1	103	99	95	92	98	94	91	88	85	82	80	76	74	73	68	67	66	62
2	95	87	81	76	90	83	78	73	75	71	67	68	65	62	61	59	56	53
3	87	78	70	65	82	74	67	62	67	62	58	61	57	53	55	52	49	46
4	80	69	61	55	76	66	59	53	60	54	50	55	50	46	49	46	43	40
5	74	62	54	48	70	59	52	47	54	48	44	49	44	41	45	41	38	35
6	68	56	48	42	65	54	46	41	49	43	38	45	40	36	41	37	34	31
7	63	51	43	38	60	49	42	36	45	39	34	41	36	32	38	33	30	28
8	59	47	39	34	56	45	38	33	41	35	31	38	33	29	35	30	27	25
9	55	43	35	30	52	41	34	29	38	32	28	35	30	26	32	28	25	23
10	52	40	32	27	49	38	31	27	35	29	25	33	28	24	30	26	23	21

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	154.8	3.1
10°-20°	450.1	9.0
20°-30°	653.3	13.1
30°-40°	689.3	13.8
40°-50°	610.4	12.2
50°-60°	487.1	9.7
60°-70°	331.1	6.6
70°-80°	169.7	3.4
80°-90°	42.1	0.8
90°-100°	16.1	0.3
100°-110°	58.9	1.2
110°-120°	157.5	3.1
120°-130°	259.9	5.2
130°-140°	276.4	5.5
140°-150°	256.9	5.1
150°-160°	206.6	4.1
160°-170°	133.1	2.7
170°-180°	45.8	0.9
0°-30°	1258.2	25.2
0°-40°	1947.5	39.0
0°-60°	3045.0	60.9
0°-90°	3587.9	71.8
90°-120°	232.4	4.6
90°-150°	1025.8	20.5
90°-180°	1411.0	28.2
0°-180°	4999.2	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	37
90°	9	0	9	0	9	6
95°	15	23	15	23	15	14
105°	26	106	26	106	26	28
115°	28	200	28	200	28	72
125°	298	283	298	283	298	258
135°	362	351	362	351	362	279
145°	413	407	413	407	413	258
155°	448	448	448	448	448	207
165°	471	472	471	472	471	133
175°	480	483	480	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	14.8	14.8	15.3	14.8	14.8	15.2	15.1	14.5	15.0	15.4	15.7
90°	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7	7.3	6.9	6.4
92.5°	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5	8.3	8.1	7.7
95°	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3	13.9	13.6	13.0
97.5°	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8	18.5	18.2	17.0
100°	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1	20.5	19.9	18.5
102.5°	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0	21.2	20.4	31.5
105°	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0	22.1	21.3	42.4
107.5°	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0	28.9	29.8	55.1
110°	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5	53.2	61.0	83.3



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3	125.6	153.8	159.3
115°	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3	179.1	215.0	213.0
117.5°	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8	229.5	238.1	236.8
120°	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3	256.3	255.4	254.0
122.5°	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0	272.5	271.9	270.4
125°	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5	295.0	294.5	293.0
127.5°	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4	315.6	314.8	313.7
130°	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6	328.7	327.9	327.1
132.5°	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5	341.8	341.0	340.1
135°	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9	360.0	359.3	358.6
137.5°	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9	377.1	376.3	375.5
140°	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9	388.2	387.5	386.6
142.5°	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1	398.4	397.8	396.8
145°	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4	412.8	412.2	410.9
147.5°	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7	425.3	424.9	423.6
150°	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4	432.9	432.4	431.2
152.5°	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3	439.9	439.4	438.2
155°	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8	449.3	448.8	447.9
157.5°	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7	457.1	456.6	456.0
160°	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3	461.9	461.4	460.9
162.5°	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6	466.1	465.5	465.1
165°	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8	470.6
167.5°	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3	475.7	475.2	475.0
170°	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5	477.9	477.4	477.3
172.5°	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1	479.6	479.1	478.9
175°	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0	481.4	480.9	480.7
177.5°	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2	481.8	481.3	481.3
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	16.1	16.0	15.9	16.7	15.1	14.9	12.7	11.1	10.8	10.4	9.5
90°	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3	1.2	2.0	2.9
92.5°	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0	6.9	6.8	6.8
95°	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7	20.1	17.5	15.0
97.5°	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9	37.7	30.6	23.3
100°	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7	51.0	40.4	29.8
102.5°	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1	77.9	75.6	73.4
105°	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9	108.3	110.6	112.9
107.5°	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4	137.3	139.2	141.0
110°	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3	156.0	157.6	159.2



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2	173.7	175.1	176.5
115°	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4	201.7	203.0	204.3
117.5°	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5	227.0	228.4	229.9
120°	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9	245.1	246.2	247.4
122.5°	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5	260.7	262.0	263.2
125°	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3	284.3	285.4	286.3
127.5°	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8	306.0	307.0	308.2
130°	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5	319.8	321.0	322.2
132.5°	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5	333.5	334.5	335.6
135°	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6	351.8	353.0	354.2
137.5°	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9	369.7	370.6	371.5
140°	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9	381.5	382.1	382.7
142.5°	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9	391.5	392.0	392.6
145°	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7	406.6	406.5	406.4
147.5°	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4	420.1	419.8	419.6
150°	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3	428.8	428.2	427.7
152.5°	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8	436.3	435.6	435.0
155°	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8	447.1	446.4	445.7
157.5°	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3	455.8	455.2	454.6
160°	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	460.9	460.5	460.0
162.5°	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9	465.4	464.9	464.5
165°	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8	471.4	470.9	470.4
167.5°	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3	475.8	475.4	474.9
170°	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8	478.3	477.8	477.4
172.5°	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5	480.0	479.6	479.1
175°	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7	482.1	481.5	481.0
177.5°	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0	482.6	482.1	481.7
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	9.2	8.9	8.5	8.6	8.2	7.9	7.5	7.6	7.7	6.7	6.8
90°	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7	8.2	8.5	8.8
92.5°	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5	8.7	8.9	9.0
95°	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3	14.8	15.2	15.3
97.5°	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8	19.2	19.4	19.6
100°	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1	21.7	22.3	22.7
102.5°	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0	22.8	23.6	24.1
105°	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0	23.8	24.7	25.3
107.5°	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0	27.1	26.3	26.0
110°	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5	37.7	30.0	26.3



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3	69.1	40.8	26.8
115°	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3	107.5	71.6	50.9
117.5°	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8	212.1	203.4	190.0
120°	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3	258.2	259.2	254.4
122.5°	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0	273.5	274.1	273.4
125°	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5	296.1	296.6	297.0
127.5°	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4	317.2	318.0	318.4
130°	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6	330.4	331.3	331.7
132.5°	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5	343.2	343.9	344.2
135°	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9	361.6	362.4	362.6
137.5°	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9	378.6	379.4	379.6
140°	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9	389.6	390.3	390.4
142.5°	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1	399.7	400.4	400.5
145°	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4	413.8	414.4	414.5
147.5°	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7	426.2	426.6	426.6
150°	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4	433.8	434.3	434.4
152.5°	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3	440.8	441.3	441.2
155°	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8	450.2	450.7	450.6
157.5°	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7	458.2	458.8	458.7
160°	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3	462.8	463.3	463.2
162.5°	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6	467.2	467.7	467.6
165°	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9	472.4	473.0	473.0
167.5°	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3	476.8	477.4	477.3
170°	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5	479.1	479.6	479.5
172.5°	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1	480.7	481.3	481.2
175°	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0	482.5	483.1	483.0
177.5°	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2	482.6	483.1	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	6.8	6.3	6.4	5.9	6.4	6.3	6.8	6.8	6.7	7.7	7.6
90°	9.0	9.1	9.3	9.4	9.3	9.1	9.0	8.8	8.5	8.2	7.7
92.5°	9.1	9.2	9.3	9.4	9.3	9.2	9.1	9.0	8.9	8.7	8.5
95°	15.2	15.2	15.1	15.0	15.1	15.2	15.2	15.3	15.2	14.8	14.3
97.5°	19.7	19.8	19.9	20.0	19.9	19.8	19.7	19.6	19.4	19.2	18.8
100°	22.9	23.1	23.2	23.3	23.2	23.1	22.9	22.7	22.3	21.7	21.1
102.5°	24.4	24.6	24.8	25.0	24.8	24.6	24.4	24.1	23.6	22.8	22.0
105°	25.5	25.8	26.2	26.5	26.2	25.8	25.5	25.3	24.7	23.8	23.0
107.5°	26.3	26.7	26.9	27.2	26.9	26.7	26.3	26.0	26.3	27.1	28.0
110°	26.6	26.9	27.2	27.6	27.2	26.9	26.6	26.3	30.0	37.7	45.5



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	27.1	27.3	27.6	27.8	27.6	27.3	27.1	26.8	40.8	69.1	97.3
115°	45.3	39.7	34.2	28.5	34.2	39.7	45.3	50.9	71.6	107.5	143.3
117.5°	171.6	153.3	135.0	116.7	135.0	153.3	171.6	190.0	203.4	212.1	220.8
120°	243.9	233.5	223.0	212.5	223.0	233.5	243.9	254.4	259.2	258.2	257.3
122.5°	271.3	269.3	267.3	265.2	267.3	269.3	271.3	273.4	274.1	273.5	273.0
125°	297.3	297.5	297.7	297.9	297.7	297.5	297.3	297.0	296.6	296.1	295.5
127.5°	318.5	318.5	318.5	318.5	318.5	318.5	318.5	318.4	318.0	317.2	316.4
130°	331.7	331.6	331.5	331.4	331.5	331.6	331.7	331.7	331.3	330.4	329.6
132.5°	344.1	344.1	344.1	344.0	344.1	344.1	344.1	344.2	343.9	343.2	342.5
135°	362.6	362.4	362.2	362.1	362.2	362.4	362.6	362.6	362.4	361.6	360.9
137.5°	379.4	379.1	378.9	378.5	378.9	379.1	379.4	379.6	379.4	378.6	377.9
140°	390.0	389.6	389.3	388.9	389.3	389.6	390.0	390.4	390.3	389.6	388.9
142.5°	400.1	399.7	399.3	398.9	399.3	399.7	400.1	400.5	400.4	399.7	399.1
145°	414.1	413.7	413.4	412.9	413.4	413.7	414.1	414.5	414.4	413.8	413.4
147.5°	426.2	425.9	425.6	425.3	425.6	425.9	426.2	426.6	426.6	426.2	425.7
150°	434.0	433.6	433.2	432.8	433.2	433.6	434.0	434.4	434.3	433.8	433.4
152.5°	440.8	440.3	439.7	439.2	439.7	440.3	440.8	441.2	441.3	440.8	440.3
155°	450.0	449.4	448.7	448.2	448.7	449.4	450.0	450.6	450.7	450.2	449.8
157.5°	458.1	457.5	456.9	456.3	456.9	457.5	458.1	458.7	458.8	458.2	457.7
160°	462.7	462.1	461.5	461.1	461.5	462.1	462.7	463.2	463.3	462.8	462.3
162.5°	466.9	466.3	465.6	465.0	465.6	466.3	466.9	467.6	467.7	467.2	466.6
165°	472.4	471.9	471.3	470.8	471.3	471.9	472.4	473.0	473.0	472.4	471.9
167.5°	476.5	475.9	475.2	474.5	475.2	475.9	476.5	477.3	477.4	476.8	476.3
170°	478.8	478.1	477.4	476.7	477.4	478.1	478.8	479.5	479.6	479.1	478.5
172.5°	480.5	479.8	479.1	478.4	479.1	479.8	480.5	481.2	481.3	480.7	480.1
175°	482.2	481.4	480.6	479.9	480.6	481.4	482.2	483.0	483.1	482.5	482.0
177.5°	482.4	481.8	481.3	480.8	481.3	481.8	482.4	483.0	483.1	482.6	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	7.5	7.9	8.2	8.6	8.5	8.9	9.2	9.5	10.4	10.8	11.1
90°	7.3	6.9	6.4	5.7	5.1	4.5	3.8	2.9	2.0	1.2	0.3
92.5°	8.3	8.1	7.7	7.5	7.2	6.8	6.8	6.8	6.8	6.9	7.0
95°	13.9	13.6	13.0	12.5	12.0	11.4	12.4	15.0	17.5	20.1	22.7
97.5°	18.5	18.2	17.0	15.7	14.4	13.2	16.1	23.3	30.6	37.7	44.9
100°	20.5	19.9	18.5	17.2	15.9	14.6	19.2	29.8	40.4	51.0	61.7
102.5°	21.2	20.4	31.5	42.5	53.5	64.5	71.1	73.4	75.6	77.9	80.1
105°	22.1	21.3	42.4	63.5	84.7	105.8	115.2	112.9	110.6	108.3	105.9
107.5°	28.9	29.8	55.1	80.5	105.8	131.2	142.9	141.0	139.2	137.3	135.4
110°	53.2	61.0	83.3	105.7	128.1	150.5	160.9	159.2	157.6	156.0	154.3



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	125.6	153.8	159.3	164.9	170.4	175.9	178.0	176.5	175.1	173.7	172.2
115°	179.1	215.0	213.0	211.2	209.2	207.2	205.6	204.3	203.0	201.7	200.4
117.5°	229.5	238.1	236.8	235.5	234.2	232.8	231.4	229.9	228.4	227.0	225.5
120°	256.3	255.4	254.0	252.7	251.3	249.9	248.6	247.4	246.2	245.1	243.9
122.5°	272.5	271.9	270.4	268.8	267.3	265.8	264.4	263.2	262.0	260.7	259.5
125°	295.0	294.5	293.0	291.6	290.1	288.5	287.3	286.3	285.4	284.3	283.3
127.5°	315.6	314.8	313.7	312.6	311.5	310.4	309.3	308.2	307.0	306.0	304.8
130°	328.7	327.9	327.1	326.2	325.4	324.5	323.4	322.2	321.0	319.8	318.5
132.5°	341.8	341.0	340.1	339.3	338.4	337.6	336.6	335.6	334.5	333.5	332.5
135°	360.0	359.3	358.6	357.9	357.2	356.4	355.6	354.2	353.0	351.8	350.6
137.5°	377.1	376.3	375.5	374.8	374.0	373.2	372.3	371.5	370.6	369.7	368.9
140°	388.2	387.5	386.6	385.8	385.0	384.1	383.4	382.7	382.1	381.5	380.9
142.5°	398.4	397.8	396.8	395.8	394.8	394.0	393.1	392.6	392.0	391.5	390.9
145°	412.8	412.2	410.9	409.6	408.3	407.0	406.3	406.4	406.5	406.6	406.7
147.5°	425.3	424.9	423.6	422.3	421.0	419.7	419.2	419.6	419.8	420.1	420.4
150°	432.9	432.4	431.2	430.0	428.8	427.5	427.1	427.7	428.2	428.8	429.3
152.5°	439.9	439.4	438.2	437.1	435.9	434.7	434.4	435.0	435.6	436.3	436.8
155°	449.3	448.8	447.9	446.9	446.1	445.2	445.0	445.7	446.4	447.1	447.8
157.5°	457.1	456.6	456.0	455.3	454.7	454.0	454.0	454.6	455.2	455.8	456.3
160°	461.9	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4
162.5°	466.1	465.5	465.1	464.7	464.3	464.0	464.0	464.5	464.9	465.4	465.9
165°	471.3	470.8	470.6	470.3	470.1	469.9	469.9	470.4	470.9	471.4	471.8
167.5°	475.7	475.2	475.0	474.7	474.5	474.3	474.4	474.9	475.4	475.8	476.3
170°	477.9	477.4	477.3	477.1	477.0	476.8	477.0	477.4	477.8	478.3	478.8
172.5°	479.6	479.1	478.9	478.7	478.6	478.5	478.6	479.1	479.6	480.0	480.5
175°	481.4	480.9	480.7	480.6	480.5	480.3	480.5	481.0	481.5	482.1	482.7
177.5°	481.8	481.3	481.3	481.2	481.1	481.0	481.3	481.7	482.1	482.6	483.0
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	12.7	14.9	15.1	16.7	15.9	16.0	16.1	15.7	15.4	15.0	14.5
90°	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3	7.7
92.5°	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3	8.5
95°	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9	14.3
97.5°	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5	18.8
100°	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5	21.1
102.5°	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2	22.0
105°	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1	23.0
107.5°	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9	28.0
110°	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2	45.5



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6	97.3
115°	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1	143.3
117.5°	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5	220.8
120°	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3	257.3
122.5°	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5	273.0
125°	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0	295.5
127.5°	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6	316.4
130°	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7	329.6
132.5°	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8	342.5
135°	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0	360.9
137.5°	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1	377.9
140°	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2	388.9
142.5°	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4	399.1
145°	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8	413.4
147.5°	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3	425.7
150°	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9	433.4
152.5°	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9	440.3
155°	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3	449.8
157.5°	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1	457.7
160°	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9	462.3
162.5°	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1	466.6
165°	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3	471.9
167.5°	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7	476.3
170°	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9	478.5
172.5°	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6	480.1
175°	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4	482.0
177.5°	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8	482.2
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	15.1	15.2	14.8	14.8	15.3	14.8	14.8
90°	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331585-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)