

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331590-930

Luminaire Tested: **S122DIW-S1005D435U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331590-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D435U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4531.7 lumens
Efficiency: N/A
Efficacy: 86.5 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	113	113	113	113	107	107	107	107	96	96	96	86	86	86	77	77	77	73
1	103	98	94	91	98	94	90	87	84	82	79	76	74	72	68	67	65	61
2	94	86	80	74	89	82	76	71	74	70	66	67	63	60	60	57	55	52
3	86	76	68	62	81	72	65	60	65	60	55	59	55	51	53	50	47	44
4	78	67	59	53	74	64	57	51	58	52	47	53	48	44	48	44	40	37
5	72	60	51	45	68	57	50	44	52	46	41	47	42	38	43	39	35	33
6	67	54	45	39	63	52	44	38	47	41	36	43	38	33	39	35	31	29
7	62	49	41	35	58	47	39	34	43	36	32	39	34	30	36	31	28	25
8	57	45	36	31	54	43	35	30	39	33	28	36	30	27	33	28	25	23
9	53	41	33	28	51	39	32	27	36	30	25	33	28	24	30	26	22	20
10	50	38	30	25	48	36	29	24	33	27	23	31	25	22	28	24	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	2.7
10°-20°	343.8	7.6
20°-30°	505.4	11.2
30°-40°	587.0	13.0
40°-50°	586.4	12.9
50°-60°	511.4	11.3
60°-70°	378.1	8.3
70°-80°	214.2	4.7
80°-90°	59.3	1.3
90°-100°	27.7	0.6
100°-110°	86.1	1.9
110°-120°	147.2	3.2
120°-130°	193.6	4.3
130°-140°	217.3	4.8
140°-150°	213.1	4.7
150°-160°	178.7	3.9
160°-170°	118.6	2.6
170°-180°	41.4	0.9
0°-30°	971.4	21.4
0°-40°	1558.4	34.4
0°-60°	2656.1	58.6
0°-90°	3307.7	73.0
90°-120°	261.1	5.8
90°-150°	885.2	19.5
90°-180°	1224.0	27.0
0°-180°	4531.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	0	5	13	12	13	3
95°	19	23	24	24	23	22
105°	79	80	81	82	82	84
115°	148	150	149	149	148	146
125°	215	218	217	216	216	192
135°	278	282	283	282	281	215
145°	338	340	342	343	341	211
155°	386	387	388	390	389	178
165°	420	420	420	422	420	118
175°	437	436	435	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.1	17.9	17.6	17.3	17.0	16.9	16.8	16.7	16.6	16.6	15.9
90°	0.4	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8
92.5°	6.6	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7
95°	19.2	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6
97.5°	35.1	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7
100°	46.9	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0
102.5°	59.4	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2
105°	79.4	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4
107.5°	99.6	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3
110°	112.7	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.9	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6
115°	147.7	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1
117.5°	168.6	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3
120°	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5
122.5°	195.2	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5
125°	215.0	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0
127.5°	234.2	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8
130°	246.4	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3
132.5°	260.0	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7
135°	278.2	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8
137.5°	297.3	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5
140°	308.8	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0
142.5°	320.7	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3
145°	337.6	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5
147.5°	352.8	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5
150°	363.1	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0
152.5°	372.3	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6
155°	386.0	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7
157.5°	397.8	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7
160°	404.9	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4
162.5°	411.3	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4
165°	420.0	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2
167.5°	427.2	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6
170°	431.0	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2
172.5°	433.7	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8
175°	437.0	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7
177.5°	438.3	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	15.2	14.5	13.8	13.4	13.1	12.9	12.7	12.5
90°	12.6	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.2	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.6	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.4	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331590-930

CATALOG NUMBER: S122DIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	128.4	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	169.1	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.2	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.7	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.5	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.1	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	263.3	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.4	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.3	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.6	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.7	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.1	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.2	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	406.9	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	412.9	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	420.8	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.2	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	430.7	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	433.4	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.3	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)