

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331500-935

Luminaire Tested: **S122DIW-S485D435U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331500-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2995.8 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10797	10797	10797
5°	10838	10682	10746
10°	10775	10575	10627
15°	10641	10437	10425
20°	10452	10232	10220
25°	10265	9978	9978
30°	10023	9747	9661
35°	9798	9469	9329
40°	9514	9190	9012
45°	9236	8912	8690
50°	8932	8626	8317
55°	8617	8290	7983
60°	8263	7892	7598
65°	7885	7492	7148
70°	7407	7010	6680
75°	6744	6457	6301
80°	5979	5793	5504
85°	4872	4650	4168



TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	62.9	2.1
10°-20°	176.9	5.9
20°-30°	260.1	8.7
30°-40°	302.1	10.1
40°-50°	301.8	10.1
50°-60°	263.2	8.8
60°-70°	194.6	6.5
70°-80°	110.2	3.7
80°-90°	31.5	1.1
90°-100°	29.3	1.0
100°-110°	91.0	3.0
110°-120°	155.5	5.2
120°-130°	204.5	6.8
130°-140°	229.5	7.7
140°-150°	225.0	7.5
150°-160°	188.8	6.3
160°-170°	125.2	4.2
170°-180°	43.8	1.5
0°-30°	499.9	16.7
0°-40°	802.0	26.8
0°-60°	1366.9	45.6
0°-90°	1703.2	56.9
90°-120°	275.7	9.2
90°-150°	934.8	31.2
90°-180°	1293.0	43.2
0°-180°	2995.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	669	669	669	669	669	
5°	669	666	659	664	663	63
15°	637	632	624	627	624	179
25°	576	571	560	561	560	265
35°	497	490	480	476	473	310
45°	404	400	390	384	381	312
55°	306	302	294	287	284	274
65°	206	202	196	190	187	204
75°	108	107	104	100	101	115
85°	26	26	25	23	22	30
90°	0	5	14	13	13	2
95°	20	24	25	25	24	23
105°	84	85	86	87	87	89
115°	156	158	158	157	156	154
125°	227	230	229	228	228	203
135°	294	298	299	298	297	227
145°	356	359	362	362	360	223
155°	408	409	410	412	411	188
165°	444	443	443	446	444	125
175°	462	460	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	671.8	671.2	670.7	670.1	669.5	668.7	667.4	666.2	664.9	663.6	664.8
5°	668.7	668.1	667.6	667.0	666.5	665.4	663.8	662.3	660.6	659.1	660.2
7.5°	662.8	661.9	661.1	660.1	659.3	658.1	656.4	654.9	653.2	651.6	652.8
10°	657.2	656.2	655.1	654.2	653.2	651.8	650.1	648.4	646.7	645.0	646.1
12.5°	649.5	648.6	647.6	646.8	645.9	644.6	642.9	641.2	639.5	637.7	638.5
15°	636.6	635.8	634.9	634.0	633.2	631.8	629.9	628.1	626.2	624.4	624.9
17.5°	620.1	619.3	618.5	617.6	616.7	615.4	613.5	611.6	609.7	607.8	608.5
20°	608.3	607.4	606.6	605.7	604.9	603.5	601.4	599.4	597.4	595.5	595.9
22.5°	596.5	595.3	594.1	592.9	591.7	590.1	588.2	586.3	584.4	582.6	582.6
25°	576.2	575.0	573.9	572.7	571.6	569.8	567.4	564.9	562.5	560.1	560.3
27.5°	553.0	552.0	551.0	549.9	548.9	547.4	545.5	543.5	541.7	539.8	539.3
30°	537.6	536.4	535.3	534.2	533.0	531.3	529.2	527.1	525.0	522.8	522.4
32.5°	521.1	520.2	519.3	518.3	517.5	515.8	513.6	511.3	509.1	506.9	506.1
35°	497.1	495.6	494.2	492.8	491.4	489.5	487.2	484.9	482.6	480.4	479.5
37.5°	469.9	468.6	467.4	466.1	464.9	463.1	460.8	458.6	456.2	454.0	452.9
40°	451.4	450.2	449.1	448.0	446.9	445.1	442.8	440.6	438.2	436.0	434.7
42.5°	433.4	432.2	431.1	430.0	428.9	427.1	424.8	422.6	420.3	417.9	416.6
45°	404.5	403.5	402.4	401.5	400.5	398.9	396.7	394.6	392.4	390.3	388.7
47.5°	375.7	374.7	373.8	372.8	371.9	370.3	368.1	365.8	363.6	361.4	359.7
50°	355.6	354.9	354.1	353.4	352.8	351.4	349.4	347.4	345.3	343.4	341.4
52.5°	336.0	335.1	334.2	333.2	332.3	330.9	329.0	327.1	325.2	323.3	321.7
55°	306.1	305.2	304.4	303.5	302.6	301.4	299.6	297.9	296.2	294.5	292.8
57.5°	276.0	275.3	274.6	274.0	273.3	272.0	270.1	268.2	266.3	264.4	262.7
60°	255.9	255.4	254.8	254.2	253.7	252.4	250.4	248.3	246.3	244.4	242.8
62.5°	236.3	235.5	234.5	233.6	232.7	231.5	230.0	228.4	226.9	225.3	223.9
65°	206.4	205.5	204.7	203.8	203.0	201.8	200.4	199.0	197.5	196.1	194.8
67.5°	175.9	175.2	174.5	173.8	173.1	172.2	170.9	169.6	168.3	167.0	166.1
70°	156.9	156.4	155.8	155.2	154.6	153.7	152.4	151.1	149.8	148.5	147.6
72.5°	137.3	136.8	136.2	135.6	135.1	134.4	133.5	132.7	131.9	131.0	130.0
75°	108.1	107.7	107.5	107.2	106.9	106.4	105.6	105.0	104.3	103.5	102.6
77.5°	81.8	81.3	80.8	80.3	79.8	79.5	79.2	78.9	78.6	78.4	77.9
80°	64.3	64.1	64.1	63.9	63.7	63.5	63.2	62.9	62.7	62.3	61.9
82.5°	47.9	47.8	47.8	47.8	47.7	47.6	47.4	47.3	47.1	46.9	46.4
85°	26.3	26.3	26.1	25.9	25.8	25.7	25.5	25.4	25.2	25.1	24.6
87.5°	9.3	9.3	9.3	9.3	9.2	9.3	9.5	9.6	9.8	9.9	9.6
90°	0.4	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5
92.5°	7.0	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4
95°	20.3	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0
97.5°	37.0	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9
100°	49.5	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8
102.5°	62.7	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7
105°	83.9	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0
107.5°	105.2	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0
110°	119.0	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.0	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8
115°	156.0	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5
117.5°	178.1	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7
120°	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7
122.5°	206.1	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5
125°	227.0	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1
127.5°	247.4	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1
130°	260.2	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3
132.5°	274.6	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4
135°	293.8	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7
137.5°	313.9	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4
140°	326.1	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6
142.5°	338.6	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5
145°	356.5	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7
147.5°	372.6	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5
150°	383.5	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6
152.5°	393.1	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7
155°	407.6	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4
157.5°	420.1	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1
160°	427.6	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2
162.5°	434.4	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5
165°	443.5	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8
167.5°	451.2	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6
170°	455.2	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3
172.5°	458.1	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1
175°	461.5	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1
177.5°	462.9	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	668.7	668.7	668.7	668.7	668.7	668.7	668.7	668.7
2.5°	665.9	667.0	668.1	668.7	668.4	668.1	668.0	667.7
5°	661.4	662.5	663.7	664.1	663.8	663.5	663.2	663.0
7.5°	653.9	655.0	656.3	656.6	656.3	656.0	655.7	655.4
10°	647.2	648.4	649.5	649.9	649.5	649.0	648.6	648.2
12.5°	639.4	640.2	640.9	641.2	640.8	640.6	640.2	639.9
15°	625.5	626.1	626.6	626.5	625.9	625.2	624.5	623.7
17.5°	609.1	609.8	610.4	610.4	609.7	609.1	608.4	607.7
20°	596.3	596.8	597.2	597.1	596.5	595.9	595.4	594.8
22.5°	582.7	582.8	582.9	582.8	582.5	582.1	581.8	581.4
25°	560.7	560.9	561.2	561.2	560.9	560.7	560.3	560.1
27.5°	538.9	538.5	538.0	537.5	536.8	536.1	535.5	534.8
30°	521.9	521.5	521.1	520.6	520.0	519.4	518.8	518.2
32.5°	505.3	504.5	503.8	503.1	502.5	502.0	501.4	500.8
35°	478.6	477.8	476.9	476.1	475.4	474.7	474.0	473.3
37.5°	451.9	450.8	449.8	448.8	448.2	447.5	446.8	446.2
40°	433.4	432.1	430.8	429.9	429.3	428.8	428.2	427.6
42.5°	415.2	413.8	412.3	411.3	410.4	409.7	408.9	408.0
45°	387.2	385.6	384.0	383.0	382.4	381.9	381.3	380.6
47.5°	358.1	356.4	354.7	353.5	352.7	351.9	351.0	350.2
50°	339.4	337.3	335.4	334.0	333.3	332.6	331.8	331.1
52.5°	320.0	318.3	316.7	315.4	314.4	313.5	312.5	311.6
55°	291.1	289.4	287.7	286.5	285.7	285.0	284.3	283.6
57.5°	261.1	259.3	257.7	256.6	256.0	255.5	254.9	254.3
60°	241.2	239.6	238.1	237.0	236.6	236.2	235.7	235.3
62.5°	222.4	220.9	219.5	218.5	217.9	217.4	216.9	216.3
65°	193.6	192.3	191.0	189.9	189.2	188.6	187.9	187.1
67.5°	165.1	164.0	163.1	162.3	161.7	161.1	160.6	160.0
70°	146.5	145.5	144.6	143.8	143.2	142.6	142.1	141.5
72.5°	129.1	128.0	127.1	126.3	125.9	125.4	124.9	124.5
75°	101.8	101.0	100.1	99.8	100.1	100.4	100.7	101.0
77.5°	77.5	77.1	76.6	76.2	75.8	75.4	75.0	74.6
80°	61.5	61.0	60.7	60.3	60.0	59.8	59.4	59.2
82.5°	45.9	45.3	44.8	44.4	44.4	44.3	44.3	44.3
85°	24.2	23.8	23.3	23.1	22.9	22.8	22.6	22.5
87.5°	9.2	8.8	8.4	8.2	8.1	8.0	7.9	7.8
90°	13.3	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.7	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.2	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.1	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.3	121.1	120.9	120.6	120.4	120.1



TEST NUMBER: P331500-935

CATALOG NUMBER: S122DIW-S485D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.6	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.4	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.6	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.2	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.9	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.8	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.2	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	278.1	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.6	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.3	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.5	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.8	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	377.7	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	410.9	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	422.7	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	429.7	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.1	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	444.4	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.2	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	454.9	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	457.7	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	460.7	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)