

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331591-930

Luminaire Tested: **S122DIW-S1005D710U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331591-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S1005D710U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5900.2 lumens  
Efficiency: N/A  
Efficacy: 98.7 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	101	97	93	90	94	91	87	84	79	77	75	69	67	66	59	58	57	52
2	92	85	79	74	86	80	75	70	70	66	63	61	58	56	53	51	49	45
3	85	75	68	62	79	71	65	59	62	58	54	55	51	48	47	45	42	39
4	78	67	59	53	73	63	56	51	56	50	46	49	45	41	43	40	37	34
5	72	60	52	46	67	57	50	44	50	45	40	44	40	36	39	35	33	30
6	66	54	46	41	62	51	44	39	46	40	36	40	36	32	35	32	29	26
7	61	49	41	36	57	47	40	34	42	36	32	37	32	29	33	29	26	24
8	57	45	37	32	54	43	36	31	38	32	28	34	29	26	30	26	24	21
9	53	41	34	29	50	39	32	28	35	30	26	31	27	23	28	24	21	19
10	50	38	31	26	47	36	30	25	33	27	23	29	25	21	26	22	20	18

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	26248	26248	26248	26248
5°	29428	26420	23412	26420
10°	33721	26202	20261	26202
15°	37305	25723	17901	25723
20°	36737	25206	16318	25206
25°	33127	24522	15316	24522
30°	27374	23426	14585	23426
35°	19951	22277	14063	22277
40°	15934	20925	13774	20925
45°	13924	19358	13381	19358
50°	13089	17844	13122	17844
55°	12065	16304	12769	16304
60°	11057	14667	12226	14667
65°	10074	13200	11694	13200
70°	9144	11769	10914	11769
75°	8110	10175	9669	10175
80°	6974	8424	7782	8424
85°	6262	6262	4631	6262



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	154.8	2.6
10°-20°	450.1	7.6
20°-30°	653.3	11.1
30°-40°	689.3	11.7
40°-50°	610.4	10.3
50°-60°	487.1	8.3
60°-70°	331.1	5.6
70°-80°	169.7	2.9
80°-90°	42.9	0.7
90°-100°	26.3	0.4
100°-110°	96.5	1.6
110°-120°	257.9	4.4
120°-130°	425.7	7.2
130°-140°	452.8	7.7
140°-150°	420.8	7.1
150°-160°	338.4	5.7
160°-170°	218.0	3.7
170°-180°	75.1	1.3
0°-30°	1258.2	21.3
0°-40°	1947.5	33.0
0°-60°	3045.0	51.6
0°-90°	3588.7	60.8
90°-120°	380.7	6.5
90°-150°	1680.1	28.5
90°-180°	2312.0	39.2
0°-180°	5900.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1626	1626	1626	1626	1626	
5°	1816	1630	1444	1630	1816	181
15°	2232	1539	1071	1539	2232	616
25°	1860	1376	860	1376	1860	840
35°	1012	1130	714	1130	1012	658
45°	610	848	586	848	610	480
55°	429	579	454	579	429	384
65°	264	346	306	346	264	262
75°	130	163	155	163	130	139
85°	34	34	25	34	34	37
90°	15	1	15	1	15	9
95°	24	37	24	37	24	23
105°	43	174	43	174	43	45
115°	47	328	47	328	47	117
125°	488	464	488	464	488	422
135°	593	574	593	574	593	457
145°	676	666	676	666	676	423
155°	734	733	734	733	734	339
165°	771	773	771	773	771	218
175°	786	790	786	790	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1700.7	1701.2	1702.2	1694.2	1693.2	1693.2	1686.2	1680.3	1673.2	1663.7	1664.8
5°	1815.7	1822.5	1825.0	1817.5	1806.3	1805.1	1794.5	1776.9	1760.7	1747.6	1738.2
7.5°	1952.9	1955.7	1949.5	1939.7	1931.3	1916.3	1896.5	1877.1	1850.1	1825.2	1806.7
10°	2056.8	2060.6	2050.0	2035.6	2023.7	2006.3	1977.5	1948.2	1912.5	1878.2	1850.6
12.5°	2135.8	2145.1	2131.4	2129.6	2109.3	2085.2	2051.0	2036.1	1986.0	1938.1	1908.7
15°	2231.8	2231.1	2232.5	2220.5	2205.5	2201.8	2165.6	2126.2	2055.6	2027.5	1978.7
17.5°	2204.1	2213.5	2217.9	2217.8	2217.5	2215.1	2203.4	2178.6	2143.2	2097.6	2041.3
20°	2138.1	2150.6	2152.5	2166.8	2175.0	2185.6	2190.0	2183.0	2161.2	2123.1	2074.4
22.5°	2036.1	2039.6	2045.5	2067.8	2085.5	2112.1	2126.0	2149.0	2140.7	2122.1	2081.4
25°	1859.5	1853.2	1875.0	1886.3	1926.9	1969.4	2000.0	2033.8	2063.8	2081.9	2070.0
27.5°	1647.2	1637.9	1670.6	1700.5	1733.5	1779.5	1827.2	1883.5	1930.4	1989.0	2009.1
30°	1468.3	1473.9	1505.1	1537.0	1587.0	1652.0	1705.7	1767.6	1834.4	1900.1	1945.6
32.5°	1275.4	1297.0	1316.7	1365.5	1409.6	1482.1	1560.7	1638.1	1721.5	1796.1	1866.7
35°	1012.2	1037.1	1064.7	1100.2	1162.1	1234.0	1310.8	1415.2	1528.9	1630.8	1714.5
37.5°	852.0	848.0	863.7	889.5	939.6	997.6	1086.1	1189.1	1323.0	1442.7	1560.7
40°	756.0	753.5	764.8	788.5	826.6	869.1	946.6	1037.1	1161.5	1307.7	1448.3
42.5°	690.1	691.5	697.8	714.5	740.6	775.6	833.6	910.7	1024.6	1162.3	1313.4
45°	609.8	614.2	621.1	629.2	644.2	672.9	705.4	760.4	850.4	965.3	1114.0
47.5°	552.0	552.2	559.2	566.3	575.2	591.4	617.9	652.4	715.9	809.5	937.3
50°	521.1	516.7	521.7	527.3	536.7	548.0	565.4	597.9	640.4	716.0	822.9
52.5°	483.1	483.2	487.7	489.8	498.2	509.5	525.5	548.0	586.4	645.6	733.4
55°	428.6	431.7	434.2	438.0	445.5	453.6	466.1	481.1	511.1	555.5	620.4
57.5°	377.4	378.4	380.9	388.0	392.7	400.2	412.1	425.7	445.2	478.1	526.9
60°	342.4	342.4	347.4	350.5	356.8	364.3	373.7	386.8	404.2	431.1	470.5
62.5°	310.4	309.9	311.9	317.0	321.8	328.8	338.1	349.3	365.7	389.6	422.0
65°	263.7	262.4	266.2	267.4	272.4	279.3	286.8	298.6	311.8	329.3	358.0
67.5°	218.7	220.2	222.2	224.5	227.3	234.6	239.5	247.9	259.0	273.5	293.0
70°	193.7	193.7	193.7	195.6	199.3	203.1	208.1	214.9	225.6	238.1	255.5
72.5°	165.7	167.7	169.7	168.6	173.3	175.5	181.6	185.5	195.6	203.6	219.1
75°	130.0	130.0	130.0	133.1	134.9	136.8	140.6	144.3	149.4	159.3	167.5
77.5°	96.9	96.7	97.3	98.1	100.1	102.3	103.5	106.8	111.5	116.1	122.9
80°	75.0	76.2	76.9	78.1	78.1	79.3	80.0	84.4	87.5	90.6	95.0
82.5°	58.0	58.2	58.4	58.6	59.1	59.8	61.5	62.9	64.0	66.6	70.0
85°	33.8	33.1	33.1	34.3	33.8	33.8	35.0	36.2	36.2	36.9	38.7
87.5°	16.1	16.1	16.5	15.9	15.9	16.3	16.1	15.6	15.9	16.3	16.6
90°	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7	12.1	11.4	10.4
92.5°	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9	13.5	13.2	12.7
95°	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6	22.9	22.3	21.4
97.5°	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8	30.3	29.8	27.7
100°	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6	33.5	32.5	30.4
102.5°	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1	34.7	33.4	31.4
105°	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6	36.2	34.8	32.5
107.5°	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9	47.3	48.8	49.3
110°	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5	87.2	99.9	136.6



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4	205.7	251.9	261.0
115°	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7	293.4	352.1	348.9
117.5°	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7	375.9	390.0	387.8
120°	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4	419.9	418.3	416.0
122.5°	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1	446.2	445.3	442.8
125°	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0	483.1	482.2	479.9
127.5°	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2	516.9	515.6	513.8
130°	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9	538.5	537.1	535.7
132.5°	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9	559.7	558.6	557.2
135°	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0	589.7	588.5	587.3
137.5°	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9	617.7	616.4	615.1
140°	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0	635.9	634.7	633.2
142.5°	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6	652.6	651.6	650.0
145°	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9	676.1	675.2	673.0
147.5°	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3	696.7	695.9	693.8
150°	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8	709.1	708.3	706.3
152.5°	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2	720.5	719.7	717.8
155°	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6	735.9	735.2	733.6
157.5°	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7	748.8	747.9	746.8
160°	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2	756.4	755.7	754.9
162.5°	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3	763.4	762.5	761.9
165°	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1	770.7
167.5°	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1	779.2	778.3	778.0
170°	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7	782.9	782.0	781.7
172.5°	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4	785.5	784.6	784.4
175°	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5	788.6	787.7	787.4
177.5°	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8	789.0	788.3	788.2
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1668.3	1664.3	1661.7	1652.8	1644.7	1636.7	1634.3	1635.2	1624.2	1613.7	1609.2
5°	1733.2	1720.7	1708.9	1692.0	1672.0	1650.1	1638.8	1630.1	1608.3	1584.5	1570.8
7.5°	1791.5	1773.6	1750.7	1719.0	1689.9	1655.5	1633.6	1614.2	1582.3	1548.7	1528.3
10°	1826.9	1802.5	1773.2	1734.5	1698.8	1657.0	1627.6	1598.2	1560.7	1520.8	1495.7
12.5°	1857.4	1824.6	1795.7	1746.0	1703.8	1651.5	1616.7	1575.2	1535.8	1488.2	1463.8
15°	1930.1	1869.4	1814.4	1758.2	1706.3	1633.2	1594.5	1538.9	1487.0	1428.3	1400.2
17.5°	1986.2	1918.0	1831.4	1760.0	1699.5	1618.5	1561.6	1495.0	1433.7	1366.6	1328.4
20°	2018.1	1940.0	1846.9	1761.9	1689.5	1597.0	1535.1	1467.0	1395.2	1319.6	1278.4
22.5°	2037.1	1955.0	1863.0	1754.4	1669.5	1579.5	1501.6	1427.0	1354.2	1272.6	1229.4
25°	2043.1	1968.1	1870.7	1748.2	1644.5	1542.6	1448.9	1376.5	1288.3	1212.1	1149.0
27.5°	2013.4	1959.7	1865.9	1736.4	1615.6	1496.6	1392.0	1309.9	1217.0	1134.2	1070.8
30°	1976.9	1945.6	1854.4	1724.4	1592.6	1464.5	1349.6	1256.5	1164.0	1080.3	1015.3
32.5°	1920.4	1913.7	1833.4	1707.5	1568.1	1424.1	1305.1	1211.0	1108.6	1026.3	964.3
35°	1809.5	1839.4	1788.8	1669.5	1522.0	1366.4	1237.7	1130.2	1024.1	945.3	887.2
37.5°	1660.8	1735.2	1722.0	1613.9	1459.8	1303.7	1161.6	1049.3	948.1	868.6	811.6
40°	1558.3	1653.3	1667.0	1571.4	1415.8	1255.2	1104.6	992.8	894.1	821.7	764.1
42.5°	1448.3	1559.3	1597.0	1520.4	1367.8	1204.3	1053.7	937.8	840.1	769.6	718.7
45°	1264.0	1410.8	1479.0	1435.2	1287.8	1120.3	965.3	847.8	759.1	692.9	653.5
47.5°	1091.7	1252.1	1343.7	1328.2	1198.7	1032.8	879.6	766.9	680.5	627.7	592.5
50°	969.7	1134.7	1245.2	1250.3	1134.7	970.3	816.6	710.4	631.0	581.7	552.9
52.5°	863.7	1021.2	1141.7	1168.2	1063.2	905.3	760.1	654.4	584.6	539.2	513.5
55°	725.4	858.5	992.2	1040.9	956.6	806.7	672.3	579.2	513.6	482.3	459.8
57.5°	603.1	714.0	837.5	891.4	839.4	711.0	585.1	504.2	451.0	423.6	406.3
60°	538.6	626.1	736.1	800.4	755.4	641.1	531.1	454.2	410.5	386.1	369.9
62.5°	478.6	556.1	649.1	707.9	683.4	575.6	477.1	409.3	371.5	348.6	336.9
65°	394.8	456.1	528.0	582.3	566.1	484.2	403.7	345.5	315.5	297.4	288.0
67.5°	325.1	369.4	419.2	466.8	453.7	395.7	331.0	285.8	263.4	247.8	242.1
70°	281.2	314.9	359.3	397.4	386.8	339.2	288.0	249.3	229.9	216.8	211.2
72.5°	239.2	266.9	300.8	331.9	324.7	285.3	242.6	213.3	198.4	186.3	181.7
75°	180.6	201.8	222.4	243.0	241.2	210.6	185.6	163.1	151.2	141.9	140.0
77.5°	133.3	145.2	159.2	171.5	168.0	150.6	130.9	118.1	109.3	103.1	102.1
80°	101.8	108.7	118.7	127.4	123.1	115.6	100.0	90.6	84.4	78.1	75.6
82.5°	73.9	80.7	86.7	91.5	88.1	81.1	71.5	65.1	61.4	57.1	56.1
85°	38.7	42.5	45.0	46.2	45.0	40.6	36.2	33.8	30.7	28.8	28.1
87.5°	16.9	16.6	16.5	17.2	15.4	15.2	12.9	11.1	10.9	10.7	9.9
90°	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6	2.0	3.3	4.7
92.5°	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5	11.4	11.3	11.2
95°	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1	32.9	28.7	24.5
97.5°	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6	61.8	50.1	38.2
100°	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0	83.6	66.3	48.9
102.5°	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2	127.5	123.8	120.1
105°	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5	177.3	181.2	184.9
107.5°	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8	224.9	228.0	231.0
110°	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8	255.5	258.2	260.8





TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1	284.5	286.8	289.1
115°	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2	330.4	332.5	334.7
117.5°	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4	371.8	374.2	376.6
120°	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5	401.5	403.3	405.2
122.5°	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1	427.1	429.1	431.1
125°	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0	465.7	467.3	469.0
127.5°	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3	501.1	503.0	504.8
130°	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6	523.7	525.7	527.7
132.5°	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5	546.3	548.0	549.7
135°	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2	576.2	578.2	580.2
137.5°	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2	605.6	607.1	608.5
140°	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9	624.8	625.8	626.9
142.5°	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3	641.2	642.1	643.0
145°	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1	665.9	665.9	665.7
147.5°	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5	688.1	687.6	687.1
150°	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2	702.3	701.4	700.5
152.5°	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5	714.5	713.5	712.5
155°	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4	732.3	731.2	730.0
157.5°	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5	746.5	745.5	744.5
160°	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	754.9	754.2	753.4
162.5°	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0	762.2	761.5	760.7
165°	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8	772.0	771.3	770.5
167.5°	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1	779.3	778.6	777.8
170°	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2	783.4	782.7	782.0
172.5°	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9	786.2	785.5	784.6
175°	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5	789.6	788.7	787.8
177.5°	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1	790.4	789.6	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1604.3	1601.2	1590.7	1585.3	1576.3	1567.7	1562.3	1564.8	1566.8	1565.8	1564.2
5°	1558.3	1546.4	1528.3	1512.6	1501.4	1480.8	1472.0	1467.7	1464.0	1459.5	1455.1
7.5°	1503.5	1484.8	1458.8	1436.6	1415.5	1389.9	1375.3	1366.6	1357.6	1347.7	1339.0
10°	1464.5	1438.3	1410.8	1379.6	1354.6	1331.5	1310.8	1297.1	1284.6	1272.8	1264.0
12.5°	1423.6	1393.3	1359.3	1316.6	1289.1	1256.0	1252.9	1228.7	1209.1	1201.8	1191.5
15°	1358.3	1315.8	1272.8	1222.1	1200.3	1170.3	1151.5	1132.8	1115.9	1104.0	1100.9
17.5°	1284.3	1229.2	1186.3	1150.0	1114.2	1083.5	1066.2	1051.2	1037.3	1021.4	1019.3
20°	1227.8	1180.2	1133.4	1101.6	1064.7	1033.4	1012.2	997.2	985.3	975.9	967.8
22.5°	1174.3	1122.3	1079.4	1044.6	1008.2	982.9	966.2	951.7	941.8	931.5	923.8
25°	1088.4	1047.8	1000.9	961.6	931.6	915.3	901.6	889.1	882.9	876.0	867.2
27.5°	1013.3	968.2	924.3	893.8	867.5	853.1	843.3	834.9	829.0	825.0	820.0
30°	960.3	914.7	880.4	850.4	828.5	814.2	807.9	802.9	796.0	793.5	791.0
32.5°	909.3	868.2	838.9	812.9	792.0	782.6	776.9	772.4	767.0	764.5	759.5
35°	837.2	802.9	774.1	759.8	742.9	734.7	730.4	724.1	719.2	716.6	716.0
37.5°	769.4	739.6	720.6	702.1	695.0	690.1	684.0	679.8	678.3	677.9	677.3
40°	725.4	701.0	684.2	669.2	666.0	658.5	653.5	649.8	649.8	650.4	649.8
42.5°	685.4	663.6	648.7	635.7	632.0	627.5	622.6	622.3	623.3	625.4	623.3
45°	624.8	609.2	598.6	592.3	585.5	581.1	580.4	582.3	582.9	583.6	585.5
47.5°	569.1	558.7	549.1	542.2	539.2	538.4	537.7	541.0	544.0	545.1	548.0
50°	536.1	524.2	516.1	511.7	509.2	507.9	509.2	513.0	515.4	518.6	520.5
52.5°	499.1	490.7	485.1	481.8	480.7	481.5	481.8	486.0	490.0	491.1	492.0
55°	448.0	441.7	440.5	434.9	437.3	436.8	439.9	442.4	446.1	449.9	450.5
57.5°	397.0	392.0	388.7	389.1	389.9	392.6	395.3	399.7	403.7	407.6	408.0
60°	363.1	360.5	358.7	358.7	359.9	363.6	366.7	371.1	373.7	376.1	378.0
62.5°	332.0	329.5	327.7	328.6	331.9	334.1	337.8	340.1	342.7	345.1	346.0
65°	283.1	281.8	283.6	284.9	285.5	288.7	293.0	294.9	297.4	298.6	303.0
67.5°	237.9	238.1	237.9	239.7	243.3	244.0	248.2	252.6	253.1	255.4	258.3
70°	207.4	208.7	209.9	211.2	214.3	215.6	218.7	220.5	223.1	224.9	226.8
72.5°	179.4	179.7	180.9	180.7	183.3	186.1	188.7	190.5	193.1	195.4	197.3
75°	138.1	138.1	139.3	140.0	143.1	146.2	145.6	146.8	149.4	151.8	153.1
77.5°	100.9	99.5	100.9	101.5	102.5	105.1	105.6	107.4	110.2	109.3	110.7
80°	76.9	75.0	76.9	77.5	77.5	80.6	80.6	81.9	83.7	81.9	83.7
82.5°	54.9	54.0	55.4	55.5	56.5	56.6	57.6	57.9	59.8	58.9	59.8
85°	27.5	26.9	27.5	26.9	27.5	28.1	28.1	27.5	27.5	28.8	26.9
87.5°	9.7	9.5	9.1	9.4	9.0	8.8	8.4	8.6	8.6	7.8	7.9
90°	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7	13.3	13.9	14.4
92.5°	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9	14.3	14.6	14.8
95°	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6	24.1	24.8	25.0
97.5°	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8	31.3	31.8	32.1
100°	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6	35.5	36.6	37.3
102.5°	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1	37.4	38.7	39.5
105°	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6	39.0	40.4	41.3
107.5°	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9	44.5	43.0	42.6
110°	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5	61.8	49.2	43.0



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4	113.2	66.9	43.9
115°	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7	175.9	117.2	83.3
117.5°	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7	347.4	333.2	311.1
120°	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4	422.9	424.4	416.6
122.5°	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1	448.0	449.0	447.8
125°	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0	484.9	485.8	486.5
127.5°	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2	519.5	520.8	521.5
130°	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9	541.3	542.7	543.3
132.5°	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9	562.1	563.3	563.9
135°	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0	592.2	593.5	594.0
137.5°	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9	620.1	621.4	621.8
140°	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0	638.1	639.3	639.5
142.5°	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6	654.7	655.7	655.9
145°	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9	677.8	678.7	678.9
147.5°	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3	698.0	698.6	698.7
150°	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8	710.6	711.3	711.4
152.5°	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2	722.0	722.8	722.8
155°	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6	737.4	738.2	738.0
157.5°	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7	750.5	751.4	751.3
160°	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2	758.0	758.7	758.6
162.5°	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3	765.1	766.0	765.9
165°	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9	773.7	774.6	774.6
167.5°	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1	781.0	781.8	781.7
170°	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7	784.6	785.5	785.4
172.5°	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4	787.3	788.2	788.1
175°	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5	790.3	791.2	791.0
177.5°	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8	790.4	791.2	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1559.3	1558.3	1558.3	1553.8	1558.3	1558.3	1559.3	1564.2	1565.8	1566.8	1564.8
5°	1446.4	1444.5	1441.4	1444.5	1441.4	1444.5	1446.4	1455.1	1459.5	1464.0	1467.7
7.5°	1334.8	1327.3	1326.2	1318.8	1326.2	1327.3	1334.8	1339.0	1347.7	1357.6	1366.6
10°	1253.4	1248.4	1247.7	1235.8	1247.7	1248.4	1253.4	1264.0	1272.8	1284.6	1297.1
12.5°	1191.4	1179.4	1181.8	1174.8	1181.8	1179.4	1191.4	1191.5	1201.8	1209.1	1228.7
15°	1084.0	1084.0	1081.6	1070.9	1081.6	1084.0	1084.0	1100.9	1104.0	1115.9	1132.8
17.5°	1007.0	1005.7	999.7	1002.7	999.7	1005.7	1007.0	1019.3	1021.4	1037.3	1051.2
20°	960.9	957.2	949.7	949.7	949.7	957.2	960.9	967.8	975.9	985.3	997.2
22.5°	917.5	917.2	909.2	911.7	909.2	917.2	917.5	923.8	931.5	941.8	951.7
25°	866.6	861.6	857.9	859.7	857.9	861.6	866.6	867.2	876.0	882.9	889.1
27.5°	818.4	815.6	815.4	810.2	815.4	815.6	818.4	820.0	825.0	829.0	834.9
30°	790.4	784.2	785.4	782.3	785.4	784.2	790.4	791.0	793.5	796.0	802.9
32.5°	758.4	756.1	754.9	752.3	754.9	756.1	758.4	759.5	764.5	767.0	772.4
35°	714.8	715.4	712.2	713.5	712.2	715.4	714.8	716.0	716.6	719.2	724.1
37.5°	676.7	678.7	677.2	677.5	677.2	678.7	676.7	677.3	677.9	678.3	679.8
40°	651.7	651.7	651.7	653.5	651.7	651.7	651.7	649.8	650.4	649.8	649.8
42.5°	627.7	626.7	625.7	625.6	625.7	626.7	627.7	623.3	625.4	623.3	622.3
45°	586.7	588.6	589.2	586.0	589.2	588.6	586.7	585.5	583.6	582.9	582.3
47.5°	549.6	549.8	549.6	552.4	549.6	549.8	549.6	548.0	545.1	544.0	541.0
50°	523.6	522.4	523.6	522.4	523.6	522.4	523.6	520.5	518.6	515.4	513.0
52.5°	496.1	496.4	495.6	495.4	495.6	496.4	496.1	492.0	491.1	490.0	486.0
55°	453.0	454.2	453.6	453.6	453.6	454.2	453.0	450.5	449.9	446.1	442.4
57.5°	408.4	409.5	410.3	407.6	410.3	409.5	408.4	408.0	407.6	403.7	399.7
60°	377.4	380.5	379.8	378.6	379.8	380.5	377.4	378.0	376.1	373.7	371.1
62.5°	348.9	350.0	349.9	349.7	349.9	350.0	348.9	346.0	345.1	342.7	340.1
65°	304.9	306.1	304.3	306.1	304.3	306.1	304.9	303.0	298.6	297.4	294.9
67.5°	257.6	258.0	259.3	260.2	259.3	258.0	257.6	258.3	255.4	253.1	252.6
70°	228.0	227.5	229.3	231.2	229.3	227.5	228.0	226.8	224.9	223.1	220.5
72.5°	197.1	198.4	197.8	199.2	197.8	198.4	197.1	197.3	195.4	193.1	190.5
75°	151.8	153.7	153.1	155.0	153.1	153.7	151.8	153.1	151.8	149.4	146.8
77.5°	109.7	110.0	109.7	110.7	109.7	110.0	109.7	110.7	109.3	110.2	107.4
80°	83.7	82.5	81.2	83.7	81.2	82.5	83.7	83.7	81.9	83.7	81.9
82.5°	58.2	58.9	57.7	57.7	57.7	58.9	58.2	59.8	58.9	59.8	57.9
85°	26.9	26.3	25.0	25.0	25.0	26.3	26.9	26.9	28.8	27.5	27.5
87.5°	7.9	7.5	7.5	7.1	7.5	7.5	7.9	7.9	7.8	8.6	8.6
90°	14.7	14.9	15.2	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7
92.5°	14.9	15.1	15.2	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9
95°	24.9	24.8	24.7	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6
97.5°	32.3	32.4	32.6	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8
100°	37.5	37.7	38.0	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6
102.5°	39.9	40.3	40.6	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1
105°	41.8	42.4	42.9	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6
107.5°	43.1	43.6	44.1	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9
110°	43.5	44.1	44.6	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.4	44.8	45.2	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4
115°	74.2	65.1	55.9	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7
117.5°	281.1	251.1	221.1	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7
120°	399.5	382.4	365.3	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4
122.5°	444.4	441.1	437.8	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1
125°	486.8	487.2	487.6	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0
127.5°	521.5	521.6	521.7	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2
130°	543.2	543.1	542.9	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9
132.5°	563.7	563.6	563.5	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9
135°	593.8	593.5	593.3	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0
137.5°	621.3	620.9	620.5	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9
140°	638.9	638.2	637.6	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0
142.5°	655.3	654.7	654.0	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6
145°	678.2	677.6	676.9	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9
147.5°	698.1	697.7	697.1	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3
150°	710.8	710.1	709.5	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8
152.5°	721.9	721.1	720.2	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2
155°	737.0	736.1	735.0	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6
157.5°	750.3	749.3	748.4	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7
160°	757.7	756.8	756.0	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2
162.5°	764.8	763.7	762.5	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3
165°	773.7	772.9	772.0	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9
167.5°	780.6	779.4	778.3	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1
170°	784.2	783.1	782.0	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7
172.5°	786.9	785.8	784.6	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4
175°	789.7	788.5	787.2	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5
177.5°	790.2	789.2	788.3	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1562.3	1567.7	1576.3	1585.3	1590.7	1601.2	1604.3	1609.2	1613.7	1624.2	1635.2
5°	1472.0	1480.8	1501.4	1512.6	1528.3	1546.4	1558.3	1570.8	1584.5	1608.3	1630.1
7.5°	1375.3	1389.9	1415.5	1436.6	1458.8	1484.8	1503.5	1528.3	1548.7	1582.3	1614.2
10°	1310.8	1331.5	1354.6	1379.6	1410.8	1438.3	1464.5	1495.7	1520.8	1560.7	1598.2
12.5°	1252.9	1256.0	1289.1	1316.6	1359.3	1393.3	1423.6	1463.8	1488.2	1535.8	1575.2
15°	1151.5	1170.3	1200.3	1222.1	1272.8	1315.8	1358.3	1400.2	1428.3	1487.0	1538.9
17.5°	1066.2	1083.5	1114.2	1150.0	1186.3	1229.2	1284.3	1328.4	1366.6	1433.7	1495.0
20°	1012.2	1033.4	1064.7	1101.6	1133.4	1180.2	1227.8	1278.4	1319.6	1395.2	1467.0
22.5°	966.2	982.9	1008.2	1044.6	1079.4	1122.3	1174.3	1229.4	1272.6	1354.2	1427.0
25°	901.6	915.3	931.6	961.6	1000.9	1047.8	1088.4	1149.0	1212.1	1288.3	1376.5
27.5°	843.3	853.1	867.5	893.8	924.3	968.2	1013.3	1070.8	1134.2	1217.0	1309.9
30°	807.9	814.2	828.5	850.4	880.4	914.7	960.3	1015.3	1080.3	1164.0	1256.5
32.5°	776.9	782.6	792.0	812.9	838.9	868.2	909.3	964.3	1026.3	1108.6	1211.0
35°	730.4	734.7	742.9	759.8	774.1	802.9	837.2	887.2	945.3	1024.1	1130.2
37.5°	684.0	690.1	695.0	702.1	720.6	739.6	769.4	811.6	868.6	948.1	1049.3
40°	653.5	658.5	666.0	669.2	684.2	701.0	725.4	764.1	821.7	894.1	992.8
42.5°	622.6	627.5	632.0	635.7	648.7	663.6	685.4	718.7	769.6	840.1	937.8
45°	580.4	581.1	585.5	592.3	598.6	609.2	624.8	653.5	692.9	759.1	847.8
47.5°	537.7	538.4	539.2	542.2	549.1	558.7	569.1	592.5	627.7	680.5	766.9
50°	509.2	507.9	509.2	511.7	516.1	524.2	536.1	552.9	581.7	631.0	710.4
52.5°	481.8	481.5	480.7	481.8	485.1	490.7	499.1	513.5	539.2	584.6	654.4
55°	439.9	436.8	437.3	434.9	440.5	441.7	448.0	459.8	482.3	513.6	579.2
57.5°	395.3	392.6	389.9	389.1	388.7	392.0	397.0	406.3	423.6	451.0	504.2
60°	366.7	363.6	359.9	358.7	358.7	360.5	363.1	369.9	386.1	410.5	454.2
62.5°	337.8	334.1	331.9	328.6	327.7	329.5	332.0	336.9	348.6	371.5	409.3
65°	293.0	288.7	285.5	284.9	283.6	281.8	283.1	288.0	297.4	315.5	345.5
67.5°	248.2	244.0	243.3	239.7	237.9	238.1	237.9	242.1	247.8	263.4	285.8
70°	218.7	215.6	214.3	211.2	209.9	208.7	207.4	211.2	216.8	229.9	249.3
72.5°	188.7	186.1	183.3	180.7	180.9	179.7	179.4	181.7	186.3	198.4	213.3
75°	145.6	146.2	143.1	140.0	139.3	138.1	138.1	140.0	141.9	151.2	163.1
77.5°	105.6	105.1	102.5	101.5	100.9	99.5	100.9	102.1	103.1	109.3	118.1
80°	80.6	80.6	77.5	77.5	76.9	75.0	76.9	75.6	78.1	84.4	90.6
82.5°	57.6	56.6	56.5	55.5	55.4	54.0	54.9	56.1	57.1	61.4	65.1
85°	28.1	28.1	27.5	26.9	27.5	26.9	27.5	28.1	28.8	30.7	33.8
87.5°	8.4	8.8	9.0	9.4	9.1	9.5	9.7	9.9	10.7	10.9	11.1
90°	12.1	11.4	10.4	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5
95°	22.9	22.3	21.4	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1
97.5°	30.3	29.8	27.7	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6
100°	33.5	32.5	30.4	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0
102.5°	34.7	33.4	51.4	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2
105°	36.2	34.8	69.5	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5
107.5°	47.3	48.8	90.3	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8
110°	87.2	99.9	136.6	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.7	251.9	261.0	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1
115°	293.4	352.1	348.9	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2
117.5°	375.9	390.0	387.8	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4
120°	419.9	418.3	416.0	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5
122.5°	446.2	445.3	442.8	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1
125°	483.1	482.2	479.9	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0
127.5°	516.9	515.6	513.8	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3
130°	538.5	537.1	535.7	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6
132.5°	559.7	558.6	557.2	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5
135°	589.7	588.5	587.3	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2
137.5°	617.7	616.4	615.1	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2
140°	635.9	634.7	633.2	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9
142.5°	652.6	651.6	650.0	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3
145°	676.1	675.2	673.0	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1
147.5°	696.7	695.9	693.8	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5
150°	709.1	708.3	706.3	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2
152.5°	720.5	719.7	717.8	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5
155°	735.9	735.2	733.6	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4
157.5°	748.8	747.9	746.8	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5
160°	756.4	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7
162.5°	763.4	762.5	761.9	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0
165°	772.0	771.1	770.7	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8
167.5°	779.2	778.3	778.0	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1
170°	782.9	782.0	781.7	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2
172.5°	785.5	784.6	784.4	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9
175°	788.6	787.7	787.4	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5
177.5°	789.0	788.3	788.2	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1634.3	1636.7	1644.7	1652.8	1661.7	1664.3	1668.3	1664.8	1663.7	1673.2	1680.3
5°	1638.8	1650.1	1672.0	1692.0	1708.9	1720.7	1733.2	1738.2	1747.6	1760.7	1776.9
7.5°	1633.6	1655.5	1689.9	1719.0	1750.7	1773.6	1791.5	1806.7	1825.2	1850.1	1877.1
10°	1627.6	1657.0	1698.8	1734.5	1773.2	1802.5	1826.9	1850.6	1878.2	1912.5	1948.2
12.5°	1616.7	1651.5	1703.8	1746.0	1795.7	1824.6	1857.4	1908.7	1938.1	1986.0	2036.1
15°	1594.5	1633.2	1706.3	1758.2	1814.4	1869.4	1930.1	1978.7	2027.5	2055.6	2126.2
17.5°	1561.6	1618.5	1699.5	1760.0	1831.4	1918.0	1986.2	2041.3	2097.6	2143.2	2178.6
20°	1535.1	1597.0	1689.5	1761.9	1846.9	1940.0	2018.1	2074.4	2123.1	2161.2	2183.0
22.5°	1501.6	1579.5	1669.5	1754.4	1863.0	1955.0	2037.1	2081.4	2122.1	2140.7	2149.0
25°	1448.9	1542.6	1644.5	1748.2	1870.7	1968.1	2043.1	2070.0	2081.9	2063.8	2033.8
27.5°	1392.0	1496.6	1615.6	1736.4	1865.9	1959.7	2013.4	2009.1	1989.0	1930.4	1883.5
30°	1349.6	1464.5	1592.6	1724.4	1854.4	1945.6	1976.9	1945.6	1900.1	1834.4	1767.6
32.5°	1305.1	1424.1	1568.1	1707.5	1833.4	1913.7	1920.4	1866.7	1796.1	1721.5	1638.1
35°	1237.7	1366.4	1522.0	1669.5	1788.8	1839.4	1809.5	1714.5	1630.8	1528.9	1415.2
37.5°	1161.6	1303.7	1459.8	1613.9	1722.0	1735.2	1660.8	1560.7	1442.7	1323.0	1189.1
40°	1104.6	1255.2	1415.8	1571.4	1667.0	1653.3	1558.3	1448.3	1307.7	1161.5	1037.1
42.5°	1053.7	1204.3	1367.8	1520.4	1597.0	1559.3	1448.3	1313.4	1162.3	1024.6	910.7
45°	965.3	1120.3	1287.8	1435.2	1479.0	1410.8	1264.0	1114.0	965.3	850.4	760.4
47.5°	879.6	1032.8	1198.7	1328.2	1343.7	1252.1	1091.7	937.3	809.5	715.9	652.4
50°	816.6	970.3	1134.7	1250.3	1245.2	1134.7	969.7	822.9	716.0	640.4	597.9
52.5°	760.1	905.3	1063.2	1168.2	1141.7	1021.2	863.7	733.4	645.6	586.4	548.0
55°	672.3	806.7	956.6	1040.9	992.2	858.5	725.4	620.4	555.5	511.1	481.1
57.5°	585.1	711.0	839.4	891.4	837.5	714.0	603.1	526.9	478.1	445.2	425.7
60°	531.1	641.1	755.4	800.4	736.1	626.1	538.6	470.5	431.1	404.2	386.8
62.5°	477.1	575.6	683.4	707.9	649.1	556.1	478.6	422.0	389.6	365.7	349.3
65°	403.7	484.2	566.1	582.3	528.0	456.1	394.8	358.0	329.3	311.8	298.6
67.5°	331.0	395.7	453.7	466.8	419.2	369.4	325.1	293.0	273.5	259.0	247.9
70°	288.0	339.2	386.8	397.4	359.3	314.9	281.2	255.5	238.1	225.6	214.9
72.5°	242.6	285.3	324.7	331.9	300.8	266.9	239.2	219.1	203.6	195.6	185.5
75°	185.6	210.6	241.2	243.0	222.4	201.8	180.6	167.5	159.3	149.4	144.3
77.5°	130.9	150.6	168.0	171.5	159.2	145.2	133.3	122.9	116.1	111.5	106.8
80°	100.0	115.6	123.1	127.4	118.7	108.7	101.8	95.0	90.6	87.5	84.4
82.5°	71.5	81.1	88.1	91.5	86.7	80.7	73.9	70.0	66.6	64.0	62.9
85°	36.2	40.6	45.0	46.2	45.0	42.5	38.7	38.7	36.9	36.2	36.2
87.5°	12.9	15.2	15.4	17.2	16.5	16.6	16.9	16.6	16.3	15.9	15.6
90°	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7
92.5°	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9
95°	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6
97.5°	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8
100°	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6
102.5°	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1
105°	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6
107.5°	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9
110°	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5





TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4
115°	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7
117.5°	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7
120°	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4
122.5°	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1
125°	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0
127.5°	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2
130°	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9
132.5°	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9
135°	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0
137.5°	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9
140°	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0
142.5°	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6
145°	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9
147.5°	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3
150°	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8
152.5°	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2
155°	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6
157.5°	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7
160°	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2
162.5°	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3
165°	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9
167.5°	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1
170°	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7
172.5°	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4
175°	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5
177.5°	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7	1625.7
2.5°	1686.2	1693.2	1693.2	1694.2	1702.2	1701.2	1700.7
5°	1794.5	1805.1	1806.3	1817.5	1825.0	1822.5	1815.7
7.5°	1896.5	1916.3	1931.3	1939.7	1949.5	1955.7	1952.9
10°	1977.5	2006.3	2023.7	2035.6	2050.0	2060.6	2056.8
12.5°	2051.0	2085.2	2109.3	2129.6	2131.4	2145.1	2135.8
15°	2165.6	2201.8	2205.5	2220.5	2232.5	2231.1	2231.8
17.5°	2203.4	2215.1	2217.5	2217.8	2217.9	2213.5	2204.1
20°	2190.0	2185.6	2175.0	2166.8	2152.5	2150.6	2138.1
22.5°	2126.0	2112.1	2085.5	2067.8	2045.5	2039.6	2036.1
25°	2000.0	1969.4	1926.9	1886.3	1875.0	1853.2	1859.5
27.5°	1827.2	1779.5	1733.5	1700.5	1670.6	1637.9	1647.2
30°	1705.7	1652.0	1587.0	1537.0	1505.1	1473.9	1468.3
32.5°	1560.7	1482.1	1409.6	1365.5	1316.7	1297.0	1275.4
35°	1310.8	1234.0	1162.1	1100.2	1064.7	1037.1	1012.2
37.5°	1086.1	997.6	939.6	889.5	863.7	848.0	852.0
40°	946.6	869.1	826.6	788.5	764.8	753.5	756.0
42.5°	833.6	775.6	740.6	714.5	697.8	691.5	690.1
45°	705.4	672.9	644.2	629.2	621.1	614.2	609.8
47.5°	617.9	591.4	575.2	566.3	559.2	552.2	552.0
50°	565.4	548.0	536.7	527.3	521.7	516.7	521.1
52.5°	525.5	509.5	498.2	489.8	487.7	483.2	483.1
55°	466.1	453.6	445.5	438.0	434.2	431.7	428.6
57.5°	412.1	400.2	392.7	388.0	380.9	378.4	377.4
60°	373.7	364.3	356.8	350.5	347.4	342.4	342.4
62.5°	338.1	328.8	321.8	317.0	311.9	309.9	310.4
65°	286.8	279.3	272.4	267.4	266.2	262.4	263.7
67.5°	239.5	234.6	227.3	224.5	222.2	220.2	218.7
70°	208.1	203.1	199.3	195.6	193.7	193.7	193.7
72.5°	181.6	175.5	173.3	168.6	169.7	167.7	165.7
75°	140.6	136.8	134.9	133.1	130.0	130.0	130.0
77.5°	103.5	102.3	100.1	98.1	97.3	96.7	96.9
80°	80.0	79.3	78.1	78.1	76.9	76.2	75.0
82.5°	61.5	59.8	59.1	58.6	58.4	58.2	58.0
85°	35.0	33.8	33.8	34.3	33.1	33.1	33.8
87.5°	16.1	16.3	15.9	15.9	16.5	16.1	16.1
90°	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331591-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)