

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331596-930

Luminaire Tested: **S122DIW-S1005D710U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331596-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S1005D710U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5313.5 lumens
Efficiency: N/A
Efficacy: 88.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	110	110	110	110	103	103	103	103	90	90	90		78	78	78		67	67	67	62
1	101	96	92	89	94	90	87	84	79	77	74		69	67	65		60	58	57	52
2	92	84	78	72	86	79	73	69	69	65	61		61	57	55		52	50	48	44
3	84	74	66	60	78	69	63	57	61	56	52		54	50	46		46	43	41	37
4	76	65	57	51	71	62	54	49	54	49	44		48	43	40		42	38	35	32
5	70	58	50	44	66	55	48	42	49	43	38		43	38	34		37	34	31	28
6	65	52	44	38	61	50	42	37	44	38	33		39	34	30		34	30	27	24
7	60	47	39	34	56	45	37	32	40	34	29		35	30	27		31	27	24	22
8	56	43	35	30	52	41	34	29	37	31	26		32	28	24		29	25	22	19
9	52	39	32	27	49	37	30	26	34	28	24		30	25	22		26	22	20	17
10	49	36	29	24	46	34	28	23	31	25	21		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	20980	20980	20980
5°	21060	20757	20879
10°	20935	20546	20649
15°	20677	20279	20259
20°	20309	19880	19859
25°	19946	19388	19388
30°	19475	18938	18776
35°	19036	18398	18126
40°	18487	17856	17513
45°	17945	17317	16890
50°	17357	16759	16164
55°	16743	16110	15510
60°	16059	15332	14767
65°	15320	14560	13891
70°	14389	13624	12977
75°	13094	12545	12239
80°	11623	11269	10693
85°	9485	9040	8096



TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	122.2	2.3
10°-20°	343.8	6.5
20°-30°	505.4	9.5
30°-40°	587.0	11.0
40°-50°	586.4	11.0
50°-60°	511.4	9.6
60°-70°	378.1	7.1
70°-80°	214.2	4.0
80°-90°	60.5	1.1
90°-100°	45.4	0.9
100°-110°	141.1	2.7
110°-120°	241.2	4.5
120°-130°	317.1	6.0
130°-140°	356.0	6.7
140°-150°	349.0	6.6
150°-160°	292.8	5.5
160°-170°	194.2	3.7
170°-180°	67.9	1.3
0°-30°	971.4	18.3
0°-40°	1558.4	29.3
0°-60°	2656.1	50.0
0°-90°	3308.9	62.3
90°-120°	427.7	8.0
90°-150°	1449.8	27.3
90°-180°	2005.0	37.7
0°-180°	5313.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1299	1299	1299	1299	1299	
5°	1299	1294	1281	1290	1288	123
15°	1237	1229	1213	1218	1212	348
25°	1120	1109	1088	1090	1088	515
35°	966	953	933	926	920	603
45°	786	777	758	745	740	606
55°	595	587	572	558	551	532
65°	401	393	381	370	364	397
75°	210	207	201	194	196	224
85°	51	50	49	45	44	59
90°	1	8	21	20	20	4
95°	32	37	39	39	38	36
105°	130	132	133	134	134	137
115°	242	245	244	244	242	239
125°	352	357	356	354	353	315
135°	456	462	463	463	461	352
145°	553	557	561	561	559	345
155°	632	634	636	639	637	291
165°	688	687	687	691	688	194
175°	716	714	713	716	713	68
180°	717	717	717	717	717	



TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1305.5	1304.3	1303.3	1302.1	1301.0	1299.3	1296.8	1294.4	1291.9	1289.5	1291.7
5°	1299.4	1298.4	1297.2	1296.1	1295.0	1292.9	1289.9	1286.8	1283.8	1280.7	1283.0
7.5°	1287.9	1286.2	1284.5	1282.8	1281.1	1278.6	1275.5	1272.4	1269.3	1266.2	1268.4
10°	1276.9	1275.0	1273.1	1271.1	1269.2	1266.6	1263.2	1259.9	1256.5	1253.2	1255.5
12.5°	1262.0	1260.2	1258.5	1256.8	1255.1	1252.5	1249.2	1245.9	1242.6	1239.3	1240.8
15°	1237.0	1235.3	1233.6	1232.0	1230.3	1227.7	1224.1	1220.4	1216.8	1213.2	1214.4
17.5°	1205.0	1203.3	1201.7	1200.0	1198.3	1195.6	1192.0	1188.3	1184.6	1181.0	1182.3
20°	1182.0	1180.3	1178.7	1177.0	1175.3	1172.6	1168.7	1164.8	1160.9	1157.0	1157.8
22.5°	1159.0	1156.7	1154.4	1152.0	1149.7	1146.7	1143.0	1139.4	1135.7	1132.0	1132.2
25°	1119.6	1117.3	1115.1	1112.9	1110.7	1107.2	1102.4	1097.7	1093.0	1088.3	1088.8
27.5°	1074.6	1072.5	1070.6	1068.5	1066.6	1063.7	1060.0	1056.2	1052.6	1048.8	1048.0
30°	1044.6	1042.4	1040.1	1037.9	1035.7	1032.5	1028.3	1024.2	1020.0	1015.8	1015.0
32.5°	1012.6	1010.8	1009.0	1007.2	1005.4	1002.4	998.0	993.6	989.2	984.8	983.3
35°	965.8	963.0	960.3	957.5	954.7	951.1	946.6	942.2	937.8	933.4	931.7
37.5°	913.1	910.7	908.2	905.8	903.4	899.9	895.4	891.0	886.6	882.2	880.0
40°	877.1	874.9	872.7	870.5	868.2	865.0	860.5	856.1	851.6	847.2	844.7
42.5°	842.1	839.9	837.7	835.5	833.2	829.9	825.5	821.0	816.6	812.1	809.4
45°	785.9	784.0	782.0	780.1	778.1	775.1	770.9	766.8	762.6	758.4	755.4
47.5°	729.9	728.1	726.3	724.5	722.6	719.5	715.2	710.9	706.5	702.2	699.0
50°	691.0	689.6	688.2	686.8	685.4	682.7	678.9	675.0	671.1	667.2	663.3
52.5°	653.0	651.2	649.3	647.5	645.6	642.9	639.2	635.5	631.9	628.3	625.0
55°	594.8	593.0	591.4	589.8	588.1	585.5	582.3	578.9	575.6	572.3	568.9
57.5°	536.3	534.9	533.6	532.3	530.9	528.5	524.8	521.1	517.5	513.8	510.5
60°	497.3	496.2	495.0	494.0	492.8	490.3	486.5	482.6	478.7	474.8	471.7
62.5°	459.3	457.5	455.8	454.0	452.2	449.8	446.8	443.8	440.8	437.8	435.0
65°	401.0	399.4	397.8	396.1	394.4	392.2	389.4	386.6	383.8	381.1	378.6
67.5°	341.9	340.6	339.2	337.9	336.6	334.6	332.1	329.6	327.1	324.7	322.7
70°	304.8	303.8	302.6	301.6	300.4	298.6	296.1	293.6	291.1	288.6	286.7
72.5°	266.8	265.8	264.6	263.6	262.4	261.1	259.5	257.9	256.2	254.6	252.7
75°	209.9	209.4	208.8	208.2	207.7	206.7	205.3	203.9	202.5	201.1	199.5
77.5°	158.9	158.0	157.0	156.1	155.2	154.4	153.8	153.3	152.7	152.2	151.3
80°	125.0	124.7	124.4	124.1	123.8	123.4	122.9	122.3	121.7	121.2	120.3
82.5°	92.9	92.9	92.9	92.8	92.7	92.5	92.2	91.9	91.6	91.2	90.2
85°	51.2	51.0	50.7	50.4	50.1	49.8	49.6	49.2	49.0	48.8	47.9
87.5°	18.1	18.0	17.9	17.8	17.6	17.6	17.8	17.9	18.1	18.3	17.5
90°	0.6	2.2	3.8	5.5	7.1	9.4	12.3	15.2	18.2	21.2	20.9
92.5°	10.8	12.0	13.1	14.3	15.5	16.5	17.1	17.9	18.5	19.2	19.3
95°	31.5	32.8	34.2	35.5	36.9	37.7	37.9	38.2	38.5	38.7	38.7
97.5°	57.5	58.6	59.8	61.0	62.2	63.0	63.6	64.1	64.6	65.1	65.1
100°	76.8	77.9	79.0	80.1	81.1	81.9	82.3	82.7	83.1	83.5	83.5
102.5°	97.2	98.0	98.9	99.7	100.6	101.3	101.8	102.3	102.8	103.3	103.5
105°	130.0	130.4	130.9	131.3	131.7	132.0	132.3	132.6	132.8	133.1	133.4
107.5°	163.2	163.8	164.4	165.0	165.6	165.9	165.9	165.9	165.9	165.9	166.0
110°	184.5	185.3	186.1	186.9	187.8	188.2	188.2	188.2	188.2	188.2	188.2



TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	207.7	208.6	209.4	210.2	211.0	211.3	211.2	211.1	211.0	210.9	210.6
115°	242.0	242.8	243.6	244.4	245.2	245.5	245.2	244.9	244.7	244.4	244.3
117.5°	276.1	277.2	278.3	279.3	280.4	280.5	279.8	279.1	278.3	277.6	277.3
120°	298.9	299.9	301.0	302.1	303.1	303.1	302.1	301.0	299.9	298.9	298.9
122.5°	319.7	321.0	322.3	323.5	324.8	325.1	324.3	323.6	322.9	322.1	321.8
125°	352.1	353.4	354.5	355.7	356.9	357.3	356.9	356.5	356.1	355.7	355.3
127.5°	383.7	385.2	386.8	388.2	389.8	390.4	389.9	389.4	388.9	388.4	387.9
130°	403.5	405.3	407.0	408.8	410.5	411.2	411.0	410.7	410.4	410.2	409.9
132.5°	425.8	427.2	428.7	430.1	431.5	432.3	432.3	432.4	432.4	432.4	431.9
135°	455.6	457.1	458.5	460.0	461.5	462.4	462.6	462.9	463.2	463.4	463.3
137.5°	486.9	488.1	489.3	490.6	491.7	492.5	492.8	493.3	493.6	493.9	493.8
140°	505.8	507.0	508.2	509.4	510.6	511.5	512.3	512.9	513.6	514.2	514.2
142.5°	525.1	526.4	527.6	528.8	529.9	530.8	531.2	531.7	532.1	532.6	532.7
145°	552.9	553.9	554.8	555.8	556.8	557.6	558.4	559.2	560.0	560.8	560.9
147.5°	577.8	578.9	580.0	581.1	582.3	583.1	583.7	584.2	584.7	585.3	585.5
150°	594.7	595.5	596.3	597.1	597.9	598.6	599.2	599.7	600.2	600.8	601.2
152.5°	609.7	610.5	611.3	612.1	612.9	613.7	614.3	615.0	615.6	616.3	616.8
155°	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.4	635.9	636.5
157.5°	651.4	651.8	652.0	652.2	652.6	652.8	653.1	653.3	653.5	653.8	654.7
160°	663.1	663.3	663.6	663.9	664.1	664.4	664.5	664.6	664.7	664.9	665.7
162.5°	673.7	673.8	673.8	673.8	673.9	674.0	674.2	674.3	674.4	674.6	675.5
165°	687.9	687.7	687.6	687.5	687.4	687.3	687.3	687.3	687.3	687.3	688.2
167.5°	699.8	699.4	699.0	698.5	698.1	697.9	697.9	697.8	697.8	697.8	698.7
170°	706.0	705.6	705.2	704.8	704.4	704.2	704.0	703.8	703.8	703.6	704.6
172.5°	710.4	710.0	709.6	709.1	708.7	708.5	708.3	708.3	708.1	707.9	708.9
175°	715.7	715.3	714.9	714.5	714.1	713.8	713.5	713.2	713.0	712.7	713.6
177.5°	717.9	717.5	717.2	716.9	716.6	716.3	716.1	715.9	715.7	715.4	716.1
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9



TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4	1299.4
2.5°	1293.9	1296.1	1298.4	1299.3	1298.8	1298.4	1297.9	1297.5
5°	1285.2	1287.4	1289.6	1290.5	1289.9	1289.3	1288.7	1288.2
7.5°	1270.6	1272.8	1275.1	1275.9	1275.3	1274.7	1274.1	1273.5
10°	1257.7	1259.9	1262.1	1262.8	1262.0	1261.1	1260.3	1259.5
12.5°	1242.4	1243.9	1245.5	1245.9	1245.3	1244.7	1244.1	1243.5
15°	1215.4	1216.6	1217.6	1217.6	1216.2	1214.8	1213.4	1212.0
17.5°	1183.6	1184.9	1186.1	1186.1	1184.7	1183.4	1182.1	1180.7
20°	1158.7	1159.5	1160.3	1160.2	1159.1	1158.0	1156.9	1155.8
22.5°	1132.4	1132.5	1132.7	1132.5	1131.8	1131.1	1130.4	1129.8
25°	1089.4	1090.0	1090.5	1090.5	1090.0	1089.4	1088.8	1088.3
27.5°	1047.2	1046.3	1045.5	1044.4	1043.1	1041.7	1040.4	1039.1
30°	1014.2	1013.3	1012.5	1011.5	1010.4	1009.3	1008.2	1007.1
32.5°	981.9	980.3	978.8	977.5	976.4	975.3	974.2	973.1
35°	930.0	928.4	926.7	925.2	923.8	922.4	921.0	919.6
37.5°	878.0	876.0	873.9	872.2	870.9	869.5	868.2	866.9
40°	842.1	839.7	837.1	835.4	834.2	833.2	832.0	830.9
42.5°	806.7	804.0	801.3	799.2	797.6	796.1	794.5	792.9
45°	752.4	749.3	746.2	744.1	743.0	741.9	740.8	739.7
47.5°	695.8	692.5	689.3	686.9	685.3	683.7	682.1	680.4
50°	659.4	655.6	651.7	649.1	647.7	646.3	644.9	643.5
52.5°	621.8	618.6	615.4	612.9	611.0	609.2	607.3	605.5
55°	565.6	562.2	559.0	556.6	555.2	553.8	552.4	551.0
57.5°	507.2	503.9	500.7	498.5	497.5	496.4	495.4	494.3
60°	468.7	465.6	462.6	460.6	459.8	459.0	458.1	457.3
62.5°	432.2	429.3	426.5	424.5	423.5	422.4	421.3	420.3
65°	376.1	373.6	371.1	369.2	367.8	366.4	365.0	363.6
67.5°	320.7	318.8	316.8	315.3	314.2	313.1	312.0	310.9
70°	284.7	282.8	280.9	279.3	278.2	277.1	276.0	274.9
72.5°	250.8	248.8	246.9	245.5	244.6	243.7	242.8	241.9
75°	197.9	196.2	194.5	194.0	194.5	195.0	195.6	196.2
77.5°	150.5	149.7	148.9	148.1	147.2	146.5	145.7	145.0
80°	119.5	118.7	117.9	117.2	116.6	116.1	115.5	115.0
82.5°	89.1	88.1	87.0	86.4	86.3	86.2	86.1	85.9
85°	47.0	46.2	45.4	44.8	44.6	44.3	44.0	43.7
87.5°	16.8	16.1	15.3	14.9	14.7	14.5	14.3	14.1
90°	20.6	20.4	20.1	20.1	20.1	20.3	20.5	20.5
92.5°	19.3	19.4	19.5	19.5	19.5	19.6	19.6	19.6
95°	38.7	38.7	38.7	38.6	38.3	38.1	37.7	37.5
97.5°	65.1	65.1	65.1	65.1	65.1	65.1	65.0	65.0
100°	83.5	83.5	83.5	83.4	83.3	83.2	83.0	82.9
102.5°	103.5	103.6	103.8	103.8	103.6	103.5	103.4	103.2
105°	133.6	133.9	134.2	134.3	134.3	134.3	134.3	134.3
107.5°	166.1	166.2	166.3	166.1	165.4	164.9	164.2	163.6
110°	188.2	188.2	188.2	187.9	187.5	187.1	186.7	186.4



TEST NUMBER: P331596-930

CATALOG NUMBER: S122DIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	209.9	209.6	209.3	209.0	208.7	208.4	208.1
115°	244.2	244.0	243.9	243.6	243.2	242.8	242.4	242.0
117.5°	277.0	276.6	276.3	275.9	275.5	275.1	274.7	274.3
120°	298.9	298.9	298.9	298.6	298.2	297.8	297.4	297.0
122.5°	321.5	321.1	320.8	320.5	320.2	319.9	319.6	319.4
125°	354.9	354.5	354.1	353.8	353.8	353.6	353.4	353.4
127.5°	387.4	386.9	386.5	386.0	385.6	385.1	384.7	384.3
130°	409.7	409.4	409.1	408.7	408.1	407.6	407.1	406.6
132.5°	431.3	430.6	430.1	429.6	429.2	428.7	428.3	427.9
135°	463.2	463.0	462.9	462.6	462.2	461.8	461.4	461.0
137.5°	493.7	493.6	493.5	493.2	492.6	492.1	491.5	491.0
140°	514.2	514.2	514.2	514.0	513.5	512.9	512.3	511.8
142.5°	532.9	533.0	533.0	532.9	532.3	531.7	531.2	530.7
145°	561.1	561.3	561.3	561.2	560.6	560.1	559.5	559.1
147.5°	585.9	586.1	586.4	586.4	585.9	585.3	584.8	584.3
150°	601.5	601.9	602.3	602.3	601.9	601.5	601.2	600.8
152.5°	617.3	617.8	618.3	618.3	617.8	617.3	616.8	616.3
155°	637.2	637.9	638.5	638.7	638.3	637.9	637.5	637.1
157.5°	655.6	656.5	657.4	657.5	656.9	656.2	655.6	654.9
160°	666.5	667.3	668.1	668.2	667.7	667.2	666.7	666.1
162.5°	676.4	677.4	678.2	678.3	677.7	677.1	676.5	675.8
165°	689.2	690.1	691.0	691.2	690.5	689.8	689.2	688.5
167.5°	699.7	700.6	701.6	701.6	701.0	700.3	699.6	698.9
170°	705.5	706.5	707.4	707.4	706.6	705.8	705.0	704.2
172.5°	709.9	710.8	711.8	711.8	711.0	710.2	709.4	708.6
175°	714.5	715.5	716.5	716.5	715.7	714.9	714.1	713.3
177.5°	716.7	717.4	718.0	718.0	717.4	716.7	716.1	715.4
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9

(END OF REPORT)