

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331502-935

Luminaire Tested: **S122DIW-S485D710U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331502-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D710U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3965.9 lumens
Efficiency: N/A
Efficacy: 105.5 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 37.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20			20			20			20
RC	80				70				50			30			10			0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	50	45	41	42	38	35	34	32	29	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	33	27	23	29	24	20	25	21	18	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	2.0
10°-20°	231.6	5.8
20°-30°	336.2	8.5
30°-40°	354.8	8.9
40°-50°	314.1	7.9
50°-60°	250.7	6.3
60°-70°	170.4	4.3
70°-80°	87.4	2.2
80°-90°	24.1	0.6
90°-100°	48.0	1.2
100°-110°	149.0	3.8
110°-120°	254.7	6.4
120°-130°	334.9	8.4
130°-140°	375.9	9.5
140°-150°	368.6	9.3
150°-160°	309.2	7.8
160°-170°	205.1	5.2
170°-180°	71.7	1.8
0°-30°	647.5	16.3
0°-40°	1002.3	25.3
0°-60°	1567.1	39.5
0°-90°	1848.9	46.6
90°-120°	451.7	11.4
90°-150°	1531.1	38.6
90°-180°	2117.0	53.4
0°-180°	3965.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	22	1	22	1	22	10
95°	40	33	40	33	40	44
105°	142	137	142	137	142	149
115°	256	256	256	256	256	252
125°	373	372	373	372	373	333
135°	487	481	487	481	487	375
145°	590	584	590	584	590	369
155°	673	668	673	668	673	310
165°	727	726	727	726	727	205
175°	753	756	753	756	753	72
180°	757	757	757	757	757	



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	11.0	11.0	11.2	10.9	10.9	11.2	11.3	11.0	11.4	11.7	11.3
90°	21.7	21.6	21.4	21.3	21.2	21.3	21.5	21.8	22.0	22.4	19.2
92.5°	20.7	20.7	20.7	20.6	20.6	20.6	20.5	20.4	20.4	20.3	19.5
95°	39.6	39.9	40.2	40.5	40.7	40.9	40.9	40.9	40.9	40.9	40.6
97.5°	68.6	68.6	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.7	68.2
100°	87.6	87.6	87.8	88.0	88.1	88.2	88.2	88.2	88.2	88.2	87.7
102.5°	109.0	109.2	109.3	109.4	109.6	109.6	109.4	109.3	109.3	109.1	108.6
105°	141.8	141.8	141.8	141.8	141.8	141.7	141.4	141.1	140.9	140.6	140.3
107.5°	172.8	173.4	174.1	174.7	175.4	175.6	175.6	175.4	175.3	175.2	175.2
110°	196.8	197.2	197.6	198.0	198.5	198.7	198.7	198.7	198.7	198.7	198.7



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	219.8	220.1	220.4	220.8	221.0	221.4	221.7	222.1	222.4	222.7	222.8
115°	255.5	256.0	256.4	256.8	257.3	257.5	257.7	257.9	258.0	258.1	258.4
117.5°	289.6	290.1	290.5	290.9	291.4	291.8	292.1	292.5	292.8	293.2	293.9
120°	313.7	314.1	314.5	315.0	315.4	315.6	315.6	315.6	315.6	315.6	316.8
122.5°	337.3	337.5	337.9	338.1	338.5	338.8	339.1	339.5	339.8	340.2	341.0
125°	373.2	373.2	373.4	373.6	373.7	373.9	374.4	374.8	375.2	375.7	376.1
127.5°	405.9	406.3	406.7	407.2	407.7	408.1	408.6	409.1	409.7	410.2	410.7
130°	429.4	429.9	430.5	431.0	431.6	432.0	432.3	432.7	432.9	433.2	433.4
132.5°	451.9	452.3	452.7	453.2	453.7	454.2	454.8	455.5	456.1	456.7	456.7
135°	486.8	487.2	487.7	488.1	488.5	488.9	489.0	489.1	489.2	489.4	489.1
137.5°	518.5	519.1	519.7	520.2	520.8	521.2	521.2	521.3	521.5	521.6	521.2
140°	540.5	541.1	541.7	542.3	542.8	543.0	543.0	543.0	543.0	543.0	542.3
142.5°	560.4	561.0	561.5	562.1	562.7	562.9	562.8	562.7	562.6	562.5	562.0
145°	590.4	590.9	591.5	592.0	592.6	592.8	592.7	592.5	592.4	592.3	591.4
147.5°	617.1	617.6	618.1	618.7	619.2	619.3	619.0	618.7	618.4	618.1	617.5
150°	634.5	634.9	635.2	635.7	636.1	636.1	635.7	635.2	634.9	634.5	633.9
152.5°	650.8	651.3	651.9	652.4	653.0	653.0	652.4	651.9	651.3	650.8	650.1
155°	672.8	673.2	673.6	674.1	674.5	674.3	673.6	672.9	672.2	671.5	671.1
157.5°	691.6	692.3	693.0	693.7	694.4	694.2	693.3	692.3	691.4	690.4	690.2
160°	703.4	704.0	704.6	705.2	705.7	705.6	704.7	703.9	703.0	702.1	702.0
162.5°	713.7	714.4	715.1	715.7	716.4	716.3	715.3	714.3	713.3	712.4	712.2
165°	727.1	727.8	728.5	729.2	730.0	729.8	728.8	727.8	726.8	725.8	725.8
167.5°	738.0	738.8	739.5	740.3	741.0	740.9	739.9	738.9	737.9	736.9	736.9
170°	743.6	744.5	745.4	746.2	747.1	747.0	746.1	745.0	744.1	743.0	743.2
172.5°	748.3	749.2	750.0	750.9	751.7	751.7	750.6	749.7	748.6	747.6	747.8
175°	753.3	754.1	755.0	755.8	756.6	756.6	755.6	754.6	753.6	752.6	752.9
177.5°	755.5	756.2	756.9	757.6	758.3	758.3	757.6	756.9	756.2	755.5	755.8
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	10.9	10.3	9.7	9.7	8.6	8.3	6.9	5.8	5.9	5.9	5.8
90°	16.1	13.0	9.9	7.5	5.8	4.0	2.3	0.6	2.3	4.0	5.8
92.5°	18.9	18.1	17.4	16.4	15.2	13.9	12.7	11.4	12.7	13.9	15.2
95°	40.3	40.0	39.8	38.9	37.5	36.1	34.6	33.2	34.6	36.1	37.5
97.5°	67.7	67.2	66.6	65.7	64.4	63.2	61.9	60.7	61.9	63.2	64.4
100°	87.3	86.9	86.4	85.7	84.6	83.4	82.3	81.1	82.3	83.4	84.6
102.5°	108.1	107.5	106.9	106.2	105.3	104.4	103.5	102.6	103.5	104.4	105.3
105°	140.0	139.7	139.4	139.1	138.6	138.2	137.8	137.3	137.8	138.2	138.6
107.5°	175.2	175.2	175.2	174.9	174.3	173.7	173.0	172.4	173.0	173.7	174.3
110°	198.7	198.7	198.7	198.3	197.4	196.6	195.7	194.8	195.7	196.6	197.4



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	222.9	223.1	223.2	222.8	222.0	221.1	220.2	219.4	220.2	221.1	222.0
115°	258.6	259.0	259.2	259.0	258.1	257.3	256.4	255.5	256.4	257.3	258.1
117.5°	294.7	295.5	296.3	296.1	295.0	293.9	292.7	291.6	292.7	293.9	295.0
120°	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	316.8	317.9	319.0
122.5°	341.7	342.5	343.4	343.0	341.6	340.4	339.0	337.6	339.0	340.4	341.6
125°	376.5	376.9	377.4	376.9	375.7	374.4	373.2	371.9	373.2	374.4	375.7
127.5°	411.2	411.7	412.2	411.6	410.0	408.5	406.8	405.2	406.8	408.5	410.0
130°	433.8	434.0	434.3	433.5	431.7	429.8	428.0	426.1	428.0	429.8	431.7
132.5°	456.6	456.5	456.5	455.6	454.2	452.7	451.2	449.7	451.2	452.7	454.2
135°	488.9	488.5	488.3	487.3	485.8	484.2	482.7	481.1	482.7	484.2	485.8
137.5°	520.9	520.5	520.1	519.3	518.1	516.8	515.5	514.2	515.5	516.8	518.1
140°	541.7	541.0	540.2	539.2	538.0	536.7	535.4	534.2	535.4	536.7	538.0
142.5°	561.5	561.0	560.6	559.6	558.4	557.2	555.9	554.6	555.9	557.2	558.4
145°	590.6	589.7	588.8	588.0	586.9	585.9	585.0	583.9	585.0	585.9	586.9
147.5°	616.9	616.4	615.8	614.9	613.7	612.5	611.3	610.2	611.3	612.5	613.7
150°	633.3	632.7	632.1	631.5	630.6	629.7	628.9	628.0	628.9	629.7	630.6
152.5°	649.5	648.8	648.1	647.3	646.4	645.6	644.7	643.9	644.7	645.6	646.4
155°	670.6	670.2	669.8	669.3	668.9	668.5	668.0	667.6	668.0	668.5	668.9
157.5°	689.9	689.7	689.4	689.1	688.8	688.5	688.3	687.9	688.3	688.5	688.8
160°	701.9	701.7	701.6	701.4	701.1	700.8	700.5	700.3	700.5	700.8	701.1
162.5°	712.1	712.0	711.8	711.7	711.6	711.6	711.5	711.4	711.5	711.6	711.6
165°	725.8	725.8	725.8	725.9	726.0	726.2	726.3	726.4	726.3	726.2	726.0
167.5°	736.9	737.0	737.0	737.3	737.7	738.1	738.6	739.0	738.6	738.1	737.7
170°	743.3	743.5	743.6	743.9	744.3	744.8	745.2	745.6	745.2	744.8	744.3
172.5°	748.0	748.0	748.2	748.5	748.9	749.3	749.8	750.2	749.8	749.3	748.9
175°	753.2	753.5	753.8	754.1	754.6	755.0	755.4	755.8	755.4	755.0	754.6
177.5°	756.0	756.2	756.5	756.7	757.1	757.4	757.8	758.1	757.8	757.4	757.1
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	5.9	6.1	6.5	7.1	7.5	7.8	7.5	7.4	7.4	6.8	6.8
90°	7.5	9.9	13.0	16.1	19.2	22.4	22.0	21.8	21.5	21.3	21.2
92.5°	16.4	17.4	18.1	18.9	19.5	20.3	20.4	20.4	20.5	20.6	20.6
95°	38.9	39.8	40.0	40.3	40.6	40.9	40.9	40.9	40.9	40.9	40.7
97.5°	65.7	66.6	67.2	67.7	68.2	68.7	68.7	68.7	68.7	68.7	68.7
100°	85.7	86.4	86.9	87.3	87.7	88.2	88.2	88.2	88.2	88.2	88.1
102.5°	106.2	106.9	107.5	108.1	108.6	109.1	109.3	109.3	109.4	109.6	109.6
105°	139.1	139.4	139.7	140.0	140.3	140.6	140.9	141.1	141.4	141.7	141.8
107.5°	174.9	175.2	175.2	175.2	175.2	175.2	175.3	175.4	175.6	175.6	175.4
110°	198.3	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.7	198.5



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	222.8	223.2	223.1	222.9	222.8	222.7	222.4	222.1	221.7	221.4	221.0
115°	259.0	259.2	259.0	258.6	258.4	258.1	258.0	257.9	257.7	257.5	257.3
117.5°	296.1	296.3	295.5	294.7	293.9	293.2	292.8	292.5	292.1	291.8	291.4
120°	320.1	320.1	319.0	317.9	316.8	315.6	315.6	315.6	315.6	315.6	315.4
122.5°	343.0	343.4	342.5	341.7	341.0	340.2	339.8	339.5	339.1	338.8	338.5
125°	376.9	377.4	376.9	376.5	376.1	375.7	375.2	374.8	374.4	373.9	373.7
127.5°	411.6	412.2	411.7	411.2	410.7	410.2	409.7	409.1	408.6	408.1	407.7
130°	433.5	434.3	434.0	433.8	433.4	433.2	432.9	432.7	432.3	432.0	431.6
132.5°	455.6	456.5	456.5	456.6	456.7	456.7	456.1	455.5	454.8	454.2	453.7
135°	487.3	488.3	488.5	488.9	489.1	489.4	489.2	489.1	489.0	488.9	488.5
137.5°	519.3	520.1	520.5	520.9	521.2	521.6	521.5	521.3	521.2	521.2	520.8
140°	539.2	540.2	541.0	541.7	542.3	543.0	543.0	543.0	543.0	543.0	542.8
142.5°	559.6	560.6	561.0	561.5	562.0	562.5	562.6	562.7	562.8	562.9	562.7
145°	588.0	588.8	589.7	590.6	591.4	592.3	592.4	592.5	592.7	592.8	592.6
147.5°	614.9	615.8	616.4	616.9	617.5	618.1	618.4	618.7	619.0	619.3	619.2
150°	631.5	632.1	632.7	633.3	633.9	634.5	634.9	635.2	635.7	636.1	636.1
152.5°	647.3	648.1	648.8	649.5	650.1	650.8	651.3	651.9	652.4	653.0	653.0
155°	669.3	669.8	670.2	670.6	671.1	671.5	672.2	672.9	673.6	674.3	674.5
157.5°	689.1	689.4	689.7	689.9	690.2	690.4	691.4	692.3	693.3	694.2	694.4
160°	701.4	701.6	701.7	701.9	702.0	702.1	703.0	703.9	704.7	705.6	705.7
162.5°	711.7	711.8	712.0	712.1	712.2	712.4	713.3	714.3	715.3	716.3	716.4
165°	725.9	725.8	725.8	725.8	725.8	725.8	726.8	727.8	728.8	729.8	730.0
167.5°	737.3	737.0	737.0	736.9	736.9	736.9	737.9	738.9	739.9	740.9	741.0
170°	743.9	743.6	743.5	743.3	743.2	743.0	744.1	745.0	746.1	747.0	747.1
172.5°	748.5	748.2	748.0	748.0	747.8	747.6	748.6	749.7	750.6	751.7	751.7
175°	754.1	753.8	753.5	753.2	752.9	752.6	753.6	754.6	755.6	756.6	756.6
177.5°	756.7	756.5	756.2	756.0	755.8	755.5	756.2	756.9	757.6	758.3	758.3
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	6.8	6.6	6.6	6.4	6.6	6.6	6.8	6.8	6.8	7.4	7.4
90°	21.3	21.4	21.6	21.7	21.6	21.4	21.3	21.2	21.3	21.5	21.8
92.5°	20.6	20.7	20.7	20.7	20.7	20.7	20.6	20.6	20.6	20.5	20.4
95°	40.5	40.2	39.9	39.6	39.9	40.2	40.5	40.7	40.9	40.9	40.9
97.5°	68.7	68.7	68.6	68.6	68.6	68.7	68.7	68.7	68.7	68.7	68.7
100°	88.0	87.8	87.6	87.6	87.6	87.8	88.0	88.1	88.2	88.2	88.2
102.5°	109.4	109.3	109.2	109.0	109.2	109.3	109.4	109.6	109.6	109.4	109.3
105°	141.8	141.8	141.8	141.8	141.8	141.8	141.8	141.8	141.7	141.4	141.1
107.5°	174.7	174.1	173.4	172.8	173.4	174.1	174.7	175.4	175.6	175.6	175.4
110°	198.0	197.6	197.2	196.8	197.2	197.6	198.0	198.5	198.7	198.7	198.7



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	220.8	220.4	220.1	219.8	220.1	220.4	220.8	221.0	221.4	221.7	222.1
115°	256.8	256.4	256.0	255.5	256.0	256.4	256.8	257.3	257.5	257.7	257.9
117.5°	290.9	290.5	290.1	289.6	290.1	290.5	290.9	291.4	291.8	292.1	292.5
120°	315.0	314.5	314.1	313.7	314.1	314.5	315.0	315.4	315.6	315.6	315.6
122.5°	338.1	337.9	337.5	337.3	337.5	337.9	338.1	338.5	338.8	339.1	339.5
125°	373.6	373.4	373.2	373.2	373.2	373.4	373.6	373.7	373.9	374.4	374.8
127.5°	407.2	406.7	406.3	405.9	406.3	406.7	407.2	407.7	408.1	408.6	409.1
130°	431.0	430.5	429.9	429.4	429.9	430.5	431.0	431.6	432.0	432.3	432.7
132.5°	453.2	452.7	452.3	451.9	452.3	452.7	453.2	453.7	454.2	454.8	455.5
135°	488.1	487.7	487.2	486.8	487.2	487.7	488.1	488.5	488.9	489.0	489.1
137.5°	520.2	519.7	519.1	518.5	519.1	519.7	520.2	520.8	521.2	521.2	521.3
140°	542.3	541.7	541.1	540.5	541.1	541.7	542.3	542.8	543.0	543.0	543.0
142.5°	562.1	561.5	561.0	560.4	561.0	561.5	562.1	562.7	562.9	562.8	562.7
145°	592.0	591.5	590.9	590.4	590.9	591.5	592.0	592.6	592.8	592.7	592.5
147.5°	618.7	618.1	617.6	617.1	617.6	618.1	618.7	619.2	619.3	619.0	618.7
150°	635.7	635.2	634.9	634.5	634.9	635.2	635.7	636.1	636.1	635.7	635.2
152.5°	652.4	651.9	651.3	650.8	651.3	651.9	652.4	653.0	653.0	652.4	651.9
155°	674.1	673.6	673.2	672.8	673.2	673.6	674.1	674.5	674.3	673.6	672.9
157.5°	693.7	693.0	692.3	691.6	692.3	693.0	693.7	694.4	694.2	693.3	692.3
160°	705.2	704.6	704.0	703.4	704.0	704.6	705.2	705.7	705.6	704.7	703.9
162.5°	715.7	715.1	714.4	713.7	714.4	715.1	715.7	716.4	716.3	715.3	714.3
165°	729.2	728.5	727.8	727.1	727.8	728.5	729.2	730.0	729.8	728.8	727.8
167.5°	740.3	739.5	738.8	738.0	738.8	739.5	740.3	741.0	740.9	739.9	738.9
170°	746.2	745.4	744.5	743.6	744.5	745.4	746.2	747.1	747.0	746.1	745.0
172.5°	750.9	750.0	749.2	748.3	749.2	750.0	750.9	751.7	751.7	750.6	749.7
175°	755.8	755.0	754.1	753.3	754.1	755.0	755.8	756.6	756.6	755.6	754.6
177.5°	757.6	756.9	756.2	755.5	756.2	756.9	757.6	758.3	758.3	757.6	756.9
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	7.5	7.8	7.5	7.1	6.5	6.1	5.9	5.8	5.9	5.9	5.8
90°	22.0	22.4	19.2	16.1	13.0	9.9	7.5	5.8	4.0	2.3	0.6
92.5°	20.4	20.3	19.5	18.9	18.1	17.4	16.4	15.2	13.9	12.7	11.4
95°	40.9	40.9	40.6	40.3	40.0	39.8	38.9	37.5	36.1	34.6	33.2
97.5°	68.7	68.7	68.2	67.7	67.2	66.6	65.7	64.4	63.2	61.9	60.7
100°	88.2	88.2	87.7	87.3	86.9	86.4	85.7	84.6	83.4	82.3	81.1
102.5°	109.3	109.1	108.6	108.1	107.5	106.9	106.2	105.3	104.4	103.5	102.6
105°	140.9	140.6	140.3	140.0	139.7	139.4	139.1	138.6	138.2	137.8	137.3
107.5°	175.3	175.2	175.2	175.2	175.2	175.2	174.9	174.3	173.7	173.0	172.4
110°	198.7	198.7	198.7	198.7	198.7	198.7	198.3	197.4	196.6	195.7	194.8



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	222.4	222.7	222.8	222.9	223.1	223.2	222.8	222.0	221.1	220.2	219.4
115°	258.0	258.1	258.4	258.6	259.0	259.2	259.0	258.1	257.3	256.4	255.5
117.5°	292.8	293.2	293.9	294.7	295.5	296.3	296.1	295.0	293.9	292.7	291.6
120°	315.6	315.6	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6
122.5°	339.8	340.2	341.0	341.7	342.5	343.4	343.0	341.6	340.4	339.0	337.6
125°	375.2	375.7	376.1	376.5	376.9	377.4	376.9	375.7	374.4	373.2	371.9
127.5°	409.7	410.2	410.7	411.2	411.7	412.2	411.6	410.0	408.5	406.8	405.2
130°	432.9	433.2	433.4	433.8	434.0	434.3	433.5	431.7	429.8	428.0	426.1
132.5°	456.1	456.7	456.7	456.6	456.5	456.5	455.6	454.2	452.7	451.2	449.7
135°	489.2	489.4	489.1	488.9	488.5	488.3	487.3	485.8	484.2	482.7	481.1
137.5°	521.5	521.6	521.2	520.9	520.5	520.1	519.3	518.1	516.8	515.5	514.2
140°	543.0	543.0	542.3	541.7	541.0	540.2	539.2	538.0	536.7	535.4	534.2
142.5°	562.6	562.5	562.0	561.5	561.0	560.6	559.6	558.4	557.2	555.9	554.6
145°	592.4	592.3	591.4	590.6	589.7	588.8	588.0	586.9	585.9	585.0	583.9
147.5°	618.4	618.1	617.5	616.9	616.4	615.8	614.9	613.7	612.5	611.3	610.2
150°	634.9	634.5	633.9	633.3	632.7	632.1	631.5	630.6	629.7	628.9	628.0
152.5°	651.3	650.8	650.1	649.5	648.8	648.1	647.3	646.4	645.6	644.7	643.9
155°	672.2	671.5	671.1	670.6	670.2	669.8	669.3	668.9	668.5	668.0	667.6
157.5°	691.4	690.4	690.2	689.9	689.7	689.4	689.1	688.8	688.5	688.3	687.9
160°	703.0	702.1	702.0	701.9	701.7	701.6	701.4	701.1	700.8	700.5	700.3
162.5°	713.3	712.4	712.2	712.1	712.0	711.8	711.7	711.6	711.6	711.5	711.4
165°	726.8	725.8	725.8	725.8	725.8	725.8	725.9	726.0	726.2	726.3	726.4
167.5°	737.9	736.9	736.9	736.9	737.0	737.0	737.3	737.7	738.1	738.6	739.0
170°	744.1	743.0	743.2	743.3	743.5	743.6	743.9	744.3	744.8	745.2	745.6
172.5°	748.6	747.6	747.8	748.0	748.0	748.2	748.5	748.9	749.3	749.8	750.2
175°	753.6	752.6	752.9	753.2	753.5	753.8	754.1	754.6	755.0	755.4	755.8
177.5°	756.2	755.5	755.8	756.0	756.2	756.5	756.7	757.1	757.4	757.8	758.1
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	6.9	8.3	8.6	9.7	9.7	10.3	10.9	11.3	11.7	11.4	11.0
90°	2.3	4.0	5.8	7.5	9.9	13.0	16.1	19.2	22.4	22.0	21.8
92.5°	12.7	13.9	15.2	16.4	17.4	18.1	18.9	19.5	20.3	20.4	20.4
95°	34.6	36.1	37.5	38.9	39.8	40.0	40.3	40.6	40.9	40.9	40.9
97.5°	61.9	63.2	64.4	65.7	66.6	67.2	67.7	68.2	68.7	68.7	68.7
100°	82.3	83.4	84.6	85.7	86.4	86.9	87.3	87.7	88.2	88.2	88.2
102.5°	103.5	104.4	105.3	106.2	106.9	107.5	108.1	108.6	109.1	109.3	109.3
105°	137.8	138.2	138.6	139.1	139.4	139.7	140.0	140.3	140.6	140.9	141.1
107.5°	173.0	173.7	174.3	174.9	175.2	175.2	175.2	175.2	175.2	175.3	175.4
110°	195.7	196.6	197.4	198.3	198.7	198.7	198.7	198.7	198.7	198.7	198.7



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	220.2	221.1	222.0	222.8	223.2	223.1	222.9	222.8	222.7	222.4	222.1
115°	256.4	257.3	258.1	259.0	259.2	259.0	258.6	258.4	258.1	258.0	257.9
117.5°	292.7	293.9	295.0	296.1	296.3	295.5	294.7	293.9	293.2	292.8	292.5
120°	316.8	317.9	319.0	320.1	320.1	319.0	317.9	316.8	315.6	315.6	315.6
122.5°	339.0	340.4	341.6	343.0	343.4	342.5	341.7	341.0	340.2	339.8	339.5
125°	373.2	374.4	375.7	376.9	377.4	376.9	376.5	376.1	375.7	375.2	374.8
127.5°	406.8	408.5	410.0	411.6	412.2	411.7	411.2	410.7	410.2	409.7	409.1
130°	428.0	429.8	431.7	433.5	434.3	434.0	433.8	433.4	433.2	432.9	432.7
132.5°	451.2	452.7	454.2	455.6	456.5	456.5	456.6	456.7	456.7	456.1	455.5
135°	482.7	484.2	485.8	487.3	488.3	488.5	488.9	489.1	489.4	489.2	489.1
137.5°	515.5	516.8	518.1	519.3	520.1	520.5	520.9	521.2	521.6	521.5	521.3
140°	535.4	536.7	538.0	539.2	540.2	541.0	541.7	542.3	543.0	543.0	543.0
142.5°	555.9	557.2	558.4	559.6	560.6	561.0	561.5	562.0	562.5	562.6	562.7
145°	585.0	585.9	586.9	588.0	588.8	589.7	590.6	591.4	592.3	592.4	592.5
147.5°	611.3	612.5	613.7	614.9	615.8	616.4	616.9	617.5	618.1	618.4	618.7
150°	628.9	629.7	630.6	631.5	632.1	632.7	633.3	633.9	634.5	634.9	635.2
152.5°	644.7	645.6	646.4	647.3	648.1	648.8	649.5	650.1	650.8	651.3	651.9
155°	668.0	668.5	668.9	669.3	669.8	670.2	670.6	671.1	671.5	672.2	672.9
157.5°	688.3	688.5	688.8	689.1	689.4	689.7	689.9	690.2	690.4	691.4	692.3
160°	700.5	700.8	701.1	701.4	701.6	701.7	701.9	702.0	702.1	703.0	703.9
162.5°	711.5	711.6	711.6	711.7	711.8	712.0	712.1	712.2	712.4	713.3	714.3
165°	726.3	726.2	726.0	725.9	725.8	725.8	725.8	725.8	725.8	726.8	727.8
167.5°	738.6	738.1	737.7	737.3	737.0	737.0	736.9	736.9	736.9	737.9	738.9
170°	745.2	744.8	744.3	743.9	743.6	743.5	743.3	743.2	743.0	744.1	745.0
172.5°	749.8	749.3	748.9	748.5	748.2	748.0	748.0	747.8	747.6	748.6	749.7
175°	755.4	755.0	754.6	754.1	753.8	753.5	753.2	752.9	752.6	753.6	754.6
177.5°	757.8	757.4	757.1	756.7	756.5	756.2	756.0	755.8	755.5	756.2	756.9
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1	757.1



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	11.3	11.2	10.9	10.9	11.2	11.0	11.0
90°	21.5	21.3	21.2	21.3	21.4	21.6	21.7
92.5°	20.5	20.6	20.6	20.6	20.7	20.7	20.7
95°	40.9	40.9	40.7	40.5	40.2	39.9	39.6
97.5°	68.7	68.7	68.7	68.7	68.7	68.6	68.6
100°	88.2	88.2	88.1	88.0	87.8	87.6	87.6
102.5°	109.4	109.6	109.6	109.4	109.3	109.2	109.0
105°	141.4	141.7	141.8	141.8	141.8	141.8	141.8
107.5°	175.6	175.6	175.4	174.7	174.1	173.4	172.8
110°	198.7	198.7	198.5	198.0	197.6	197.2	196.8



TEST NUMBER: P331502-935

CATALOG NUMBER: S122DIW-S485D710U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	221.7	221.4	221.0	220.8	220.4	220.1	219.8
115°	257.7	257.5	257.3	256.8	256.4	256.0	255.5
117.5°	292.1	291.8	291.4	290.9	290.5	290.1	289.6
120°	315.6	315.6	315.4	315.0	314.5	314.1	313.7
122.5°	339.1	338.8	338.5	338.1	337.9	337.5	337.3
125°	374.4	373.9	373.7	373.6	373.4	373.2	373.2
127.5°	408.6	408.1	407.7	407.2	406.7	406.3	405.9
130°	432.3	432.0	431.6	431.0	430.5	429.9	429.4
132.5°	454.8	454.2	453.7	453.2	452.7	452.3	451.9
135°	489.0	488.9	488.5	488.1	487.7	487.2	486.8
137.5°	521.2	521.2	520.8	520.2	519.7	519.1	518.5
140°	543.0	543.0	542.8	542.3	541.7	541.1	540.5
142.5°	562.8	562.9	562.7	562.1	561.5	561.0	560.4
145°	592.7	592.8	592.6	592.0	591.5	590.9	590.4
147.5°	619.0	619.3	619.2	618.7	618.1	617.6	617.1
150°	635.7	636.1	636.1	635.7	635.2	634.9	634.5
152.5°	652.4	653.0	653.0	652.4	651.9	651.3	650.8
155°	673.6	674.3	674.5	674.1	673.6	673.2	672.8
157.5°	693.3	694.2	694.4	693.7	693.0	692.3	691.6
160°	704.7	705.6	705.7	705.2	704.6	704.0	703.4
162.5°	715.3	716.3	716.4	715.7	715.1	714.4	713.7
165°	728.8	729.8	730.0	729.2	728.5	727.8	727.1
167.5°	739.9	740.9	741.0	740.3	739.5	738.8	738.0
170°	746.1	747.0	747.1	746.2	745.4	744.5	743.6
172.5°	750.6	751.7	751.7	750.9	750.0	749.2	748.3
175°	755.6	756.6	756.6	755.8	755.0	754.1	753.3
177.5°	757.6	758.3	758.3	757.6	756.9	756.2	755.5
180°	757.1	757.1	757.1	757.1	757.1	757.1	757.1

(END OF REPORT)