

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331482-930

Luminaire Tested: **S122DIW-S290D970U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331482-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S290D970U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3720.1 lumens
Efficiency: N/A
Efficacy: 97.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 38
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	34	34	34	26
1	92	88	85	81	82	79	76	73	61	59	57	45	44	43	30	30	29	22
2	84	77	71	66	75	69	64	60	54	50	47	40	38	36	27	25	24	19
3	77	68	61	55	68	61	55	50	47	43	40	35	32	30	24	22	21	16
4	70	60	52	46	62	54	47	42	42	37	34	31	28	26	21	19	18	14
5	64	53	45	40	57	48	41	36	37	33	29	28	25	22	19	17	16	12
6	59	47	40	34	52	43	36	31	34	29	25	25	22	19	17	15	14	10
7	54	43	35	30	48	38	32	27	30	26	22	23	19	17	16	14	12	9
8	50	39	31	26	45	35	28	24	28	23	19	21	17	15	14	12	11	8
9	47	35	28	23	42	32	25	21	25	21	17	19	16	13	13	11	10	7
10	44	32	25	20	39	29	23	19	23	19	15	18	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6218	6218	6218
5°	6242	6152	6190
10°	6205	6091	6120
15°	6128	6011	6006
20°	6019	5893	5887
25°	5911	5747	5747
30°	5774	5614	5565
35°	5643	5452	5373
40°	5480	5292	5191
45°	5318	5133	5005
50°	5144	4968	4793
55°	4963	4777	4597
60°	4760	4543	4379
65°	4542	4317	4118
70°	4263	4036	3843
75°	3880	3718	3624
80°	3440	3347	3171
85°	2816	2668	2408



TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	36.2	1.0
10°-20°	101.9	2.7
20°-30°	149.8	4.0
30°-40°	174.0	4.7
40°-50°	173.8	4.7
50°-60°	151.6	4.1
60°-70°	112.1	3.0
70°-80°	63.5	1.7
80°-90°	21.0	0.6
90°-100°	62.0	1.7
100°-110°	192.6	5.2
110°-120°	329.2	8.8
120°-130°	432.9	11.6
130°-140°	485.9	13.1
140°-150°	476.4	12.8
150°-160°	399.6	10.7
160°-170°	265.0	7.1
170°-180°	92.6	2.5
0°-30°	287.9	7.7
0°-40°	461.9	12.4
0°-60°	787.3	21.2
0°-90°	983.9	26.4
90°-120°	583.8	15.7
90°-150°	1979.0	53.2
90°-180°	2736.0	73.5
0°-180°	3720.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	385	385	385	385	385	
5°	385	384	380	382	382	37
15°	367	364	360	361	359	103
25°	332	329	323	323	323	153
35°	286	282	277	274	273	179
45°	233	230	225	221	219	180
55°	176	174	170	165	163	158
65°	119	117	113	110	108	118
75°	62	61	60	58	58	66
85°	15	15	14	13	13	17
90°	1	11	29	27	28	3
95°	43	51	53	53	51	49
105°	178	180	182	183	183	188
115°	330	335	334	333	330	327
125°	481	488	486	483	482	429
135°	622	630	632	632	629	480
145°	755	760	766	766	763	471
155°	863	865	868	872	870	397
165°	939	938	938	943	940	265
175°	977	974	973	978	974	93
180°	978	978	978	978	978	



TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	386.9	386.6	386.3	386.0	385.6	385.1	384.4	383.7	382.9	382.2	382.9
5°	385.1	384.8	384.5	384.2	383.8	383.3	382.4	381.5	380.5	379.6	380.3
7.5°	381.8	381.2	380.7	380.3	379.8	379.0	378.1	377.2	376.3	375.4	376.0
10°	378.5	378.0	377.4	376.8	376.2	375.4	374.5	373.5	372.5	371.5	372.1
12.5°	374.1	373.6	373.1	372.5	372.0	371.3	370.3	369.3	368.4	367.4	367.8
15°	366.6	366.2	365.7	365.2	364.7	363.9	362.8	361.7	360.7	359.6	360.0
17.5°	357.2	356.7	356.2	355.7	355.2	354.4	353.4	352.2	351.1	350.1	350.4
20°	350.3	349.8	349.4	348.9	348.4	347.6	346.4	345.3	344.1	343.0	343.2
22.5°	343.6	342.8	342.2	341.4	340.8	339.9	338.8	337.7	336.6	335.6	335.6
25°	331.8	331.2	330.5	329.9	329.2	328.2	326.8	325.4	324.0	322.6	322.8
27.5°	318.5	318.0	317.3	316.7	316.2	315.3	314.2	313.1	312.0	310.9	310.6
30°	309.7	309.0	308.3	307.7	307.0	306.1	304.8	303.6	302.3	301.1	300.8
32.5°	300.1	299.6	299.1	298.6	298.1	297.1	295.8	294.6	293.3	292.0	291.5
35°	286.3	285.4	284.6	283.8	283.0	281.9	280.6	279.3	278.0	276.6	276.1
37.5°	270.7	269.9	269.2	268.5	267.7	266.8	265.5	264.2	262.8	261.5	260.9
40°	260.0	259.3	258.7	258.0	257.4	256.4	255.0	253.7	252.4	251.1	250.4
42.5°	249.6	249.0	248.3	247.7	247.0	246.0	244.7	243.4	242.1	240.8	239.9
45°	232.9	232.4	231.8	231.2	230.6	229.8	228.5	227.3	226.1	224.8	223.9
47.5°	216.4	215.8	215.3	214.7	214.2	213.3	212.0	210.8	209.5	208.1	207.2
50°	204.8	204.4	204.0	203.6	203.2	202.4	201.2	200.1	198.9	197.8	196.7
52.5°	193.6	193.0	192.5	191.9	191.4	190.5	189.5	188.4	187.3	186.2	185.2
55°	176.3	175.8	175.3	174.8	174.3	173.6	172.6	171.6	170.6	169.7	168.6
57.5°	159.0	158.6	158.2	157.8	157.4	156.6	155.6	154.5	153.4	152.3	151.3
60°	147.4	147.1	146.8	146.4	146.1	145.4	144.2	143.1	141.9	140.7	139.8
62.5°	136.2	135.6	135.1	134.6	134.0	133.3	132.4	131.6	130.7	129.8	128.9
65°	118.9	118.4	117.9	117.4	116.9	116.3	115.4	114.6	113.8	113.0	112.2
67.5°	101.3	100.9	100.5	100.1	99.8	99.2	98.4	97.7	96.9	96.2	95.6
70°	90.3	90.0	89.7	89.4	89.0	88.5	87.8	87.1	86.3	85.5	85.0
72.5°	79.1	78.8	78.4	78.1	77.8	77.4	76.9	76.5	76.0	75.5	74.9
75°	62.2	62.0	61.9	61.7	61.6	61.3	60.9	60.4	60.0	59.6	59.1
77.5°	47.1	46.8	46.6	46.3	46.0	45.7	45.6	45.4	45.2	45.1	44.8
80°	37.0	36.9	36.9	36.8	36.7	36.6	36.4	36.3	36.1	36.0	35.7
82.5°	27.6	27.6	27.6	27.5	27.5	27.4	27.3	27.2	27.1	27.1	26.7
85°	15.2	15.1	15.0	14.9	14.8	14.8	14.7	14.6	14.5	14.4	14.2
87.5°	5.5	5.8	6.1	6.4	6.8	7.3	7.9	8.6	9.2	9.9	9.6
90°	0.8	3.0	5.2	7.4	9.6	12.7	16.8	20.8	24.9	28.9	28.5
92.5°	14.7	16.3	17.9	19.6	21.2	22.4	23.4	24.4	25.3	26.3	26.3
95°	43.0	44.8	46.6	48.4	50.3	51.4	51.8	52.1	52.5	52.8	52.8
97.5°	78.4	80.1	81.7	83.3	84.9	86.1	86.7	87.5	88.1	88.9	88.9
100°	104.8	106.3	107.8	109.3	110.7	111.8	112.3	112.8	113.4	114.0	114.0
102.5°	132.6	133.8	134.9	136.2	137.3	138.3	138.9	139.7	140.3	141.0	141.2
105°	177.6	178.1	178.6	179.2	179.8	180.2	180.6	180.9	181.3	181.6	182.1
107.5°	222.8	223.6	224.4	225.2	226.0	226.4	226.4	226.4	226.4	226.4	226.6
110°	251.8	253.0	254.0	255.2	256.2	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	283.6	284.7	285.8	286.9	288.0	288.5	288.3	288.1	288.0	287.9	287.4
115°	330.3	331.4	332.5	333.6	334.7	335.1	334.7	334.4	333.9	333.6	333.5
117.5°	376.9	378.4	379.8	381.3	382.8	382.9	382.0	380.9	379.9	378.9	378.5
120°	408.0	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	408.0
122.5°	436.3	438.1	439.9	441.6	443.4	443.8	442.7	441.7	440.7	439.6	439.2
125°	480.6	482.2	483.9	485.6	487.2	487.8	487.2	486.7	486.1	485.6	485.0
127.5°	523.7	525.8	527.9	530.0	532.1	532.8	532.1	531.5	530.8	530.2	529.5
130°	550.8	553.2	555.5	558.0	560.4	561.3	561.0	560.6	560.3	559.9	559.5
132.5°	581.1	583.1	585.1	587.0	589.0	590.0	590.0	590.1	590.2	590.3	589.5
135°	621.8	623.9	625.8	627.9	629.9	631.0	631.4	631.8	632.2	632.5	632.3
137.5°	664.6	666.3	667.9	669.5	671.2	672.3	672.7	673.2	673.7	674.2	674.0
140°	690.3	692.0	693.7	695.3	696.9	698.2	699.2	700.1	701.0	701.9	701.9
142.5°	716.8	718.4	720.1	721.7	723.4	724.6	725.1	725.8	726.4	727.0	727.2
145°	754.7	756.0	757.3	758.6	759.9	761.1	762.2	763.3	764.4	765.5	765.6
147.5°	788.6	790.2	791.7	793.2	794.8	795.9	796.6	797.4	798.1	798.8	799.2
150°	811.7	812.9	813.9	815.1	816.1	817.1	817.8	818.6	819.3	820.0	820.5
152.5°	832.3	833.3	834.5	835.5	836.7	837.6	838.5	839.4	840.2	841.1	841.8
155°	862.9	863.5	864.1	864.6	865.1	865.7	866.3	866.8	867.3	867.9	868.8
157.5°	889.2	889.6	889.9	890.3	890.6	891.0	891.4	891.7	892.0	892.3	893.6
160°	905.1	905.4	905.8	906.1	906.5	906.8	907.0	907.2	907.3	907.5	908.7
162.5°	919.6	919.7	919.7	919.8	919.9	920.0	920.2	920.4	920.6	920.7	922.0
165°	938.9	938.7	938.6	938.3	938.2	938.1	938.1	938.1	938.1	938.1	939.4
167.5°	955.1	954.6	954.0	953.4	952.9	952.6	952.6	952.5	952.5	952.4	953.7
170°	963.7	963.1	962.6	962.1	961.5	961.2	960.9	960.7	960.6	960.4	961.6
172.5°	969.6	969.1	968.5	968.0	967.4	967.0	966.9	966.7	966.5	966.3	967.6
175°	976.9	976.3	975.8	975.3	974.7	974.2	973.9	973.5	973.1	972.7	974.0
177.5°	979.9	979.4	979.0	978.5	978.1	977.7	977.5	977.1	976.9	976.6	977.5
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	385.1	385.1	385.1	385.1	385.1	385.1	385.1	385.1
2.5°	383.5	384.2	384.8	385.1	385.0	384.8	384.7	384.6
5°	381.0	381.6	382.3	382.5	382.4	382.2	382.0	381.9
7.5°	376.7	377.3	378.0	378.2	378.1	377.8	377.6	377.5
10°	372.8	373.5	374.1	374.3	374.1	373.8	373.6	373.3
12.5°	368.3	368.7	369.2	369.3	369.2	368.9	368.8	368.6
15°	360.3	360.6	360.9	360.9	360.5	360.1	359.7	359.3
17.5°	350.8	351.2	351.6	351.6	351.1	350.8	350.4	350.0
20°	343.5	343.7	344.0	343.9	343.6	343.2	342.9	342.6
22.5°	335.7	335.7	335.7	335.7	335.5	335.3	335.1	334.9
25°	322.9	323.1	323.3	323.3	323.1	322.9	322.8	322.6
27.5°	310.4	310.1	309.9	309.6	309.2	308.8	308.4	308.0
30°	300.6	300.4	300.1	299.9	299.5	299.2	298.9	298.5
32.5°	291.1	290.6	290.2	289.8	289.4	289.1	288.8	288.5
35°	275.7	275.2	274.7	274.3	273.9	273.5	273.0	272.6
37.5°	260.2	259.7	259.0	258.5	258.1	257.7	257.4	257.0
40°	249.6	248.9	248.2	247.6	247.3	247.0	246.6	246.3
42.5°	239.1	238.3	237.5	236.8	236.4	235.9	235.5	235.1
45°	223.0	222.1	221.2	220.5	220.2	219.9	219.6	219.2
47.5°	206.3	205.3	204.3	203.6	203.2	202.7	202.2	201.7
50°	195.5	194.3	193.1	192.4	192.0	191.6	191.2	190.8
52.5°	184.3	183.4	182.4	181.6	181.1	180.6	180.0	179.4
55°	167.6	166.6	165.7	165.0	164.6	164.1	163.7	163.3
57.5°	150.3	149.4	148.4	147.7	147.5	147.2	146.8	146.5
60°	138.9	138.0	137.1	136.6	136.3	136.1	135.8	135.6
62.5°	128.1	127.3	126.5	125.9	125.6	125.2	124.9	124.6
65°	111.5	110.7	110.0	109.4	109.0	108.6	108.2	107.8
67.5°	95.1	94.5	93.9	93.4	93.1	92.8	92.5	92.1
70°	84.4	83.8	83.2	82.8	82.5	82.1	81.8	81.4
72.5°	74.4	73.8	73.2	72.7	72.5	72.2	72.0	71.7
75°	58.6	58.1	57.6	57.5	57.6	57.8	58.0	58.1
77.5°	44.6	44.4	44.1	43.9	43.6	43.5	43.2	43.0
80°	35.5	35.2	35.0	34.7	34.6	34.4	34.2	34.1
82.5°	26.4	26.1	25.8	25.6	25.6	25.5	25.5	25.5
85°	13.9	13.7	13.5	13.3	13.2	13.1	13.0	13.0
87.5°	9.4	9.1	8.8	8.7	8.6	8.6	8.6	8.6
90°	28.1	27.8	27.4	27.3	27.6	27.7	27.9	28.0
92.5°	26.4	26.5	26.6	26.6	26.7	26.7	26.7	26.7
95°	52.8	52.8	52.8	52.7	52.3	51.9	51.5	51.2
97.5°	88.9	88.9	88.9	88.9	88.8	88.8	88.7	88.7
100°	114.0	114.0	114.0	113.9	113.7	113.5	113.3	113.2
102.5°	141.4	141.5	141.6	141.6	141.5	141.2	141.0	140.9
105°	182.4	182.8	183.1	183.4	183.4	183.4	183.4	183.4
107.5°	226.7	226.9	227.0	226.7	225.8	224.9	224.1	223.3
110°	256.8	256.8	256.8	256.6	256.0	255.4	254.9	254.4



TEST NUMBER: P331482-930

CATALOG NUMBER: S122DIW-S290D970U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	287.0	286.6	286.1	285.7	285.3	284.9	284.5	284.1
115°	333.2	333.0	332.9	332.5	332.0	331.4	330.8	330.3
117.5°	378.0	377.6	377.1	376.6	376.1	375.5	375.0	374.4
120°	408.0	408.0	408.0	407.6	407.1	406.6	406.0	405.4
122.5°	438.8	438.3	437.9	437.5	437.1	436.7	436.3	435.9
125°	484.5	483.9	483.4	483.0	482.8	482.7	482.4	482.2
127.5°	528.8	528.2	527.5	526.8	526.3	525.7	525.1	524.6
130°	559.1	558.8	558.4	557.8	557.1	556.4	555.6	554.9
132.5°	588.6	587.8	587.0	586.4	585.8	585.1	584.6	584.0
135°	632.2	632.0	631.8	631.4	630.9	630.3	629.8	629.2
137.5°	673.8	673.8	673.6	673.1	672.4	671.6	670.9	670.2
140°	701.9	701.9	701.9	701.6	700.8	700.1	699.4	698.6
142.5°	727.3	727.5	727.6	727.3	726.6	725.9	725.1	724.4
145°	765.9	766.1	766.2	766.0	765.2	764.5	763.8	763.0
147.5°	799.6	800.1	800.5	800.3	799.6	798.9	798.3	797.5
150°	821.1	821.7	822.2	822.2	821.7	821.1	820.5	820.0
152.5°	842.5	843.3	843.9	843.9	843.3	842.5	841.8	841.1
155°	869.8	870.7	871.6	871.7	871.2	870.7	870.1	869.5
157.5°	894.9	896.1	897.3	897.5	896.7	895.8	894.9	894.0
160°	909.7	910.9	911.9	912.2	911.4	910.7	910.0	909.2
162.5°	923.2	924.5	925.8	925.9	925.0	924.1	923.2	922.4
165°	940.7	941.9	943.2	943.4	942.5	941.6	940.7	939.7
167.5°	955.0	956.3	957.6	957.7	956.8	955.9	954.9	954.0
170°	963.0	964.3	965.6	965.6	964.5	963.4	962.3	961.2
172.5°	968.9	970.2	971.4	971.6	970.5	969.4	968.2	967.2
175°	975.3	976.6	977.9	978.0	976.9	975.8	974.7	973.6
177.5°	978.4	979.2	980.1	980.1	979.2	978.4	977.5	976.6
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5

(END OF REPORT)