

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331508-935

Luminaire Tested: **S122DIW-S485D970U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331508-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D970U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4739.6 lumens
Efficiency: N/A
Efficacy: 104.9 lumens/watt
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 45.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	105	105	105	105	95	95	95	95	77	77	77	61	61	61	46	46	46	39
1	96	92	88	85	87	83	80	77	68	66	64	54	53	51	41	40	40	34
2	87	80	75	70	79	73	68	64	60	57	54	48	46	43	37	35	34	29
3	80	71	64	58	72	65	59	54	53	49	45	43	40	37	33	31	29	25
4	73	63	55	50	66	58	51	46	48	43	39	38	35	32	30	27	26	22
5	67	56	48	43	61	52	45	40	43	38	34	35	31	28	27	24	22	19
6	62	51	43	37	56	46	40	35	39	33	30	31	28	25	24	22	20	17
7	57	46	38	33	52	42	35	30	35	30	26	29	25	22	22	20	18	15
8	53	41	34	29	49	38	32	27	32	27	23	26	22	20	21	18	16	14
9	50	38	31	26	45	35	29	24	29	24	21	24	20	18	19	17	15	12
10	46	35	28	23	42	32	26	22	27	22	19	22	19	16	18	15	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	13508	13508	13508	13508
5°	15144	13598	12049	13598
10°	17354	13485	10427	13485
15°	19199	13237	9212	13237
20°	18907	12972	8399	12972
25°	17047	12618	7883	12618
30°	14087	12055	7506	12055
35°	10267	11466	7238	11466
40°	8201	10768	7088	10768
45°	7165	9965	6887	9965
50°	6737	9183	6752	9183
55°	6210	8391	6570	8391
60°	5690	7550	6290	7550
65°	5184	6793	6021	6793
70°	4707	6057	5618	6057
75°	4173	5234	4972	5234
80°	3589	4342	3998	4342
85°	3223	3223	2371	3223



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	79.7	1.7
10°-20°	231.6	4.9
20°-30°	336.2	7.1
30°-40°	354.8	7.5
40°-50°	314.1	6.6
50°-60°	250.7	5.3
60°-70°	170.4	3.6
70°-80°	87.4	1.8
80°-90°	25.2	0.5
90°-100°	65.5	1.4
100°-110°	203.4	4.3
110°-120°	347.6	7.3
120°-130°	457.2	9.6
130°-140°	513.1	10.8
140°-150°	503.1	10.6
150°-160°	422.0	8.9
160°-170°	279.9	5.9
170°-180°	97.8	2.1
0°-30°	647.5	13.7
0°-40°	1002.3	21.1
0°-60°	1567.1	33.1
0°-90°	1850.0	39.0
90°-120°	616.5	13.0
90°-150°	2089.9	44.1
90°-180°	2890.0	61.0
0°-180°	4739.6	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	837	837	837	837	837	
5°	934	839	743	839	934	93
15°	1149	792	551	792	1149	317
25°	957	708	442	708	957	432
35°	521	582	367	582	521	339
45°	314	436	302	436	314	247
55°	221	298	233	298	221	198
65°	136	178	158	178	136	135
75°	67	84	80	84	67	71
85°	17	17	13	17	17	20
90°	30	1	30	1	30	14
95°	54	45	54	45	54	60
105°	194	188	194	188	194	204
115°	349	349	349	349	349	344
125°	509	508	509	508	509	454
135°	664	657	664	657	664	511
145°	806	797	806	797	806	503
155°	918	911	918	911	918	423
165°	992	992	992	992	992	280
175°	1028	1032	1028	1032	1028	98
180°	1033	1033	1033	1033	1033	



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	875.3	875.6	876.0	871.9	871.4	871.4	867.8	864.7	861.1	856.2	856.7
5°	934.4	938.0	939.3	935.4	929.6	928.9	923.5	914.5	906.1	899.4	894.6
7.5°	1005.0	1006.4	1003.3	998.2	993.9	986.2	976.0	966.0	952.1	939.3	929.8
10°	1058.5	1060.5	1055.0	1047.6	1041.5	1032.5	1017.7	1002.5	984.3	966.6	952.4
12.5°	1099.2	1104.0	1096.9	1096.0	1085.5	1073.2	1055.5	1047.8	1022.1	997.5	982.2
15°	1148.6	1148.2	1148.9	1142.8	1135.1	1133.2	1114.5	1094.2	1057.9	1043.4	1018.3
17.5°	1134.3	1139.2	1141.4	1141.3	1141.2	1140.0	1133.9	1121.2	1102.9	1079.5	1050.6
20°	1100.4	1106.7	1107.8	1115.2	1119.3	1124.8	1127.0	1123.5	1112.2	1092.6	1067.6
22.5°	1047.8	1049.6	1052.7	1064.2	1073.2	1086.9	1094.1	1106.0	1101.6	1092.1	1071.2
25°	956.9	953.7	964.9	970.8	991.6	1013.5	1029.2	1046.6	1062.0	1071.4	1065.3
27.5°	847.7	842.9	859.8	875.1	892.1	915.8	940.3	969.3	993.4	1023.6	1034.0
30°	755.6	758.5	774.6	791.0	816.7	850.2	877.8	909.6	944.1	977.8	1001.3
32.5°	656.3	667.4	677.6	702.7	725.4	762.7	803.2	843.0	886.0	924.3	960.6
35°	520.9	533.7	547.9	566.3	598.1	635.1	674.6	728.3	786.9	839.2	882.4
37.5°	438.4	436.4	444.5	457.8	483.5	513.4	558.9	612.0	680.9	742.4	803.2
40°	389.1	387.8	393.6	405.8	425.4	447.3	487.2	533.7	597.8	673.0	745.4
42.5°	355.1	355.9	359.1	367.7	381.2	399.2	429.0	468.7	527.3	598.1	675.9
45°	313.8	316.1	319.6	323.8	331.5	346.3	363.0	391.3	437.6	496.8	573.3
47.5°	284.1	284.2	287.7	291.4	296.0	304.4	318.1	335.8	368.4	416.6	482.4
50°	268.2	265.9	268.5	271.4	276.2	282.0	291.0	307.7	329.6	368.5	423.4
52.5°	248.7	248.7	251.0	252.1	256.4	262.2	270.4	282.0	301.8	332.3	377.5
55°	220.6	222.2	223.5	225.4	229.3	233.4	239.9	247.6	263.0	285.9	319.3
57.5°	194.2	194.8	196.0	199.7	202.2	206.0	212.1	219.1	229.1	246.1	271.2
60°	176.2	176.2	178.7	180.4	183.6	187.4	192.3	199.1	208.0	221.9	242.1
62.5°	159.7	159.5	160.5	163.2	165.6	169.2	174.0	179.8	188.2	200.5	217.1
65°	135.7	135.1	137.0	137.6	140.2	143.7	147.6	153.7	160.5	169.4	184.3
67.5°	112.5	113.3	114.3	115.5	117.0	120.7	123.3	127.6	133.3	140.8	150.8
70°	99.7	99.7	99.7	100.7	102.5	104.5	107.1	110.6	116.1	122.5	131.5
72.5°	85.2	86.3	87.3	86.8	89.2	90.3	93.4	95.4	100.7	104.8	112.7
75°	66.9	66.9	66.9	68.4	69.5	70.4	72.3	74.3	76.9	82.0	86.2
77.5°	49.9	49.8	50.1	50.5	51.5	52.7	53.2	55.0	57.3	59.8	63.3
80°	38.6	39.3	39.5	40.2	40.2	40.8	41.2	43.4	45.0	46.7	48.9
82.5°	29.9	30.0	30.0	30.1	30.4	30.8	31.6	32.4	32.9	34.3	36.0
85°	17.4	17.0	17.0	17.7	17.4	17.4	18.0	18.7	18.7	18.9	20.0
87.5°	12.7	12.6	12.8	12.5	12.5	12.7	12.8	12.7	13.0	13.3	12.7
90°	29.6	29.4	29.3	29.1	28.8	28.9	29.4	29.7	30.1	30.5	26.3
92.5°	28.2	28.2	28.2	28.2	28.1	28.1	28.0	27.9	27.8	27.7	26.7
95°	54.1	54.4	54.8	55.2	55.6	55.8	55.8	55.8	55.8	55.8	55.4
97.5°	93.7	93.7	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.8	93.1
100°	119.5	119.7	119.9	120.0	120.3	120.4	120.4	120.4	120.4	120.4	119.8
102.5°	148.8	149.0	149.1	149.4	149.6	149.6	149.4	149.3	149.1	149.0	148.2
105°	193.6	193.6	193.6	193.6	193.6	193.4	193.0	192.6	192.3	191.8	191.5
107.5°	235.8	236.7	237.5	238.5	239.4	239.7	239.6	239.4	239.3	239.1	239.1
110°	268.6	269.1	269.8	270.4	271.0	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	300.0	300.4	300.8	301.3	301.7	302.1	302.6	303.1	303.5	304.0	304.2
115°	348.8	349.4	350.0	350.6	351.1	351.5	351.7	351.9	352.1	352.3	352.7
117.5°	395.4	396.0	396.6	397.2	397.7	398.2	398.7	399.2	399.7	400.1	401.2
120°	428.2	428.8	429.4	429.9	430.5	430.8	430.8	430.8	430.8	430.8	432.4
122.5°	460.3	460.7	461.2	461.6	462.0	462.4	462.9	463.4	463.8	464.3	465.4
125°	509.3	509.5	509.7	509.9	510.1	510.5	511.0	511.6	512.2	512.8	513.3
127.5°	554.0	554.6	555.2	555.8	556.4	557.1	557.8	558.4	559.1	559.9	560.6
130°	586.0	586.8	587.5	588.3	589.1	589.7	590.1	590.5	590.9	591.2	591.7
132.5°	616.7	617.3	617.9	618.6	619.2	619.9	620.8	621.6	622.5	623.4	623.3
135°	664.5	665.1	665.6	666.2	666.8	667.2	667.4	667.6	667.8	668.0	667.6
137.5°	707.7	708.5	709.3	710.1	710.8	711.4	711.5	711.6	711.8	712.0	711.4
140°	737.8	738.6	739.3	740.1	740.9	741.2	741.2	741.2	741.2	741.2	740.3
142.5°	765.0	765.8	766.5	767.3	768.1	768.4	768.3	768.1	767.9	767.8	767.2
145°	805.8	806.6	807.4	808.1	808.9	809.2	809.0	808.8	808.6	808.4	807.3
147.5°	842.2	843.0	843.7	844.5	845.2	845.3	844.9	844.5	844.0	843.6	842.8
150°	866.0	866.5	867.1	867.7	868.3	868.3	867.7	867.1	866.5	866.0	865.2
152.5°	888.3	889.0	889.8	890.5	891.2	891.2	890.5	889.8	889.0	888.3	887.3
155°	918.3	918.9	919.5	920.1	920.6	920.4	919.5	918.5	917.5	916.5	915.9
157.5°	944.1	945.0	946.0	946.9	947.8	947.6	946.3	945.0	943.7	942.4	942.0
160°	960.2	961.0	961.7	962.5	963.3	963.0	961.9	960.7	959.6	958.4	958.2
162.5°	974.1	975.0	975.9	976.9	977.8	977.7	976.3	975.0	973.7	972.3	972.2
165°	992.4	993.4	994.4	995.3	996.3	996.1	994.7	993.4	992.0	990.7	990.7
167.5°	1007.5	1008.4	1009.4	1010.5	1011.4	1011.2	1010.0	1008.6	1007.2	1005.8	1005.9
170°	1015.1	1016.2	1017.4	1018.6	1019.8	1019.7	1018.3	1016.9	1015.5	1014.3	1014.4
172.5°	1021.4	1022.5	1023.7	1024.8	1026.1	1025.9	1024.6	1023.2	1021.8	1020.5	1020.7
175°	1028.2	1029.3	1030.5	1031.7	1032.9	1032.7	1031.4	1030.0	1028.6	1027.3	1027.7
177.5°	1031.3	1032.3	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3	1031.7
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	858.5	856.4	855.1	850.6	846.4	842.3	841.0	841.5	835.9	830.5	828.2
5°	892.0	885.5	879.4	870.7	860.5	849.2	843.4	839.0	827.7	815.5	808.4
7.5°	922.0	912.7	901.0	884.7	869.7	852.0	840.7	830.8	814.2	797.0	786.5
10°	940.2	927.6	912.6	892.6	874.3	852.7	837.7	822.5	803.2	782.6	769.8
12.5°	955.9	939.0	924.1	898.5	876.8	849.9	832.0	810.7	790.4	765.9	753.3
15°	993.2	962.1	933.8	904.8	878.1	840.5	820.6	791.9	765.3	735.0	720.6
17.5°	1022.1	987.1	942.5	905.8	874.6	832.9	803.7	769.4	737.8	703.3	683.6
20°	1038.6	998.4	950.5	906.8	869.4	821.9	790.1	755.0	718.0	679.1	657.9
22.5°	1048.4	1006.2	958.7	902.9	859.2	812.9	772.8	734.4	696.9	655.0	632.7
25°	1051.5	1012.9	962.7	899.7	846.3	793.9	745.6	708.3	663.1	623.8	591.3
27.5°	1036.1	1008.5	960.3	893.6	831.5	770.2	716.4	674.2	626.3	583.8	551.0
30°	1017.4	1001.3	954.3	887.4	819.6	753.7	694.6	646.6	599.1	555.9	522.5
32.5°	988.3	984.8	943.6	878.7	807.0	732.9	671.7	623.2	570.5	528.1	496.3
35°	931.2	946.7	920.6	859.2	783.3	703.3	637.0	581.7	527.0	486.5	456.6
37.5°	854.7	893.0	886.2	830.5	751.2	671.0	597.8	540.0	487.9	447.0	417.7
40°	801.9	850.8	857.9	808.7	728.7	646.0	568.5	510.9	460.1	422.8	393.2
42.5°	745.4	802.5	821.9	782.5	704.0	619.7	542.3	482.7	432.4	396.1	369.9
45°	650.5	726.1	761.1	738.6	662.7	576.5	496.8	436.4	390.7	356.6	336.3
47.5°	561.8	644.4	691.6	683.5	616.8	531.5	452.7	394.7	350.3	323.0	304.9
50°	499.0	583.9	640.8	643.4	583.9	499.4	420.3	365.6	324.8	299.4	284.6
52.5°	444.5	525.6	587.6	601.2	547.2	465.9	391.2	336.8	300.8	277.5	264.2
55°	373.3	441.8	510.7	535.7	492.3	415.1	345.9	298.1	264.3	248.2	236.7
57.5°	310.4	367.5	431.0	458.7	432.0	365.9	301.1	259.5	232.1	218.0	209.1
60°	277.2	322.2	378.8	411.9	388.7	329.9	273.3	233.8	211.3	198.7	190.4
62.5°	246.3	286.2	334.0	364.3	351.7	296.2	245.6	210.6	191.2	179.4	173.4
65°	203.2	234.7	271.7	299.7	291.4	249.2	207.8	177.8	162.4	153.1	148.3
67.5°	167.3	190.1	215.8	240.2	233.5	203.6	170.4	147.1	135.5	127.5	124.7
70°	144.7	162.0	184.9	204.5	199.1	174.6	148.3	128.3	118.3	111.6	108.7
72.5°	123.1	137.3	154.8	170.8	167.1	146.8	124.8	109.8	102.1	95.9	93.5
75°	92.9	103.8	114.5	125.1	124.2	108.4	95.5	83.9	77.8	73.0	72.1
77.5°	68.6	74.7	82.0	88.3	86.5	77.5	67.4	60.8	56.3	53.0	52.5
80°	52.4	56.0	61.1	65.6	63.4	59.5	51.5	46.7	43.4	40.2	38.9
82.5°	38.0	41.6	44.6	47.1	45.4	41.8	36.8	33.5	31.6	29.4	28.8
85°	20.0	21.9	23.2	23.8	23.2	20.9	18.7	17.4	15.8	14.8	14.5
87.5°	12.1	11.3	10.4	10.2	9.0	8.5	7.1	5.9	6.0	6.3	6.2
90°	22.0	17.7	13.4	10.2	7.8	5.5	3.2	0.9	3.2	5.5	7.8
92.5°	25.7	24.7	23.7	22.4	20.7	18.9	17.2	15.5	17.2	18.9	20.7
95°	55.0	54.7	54.2	53.1	51.1	49.2	47.3	45.4	47.3	49.2	51.1
97.5°	92.4	91.6	90.9	89.6	88.0	86.3	84.6	82.8	84.6	86.3	88.0
100°	119.2	118.6	118.0	116.9	115.4	113.8	112.3	110.7	112.3	113.8	115.4
102.5°	147.5	146.7	146.0	145.0	143.8	142.5	141.3	140.1	141.3	142.5	143.8
105°	191.1	190.7	190.3	189.9	189.2	188.6	188.0	187.5	188.0	188.6	189.2
107.5°	239.1	239.1	239.1	238.7	237.8	236.9	236.2	235.3	236.2	236.9	237.8
110°	271.2	271.2	271.2	270.6	269.5	268.3	267.2	266.0	267.2	268.3	269.5



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	304.3	304.4	304.6	304.1	303.0	301.8	300.7	299.5	300.7	301.8	303.0
115°	353.1	353.4	353.9	353.4	352.3	351.1	350.0	348.8	350.0	351.1	352.3
117.5°	402.3	403.4	404.4	404.2	402.7	401.1	399.6	398.0	399.6	401.1	402.7
120°	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	432.4	433.9	435.5
122.5°	466.5	467.5	468.6	468.2	466.4	464.5	462.7	460.8	462.7	464.5	466.4
125°	513.9	514.5	515.1	514.5	512.8	511.0	509.3	507.6	509.3	511.0	512.8
127.5°	561.3	562.0	562.7	561.9	559.7	557.5	555.3	553.1	555.3	557.5	559.7
130°	592.0	592.5	592.8	591.8	589.3	586.7	584.2	581.7	584.2	586.7	589.3
132.5°	623.2	623.1	623.0	622.0	619.9	617.9	615.8	613.7	615.8	617.9	619.9
135°	667.2	666.8	666.4	665.2	663.1	660.9	658.8	656.7	658.8	660.9	663.1
137.5°	710.9	710.4	710.0	708.8	707.1	705.3	703.6	701.8	703.6	705.3	707.1
140°	739.3	738.4	737.4	736.0	734.3	732.5	730.8	729.0	730.8	732.5	734.3
142.5°	766.5	765.8	765.2	764.0	762.2	760.4	758.7	757.0	758.7	760.4	762.2
145°	806.1	804.9	803.7	802.5	801.2	799.8	798.4	797.0	798.4	799.8	801.2
147.5°	842.1	841.3	840.5	839.3	837.7	836.1	834.5	832.8	834.5	836.1	837.7
150°	864.4	863.7	862.9	861.9	860.7	859.5	858.4	857.2	858.4	859.5	860.7
152.5°	886.4	885.5	884.6	883.6	882.4	881.2	880.0	878.9	880.0	881.2	882.4
155°	915.4	914.8	914.2	913.6	913.1	912.5	911.9	911.3	911.9	912.5	913.1
157.5°	941.7	941.3	941.0	940.6	940.2	939.8	939.4	939.0	939.4	939.8	940.2
160°	958.0	957.9	957.6	957.3	956.9	956.6	956.1	955.8	956.1	956.6	956.9
162.5°	972.0	971.8	971.6	971.5	971.4	971.3	971.2	971.1	971.2	971.3	971.4
165°	990.7	990.7	990.7	990.8	990.9	991.2	991.4	991.5	991.4	991.2	990.9
167.5°	1005.9	1006.0	1006.0	1006.3	1006.9	1007.5	1008.1	1008.7	1008.1	1007.5	1006.9
170°	1014.6	1014.8	1015.0	1015.4	1016.0	1016.6	1017.1	1017.7	1017.1	1016.6	1016.0
172.5°	1020.9	1021.1	1021.2	1021.7	1022.3	1022.8	1023.4	1024.0	1023.4	1022.8	1022.3
175°	1028.0	1028.5	1028.8	1029.3	1029.9	1030.5	1031.0	1031.7	1031.0	1030.5	1029.9
177.5°	1031.9	1032.3	1032.5	1032.9	1033.4	1033.9	1034.3	1034.8	1034.3	1033.9	1033.4
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	825.6	824.1	818.6	815.8	811.2	806.8	804.0	805.3	806.3	805.8	805.0
5°	801.9	795.8	786.5	778.4	772.7	762.1	757.6	755.4	753.4	751.1	748.9
7.5°	773.8	764.1	750.8	739.3	728.5	715.3	707.8	703.3	698.6	693.5	689.1
10°	753.7	740.2	726.1	710.0	697.2	685.2	674.6	667.5	661.1	655.0	650.5
12.5°	732.6	717.0	699.6	677.6	663.4	646.4	644.8	632.3	622.2	618.5	613.2
15°	699.0	677.2	655.0	629.0	617.7	602.3	592.6	583.0	574.3	568.2	566.5
17.5°	660.9	632.6	610.5	591.9	573.4	557.6	548.7	541.0	533.8	525.6	524.6
20°	631.8	607.4	583.3	566.9	547.9	531.8	520.9	513.2	507.0	502.2	498.1
22.5°	604.3	577.6	555.5	537.5	518.8	505.8	497.2	489.8	484.7	479.4	475.4
25°	560.2	539.2	515.1	494.9	479.4	471.1	464.0	457.5	454.3	450.8	446.3
27.5°	521.5	498.3	475.7	460.0	446.4	439.0	434.0	429.6	426.6	424.6	422.0
30°	494.2	470.7	453.1	437.6	426.4	419.0	415.8	413.2	409.7	408.4	407.1
32.5°	468.0	446.9	431.7	418.4	407.6	402.8	399.8	397.5	394.8	393.5	390.9
35°	430.8	413.2	398.4	391.0	382.3	378.2	375.9	372.6	370.1	368.9	368.5
37.5°	396.0	380.6	370.8	361.4	357.7	355.1	352.1	349.8	349.0	348.9	348.5
40°	373.3	360.8	352.1	344.4	342.8	338.9	336.3	334.4	334.4	334.8	334.4
42.5°	352.8	341.5	333.8	327.2	325.3	323.0	320.4	320.3	320.8	321.8	320.8
45°	321.6	313.5	308.1	304.8	301.3	299.0	298.7	299.7	300.0	300.3	301.3
47.5°	292.8	287.5	282.6	279.1	277.5	277.1	276.7	278.4	279.9	280.5	282.0
50°	275.9	269.8	265.6	263.4	262.1	261.4	262.1	264.0	265.3	266.9	267.9
52.5°	256.8	252.5	249.7	247.9	247.4	247.8	247.9	250.1	252.2	252.7	253.2
55°	230.6	227.3	226.7	223.8	225.1	224.7	226.4	227.6	229.5	231.5	231.9
57.5°	204.3	201.7	200.0	200.3	200.6	202.1	203.4	205.7	207.8	209.7	210.0
60°	186.8	185.5	184.6	184.6	185.2	187.2	188.7	191.0	192.3	193.6	194.5
62.5°	170.9	169.6	168.6	169.1	170.8	171.9	173.8	175.0	176.3	177.6	178.1
65°	145.7	145.0	146.0	146.6	147.0	148.5	150.8	151.8	153.1	153.7	155.9
67.5°	122.4	122.6	122.4	123.4	125.2	125.6	127.7	130.0	130.3	131.5	132.9
70°	106.8	107.4	108.1	108.7	110.3	110.9	112.5	113.5	114.8	115.7	116.8
72.5°	92.4	92.5	93.2	93.0	94.4	95.7	97.1	98.1	99.4	100.6	101.5
75°	71.0	71.0	71.7	72.1	73.6	75.3	74.9	75.6	76.9	78.2	78.8
77.5°	51.9	51.2	51.9	52.2	52.7	54.1	54.3	55.3	56.7	56.3	57.0
80°	39.5	38.6	39.5	39.9	39.9	41.5	41.5	42.1	43.0	42.1	43.0
82.5°	28.2	27.8	28.5	28.6	29.1	29.1	29.6	29.8	30.7	30.3	30.7
85°	14.1	13.9	14.1	13.9	14.1	14.5	14.5	14.1	14.1	14.8	13.9
87.5°	6.4	6.8	7.4	8.3	8.9	9.5	9.1	9.0	9.0	8.4	8.4
90°	10.2	13.4	17.7	22.0	26.3	30.5	30.1	29.7	29.4	28.9	28.8
92.5°	22.4	23.7	24.7	25.7	26.7	27.7	27.8	27.9	28.0	28.1	28.1
95°	53.1	54.2	54.7	55.0	55.4	55.8	55.8	55.8	55.8	55.8	55.6
97.5°	89.6	90.9	91.6	92.4	93.1	93.8	93.8	93.8	93.8	93.8	93.8
100°	116.9	118.0	118.6	119.2	119.8	120.4	120.4	120.4	120.4	120.4	120.3
102.5°	145.0	146.0	146.7	147.5	148.2	149.0	149.1	149.3	149.4	149.6	149.6
105°	189.9	190.3	190.7	191.1	191.5	191.8	192.3	192.6	193.0	193.4	193.6
107.5°	238.7	239.1	239.1	239.1	239.1	239.1	239.3	239.4	239.6	239.7	239.4
110°	270.6	271.2	271.2	271.2	271.2	271.2	271.2	271.2	271.2	271.2	271.0



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	304.1	304.6	304.4	304.3	304.2	304.0	303.5	303.1	302.6	302.1	301.7
115°	353.4	353.9	353.4	353.1	352.7	352.3	352.1	351.9	351.7	351.5	351.1
117.5°	404.2	404.4	403.4	402.3	401.2	400.1	399.7	399.2	398.7	398.2	397.7
120°	437.0	437.0	435.5	433.9	432.4	430.8	430.8	430.8	430.8	430.8	430.5
122.5°	468.2	468.6	467.5	466.5	465.4	464.3	463.8	463.4	462.9	462.4	462.0
125°	514.5	515.1	514.5	513.9	513.3	512.8	512.2	511.6	511.0	510.5	510.1
127.5°	561.9	562.7	562.0	561.3	560.6	559.9	559.1	558.4	557.8	557.1	556.4
130°	591.8	592.8	592.5	592.0	591.7	591.2	590.9	590.5	590.1	589.7	589.1
132.5°	622.0	623.0	623.1	623.2	623.3	623.4	622.5	621.6	620.8	619.9	619.2
135°	665.2	666.4	666.8	667.2	667.6	668.0	667.8	667.6	667.4	667.2	666.8
137.5°	708.8	710.0	710.4	710.9	711.4	712.0	711.8	711.6	711.5	711.4	710.8
140°	736.0	737.4	738.4	739.3	740.3	741.2	741.2	741.2	741.2	741.2	740.9
142.5°	764.0	765.2	765.8	766.5	767.2	767.8	767.9	768.1	768.3	768.4	768.1
145°	802.5	803.7	804.9	806.1	807.3	808.4	808.6	808.8	809.0	809.2	808.9
147.5°	839.3	840.5	841.3	842.1	842.8	843.6	844.0	844.5	844.9	845.3	845.2
150°	861.9	862.9	863.7	864.4	865.2	866.0	866.5	867.1	867.7	868.3	868.3
152.5°	883.6	884.6	885.5	886.4	887.3	888.3	889.0	889.8	890.5	891.2	891.2
155°	913.6	914.2	914.8	915.4	915.9	916.5	917.5	918.5	919.5	920.4	920.6
157.5°	940.6	941.0	941.3	941.7	942.0	942.4	943.7	945.0	946.3	947.6	947.8
160°	957.3	957.6	957.9	958.0	958.2	958.4	959.6	960.7	961.9	963.0	963.3
162.5°	971.5	971.6	971.8	972.0	972.2	972.3	973.7	975.0	976.3	977.7	977.8
165°	990.8	990.7	990.7	990.7	990.7	990.7	992.0	993.4	994.7	996.1	996.3
167.5°	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2	1008.6	1010.0	1011.2	1011.4
170°	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5	1016.9	1018.3	1019.7	1019.8
172.5°	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8	1023.2	1024.6	1025.9	1026.1
175°	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6	1030.0	1031.4	1032.7	1032.9
177.5°	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3	1033.2	1034.1	1035.0	1035.0
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	802.5	801.9	801.9	799.6	801.9	801.9	802.5	805.0	805.8	806.3	805.3
5°	744.4	743.4	741.8	743.4	741.8	743.4	744.4	748.9	751.1	753.4	755.4
7.5°	687.0	683.1	682.5	678.7	682.5	683.1	687.0	689.1	693.5	698.6	703.3
10°	645.1	642.5	642.1	636.0	642.1	642.5	645.1	650.5	655.0	661.1	667.5
12.5°	613.1	606.9	608.2	604.7	608.2	606.9	613.1	613.2	618.5	622.2	632.3
15°	557.8	557.8	556.6	551.1	556.6	557.8	557.8	566.5	568.2	574.3	583.0
17.5°	518.2	517.5	514.4	516.0	514.4	517.5	518.2	524.6	525.6	533.8	541.0
20°	494.6	492.6	488.8	488.8	488.8	492.6	494.6	498.1	502.2	507.0	513.2
22.5°	472.2	472.0	468.0	469.2	468.0	472.0	472.2	475.4	479.4	484.7	489.8
25°	446.0	443.4	441.5	442.5	441.5	443.4	446.0	446.3	450.8	454.3	457.5
27.5°	421.2	419.7	419.7	417.0	419.7	419.7	421.2	422.0	424.6	426.6	429.6
30°	406.7	403.6	404.2	402.6	404.2	403.6	406.7	407.1	408.4	409.7	413.2
32.5°	390.3	389.2	388.5	387.1	388.5	389.2	390.3	390.9	393.5	394.8	397.5
35°	367.8	368.2	366.5	367.2	366.5	368.2	367.8	368.5	368.9	370.1	372.6
37.5°	348.3	349.3	348.5	348.7	348.5	349.3	348.3	348.5	348.9	349.0	349.8
40°	335.4	335.4	335.4	336.3	335.4	335.4	335.4	334.4	334.8	334.4	334.4
42.5°	323.0	322.5	322.0	321.9	322.0	322.5	323.0	320.8	321.8	320.8	320.3
45°	302.0	302.9	303.2	301.6	303.2	302.9	302.0	301.3	300.3	300.0	299.7
47.5°	282.8	282.9	282.8	284.2	282.8	282.9	282.8	282.0	280.5	279.9	278.4
50°	269.5	268.8	269.5	268.8	269.5	268.8	269.5	267.9	266.9	265.3	264.0
52.5°	255.3	255.5	255.0	254.9	255.0	255.5	255.3	253.2	252.7	252.2	250.1
55°	233.2	233.8	233.4	233.4	233.4	233.8	233.2	231.9	231.5	229.5	227.6
57.5°	210.2	210.8	211.2	209.7	211.2	210.8	210.2	210.0	209.7	207.8	205.7
60°	194.2	195.8	195.5	194.8	195.5	195.8	194.2	194.5	193.6	192.3	191.0
62.5°	179.5	180.1	180.0	179.9	180.0	180.1	179.5	178.1	177.6	176.3	175.0
65°	156.9	157.6	156.6	157.6	156.6	157.6	156.9	155.9	153.7	153.1	151.8
67.5°	132.5	132.8	133.5	133.9	133.5	132.8	132.5	132.9	131.5	130.3	130.0
70°	117.4	117.0	118.0	119.0	118.0	117.0	117.4	116.8	115.7	114.8	113.5
72.5°	101.4	102.1	101.8	102.5	101.8	102.1	101.4	101.5	100.6	99.4	98.1
75°	78.2	79.1	78.8	79.7	78.8	79.1	78.2	78.8	78.2	76.9	75.6
77.5°	56.5	56.6	56.5	57.0	56.5	56.6	56.5	57.0	56.3	56.7	55.3
80°	43.0	42.4	41.8	43.0	41.8	42.4	43.0	43.0	42.1	43.0	42.1
82.5°	30.0	30.4	29.7	29.7	29.7	30.4	30.0	30.7	30.3	30.7	29.8
85°	13.9	13.5	12.8	12.8	12.8	13.5	13.9	13.9	14.8	14.1	14.1
87.5°	8.4	8.2	8.2	8.0	8.2	8.2	8.4	8.4	8.4	9.0	9.0
90°	29.1	29.3	29.4	29.6	29.4	29.3	29.1	28.8	28.9	29.4	29.7
92.5°	28.2	28.2	28.2	28.2	28.2	28.2	28.2	28.1	28.1	28.0	27.9
95°	55.2	54.8	54.4	54.1	54.4	54.8	55.2	55.6	55.8	55.8	55.8
97.5°	93.8	93.8	93.7	93.7	93.7	93.8	93.8	93.8	93.8	93.8	93.8
100°	120.0	119.9	119.7	119.5	119.7	119.9	120.0	120.3	120.4	120.4	120.4
102.5°	149.4	149.1	149.0	148.8	149.0	149.1	149.4	149.6	149.6	149.4	149.3
105°	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.6	193.4	193.0	192.6
107.5°	238.5	237.5	236.7	235.8	236.7	237.5	238.5	239.4	239.7	239.6	239.4
110°	270.4	269.8	269.1	268.6	269.1	269.8	270.4	271.0	271.2	271.2	271.2



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	301.3	300.8	300.4	300.0	300.4	300.8	301.3	301.7	302.1	302.6	303.1
115°	350.6	350.0	349.4	348.8	349.4	350.0	350.6	351.1	351.5	351.7	351.9
117.5°	397.2	396.6	396.0	395.4	396.0	396.6	397.2	397.7	398.2	398.7	399.2
120°	429.9	429.4	428.8	428.2	428.8	429.4	429.9	430.5	430.8	430.8	430.8
122.5°	461.6	461.2	460.7	460.3	460.7	461.2	461.6	462.0	462.4	462.9	463.4
125°	509.9	509.7	509.5	509.3	509.5	509.7	509.9	510.1	510.5	511.0	511.6
127.5°	555.8	555.2	554.6	554.0	554.6	555.2	555.8	556.4	557.1	557.8	558.4
130°	588.3	587.5	586.8	586.0	586.8	587.5	588.3	589.1	589.7	590.1	590.5
132.5°	618.6	617.9	617.3	616.7	617.3	617.9	618.6	619.2	619.9	620.8	621.6
135°	666.2	665.6	665.1	664.5	665.1	665.6	666.2	666.8	667.2	667.4	667.6
137.5°	710.1	709.3	708.5	707.7	708.5	709.3	710.1	710.8	711.4	711.5	711.6
140°	740.1	739.3	738.6	737.8	738.6	739.3	740.1	740.9	741.2	741.2	741.2
142.5°	767.3	766.5	765.8	765.0	765.8	766.5	767.3	768.1	768.4	768.3	768.1
145°	808.1	807.4	806.6	805.8	806.6	807.4	808.1	808.9	809.2	809.0	808.8
147.5°	844.5	843.7	843.0	842.2	843.0	843.7	844.5	845.2	845.3	844.9	844.5
150°	867.7	867.1	866.5	866.0	866.5	867.1	867.7	868.3	868.3	867.7	867.1
152.5°	890.5	889.8	889.0	888.3	889.0	889.8	890.5	891.2	891.2	890.5	889.8
155°	920.1	919.5	918.9	918.3	918.9	919.5	920.1	920.6	920.4	919.5	918.5
157.5°	946.9	946.0	945.0	944.1	945.0	946.0	946.9	947.8	947.6	946.3	945.0
160°	962.5	961.7	961.0	960.2	961.0	961.7	962.5	963.3	963.0	961.9	960.7
162.5°	976.9	975.9	975.0	974.1	975.0	975.9	976.9	977.8	977.7	976.3	975.0
165°	995.3	994.4	993.4	992.4	993.4	994.4	995.3	996.3	996.1	994.7	993.4
167.5°	1010.5	1009.4	1008.4	1007.5	1008.4	1009.4	1010.5	1011.4	1011.2	1010.0	1008.6
170°	1018.6	1017.4	1016.2	1015.1	1016.2	1017.4	1018.6	1019.8	1019.7	1018.3	1016.9
172.5°	1024.8	1023.7	1022.5	1021.4	1022.5	1023.7	1024.8	1026.1	1025.9	1024.6	1023.2
175°	1031.7	1030.5	1029.3	1028.2	1029.3	1030.5	1031.7	1032.9	1032.7	1031.4	1030.0
177.5°	1034.1	1033.2	1032.3	1031.3	1032.3	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	804.0	806.8	811.2	815.8	818.6	824.1	825.6	828.2	830.5	835.9	841.5
5°	757.6	762.1	772.7	778.4	786.5	795.8	801.9	808.4	815.5	827.7	839.0
7.5°	707.8	715.3	728.5	739.3	750.8	764.1	773.8	786.5	797.0	814.2	830.8
10°	674.6	685.2	697.2	710.0	726.1	740.2	753.7	769.8	782.6	803.2	822.5
12.5°	644.8	646.4	663.4	677.6	699.6	717.0	732.6	753.3	765.9	790.4	810.7
15°	592.6	602.3	617.7	629.0	655.0	677.2	699.0	720.6	735.0	765.3	791.9
17.5°	548.7	557.6	573.4	591.9	610.5	632.6	660.9	683.6	703.3	737.8	769.4
20°	520.9	531.8	547.9	566.9	583.3	607.4	631.8	657.9	679.1	718.0	755.0
22.5°	497.2	505.8	518.8	537.5	555.5	577.6	604.3	632.7	655.0	696.9	734.4
25°	464.0	471.1	479.4	494.9	515.1	539.2	560.2	591.3	623.8	663.1	708.3
27.5°	434.0	439.0	446.4	460.0	475.7	498.3	521.5	551.0	583.8	626.3	674.2
30°	415.8	419.0	426.4	437.6	453.1	470.7	494.2	522.5	555.9	599.1	646.6
32.5°	399.8	402.8	407.6	418.4	431.7	446.9	468.0	496.3	528.1	570.5	623.2
35°	375.9	378.2	382.3	391.0	398.4	413.2	430.8	456.6	486.5	527.0	581.7
37.5°	352.1	355.1	357.7	361.4	370.8	380.6	396.0	417.7	447.0	487.9	540.0
40°	336.3	338.9	342.8	344.4	352.1	360.8	373.3	393.2	422.8	460.1	510.9
42.5°	320.4	323.0	325.3	327.2	333.8	341.5	352.8	369.9	396.1	432.4	482.7
45°	298.7	299.0	301.3	304.8	308.1	313.5	321.6	336.3	356.6	390.7	436.4
47.5°	276.7	277.1	277.5	279.1	282.6	287.5	292.8	304.9	323.0	350.3	394.7
50°	262.1	261.4	262.1	263.4	265.6	269.8	275.9	284.6	299.4	324.8	365.6
52.5°	247.9	247.8	247.4	247.9	249.7	252.5	256.8	264.2	277.5	300.8	336.8
55°	226.4	224.7	225.1	223.8	226.7	227.3	230.6	236.7	248.2	264.3	298.1
57.5°	203.4	202.1	200.6	200.3	200.0	201.7	204.3	209.1	218.0	232.1	259.5
60°	188.7	187.2	185.2	184.6	184.6	185.5	186.8	190.4	198.7	211.3	233.8
62.5°	173.8	171.9	170.8	169.1	168.6	169.6	170.9	173.4	179.4	191.2	210.6
65°	150.8	148.5	147.0	146.6	146.0	145.0	145.7	148.3	153.1	162.4	177.8
67.5°	127.7	125.6	125.2	123.4	122.4	122.6	122.4	124.7	127.5	135.5	147.1
70°	112.5	110.9	110.3	108.7	108.1	107.4	106.8	108.7	111.6	118.3	128.3
72.5°	97.1	95.7	94.4	93.0	93.2	92.5	92.4	93.5	95.9	102.1	109.8
75°	74.9	75.3	73.6	72.1	71.7	71.0	71.0	72.1	73.0	77.8	83.9
77.5°	54.3	54.1	52.7	52.2	51.9	51.2	51.9	52.5	53.0	56.3	60.8
80°	41.5	41.5	39.9	39.9	39.5	38.6	39.5	38.9	40.2	43.4	46.7
82.5°	29.6	29.1	29.1	28.6	28.5	27.8	28.2	28.8	29.4	31.6	33.5
85°	14.5	14.5	14.1	13.9	14.1	13.9	14.1	14.5	14.8	15.8	17.4
87.5°	9.1	9.5	8.9	8.3	7.4	6.8	6.4	6.2	6.3	6.0	5.9
90°	30.1	30.5	26.3	22.0	17.7	13.4	10.2	7.8	5.5	3.2	0.9
92.5°	27.8	27.7	26.7	25.7	24.7	23.7	22.4	20.7	18.9	17.2	15.5
95°	55.8	55.8	55.4	55.0	54.7	54.2	53.1	51.1	49.2	47.3	45.4
97.5°	93.8	93.8	93.1	92.4	91.6	90.9	89.6	88.0	86.3	84.6	82.8
100°	120.4	120.4	119.8	119.2	118.6	118.0	116.9	115.4	113.8	112.3	110.7
102.5°	149.1	149.0	148.2	147.5	146.7	146.0	145.0	143.8	142.5	141.3	140.1
105°	192.3	191.8	191.5	191.1	190.7	190.3	189.9	189.2	188.6	188.0	187.5
107.5°	239.3	239.1	239.1	239.1	239.1	239.1	238.7	237.8	236.9	236.2	235.3
110°	271.2	271.2	271.2	271.2	271.2	271.2	270.6	269.5	268.3	267.2	266.0



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	303.5	304.0	304.2	304.3	304.4	304.6	304.1	303.0	301.8	300.7	299.5
115°	352.1	352.3	352.7	353.1	353.4	353.9	353.4	352.3	351.1	350.0	348.8
117.5°	399.7	400.1	401.2	402.3	403.4	404.4	404.2	402.7	401.1	399.6	398.0
120°	430.8	430.8	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8
122.5°	463.8	464.3	465.4	466.5	467.5	468.6	468.2	466.4	464.5	462.7	460.8
125°	512.2	512.8	513.3	513.9	514.5	515.1	514.5	512.8	511.0	509.3	507.6
127.5°	559.1	559.9	560.6	561.3	562.0	562.7	561.9	559.7	557.5	555.3	553.1
130°	590.9	591.2	591.7	592.0	592.5	592.8	591.8	589.3	586.7	584.2	581.7
132.5°	622.5	623.4	623.3	623.2	623.1	623.0	622.0	619.9	617.9	615.8	613.7
135°	667.8	668.0	667.6	667.2	666.8	666.4	665.2	663.1	660.9	658.8	656.7
137.5°	711.8	712.0	711.4	710.9	710.4	710.0	708.8	707.1	705.3	703.6	701.8
140°	741.2	741.2	740.3	739.3	738.4	737.4	736.0	734.3	732.5	730.8	729.0
142.5°	767.9	767.8	767.2	766.5	765.8	765.2	764.0	762.2	760.4	758.7	757.0
145°	808.6	808.4	807.3	806.1	804.9	803.7	802.5	801.2	799.8	798.4	797.0
147.5°	844.0	843.6	842.8	842.1	841.3	840.5	839.3	837.7	836.1	834.5	832.8
150°	866.5	866.0	865.2	864.4	863.7	862.9	861.9	860.7	859.5	858.4	857.2
152.5°	889.0	888.3	887.3	886.4	885.5	884.6	883.6	882.4	881.2	880.0	878.9
155°	917.5	916.5	915.9	915.4	914.8	914.2	913.6	913.1	912.5	911.9	911.3
157.5°	943.7	942.4	942.0	941.7	941.3	941.0	940.6	940.2	939.8	939.4	939.0
160°	959.6	958.4	958.2	958.0	957.9	957.6	957.3	956.9	956.6	956.1	955.8
162.5°	973.7	972.3	972.2	972.0	971.8	971.6	971.5	971.4	971.3	971.2	971.1
165°	992.0	990.7	990.7	990.7	990.7	990.7	990.8	990.9	991.2	991.4	991.5
167.5°	1007.2	1005.8	1005.9	1005.9	1006.0	1006.0	1006.3	1006.9	1007.5	1008.1	1008.7
170°	1015.5	1014.3	1014.4	1014.6	1014.8	1015.0	1015.4	1016.0	1016.6	1017.1	1017.7
172.5°	1021.8	1020.5	1020.7	1020.9	1021.1	1021.2	1021.7	1022.3	1022.8	1023.4	1024.0
175°	1028.6	1027.3	1027.7	1028.0	1028.5	1028.8	1029.3	1029.9	1030.5	1031.0	1031.7
177.5°	1032.3	1031.3	1031.7	1031.9	1032.3	1032.5	1032.9	1033.4	1033.9	1034.3	1034.8
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	841.0	842.3	846.4	850.6	855.1	856.4	858.5	856.7	856.2	861.1	864.7
5°	843.4	849.2	860.5	870.7	879.4	885.5	892.0	894.6	899.4	906.1	914.5
7.5°	840.7	852.0	869.7	884.7	901.0	912.7	922.0	929.8	939.3	952.1	966.0
10°	837.7	852.7	874.3	892.6	912.6	927.6	940.2	952.4	966.6	984.3	1002.5
12.5°	832.0	849.9	876.8	898.5	924.1	939.0	955.9	982.2	997.5	1022.1	1047.8
15°	820.6	840.5	878.1	904.8	933.8	962.1	993.2	1018.3	1043.4	1057.9	1094.2
17.5°	803.7	832.9	874.6	905.8	942.5	987.1	1022.1	1050.6	1079.5	1102.9	1121.2
20°	790.1	821.9	869.4	906.8	950.5	998.4	1038.6	1067.6	1092.6	1112.2	1123.5
22.5°	772.8	812.9	859.2	902.9	958.7	1006.2	1048.4	1071.2	1092.1	1101.6	1106.0
25°	745.6	793.9	846.3	899.7	962.7	1012.9	1051.5	1065.3	1071.4	1062.0	1046.6
27.5°	716.4	770.2	831.5	893.6	960.3	1008.5	1036.1	1034.0	1023.6	993.4	969.3
30°	694.6	753.7	819.6	887.4	954.3	1001.3	1017.4	1001.3	977.8	944.1	909.6
32.5°	671.7	732.9	807.0	878.7	943.6	984.8	988.3	960.6	924.3	886.0	843.0
35°	637.0	703.3	783.3	859.2	920.6	946.7	931.2	882.4	839.2	786.9	728.3
37.5°	597.8	671.0	751.2	830.5	886.2	893.0	854.7	803.2	742.4	680.9	612.0
40°	568.5	646.0	728.7	808.7	857.9	850.8	801.9	745.4	673.0	597.8	533.7
42.5°	542.3	619.7	704.0	782.5	821.9	802.5	745.4	675.9	598.1	527.3	468.7
45°	496.8	576.5	662.7	738.6	761.1	726.1	650.5	573.3	496.8	437.6	391.3
47.5°	452.7	531.5	616.8	683.5	691.6	644.4	561.8	482.4	416.6	368.4	335.8
50°	420.3	499.4	583.9	643.4	640.8	583.9	499.0	423.4	368.5	329.6	307.7
52.5°	391.2	465.9	547.2	601.2	587.6	525.6	444.5	377.5	332.3	301.8	282.0
55°	345.9	415.1	492.3	535.7	510.7	441.8	373.3	319.3	285.9	263.0	247.6
57.5°	301.1	365.9	432.0	458.7	431.0	367.5	310.4	271.2	246.1	229.1	219.1
60°	273.3	329.9	388.7	411.9	378.8	322.2	277.2	242.1	221.9	208.0	199.1
62.5°	245.6	296.2	351.7	364.3	334.0	286.2	246.3	217.1	200.5	188.2	179.8
65°	207.8	249.2	291.4	299.7	271.7	234.7	203.2	184.3	169.4	160.5	153.7
67.5°	170.4	203.6	233.5	240.2	215.8	190.1	167.3	150.8	140.8	133.3	127.6
70°	148.3	174.6	199.1	204.5	184.9	162.0	144.7	131.5	122.5	116.1	110.6
72.5°	124.8	146.8	167.1	170.8	154.8	137.3	123.1	112.7	104.8	100.7	95.4
75°	95.5	108.4	124.2	125.1	114.5	103.8	92.9	86.2	82.0	76.9	74.3
77.5°	67.4	77.5	86.5	88.3	82.0	74.7	68.6	63.3	59.8	57.3	55.0
80°	51.5	59.5	63.4	65.6	61.1	56.0	52.4	48.9	46.7	45.0	43.4
82.5°	36.8	41.8	45.4	47.1	44.6	41.6	38.0	36.0	34.3	32.9	32.4
85°	18.7	20.9	23.2	23.8	23.2	21.9	20.0	20.0	18.9	18.7	18.7
87.5°	7.1	8.5	9.0	10.2	10.4	11.3	12.1	12.7	13.3	13.0	12.7
90°	3.2	5.5	7.8	10.2	13.4	17.7	22.0	26.3	30.5	30.1	29.7
92.5°	17.2	18.9	20.7	22.4	23.7	24.7	25.7	26.7	27.7	27.8	27.9
95°	47.3	49.2	51.1	53.1	54.2	54.7	55.0	55.4	55.8	55.8	55.8
97.5°	84.6	86.3	88.0	89.6	90.9	91.6	92.4	93.1	93.8	93.8	93.8
100°	112.3	113.8	115.4	116.9	118.0	118.6	119.2	119.8	120.4	120.4	120.4
102.5°	141.3	142.5	143.8	145.0	146.0	146.7	147.5	148.2	149.0	149.1	149.3
105°	188.0	188.6	189.2	189.9	190.3	190.7	191.1	191.5	191.8	192.3	192.6
107.5°	236.2	236.9	237.8	238.7	239.1	239.1	239.1	239.1	239.1	239.3	239.4
110°	267.2	268.3	269.5	270.6	271.2	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.7	301.8	303.0	304.1	304.6	304.4	304.3	304.2	304.0	303.5	303.1
115°	350.0	351.1	352.3	353.4	353.9	353.4	353.1	352.7	352.3	352.1	351.9
117.5°	399.6	401.1	402.7	404.2	404.4	403.4	402.3	401.2	400.1	399.7	399.2
120°	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	430.8	430.8
122.5°	462.7	464.5	466.4	468.2	468.6	467.5	466.5	465.4	464.3	463.8	463.4
125°	509.3	511.0	512.8	514.5	515.1	514.5	513.9	513.3	512.8	512.2	511.6
127.5°	555.3	557.5	559.7	561.9	562.7	562.0	561.3	560.6	559.9	559.1	558.4
130°	584.2	586.7	589.3	591.8	592.8	592.5	592.0	591.7	591.2	590.9	590.5
132.5°	615.8	617.9	619.9	622.0	623.0	623.1	623.2	623.3	623.4	622.5	621.6
135°	658.8	660.9	663.1	665.2	666.4	666.8	667.2	667.6	668.0	667.8	667.6
137.5°	703.6	705.3	707.1	708.8	710.0	710.4	710.9	711.4	712.0	711.8	711.6
140°	730.8	732.5	734.3	736.0	737.4	738.4	739.3	740.3	741.2	741.2	741.2
142.5°	758.7	760.4	762.2	764.0	765.2	765.8	766.5	767.2	767.8	767.9	768.1
145°	798.4	799.8	801.2	802.5	803.7	804.9	806.1	807.3	808.4	808.6	808.8
147.5°	834.5	836.1	837.7	839.3	840.5	841.3	842.1	842.8	843.6	844.0	844.5
150°	858.4	859.5	860.7	861.9	862.9	863.7	864.4	865.2	866.0	866.5	867.1
152.5°	880.0	881.2	882.4	883.6	884.6	885.5	886.4	887.3	888.3	889.0	889.8
155°	911.9	912.5	913.1	913.6	914.2	914.8	915.4	915.9	916.5	917.5	918.5
157.5°	939.4	939.8	940.2	940.6	941.0	941.3	941.7	942.0	942.4	943.7	945.0
160°	956.1	956.6	956.9	957.3	957.6	957.9	958.0	958.2	958.4	959.6	960.7
162.5°	971.2	971.3	971.4	971.5	971.6	971.8	972.0	972.2	972.3	973.7	975.0
165°	991.4	991.2	990.9	990.8	990.7	990.7	990.7	990.7	990.7	992.0	993.4
167.5°	1008.1	1007.5	1006.9	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2	1008.6
170°	1017.1	1016.6	1016.0	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5	1016.9
172.5°	1023.4	1022.8	1022.3	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8	1023.2
175°	1031.0	1030.5	1029.9	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6	1030.0
177.5°	1034.3	1033.9	1033.4	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3	1033.2
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	836.6	836.6	836.6	836.6	836.6	836.6	836.6
2.5°	867.8	871.4	871.4	871.9	876.0	875.6	875.3
5°	923.5	928.9	929.6	935.4	939.3	938.0	934.4
7.5°	976.0	986.2	993.9	998.2	1003.3	1006.4	1005.0
10°	1017.7	1032.5	1041.5	1047.6	1055.0	1060.5	1058.5
12.5°	1055.5	1073.2	1085.5	1096.0	1096.9	1104.0	1099.2
15°	1114.5	1133.2	1135.1	1142.8	1148.9	1148.2	1148.6
17.5°	1133.9	1140.0	1141.2	1141.3	1141.4	1139.2	1134.3
20°	1127.0	1124.8	1119.3	1115.2	1107.8	1106.7	1100.4
22.5°	1094.1	1086.9	1073.2	1064.2	1052.7	1049.6	1047.8
25°	1029.2	1013.5	991.6	970.8	964.9	953.7	956.9
27.5°	940.3	915.8	892.1	875.1	859.8	842.9	847.7
30°	877.8	850.2	816.7	791.0	774.6	758.5	755.6
32.5°	803.2	762.7	725.4	702.7	677.6	667.4	656.3
35°	674.6	635.1	598.1	566.3	547.9	533.7	520.9
37.5°	558.9	513.4	483.5	457.8	444.5	436.4	438.4
40°	487.2	447.3	425.4	405.8	393.6	387.8	389.1
42.5°	429.0	399.2	381.2	367.7	359.1	355.9	355.1
45°	363.0	346.3	331.5	323.8	319.6	316.1	313.8
47.5°	318.1	304.4	296.0	291.4	287.7	284.2	284.1
50°	291.0	282.0	276.2	271.4	268.5	265.9	268.2
52.5°	270.4	262.2	256.4	252.1	251.0	248.7	248.7
55°	239.9	233.4	229.3	225.4	223.5	222.2	220.6
57.5°	212.1	206.0	202.2	199.7	196.0	194.8	194.2
60°	192.3	187.4	183.6	180.4	178.7	176.2	176.2
62.5°	174.0	169.2	165.6	163.2	160.5	159.5	159.7
65°	147.6	143.7	140.2	137.6	137.0	135.1	135.7
67.5°	123.3	120.7	117.0	115.5	114.3	113.3	112.5
70°	107.1	104.5	102.5	100.7	99.7	99.7	99.7
72.5°	93.4	90.3	89.2	86.8	87.3	86.3	85.2
75°	72.3	70.4	69.5	68.4	66.9	66.9	66.9
77.5°	53.2	52.7	51.5	50.5	50.1	49.8	49.9
80°	41.2	40.8	40.2	40.2	39.5	39.3	38.6
82.5°	31.6	30.8	30.4	30.1	30.0	30.0	29.9
85°	18.0	17.4	17.4	17.7	17.0	17.0	17.4
87.5°	12.8	12.7	12.5	12.5	12.8	12.6	12.7
90°	29.4	28.9	28.8	29.1	29.3	29.4	29.6
92.5°	28.0	28.1	28.1	28.2	28.2	28.2	28.2
95°	55.8	55.8	55.6	55.2	54.8	54.4	54.1
97.5°	93.8	93.8	93.8	93.8	93.8	93.7	93.7
100°	120.4	120.4	120.3	120.0	119.9	119.7	119.5
102.5°	149.4	149.6	149.6	149.4	149.1	149.0	148.8
105°	193.0	193.4	193.6	193.6	193.6	193.6	193.6
107.5°	239.6	239.7	239.4	238.5	237.5	236.7	235.8
110°	271.2	271.2	271.0	270.4	269.8	269.1	268.6



TEST NUMBER: P331508-935

CATALOG NUMBER: S122DIW-S485D970U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	302.6	302.1	301.7	301.3	300.8	300.4	300.0
115°	351.7	351.5	351.1	350.6	350.0	349.4	348.8
117.5°	398.7	398.2	397.7	397.2	396.6	396.0	395.4
120°	430.8	430.8	430.5	429.9	429.4	428.8	428.2
122.5°	462.9	462.4	462.0	461.6	461.2	460.7	460.3
125°	511.0	510.5	510.1	509.9	509.7	509.5	509.3
127.5°	557.8	557.1	556.4	555.8	555.2	554.6	554.0
130°	590.1	589.7	589.1	588.3	587.5	586.8	586.0
132.5°	620.8	619.9	619.2	618.6	617.9	617.3	616.7
135°	667.4	667.2	666.8	666.2	665.6	665.1	664.5
137.5°	711.5	711.4	710.8	710.1	709.3	708.5	707.7
140°	741.2	741.2	740.9	740.1	739.3	738.6	737.8
142.5°	768.3	768.4	768.1	767.3	766.5	765.8	765.0
145°	809.0	809.2	808.9	808.1	807.4	806.6	805.8
147.5°	844.9	845.3	845.2	844.5	843.7	843.0	842.2
150°	867.7	868.3	868.3	867.7	867.1	866.5	866.0
152.5°	890.5	891.2	891.2	890.5	889.8	889.0	888.3
155°	919.5	920.4	920.6	920.1	919.5	918.9	918.3
157.5°	946.3	947.6	947.8	946.9	946.0	945.0	944.1
160°	961.9	963.0	963.3	962.5	961.7	961.0	960.2
162.5°	976.3	977.7	977.8	976.9	975.9	975.0	974.1
165°	994.7	996.1	996.3	995.3	994.4	993.4	992.4
167.5°	1010.0	1011.2	1011.4	1010.5	1009.4	1008.4	1007.5
170°	1018.3	1019.7	1019.8	1018.6	1017.4	1016.2	1015.1
172.5°	1024.6	1025.9	1026.1	1024.8	1023.7	1022.5	1021.4
175°	1031.4	1032.7	1032.9	1031.7	1030.5	1029.3	1028.2
177.5°	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4

(END OF REPORT)