

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331500-930

Luminaire Tested: **S122DIW-S485D435U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331500-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S485D435U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2836.8 lumens
Efficiency: N/A
Efficacy: 93.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	74	74	74	62	62	62	57
1	99	95	91	87	92	88	85	82	76	74	72	65	64	62	55	54	53	48
2	90	83	77	71	84	77	72	67	67	63	59	57	54	52	49	46	44	40
3	83	73	65	60	76	68	62	56	59	54	50	51	47	44	43	40	38	34
4	76	65	57	50	70	60	53	48	53	47	43	45	41	37	38	35	33	29
5	69	58	49	43	64	54	47	41	47	41	37	41	36	33	35	31	28	25
6	64	52	43	38	59	48	41	36	42	37	32	37	32	29	31	28	25	22
7	59	47	39	33	55	44	37	31	39	33	28	33	29	25	29	25	22	20
8	55	42	35	29	51	40	33	28	35	29	25	31	26	23	26	23	20	18
9	51	39	31	26	48	37	30	25	32	27	23	28	24	20	24	21	18	16
10	48	36	28	23	45	34	27	22	30	24	20	26	22	18	23	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	10224	10224	10224
5°	10263	10115	10175
10°	10203	10012	10063
15°	10076	9884	9872
20°	9897	9689	9677
25°	9720	9449	9449
30°	9491	9229	9148
35°	9278	8966	8834
40°	9010	8703	8534
45°	8745	8439	8229
50°	8457	8166	7877
55°	8158	7848	7561
60°	7824	7472	7195
65°	7465	7095	6770
70°	7010	6637	6326
75°	6382	6114	5964
80°	5662	5486	5207
85°	4613	4390	3946



TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	59.5	2.1
10°-20°	167.6	5.9
20°-30°	246.3	8.7
30°-40°	286.1	10.1
40°-50°	285.8	10.1
50°-60°	249.2	8.8
60°-70°	184.3	6.5
70°-80°	104.4	3.7
80°-90°	29.8	1.1
90°-100°	27.7	1.0
100°-110°	86.1	3.0
110°-120°	147.2	5.2
120°-130°	193.6	6.8
130°-140°	217.3	7.7
140°-150°	213.1	7.5
150°-160°	178.7	6.3
160°-170°	118.6	4.2
170°-180°	41.4	1.5
0°-30°	473.4	16.7
0°-40°	759.4	26.8
0°-60°	1294.4	45.6
0°-90°	1612.8	56.9
90°-120°	261.1	9.2
90°-150°	885.2	31.2
90°-180°	1224.0	43.1
0°-180°	2836.8	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	633	633	633	633	633	
5°	633	631	624	629	628	60
15°	603	599	591	593	591	170
25°	546	540	530	531	530	251
35°	471	464	455	451	448	294
45°	383	378	370	363	360	295
55°	290	286	279	272	269	259
65°	195	192	186	180	177	193
75°	102	101	98	95	96	109
85°	25	24	24	22	21	29
90°	0	5	13	12	13	2
95°	19	23	24	24	23	22
105°	79	80	81	82	82	84
115°	148	150	149	149	148	146
125°	215	218	217	216	216	192
135°	278	282	283	282	281	215
145°	338	340	342	343	341	211
155°	386	387	388	390	389	178
165°	420	420	420	422	420	118
175°	437	436	435	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	636.2	635.6	635.1	634.5	634.0	633.2	631.9	630.8	629.6	628.4	629.5
5°	633.2	632.7	632.2	631.6	631.1	630.1	628.6	627.1	625.6	624.1	625.2
7.5°	627.6	626.8	626.0	625.1	624.3	623.1	621.6	620.1	618.6	617.0	618.2
10°	622.3	621.3	620.4	619.5	618.5	617.2	615.6	614.0	612.4	610.7	611.8
12.5°	615.0	614.2	613.3	612.5	611.6	610.4	608.8	607.2	605.5	603.9	604.6
15°	602.8	602.0	601.2	600.4	599.6	598.3	596.5	594.8	593.0	591.3	591.7
17.5°	587.2	586.4	585.6	584.8	584.0	582.7	580.9	579.1	577.3	575.5	576.2
20°	576.0	575.2	574.4	573.6	572.7	571.4	569.5	567.6	565.7	563.9	564.3
22.5°	564.8	563.7	562.6	561.4	560.3	558.8	557.0	555.2	553.4	551.6	551.7
25°	545.6	544.5	543.4	542.3	541.3	539.6	537.3	534.9	532.6	530.4	530.6
27.5°	523.7	522.7	521.7	520.7	519.8	518.4	516.6	514.7	512.9	511.1	510.7
30°	509.1	507.9	506.9	505.8	504.7	503.1	501.1	499.1	497.1	495.0	494.6
32.5°	493.4	492.6	491.7	490.8	490.0	488.4	486.3	484.2	482.1	480.0	479.2
35°	470.7	469.3	468.0	466.6	465.3	463.5	461.4	459.2	457.0	454.9	454.0
37.5°	445.0	443.8	442.6	441.4	440.2	438.5	436.3	434.2	432.0	429.9	428.8
40°	427.5	426.3	425.3	424.2	423.1	421.5	419.3	417.2	415.0	412.9	411.6
42.5°	410.4	409.3	408.2	407.2	406.1	404.5	402.3	400.1	397.9	395.7	394.4
45°	383.0	382.0	381.1	380.2	379.2	377.7	375.7	373.7	371.6	369.6	368.1
47.5°	355.7	354.8	353.9	353.0	352.1	350.7	348.5	346.4	344.3	342.2	340.6
50°	336.7	336.1	335.3	334.7	334.0	332.7	330.8	329.0	327.0	325.1	323.3
52.5°	318.2	317.3	316.4	315.5	314.6	313.3	311.5	309.7	307.9	306.1	304.6
55°	289.8	289.0	288.2	287.4	286.6	285.4	283.7	282.1	280.5	278.8	277.3
57.5°	261.3	260.7	260.0	259.4	258.8	257.6	255.8	254.0	252.2	250.4	248.7
60°	242.3	241.8	241.2	240.7	240.2	239.0	237.1	235.1	233.3	231.4	229.9
62.5°	223.8	223.0	222.1	221.2	220.4	219.2	217.8	216.3	214.8	213.4	212.0
65°	195.4	194.6	193.8	193.0	192.2	191.1	189.8	188.4	187.0	185.7	184.5
67.5°	166.6	165.9	165.3	164.6	164.0	163.1	161.8	160.6	159.4	158.2	157.3
70°	148.5	148.1	147.5	146.9	146.4	145.5	144.3	143.1	141.9	140.6	139.7
72.5°	130.0	129.6	129.0	128.4	127.9	127.3	126.5	125.6	124.9	124.1	123.1
75°	102.3	102.0	101.7	101.5	101.2	100.8	100.0	99.4	98.7	98.0	97.2
77.5°	77.5	77.0	76.6	76.1	75.6	75.3	75.0	74.7	74.4	74.2	73.8
80°	60.9	60.7	60.7	60.5	60.3	60.2	59.8	59.6	59.4	59.0	58.6
82.5°	45.3	45.2	45.2	45.2	45.2	45.1	44.9	44.8	44.6	44.4	43.9
85°	24.9	24.9	24.7	24.5	24.5	24.3	24.1	24.1	23.9	23.7	23.3
87.5°	8.8	8.8	8.8	8.8	8.7	8.8	9.0	9.1	9.3	9.4	9.0
90°	0.4	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8
92.5°	6.6	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7
95°	19.2	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6
97.5°	35.1	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7
100°	46.9	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0
102.5°	59.4	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2
105°	79.4	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4
107.5°	99.6	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3
110°	112.7	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.9	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6
115°	147.7	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1
117.5°	168.6	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3
120°	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5
122.5°	195.2	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5
125°	215.0	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0
127.5°	234.2	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8
130°	246.4	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3
132.5°	260.0	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7
135°	278.2	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8
137.5°	297.3	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5
140°	308.8	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0
142.5°	320.7	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3
145°	337.6	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5
147.5°	352.8	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5
150°	363.1	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0
152.5°	372.3	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6
155°	386.0	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7
157.5°	397.8	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7
160°	404.9	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4
162.5°	411.3	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4
165°	420.0	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2
167.5°	427.2	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6
170°	431.0	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2
172.5°	433.7	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8
175°	437.0	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7
177.5°	438.3	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	633.2	633.2	633.2	633.2	633.2	633.2	633.2	633.2
2.5°	630.6	631.6	632.7	633.2	632.9	632.7	632.5	632.3
5°	626.3	627.4	628.4	628.8	628.6	628.3	628.0	627.8
7.5°	619.2	620.3	621.4	621.7	621.5	621.2	620.9	620.6
10°	612.9	614.0	615.1	615.4	615.0	614.6	614.2	613.8
12.5°	605.4	606.2	606.9	607.2	606.8	606.6	606.3	605.9
15°	592.3	592.9	593.4	593.3	592.6	592.0	591.3	590.6
17.5°	576.7	577.4	578.0	578.0	577.3	576.7	576.1	575.4
20°	564.7	565.1	565.5	565.4	564.8	564.3	563.8	563.2
22.5°	551.8	551.9	552.0	551.9	551.5	551.2	550.9	550.6
25°	530.9	531.2	531.4	531.4	531.2	530.9	530.6	530.4
27.5°	510.3	509.9	509.5	509.0	508.3	507.7	507.0	506.4
30°	494.2	493.8	493.4	492.9	492.4	491.9	491.3	490.7
32.5°	478.5	477.8	477.0	476.4	475.8	475.3	474.7	474.2
35°	453.2	452.4	451.6	450.9	450.2	449.5	448.8	448.2
37.5°	427.9	426.9	425.9	425.0	424.4	423.7	423.1	422.5
40°	410.4	409.2	408.0	407.1	406.5	406.0	405.4	404.9
42.5°	393.1	391.8	390.4	389.5	388.7	387.9	387.2	386.4
45°	366.6	365.2	363.6	362.6	362.1	361.6	361.0	360.4
47.5°	339.1	337.5	335.9	334.8	333.9	333.2	332.4	331.6
50°	321.4	319.4	317.6	316.3	315.6	315.0	314.2	313.6
52.5°	303.0	301.4	299.9	298.6	297.7	296.9	296.0	295.1
55°	275.7	274.0	272.4	271.3	270.5	269.9	269.2	268.6
57.5°	247.2	245.6	244.0	243.0	242.4	241.9	241.4	240.8
60°	228.4	226.9	225.4	224.5	224.0	223.6	223.2	222.8
62.5°	210.6	209.2	207.8	206.9	206.4	205.9	205.4	204.8
65°	183.3	182.1	180.8	179.9	179.2	178.6	177.9	177.2
67.5°	156.3	155.3	154.4	153.7	153.1	152.5	152.1	151.5
70°	138.8	137.8	136.9	136.2	135.6	135.0	134.5	134.0
72.5°	122.2	121.2	120.3	119.6	119.2	118.7	118.3	117.9
75°	96.4	95.6	94.8	94.5	94.8	95.1	95.3	95.6
77.5°	73.4	73.0	72.6	72.2	71.7	71.4	71.0	70.6
80°	58.2	57.8	57.5	57.1	56.8	56.6	56.3	56.0
82.5°	43.5	42.9	42.4	42.1	42.1	42.0	41.9	41.9
85°	22.9	22.5	22.1	21.9	21.7	21.6	21.4	21.3
87.5°	8.7	8.3	8.0	7.7	7.7	7.6	7.5	7.4
90°	12.6	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.2	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.6	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.4	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331500-930

CATALOG NUMBER: S122DIW-S485D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	128.4	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	169.1	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.2	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.7	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.5	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.1	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	263.3	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.4	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.3	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.6	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.7	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.1	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.2	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	406.9	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	412.9	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	420.8	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.2	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	430.7	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	433.4	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.3	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)