

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331529-935

Luminaire Tested: **S122DIW-S675D435U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331529-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3817.3 lumens
Efficiency: N/A
Efficacy: 101.3 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	61
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	59	57	56	51
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	43
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	36
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	31
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	27
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	24
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	21
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	19
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19	17
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	2.3
10°-20°	241.9	6.3
20°-30°	355.5	9.3
30°-40°	412.9	10.8
40°-50°	412.5	10.8
50°-60°	359.7	9.4
60°-70°	266.0	7.0
70°-80°	150.6	3.9
80°-90°	41.8	1.1
90°-100°	17.0	0.4
100°-110°	62.2	1.6
110°-120°	166.3	4.4
120°-130°	274.5	7.2
130°-140°	291.9	7.6
140°-150°	271.3	7.1
150°-160°	218.2	5.7
160°-170°	140.6	3.7
170°-180°	48.4	1.3
0°-30°	683.3	17.9
0°-40°	1096.3	28.7
0°-60°	1868.5	48.9
0°-90°	2326.9	61.0
90°-120°	245.5	6.4
90°-150°	1083.3	28.4
90°-180°	1490.0	39.0
0°-180°	3817.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	0	4	7	9	10	3
95°	24	13	14	16	16	29
105°	112	117	22	26	28	120
115°	212	218	227	65	30	208
125°	299	304	311	313	315	267
135°	370	376	379	383	382	286
145°	430	429	435	438	436	269
155°	473	470	474	476	473	218
165°	498	496	497	500	497	141
175°	510	507	508	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.7	12.6	12.5	12.3	12.2	12.1	11.9	11.7	11.5	11.3	10.9
90°	0.3	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7
92.5°	7.4	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8
95°	23.9	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7
97.5°	47.4	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5
100°	65.2	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6
102.5°	84.6	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4
105°	111.8	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3
107.5°	143.0	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5
110°	163.0	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2



TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.8	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6
115°	211.6	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2
117.5°	238.2	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4
120°	257.6	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7
122.5°	274.1	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7
125°	299.2	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5
127.5°	321.9	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3
130°	336.4	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2
132.5°	351.1	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9
135°	370.2	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2
137.5°	389.6	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2
140°	402.3	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9
142.5°	412.8	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8
145°	429.5	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9
147.5°	443.9	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2
150°	453.4	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2
152.5°	461.3	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5
155°	472.9	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5
157.5°	481.9	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8
160°	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8
162.5°	492.0	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2
165°	498.3	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7
167.5°	503.0	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4
170°	505.7	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7
172.5°	507.4	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5
175°	509.7	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4
177.5°	510.1	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	10.5	10.2	9.7	9.5	9.4	9.3	9.1	9.0
90°	8.2	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.0	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.2	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	19.9	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.3	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	23.2	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	24.3	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	29.6	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	48.0	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331529-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	102.8	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	151.4	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	233.2	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	271.7	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.3	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.1	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.2	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	348.1	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	361.7	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.1	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.1	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	410.7	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	421.5	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	436.5	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	449.6	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	457.7	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.0	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.0	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.4	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.2	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	492.8	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.0	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.3	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.0	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.0	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.2	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)