

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331530-935

Luminaire Tested: **S122DIW-S675D435U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331530-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3620.0 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	111	111	111	111	104	104	104	104	91	91	91		80	80	80		69	69	69	64
1	101	97	93	89	95	91	87	84	80	77	75		70	68	67		61	60	58	54
2	92	84	78	73	86	79	74	69	70	66	62		62	58	56		54	51	49	45
3	84	74	67	61	79	70	63	58	62	57	52		55	51	47		48	45	42	38
4	77	66	58	51	72	62	55	49	55	49	45		49	44	40		43	39	36	33
5	71	59	50	44	66	55	48	42	49	43	39		44	39	35		39	35	32	29
6	65	53	44	38	61	50	42	37	45	38	34		40	35	31		35	31	28	25
7	60	48	40	34	56	45	38	32	41	34	30		36	31	27		32	28	25	22
8	56	43	35	30	53	41	34	29	37	31	27		33	28	24		29	25	22	20
9	52	40	32	27	49	38	31	26	34	28	24		30	26	22		27	23	20	18
10	49	37	29	24	46	35	28	23	31	26	22		28	23	20		25	21	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	2.4
10°-20°	241.9	6.7
20°-30°	355.5	9.8
30°-40°	412.9	11.4
40°-50°	412.5	11.4
50°-60°	359.7	9.9
60°-70°	266.0	7.3
70°-80°	150.6	4.2
80°-90°	42.4	1.2
90°-100°	29.3	0.8
100°-110°	91.0	2.5
110°-120°	155.5	4.3
120°-130°	204.5	5.6
130°-140°	229.5	6.3
140°-150°	225.0	6.2
150°-160°	188.8	5.2
160°-170°	125.2	3.5
170°-180°	43.8	1.2
0°-30°	683.3	18.9
0°-40°	1096.3	30.3
0°-60°	1868.5	51.6
0°-90°	2327.5	64.3
90°-120°	275.7	7.6
90°-150°	934.8	25.8
90°-180°	1293.0	35.7
0°-180°	3620.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	0	5	14	13	13	3
95°	20	24	25	25	24	23
105°	84	85	86	87	87	89
115°	156	158	158	157	156	154
125°	227	230	229	228	228	203
135°	294	298	299	298	297	227
145°	356	359	362	362	360	223
155°	408	409	410	412	411	188
165°	444	443	443	446	444	125
175°	462	460	460	462	460	44
180°	462	462	462	462	462	



TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.7	12.7	12.5	12.4	12.3	12.3	12.4	12.4	12.5	12.6	12.1
90°	0.4	1.5	2.5	3.5	4.6	6.0	7.9	9.8	11.7	13.7	13.5
92.5°	7.0	7.7	8.4	9.2	10.0	10.6	11.0	11.5	12.0	12.4	12.4
95°	20.3	21.2	22.0	22.9	23.8	24.3	24.5	24.6	24.8	25.0	25.0
97.5°	37.0	37.8	38.6	39.3	40.1	40.6	41.0	41.3	41.7	41.9	41.9
100°	49.5	50.2	50.9	51.7	52.3	52.8	53.0	53.3	53.6	53.8	53.8
102.5°	62.7	63.2	63.7	64.3	64.8	65.3	65.6	66.0	66.3	66.6	66.7
105°	83.9	84.1	84.4	84.6	84.9	85.2	85.3	85.5	85.7	85.8	86.0
107.5°	105.2	105.6	106.0	106.4	106.8	106.9	106.9	106.9	106.9	106.9	107.0
110°	119.0	119.5	120.0	120.5	121.1	121.3	121.3	121.3	121.3	121.3	121.3



TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	134.0	134.5	135.0	135.5	136.0	136.3	136.2	136.1	136.0	136.0	135.8
115°	156.0	156.5	157.0	157.6	158.1	158.3	158.1	157.9	157.7	157.6	157.5
117.5°	178.1	178.7	179.4	180.1	180.8	180.9	180.5	179.9	179.4	179.0	178.7
120°	192.7	193.4	194.1	194.8	195.4	195.4	194.8	194.1	193.4	192.7	192.7
122.5°	206.1	207.0	207.8	208.6	209.5	209.7	209.1	208.6	208.2	207.7	207.5
125°	227.0	227.8	228.6	229.4	230.1	230.4	230.1	229.9	229.6	229.4	229.1
127.5°	247.4	248.4	249.3	250.4	251.3	251.7	251.4	251.1	250.7	250.5	250.1
130°	260.2	261.3	262.4	263.6	264.7	265.2	265.0	264.8	264.7	264.5	264.3
132.5°	274.6	275.4	276.4	277.3	278.2	278.7	278.7	278.8	278.8	278.8	278.4
135°	293.8	294.7	295.7	296.6	297.6	298.1	298.3	298.4	298.6	298.8	298.7
137.5°	313.9	314.7	315.5	316.2	317.0	317.5	317.8	318.1	318.2	318.5	318.4
140°	326.1	326.9	327.7	328.5	329.2	329.8	330.3	330.7	331.1	331.6	331.6
142.5°	338.6	339.4	340.2	341.0	341.7	342.2	342.5	342.9	343.1	343.5	343.5
145°	356.5	357.1	357.7	358.3	359.0	359.6	360.1	360.6	361.1	361.6	361.7
147.5°	372.6	373.2	374.0	374.7	375.5	376.0	376.3	376.7	377.0	377.4	377.5
150°	383.5	384.0	384.5	385.0	385.6	386.0	386.3	386.7	387.0	387.4	387.6
152.5°	393.1	393.6	394.2	394.7	395.2	395.7	396.1	396.5	396.9	397.4	397.7
155°	407.6	407.9	408.1	408.5	408.7	409.0	409.2	409.5	409.7	410.0	410.4
157.5°	420.1	420.3	420.4	420.6	420.8	420.9	421.0	421.2	421.4	421.5	422.1
160°	427.6	427.7	427.9	428.1	428.3	428.3	428.4	428.5	428.6	428.7	429.2
162.5°	434.4	434.5	434.5	434.5	434.5	434.6	434.7	434.8	434.9	435.0	435.5
165°	443.5	443.4	443.3	443.2	443.2	443.2	443.2	443.2	443.2	443.2	443.8
167.5°	451.2	450.9	450.6	450.4	450.1	450.0	450.0	450.0	450.0	450.0	450.6
170°	455.2	455.0	454.7	454.4	454.2	454.0	453.9	453.8	453.7	453.7	454.3
172.5°	458.1	457.8	457.5	457.3	457.0	456.8	456.8	456.7	456.6	456.5	457.1
175°	461.5	461.2	461.0	460.7	460.5	460.2	460.0	459.9	459.7	459.5	460.1
177.5°	462.9	462.7	462.4	462.3	462.0	461.8	461.8	461.6	461.4	461.3	461.8
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3



TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	11.5	11.1	10.6	10.2	10.1	10.0	9.8	9.6
90°	13.3	13.2	13.0	12.9	13.0	13.1	13.2	13.3
92.5°	12.5	12.5	12.6	12.6	12.6	12.6	12.7	12.7
95°	25.0	25.0	25.0	24.9	24.7	24.5	24.4	24.2
97.5°	41.9	41.9	41.9	41.9	41.9	41.9	41.9	41.9
100°	53.8	53.8	53.8	53.8	53.7	53.6	53.6	53.5
102.5°	66.7	66.8	66.9	66.9	66.8	66.7	66.6	66.6
105°	86.2	86.4	86.5	86.6	86.6	86.6	86.6	86.6
107.5°	107.1	107.2	107.3	107.1	106.7	106.2	105.9	105.5
110°	121.3	121.3	121.3	121.1	120.9	120.6	120.4	120.1



TEST NUMBER: P331530-935

CATALOG NUMBER: S122DIW-S675D435U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	135.6	135.3	135.2	134.9	134.7	134.6	134.4	134.2
115°	157.4	157.3	157.2	157.0	156.8	156.5	156.3	156.0
117.5°	178.6	178.3	178.1	177.9	177.6	177.4	177.1	176.8
120°	192.7	192.7	192.7	192.6	192.3	192.1	191.8	191.6
122.5°	207.2	207.1	206.8	206.6	206.5	206.3	206.0	205.9
125°	228.9	228.6	228.3	228.2	228.1	228.0	227.9	227.8
127.5°	249.8	249.5	249.2	248.9	248.6	248.3	248.1	247.8
130°	264.2	264.0	263.8	263.6	263.2	262.9	262.5	262.2
132.5°	278.1	277.7	277.3	277.0	276.7	276.4	276.1	275.9
135°	298.6	298.5	298.4	298.3	298.0	297.7	297.5	297.2
137.5°	318.3	318.2	318.2	318.0	317.6	317.3	316.9	316.6
140°	331.6	331.6	331.6	331.4	331.1	330.7	330.4	330.0
142.5°	343.5	343.6	343.7	343.5	343.2	342.9	342.5	342.2
145°	361.8	361.9	362.0	361.8	361.4	361.1	360.8	360.4
147.5°	377.7	378.0	378.2	378.1	377.7	377.4	377.0	376.8
150°	387.9	388.1	388.4	388.4	388.1	387.9	387.6	387.4
152.5°	398.0	398.3	398.6	398.6	398.3	398.0	397.7	397.4
155°	410.9	411.3	411.7	411.8	411.6	411.3	411.0	410.8
157.5°	422.7	423.3	423.9	424.0	423.5	423.1	422.8	422.3
160°	429.7	430.2	430.8	430.8	430.5	430.2	429.8	429.5
162.5°	436.1	436.7	437.3	437.4	437.0	436.5	436.1	435.8
165°	444.4	445.0	445.6	445.7	445.2	444.8	444.4	443.9
167.5°	451.2	451.8	452.4	452.5	451.9	451.5	451.1	450.6
170°	454.9	455.5	456.1	456.2	455.6	455.1	454.6	454.1
172.5°	457.7	458.3	458.9	458.9	458.4	457.9	457.4	456.8
175°	460.7	461.3	461.9	462.0	461.5	461.0	460.5	459.9
177.5°	462.2	462.5	463.0	463.0	462.5	462.2	461.8	461.3
180°	462.3	462.3	462.3	462.3	462.3	462.3	462.3	462.3

(END OF REPORT)