

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331537-935

Luminaire Tested: **S122DIW-S675D970U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331537-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D970U935-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5857.9 lumens  
Efficiency: N/A  
Efficacy: 111.4 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20										
RC	80									70									50									30									10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0														
RCR																																						
0	106	106	106	106	96	96	96	96	80	80	80	64	64	64	50	50	50	43																				
1	97	93	89	85	88	85	82	79	70	68	66	57	55	54	45	44	43	37																				
2	88	81	75	70	81	75	70	65	62	58	55	50	48	46	40	38	37	32																				
3	81	72	65	59	74	66	60	55	55	51	47	45	42	39	36	34	32	27																				
4	74	64	56	50	68	59	52	47	49	44	40	40	37	34	32	30	28	24																				
5	68	57	49	43	62	53	46	41	44	39	35	36	33	30	29	26	24	21																				
6	63	51	43	38	57	47	40	35	40	35	31	33	29	26	27	24	22	19																				
7	58	46	39	33	53	43	36	31	36	31	27	30	26	23	24	22	19	17																				
8	54	42	35	29	49	39	32	28	33	28	24	28	24	21	22	20	18	15																				
9	50	39	31	26	46	36	29	25	30	25	22	25	22	19	21	18	16	14																				
10	47	35	28	24	43	33	27	22	28	23	20	24	20	17	19	17	15	13																				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	18466	18466	18466	18466
5°	20702	18585	16470	18585
10°	23722	18433	14254	18433
15°	26242	18094	12593	18094
20°	25844	17732	11478	17732
25°	23302	17250	10774	17250
30°	19257	16479	10260	16479
35°	14034	15672	9895	15672
40°	11209	14720	9691	14720
45°	9796	13618	9412	13618
50°	9206	12552	9231	12552
55°	8487	11468	8982	11468
60°	7776	10317	8603	10317
65°	7087	9287	8225	9287
70°	6430	8280	7676	8280
75°	5702	7155	6800	7155
80°	4909	5923	5477	5923
85°	4409	4409	3260	4409



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	108.9	1.9
10°-20°	316.6	5.4
20°-30°	459.5	7.8
30°-40°	484.9	8.3
40°-50°	429.4	7.3
50°-60°	342.6	5.8
60°-70°	232.9	4.0
70°-80°	119.4	2.0
80°-90°	31.6	0.5
90°-100°	37.9	0.6
100°-110°	139.1	2.4
110°-120°	371.8	6.3
120°-130°	613.7	10.5
130°-140°	652.7	11.1
140°-150°	606.6	10.4
150°-160°	487.7	8.3
160°-170°	314.3	5.4
170°-180°	108.2	1.8
0°-30°	885.1	15.1
0°-40°	1370.0	23.4
0°-60°	2142.0	36.6
0°-90°	2525.9	43.1
90°-120°	548.8	9.4
90°-150°	2421.8	41.3
90°-180°	3332.0	56.9
0°-180°	5857.9	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1144	1144	1144	1144	1144	
5°	1277	1147	1016	1147	1277	128
15°	1570	1082	753	1082	1570	433
25°	1308	968	605	968	1308	591
35°	712	795	502	795	712	463
45°	429	596	412	596	429	337
55°	302	407	319	407	302	270
65°	186	243	215	243	186	184
75°	91	115	109	115	91	98
85°	24	24	18	24	24	27
90°	22	1	22	1	22	11
95°	35	54	35	54	35	33
105°	62	250	62	250	62	65
115°	68	473	68	473	68	169
125°	703	669	703	669	703	609
135°	855	828	855	828	855	659
145°	975	960	975	960	975	610
155°	1058	1057	1058	1057	1058	488
165°	1112	1114	1112	1114	1112	314
175°	1133	1139	1133	1139	1133	108
180°	1137	1137	1137	1137	1137	



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1196.4	1196.7	1197.5	1191.8	1191.1	1191.1	1186.2	1182.0	1177.1	1170.4	1171.0
5°	1277.3	1282.1	1283.8	1278.6	1270.7	1269.8	1262.3	1250.0	1238.5	1229.3	1222.8
7.5°	1373.8	1375.7	1371.4	1364.4	1358.6	1348.1	1334.1	1320.5	1301.4	1283.9	1270.9
10°	1446.9	1449.6	1442.1	1432.0	1423.7	1411.4	1391.1	1370.5	1345.4	1321.2	1301.8
12.5°	1502.4	1509.0	1499.4	1498.1	1483.8	1466.9	1442.8	1432.4	1397.1	1363.4	1342.6
15°	1569.9	1569.5	1570.5	1562.1	1551.5	1548.9	1523.4	1495.7	1446.0	1426.2	1392.0
17.5°	1550.5	1557.1	1560.2	1560.1	1559.9	1558.2	1550.1	1532.6	1507.7	1475.6	1436.0
20°	1504.1	1512.9	1514.2	1524.3	1530.0	1537.5	1540.5	1535.7	1520.4	1493.5	1459.2
22.5°	1432.4	1434.8	1438.9	1454.7	1467.1	1485.7	1495.6	1511.8	1505.9	1492.8	1464.1
25°	1308.0	1303.6	1319.1	1326.9	1355.5	1385.3	1407.0	1430.6	1451.7	1464.5	1456.1
27.5°	1158.7	1152.2	1175.2	1196.2	1219.4	1251.8	1285.4	1325.0	1358.0	1399.2	1413.3
30°	1032.9	1036.8	1058.9	1081.2	1116.4	1162.1	1199.9	1243.5	1290.5	1336.6	1368.6
32.5°	897.2	912.4	926.3	960.6	991.5	1042.6	1097.9	1152.4	1211.0	1263.4	1313.1
35°	712.0	729.6	749.0	774.0	817.5	868.1	922.1	995.5	1075.6	1147.2	1206.1
37.5°	599.3	596.5	607.6	625.7	661.0	701.7	764.0	836.5	930.7	1014.9	1097.9
40°	531.8	530.0	538.0	554.7	581.5	611.4	665.9	729.6	817.1	919.9	1018.8
42.5°	485.4	486.5	490.9	502.7	521.0	545.6	586.4	640.7	720.7	817.6	923.9
45°	429.0	432.0	436.9	442.6	453.1	473.4	496.2	534.9	598.2	679.1	783.7
47.5°	388.4	388.5	393.4	398.4	404.7	416.0	434.7	458.9	503.6	569.5	659.4
50°	366.5	363.5	367.0	370.9	377.5	385.5	397.8	420.6	450.5	503.7	578.9
52.5°	339.8	339.9	343.1	344.6	350.5	358.3	369.6	385.5	412.5	454.1	515.9
55°	301.5	303.7	305.5	308.1	313.4	319.1	327.9	338.5	359.6	390.7	436.4
57.5°	265.4	266.1	267.9	272.9	276.3	281.5	289.9	299.5	313.2	336.3	370.7
60°	240.8	240.8	244.4	246.6	251.0	256.2	262.9	272.1	284.4	303.2	331.0
62.5°	218.3	218.0	219.4	223.0	226.4	231.3	237.9	245.7	257.3	274.1	296.9
65°	185.5	184.6	187.3	188.1	191.7	196.5	201.7	210.1	219.3	231.6	251.8
67.5°	153.9	154.9	156.3	158.0	159.9	165.0	168.5	174.4	182.2	192.4	206.1
70°	136.2	136.2	136.2	137.6	140.2	142.8	146.4	151.2	158.7	167.5	179.8
72.5°	116.6	118.0	119.3	118.6	121.9	123.5	127.7	130.4	137.6	143.2	154.1
75°	91.4	91.4	91.4	93.6	95.0	96.3	98.9	101.5	105.0	112.1	117.8
77.5°	68.2	68.0	68.4	69.0	70.4	72.0	72.8	75.2	78.4	81.6	86.5
80°	52.8	53.6	54.1	54.9	54.9	55.8	56.2	59.3	61.6	63.7	66.8
82.5°	40.8	41.0	41.1	41.2	41.6	42.1	43.2	44.3	45.0	46.8	49.2
85°	23.8	23.3	23.3	24.2	23.8	23.8	24.6	25.5	25.5	25.9	27.2
87.5°	13.6	13.5	13.8	13.3	13.3	13.5	13.3	12.8	13.0	13.2	13.2
90°	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3	17.4	16.4	15.0
92.5°	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1	19.5	19.1	18.3
95°	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9	33.0	32.1	30.8
97.5°	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4	43.7	43.0	40.0
100°	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9	48.4	46.9	43.8
102.5°	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0	50.1	48.2	44.2
105°	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2	52.2	50.2	46.1
107.5°	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1	68.2	70.3	74.1
110°	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4	125.7	144.0	196.8



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7	296.4	363.2	376.2
115°	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3	422.9	507.6	503.1
117.5°	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2	541.7	562.2	559.1
120°	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4	605.3	603.0	599.8
122.5°	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5	643.2	641.9	638.3
125°	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8	696.5	695.2	691.7
127.5°	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0	745.1	743.2	740.6
130°	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2	776.2	774.2	772.1
132.5°	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6	806.8	805.1	803.1
135°	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9	850.1	848.3	846.5
137.5°	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1	890.4	888.6	886.7
140°	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2	916.5	914.9	912.8
142.5°	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2	940.7	939.2	936.9
145°	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9	974.6	973.3	970.2
147.5°	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1	1004.2	1003.2	1000.1
150°	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2	1022.1	1021.0	1018.0
152.5°	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7	1038.5	1037.4	1034.7
155°	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9	1060.8	1059.6	1057.5
157.5°	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6	1079.3	1078.1	1076.5
160°	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5	1090.4	1089.3	1088.2
162.5°	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6	1100.4	1099.2	1098.2
165°	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5	1110.9
167.5°	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4	1123.1	1121.9	1121.4
170°	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7	1128.4	1127.1	1126.8
172.5°	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6	1132.4	1131.1	1130.7
175°	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9	1136.6	1135.3	1135.0
177.5°	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4	1137.4	1136.3	1136.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1173.5	1170.7	1169.0	1162.6	1157.0	1151.4	1149.6	1150.3	1142.6	1135.2	1132.0
5°	1219.3	1210.5	1202.1	1190.2	1176.2	1160.8	1152.9	1146.7	1131.4	1114.7	1105.0
7.5°	1260.2	1247.7	1231.6	1209.2	1188.8	1164.6	1149.2	1135.6	1113.0	1089.5	1075.0
10°	1285.2	1268.0	1247.3	1220.1	1195.1	1165.6	1145.0	1124.3	1097.9	1069.8	1052.2
12.5°	1306.7	1283.5	1263.2	1228.2	1198.6	1161.7	1137.2	1108.1	1080.4	1047.0	1029.8
15°	1357.7	1315.1	1276.3	1236.8	1200.3	1148.9	1121.7	1082.5	1046.0	1004.8	985.0
17.5°	1397.1	1349.3	1288.3	1238.0	1195.5	1138.6	1098.5	1051.7	1008.6	961.3	934.4
20°	1419.7	1364.7	1299.2	1239.5	1188.4	1123.4	1080.0	1032.0	981.5	928.2	899.2
22.5°	1433.0	1375.3	1310.5	1234.2	1174.4	1111.1	1056.4	1003.8	952.6	895.3	864.8
25°	1437.3	1384.5	1316.0	1229.8	1156.8	1085.2	1019.3	968.3	906.3	852.6	808.3
27.5°	1416.3	1378.5	1312.6	1221.5	1136.5	1052.7	979.3	921.5	856.1	797.9	753.3
30°	1390.7	1368.6	1304.5	1213.1	1120.3	1030.3	949.3	883.9	818.8	759.9	714.2
32.5°	1350.9	1346.2	1289.8	1201.1	1103.1	1001.8	918.1	851.9	779.8	721.9	678.4
35°	1272.9	1294.0	1258.4	1174.4	1070.7	961.2	870.7	795.1	720.4	665.0	624.1
37.5°	1168.3	1220.6	1211.3	1135.3	1026.9	917.1	817.2	738.1	666.9	611.1	570.9
40°	1096.1	1163.0	1172.7	1105.4	996.0	883.0	777.1	698.4	629.0	578.0	537.5
42.5°	1018.8	1096.9	1123.4	1069.5	962.2	847.1	741.2	659.7	591.0	541.4	505.6
45°	889.2	992.5	1040.3	1009.6	905.9	788.1	679.1	596.4	534.0	487.4	459.8
47.5°	767.9	880.8	945.2	934.4	843.2	726.5	618.8	539.5	478.7	441.5	416.7
50°	682.2	798.1	876.0	879.5	798.1	682.6	574.5	499.7	443.9	409.2	389.0
52.5°	607.6	718.3	803.2	821.8	747.9	636.9	534.8	460.4	411.2	379.3	361.2
55°	510.3	603.9	697.9	732.3	672.9	567.4	472.9	407.4	361.3	339.3	323.5
57.5°	424.2	502.3	589.2	627.1	590.5	500.2	411.6	354.7	317.3	298.0	285.9
60°	378.8	440.4	517.7	563.0	531.4	451.0	373.6	319.5	288.8	271.6	260.2
62.5°	336.7	391.2	456.6	498.0	480.8	404.9	335.6	287.9	261.3	245.2	237.0
65°	277.8	320.9	371.4	409.7	398.2	340.6	284.0	243.1	222.0	209.2	202.6
67.5°	228.8	259.8	294.9	328.4	319.2	278.4	232.9	201.0	185.3	174.4	170.4
70°	197.8	221.5	252.7	279.6	272.1	238.7	202.6	175.4	161.8	152.5	148.5
72.5°	168.2	187.8	211.5	233.5	228.4	200.7	170.7	150.1	139.6	131.0	127.8
75°	127.0	142.0	156.4	171.0	169.6	148.1	130.5	114.7	106.3	99.8	98.4
77.5°	93.8	102.1	112.0	120.6	118.2	105.9	92.1	83.1	76.9	72.5	71.8
80°	71.6	76.5	83.5	89.6	86.6	81.3	70.3	63.7	59.3	54.9	53.2
82.5°	51.9	56.8	61.0	64.3	62.0	57.1	50.3	45.8	43.1	40.2	39.4
85°	27.2	29.9	31.7	32.5	31.7	28.6	25.5	23.8	21.5	20.2	19.8
87.5°	13.3	13.0	12.7	13.0	11.5	11.2	9.4	7.9	7.9	8.0	7.7
90°	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9	2.8	4.8	6.9
92.5°	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6	16.4	16.3	16.1
95°	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5	47.4	41.4	35.4
97.5°	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2	89.1	72.2	55.1
100°	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6	120.5	95.5	70.5
102.5°	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1	183.7	178.5	173.1
105°	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1	255.6	261.1	266.6
107.5°	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7	324.2	328.6	332.9
110°	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5	368.3	372.1	376.0





TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6	410.0	413.4	416.8
115°	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0	476.1	479.3	482.4
117.5°	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4	536.0	539.4	542.9
120°	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9	578.7	581.3	584.1
122.5°	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8	615.6	618.5	621.4
125°	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8	671.2	673.6	676.0
127.5°	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7	722.4	725.0	727.6
130°	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0	754.9	757.9	760.7
132.5°	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9	787.4	789.9	792.3
135°	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7	830.6	833.5	836.5
137.5°	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9	873.0	875.0	877.1
140°	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2	900.7	902.2	903.6
142.5°	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9	924.2	925.6	926.9
145°	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1	959.9	959.8	959.6
147.5°	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6	991.8	991.1	990.4
150°	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6	1012.3	1011.0	1009.8
152.5°	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4	1029.9	1028.5	1027.1
155°	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2	1055.5	1053.9	1052.2
157.5°	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5	1076.1	1074.6	1073.2
160°	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1088.2	1087.1	1086.0
162.5°	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8	1098.7	1097.6	1096.5
165°	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0	1112.8	1111.7	1110.7
167.5°	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5	1123.3	1122.3	1121.2
170°	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4	1129.3	1128.3	1127.1
172.5°	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4	1133.2	1132.1	1131.1
175°	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4	1138.2	1136.9	1135.7
177.5°	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3	1139.3	1138.2	1137.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1128.5	1126.4	1119.0	1115.2	1108.8	1102.9	1099.0	1100.8	1102.2	1101.5	1100.4
5°	1096.1	1087.8	1075.0	1064.1	1056.2	1041.6	1035.5	1032.4	1029.8	1026.7	1023.6
7.5°	1057.7	1044.5	1026.2	1010.6	995.7	977.8	967.5	961.3	955.0	948.0	941.9
10°	1030.3	1011.8	992.5	970.4	952.9	936.6	922.1	912.5	903.7	895.4	889.2
12.5°	1001.4	980.2	956.2	926.2	906.8	883.6	881.3	864.3	850.6	845.4	838.2
15°	955.5	925.7	895.4	859.7	844.3	823.2	810.0	796.9	785.0	776.6	774.5
17.5°	903.4	864.7	834.6	809.0	783.8	762.2	750.0	739.4	729.7	718.5	717.0
20°	863.7	830.3	797.3	774.9	749.0	726.9	712.0	701.5	693.1	686.6	680.8
22.5°	826.0	789.5	759.3	734.8	709.2	691.5	679.7	669.5	662.5	655.2	649.9
25°	765.7	737.1	704.1	676.4	655.3	643.9	634.2	625.4	621.0	616.2	610.1
27.5°	712.8	681.1	650.2	628.8	610.3	600.1	593.2	587.3	583.2	580.3	576.9
30°	675.5	643.4	619.3	598.2	582.8	572.7	568.3	564.8	560.0	558.2	556.5
32.5°	639.7	610.8	590.1	571.8	557.2	550.5	546.5	543.4	539.6	537.8	534.3
35°	588.9	564.8	544.6	534.4	522.6	516.9	513.8	509.4	505.9	504.1	503.7
37.5°	541.2	520.2	507.0	494.0	489.0	485.4	481.2	478.2	477.2	476.9	476.5
40°	510.3	493.2	481.3	470.7	468.6	463.2	459.8	457.1	457.1	457.5	457.1
42.5°	482.2	466.7	456.3	447.2	444.6	441.4	437.9	437.7	438.5	440.0	438.5
45°	439.5	428.5	421.0	416.6	411.8	408.7	408.3	409.7	410.1	410.5	411.8
47.5°	400.3	393.0	386.2	381.4	379.3	378.8	378.2	380.6	382.6	383.4	385.5
50°	377.1	368.8	363.1	360.0	358.2	357.3	358.2	360.8	362.6	364.8	366.1
52.5°	351.1	345.2	341.2	338.9	338.2	338.7	338.9	341.9	344.7	345.4	346.1
55°	315.1	310.7	309.9	305.9	307.6	307.2	309.4	311.2	313.8	316.4	316.9
57.5°	279.3	275.8	273.4	273.7	274.2	276.2	278.0	281.1	284.0	286.7	287.0
60°	255.4	253.6	252.3	252.3	253.1	255.8	258.0	261.1	262.9	264.6	265.9
62.5°	233.6	231.8	230.5	231.2	233.5	235.1	237.6	239.3	241.0	242.8	243.4
65°	199.1	198.2	199.6	200.4	200.9	203.0	206.1	207.4	209.2	210.1	213.2
67.5°	167.4	167.6	167.4	168.6	171.2	171.7	174.6	177.6	178.0	179.7	181.7
70°	145.9	146.8	147.7	148.5	150.8	151.6	153.9	155.2	156.9	158.3	159.5
72.5°	126.2	126.4	127.3	127.1	129.0	130.9	132.8	134.1	135.8	137.5	138.8
75°	97.1	97.1	98.0	98.4	100.7	102.9	102.4	103.3	105.0	106.8	107.7
77.5°	70.9	70.0	70.9	71.4	72.1	74.0	74.3	75.5	77.5	76.9	77.9
80°	54.1	52.8	54.1	54.5	54.5	56.7	56.7	57.6	58.9	57.6	58.9
82.5°	38.6	38.0	38.9	39.0	39.7	39.8	40.6	40.7	42.0	41.4	42.0
85°	19.4	18.9	19.4	18.9	19.4	19.8	19.8	19.4	19.4	20.2	18.9
87.5°	7.7	7.7	7.7	8.0	7.9	7.8	7.7	7.8	8.1	7.6	7.7
90°	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3	19.2	20.1	20.8
92.5°	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1	20.5	21.0	21.4
95°	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9	34.9	35.7	36.1
97.5°	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4	45.1	45.9	46.3
100°	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9	51.3	52.8	53.6
102.5°	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0	53.9	55.8	57.0
105°	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2	56.2	58.2	59.6
107.5°	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1	64.1	62.1	61.4
110°	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4	89.1	70.9	62.1



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7	163.1	96.3	63.3
115°	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3	253.7	169.0	120.1
117.5°	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2	500.8	480.4	448.5
120°	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4	609.6	611.8	600.5
122.5°	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5	645.8	647.1	645.4
125°	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8	699.0	700.3	701.2
127.5°	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0	748.8	750.7	751.7
130°	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2	780.2	782.2	783.2
132.5°	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6	810.3	812.0	812.8
135°	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9	853.7	855.5	856.3
137.5°	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1	893.9	895.7	896.3
140°	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2	919.8	921.4	921.8
142.5°	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2	943.7	945.2	945.5
145°	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9	977.1	978.4	978.6
147.5°	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1	1006.1	1007.0	1007.1
150°	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2	1024.2	1025.4	1025.5
152.5°	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7	1040.7	1041.8	1041.8
155°	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9	1062.9	1064.0	1063.9
157.5°	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6	1081.8	1083.1	1083.0
160°	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5	1092.5	1093.6	1093.6
162.5°	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6	1102.9	1104.1	1104.0
165°	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6
167.5°	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4	1125.7	1127.0	1126.8
170°	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7	1130.9	1132.2	1132.0
172.5°	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6	1134.9	1136.2	1136.0
175°	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9	1139.2	1140.5	1140.2
177.5°	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4	1139.4	1140.4	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1096.9	1096.1	1096.1	1093.0	1096.1	1096.1	1096.9	1100.4	1101.5	1102.2	1100.8
5°	1017.5	1016.2	1014.0	1016.2	1014.0	1016.2	1017.5	1023.6	1026.7	1029.8	1032.4
7.5°	939.0	933.8	933.0	927.7	933.0	933.8	939.0	941.9	948.0	955.0	961.3
10°	881.7	878.1	877.7	869.4	877.7	878.1	881.7	889.2	895.4	903.7	912.5
12.5°	838.1	829.7	831.3	826.5	831.3	829.7	838.1	838.2	845.4	850.6	864.3
15°	762.6	762.6	760.8	753.4	760.8	762.6	762.6	774.5	776.6	785.0	796.9
17.5°	708.3	707.5	703.3	705.3	703.3	707.5	708.3	717.0	718.5	729.7	739.4
20°	676.0	673.4	668.0	668.0	668.0	673.4	676.0	680.8	686.6	693.1	701.5
22.5°	645.4	645.2	639.6	641.4	639.6	645.2	645.4	649.9	655.2	662.5	669.5
25°	609.6	606.1	603.5	604.8	603.5	606.1	609.6	610.1	616.2	621.0	625.4
27.5°	575.7	573.8	573.6	570.0	573.6	573.8	575.7	576.9	580.3	583.2	587.3
30°	556.0	551.6	552.5	550.3	552.5	551.6	556.0	556.5	558.2	560.0	564.8
32.5°	533.5	531.9	531.1	529.2	531.1	531.9	533.5	534.3	537.8	539.6	543.4
35°	502.8	503.3	501.1	502.0	501.1	503.3	502.8	503.7	504.1	505.9	509.4
37.5°	476.0	477.4	476.4	476.6	476.4	477.4	476.0	476.5	476.9	477.2	478.2
40°	458.4	458.4	458.4	459.8	458.4	458.4	458.4	457.1	457.5	457.1	457.1
42.5°	441.5	440.8	440.1	440.1	440.1	440.8	441.5	438.5	440.0	438.5	437.7
45°	412.7	414.1	414.5	412.2	414.5	414.1	412.7	411.8	410.5	410.1	409.7
47.5°	386.6	386.8	386.6	388.6	386.6	386.8	386.6	385.5	383.4	382.6	380.6
50°	368.3	367.5	368.3	367.5	368.3	367.5	368.3	366.1	364.8	362.6	360.8
52.5°	349.0	349.1	348.6	348.4	348.6	349.1	349.0	346.1	345.4	344.7	341.9
55°	318.7	319.5	319.1	319.1	319.1	319.5	318.7	316.9	316.4	313.8	311.2
57.5°	287.3	288.1	288.7	286.7	288.7	288.1	287.3	287.0	286.7	284.0	281.1
60°	265.4	267.7	267.3	266.4	267.3	267.7	265.4	265.9	264.6	262.9	261.1
62.5°	245.5	246.2	246.2	246.0	246.2	246.2	245.5	243.4	242.8	241.0	239.3
65°	214.5	215.3	214.0	215.3	214.0	215.3	214.5	213.2	210.1	209.2	207.4
67.5°	181.2	181.4	182.4	183.0	182.4	181.4	181.2	181.7	179.7	178.0	177.6
70°	160.4	160.0	161.3	162.6	161.3	160.0	160.4	159.5	158.3	156.9	155.2
72.5°	138.6	139.6	139.1	140.1	139.1	139.6	138.6	138.8	137.5	135.8	134.1
75°	106.8	108.1	107.7	109.0	107.7	108.1	106.8	107.7	106.8	105.0	103.3
77.5°	77.1	77.3	77.1	77.9	77.1	77.3	77.1	77.9	76.9	77.5	75.5
80°	58.9	58.0	57.2	58.9	57.2	58.0	58.9	58.9	57.6	58.9	57.6
82.5°	41.0	41.5	40.6	40.6	40.6	41.5	41.0	42.0	41.4	42.0	40.7
85°	18.9	18.4	17.6	17.6	17.6	18.4	18.9	18.9	20.2	19.4	19.4
87.5°	7.7	7.5	7.6	7.2	7.6	7.5	7.7	7.7	7.6	8.1	7.8
90°	21.1	21.4	21.9	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3
92.5°	21.5	21.8	22.0	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1
95°	35.9	35.7	35.6	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9
97.5°	46.6	46.8	47.0	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4
100°	54.0	54.4	54.8	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9
102.5°	57.5	58.0	58.5	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0
105°	60.4	61.0	61.8	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2
107.5°	62.2	62.9	63.6	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1
110°	62.8	63.5	64.2	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	63.9	64.5	65.1	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7
115°	106.9	93.8	80.6	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3
117.5°	405.2	362.0	318.7	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2
120°	575.9	551.2	526.5	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4
122.5°	640.6	635.8	631.0	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5
125°	701.8	702.3	702.8	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8
127.5°	751.8	751.9	752.0	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0
130°	782.9	782.7	782.6	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2
132.5°	812.5	812.4	812.2	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6
135°	855.9	855.5	855.1	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9
137.5°	895.7	895.0	894.4	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1
140°	920.9	920.0	919.0	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2
142.5°	944.6	943.7	942.8	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2
145°	977.7	976.7	975.9	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9
147.5°	1006.3	1005.6	1004.8	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1
150°	1024.6	1023.6	1022.7	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2
152.5°	1040.6	1039.4	1038.2	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7
155°	1062.4	1060.9	1059.5	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9
157.5°	1081.5	1080.1	1078.7	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6
160°	1092.3	1091.0	1089.8	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5
162.5°	1102.3	1100.8	1099.2	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6
165°	1115.3	1114.0	1112.8	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0
167.5°	1125.2	1123.5	1121.9	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4
170°	1130.4	1128.8	1127.1	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7
172.5°	1134.4	1132.7	1131.1	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6
175°	1138.3	1136.5	1134.7	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9
177.5°	1138.9	1137.6	1136.3	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1099.0	1102.9	1108.8	1115.2	1119.0	1126.4	1128.5	1132.0	1135.2	1142.6	1150.3
5°	1035.5	1041.6	1056.2	1064.1	1075.0	1087.8	1096.1	1105.0	1114.7	1131.4	1146.7
7.5°	967.5	977.8	995.7	1010.6	1026.2	1044.5	1057.7	1075.0	1089.5	1113.0	1135.6
10°	922.1	936.6	952.9	970.4	992.5	1011.8	1030.3	1052.2	1069.8	1097.9	1124.3
12.5°	881.3	883.6	906.8	926.2	956.2	980.2	1001.4	1029.8	1047.0	1080.4	1108.1
15°	810.0	823.2	844.3	859.7	895.4	925.7	955.5	985.0	1004.8	1046.0	1082.5
17.5°	750.0	762.2	783.8	809.0	834.6	864.7	903.4	934.4	961.3	1008.6	1051.7
20°	712.0	726.9	749.0	774.9	797.3	830.3	863.7	899.2	928.2	981.5	1032.0
22.5°	679.7	691.5	709.2	734.8	759.3	789.5	826.0	864.8	895.3	952.6	1003.8
25°	634.2	643.9	655.3	676.4	704.1	737.1	765.7	808.3	852.6	906.3	968.3
27.5°	593.2	600.1	610.3	628.8	650.2	681.1	712.8	753.3	797.9	856.1	921.5
30°	568.3	572.7	582.8	598.2	619.3	643.4	675.5	714.2	759.9	818.8	883.9
32.5°	546.5	550.5	557.2	571.8	590.1	610.8	639.7	678.4	721.9	779.8	851.9
35°	513.8	516.9	522.6	534.4	544.6	564.8	588.9	624.1	665.0	720.4	795.1
37.5°	481.2	485.4	489.0	494.0	507.0	520.2	541.2	570.9	611.1	666.9	738.1
40°	459.8	463.2	468.6	470.7	481.3	493.2	510.3	537.5	578.0	629.0	698.4
42.5°	437.9	441.4	444.6	447.2	456.3	466.7	482.2	505.6	541.4	591.0	659.7
45°	408.3	408.7	411.8	416.6	421.0	428.5	439.5	459.8	487.4	534.0	596.4
47.5°	378.2	378.8	379.3	381.4	386.2	393.0	400.3	416.7	441.5	478.7	539.5
50°	358.2	357.3	358.2	360.0	363.1	368.8	377.1	389.0	409.2	443.9	499.7
52.5°	338.9	338.7	338.2	338.9	341.2	345.2	351.1	361.2	379.3	411.2	460.4
55°	309.4	307.2	307.6	305.9	309.9	310.7	315.1	323.5	339.3	361.3	407.4
57.5°	278.0	276.2	274.2	273.7	273.4	275.8	279.3	285.9	298.0	317.3	354.7
60°	258.0	255.8	253.1	252.3	252.3	253.6	255.4	260.2	271.6	288.8	319.5
62.5°	237.6	235.1	233.5	231.2	230.5	231.8	233.6	237.0	245.2	261.3	287.9
65°	206.1	203.0	200.9	200.4	199.6	198.2	199.1	202.6	209.2	222.0	243.1
67.5°	174.6	171.7	171.2	168.6	167.4	167.6	167.4	170.4	174.4	185.3	201.0
70°	153.9	151.6	150.8	148.5	147.7	146.8	145.9	148.5	152.5	161.8	175.4
72.5°	132.8	130.9	129.0	127.1	127.3	126.4	126.2	127.8	131.0	139.6	150.1
75°	102.4	102.9	100.7	98.4	98.0	97.1	97.1	98.4	99.8	106.3	114.7
77.5°	74.3	74.0	72.1	71.4	70.9	70.0	70.9	71.8	72.5	76.9	83.1
80°	56.7	56.7	54.5	54.5	54.1	52.8	54.1	53.2	54.9	59.3	63.7
82.5°	40.6	39.8	39.7	39.0	38.9	38.0	38.6	39.4	40.2	43.1	45.8
85°	19.8	19.8	19.4	18.9	19.4	18.9	19.4	19.8	20.2	21.5	23.8
87.5°	7.7	7.8	7.9	8.0	7.7	7.7	7.7	7.7	8.0	7.9	7.9
90°	17.4	16.4	15.0	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9
92.5°	19.5	19.1	18.3	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6
95°	33.0	32.1	30.8	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5
97.5°	43.7	43.0	40.0	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2
100°	48.4	46.9	43.8	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6
102.5°	50.1	48.2	74.2	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1
105°	52.2	50.2	100.1	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1
107.5°	68.2	70.3	130.1	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7
110°	125.7	144.0	196.8	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	296.4	363.2	376.2	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6
115°	422.9	507.6	503.1	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0
117.5°	541.7	562.2	559.1	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4
120°	605.3	603.0	599.8	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9
122.5°	643.2	641.9	638.3	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8
125°	696.5	695.2	691.7	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8
127.5°	745.1	743.2	740.6	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7
130°	776.2	774.2	772.1	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0
132.5°	806.8	805.1	803.1	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9
135°	850.1	848.3	846.5	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7
137.5°	890.4	888.6	886.7	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9
140°	916.5	914.9	912.8	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2
142.5°	940.7	939.2	936.9	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9
145°	974.6	973.3	970.2	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1
147.5°	1004.2	1003.2	1000.1	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6
150°	1022.1	1021.0	1018.0	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6
152.5°	1038.5	1037.4	1034.7	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4
155°	1060.8	1059.6	1057.5	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2
157.5°	1079.3	1078.1	1076.5	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5
160°	1090.4	1089.3	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3
162.5°	1100.4	1099.2	1098.2	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8
165°	1112.8	1111.5	1110.9	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0
167.5°	1123.1	1121.9	1121.4	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5
170°	1128.4	1127.1	1126.8	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4
172.5°	1132.4	1131.1	1130.7	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4
175°	1136.6	1135.3	1135.0	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4
177.5°	1137.4	1136.3	1136.2	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1149.6	1151.4	1157.0	1162.6	1169.0	1170.7	1173.5	1171.0	1170.4	1177.1	1182.0
5°	1152.9	1160.8	1176.2	1190.2	1202.1	1210.5	1219.3	1222.8	1229.3	1238.5	1250.0
7.5°	1149.2	1164.6	1188.8	1209.2	1231.6	1247.7	1260.2	1270.9	1283.9	1301.4	1320.5
10°	1145.0	1165.6	1195.1	1220.1	1247.3	1268.0	1285.2	1301.8	1321.2	1345.4	1370.5
12.5°	1137.2	1161.7	1198.6	1228.2	1263.2	1283.5	1306.7	1342.6	1363.4	1397.1	1432.4
15°	1121.7	1148.9	1200.3	1236.8	1276.3	1315.1	1357.7	1392.0	1426.2	1446.0	1495.7
17.5°	1098.5	1138.6	1195.5	1238.0	1288.3	1349.3	1397.1	1436.0	1475.6	1507.7	1532.6
20°	1080.0	1123.4	1188.4	1239.5	1299.2	1364.7	1419.7	1459.2	1493.5	1520.4	1535.7
22.5°	1056.4	1111.1	1174.4	1234.2	1310.5	1375.3	1433.0	1464.1	1492.8	1505.9	1511.8
25°	1019.3	1085.2	1156.8	1229.8	1316.0	1384.5	1437.3	1456.1	1464.5	1451.7	1430.6
27.5°	979.3	1052.7	1136.5	1221.5	1312.6	1378.5	1416.3	1413.3	1399.2	1358.0	1325.0
30°	949.3	1030.3	1120.3	1213.1	1304.5	1368.6	1390.7	1368.6	1336.6	1290.5	1243.5
32.5°	918.1	1001.8	1103.1	1201.1	1289.8	1346.2	1350.9	1313.1	1263.4	1211.0	1152.4
35°	870.7	961.2	1070.7	1174.4	1258.4	1294.0	1272.9	1206.1	1147.2	1075.6	995.5
37.5°	817.2	917.1	1026.9	1135.3	1211.3	1220.6	1168.3	1097.9	1014.9	930.7	836.5
40°	777.1	883.0	996.0	1105.4	1172.7	1163.0	1096.1	1018.8	919.9	817.1	729.6
42.5°	741.2	847.1	962.2	1069.5	1123.4	1096.9	1018.8	923.9	817.6	720.7	640.7
45°	679.1	788.1	905.9	1009.6	1040.3	992.5	889.2	783.7	679.1	598.2	534.9
47.5°	618.8	726.5	843.2	934.4	945.2	880.8	767.9	659.4	569.5	503.6	458.9
50°	574.5	682.6	798.1	879.5	876.0	798.1	682.2	578.9	503.7	450.5	420.6
52.5°	534.8	636.9	747.9	821.8	803.2	718.3	607.6	515.9	454.1	412.5	385.5
55°	472.9	567.4	672.9	732.3	697.9	603.9	510.3	436.4	390.7	359.6	338.5
57.5°	411.6	500.2	590.5	627.1	589.2	502.3	424.2	370.7	336.3	313.2	299.5
60°	373.6	451.0	531.4	563.0	517.7	440.4	378.8	331.0	303.2	284.4	272.1
62.5°	335.6	404.9	480.8	498.0	456.6	391.2	336.7	296.9	274.1	257.3	245.7
65°	284.0	340.6	398.2	409.7	371.4	320.9	277.8	251.8	231.6	219.3	210.1
67.5°	232.9	278.4	319.2	328.4	294.9	259.8	228.8	206.1	192.4	182.2	174.4
70°	202.6	238.7	272.1	279.6	252.7	221.5	197.8	179.8	167.5	158.7	151.2
72.5°	170.7	200.7	228.4	233.5	211.5	187.8	168.2	154.1	143.2	137.6	130.4
75°	130.5	148.1	169.6	171.0	156.4	142.0	127.0	117.8	112.1	105.0	101.5
77.5°	92.1	105.9	118.2	120.6	112.0	102.1	93.8	86.5	81.6	78.4	75.2
80°	70.3	81.3	86.6	89.6	83.5	76.5	71.6	66.8	63.7	61.6	59.3
82.5°	50.3	57.1	62.0	64.3	61.0	56.8	51.9	49.2	46.8	45.0	44.3
85°	25.5	28.6	31.7	32.5	31.7	29.9	27.2	27.2	25.9	25.5	25.5
87.5°	9.4	11.2	11.5	13.0	12.7	13.0	13.3	13.2	13.2	13.0	12.8
90°	2.8	4.8	6.9	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3
92.5°	16.4	16.3	16.1	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1
95°	47.4	41.4	35.4	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9
97.5°	89.1	72.2	55.1	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4
100°	120.5	95.5	70.5	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9
102.5°	183.7	178.5	173.1	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0
105°	255.6	261.1	266.6	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2
107.5°	324.2	328.6	332.9	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1
110°	368.3	372.1	376.0	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4





TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	410.0	413.4	416.8	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7
115°	476.1	479.3	482.4	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3
117.5°	536.0	539.4	542.9	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2
120°	578.7	581.3	584.1	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4
122.5°	615.6	618.5	621.4	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5
125°	671.2	673.6	676.0	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8
127.5°	722.4	725.0	727.6	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0
130°	754.9	757.9	760.7	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2
132.5°	787.4	789.9	792.3	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6
135°	830.6	833.5	836.5	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9
137.5°	873.0	875.0	877.1	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1
140°	900.7	902.2	903.6	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2
142.5°	924.2	925.6	926.9	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2
145°	959.9	959.8	959.6	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9
147.5°	991.8	991.1	990.4	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1
150°	1012.3	1011.0	1009.8	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2
152.5°	1029.9	1028.5	1027.1	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7
155°	1055.5	1053.9	1052.2	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9
157.5°	1076.1	1074.6	1073.2	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6
160°	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5
162.5°	1098.7	1097.6	1096.5	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6
165°	1112.8	1111.7	1110.7	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0
167.5°	1123.3	1122.3	1121.2	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4
170°	1129.3	1128.3	1127.1	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7
172.5°	1133.2	1132.1	1131.1	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6
175°	1138.2	1136.9	1135.7	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9
177.5°	1139.3	1138.2	1137.2	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7	1143.7
2.5°	1186.2	1191.1	1191.1	1191.8	1197.5	1196.7	1196.4
5°	1262.3	1269.8	1270.7	1278.6	1283.8	1282.1	1277.3
7.5°	1334.1	1348.1	1358.6	1364.4	1371.4	1375.7	1373.8
10°	1391.1	1411.4	1423.7	1432.0	1442.1	1449.6	1446.9
12.5°	1442.8	1466.9	1483.8	1498.1	1499.4	1509.0	1502.4
15°	1523.4	1548.9	1551.5	1562.1	1570.5	1569.5	1569.9
17.5°	1550.1	1558.2	1559.9	1560.1	1560.2	1557.1	1550.5
20°	1540.5	1537.5	1530.0	1524.3	1514.2	1512.9	1504.1
22.5°	1495.6	1485.7	1467.1	1454.7	1438.9	1434.8	1432.4
25°	1407.0	1385.3	1355.5	1326.9	1319.1	1303.6	1308.0
27.5°	1285.4	1251.8	1219.4	1196.2	1175.2	1152.2	1158.7
30°	1199.9	1162.1	1116.4	1081.2	1058.9	1036.8	1032.9
32.5°	1097.9	1042.6	991.5	960.6	926.3	912.4	897.2
35°	922.1	868.1	817.5	774.0	749.0	729.6	712.0
37.5°	764.0	701.7	661.0	625.7	607.6	596.5	599.3
40°	665.9	611.4	581.5	554.7	538.0	530.0	531.8
42.5°	586.4	545.6	521.0	502.7	490.9	486.5	485.4
45°	496.2	473.4	453.1	442.6	436.9	432.0	429.0
47.5°	434.7	416.0	404.7	398.4	393.4	388.5	388.4
50°	397.8	385.5	377.5	370.9	367.0	363.5	366.5
52.5°	369.6	358.3	350.5	344.6	343.1	339.9	339.8
55°	327.9	319.1	313.4	308.1	305.5	303.7	301.5
57.5°	289.9	281.5	276.3	272.9	267.9	266.1	265.4
60°	262.9	256.2	251.0	246.6	244.4	240.8	240.8
62.5°	237.9	231.3	226.4	223.0	219.4	218.0	218.3
65°	201.7	196.5	191.7	188.1	187.3	184.6	185.5
67.5°	168.5	165.0	159.9	158.0	156.3	154.9	153.9
70°	146.4	142.8	140.2	137.6	136.2	136.2	136.2
72.5°	127.7	123.5	121.9	118.6	119.3	118.0	116.6
75°	98.9	96.3	95.0	93.6	91.4	91.4	91.4
77.5°	72.8	72.0	70.4	69.0	68.4	68.0	68.2
80°	56.2	55.8	54.9	54.9	54.1	53.6	52.8
82.5°	43.2	42.1	41.6	41.2	41.1	41.0	40.8
85°	24.6	23.8	23.8	24.2	23.3	23.3	23.8
87.5°	13.3	13.5	13.3	13.3	13.8	13.5	13.6
90°	19.2	20.1	20.8	21.1	21.4	21.9	22.2
92.5°	20.5	21.0	21.4	21.5	21.8	22.0	22.2
95°	34.9	35.7	36.1	35.9	35.7	35.6	35.4
97.5°	45.1	45.9	46.3	46.6	46.8	47.0	47.2
100°	51.3	52.8	53.6	54.0	54.4	54.8	55.1
102.5°	53.9	55.8	57.0	57.5	58.0	58.5	59.1
105°	56.2	58.2	59.6	60.4	61.0	61.8	62.5
107.5°	64.1	62.1	61.4	62.2	62.9	63.6	64.3
110°	89.1	70.9	62.1	62.8	63.5	64.2	65.0



TEST NUMBER: P331537-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	163.1	96.3	63.3	63.9	64.5	65.1	65.7
115°	253.7	169.0	120.1	106.9	93.8	80.6	67.5
117.5°	500.8	480.4	448.5	405.2	362.0	318.7	275.4
120°	609.6	611.8	600.5	575.9	551.2	526.5	501.9
122.5°	645.8	647.1	645.4	640.6	635.8	631.0	626.3
125°	699.0	700.3	701.2	701.8	702.3	702.8	703.4
127.5°	748.8	750.7	751.7	751.8	751.9	752.0	752.1
130°	780.2	782.2	783.2	782.9	782.7	782.6	782.4
132.5°	810.3	812.0	812.8	812.5	812.4	812.2	812.0
135°	853.7	855.5	856.3	855.9	855.5	855.1	854.8
137.5°	893.9	895.7	896.3	895.7	895.0	894.4	893.8
140°	919.8	921.4	921.8	920.9	920.0	919.0	918.2
142.5°	943.7	945.2	945.5	944.6	943.7	942.8	941.8
145°	977.1	978.4	978.6	977.7	976.7	975.9	974.9
147.5°	1006.1	1007.0	1007.1	1006.3	1005.6	1004.8	1004.0
150°	1024.2	1025.4	1025.5	1024.6	1023.6	1022.7	1021.8
152.5°	1040.7	1041.8	1041.8	1040.6	1039.4	1038.2	1037.0
155°	1062.9	1064.0	1063.9	1062.4	1060.9	1059.5	1058.0
157.5°	1081.8	1083.1	1083.0	1081.5	1080.1	1078.7	1077.3
160°	1092.5	1093.6	1093.6	1092.3	1091.0	1089.8	1088.5
162.5°	1102.9	1104.1	1104.0	1102.3	1100.8	1099.2	1097.7
165°	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5
167.5°	1125.7	1127.0	1126.8	1125.2	1123.5	1121.9	1120.2
170°	1130.9	1132.2	1132.0	1130.4	1128.8	1127.1	1125.5
172.5°	1134.9	1136.2	1136.0	1134.4	1132.7	1131.1	1129.5
175°	1139.2	1140.5	1140.2	1138.3	1136.5	1134.7	1132.9
177.5°	1139.4	1140.4	1140.3	1138.9	1137.6	1136.3	1135.1
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0

(END OF REPORT)