

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331542-935

Luminaire Tested: **S122DIW-S675D970U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331542-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D970U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5219.3 lumens
Efficiency: N/A
Efficacy: 99.2 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 52.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	65	65	65	51	51	51	45
1	97	92	88	85	88	85	81	78	70	68	66	57	56	54	45	44	43	38
2	88	81	74	69	80	74	69	64	62	58	55	50	48	45	40	38	36	31
3	80	71	64	58	73	65	59	54	54	50	46	44	41	38	35	33	31	27
4	73	63	55	49	67	58	51	45	48	43	39	40	36	33	32	29	27	23
5	67	56	48	42	61	51	44	39	43	38	34	36	32	28	28	26	23	20
6	62	50	42	36	57	46	39	34	39	33	29	32	28	25	26	23	20	17
7	57	45	37	32	52	42	35	30	35	30	26	29	25	22	24	20	18	15
8	53	41	33	28	49	38	31	26	32	27	23	27	23	20	22	19	16	14
9	49	37	30	25	45	35	28	23	29	24	20	25	20	18	20	17	15	13
10	46	34	27	22	42	32	25	21	27	22	18	23	19	16	18	16	13	11

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	14759	14759	14759
5°	14815	14603	14687
10°	14728	14454	14526
15°	14544	14265	14252
20°	14287	13984	13969
25°	14031	13639	13639
30°	13699	13323	13207
35°	13391	12942	12751
40°	13004	12560	12319
45°	12622	12184	11880
50°	12208	11788	11369
55°	11778	11333	10911
60°	11296	10785	10388
65°	10777	10243	9773
70°	10126	9583	9130
75°	9214	8827	8609
80°	8173	7922	7513
85°	6688	6354	5687



TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	86.0	1.6
10°-20°	241.9	4.6
20°-30°	355.5	6.8
30°-40°	412.9	7.9
40°-50°	412.5	7.9
50°-60°	359.7	6.9
60°-70°	266.0	5.1
70°-80°	150.6	2.9
80°-90°	44.6	0.9
90°-100°	65.5	1.3
100°-110°	203.4	3.9
110°-120°	347.6	6.7
120°-130°	457.2	8.8
130°-140°	513.1	9.8
140°-150°	503.1	9.6
150°-160°	422.0	8.1
160°-170°	279.9	5.4
170°-180°	97.8	1.9
0°-30°	683.3	13.1
0°-40°	1096.3	21.0
0°-60°	1868.5	35.8
0°-90°	2329.7	44.6
90°-120°	616.5	11.8
90°-150°	2089.9	40.0
90°-180°	2890.0	55.4
0°-180°	5219.3	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	914	914	914	914	914	
5°	914	910	901	907	906	87
15°	870	865	853	857	853	245
25°	788	780	766	767	766	362
35°	679	670	657	651	647	424
45°	553	546	534	524	520	426
55°	418	413	403	392	388	374
65°	282	277	268	260	256	279
75°	148	146	142	137	138	158
85°	36	35	34	32	31	41
90°	1	12	30	29	30	4
95°	45	54	56	56	54	52
105°	188	190	192	194	194	198
115°	349	354	352	351	349	345
125°	508	515	513	510	509	453
135°	657	666	668	667	664	507
145°	797	803	808	809	806	498
155°	911	914	916	920	918	419
165°	992	991	991	996	992	280
175°	1032	1029	1027	1033	1028	98
180°	1033	1033	1033	1033	1033	



TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	918.3	917.6	916.8	916.0	915.2	914.0	912.2	910.5	908.8	907.1	908.6
5°	914.1	913.3	912.6	911.8	911.0	909.6	907.4	905.3	903.1	901.0	902.5
7.5°	906.0	904.8	903.6	902.4	901.2	899.5	897.3	895.1	892.9	890.7	892.3
10°	898.3	896.9	895.5	894.1	892.9	891.0	888.6	886.3	883.9	881.6	883.1
12.5°	887.8	886.6	885.3	884.1	882.9	881.1	878.7	876.4	874.1	871.8	872.9
15°	870.1	869.0	867.8	866.7	865.5	863.6	861.1	858.5	856.0	853.4	854.3
17.5°	847.7	846.4	845.3	844.1	843.0	841.1	838.5	835.9	833.4	830.8	831.7
20°	831.5	830.3	829.1	827.9	826.8	824.8	822.1	819.4	816.7	813.9	814.5
22.5°	815.3	813.6	812.0	810.4	808.7	806.7	804.1	801.5	798.9	796.3	796.4
25°	787.6	786.0	784.5	782.8	781.3	778.9	775.5	772.2	768.9	765.6	765.9
27.5°	755.9	754.5	753.1	751.7	750.3	748.3	745.6	743.0	740.4	737.8	737.2
30°	734.8	733.2	731.7	730.1	728.6	726.3	723.4	720.5	717.6	714.6	714.0
32.5°	712.3	711.0	709.8	708.5	707.3	705.2	702.1	699.0	695.9	692.8	691.7
35°	679.4	677.5	675.5	673.6	671.6	669.1	666.0	662.8	659.7	656.6	655.4
37.5°	642.3	640.6	638.9	637.1	635.5	633.0	629.9	626.8	623.7	620.5	619.1
40°	617.0	615.4	613.9	612.3	610.8	608.5	605.3	602.2	599.1	595.9	594.2
42.5°	592.5	590.8	589.3	587.7	586.2	583.8	580.7	577.6	574.5	571.4	569.4
45°	552.8	551.5	550.1	548.8	547.4	545.3	542.3	539.4	536.5	533.6	531.4
47.5°	513.5	512.2	510.9	509.6	508.3	506.2	503.1	500.1	497.1	494.0	491.7
50°	486.0	485.1	484.1	483.1	482.2	480.3	477.6	474.8	472.1	469.3	466.7
52.5°	459.3	458.1	456.8	455.5	454.2	452.3	449.7	447.1	444.5	442.0	439.7
55°	418.4	417.2	416.0	414.8	413.7	411.9	409.6	407.3	404.9	402.6	400.2
57.5°	377.2	376.3	375.4	374.4	373.5	371.8	369.2	366.6	364.0	361.4	359.1
60°	349.8	349.0	348.3	347.5	346.7	344.9	342.2	339.5	336.7	334.0	331.8
62.5°	323.1	321.8	320.6	319.3	318.1	316.4	314.4	312.2	310.1	308.0	306.0
65°	282.1	280.9	279.8	278.6	277.4	275.9	274.0	272.0	270.0	268.1	266.3
67.5°	240.5	239.5	238.6	237.6	236.7	235.4	233.6	231.9	230.1	228.3	227.0
70°	214.5	213.7	212.9	212.2	211.4	210.1	208.3	206.6	204.8	203.0	201.6
72.5°	187.8	186.9	186.1	185.4	184.6	183.7	182.5	181.4	180.3	179.1	177.8
75°	147.7	147.2	146.9	146.5	146.1	145.4	144.5	143.4	142.5	141.5	140.3
77.5°	111.8	111.2	110.5	109.8	109.2	108.7	108.2	107.8	107.5	107.0	106.5
80°	87.9	87.7	87.5	87.3	87.1	86.8	86.4	86.0	85.7	85.2	84.6
82.5°	65.4	65.3	65.3	65.3	65.3	65.1	64.8	64.7	64.4	64.1	63.5
85°	36.1	35.8	35.6	35.5	35.2	35.0	34.9	34.7	34.4	34.3	33.7
87.5°	12.8	13.0	13.2	13.3	13.4	13.8	14.3	14.9	15.4	15.9	15.4
90°	0.9	3.2	5.5	7.8	10.2	13.4	17.7	22.0	26.3	30.5	30.1
92.5°	15.5	17.2	18.9	20.7	22.4	23.7	24.7	25.7	26.7	27.7	27.8
95°	45.4	47.3	49.2	51.1	53.1	54.2	54.7	55.0	55.4	55.8	55.8
97.5°	82.8	84.6	86.3	88.0	89.6	90.9	91.6	92.4	93.1	93.8	93.8
100°	110.7	112.3	113.8	115.4	116.9	118.0	118.6	119.2	119.8	120.4	120.4
102.5°	140.1	141.3	142.5	143.8	145.0	146.0	146.7	147.5	148.2	149.0	149.1
105°	187.5	188.0	188.6	189.2	189.9	190.3	190.7	191.1	191.5	191.8	192.3
107.5°	235.3	236.2	236.9	237.8	238.7	239.1	239.1	239.1	239.1	239.1	239.3
110°	266.0	267.2	268.3	269.5	270.6	271.2	271.2	271.2	271.2	271.2	271.2



TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	299.5	300.7	301.8	303.0	304.1	304.6	304.4	304.3	304.2	304.0	303.5
115°	348.8	350.0	351.1	352.3	353.4	353.9	353.4	353.1	352.7	352.3	352.1
117.5°	398.0	399.6	401.1	402.7	404.2	404.4	403.4	402.3	401.2	400.1	399.7
120°	430.8	432.4	433.9	435.5	437.0	437.0	435.5	433.9	432.4	430.8	430.8
122.5°	460.8	462.7	464.5	466.4	468.2	468.6	467.5	466.5	465.4	464.3	463.8
125°	507.6	509.3	511.0	512.8	514.5	515.1	514.5	513.9	513.3	512.8	512.2
127.5°	553.1	555.3	557.5	559.7	561.9	562.7	562.0	561.3	560.6	559.9	559.1
130°	581.7	584.2	586.7	589.3	591.8	592.8	592.5	592.0	591.7	591.2	590.9
132.5°	613.7	615.8	617.9	619.9	622.0	623.0	623.1	623.2	623.3	623.4	622.5
135°	656.7	658.8	660.9	663.1	665.2	666.4	666.8	667.2	667.6	668.0	667.8
137.5°	701.8	703.6	705.3	707.1	708.8	710.0	710.4	710.9	711.4	712.0	711.8
140°	729.0	730.8	732.5	734.3	736.0	737.4	738.4	739.3	740.3	741.2	741.2
142.5°	757.0	758.7	760.4	762.2	764.0	765.2	765.8	766.5	767.2	767.8	767.9
145°	797.0	798.4	799.8	801.2	802.5	803.7	804.9	806.1	807.3	808.4	808.6
147.5°	832.8	834.5	836.1	837.7	839.3	840.5	841.3	842.1	842.8	843.6	844.0
150°	857.2	858.4	859.5	860.7	861.9	862.9	863.7	864.4	865.2	866.0	866.5
152.5°	878.9	880.0	881.2	882.4	883.6	884.6	885.5	886.4	887.3	888.3	889.0
155°	911.3	911.9	912.5	913.1	913.6	914.2	914.8	915.4	915.9	916.5	917.5
157.5°	939.0	939.4	939.8	940.2	940.6	941.0	941.3	941.7	942.0	942.4	943.7
160°	955.8	956.1	956.6	956.9	957.3	957.6	957.9	958.0	958.2	958.4	959.6
162.5°	971.1	971.2	971.3	971.4	971.5	971.6	971.8	972.0	972.2	972.3	973.7
165°	991.5	991.4	991.2	990.9	990.8	990.7	990.7	990.7	990.7	990.7	992.0
167.5°	1008.7	1008.1	1007.5	1006.9	1006.3	1006.0	1006.0	1005.9	1005.9	1005.8	1007.2
170°	1017.7	1017.1	1016.6	1016.0	1015.4	1015.0	1014.8	1014.6	1014.4	1014.3	1015.5
172.5°	1024.0	1023.4	1022.8	1022.3	1021.7	1021.2	1021.1	1020.9	1020.7	1020.5	1021.8
175°	1031.7	1031.0	1030.5	1029.9	1029.3	1028.8	1028.5	1028.0	1027.7	1027.3	1028.6
177.5°	1034.8	1034.3	1033.9	1033.4	1032.9	1032.5	1032.3	1031.9	1031.7	1031.3	1032.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4



TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	914.1	914.1	914.1	914.1	914.1	914.1	914.1	914.1
2.5°	910.2	911.8	913.3	914.0	913.6	913.3	913.0	912.7
5°	904.0	905.6	907.1	907.8	907.4	907.0	906.6	906.2
7.5°	893.9	895.4	897.0	897.5	897.1	896.7	896.3	895.9
10°	884.7	886.3	887.9	888.3	887.8	887.2	886.6	886.0
12.5°	873.9	875.0	876.2	876.4	876.0	875.6	875.2	874.8
15°	855.1	855.8	856.6	856.5	855.5	854.5	853.6	852.6
17.5°	832.6	833.4	834.4	834.4	833.4	832.5	831.6	830.6
20°	815.1	815.7	816.2	816.1	815.4	814.6	813.8	813.0
22.5°	796.6	796.7	796.8	796.6	796.2	795.7	795.2	794.8
25°	766.4	766.7	767.2	767.2	766.7	766.4	765.9	765.6
27.5°	736.6	736.1	735.5	734.7	733.7	732.8	731.8	730.9
30°	713.4	712.8	712.2	711.5	710.8	710.0	709.2	708.4
32.5°	690.7	689.7	688.5	687.7	686.9	686.1	685.3	684.5
35°	654.3	653.1	651.9	650.8	649.9	648.8	647.9	646.9
37.5°	617.7	616.2	614.8	613.5	612.6	611.7	610.8	609.8
40°	592.5	590.6	588.9	587.6	586.9	586.1	585.3	584.5
42.5°	567.5	565.6	563.7	562.1	561.0	560.0	558.9	557.8
45°	529.3	527.1	525.0	523.5	522.7	521.9	521.2	520.3
47.5°	489.5	487.2	484.9	483.2	482.1	481.0	479.8	478.7
50°	463.9	461.2	458.4	456.6	455.6	454.6	453.7	452.6
52.5°	437.4	435.1	432.9	431.1	429.8	428.5	427.2	425.9
55°	397.9	395.5	393.2	391.5	390.5	389.6	388.6	387.6
57.5°	356.8	354.5	352.2	350.7	349.9	349.2	348.4	347.7
60°	329.7	327.5	325.4	324.1	323.5	322.9	322.3	321.7
62.5°	304.0	302.0	300.1	298.7	297.9	297.1	296.4	295.7
65°	264.6	262.8	261.1	259.7	258.7	257.7	256.8	255.8
67.5°	225.6	224.3	222.9	221.8	221.0	220.2	219.5	218.7
70°	200.3	199.0	197.6	196.5	195.7	194.9	194.2	193.4
72.5°	176.4	175.0	173.7	172.6	172.0	171.4	170.8	170.1
75°	139.1	138.0	136.8	136.5	136.8	137.2	137.6	138.0
77.5°	105.9	105.3	104.7	104.2	103.6	103.1	102.5	101.9
80°	84.1	83.5	82.9	82.4	82.1	81.6	81.3	80.8
82.5°	62.7	61.9	61.2	60.8	60.7	60.6	60.5	60.4
85°	33.1	32.5	31.9	31.5	31.3	31.2	31.0	30.7
87.5°	14.9	14.3	13.8	13.4	13.3	13.2	13.1	13.0
90°	29.7	29.4	28.9	28.8	29.1	29.3	29.4	29.6
92.5°	27.9	28.0	28.1	28.1	28.2	28.2	28.2	28.2
95°	55.8	55.8	55.8	55.6	55.2	54.8	54.4	54.1
97.5°	93.8	93.8	93.8	93.8	93.8	93.8	93.7	93.7
100°	120.4	120.4	120.4	120.3	120.0	119.9	119.7	119.5
102.5°	149.3	149.4	149.6	149.6	149.4	149.1	149.0	148.8
105°	192.6	193.0	193.4	193.6	193.6	193.6	193.6	193.6
107.5°	239.4	239.6	239.7	239.4	238.5	237.5	236.7	235.8
110°	271.2	271.2	271.2	271.0	270.4	269.8	269.1	268.6



TEST NUMBER: P331542-935

CATALOG NUMBER: S122DIW-S675D970U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	303.1	302.6	302.1	301.7	301.3	300.8	300.4	300.0
115°	351.9	351.7	351.5	351.1	350.6	350.0	349.4	348.8
117.5°	399.2	398.7	398.2	397.7	397.2	396.6	396.0	395.4
120°	430.8	430.8	430.8	430.5	429.9	429.4	428.8	428.2
122.5°	463.4	462.9	462.4	462.0	461.6	461.2	460.7	460.3
125°	511.6	511.0	510.5	510.1	509.9	509.7	509.5	509.3
127.5°	558.4	557.8	557.1	556.4	555.8	555.2	554.6	554.0
130°	590.5	590.1	589.7	589.1	588.3	587.5	586.8	586.0
132.5°	621.6	620.8	619.9	619.2	618.6	617.9	617.3	616.7
135°	667.6	667.4	667.2	666.8	666.2	665.6	665.1	664.5
137.5°	711.6	711.5	711.4	710.8	710.1	709.3	708.5	707.7
140°	741.2	741.2	741.2	740.9	740.1	739.3	738.6	737.8
142.5°	768.1	768.3	768.4	768.1	767.3	766.5	765.8	765.0
145°	808.8	809.0	809.2	808.9	808.1	807.4	806.6	805.8
147.5°	844.5	844.9	845.3	845.2	844.5	843.7	843.0	842.2
150°	867.1	867.7	868.3	868.3	867.7	867.1	866.5	866.0
152.5°	889.8	890.5	891.2	891.2	890.5	889.8	889.0	888.3
155°	918.5	919.5	920.4	920.6	920.1	919.5	918.9	918.3
157.5°	945.0	946.3	947.6	947.8	946.9	946.0	945.0	944.1
160°	960.7	961.9	963.0	963.3	962.5	961.7	961.0	960.2
162.5°	975.0	976.3	977.7	977.8	976.9	975.9	975.0	974.1
165°	993.4	994.7	996.1	996.3	995.3	994.4	993.4	992.4
167.5°	1008.6	1010.0	1011.2	1011.4	1010.5	1009.4	1008.4	1007.5
170°	1016.9	1018.3	1019.7	1019.8	1018.6	1017.4	1016.2	1015.1
172.5°	1023.2	1024.6	1025.9	1026.1	1024.8	1023.7	1022.5	1021.4
175°	1030.0	1031.4	1032.7	1032.9	1031.7	1030.5	1029.3	1028.2
177.5°	1033.2	1034.1	1035.0	1035.0	1034.1	1033.2	1032.3	1031.3
180°	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4	1033.4

(END OF REPORT)