

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331529-930

Luminaire Tested: **S122DIW-S675D435U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331529-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S675D435U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 675 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3614.7 lumens
Efficiency: N/A
Efficacy: 95.9 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 37.7
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20					
RC	80					70					50					30					10					0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0		
RCR																										
0	110	110	110	110	103	103	103	103	89	89	89	77	77	77	66	66	66	66	66	66	66	66	66	61		
1	100	96	92	88	94	90	86	83	78	76	74	68	66	64	59	57	56	56	56	56	56	56	56	51		
2	91	84	77	72	85	79	73	68	69	65	61	60	57	54	52	49	47	47	47	47	47	47	47	43		
3	83	74	66	60	78	69	62	57	61	56	51	53	49	46	46	43	40	40	40	40	40	40	40	36		
4	76	65	57	51	71	61	54	49	54	48	44	47	43	39	41	37	35	35	35	35	35	35	35	31		
5	70	58	50	44	65	55	47	42	48	42	38	42	38	34	37	33	30	30	30	30	30	30	30	27		
6	65	52	44	38	60	49	42	36	44	38	33	38	33	30	33	30	27	27	27	27	27	27	27	24		
7	60	47	39	33	56	45	37	32	40	34	29	35	30	26	31	27	24	24	24	24	24	24	24	21		
8	56	43	35	30	52	41	33	28	36	30	26	32	27	24	28	24	21	21	21	21	21	21	21	19		
9	52	39	32	27	48	37	30	25	33	27	23	29	25	21	26	22	19	19	19	19	19	19	19	17		
10	48	36	29	24	45	34	27	23	31	25	21	27	23	19	24	20	17	17	17	17	17	17	17	16		

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	13976	13976	13976
5°	14029	13827	13908
10°	13946	13686	13754
15°	13772	13508	13494
20°	13527	13242	13228
25°	13286	12916	12916
30°	12972	12616	12506
35°	12682	12254	12073
40°	12313	11894	11666
45°	11953	11536	11250
50°	11560	11163	10766
55°	11153	10731	10331
60°	10698	10214	9836
65°	10208	9700	9253
70°	9588	9073	8644
75°	8721	8359	8153
80°	7736	7504	7122
85°	6336	6002	5391



TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	81.4	2.3
10°-20°	229.0	6.3
20°-30°	336.6	9.3
30°-40°	391.0	10.8
40°-50°	390.6	10.8
50°-60°	340.6	9.4
60°-70°	251.9	7.0
70°-80°	142.7	3.9
80°-90°	39.6	1.1
90°-100°	16.1	0.4
100°-110°	58.9	1.6
110°-120°	157.5	4.4
120°-130°	259.9	7.2
130°-140°	276.4	7.6
140°-150°	256.9	7.1
150°-160°	206.6	5.7
160°-170°	133.1	3.7
170°-180°	45.8	1.3
0°-30°	647.0	17.9
0°-40°	1038.1	28.7
0°-60°	1769.3	48.9
0°-90°	2203.4	61.0
90°-120°	232.4	6.4
90°-150°	1025.8	28.4
90°-180°	1411.0	39.0
0°-180°	3614.7	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	866	866	866	866	866	
5°	866	862	853	859	858	82
15°	824	819	808	811	807	232
25°	746	739	725	726	725	343
35°	643	635	622	617	612	402
45°	524	517	505	496	493	404
55°	396	391	381	372	367	354
65°	267	262	254	247	242	264
75°	140	138	134	129	131	149
85°	34	33	32	30	29	39
90°	0	4	7	9	9	3
95°	23	12	14	15	15	28
105°	106	110	21	25	26	113
115°	200	206	215	61	28	197
125°	283	288	294	297	298	252
135°	351	356	359	362	362	271
145°	407	407	412	414	413	254
155°	448	445	449	451	448	206
165°	472	470	471	473	471	133
175°	483	480	481	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	869.6	868.9	868.1	867.4	866.7	865.4	863.8	862.2	860.5	858.9	860.4
5°	865.6	864.9	864.1	863.4	862.7	861.3	859.2	857.2	855.2	853.1	854.6
7.5°	857.9	856.8	855.7	854.5	853.4	851.7	849.7	847.6	845.5	843.4	844.9
10°	850.6	849.3	848.0	846.7	845.5	843.7	841.5	839.3	837.0	834.8	836.3
12.5°	840.7	839.5	838.3	837.1	836.0	834.4	832.1	829.9	827.7	825.5	826.6
15°	823.9	822.9	821.7	820.7	819.5	817.7	815.4	812.9	810.6	808.1	808.9
17.5°	802.7	801.5	800.5	799.3	798.3	796.5	794.0	791.6	789.1	786.7	787.6
20°	787.3	786.3	785.1	784.0	782.9	781.1	778.4	775.9	773.3	770.7	771.3
22.5°	772.0	770.5	768.9	767.4	765.8	763.9	761.4	759.0	756.5	754.1	754.2
25°	745.8	744.3	742.8	741.3	739.8	737.5	734.3	731.2	728.1	725.0	725.3
27.5°	715.8	714.4	713.1	711.8	710.5	708.6	706.0	703.6	701.1	698.6	698.1
30°	695.8	694.3	692.8	691.4	689.9	687.8	685.0	682.2	679.5	676.7	676.1
32.5°	674.5	673.3	672.1	670.9	669.8	667.7	664.8	661.9	658.9	656.0	655.0
35°	643.4	641.6	639.7	637.8	635.9	633.6	630.6	627.6	624.7	621.7	620.6
37.5°	608.2	606.6	605.0	603.3	601.8	599.4	596.5	593.5	590.6	587.6	586.2
40°	584.2	582.8	581.3	579.8	578.4	576.2	573.2	570.2	567.3	564.3	562.6
42.5°	561.0	559.5	558.0	556.5	555.1	552.9	549.8	546.9	544.0	541.0	539.2
45°	523.5	522.2	520.9	519.7	518.4	516.3	513.6	510.8	508.0	505.2	503.2
47.5°	486.2	485.0	483.8	482.6	481.4	479.3	476.4	473.5	470.7	467.7	465.6
50°	460.2	459.3	458.4	457.5	456.6	454.8	452.2	449.6	447.0	444.4	441.9
52.5°	435.0	433.7	432.5	431.3	430.1	428.3	425.8	423.4	420.9	418.5	416.4
55°	396.2	395.1	394.0	392.8	391.8	390.0	387.8	385.6	383.4	381.2	379.0
57.5°	357.2	356.4	355.5	354.6	353.7	352.0	349.6	347.2	344.7	342.3	340.1
60°	331.3	330.5	329.8	329.1	328.3	326.6	324.1	321.5	318.9	316.3	314.2
62.5°	306.0	304.8	303.6	302.4	301.3	299.6	297.7	295.6	293.7	291.6	289.8
65°	267.2	266.0	265.0	263.8	262.7	261.2	259.4	257.6	255.7	253.9	252.2
67.5°	227.7	226.8	225.9	225.0	224.1	222.9	221.2	219.6	217.9	216.2	214.9
70°	203.1	202.4	201.6	200.9	200.2	198.9	197.2	195.6	194.0	192.2	190.9
72.5°	177.8	177.0	176.3	175.5	174.8	173.9	172.8	171.8	170.7	169.6	168.4
75°	139.8	139.4	139.1	138.7	138.4	137.7	136.8	135.8	134.9	134.0	132.9
77.5°	105.9	105.3	104.6	104.0	103.4	102.9	102.5	102.1	101.7	101.3	100.9
80°	83.2	83.1	82.8	82.7	82.5	82.2	81.9	81.4	81.1	80.7	80.1
82.5°	62.0	61.9	61.9	61.8	61.8	61.6	61.4	61.2	61.0	60.7	60.1
85°	34.2	33.9	33.8	33.6	33.3	33.2	33.0	32.9	32.6	32.4	31.9
87.5°	12.1	11.9	11.8	11.7	11.6	11.4	11.3	11.1	10.9	10.7	10.4
90°	0.3	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3
92.5°	7.0	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3
95°	22.7	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9
97.5°	44.9	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5
100°	61.7	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5
102.5°	80.1	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2
105°	105.9	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1
107.5°	135.4	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9
110°	154.3	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2



TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.2	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6
115°	200.4	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1
117.5°	225.5	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5
120°	243.9	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3
122.5°	259.5	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5
125°	283.3	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0
127.5°	304.8	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6
130°	318.5	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7
132.5°	332.5	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8
135°	350.6	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0
137.5°	368.9	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1
140°	380.9	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2
142.5°	390.9	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4
145°	406.7	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8
147.5°	420.4	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3
150°	429.3	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9
152.5°	436.8	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9
155°	447.8	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3
157.5°	456.3	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1
160°	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9
162.5°	465.9	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1
165°	471.8	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3
167.5°	476.3	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7
170°	478.8	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9
172.5°	480.5	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6
175°	482.7	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4
177.5°	483.0	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	865.6	865.6	865.6	865.6	865.6	865.6	865.6	865.6
2.5°	861.9	863.4	864.9	865.4	865.1	864.9	864.5	864.3
5°	856.1	857.5	859.0	859.6	859.2	858.8	858.5	858.1
7.5°	846.4	847.9	849.4	849.9	849.5	849.1	848.7	848.3
10°	837.7	839.3	840.7	841.1	840.7	840.1	839.5	838.9
12.5°	827.5	828.6	829.6	829.9	829.5	829.2	828.8	828.3
15°	809.7	810.4	811.1	811.1	810.1	809.2	808.3	807.3
17.5°	788.4	789.2	790.1	790.1	789.2	788.3	787.4	786.5
20°	771.8	772.4	772.9	772.8	772.1	771.4	770.6	769.9
22.5°	754.3	754.4	754.5	754.3	753.9	753.4	753.0	752.6
25°	725.7	726.0	726.4	726.4	726.0	725.7	725.3	725.0
27.5°	697.5	697.0	696.4	695.7	694.8	693.9	693.0	692.1
30°	675.6	675.0	674.4	673.8	673.0	672.3	671.6	670.8
32.5°	654.0	653.1	652.0	651.2	650.4	649.7	648.9	648.2
35°	619.5	618.4	617.3	616.3	615.4	614.4	613.5	612.5
37.5°	584.9	583.5	582.1	581.0	580.1	579.2	578.4	577.5
40°	561.0	559.3	557.7	556.4	555.7	555.0	554.2	553.5
42.5°	537.4	535.6	533.8	532.3	531.2	530.3	529.2	528.2
45°	501.2	499.1	497.1	495.7	495.0	494.2	493.5	492.7
47.5°	463.5	461.3	459.2	457.5	456.5	455.4	454.4	453.3
50°	439.3	436.7	434.1	432.4	431.4	430.5	429.6	428.6
52.5°	414.2	412.1	409.9	408.2	407.0	405.8	404.6	403.3
55°	376.7	374.5	372.3	370.7	369.8	368.9	367.9	367.0
57.5°	337.9	335.7	333.5	332.1	331.3	330.7	330.0	329.2
60°	312.2	310.1	308.1	306.9	306.3	305.7	305.2	304.6
62.5°	287.9	286.0	284.1	282.8	282.1	281.4	280.7	280.0
65°	250.5	248.8	247.2	245.9	245.0	244.0	243.1	242.2
67.5°	213.6	212.4	211.1	210.0	209.3	208.6	207.8	207.1
70°	189.6	188.4	187.1	186.1	185.3	184.6	183.8	183.1
72.5°	167.1	165.8	164.4	163.5	162.9	162.3	161.8	161.1
75°	131.8	130.7	129.6	129.2	129.6	130.0	130.3	130.7
77.5°	100.3	99.7	99.1	98.7	98.1	97.6	97.1	96.5
80°	79.7	79.1	78.5	78.0	77.7	77.3	77.0	76.6
82.5°	59.4	58.6	58.0	57.6	57.5	57.4	57.3	57.2
85°	31.4	30.8	30.2	29.8	29.7	29.5	29.4	29.1
87.5°	9.9	9.6	9.2	9.0	8.9	8.8	8.6	8.6
90°	7.7	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.5	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.3	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	18.8	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.1	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.0	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.0	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	28.0	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	45.5	37.7	30.0	26.3	26.6	26.9	27.2	27.6



TEST NUMBER: P331529-930

CATALOG NUMBER: S122DIW-S675D435U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	97.3	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	143.3	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	220.8	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	257.3	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.0	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	295.5	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	316.4	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	329.6	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	342.5	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	360.9	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	377.9	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	388.9	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.1	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.4	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	425.7	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.4	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.3	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	449.8	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	457.7	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.3	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	466.6	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.3	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	478.5	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.1	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.0	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.2	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)