

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331538-930

Luminaire Tested: **S122DIW-S675D970U930-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331538-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S675D970U930-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 675 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5129.3 lumens  
Efficiency: N/A  
Efficacy: 97.5 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 52.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	81	81	81	67	67	67	53	53	53	47
1	97	93	90	86	89	86	83	80	72	70	68	59	58	56	48	47	46	40
2	89	82	76	71	82	76	71	66	64	60	57	53	50	48	42	41	39	34
3	82	72	65	60	75	67	61	56	57	52	48	47	44	41	38	36	34	30
4	75	64	57	51	69	60	53	48	51	45	42	42	38	35	34	32	30	26
5	69	58	50	44	63	53	46	41	45	40	36	38	34	31	31	28	26	23
6	64	52	44	38	58	48	41	36	41	36	32	34	30	27	28	25	23	20
7	59	47	39	34	54	44	37	32	37	32	28	31	27	24	26	23	21	18
8	55	43	35	30	50	40	33	28	34	29	25	29	25	22	24	21	19	16
9	51	39	32	27	47	36	30	25	31	26	23	27	23	20	22	19	17	15
10	48	36	29	24	44	34	27	23	29	24	20	25	21	18	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	17486	17486	17486	17486
5°	19603	17598	15595	17598
10°	22463	17454	13496	17454
15°	24849	17135	11925	17135
20°	24471	16790	10869	16790
25°	22066	16335	10203	16335
30°	18233	15605	9715	15605
35°	13291	14840	9368	14840
40°	10614	13940	9177	13940
45°	9275	12896	8914	12896
50°	8719	11886	8741	11886
55°	8037	10860	8504	10860
60°	7363	9771	8147	9771
65°	6709	8795	7790	8795
70°	6090	7841	7270	7841
75°	5402	6775	6438	6775
80°	4649	5607	5188	5607
85°	4168	4168	3075	4168



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	103.1	2.0
10°-20°	299.8	5.8
20°-30°	435.1	8.5
30°-40°	459.2	9.0
40°-50°	406.6	7.9
50°-60°	324.5	6.3
60°-70°	220.5	4.3
70°-80°	113.1	2.2
80°-90°	31.2	0.6
90°-100°	62.0	1.2
100°-110°	192.6	3.8
110°-120°	329.2	6.4
120°-130°	432.9	8.4
130°-140°	485.9	9.5
140°-150°	476.4	9.3
150°-160°	399.6	7.8
160°-170°	265.0	5.2
170°-180°	92.6	1.8
0°-30°	838.1	16.3
0°-40°	1297.3	25.3
0°-60°	2028.3	39.5
0°-90°	2393.1	46.7
90°-120°	583.8	11.4
90°-150°	1979.0	38.6
90°-180°	2736.0	53.3
0°-180°	5129.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1083	1083	1083	1083	1083	
5°	1210	1086	962	1086	1210	121
15°	1487	1025	713	1025	1487	410
25°	1239	917	573	917	1239	560
35°	674	753	475	753	674	439
45°	406	565	390	565	406	319
55°	286	386	302	386	286	256
65°	176	230	204	230	176	175
75°	87	109	103	109	87	93
85°	22	22	17	22	22	25
90°	28	1	28	1	28	13
95°	51	43	51	43	51	57
105°	183	178	183	178	183	193
115°	330	330	330	330	330	326
125°	482	481	482	481	482	430
135°	629	622	629	622	629	484
145°	763	755	763	755	763	476
155°	870	863	870	863	870	400
165°	940	939	940	939	940	265
175°	974	977	974	977	974	92
180°	978	978	978	978	978	



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1132.9	1133.2	1133.9	1128.5	1127.9	1127.9	1123.2	1119.2	1114.6	1108.2	1108.9
5°	1209.5	1214.1	1215.7	1210.7	1203.2	1202.4	1195.3	1183.7	1172.8	1164.1	1157.9
7.5°	1300.9	1302.7	1298.6	1292.0	1286.5	1276.5	1263.3	1250.4	1232.3	1215.8	1203.5
10°	1370.1	1372.6	1365.5	1356.0	1348.1	1336.4	1317.3	1297.7	1274.0	1251.1	1232.7
12.5°	1422.7	1428.9	1419.8	1418.5	1405.0	1389.0	1366.2	1356.3	1322.9	1291.0	1271.4
15°	1486.6	1486.2	1487.1	1479.2	1469.2	1466.6	1442.5	1416.3	1369.3	1350.5	1318.1
17.5°	1468.2	1474.5	1477.4	1477.3	1477.1	1475.5	1467.8	1451.2	1427.7	1397.3	1359.8
20°	1424.2	1432.6	1433.8	1443.4	1448.8	1455.9	1458.7	1454.2	1439.7	1414.2	1381.8
22.5°	1356.3	1358.6	1362.5	1377.4	1389.2	1406.9	1416.2	1431.6	1426.0	1413.6	1386.4
25°	1238.6	1234.4	1249.0	1256.5	1283.5	1311.8	1332.3	1354.7	1374.7	1386.7	1378.8
27.5°	1097.2	1091.0	1112.8	1132.7	1154.7	1185.4	1217.2	1254.7	1285.9	1324.9	1338.3
30°	978.0	981.8	1002.7	1023.9	1057.1	1100.4	1136.2	1177.5	1222.0	1265.7	1296.0
32.5°	849.5	864.0	877.1	909.6	938.9	987.2	1039.7	1091.2	1146.7	1196.4	1243.4
35°	674.3	690.9	709.2	733.0	774.1	822.0	873.2	942.6	1018.5	1086.3	1142.1
37.5°	567.5	564.8	575.4	592.5	625.9	664.5	723.4	792.1	881.3	961.0	1039.7
40°	503.6	501.9	509.4	525.2	550.7	578.9	630.6	690.9	773.7	871.1	964.7
42.5°	459.7	460.6	464.8	476.0	493.3	516.7	555.3	606.7	682.5	774.2	874.8
45°	406.2	409.1	413.7	419.1	429.1	448.3	469.9	506.5	566.5	643.0	742.1
47.5°	367.8	367.9	372.5	377.2	383.2	394.0	411.6	434.6	476.9	539.2	624.4
50°	347.1	344.2	347.6	351.2	357.5	365.0	376.7	398.3	426.6	477.0	548.1
52.5°	321.8	321.9	324.9	326.3	331.9	339.3	350.0	365.0	390.6	430.0	488.5
55°	285.5	287.6	289.3	291.7	296.8	302.1	310.5	320.5	340.5	370.0	413.3
57.5°	251.4	252.0	253.7	258.4	261.6	266.6	274.5	283.6	296.6	318.5	351.0
60°	228.0	228.0	231.4	233.5	237.7	242.6	248.9	257.6	269.3	287.1	313.4
62.5°	206.8	206.4	207.7	211.2	214.3	219.0	225.3	232.7	243.6	259.5	281.1
65°	175.6	174.8	177.3	178.1	181.5	186.1	191.0	198.9	207.7	219.3	238.5
67.5°	145.7	146.7	148.0	149.6	151.4	156.2	159.6	165.2	172.5	182.2	195.2
70°	129.0	129.0	129.0	130.3	132.7	135.3	138.6	143.2	150.3	158.6	170.2
72.5°	110.4	111.7	113.0	112.3	115.4	116.9	120.9	123.5	130.3	135.6	145.9
75°	86.6	86.6	86.6	88.6	89.9	91.2	93.7	96.1	99.5	106.2	111.5
77.5°	64.6	64.4	64.8	65.3	66.7	68.2	68.9	71.2	74.3	77.3	81.9
80°	50.0	50.8	51.2	52.0	52.0	52.8	53.2	56.2	58.3	60.3	63.3
82.5°	38.6	38.8	38.9	39.1	39.4	39.9	40.9	41.9	42.6	44.4	46.6
85°	22.5	22.1	22.1	22.9	22.5	22.5	23.3	24.1	24.1	24.5	25.8
87.5°	14.3	14.3	14.5	14.2	14.1	14.5	14.5	14.3	14.7	15.1	14.6
90°	28.0	27.9	27.7	27.6	27.3	27.4	27.8	28.1	28.5	28.9	24.9
92.5°	26.7	26.7	26.7	26.7	26.6	26.6	26.5	26.4	26.3	26.3	25.3
95°	51.2	51.5	51.9	52.3	52.7	52.8	52.8	52.8	52.8	52.8	52.5
97.5°	88.7	88.7	88.8	88.8	88.9	88.9	88.9	88.9	88.9	88.9	88.1
100°	113.2	113.3	113.5	113.7	113.9	114.0	114.0	114.0	114.0	114.0	113.4
102.5°	140.9	141.0	141.2	141.5	141.6	141.6	141.5	141.4	141.2	141.0	140.3
105°	183.4	183.4	183.4	183.4	183.4	183.1	182.8	182.4	182.1	181.6	181.3
107.5°	223.3	224.1	224.9	225.8	226.7	227.0	226.9	226.7	226.6	226.4	226.4
110°	254.4	254.9	255.4	256.0	256.6	256.8	256.8	256.8	256.8	256.8	256.8



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	284.1	284.5	284.9	285.3	285.7	286.1	286.6	287.0	287.4	287.9	288.0
115°	330.3	330.8	331.4	332.0	332.5	332.9	333.0	333.2	333.5	333.6	333.9
117.5°	374.4	375.0	375.5	376.1	376.6	377.1	377.6	378.0	378.5	378.9	379.9
120°	405.4	406.0	406.6	407.1	407.6	408.0	408.0	408.0	408.0	408.0	409.4
122.5°	435.9	436.3	436.7	437.1	437.5	437.9	438.3	438.8	439.2	439.6	440.7
125°	482.2	482.4	482.7	482.8	483.0	483.4	483.9	484.5	485.0	485.6	486.1
127.5°	524.6	525.1	525.7	526.3	526.8	527.5	528.2	528.8	529.5	530.2	530.8
130°	554.9	555.6	556.4	557.1	557.8	558.4	558.8	559.1	559.5	559.9	560.3
132.5°	584.0	584.6	585.1	585.8	586.4	587.0	587.8	588.6	589.5	590.3	590.2
135°	629.2	629.8	630.3	630.9	631.4	631.8	632.0	632.2	632.3	632.5	632.2
137.5°	670.2	670.9	671.6	672.4	673.1	673.6	673.8	673.8	674.0	674.2	673.7
140°	698.6	699.4	700.1	700.8	701.6	701.9	701.9	701.9	701.9	701.9	701.0
142.5°	724.4	725.1	725.9	726.6	727.3	727.6	727.5	727.3	727.2	727.0	726.4
145°	763.0	763.8	764.5	765.2	766.0	766.2	766.1	765.9	765.6	765.5	764.4
147.5°	797.5	798.3	798.9	799.6	800.3	800.5	800.1	799.6	799.2	798.8	798.1
150°	820.0	820.5	821.1	821.7	822.2	822.2	821.7	821.1	820.5	820.0	819.3
152.5°	841.1	841.8	842.5	843.3	843.9	843.9	843.3	842.5	841.8	841.1	840.2
155°	869.5	870.1	870.7	871.2	871.7	871.6	870.7	869.8	868.8	867.9	867.3
157.5°	894.0	894.9	895.8	896.7	897.5	897.3	896.1	894.9	893.6	892.3	892.0
160°	909.2	910.0	910.7	911.4	912.2	911.9	910.9	909.7	908.7	907.5	907.3
162.5°	922.4	923.2	924.1	925.0	925.9	925.8	924.5	923.2	922.0	920.7	920.6
165°	939.7	940.7	941.6	942.5	943.4	943.2	941.9	940.7	939.4	938.1	938.1
167.5°	954.0	954.9	955.9	956.8	957.7	957.6	956.3	955.0	953.7	952.4	952.5
170°	961.2	962.3	963.4	964.5	965.6	965.6	964.3	963.0	961.6	960.4	960.6
172.5°	967.2	968.2	969.4	970.5	971.6	971.4	970.2	968.9	967.6	966.3	966.5
175°	973.6	974.7	975.8	976.9	978.0	977.9	976.6	975.3	974.0	972.7	973.1
177.5°	976.6	977.5	978.4	979.2	980.1	980.1	979.2	978.4	977.5	976.6	976.9
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1111.3	1108.6	1106.9	1100.9	1095.6	1090.3	1088.6	1089.2	1082.0	1075.0	1072.0
5°	1154.5	1146.2	1138.3	1127.1	1113.8	1099.2	1091.7	1085.8	1071.3	1055.5	1046.4
7.5°	1193.4	1181.5	1166.2	1145.0	1125.7	1102.8	1088.2	1075.3	1053.9	1031.7	1018.0
10°	1217.0	1200.7	1181.1	1155.4	1131.6	1103.8	1084.2	1064.6	1039.7	1013.0	996.4
12.5°	1237.3	1215.4	1196.1	1163.0	1135.0	1100.1	1076.8	1049.3	1023.0	991.4	975.1
15°	1285.6	1245.3	1208.6	1171.2	1136.6	1087.9	1062.2	1025.1	990.5	951.5	932.7
17.5°	1323.0	1277.7	1219.9	1172.3	1132.0	1078.2	1040.2	995.9	955.0	910.3	884.8
20°	1344.3	1292.2	1230.3	1173.7	1125.4	1063.8	1022.6	977.2	929.4	879.0	851.5
22.5°	1357.0	1302.3	1241.0	1168.7	1112.1	1052.1	1000.3	950.6	902.0	847.7	818.9
25°	1361.0	1311.0	1246.1	1164.5	1095.4	1027.6	965.2	916.9	858.2	807.4	765.4
27.5°	1341.2	1305.4	1242.9	1156.7	1076.2	996.9	927.3	872.6	810.7	755.5	713.3
30°	1316.9	1296.0	1235.3	1148.7	1060.9	975.6	898.9	837.0	775.3	719.6	676.3
32.5°	1279.2	1274.7	1221.3	1137.3	1044.6	948.6	869.4	806.7	738.4	683.6	642.4
35°	1205.3	1225.3	1191.6	1112.1	1013.8	910.2	824.5	752.9	682.2	629.7	591.0
37.5°	1106.3	1155.8	1147.0	1075.1	972.4	868.5	773.8	699.0	631.5	578.6	540.6
40°	1038.0	1101.2	1110.4	1046.8	943.1	836.2	735.8	661.4	595.6	547.3	509.0
42.5°	964.7	1038.7	1063.8	1012.8	911.1	802.2	701.9	624.7	559.6	512.7	478.7
45°	842.0	939.8	985.1	956.0	857.8	746.2	643.0	564.8	505.6	461.5	435.4
47.5°	727.2	834.1	895.0	884.8	798.4	687.9	586.0	510.9	453.3	418.1	394.6
50°	646.0	755.8	829.5	832.8	755.8	646.4	544.0	473.2	420.4	387.5	368.4
52.5°	575.4	680.2	760.6	778.2	708.2	603.1	506.4	435.9	389.4	359.1	342.0
55°	483.2	571.9	660.9	693.4	637.2	537.3	447.8	385.8	342.1	321.3	306.3
57.5°	401.7	475.6	557.9	593.8	559.1	473.6	389.7	335.9	300.4	282.2	270.7
60°	358.7	417.0	490.2	533.1	503.2	427.1	353.8	302.6	273.5	257.2	246.4
62.5°	318.8	370.4	432.4	471.6	455.3	383.4	317.8	272.6	247.4	232.2	224.5
65°	263.0	303.9	351.7	387.9	377.1	322.5	268.9	230.2	210.2	198.1	191.8
67.5°	216.6	246.1	279.2	311.0	302.2	263.6	220.5	190.4	175.5	165.1	161.3
70°	187.3	209.8	239.3	264.7	257.6	226.0	191.8	166.1	153.2	144.4	140.6
72.5°	159.3	177.8	200.3	221.1	216.3	190.0	161.6	142.1	132.2	124.1	121.0
75°	120.3	134.4	148.1	161.9	160.6	140.2	123.6	108.6	100.7	94.5	93.2
77.5°	88.8	96.7	106.1	114.2	111.9	100.3	87.2	78.7	72.8	68.6	68.0
80°	67.8	72.4	79.1	84.9	82.0	77.0	66.6	60.3	56.2	52.0	50.4
82.5°	49.2	53.8	57.8	60.9	58.7	54.1	47.6	43.4	40.8	38.1	37.3
85°	25.8	28.3	30.0	30.8	30.0	27.1	24.1	22.5	20.4	19.2	18.8
87.5°	14.2	13.4	12.6	12.6	11.2	10.7	9.0	7.5	7.6	7.7	7.5
90°	20.8	16.8	12.7	9.6	7.4	5.2	3.0	0.8	3.0	5.2	7.4
92.5°	24.4	23.4	22.4	21.2	19.6	17.9	16.3	14.7	16.3	17.9	19.6
95°	52.1	51.8	51.4	50.3	48.4	46.6	44.8	43.0	44.8	46.6	48.4
97.5°	87.5	86.7	86.1	84.9	83.3	81.7	80.1	78.4	80.1	81.7	83.3
100°	112.8	112.3	111.8	110.7	109.3	107.8	106.3	104.8	106.3	107.8	109.3
102.5°	139.7	138.9	138.3	137.3	136.2	134.9	133.8	132.6	133.8	134.9	136.2
105°	180.9	180.6	180.2	179.8	179.2	178.6	178.1	177.6	178.1	178.6	179.2
107.5°	226.4	226.4	226.4	226.0	225.2	224.4	223.6	222.8	223.6	224.4	225.2
110°	256.8	256.8	256.8	256.2	255.2	254.0	253.0	251.8	253.0	254.0	255.2





TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	288.1	288.3	288.5	288.0	286.9	285.8	284.7	283.6	284.7	285.8	286.9
115°	334.4	334.7	335.1	334.7	333.6	332.5	331.4	330.3	331.4	332.5	333.6
117.5°	380.9	382.0	382.9	382.8	381.3	379.8	378.4	376.9	378.4	379.8	381.3
120°	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	409.4	410.9	412.4
122.5°	441.7	442.7	443.8	443.4	441.6	439.9	438.1	436.3	438.1	439.9	441.6
125°	486.7	487.2	487.8	487.2	485.6	483.9	482.2	480.6	482.2	483.9	485.6
127.5°	531.5	532.1	532.8	532.1	530.0	527.9	525.8	523.7	525.8	527.9	530.0
130°	560.6	561.0	561.3	560.4	558.0	555.5	553.2	550.8	553.2	555.5	558.0
132.5°	590.1	590.0	590.0	589.0	587.0	585.1	583.1	581.1	583.1	585.1	587.0
135°	631.8	631.4	631.0	629.9	627.9	625.8	623.9	621.8	623.9	625.8	627.9
137.5°	673.2	672.7	672.3	671.2	669.5	667.9	666.3	664.6	666.3	667.9	669.5
140°	700.1	699.2	698.2	696.9	695.3	693.7	692.0	690.3	692.0	693.7	695.3
142.5°	725.8	725.1	724.6	723.4	721.7	720.1	718.4	716.8	718.4	720.1	721.7
145°	763.3	762.2	761.1	759.9	758.6	757.3	756.0	754.7	756.0	757.3	758.6
147.5°	797.4	796.6	795.9	794.8	793.2	791.7	790.2	788.6	790.2	791.7	793.2
150°	818.6	817.8	817.1	816.1	815.1	813.9	812.9	811.7	812.9	813.9	815.1
152.5°	839.4	838.5	837.6	836.7	835.5	834.5	833.3	832.3	833.3	834.5	835.5
155°	866.8	866.3	865.7	865.1	864.6	864.1	863.5	862.9	863.5	864.1	864.6
157.5°	891.7	891.4	891.0	890.6	890.3	889.9	889.6	889.2	889.6	889.9	890.3
160°	907.2	907.0	906.8	906.5	906.1	905.8	905.4	905.1	905.4	905.8	906.1
162.5°	920.4	920.2	920.0	919.9	919.8	919.7	919.7	919.6	919.7	919.7	919.8
165°	938.1	938.1	938.1	938.2	938.3	938.6	938.7	938.9	938.7	938.6	938.3
167.5°	952.5	952.6	952.6	952.9	953.4	954.0	954.6	955.1	954.6	954.0	953.4
170°	960.7	960.9	961.2	961.5	962.1	962.6	963.1	963.7	963.1	962.6	962.1
172.5°	966.7	966.9	967.0	967.4	968.0	968.5	969.1	969.6	969.1	968.5	968.0
175°	973.5	973.9	974.2	974.7	975.3	975.8	976.3	976.9	976.3	975.8	975.3
177.5°	977.1	977.5	977.7	978.1	978.5	979.0	979.4	979.9	979.4	979.0	978.5
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1068.6	1066.7	1059.6	1056.0	1049.9	1044.3	1040.6	1042.4	1043.7	1043.0	1042.0
5°	1038.0	1030.0	1018.0	1007.6	1000.1	986.3	980.6	977.6	975.2	972.2	969.3
7.5°	1001.5	989.0	971.8	956.9	942.9	925.9	916.2	910.3	904.3	897.7	891.9
10°	975.6	958.1	939.8	918.9	902.3	886.9	873.2	864.1	855.7	847.8	842.0
12.5°	948.3	928.1	905.5	877.0	858.7	836.7	834.5	818.4	805.4	800.5	793.7
15°	904.8	876.5	847.8	814.1	799.5	779.5	767.0	754.6	743.3	735.4	733.4
17.5°	855.4	818.8	790.3	766.1	742.2	721.7	710.2	700.2	691.0	680.4	679.0
20°	817.8	786.2	755.0	733.8	709.2	688.4	674.3	664.2	656.3	650.1	644.7
22.5°	782.2	747.5	719.0	695.8	671.6	654.8	643.6	634.0	627.4	620.4	615.4
25°	725.0	698.0	666.8	640.5	620.5	609.8	600.5	592.2	588.1	583.5	577.7
27.5°	675.0	644.9	615.7	595.4	577.9	568.3	561.7	556.1	552.2	549.5	546.3
30°	639.7	609.3	586.4	566.5	551.9	542.3	538.2	534.8	530.3	528.6	526.9
32.5°	605.8	578.4	558.8	541.4	527.6	521.3	517.5	514.5	510.9	509.2	505.9
35°	557.7	534.8	515.7	506.1	494.9	489.4	486.6	482.3	479.1	477.4	477.0
37.5°	512.5	492.6	480.0	467.7	463.0	459.7	455.7	452.8	451.8	451.6	451.2
40°	483.2	467.0	455.8	445.7	443.7	438.6	435.4	432.8	432.8	433.3	432.8
42.5°	456.6	442.0	432.1	423.5	421.0	418.0	414.7	414.5	415.2	416.6	415.2
45°	416.2	405.8	398.7	394.5	390.0	387.0	386.6	387.9	388.3	388.7	390.0
47.5°	379.0	372.2	365.7	361.2	359.1	358.7	358.2	360.4	362.3	363.1	365.0
50°	357.1	349.2	343.8	340.9	339.2	338.3	339.2	341.7	343.3	345.4	346.7
52.5°	332.5	326.9	323.1	320.9	320.2	320.7	320.9	323.8	326.4	327.1	327.8
55°	298.4	294.2	293.4	289.7	291.3	290.9	293.0	294.6	297.2	299.6	300.1
57.5°	264.5	261.1	258.9	259.2	259.7	261.5	263.3	266.2	268.9	271.5	271.7
60°	241.8	240.1	238.9	238.9	239.7	242.2	244.3	247.2	248.9	250.5	251.8
62.5°	221.2	219.5	218.3	218.9	221.1	222.6	225.0	226.6	228.2	229.9	230.5
65°	188.5	187.7	189.0	189.8	190.2	192.2	195.2	196.4	198.1	198.9	201.9
67.5°	158.5	158.7	158.5	159.6	162.1	162.6	165.3	168.2	168.5	170.2	172.0
70°	138.2	139.0	139.8	140.6	142.8	143.6	145.7	146.9	148.5	149.9	151.1
72.5°	119.5	119.7	120.5	120.3	122.1	123.9	125.7	126.9	128.6	130.2	131.4
75°	92.0	92.0	92.8	93.2	95.3	97.4	96.9	97.8	99.5	101.1	102.0
77.5°	67.2	66.3	67.2	67.6	68.2	70.0	70.4	71.5	73.4	72.8	73.8
80°	51.2	50.0	51.2	51.6	51.6	53.7	53.7	54.5	55.8	54.5	55.8
82.5°	36.5	36.0	36.9	36.9	37.6	37.7	38.4	38.6	39.8	39.2	39.8
85°	18.3	17.9	18.3	17.9	18.3	18.8	18.8	18.3	18.3	19.2	17.9
87.5°	7.6	7.9	8.3	9.1	9.6	10.1	9.7	9.6	9.5	8.8	8.8
90°	9.6	12.7	16.8	20.8	24.9	28.9	28.5	28.1	27.8	27.4	27.3
92.5°	21.2	22.4	23.4	24.4	25.3	26.3	26.3	26.4	26.5	26.6	26.6
95°	50.3	51.4	51.8	52.1	52.5	52.8	52.8	52.8	52.8	52.8	52.7
97.5°	84.9	86.1	86.7	87.5	88.1	88.9	88.9	88.9	88.9	88.9	88.9
100°	110.7	111.8	112.3	112.8	113.4	114.0	114.0	114.0	114.0	114.0	113.9
102.5°	137.3	138.3	138.9	139.7	140.3	141.0	141.2	141.4	141.5	141.6	141.6
105°	179.8	180.2	180.6	180.9	181.3	181.6	182.1	182.4	182.8	183.1	183.4
107.5°	226.0	226.4	226.4	226.4	226.4	226.4	226.6	226.7	226.9	227.0	226.7
110°	256.2	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.8	256.6



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	288.0	288.5	288.3	288.1	288.0	287.9	287.4	287.0	286.6	286.1	285.7
115°	334.7	335.1	334.7	334.4	333.9	333.6	333.5	333.2	333.0	332.9	332.5
117.5°	382.8	382.9	382.0	380.9	379.9	378.9	378.5	378.0	377.6	377.1	376.6
120°	413.8	413.8	412.4	410.9	409.4	408.0	408.0	408.0	408.0	408.0	407.6
122.5°	443.4	443.8	442.7	441.7	440.7	439.6	439.2	438.8	438.3	437.9	437.5
125°	487.2	487.8	487.2	486.7	486.1	485.6	485.0	484.5	483.9	483.4	483.0
127.5°	532.1	532.8	532.1	531.5	530.8	530.2	529.5	528.8	528.2	527.5	526.8
130°	560.4	561.3	561.0	560.6	560.3	559.9	559.5	559.1	558.8	558.4	557.8
132.5°	589.0	590.0	590.0	590.1	590.2	590.3	589.5	588.6	587.8	587.0	586.4
135°	629.9	631.0	631.4	631.8	632.2	632.5	632.3	632.2	632.0	631.8	631.4
137.5°	671.2	672.3	672.7	673.2	673.7	674.2	674.0	673.8	673.8	673.6	673.1
140°	696.9	698.2	699.2	700.1	701.0	701.9	701.9	701.9	701.9	701.9	701.6
142.5°	723.4	724.6	725.1	725.8	726.4	727.0	727.2	727.3	727.5	727.6	727.3
145°	759.9	761.1	762.2	763.3	764.4	765.5	765.6	765.9	766.1	766.2	766.0
147.5°	794.8	795.9	796.6	797.4	798.1	798.8	799.2	799.6	800.1	800.5	800.3
150°	816.1	817.1	817.8	818.6	819.3	820.0	820.5	821.1	821.7	822.2	822.2
152.5°	836.7	837.6	838.5	839.4	840.2	841.1	841.8	842.5	843.3	843.9	843.9
155°	865.1	865.7	866.3	866.8	867.3	867.9	868.8	869.8	870.7	871.6	871.7
157.5°	890.6	891.0	891.4	891.7	892.0	892.3	893.6	894.9	896.1	897.3	897.5
160°	906.5	906.8	907.0	907.2	907.3	907.5	908.7	909.7	910.9	911.9	912.2
162.5°	919.9	920.0	920.2	920.4	920.6	920.7	922.0	923.2	924.5	925.8	925.9
165°	938.2	938.1	938.1	938.1	938.1	938.1	939.4	940.7	941.9	943.2	943.4
167.5°	952.9	952.6	952.6	952.5	952.5	952.4	953.7	955.0	956.3	957.6	957.7
170°	961.5	961.2	960.9	960.7	960.6	960.4	961.6	963.0	964.3	965.6	965.6
172.5°	967.4	967.0	966.9	966.7	966.5	966.3	967.6	968.9	970.2	971.4	971.6
175°	974.7	974.2	973.9	973.5	973.1	972.7	974.0	975.3	976.6	977.9	978.0
177.5°	978.1	977.7	977.5	977.1	976.9	976.6	977.5	978.4	979.2	980.1	980.1
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1038.7	1038.0	1038.0	1035.0	1038.0	1038.0	1038.7	1042.0	1043.0	1043.7	1042.4
5°	963.5	962.2	960.2	962.2	960.2	962.2	963.5	969.3	972.2	975.2	977.6
7.5°	889.2	884.2	883.5	878.5	883.5	884.2	889.2	891.9	897.7	904.3	910.3
10°	834.9	831.5	831.1	823.2	831.1	831.5	834.9	842.0	847.8	855.7	864.1
12.5°	793.6	785.6	787.2	782.6	787.2	785.6	793.6	793.7	800.5	805.4	818.4
15°	722.1	722.1	720.4	713.4	720.4	722.1	722.1	733.4	735.4	743.3	754.6
17.5°	670.7	669.9	665.9	667.9	665.9	669.9	670.7	679.0	680.4	691.0	700.2
20°	640.1	637.6	632.6	632.6	632.6	637.6	640.1	644.7	650.1	656.3	664.2
22.5°	611.1	611.0	605.7	607.3	605.7	611.0	611.1	615.4	620.4	627.4	634.0
25°	577.2	574.0	571.4	572.7	571.4	574.0	577.2	577.7	583.5	588.1	592.2
27.5°	545.1	543.3	543.2	539.7	543.2	543.3	545.1	546.3	549.5	552.2	556.1
30°	526.5	522.4	523.2	521.1	523.2	522.4	526.5	526.9	528.6	530.3	534.8
32.5°	505.2	503.7	502.9	501.1	502.9	503.7	505.2	505.9	509.2	510.9	514.5
35°	476.1	476.5	474.5	475.3	474.5	476.5	476.1	477.0	477.4	479.1	482.3
37.5°	450.8	452.1	451.1	451.3	451.1	452.1	450.8	451.2	451.6	451.8	452.8
40°	434.1	434.1	434.1	435.4	434.1	434.1	434.1	432.8	433.3	432.8	432.8
42.5°	418.1	417.4	416.8	416.7	416.8	417.4	418.1	415.2	416.6	415.2	414.5
45°	390.8	392.1	392.5	390.4	392.5	392.1	390.8	390.0	388.7	388.3	387.9
47.5°	366.1	366.2	366.1	367.9	366.1	366.2	366.1	365.0	363.1	362.3	360.4
50°	348.8	348.0	348.8	348.0	348.8	348.0	348.8	346.7	345.4	343.3	341.7
52.5°	330.4	330.6	330.1	330.0	330.1	330.6	330.4	327.8	327.1	326.4	323.8
55°	301.7	302.6	302.1	302.1	302.1	302.6	301.7	300.1	299.6	297.2	294.6
57.5°	272.1	272.8	273.4	271.5	273.4	272.8	272.1	271.7	271.5	268.9	266.2
60°	251.4	253.5	253.1	252.3	253.1	253.5	251.4	251.8	250.5	248.9	247.2
62.5°	232.4	233.2	233.1	232.9	233.1	233.2	232.4	230.5	229.9	228.2	226.6
65°	203.1	203.9	202.7	203.9	202.7	203.9	203.1	201.9	198.9	198.1	196.4
67.5°	171.5	171.8	172.8	173.3	172.8	171.8	171.5	172.0	170.2	168.5	168.2
70°	151.9	151.5	152.7	154.0	152.7	151.5	151.9	151.1	149.9	148.5	146.9
72.5°	131.3	132.2	131.8	132.6	131.8	132.2	131.3	131.4	130.2	128.6	126.9
75°	101.1	102.4	102.0	103.2	102.0	102.4	101.1	102.0	101.1	99.5	97.8
77.5°	73.1	73.2	73.1	73.8	73.1	73.2	73.1	73.8	72.8	73.4	71.5
80°	55.8	55.0	54.1	55.8	54.1	55.0	55.8	55.8	54.5	55.8	54.5
82.5°	38.8	39.3	38.5	38.5	38.5	39.3	38.8	39.8	39.2	39.8	38.6
85°	17.9	17.4	16.6	16.6	16.6	17.4	17.9	17.9	19.2	18.3	18.3
87.5°	8.8	8.6	8.6	8.3	8.6	8.6	8.8	8.8	8.8	9.5	9.6
90°	27.6	27.7	27.9	28.0	27.9	27.7	27.6	27.3	27.4	27.8	28.1
92.5°	26.7	26.7	26.7	26.7	26.7	26.7	26.7	26.6	26.6	26.5	26.4
95°	52.3	51.9	51.5	51.2	51.5	51.9	52.3	52.7	52.8	52.8	52.8
97.5°	88.8	88.8	88.7	88.7	88.7	88.8	88.8	88.9	88.9	88.9	88.9
100°	113.7	113.5	113.3	113.2	113.3	113.5	113.7	113.9	114.0	114.0	114.0
102.5°	141.5	141.2	141.0	140.9	141.0	141.2	141.5	141.6	141.6	141.5	141.4
105°	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.4	183.1	182.8	182.4
107.5°	225.8	224.9	224.1	223.3	224.1	224.9	225.8	226.7	227.0	226.9	226.7
110°	256.0	255.4	254.9	254.4	254.9	255.4	256.0	256.6	256.8	256.8	256.8



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	285.3	284.9	284.5	284.1	284.5	284.9	285.3	285.7	286.1	286.6	287.0
115°	332.0	331.4	330.8	330.3	330.8	331.4	332.0	332.5	332.9	333.0	333.2
117.5°	376.1	375.5	375.0	374.4	375.0	375.5	376.1	376.6	377.1	377.6	378.0
120°	407.1	406.6	406.0	405.4	406.0	406.6	407.1	407.6	408.0	408.0	408.0
122.5°	437.1	436.7	436.3	435.9	436.3	436.7	437.1	437.5	437.9	438.3	438.8
125°	482.8	482.7	482.4	482.2	482.4	482.7	482.8	483.0	483.4	483.9	484.5
127.5°	526.3	525.7	525.1	524.6	525.1	525.7	526.3	526.8	527.5	528.2	528.8
130°	557.1	556.4	555.6	554.9	555.6	556.4	557.1	557.8	558.4	558.8	559.1
132.5°	585.8	585.1	584.6	584.0	584.6	585.1	585.8	586.4	587.0	587.8	588.6
135°	630.9	630.3	629.8	629.2	629.8	630.3	630.9	631.4	631.8	632.0	632.2
137.5°	672.4	671.6	670.9	670.2	670.9	671.6	672.4	673.1	673.6	673.8	673.8
140°	700.8	700.1	699.4	698.6	699.4	700.1	700.8	701.6	701.9	701.9	701.9
142.5°	726.6	725.9	725.1	724.4	725.1	725.9	726.6	727.3	727.6	727.5	727.3
145°	765.2	764.5	763.8	763.0	763.8	764.5	765.2	766.0	766.2	766.1	765.9
147.5°	799.6	798.9	798.3	797.5	798.3	798.9	799.6	800.3	800.5	800.1	799.6
150°	821.7	821.1	820.5	820.0	820.5	821.1	821.7	822.2	822.2	821.7	821.1
152.5°	843.3	842.5	841.8	841.1	841.8	842.5	843.3	843.9	843.9	843.3	842.5
155°	871.2	870.7	870.1	869.5	870.1	870.7	871.2	871.7	871.6	870.7	869.8
157.5°	896.7	895.8	894.9	894.0	894.9	895.8	896.7	897.5	897.3	896.1	894.9
160°	911.4	910.7	910.0	909.2	910.0	910.7	911.4	912.2	911.9	910.9	909.7
162.5°	925.0	924.1	923.2	922.4	923.2	924.1	925.0	925.9	925.8	924.5	923.2
165°	942.5	941.6	940.7	939.7	940.7	941.6	942.5	943.4	943.2	941.9	940.7
167.5°	956.8	955.9	954.9	954.0	954.9	955.9	956.8	957.7	957.6	956.3	955.0
170°	964.5	963.4	962.3	961.2	962.3	963.4	964.5	965.6	965.6	964.3	963.0
172.5°	970.5	969.4	968.2	967.2	968.2	969.4	970.5	971.6	971.4	970.2	968.9
175°	976.9	975.8	974.7	973.6	974.7	975.8	976.9	978.0	977.9	976.6	975.3
177.5°	979.2	978.4	977.5	976.6	977.5	978.4	979.2	980.1	980.1	979.2	978.4
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1040.6	1044.3	1049.9	1056.0	1059.6	1066.7	1068.6	1072.0	1075.0	1082.0	1089.2
5°	980.6	986.3	1000.1	1007.6	1018.0	1030.0	1038.0	1046.4	1055.5	1071.3	1085.8
7.5°	916.2	925.9	942.9	956.9	971.8	989.0	1001.5	1018.0	1031.7	1053.9	1075.3
10°	873.2	886.9	902.3	918.9	939.8	958.1	975.6	996.4	1013.0	1039.7	1064.6
12.5°	834.5	836.7	858.7	877.0	905.5	928.1	948.3	975.1	991.4	1023.0	1049.3
15°	767.0	779.5	799.5	814.1	847.8	876.5	904.8	932.7	951.5	990.5	1025.1
17.5°	710.2	721.7	742.2	766.1	790.3	818.8	855.4	884.8	910.3	955.0	995.9
20°	674.3	688.4	709.2	733.8	755.0	786.2	817.8	851.5	879.0	929.4	977.2
22.5°	643.6	654.8	671.6	695.8	719.0	747.5	782.2	818.9	847.7	902.0	950.6
25°	600.5	609.8	620.5	640.5	666.8	698.0	725.0	765.4	807.4	858.2	916.9
27.5°	561.7	568.3	577.9	595.4	615.7	644.9	675.0	713.3	755.5	810.7	872.6
30°	538.2	542.3	551.9	566.5	586.4	609.3	639.7	676.3	719.6	775.3	837.0
32.5°	517.5	521.3	527.6	541.4	558.8	578.4	605.8	642.4	683.6	738.4	806.7
35°	486.6	489.4	494.9	506.1	515.7	534.8	557.7	591.0	629.7	682.2	752.9
37.5°	455.7	459.7	463.0	467.7	480.0	492.6	512.5	540.6	578.6	631.5	699.0
40°	435.4	438.6	443.7	445.7	455.8	467.0	483.2	509.0	547.3	595.6	661.4
42.5°	414.7	418.0	421.0	423.5	432.1	442.0	456.6	478.7	512.7	559.6	624.7
45°	386.6	387.0	390.0	394.5	398.7	405.8	416.2	435.4	461.5	505.6	564.8
47.5°	358.2	358.7	359.1	361.2	365.7	372.2	379.0	394.6	418.1	453.3	510.9
50°	339.2	338.3	339.2	340.9	343.8	349.2	357.1	368.4	387.5	420.4	473.2
52.5°	320.9	320.7	320.2	320.9	323.1	326.9	332.5	342.0	359.1	389.4	435.9
55°	293.0	290.9	291.3	289.7	293.4	294.2	298.4	306.3	321.3	342.1	385.8
57.5°	263.3	261.5	259.7	259.2	258.9	261.1	264.5	270.7	282.2	300.4	335.9
60°	244.3	242.2	239.7	238.9	238.9	240.1	241.8	246.4	257.2	273.5	302.6
62.5°	225.0	222.6	221.1	218.9	218.3	219.5	221.2	224.5	232.2	247.4	272.6
65°	195.2	192.2	190.2	189.8	189.0	187.7	188.5	191.8	198.1	210.2	230.2
67.5°	165.3	162.6	162.1	159.6	158.5	158.7	158.5	161.3	165.1	175.5	190.4
70°	145.7	143.6	142.8	140.6	139.8	139.0	138.2	140.6	144.4	153.2	166.1
72.5°	125.7	123.9	122.1	120.3	120.5	119.7	119.5	121.0	124.1	132.2	142.1
75°	96.9	97.4	95.3	93.2	92.8	92.0	92.0	93.2	94.5	100.7	108.6
77.5°	70.4	70.0	68.2	67.6	67.2	66.3	67.2	68.0	68.6	72.8	78.7
80°	53.7	53.7	51.6	51.6	51.2	50.0	51.2	50.4	52.0	56.2	60.3
82.5°	38.4	37.7	37.6	36.9	36.9	36.0	36.5	37.3	38.1	40.8	43.4
85°	18.8	18.8	18.3	17.9	18.3	17.9	18.3	18.8	19.2	20.4	22.5
87.5°	9.7	10.1	9.6	9.1	8.3	7.9	7.6	7.5	7.7	7.6	7.5
90°	28.5	28.9	24.9	20.8	16.8	12.7	9.6	7.4	5.2	3.0	0.8
92.5°	26.3	26.3	25.3	24.4	23.4	22.4	21.2	19.6	17.9	16.3	14.7
95°	52.8	52.8	52.5	52.1	51.8	51.4	50.3	48.4	46.6	44.8	43.0
97.5°	88.9	88.9	88.1	87.5	86.7	86.1	84.9	83.3	81.7	80.1	78.4
100°	114.0	114.0	113.4	112.8	112.3	111.8	110.7	109.3	107.8	106.3	104.8
102.5°	141.2	141.0	140.3	139.7	138.9	138.3	137.3	136.2	134.9	133.8	132.6
105°	182.1	181.6	181.3	180.9	180.6	180.2	179.8	179.2	178.6	178.1	177.6
107.5°	226.6	226.4	226.4	226.4	226.4	226.4	226.0	225.2	224.4	223.6	222.8
110°	256.8	256.8	256.8	256.8	256.8	256.8	256.2	255.2	254.0	253.0	251.8



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	287.4	287.9	288.0	288.1	288.3	288.5	288.0	286.9	285.8	284.7	283.6
115°	333.5	333.6	333.9	334.4	334.7	335.1	334.7	333.6	332.5	331.4	330.3
117.5°	378.5	378.9	379.9	380.9	382.0	382.9	382.8	381.3	379.8	378.4	376.9
120°	408.0	408.0	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0
122.5°	439.2	439.6	440.7	441.7	442.7	443.8	443.4	441.6	439.9	438.1	436.3
125°	485.0	485.6	486.1	486.7	487.2	487.8	487.2	485.6	483.9	482.2	480.6
127.5°	529.5	530.2	530.8	531.5	532.1	532.8	532.1	530.0	527.9	525.8	523.7
130°	559.5	559.9	560.3	560.6	561.0	561.3	560.4	558.0	555.5	553.2	550.8
132.5°	589.5	590.3	590.2	590.1	590.0	590.0	589.0	587.0	585.1	583.1	581.1
135°	632.3	632.5	632.2	631.8	631.4	631.0	629.9	627.9	625.8	623.9	621.8
137.5°	674.0	674.2	673.7	673.2	672.7	672.3	671.2	669.5	667.9	666.3	664.6
140°	701.9	701.9	701.0	700.1	699.2	698.2	696.9	695.3	693.7	692.0	690.3
142.5°	727.2	727.0	726.4	725.8	725.1	724.6	723.4	721.7	720.1	718.4	716.8
145°	765.6	765.5	764.4	763.3	762.2	761.1	759.9	758.6	757.3	756.0	754.7
147.5°	799.2	798.8	798.1	797.4	796.6	795.9	794.8	793.2	791.7	790.2	788.6
150°	820.5	820.0	819.3	818.6	817.8	817.1	816.1	815.1	813.9	812.9	811.7
152.5°	841.8	841.1	840.2	839.4	838.5	837.6	836.7	835.5	834.5	833.3	832.3
155°	868.8	867.9	867.3	866.8	866.3	865.7	865.1	864.6	864.1	863.5	862.9
157.5°	893.6	892.3	892.0	891.7	891.4	891.0	890.6	890.3	889.9	889.6	889.2
160°	908.7	907.5	907.3	907.2	907.0	906.8	906.5	906.1	905.8	905.4	905.1
162.5°	922.0	920.7	920.6	920.4	920.2	920.0	919.9	919.8	919.7	919.7	919.6
165°	939.4	938.1	938.1	938.1	938.1	938.1	938.2	938.3	938.6	938.7	938.9
167.5°	953.7	952.4	952.5	952.5	952.6	952.6	952.9	953.4	954.0	954.6	955.1
170°	961.6	960.4	960.6	960.7	960.9	961.2	961.5	962.1	962.6	963.1	963.7
172.5°	967.6	966.3	966.5	966.7	966.9	967.0	967.4	968.0	968.5	969.1	969.6
175°	974.0	972.7	973.1	973.5	973.9	974.2	974.7	975.3	975.8	976.3	976.9
177.5°	977.5	976.6	976.9	977.1	977.5	977.7	978.1	978.5	979.0	979.4	979.9
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1088.6	1090.3	1095.6	1100.9	1106.9	1108.6	1111.3	1108.9	1108.2	1114.6	1119.2
5°	1091.7	1099.2	1113.8	1127.1	1138.3	1146.2	1154.5	1157.9	1164.1	1172.8	1183.7
7.5°	1088.2	1102.8	1125.7	1145.0	1166.2	1181.5	1193.4	1203.5	1215.8	1232.3	1250.4
10°	1084.2	1103.8	1131.6	1155.4	1181.1	1200.7	1217.0	1232.7	1251.1	1274.0	1297.7
12.5°	1076.8	1100.1	1135.0	1163.0	1196.1	1215.4	1237.3	1271.4	1291.0	1322.9	1356.3
15°	1062.2	1087.9	1136.6	1171.2	1208.6	1245.3	1285.6	1318.1	1350.5	1369.3	1416.3
17.5°	1040.2	1078.2	1132.0	1172.3	1219.9	1277.7	1323.0	1359.8	1397.3	1427.7	1451.2
20°	1022.6	1063.8	1125.4	1173.7	1230.3	1292.2	1344.3	1381.8	1414.2	1439.7	1454.2
22.5°	1000.3	1052.1	1112.1	1168.7	1241.0	1302.3	1357.0	1386.4	1413.6	1426.0	1431.6
25°	965.2	1027.6	1095.4	1164.5	1246.1	1311.0	1361.0	1378.8	1386.7	1374.7	1354.7
27.5°	927.3	996.9	1076.2	1156.7	1242.9	1305.4	1341.2	1338.3	1324.9	1285.9	1254.7
30°	898.9	975.6	1060.9	1148.7	1235.3	1296.0	1316.9	1296.0	1265.7	1222.0	1177.5
32.5°	869.4	948.6	1044.6	1137.3	1221.3	1274.7	1279.2	1243.4	1196.4	1146.7	1091.2
35°	824.5	910.2	1013.8	1112.1	1191.6	1225.3	1205.3	1142.1	1086.3	1018.5	942.6
37.5°	773.8	868.5	972.4	1075.1	1147.0	1155.8	1106.3	1039.7	961.0	881.3	792.1
40°	735.8	836.2	943.1	1046.8	1110.4	1101.2	1038.0	964.7	871.1	773.7	690.9
42.5°	701.9	802.2	911.1	1012.8	1063.8	1038.7	964.7	874.8	774.2	682.5	606.7
45°	643.0	746.2	857.8	956.0	985.1	939.8	842.0	742.1	643.0	566.5	506.5
47.5°	586.0	687.9	798.4	884.8	895.0	834.1	727.2	624.4	539.2	476.9	434.6
50°	544.0	646.4	755.8	832.8	829.5	755.8	646.0	548.1	477.0	426.6	398.3
52.5°	506.4	603.1	708.2	778.2	760.6	680.2	575.4	488.5	430.0	390.6	365.0
55°	447.8	537.3	637.2	693.4	660.9	571.9	483.2	413.3	370.0	340.5	320.5
57.5°	389.7	473.6	559.1	593.8	557.9	475.6	401.7	351.0	318.5	296.6	283.6
60°	353.8	427.1	503.2	533.1	490.2	417.0	358.7	313.4	287.1	269.3	257.6
62.5°	317.8	383.4	455.3	471.6	432.4	370.4	318.8	281.1	259.5	243.6	232.7
65°	268.9	322.5	377.1	387.9	351.7	303.9	263.0	238.5	219.3	207.7	198.9
67.5°	220.5	263.6	302.2	311.0	279.2	246.1	216.6	195.2	182.2	172.5	165.2
70°	191.8	226.0	257.6	264.7	239.3	209.8	187.3	170.2	158.6	150.3	143.2
72.5°	161.6	190.0	216.3	221.1	200.3	177.8	159.3	145.9	135.6	130.3	123.5
75°	123.6	140.2	160.6	161.9	148.1	134.4	120.3	111.5	106.2	99.5	96.1
77.5°	87.2	100.3	111.9	114.2	106.1	96.7	88.8	81.9	77.3	74.3	71.2
80°	66.6	77.0	82.0	84.9	79.1	72.4	67.8	63.3	60.3	58.3	56.2
82.5°	47.6	54.1	58.7	60.9	57.8	53.8	49.2	46.6	44.4	42.6	41.9
85°	24.1	27.1	30.0	30.8	30.0	28.3	25.8	25.8	24.5	24.1	24.1
87.5°	9.0	10.7	11.2	12.6	12.6	13.4	14.2	14.6	15.1	14.7	14.3
90°	3.0	5.2	7.4	9.6	12.7	16.8	20.8	24.9	28.9	28.5	28.1
92.5°	16.3	17.9	19.6	21.2	22.4	23.4	24.4	25.3	26.3	26.3	26.4
95°	44.8	46.6	48.4	50.3	51.4	51.8	52.1	52.5	52.8	52.8	52.8
97.5°	80.1	81.7	83.3	84.9	86.1	86.7	87.5	88.1	88.9	88.9	88.9
100°	106.3	107.8	109.3	110.7	111.8	112.3	112.8	113.4	114.0	114.0	114.0
102.5°	133.8	134.9	136.2	137.3	138.3	138.9	139.7	140.3	141.0	141.2	141.4
105°	178.1	178.6	179.2	179.8	180.2	180.6	180.9	181.3	181.6	182.1	182.4
107.5°	223.6	224.4	225.2	226.0	226.4	226.4	226.4	226.4	226.4	226.6	226.7
110°	253.0	254.0	255.2	256.2	256.8	256.8	256.8	256.8	256.8	256.8	256.8





TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.7	285.8	286.9	288.0	288.5	288.3	288.1	288.0	287.9	287.4	287.0
115°	331.4	332.5	333.6	334.7	335.1	334.7	334.4	333.9	333.6	333.5	333.2
117.5°	378.4	379.8	381.3	382.8	382.9	382.0	380.9	379.9	378.9	378.5	378.0
120°	409.4	410.9	412.4	413.8	413.8	412.4	410.9	409.4	408.0	408.0	408.0
122.5°	438.1	439.9	441.6	443.4	443.8	442.7	441.7	440.7	439.6	439.2	438.8
125°	482.2	483.9	485.6	487.2	487.8	487.2	486.7	486.1	485.6	485.0	484.5
127.5°	525.8	527.9	530.0	532.1	532.8	532.1	531.5	530.8	530.2	529.5	528.8
130°	553.2	555.5	558.0	560.4	561.3	561.0	560.6	560.3	559.9	559.5	559.1
132.5°	583.1	585.1	587.0	589.0	590.0	590.0	590.1	590.2	590.3	589.5	588.6
135°	623.9	625.8	627.9	629.9	631.0	631.4	631.8	632.2	632.5	632.3	632.2
137.5°	666.3	667.9	669.5	671.2	672.3	672.7	673.2	673.7	674.2	674.0	673.8
140°	692.0	693.7	695.3	696.9	698.2	699.2	700.1	701.0	701.9	701.9	701.9
142.5°	718.4	720.1	721.7	723.4	724.6	725.1	725.8	726.4	727.0	727.2	727.3
145°	756.0	757.3	758.6	759.9	761.1	762.2	763.3	764.4	765.5	765.6	765.9
147.5°	790.2	791.7	793.2	794.8	795.9	796.6	797.4	798.1	798.8	799.2	799.6
150°	812.9	813.9	815.1	816.1	817.1	817.8	818.6	819.3	820.0	820.5	821.1
152.5°	833.3	834.5	835.5	836.7	837.6	838.5	839.4	840.2	841.1	841.8	842.5
155°	863.5	864.1	864.6	865.1	865.7	866.3	866.8	867.3	867.9	868.8	869.8
157.5°	889.6	889.9	890.3	890.6	891.0	891.4	891.7	892.0	892.3	893.6	894.9
160°	905.4	905.8	906.1	906.5	906.8	907.0	907.2	907.3	907.5	908.7	909.7
162.5°	919.7	919.7	919.8	919.9	920.0	920.2	920.4	920.6	920.7	922.0	923.2
165°	938.7	938.6	938.3	938.2	938.1	938.1	938.1	938.1	938.1	939.4	940.7
167.5°	954.6	954.0	953.4	952.9	952.6	952.6	952.5	952.5	952.4	953.7	955.0
170°	963.1	962.6	962.1	961.5	961.2	960.9	960.7	960.6	960.4	961.6	963.0
172.5°	969.1	968.5	968.0	967.4	967.0	966.9	966.7	966.5	966.3	967.6	968.9
175°	976.3	975.8	975.3	974.7	974.2	973.9	973.5	973.1	972.7	974.0	975.3
177.5°	979.4	979.0	978.5	978.1	977.7	977.5	977.1	976.9	976.6	977.5	978.4
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5	978.5



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0	1083.0
2.5°	1123.2	1127.9	1127.9	1128.5	1133.9	1133.2	1132.9
5°	1195.3	1202.4	1203.2	1210.7	1215.7	1214.1	1209.5
7.5°	1263.3	1276.5	1286.5	1292.0	1298.6	1302.7	1300.9
10°	1317.3	1336.4	1348.1	1356.0	1365.5	1372.6	1370.1
12.5°	1366.2	1389.0	1405.0	1418.5	1419.8	1428.9	1422.7
15°	1442.5	1466.6	1469.2	1479.2	1487.1	1486.2	1486.6
17.5°	1467.8	1475.5	1477.1	1477.3	1477.4	1474.5	1468.2
20°	1458.7	1455.9	1448.8	1443.4	1433.8	1432.6	1424.2
22.5°	1416.2	1406.9	1389.2	1377.4	1362.5	1358.6	1356.3
25°	1332.3	1311.8	1283.5	1256.5	1249.0	1234.4	1238.6
27.5°	1217.2	1185.4	1154.7	1132.7	1112.8	1091.0	1097.2
30°	1136.2	1100.4	1057.1	1023.9	1002.7	981.8	978.0
32.5°	1039.7	987.2	938.9	909.6	877.1	864.0	849.5
35°	873.2	822.0	774.1	733.0	709.2	690.9	674.3
37.5°	723.4	664.5	625.9	592.5	575.4	564.8	567.5
40°	630.6	578.9	550.7	525.2	509.4	501.9	503.6
42.5°	555.3	516.7	493.3	476.0	464.8	460.6	459.7
45°	469.9	448.3	429.1	419.1	413.7	409.1	406.2
47.5°	411.6	394.0	383.2	377.2	372.5	367.9	367.8
50°	376.7	365.0	357.5	351.2	347.6	344.2	347.1
52.5°	350.0	339.3	331.9	326.3	324.9	321.9	321.8
55°	310.5	302.1	296.8	291.7	289.3	287.6	285.5
57.5°	274.5	266.6	261.6	258.4	253.7	252.0	251.4
60°	248.9	242.6	237.7	233.5	231.4	228.0	228.0
62.5°	225.3	219.0	214.3	211.2	207.7	206.4	206.8
65°	191.0	186.1	181.5	178.1	177.3	174.8	175.6
67.5°	159.6	156.2	151.4	149.6	148.0	146.7	145.7
70°	138.6	135.3	132.7	130.3	129.0	129.0	129.0
72.5°	120.9	116.9	115.4	112.3	113.0	111.7	110.4
75°	93.7	91.2	89.9	88.6	86.6	86.6	86.6
77.5°	68.9	68.2	66.7	65.3	64.8	64.4	64.6
80°	53.2	52.8	52.0	52.0	51.2	50.8	50.0
82.5°	40.9	39.9	39.4	39.1	38.9	38.8	38.6
85°	23.3	22.5	22.5	22.9	22.1	22.1	22.5
87.5°	14.5	14.5	14.1	14.2	14.5	14.3	14.3
90°	27.8	27.4	27.3	27.6	27.7	27.9	28.0
92.5°	26.5	26.6	26.6	26.7	26.7	26.7	26.7
95°	52.8	52.8	52.7	52.3	51.9	51.5	51.2
97.5°	88.9	88.9	88.9	88.8	88.8	88.7	88.7
100°	114.0	114.0	113.9	113.7	113.5	113.3	113.2
102.5°	141.5	141.6	141.6	141.5	141.2	141.0	140.9
105°	182.8	183.1	183.4	183.4	183.4	183.4	183.4
107.5°	226.9	227.0	226.7	225.8	224.9	224.1	223.3
110°	256.8	256.8	256.6	256.0	255.4	254.9	254.4



TEST NUMBER: P331538-930

CATALOG NUMBER: S122DIW-S675D970U930-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	286.6	286.1	285.7	285.3	284.9	284.5	284.1
115°	333.0	332.9	332.5	332.0	331.4	330.8	330.3
117.5°	377.6	377.1	376.6	376.1	375.5	375.0	374.4
120°	408.0	408.0	407.6	407.1	406.6	406.0	405.4
122.5°	438.3	437.9	437.5	437.1	436.7	436.3	435.9
125°	483.9	483.4	483.0	482.8	482.7	482.4	482.2
127.5°	528.2	527.5	526.8	526.3	525.7	525.1	524.6
130°	558.8	558.4	557.8	557.1	556.4	555.6	554.9
132.5°	587.8	587.0	586.4	585.8	585.1	584.6	584.0
135°	632.0	631.8	631.4	630.9	630.3	629.8	629.2
137.5°	673.8	673.6	673.1	672.4	671.6	670.9	670.2
140°	701.9	701.9	701.6	700.8	700.1	699.4	698.6
142.5°	727.5	727.6	727.3	726.6	725.9	725.1	724.4
145°	766.1	766.2	766.0	765.2	764.5	763.8	763.0
147.5°	800.1	800.5	800.3	799.6	798.9	798.3	797.5
150°	821.7	822.2	822.2	821.7	821.1	820.5	820.0
152.5°	843.3	843.9	843.9	843.3	842.5	841.8	841.1
155°	870.7	871.6	871.7	871.2	870.7	870.1	869.5
157.5°	896.1	897.3	897.5	896.7	895.8	894.9	894.0
160°	910.9	911.9	912.2	911.4	910.7	910.0	909.2
162.5°	924.5	925.8	925.9	925.0	924.1	923.2	922.4
165°	941.9	943.2	943.4	942.5	941.6	940.7	939.7
167.5°	956.3	957.6	957.7	956.8	955.9	954.9	954.0
170°	964.3	965.6	965.6	964.5	963.4	962.3	961.2
172.5°	970.2	971.4	971.6	970.5	969.4	968.2	967.2
175°	976.6	977.9	978.0	976.9	975.8	974.7	973.6
177.5°	979.2	980.1	980.1	979.2	978.4	977.5	976.6
180°	978.5	978.5	978.5	978.5	978.5	978.5	978.5

(END OF REPORT)