

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331858-935

Luminaire Tested: **S122RDIW-S1005D1240U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331858-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6986.2 lumens  
Efficiency: N/A  
Efficacy: 91.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

### Luminous Intensity Polar Plot





TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	98	98	98	98	82	82	82	67	67	67	53	53	53	47
1	98	94	90	87	90	86	83	81	73	70	68	60	58	57	48	47	46	41
2	90	83	77	72	82	76	72	67	65	61	58	54	51	49	43	42	40	36
3	82	73	67	61	76	68	62	57	58	53	50	48	45	42	39	37	35	31
4	76	66	58	52	70	61	54	49	52	47	43	43	40	37	36	33	31	27
5	70	59	51	46	64	55	48	43	47	42	38	39	36	33	33	30	28	24
6	65	53	45	40	59	49	43	38	42	37	33	36	32	29	30	27	25	22
7	60	48	41	35	55	45	38	34	39	34	30	33	29	26	28	25	22	20
8	56	44	37	32	51	41	35	30	36	30	27	30	26	24	26	23	20	18
9	52	40	33	28	48	38	31	27	33	28	24	28	24	21	24	21	19	17
10	49	37	30	26	45	35	29	25	30	25	22	26	22	20	22	19	17	15

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	180.0	2.6
10°-20°	501.6	7.2
20°-30°	646.3	9.3
30°-40°	614.2	8.8
40°-50°	526.2	7.5
50°-60°	400.7	5.7
60°-70°	253.3	3.6
70°-80°	126.5	1.8
80°-90°	38.2	0.5
90°-100°	83.8	1.2
100°-110°	260.4	3.7
110°-120°	445.0	6.4
120°-130°	585.3	8.4
130°-140°	656.9	9.4
140°-150°	644.1	9.2
150°-160°	540.2	7.7
160°-170°	358.3	5.1
170°-180°	125.2	1.8
0°-30°	1327.9	19.0
0°-40°	1942.1	27.8
0°-60°	2869.0	41.1
0°-90°	3287.0	47.0
90°-120°	789.2	11.3
90°-150°	2675.4	38.3
90°-180°	3699.0	52.9
0°-180°	6986.2	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	27
90°	38	1	38	1	38	18
95°	69	58	69	58	69	77
105°	248	240	248	240	248	261
115°	447	447	447	447	447	441
125°	652	650	652	650	652	581
135°	851	841	851	841	851	655
145°	1032	1020	1032	1020	1032	644
155°	1176	1167	1176	1167	1176	541
165°	1270	1269	1270	1269	1270	358
175°	1316	1321	1316	1321	1316	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	16.0	16.5	16.4	16.4	16.4	16.4	16.5	17.1	16.7	17.3	15.7
90°	38.0	37.7	37.5	37.2	36.9	37.1	37.6	38.1	38.6	39.1	33.6
92.5°	36.2	36.2	36.1	36.0	36.0	35.9	35.8	35.7	35.6	35.5	34.2
95°	69.2	69.7	70.2	70.7	71.2	71.5	71.5	71.5	71.5	71.5	70.9
97.5°	119.9	119.9	120.0	120.0	120.1	120.1	120.1	120.1	120.1	120.1	119.2
100°	152.9	153.2	153.4	153.7	153.9	154.0	154.0	154.0	154.0	154.0	153.3
102.5°	190.5	190.7	191.0	191.2	191.5	191.5	191.3	191.1	190.9	190.7	189.8
105°	247.9	247.9	247.9	247.9	247.9	247.6	247.1	246.6	246.1	245.6	245.1
107.5°	301.9	303.0	304.2	305.3	306.4	306.9	306.7	306.5	306.3	306.1	306.1
110°	343.9	344.6	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	384.0	384.6	385.1	385.6	386.2	386.8	387.4	388.0	388.6	389.2	389.3
115°	446.6	447.3	448.1	448.8	449.5	450.0	450.3	450.6	450.8	451.0	451.5
117.5°	506.2	507.0	507.6	508.4	509.2	509.8	510.4	511.0	511.6	512.2	513.6
120°	548.2	548.9	549.7	550.4	551.1	551.5	551.5	551.5	551.5	551.5	553.5
122.5°	589.3	589.8	590.3	590.9	591.4	592.0	592.6	593.2	593.7	594.3	595.7
125°	651.9	652.2	652.5	652.7	653.0	653.5	654.2	655.0	655.7	656.4	657.2
127.5°	709.1	710.0	710.8	711.5	712.3	713.2	714.0	715.0	715.8	716.7	717.6
130°	750.2	751.2	752.3	753.2	754.2	754.9	755.4	756.0	756.4	756.9	757.4
132.5°	789.5	790.3	791.1	791.9	792.7	793.7	794.7	795.8	796.9	798.0	797.9
135°	850.7	851.4	852.2	852.9	853.7	854.2	854.5	854.7	854.9	855.1	854.7
137.5°	906.1	907.1	908.1	909.0	910.1	910.7	910.9	911.0	911.3	911.5	910.8
140°	944.5	945.5	946.5	947.4	948.5	948.9	948.9	948.9	948.9	948.9	947.7
142.5°	979.3	980.3	981.3	982.3	983.3	983.7	983.5	983.3	983.1	982.9	982.1
145°	1031.6	1032.6	1033.5	1034.6	1035.5	1035.9	1035.7	1035.4	1035.2	1034.9	1033.5
147.5°	1078.2	1079.2	1080.1	1081.1	1082.0	1082.2	1081.7	1081.1	1080.6	1080.0	1079.0
150°	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6	1107.6
152.5°	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2	1136.0
155°	1175.6	1176.3	1177.1	1177.8	1178.5	1178.3	1177.1	1175.9	1174.6	1173.4	1172.6
157.5°	1208.6	1209.8	1211.0	1212.2	1213.4	1213.1	1211.4	1209.8	1208.1	1206.4	1205.9
160°	1229.2	1230.2	1231.1	1232.2	1233.1	1232.9	1231.4	1229.9	1228.4	1226.9	1226.7
162.5°	1247.1	1248.2	1249.4	1250.6	1251.8	1251.5	1249.8	1248.2	1246.5	1244.8	1244.6
165°	1270.5	1271.7	1273.0	1274.2	1275.4	1275.2	1273.4	1271.7	1270.0	1268.3	1268.3
167.5°	1289.7	1291.0	1292.3	1293.6	1294.9	1294.6	1292.9	1291.2	1289.4	1287.6	1287.7
170°	1299.5	1301.0	1302.5	1304.0	1305.4	1305.4	1303.6	1301.8	1300.1	1298.4	1298.6
172.5°	1307.5	1309.1	1310.5	1312.0	1313.5	1313.4	1311.6	1309.9	1308.2	1306.4	1306.7
175°	1316.2	1317.8	1319.2	1320.7	1322.2	1322.1	1320.3	1318.6	1316.9	1315.1	1315.6
177.5°	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3	1320.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	14.6	14.0	12.9	11.5	11.5	11.5	13.5	15.5	14.0	13.0	12.6
90°	28.2	22.7	17.2	13.0	10.1	7.1	4.1	1.1	4.1	7.1	10.1
92.5°	32.9	31.6	30.3	28.6	26.4	24.3	22.0	19.9	22.0	24.3	26.4
95°	70.4	70.0	69.5	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	118.2	117.3	116.3	114.8	112.6	110.5	108.2	106.1	108.2	110.5	112.6
100°	152.6	151.8	151.1	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	188.8	187.9	186.9	185.6	184.1	182.4	180.9	179.3	180.9	182.4	184.1
105°	244.6	244.1	243.7	243.0	242.3	241.5	240.7	240.0	240.7	241.5	242.3
107.5°	306.1	306.1	306.1	305.6	304.4	303.4	302.3	301.2	302.3	303.4	304.4
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0





TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.6	389.8	389.9	389.3	387.9	386.3	384.9	383.4	384.9	386.3	387.9
115°	452.0	452.5	453.0	452.5	451.0	449.5	448.1	446.6	448.1	449.5	451.0
117.5°	515.0	516.3	517.8	517.5	515.5	513.5	511.5	509.5	511.5	513.5	515.5
120°	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	553.5	555.5	557.5
122.5°	597.2	598.6	599.9	599.4	597.0	594.7	592.3	589.9	592.3	594.7	597.0
125°	658.0	658.7	659.4	658.7	656.4	654.2	651.9	649.7	651.9	654.2	656.4
127.5°	718.5	719.5	720.3	719.4	716.5	713.7	710.8	708.0	710.8	713.7	716.5
130°	757.9	758.5	758.9	757.5	754.3	751.1	747.9	744.7	747.9	751.1	754.3
132.5°	797.8	797.7	797.6	796.3	793.6	791.0	788.3	785.7	788.3	791.0	793.6
135°	854.2	853.7	853.2	851.6	848.9	846.1	843.3	840.7	843.3	846.1	848.9
137.5°	910.2	909.5	908.9	907.4	905.2	902.9	900.7	898.5	900.7	902.9	905.2
140°	946.5	945.2	944.0	942.3	940.0	937.8	935.6	933.3	935.6	937.8	940.0
142.5°	981.2	980.3	979.5	978.0	975.8	973.5	971.3	969.1	971.3	973.5	975.8
145°	1031.9	1030.4	1029.0	1027.3	1025.6	1023.9	1022.2	1020.4	1022.2	1023.9	1025.6
147.5°	1078.1	1077.0	1076.1	1074.5	1072.5	1070.3	1068.2	1066.2	1068.2	1070.3	1072.5
150°	1106.6	1105.6	1104.7	1103.4	1101.9	1100.4	1098.9	1097.4	1098.9	1100.4	1101.9
152.5°	1134.8	1133.6	1132.4	1131.1	1129.5	1128.1	1126.6	1125.2	1126.6	1128.1	1129.5
155°	1171.8	1171.1	1170.4	1169.7	1168.9	1168.1	1167.4	1166.7	1167.4	1168.1	1168.9
157.5°	1205.5	1205.1	1204.6	1204.1	1203.7	1203.2	1202.6	1202.1	1202.6	1203.2	1203.7
160°	1226.4	1226.2	1226.0	1225.5	1225.1	1224.6	1224.1	1223.6	1224.1	1224.6	1225.1
162.5°	1244.3	1244.1	1243.8	1243.6	1243.5	1243.5	1243.4	1243.2	1243.4	1243.5	1243.5
165°	1268.3	1268.3	1268.3	1268.3	1268.6	1268.9	1269.1	1269.4	1269.1	1268.9	1268.6
167.5°	1287.8	1287.8	1287.9	1288.2	1289.0	1289.8	1290.5	1291.2	1290.5	1289.8	1289.0
170°	1298.9	1299.2	1299.4	1299.9	1300.6	1301.4	1302.1	1302.9	1302.1	1301.4	1300.6
172.5°	1306.9	1307.2	1307.4	1307.9	1308.6	1309.4	1310.2	1310.9	1310.2	1309.4	1308.6
175°	1316.1	1316.6	1317.2	1317.8	1318.4	1319.2	1320.0	1320.7	1320.0	1319.2	1318.4
177.5°	1321.0	1321.5	1321.9	1322.3	1322.9	1323.5	1324.1	1324.7	1324.1	1323.5	1322.9
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	12.7	12.9	13.0	14.0	15.2	15.8	15.7	15.0	14.9	14.8	14.3
90°	13.0	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1	36.9
92.5°	28.6	30.3	31.6	32.9	34.2	35.5	35.6	35.7	35.8	35.9	36.0
95°	68.0	69.5	70.0	70.4	70.9	71.5	71.5	71.5	71.5	71.5	71.2
97.5°	114.8	116.3	117.3	118.2	119.2	120.1	120.1	120.1	120.1	120.1	120.1
100°	149.7	151.1	151.8	152.6	153.3	154.0	154.0	154.0	154.0	154.0	153.9
102.5°	185.6	186.9	187.9	188.8	189.8	190.7	190.9	191.1	191.3	191.5	191.5
105°	243.0	243.7	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6	247.9
107.5°	305.6	306.1	306.1	306.1	306.1	306.1	306.3	306.5	306.7	306.9	306.4
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.8



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	389.3	389.9	389.8	389.6	389.3	389.2	388.6	388.0	387.4	386.8	386.2
115°	452.5	453.0	452.5	452.0	451.5	451.0	450.8	450.6	450.3	450.0	449.5
117.5°	517.5	517.8	516.3	515.0	513.6	512.2	511.6	511.0	510.4	509.8	509.2
120°	559.5	559.5	557.5	555.5	553.5	551.5	551.5	551.5	551.5	551.5	551.1
122.5°	599.4	599.9	598.6	597.2	595.7	594.3	593.7	593.2	592.6	592.0	591.4
125°	658.7	659.4	658.7	658.0	657.2	656.4	655.7	655.0	654.2	653.5	653.0
127.5°	719.4	720.3	719.5	718.5	717.6	716.7	715.8	715.0	714.0	713.2	712.3
130°	757.5	758.9	758.5	757.9	757.4	756.9	756.4	756.0	755.4	754.9	754.2
132.5°	796.3	797.6	797.7	797.8	797.9	798.0	796.9	795.8	794.7	793.7	792.7
135°	851.6	853.2	853.7	854.2	854.7	855.1	854.9	854.7	854.5	854.2	853.7
137.5°	907.4	908.9	909.5	910.2	910.8	911.5	911.3	911.0	910.9	910.7	910.1
140°	942.3	944.0	945.2	946.5	947.7	948.9	948.9	948.9	948.9	948.9	948.5
142.5°	978.0	979.5	980.3	981.2	982.1	982.9	983.1	983.3	983.5	983.7	983.3
145°	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2	1035.4	1035.7	1035.9	1035.5
147.5°	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6	1081.1	1081.7	1082.2	1082.0
150°	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6
152.5°	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9
155°	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6	1175.9	1177.1	1178.3	1178.5
157.5°	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1	1209.8	1211.4	1213.1	1213.4
160°	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4	1229.9	1231.4	1232.9	1233.1
162.5°	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5	1248.2	1249.8	1251.5	1251.8
165°	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0	1271.7	1273.4	1275.2	1275.4
167.5°	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4	1291.2	1292.9	1294.6	1294.9
170°	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1	1301.8	1303.6	1305.4	1305.4
172.5°	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2	1309.9	1311.6	1313.4	1313.5
175°	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9	1318.6	1320.3	1322.1	1322.2
177.5°	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	14.3	13.9	14.4	13.9	14.4	13.9	14.3	14.3	14.8	14.9	15.0
90°	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	37.1	37.6	38.1
92.5°	36.0	36.1	36.2	36.2	36.2	36.1	36.0	36.0	35.9	35.8	35.7
95°	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.5	71.5	71.5
97.5°	120.0	120.0	119.9	119.9	119.9	120.0	120.0	120.1	120.1	120.1	120.1
100°	153.7	153.4	153.2	152.9	153.2	153.4	153.7	153.9	154.0	154.0	154.0
102.5°	191.2	191.0	190.7	190.5	190.7	191.0	191.2	191.5	191.5	191.3	191.1
105°	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.6	247.1	246.6
107.5°	305.3	304.2	303.0	301.9	303.0	304.2	305.3	306.4	306.9	306.7	306.5
110°	346.1	345.3	344.6	343.9	344.6	345.3	346.1	346.8	347.2	347.2	347.2



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	385.6	385.1	384.6	384.0	384.6	385.1	385.6	386.2	386.8	387.4	388.0
115°	448.8	448.1	447.3	446.6	447.3	448.1	448.8	449.5	450.0	450.3	450.6
117.5°	508.4	507.6	507.0	506.2	507.0	507.6	508.4	509.2	509.8	510.4	511.0
120°	550.4	549.7	548.9	548.2	548.9	549.7	550.4	551.1	551.5	551.5	551.5
122.5°	590.9	590.3	589.8	589.3	589.8	590.3	590.9	591.4	592.0	592.6	593.2
125°	652.7	652.5	652.2	651.9	652.2	652.5	652.7	653.0	653.5	654.2	655.0
127.5°	711.5	710.8	710.0	709.1	710.0	710.8	711.5	712.3	713.2	714.0	715.0
130°	753.2	752.3	751.2	750.2	751.2	752.3	753.2	754.2	754.9	755.4	756.0
132.5°	791.9	791.1	790.3	789.5	790.3	791.1	791.9	792.7	793.7	794.7	795.8
135°	852.9	852.2	851.4	850.7	851.4	852.2	852.9	853.7	854.2	854.5	854.7
137.5°	909.0	908.1	907.1	906.1	907.1	908.1	909.0	910.1	910.7	910.9	911.0
140°	947.4	946.5	945.5	944.5	945.5	946.5	947.4	948.5	948.9	948.9	948.9
142.5°	982.3	981.3	980.3	979.3	980.3	981.3	982.3	983.3	983.7	983.5	983.3
145°	1034.6	1033.5	1032.6	1031.6	1032.6	1033.5	1034.6	1035.5	1035.9	1035.7	1035.4
147.5°	1081.1	1080.1	1079.2	1078.2	1079.2	1080.1	1081.1	1082.0	1082.2	1081.7	1081.1
150°	1110.9	1110.1	1109.3	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1
152.5°	1140.0	1139.1	1138.2	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1
155°	1177.8	1177.1	1176.3	1175.6	1176.3	1177.1	1177.8	1178.5	1178.3	1177.1	1175.9
157.5°	1212.2	1211.0	1209.8	1208.6	1209.8	1211.0	1212.2	1213.4	1213.1	1211.4	1209.8
160°	1232.2	1231.1	1230.2	1229.2	1230.2	1231.1	1232.2	1233.1	1232.9	1231.4	1229.9
162.5°	1250.6	1249.4	1248.2	1247.1	1248.2	1249.4	1250.6	1251.8	1251.5	1249.8	1248.2
165°	1274.2	1273.0	1271.7	1270.5	1271.7	1273.0	1274.2	1275.4	1275.2	1273.4	1271.7
167.5°	1293.6	1292.3	1291.0	1289.7	1291.0	1292.3	1293.6	1294.9	1294.6	1292.9	1291.2
170°	1304.0	1302.5	1301.0	1299.5	1301.0	1302.5	1304.0	1305.4	1305.4	1303.6	1301.8
172.5°	1312.0	1310.5	1309.1	1307.5	1309.1	1310.5	1312.0	1313.5	1313.4	1311.6	1309.9
175°	1320.7	1319.2	1317.8	1316.2	1317.8	1319.2	1320.7	1322.2	1322.1	1320.3	1318.6
177.5°	1323.9	1322.7	1321.5	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	15.7	15.8	15.2	14.0	13.0	12.9	12.7	12.6	13.0	14.0	15.5
90°	38.6	39.1	33.6	28.2	22.7	17.2	13.0	10.1	7.1	4.1	1.1
92.5°	35.6	35.5	34.2	32.9	31.6	30.3	28.6	26.4	24.3	22.0	19.9
95°	71.5	71.5	70.9	70.4	70.0	69.5	68.0	65.5	63.0	60.5	58.0
97.5°	120.1	120.1	119.2	118.2	117.3	116.3	114.8	112.6	110.5	108.2	106.1
100°	154.0	154.0	153.3	152.6	151.8	151.1	149.7	147.7	145.8	143.8	141.8
102.5°	190.9	190.7	189.8	188.8	187.9	186.9	185.6	184.1	182.4	180.9	179.3
105°	246.1	245.6	245.1	244.6	244.1	243.7	243.0	242.3	241.5	240.7	240.0
107.5°	306.3	306.1	306.1	306.1	306.1	306.1	305.6	304.4	303.4	302.3	301.2
110°	347.2	347.2	347.2	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.6	389.2	389.3	389.6	389.8	389.9	389.3	387.9	386.3	384.9	383.4
115°	450.8	451.0	451.5	452.0	452.5	453.0	452.5	451.0	449.5	448.1	446.6
117.5°	511.6	512.2	513.6	515.0	516.3	517.8	517.5	515.5	513.5	511.5	509.5
120°	551.5	551.5	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5
122.5°	593.7	594.3	595.7	597.2	598.6	599.9	599.4	597.0	594.7	592.3	589.9
125°	655.7	656.4	657.2	658.0	658.7	659.4	658.7	656.4	654.2	651.9	649.7
127.5°	715.8	716.7	717.6	718.5	719.5	720.3	719.4	716.5	713.7	710.8	708.0
130°	756.4	756.9	757.4	757.9	758.5	758.9	757.5	754.3	751.1	747.9	744.7
132.5°	796.9	798.0	797.9	797.8	797.7	797.6	796.3	793.6	791.0	788.3	785.7
135°	854.9	855.1	854.7	854.2	853.7	853.2	851.6	848.9	846.1	843.3	840.7
137.5°	911.3	911.5	910.8	910.2	909.5	908.9	907.4	905.2	902.9	900.7	898.5
140°	948.9	948.9	947.7	946.5	945.2	944.0	942.3	940.0	937.8	935.6	933.3
142.5°	983.1	982.9	982.1	981.2	980.3	979.5	978.0	975.8	973.5	971.3	969.1
145°	1035.2	1034.9	1033.5	1031.9	1030.4	1029.0	1027.3	1025.6	1023.9	1022.2	1020.4
147.5°	1080.6	1080.0	1079.0	1078.1	1077.0	1076.1	1074.5	1072.5	1070.3	1068.2	1066.2
150°	1109.3	1108.6	1107.6	1106.6	1105.6	1104.7	1103.4	1101.9	1100.4	1098.9	1097.4
152.5°	1138.2	1137.2	1136.0	1134.8	1133.6	1132.4	1131.1	1129.5	1128.1	1126.6	1125.2
155°	1174.6	1173.4	1172.6	1171.8	1171.1	1170.4	1169.7	1168.9	1168.1	1167.4	1166.7
157.5°	1208.1	1206.4	1205.9	1205.5	1205.1	1204.6	1204.1	1203.7	1203.2	1202.6	1202.1
160°	1228.4	1226.9	1226.7	1226.4	1226.2	1226.0	1225.5	1225.1	1224.6	1224.1	1223.6
162.5°	1246.5	1244.8	1244.6	1244.3	1244.1	1243.8	1243.6	1243.5	1243.5	1243.4	1243.2
165°	1270.0	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1268.6	1268.9	1269.1	1269.4
167.5°	1289.4	1287.6	1287.7	1287.8	1287.8	1287.9	1288.2	1289.0	1289.8	1290.5	1291.2
170°	1300.1	1298.4	1298.6	1298.9	1299.2	1299.4	1299.9	1300.6	1301.4	1302.1	1302.9
172.5°	1308.2	1306.4	1306.7	1306.9	1307.2	1307.4	1307.9	1308.6	1309.4	1310.2	1310.9
175°	1316.9	1315.1	1315.6	1316.1	1316.6	1317.2	1317.8	1318.4	1319.2	1320.0	1320.7
177.5°	1321.5	1320.3	1320.7	1321.0	1321.5	1321.9	1322.3	1322.9	1323.5	1324.1	1324.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.5	11.5	11.5	11.5	12.9	14.0	14.6	15.7	17.3	16.7	17.1
90°	4.1	7.1	10.1	13.0	17.2	22.7	28.2	33.6	39.1	38.6	38.1
92.5°	22.0	24.3	26.4	28.6	30.3	31.6	32.9	34.2	35.5	35.6	35.7
95°	60.5	63.0	65.5	68.0	69.5	70.0	70.4	70.9	71.5	71.5	71.5
97.5°	108.2	110.5	112.6	114.8	116.3	117.3	118.2	119.2	120.1	120.1	120.1
100°	143.8	145.8	147.7	149.7	151.1	151.8	152.6	153.3	154.0	154.0	154.0
102.5°	180.9	182.4	184.1	185.6	186.9	187.9	188.8	189.8	190.7	190.9	191.1
105°	240.7	241.5	242.3	243.0	243.7	244.1	244.6	245.1	245.6	246.1	246.6
107.5°	302.3	303.4	304.4	305.6	306.1	306.1	306.1	306.1	306.1	306.3	306.5
110°	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2





TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	384.9	386.3	387.9	389.3	389.9	389.8	389.6	389.3	389.2	388.6	388.0
115°	448.1	449.5	451.0	452.5	453.0	452.5	452.0	451.5	451.0	450.8	450.6
117.5°	511.5	513.5	515.5	517.5	517.8	516.3	515.0	513.6	512.2	511.6	511.0
120°	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	551.5	551.5
122.5°	592.3	594.7	597.0	599.4	599.9	598.6	597.2	595.7	594.3	593.7	593.2
125°	651.9	654.2	656.4	658.7	659.4	658.7	658.0	657.2	656.4	655.7	655.0
127.5°	710.8	713.7	716.5	719.4	720.3	719.5	718.5	717.6	716.7	715.8	715.0
130°	747.9	751.1	754.3	757.5	758.9	758.5	757.9	757.4	756.9	756.4	756.0
132.5°	788.3	791.0	793.6	796.3	797.6	797.7	797.8	797.9	798.0	796.9	795.8
135°	843.3	846.1	848.9	851.6	853.2	853.7	854.2	854.7	855.1	854.9	854.7
137.5°	900.7	902.9	905.2	907.4	908.9	909.5	910.2	910.8	911.5	911.3	911.0
140°	935.6	937.8	940.0	942.3	944.0	945.2	946.5	947.7	948.9	948.9	948.9
142.5°	971.3	973.5	975.8	978.0	979.5	980.3	981.2	982.1	982.9	983.1	983.3
145°	1022.2	1023.9	1025.6	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2	1035.4
147.5°	1068.2	1070.3	1072.5	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6	1081.1
150°	1098.9	1100.4	1101.9	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3	1110.1
152.5°	1126.6	1128.1	1129.5	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2	1139.1
155°	1167.4	1168.1	1168.9	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6	1175.9
157.5°	1202.6	1203.2	1203.7	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1	1209.8
160°	1224.1	1224.6	1225.1	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4	1229.9
162.5°	1243.4	1243.5	1243.5	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5	1248.2
165°	1269.1	1268.9	1268.6	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0	1271.7
167.5°	1290.5	1289.8	1289.0	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4	1291.2
170°	1302.1	1301.4	1300.6	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1	1301.8
172.5°	1310.2	1309.4	1308.6	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2	1309.9
175°	1320.0	1319.2	1318.4	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9	1318.6
177.5°	1324.1	1323.5	1322.9	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5	1322.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	16.5	16.4	16.4	16.4	16.4	16.5	16.0
90°	37.6	37.1	36.9	37.2	37.5	37.7	38.0
92.5°	35.8	35.9	36.0	36.0	36.1	36.2	36.2
95°	71.5	71.5	71.2	70.7	70.2	69.7	69.2
97.5°	120.1	120.1	120.1	120.0	120.0	119.9	119.9
100°	154.0	154.0	153.9	153.7	153.4	153.2	152.9
102.5°	191.3	191.5	191.5	191.2	191.0	190.7	190.5
105°	247.1	247.6	247.9	247.9	247.9	247.9	247.9
107.5°	306.7	306.9	306.4	305.3	304.2	303.0	301.9
110°	347.2	347.2	346.8	346.1	345.3	344.6	343.9



TEST NUMBER: P331858-935

CATALOG NUMBER: S122RDIW-S1005D1240U935-4F0-1E-UDD-A1

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	387.4	386.8	386.2	385.6	385.1	384.6	384.0
115°	450.3	450.0	449.5	448.8	448.1	447.3	446.6
117.5°	510.4	509.8	509.2	508.4	507.6	507.0	506.2
120°	551.5	551.5	551.1	550.4	549.7	548.9	548.2
122.5°	592.6	592.0	591.4	590.9	590.3	589.8	589.3
125°	654.2	653.5	653.0	652.7	652.5	652.2	651.9
127.5°	714.0	713.2	712.3	711.5	710.8	710.0	709.1
130°	755.4	754.9	754.2	753.2	752.3	751.2	750.2
132.5°	794.7	793.7	792.7	791.9	791.1	790.3	789.5
135°	854.5	854.2	853.7	852.9	852.2	851.4	850.7
137.5°	910.9	910.7	910.1	909.0	908.1	907.1	906.1
140°	948.9	948.9	948.5	947.4	946.5	945.5	944.5
142.5°	983.5	983.7	983.3	982.3	981.3	980.3	979.3
145°	1035.7	1035.9	1035.5	1034.6	1033.5	1032.6	1031.6
147.5°	1081.7	1082.2	1082.0	1081.1	1080.1	1079.2	1078.2
150°	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6
152.5°	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2
155°	1177.1	1178.3	1178.5	1177.8	1177.1	1176.3	1175.6
157.5°	1211.4	1213.1	1213.4	1212.2	1211.0	1209.8	1208.6
160°	1231.4	1232.9	1233.1	1232.2	1231.1	1230.2	1229.2
162.5°	1249.8	1251.5	1251.8	1250.6	1249.4	1248.2	1247.1
165°	1273.4	1275.2	1275.4	1274.2	1273.0	1271.7	1270.5
167.5°	1292.9	1294.6	1294.9	1293.6	1292.3	1291.0	1289.7
170°	1303.6	1305.4	1305.4	1304.0	1302.5	1301.0	1299.5
172.5°	1311.6	1313.4	1313.5	1312.0	1310.5	1309.1	1307.5
175°	1320.3	1322.1	1322.2	1320.7	1319.2	1317.8	1316.2
177.5°	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)