

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331583-930

Luminaire Tested: **S122DIW-S865D1440U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331583-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D1440U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7562.6 lumens
Efficiency: N/A
Efficacy: 98.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 76.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	104	104	104	104	95	95	95	95	77	77	77	60	60	60	45	45	45
1	95	91	87	84	86	83	79	76	67	65	63	53	51	50	40	39	38
2	87	79	73	68	78	72	67	63	59	55	52	46	44	42	35	33	32
3	79	70	62	57	71	63	57	52	52	47	44	41	38	35	31	29	27
4	72	62	54	48	65	56	49	44	46	41	37	36	33	30	28	25	23
5	66	55	47	41	60	50	43	38	41	36	32	33	29	26	25	22	20
6	61	49	41	35	55	45	38	33	37	32	28	30	26	23	23	20	18
7	56	44	36	31	51	40	34	29	33	28	24	27	23	20	21	18	16
8	52	40	32	27	47	37	30	25	30	25	22	25	21	18	19	16	14
9	48	37	29	24	44	34	27	23	28	23	19	23	19	16	17	15	13
10	45	33	26	22	41	31	24	20	26	21	17	21	17	14	16	14	12

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	1.4
10°-20°	297.7	3.9
20°-30°	437.6	5.8
30°-40°	508.3	6.7
40°-50°	507.7	6.7
50°-60°	442.8	5.9
60°-70°	327.4	4.3
70°-80°	185.4	2.5
80°-90°	53.8	0.7
90°-100°	53.5	0.7
100°-110°	196.0	2.6
110°-120°	524.0	6.9
120°-130°	865.0	11.4
130°-140°	919.9	12.2
140°-150°	855.0	11.3
150°-160°	687.4	9.1
160°-170°	443.0	5.9
170°-180°	152.5	2.0
0°-30°	841.1	11.1
0°-40°	1349.3	17.8
0°-60°	2299.8	30.4
0°-90°	2866.4	37.9
90°-120°	773.5	10.2
90°-150°	3413.3	45.1
90°-180°	4696.0	62.1
0°-180°	7562.6	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	14	23	29	31	6
95°	75	40	45	51	50	92
105°	352	368	71	83	88	377
115°	667	687	715	204	95	656
125°	943	958	980	988	991	840
135°	1166	1185	1196	1206	1205	901
145°	1353	1353	1372	1379	1374	846
155°	1490	1481	1494	1500	1491	686
165°	1570	1564	1566	1574	1566	443
175°	1606	1598	1600	1607	1597	153
180°	1602	1602	1602	1602	1602	



TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.8	16.0	16.1	16.4	16.6	16.6	16.6	16.7	16.7	16.8	16.5
90°	1.1	4.0	6.8	9.7	12.5	14.9	17.0	19.1	21.1	23.2	24.5
92.5°	23.4	23.2	22.9	22.7	22.4	22.7	23.8	24.9	25.8	26.9	27.6
95°	75.3	66.9	58.4	49.9	41.3	38.0	39.8	41.6	43.5	45.2	46.5
97.5°	149.6	125.6	101.7	77.7	53.7	43.9	48.0	52.2	56.3	60.5	61.6
100°	205.2	169.9	134.6	99.3	64.0	48.6	52.9	57.3	61.7	66.1	68.2
102.5°	266.4	259.0	251.5	244.0	236.6	214.5	177.9	141.2	104.6	67.9	70.6
105°	352.5	360.2	367.9	375.7	383.4	352.1	281.8	211.4	141.0	70.8	73.5
107.5°	450.6	456.8	463.1	469.3	475.6	436.5	352.1	267.7	183.4	99.1	96.1
110°	513.7	519.1	524.5	529.9	535.3	500.8	426.3	351.9	277.4	202.9	177.2



TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	573.1	577.8	582.6	587.4	592.2	585.4	567.0	548.6	530.2	511.8	417.8
115°	666.8	671.2	675.5	679.9	684.3	689.7	696.1	702.5	709.0	715.4	596.1
117.5°	750.5	755.4	760.3	765.2	770.1	774.7	779.1	783.6	788.0	792.5	763.6
120°	811.7	815.5	819.4	823.3	827.1	831.4	836.0	840.7	845.3	849.9	853.0
122.5°	863.6	867.7	871.8	875.9	880.0	884.5	889.5	894.5	899.6	904.7	906.5
125°	942.7	946.1	949.4	952.8	956.1	960.3	965.2	970.0	974.9	979.8	981.6
127.5°	1014.4	1018.1	1021.8	1025.5	1029.2	1032.9	1036.6	1040.2	1043.9	1047.6	1050.2
130°	1059.8	1064.0	1068.0	1072.2	1076.4	1079.8	1082.6	1085.5	1088.3	1091.1	1094.0
132.5°	1106.2	1109.7	1113.2	1116.7	1120.2	1123.4	1126.3	1129.0	1131.9	1134.7	1137.2
135°	1166.5	1170.6	1174.8	1178.8	1183.0	1186.2	1188.5	1190.8	1193.2	1195.5	1198.1
137.5°	1227.5	1230.4	1233.3	1236.2	1239.0	1241.8	1244.4	1247.1	1249.7	1252.3	1254.8
140°	1267.4	1269.4	1271.5	1273.6	1275.6	1278.1	1280.9	1283.8	1286.6	1289.4	1291.8
142.5°	1300.8	1302.6	1304.5	1306.4	1308.2	1310.8	1314.0	1317.3	1320.5	1323.7	1325.8
145°	1353.2	1352.9	1352.7	1352.4	1352.2	1354.2	1358.6	1363.0	1367.3	1371.7	1373.5
147.5°	1398.9	1397.9	1396.9	1396.0	1395.0	1396.6	1400.9	1405.3	1409.7	1414.0	1415.3
150°	1428.6	1426.8	1425.0	1423.2	1421.3	1422.5	1426.6	1430.8	1434.8	1439.0	1440.6
152.5°	1453.6	1451.6	1449.6	1447.6	1445.6	1446.5	1450.4	1454.3	1458.2	1462.2	1463.7
155°	1490.0	1487.7	1485.4	1483.0	1480.7	1481.2	1484.3	1487.4	1490.4	1493.5	1495.0
157.5°	1518.6	1516.6	1514.7	1512.7	1510.7	1510.8	1513.0	1515.2	1517.3	1519.5	1521.3
160°	1535.2	1533.7	1532.2	1530.6	1529.1	1529.1	1530.6	1532.2	1533.7	1535.2	1536.8
162.5°	1550.0	1548.6	1547.0	1545.5	1543.9	1543.8	1545.2	1546.5	1547.8	1549.2	1550.9
165°	1570.0	1568.5	1566.9	1565.4	1563.8	1563.5	1564.2	1565.0	1565.8	1566.5	1568.4
167.5°	1584.9	1583.3	1581.8	1580.2	1578.7	1578.3	1579.0	1579.7	1580.5	1581.2	1583.0
170°	1593.3	1591.7	1590.2	1588.6	1587.1	1586.5	1587.1	1587.6	1588.0	1588.6	1590.4
172.5°	1598.8	1597.3	1595.7	1594.2	1592.6	1592.1	1592.6	1593.1	1593.7	1594.2	1595.9
175°	1606.0	1604.2	1602.4	1600.6	1598.8	1598.1	1598.6	1599.1	1599.7	1600.2	1602.0
177.5°	1607.1	1605.7	1604.3	1602.8	1601.3	1600.8	1600.9	1601.2	1601.3	1601.6	1603.0
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5



TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	16.1	15.8	15.5	15.2	15.2	15.1	15.0	14.9
90°	25.8	27.1	28.4	29.3	29.8	30.2	30.8	31.3
92.5°	28.2	28.9	29.6	30.1	30.4	30.7	31.0	31.3
95°	47.8	49.1	50.4	50.9	50.6	50.4	50.1	49.9
97.5°	62.6	63.6	64.7	65.3	65.6	66.0	66.3	66.5
100°	70.2	72.3	74.4	75.7	76.1	76.6	77.2	77.7
102.5°	73.3	76.0	78.7	80.4	81.1	81.8	82.5	83.2
105°	76.4	79.2	82.1	84.0	85.0	86.1	87.1	88.1
107.5°	93.3	90.3	87.5	86.6	87.6	88.6	89.7	90.7
110°	151.4	125.6	99.9	87.5	88.5	89.5	90.6	91.6



TEST NUMBER: P331583-930

CATALOG NUMBER: S122DIW-S865D1440U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	323.8	229.8	135.8	89.2	90.1	90.9	91.7	92.5
115°	476.9	357.5	238.2	169.3	150.7	132.2	113.7	95.1
117.5°	734.7	705.9	677.0	632.1	571.1	510.1	449.1	388.2
120°	856.1	859.2	862.3	846.4	811.7	776.9	742.1	707.4
122.5°	908.4	910.3	912.1	909.6	902.9	896.2	889.4	882.6
125°	983.4	985.2	987.0	988.3	989.1	989.9	990.7	991.4
127.5°	1052.8	1055.4	1058.0	1059.5	1059.6	1059.7	1059.9	1060.1
130°	1096.8	1099.7	1102.4	1103.8	1103.5	1103.3	1103.0	1102.7
132.5°	1139.5	1142.0	1144.4	1145.5	1145.3	1145.0	1144.8	1144.4
135°	1200.6	1203.2	1205.8	1206.8	1206.3	1205.8	1205.3	1204.8
137.5°	1257.4	1259.9	1262.4	1263.2	1262.3	1261.5	1260.6	1259.7
140°	1294.0	1296.4	1298.7	1299.2	1298.0	1296.7	1295.3	1294.0
142.5°	1328.0	1330.1	1332.2	1332.6	1331.3	1330.0	1328.8	1327.5
145°	1375.3	1377.1	1379.0	1379.2	1377.9	1376.6	1375.3	1374.1
147.5°	1416.7	1418.0	1419.4	1419.4	1418.4	1417.3	1416.2	1415.1
150°	1442.1	1443.7	1445.2	1445.3	1444.1	1442.8	1441.4	1440.1
152.5°	1465.3	1466.8	1468.4	1468.3	1466.6	1464.9	1463.2	1461.5
155°	1496.6	1498.1	1499.7	1499.4	1497.4	1495.3	1493.2	1491.2
157.5°	1523.0	1524.7	1526.5	1526.3	1524.4	1522.3	1520.3	1518.3
160°	1538.3	1539.9	1541.4	1541.3	1539.5	1537.7	1535.9	1534.1
162.5°	1552.7	1554.4	1556.2	1555.9	1553.7	1551.5	1549.3	1547.1
165°	1570.2	1572.0	1573.8	1573.8	1572.0	1570.2	1568.4	1566.5
167.5°	1584.8	1586.6	1588.4	1588.1	1585.8	1583.5	1581.2	1578.8
170°	1592.2	1594.0	1595.8	1595.5	1593.3	1590.9	1588.6	1586.2
172.5°	1597.7	1599.5	1601.3	1601.1	1598.8	1596.4	1594.2	1591.8
175°	1603.8	1605.6	1607.4	1607.0	1604.4	1601.8	1599.3	1596.7
177.5°	1604.4	1605.9	1607.4	1607.1	1605.2	1603.4	1601.6	1599.7
180°	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5	1602.5

(END OF REPORT)