

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331862-935

Luminaire Tested: **S122RDIW-S1005D1440U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331862-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1440 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 7588.7 lumens
Efficiency: N/A
Efficacy: 91.5 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 82.9
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	43
1	97	93	89	86	89	85	82	79	71	69	67	57	56	55	45	44	43	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	81	73	66	60	74	67	61	56	56	52	48	46	43	40	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	41	38	35	33	31	29	25
5	69	58	50	45	63	54	47	42	45	40	36	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	37	33	38	32	29	31	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	34	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	2.4
10°-20°	501.6	6.6
20°-30°	646.3	8.5
30°-40°	614.2	8.1
40°-50°	526.2	6.9
50°-60°	400.7	5.3
60°-70°	253.3	3.3
70°-80°	126.5	1.7
80°-90°	39.1	0.5
90°-100°	97.5	1.3
100°-110°	302.7	4.0
110°-120°	517.4	6.8
120°-130°	680.4	9.0
130°-140°	763.7	10.1
140°-150°	748.8	9.9
150°-160°	628.1	8.3
160°-170°	416.6	5.5
170°-180°	145.6	1.9
0°-30°	1327.9	17.5
0°-40°	1942.1	25.6
0°-60°	2869.0	37.8
0°-90°	3287.8	43.3
90°-120°	917.6	12.1
90°-150°	3110.6	41.0
90°-180°	4301.0	56.7
0°-180°	7588.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	27
90°	44	1	44	1	44	20
95°	80	68	80	68	80	90
105°	288	279	288	279	288	303
115°	519	519	519	519	519	513
125°	758	755	758	755	758	676
135°	989	977	989	977	989	761
145°	1199	1186	1199	1186	1199	749
155°	1367	1356	1367	1356	1367	629
165°	1477	1476	1477	1476	1477	417
175°	1530	1536	1530	1536	1530	145
180°	1538	1538	1538	1538	1538	



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	17.3	17.7	17.7	17.7	17.6	17.6	17.7	18.3	17.9	18.6	16.8
90°	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3	44.9	45.5	39.1
92.5°	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5	41.4	41.2	39.8
95°	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1	83.1	83.1	82.5
97.5°	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7	139.7	139.7	138.5
100°	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1	179.1	179.1	178.2
102.5°	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1	222.0	221.7	220.6
105°	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7	286.1	285.6	285.0
107.5°	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4	356.1	355.9	355.9
110°	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1	451.8	452.5	452.7
115°	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8	524.1	524.4	525.0
117.5°	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2	594.9	595.6	597.1
120°	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2	641.2	641.2	643.5
122.5°	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7	690.3	691.0	692.7
125°	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5	762.3	763.2	764.1
127.5°	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2	832.2	833.4	834.4
130°	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9	879.5	880.0	880.6
132.5°	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3	926.5	927.8	927.7
135°	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7	994.0	994.3	993.7
137.5°	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2	1059.5	1059.7	1058.9
140°	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3	1103.3	1103.3	1101.9
142.5°	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2	1143.0	1142.8	1141.8
145°	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9	1203.5	1203.2	1201.5
147.5°	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0	1256.4	1255.7	1254.6
150°	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9	1287.8
152.5°	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2	1320.8
155°	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1	1365.6	1364.2	1363.3
157.5°	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5	1404.5	1402.7	1402.1
160°	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9	1428.2	1426.5	1426.2
162.5°	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2	1449.2	1447.3	1447.0
165°	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6	1476.5	1474.5	1474.5
167.5°	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2	1499.2	1497.1	1497.2
170°	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6	1511.6	1509.6	1509.8
172.5°	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9	1521.0	1518.9	1519.2
175°	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1	1531.1	1529.0	1529.7
177.5°	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0	1535.5
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	15.5	14.8	13.5	12.0	11.8	11.7	13.6	15.6	14.1	13.3	12.9
90°	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3	4.7	8.2	11.7
92.5°	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1	25.7	28.2	30.7
95°	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5	70.3	73.3	76.1
97.5°	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3	125.9	128.4	131.0
100°	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9	167.1	169.4	171.8
102.5°	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4	210.3	212.2	214.0
105°	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1	279.9	280.8	281.6
107.5°	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2	351.5	352.8	354.0
110°	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9	397.6	399.3	401.1



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7	447.5	449.2	450.9
115°	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2	520.9	522.6	524.4
117.5°	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5	594.7	597.0	599.3
120°	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	643.5	645.8	648.2
122.5°	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9	688.6	691.4	694.1
125°	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4	758.0	760.6	763.2
127.5°	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2	826.5	829.7	833.1
130°	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7	869.5	873.3	877.0
132.5°	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5	916.6	919.6	922.7
135°	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4	980.6	983.8	986.9
137.5°	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7	1047.2	1049.8	1052.4
140°	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1	1087.7	1090.4	1093.0
142.5°	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7	1129.3	1131.9	1134.5
145°	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4	1188.4	1190.4	1192.4
147.5°	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6	1242.0	1244.4	1246.9
150°	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9	1277.6	1279.4	1281.2
152.5°	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1	1309.8	1311.6	1313.3
155°	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4	1357.3	1358.1	1359.0
157.5°	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7	1398.3	1398.9	1399.5
160°	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6	1423.2	1423.7	1424.4
162.5°	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4	1445.6	1445.7	1445.8
165°	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8	1475.6	1475.2	1475.0
167.5°	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2	1500.4	1499.5	1498.7
170°	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8	1513.9	1513.0	1512.2
172.5°	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1	1523.3	1522.4	1521.6
175°	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5	1534.6	1533.8	1532.9
177.5°	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2	1539.6	1538.9	1538.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	13.1	13.5	13.7	15.0	16.3	17.0	16.9	16.3	16.1	16.0	15.5
90°	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3	43.7	43.1	43.0
92.5°	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5	41.6	41.8	41.8
95°	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1	83.1	83.1	82.7
97.5°	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7	139.7	139.7	139.7
100°	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1	179.1	179.1	179.0
102.5°	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1	222.4	222.7	222.6
105°	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7	287.3	287.8	288.2
107.5°	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4	356.6	356.8	356.3
110°	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.7	403.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1	450.4	449.7	449.0
115°	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8	523.5	523.2	522.6
117.5°	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2	593.5	592.8	591.9
120°	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2	641.2	641.2	640.8
122.5°	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7	689.0	688.3	687.6
125°	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5	760.6	759.7	759.2
127.5°	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2	830.2	829.1	828.2
130°	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9	878.3	877.7	876.8
132.5°	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3	924.0	922.7	921.6
135°	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7	993.4	993.2	992.6
137.5°	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2	1059.0	1058.8	1058.1
140°	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3	1103.3	1103.3	1102.8
142.5°	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2	1143.5	1143.7	1143.2
145°	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9	1204.1	1204.4	1203.9
147.5°	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0	1257.6	1258.3	1258.0
150°	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4
152.5°	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5
155°	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1	1368.6	1369.9	1370.3
157.5°	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5	1408.5	1410.5	1410.7
160°	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9	1431.7	1433.4	1433.7
162.5°	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2	1453.2	1455.1	1455.4
165°	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6	1480.6	1482.6	1482.9
167.5°	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2	1503.2	1505.2	1505.5
170°	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6	1515.6	1517.7	1517.8
172.5°	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9	1525.0	1527.0	1527.2
175°	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1	1535.1	1537.1	1537.3
177.5°	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	15.5	15.1	15.7	15.2	15.7	15.1	15.5	15.5	16.0	16.1	16.3
90°	43.3	43.6	43.8	44.2	43.8	43.6	43.3	43.0	43.1	43.7	44.3
92.5°	41.8	41.9	42.0	42.0	42.0	41.9	41.8	41.8	41.8	41.6	41.5
95°	82.2	81.6	81.0	80.5	81.0	81.6	82.2	82.7	83.1	83.1	83.1
97.5°	139.6	139.5	139.5	139.4	139.5	139.5	139.6	139.7	139.7	139.7	139.7
100°	178.7	178.4	178.1	177.8	178.1	178.4	178.7	179.0	179.1	179.1	179.1
102.5°	222.3	222.1	221.7	221.4	221.7	222.1	222.3	222.6	222.7	222.4	222.1
105°	288.2	288.2	288.2	288.2	288.2	288.2	288.2	288.2	287.8	287.3	286.7
107.5°	355.0	353.6	352.3	350.9	352.3	353.6	355.0	356.3	356.8	356.6	356.4
110°	402.3	401.5	400.6	399.8	400.6	401.5	402.3	403.2	403.7	403.7	403.7



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	448.4	447.8	447.1	446.5	447.1	447.8	448.4	449.0	449.7	450.4	451.1
115°	521.8	520.9	520.0	519.2	520.0	520.9	521.8	522.6	523.2	523.5	523.8
117.5°	591.1	590.2	589.4	588.5	589.4	590.2	591.1	591.9	592.8	593.5	594.2
120°	639.9	639.0	638.2	637.3	638.2	639.0	639.9	640.8	641.2	641.2	641.2
122.5°	687.0	686.4	685.7	685.1	685.7	686.4	687.0	687.6	688.3	689.0	689.7
125°	758.9	758.6	758.4	758.0	758.4	758.6	758.9	759.2	759.7	760.6	761.5
127.5°	827.2	826.3	825.4	824.5	825.4	826.3	827.2	828.2	829.1	830.2	831.2
130°	875.7	874.6	873.4	872.3	873.4	874.6	875.7	876.8	877.7	878.3	878.9
132.5°	920.8	919.8	918.9	917.9	918.9	919.8	920.8	921.6	922.7	924.0	925.3
135°	991.7	990.8	990.0	989.1	990.0	990.8	991.7	992.6	993.2	993.4	993.7
137.5°	1057.0	1055.8	1054.6	1053.4	1054.6	1055.8	1057.0	1058.1	1058.8	1059.0	1059.2
140°	1101.6	1100.4	1099.2	1098.1	1099.2	1100.4	1101.6	1102.8	1103.3	1103.3	1103.3
142.5°	1142.1	1140.9	1139.8	1138.6	1139.8	1140.9	1142.1	1143.2	1143.7	1143.5	1143.2
145°	1202.8	1201.7	1200.5	1199.4	1200.5	1201.7	1202.8	1203.9	1204.4	1204.1	1203.9
147.5°	1256.9	1255.8	1254.7	1253.6	1254.7	1255.8	1256.9	1258.0	1258.3	1257.6	1257.0
150°	1291.5	1290.6	1289.8	1288.9	1289.8	1290.6	1291.5	1292.4	1292.4	1291.5	1290.6
152.5°	1325.4	1324.3	1323.3	1322.2	1323.3	1324.3	1325.4	1326.5	1326.5	1325.4	1324.3
155°	1369.4	1368.6	1367.7	1366.8	1367.7	1368.6	1369.4	1370.3	1369.9	1368.6	1367.1
157.5°	1409.4	1408.0	1406.6	1405.2	1406.6	1408.0	1409.4	1410.7	1410.5	1408.5	1406.5
160°	1432.5	1431.4	1430.3	1429.1	1430.3	1431.4	1432.5	1433.7	1433.4	1431.7	1429.9
162.5°	1454.1	1452.7	1451.3	1449.8	1451.3	1452.7	1454.1	1455.4	1455.1	1453.2	1451.2
165°	1481.4	1480.1	1478.6	1477.1	1478.6	1480.1	1481.4	1482.9	1482.6	1480.6	1478.6
167.5°	1504.0	1502.4	1501.0	1499.4	1501.0	1502.4	1504.0	1505.5	1505.2	1503.2	1501.2
170°	1516.0	1514.3	1512.6	1510.9	1512.6	1514.3	1516.0	1517.8	1517.7	1515.6	1513.6
172.5°	1525.4	1523.7	1522.0	1520.3	1522.0	1523.7	1525.4	1527.2	1527.0	1525.0	1522.9
175°	1535.5	1533.8	1532.1	1530.3	1532.1	1533.8	1535.5	1537.3	1537.1	1535.1	1533.1
177.5°	1539.2	1537.8	1536.4	1535.0	1536.4	1537.8	1539.2	1540.6	1540.6	1539.2	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	16.9	17.0	16.3	15.0	13.7	13.5	13.1	12.9	13.3	14.1	15.6
90°	44.9	45.5	39.1	32.7	26.4	20.1	15.2	11.7	8.2	4.7	1.3
92.5°	41.4	41.2	39.8	38.3	36.8	35.3	33.2	30.7	28.2	25.7	23.1
95°	83.1	83.1	82.5	81.9	81.4	80.8	79.0	76.1	73.3	70.3	67.5
97.5°	139.7	139.7	138.5	137.5	136.4	135.3	133.5	131.0	128.4	125.9	123.3
100°	179.1	179.1	178.2	177.4	176.5	175.6	174.1	171.8	169.4	167.1	164.9
102.5°	222.0	221.7	220.6	219.5	218.4	217.3	215.9	214.0	212.2	210.3	208.4
105°	286.1	285.6	285.0	284.4	283.9	283.3	282.5	281.6	280.8	279.9	279.1
107.5°	356.1	355.9	355.9	355.9	355.9	355.9	355.2	354.0	352.8	351.5	350.2
110°	403.7	403.7	403.7	403.7	403.7	403.7	402.8	401.1	399.3	397.6	395.9



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	451.8	452.5	452.7	453.0	453.1	453.4	452.6	450.9	449.2	447.5	445.7
115°	524.1	524.4	525.0	525.6	526.2	526.7	526.2	524.4	522.6	520.9	519.2
117.5°	594.9	595.6	597.1	598.7	600.4	602.0	601.7	599.3	597.0	594.7	592.5
120°	641.2	641.2	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2
122.5°	690.3	691.0	692.7	694.3	695.9	697.5	697.0	694.1	691.4	688.6	685.9
125°	762.3	763.2	764.1	765.0	765.9	766.7	765.9	763.2	760.6	758.0	755.4
127.5°	832.2	833.4	834.4	835.4	836.5	837.5	836.4	833.1	829.7	826.5	823.2
130°	879.5	880.0	880.6	881.2	881.8	882.4	880.8	877.0	873.3	869.5	865.7
132.5°	926.5	927.8	927.7	927.6	927.5	927.4	925.7	922.7	919.6	916.6	913.5
135°	994.0	994.3	993.7	993.2	992.6	992.0	990.1	986.9	983.8	980.6	977.4
137.5°	1059.5	1059.7	1058.9	1058.2	1057.5	1056.7	1055.0	1052.4	1049.8	1047.2	1044.7
140°	1103.3	1103.3	1101.9	1100.4	1099.0	1097.5	1095.5	1093.0	1090.4	1087.7	1085.1
142.5°	1143.0	1142.8	1141.8	1140.8	1139.8	1138.8	1137.0	1134.5	1131.9	1129.3	1126.7
145°	1203.5	1203.2	1201.5	1199.8	1198.1	1196.4	1194.5	1192.4	1190.4	1188.4	1186.4
147.5°	1256.4	1255.7	1254.6	1253.4	1252.2	1251.1	1249.3	1246.9	1244.4	1242.0	1239.6
150°	1289.8	1288.9	1287.8	1286.6	1285.5	1284.3	1282.9	1281.2	1279.4	1277.6	1275.9
152.5°	1323.3	1322.2	1320.8	1319.4	1318.0	1316.6	1315.1	1313.3	1311.6	1309.8	1308.1
155°	1365.6	1364.2	1363.3	1362.4	1361.6	1360.7	1359.9	1359.0	1358.1	1357.3	1356.4
157.5°	1404.5	1402.7	1402.1	1401.6	1401.1	1400.6	1400.0	1399.5	1398.9	1398.3	1397.7
160°	1428.2	1426.5	1426.2	1425.9	1425.6	1425.4	1425.0	1424.4	1423.7	1423.2	1422.6
162.5°	1449.2	1447.3	1447.0	1446.7	1446.4	1446.1	1446.0	1445.8	1445.7	1445.6	1445.4
165°	1476.5	1474.5	1474.5	1474.5	1474.5	1474.5	1474.7	1475.0	1475.2	1475.6	1475.8
167.5°	1499.2	1497.1	1497.2	1497.3	1497.3	1497.4	1497.8	1498.7	1499.5	1500.4	1501.2
170°	1511.6	1509.6	1509.8	1510.2	1510.5	1510.7	1511.3	1512.2	1513.0	1513.9	1514.8
172.5°	1521.0	1518.9	1519.2	1519.5	1519.8	1520.1	1520.7	1521.6	1522.4	1523.3	1524.1
175°	1531.1	1529.0	1529.7	1530.2	1530.8	1531.4	1532.1	1532.9	1533.8	1534.6	1535.5
177.5°	1536.4	1535.0	1535.5	1535.9	1536.4	1536.9	1537.5	1538.2	1538.9	1539.6	1540.2
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.6	11.7	11.8	12.0	13.5	14.8	15.5	16.8	18.6	17.9	18.3
90°	4.7	8.2	11.7	15.2	20.1	26.4	32.7	39.1	45.5	44.9	44.3
92.5°	25.7	28.2	30.7	33.2	35.3	36.8	38.3	39.8	41.2	41.4	41.5
95°	70.3	73.3	76.1	79.0	80.8	81.4	81.9	82.5	83.1	83.1	83.1
97.5°	125.9	128.4	131.0	133.5	135.3	136.4	137.5	138.5	139.7	139.7	139.7
100°	167.1	169.4	171.8	174.1	175.6	176.5	177.4	178.2	179.1	179.1	179.1
102.5°	210.3	212.2	214.0	215.9	217.3	218.4	219.5	220.6	221.7	222.0	222.1
105°	279.9	280.8	281.6	282.5	283.3	283.9	284.4	285.0	285.6	286.1	286.7
107.5°	351.5	352.8	354.0	355.2	355.9	355.9	355.9	355.9	355.9	356.1	356.4
110°	397.6	399.3	401.1	402.8	403.7	403.7	403.7	403.7	403.7	403.7	403.7



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	447.5	449.2	450.9	452.6	453.4	453.1	453.0	452.7	452.5	451.8	451.1
115°	520.9	522.6	524.4	526.2	526.7	526.2	525.6	525.0	524.4	524.1	523.8
117.5°	594.7	597.0	599.3	601.7	602.0	600.4	598.7	597.1	595.6	594.9	594.2
120°	643.5	645.8	648.2	650.5	650.5	648.2	645.8	643.5	641.2	641.2	641.2
122.5°	688.6	691.4	694.1	697.0	697.5	695.9	694.3	692.7	691.0	690.3	689.7
125°	758.0	760.6	763.2	765.9	766.7	765.9	765.0	764.1	763.2	762.3	761.5
127.5°	826.5	829.7	833.1	836.4	837.5	836.5	835.4	834.4	833.4	832.2	831.2
130°	869.5	873.3	877.0	880.8	882.4	881.8	881.2	880.6	880.0	879.5	878.9
132.5°	916.6	919.6	922.7	925.7	927.4	927.5	927.6	927.7	927.8	926.5	925.3
135°	980.6	983.8	986.9	990.1	992.0	992.6	993.2	993.7	994.3	994.0	993.7
137.5°	1047.2	1049.8	1052.4	1055.0	1056.7	1057.5	1058.2	1058.9	1059.7	1059.5	1059.2
140°	1087.7	1090.4	1093.0	1095.5	1097.5	1099.0	1100.4	1101.9	1103.3	1103.3	1103.3
142.5°	1129.3	1131.9	1134.5	1137.0	1138.8	1139.8	1140.8	1141.8	1142.8	1143.0	1143.2
145°	1188.4	1190.4	1192.4	1194.5	1196.4	1198.1	1199.8	1201.5	1203.2	1203.5	1203.9
147.5°	1242.0	1244.4	1246.9	1249.3	1251.1	1252.2	1253.4	1254.6	1255.7	1256.4	1257.0
150°	1277.6	1279.4	1281.2	1282.9	1284.3	1285.5	1286.6	1287.8	1288.9	1289.8	1290.6
152.5°	1309.8	1311.6	1313.3	1315.1	1316.6	1318.0	1319.4	1320.8	1322.2	1323.3	1324.3
155°	1357.3	1358.1	1359.0	1359.9	1360.7	1361.6	1362.4	1363.3	1364.2	1365.6	1367.1
157.5°	1398.3	1398.9	1399.5	1400.0	1400.6	1401.1	1401.6	1402.1	1402.7	1404.5	1406.5
160°	1423.2	1423.7	1424.4	1425.0	1425.4	1425.6	1425.9	1426.2	1426.5	1428.2	1429.9
162.5°	1445.6	1445.7	1445.8	1446.0	1446.1	1446.4	1446.7	1447.0	1447.3	1449.2	1451.2
165°	1475.6	1475.2	1475.0	1474.7	1474.5	1474.5	1474.5	1474.5	1474.5	1476.5	1478.6
167.5°	1500.4	1499.5	1498.7	1497.8	1497.4	1497.3	1497.3	1497.2	1497.1	1499.2	1501.2
170°	1513.9	1513.0	1512.2	1511.3	1510.7	1510.5	1510.2	1509.8	1509.6	1511.6	1513.6
172.5°	1523.3	1522.4	1521.6	1520.7	1520.1	1519.8	1519.5	1519.2	1518.9	1521.0	1522.9
175°	1534.6	1533.8	1532.9	1532.1	1531.4	1530.8	1530.2	1529.7	1529.0	1531.1	1533.1
177.5°	1539.6	1538.9	1538.2	1537.5	1536.9	1536.4	1535.9	1535.5	1535.0	1536.4	1537.8
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	17.7	17.6	17.6	17.7	17.7	17.7	17.3
90°	43.7	43.1	43.0	43.3	43.6	43.8	44.2
92.5°	41.6	41.8	41.8	41.8	41.9	42.0	42.0
95°	83.1	83.1	82.7	82.2	81.6	81.0	80.5
97.5°	139.7	139.7	139.7	139.6	139.5	139.5	139.4
100°	179.1	179.1	179.0	178.7	178.4	178.1	177.8
102.5°	222.4	222.7	222.6	222.3	222.1	221.7	221.4
105°	287.3	287.8	288.2	288.2	288.2	288.2	288.2
107.5°	356.6	356.8	356.3	355.0	353.6	352.3	350.9
110°	403.7	403.7	403.2	402.3	401.5	400.6	399.8



TEST NUMBER: P331862-935

CATALOG NUMBER: S122RDIW-S1005D1440U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	450.4	449.7	449.0	448.4	447.8	447.1	446.5
115°	523.5	523.2	522.6	521.8	520.9	520.0	519.2
117.5°	593.5	592.8	591.9	591.1	590.2	589.4	588.5
120°	641.2	641.2	640.8	639.9	639.0	638.2	637.3
122.5°	689.0	688.3	687.6	687.0	686.4	685.7	685.1
125°	760.6	759.7	759.2	758.9	758.6	758.4	758.0
127.5°	830.2	829.1	828.2	827.2	826.3	825.4	824.5
130°	878.3	877.7	876.8	875.7	874.6	873.4	872.3
132.5°	924.0	922.7	921.6	920.8	919.8	918.9	917.9
135°	993.4	993.2	992.6	991.7	990.8	990.0	989.1
137.5°	1059.0	1058.8	1058.1	1057.0	1055.8	1054.6	1053.4
140°	1103.3	1103.3	1102.8	1101.6	1100.4	1099.2	1098.1
142.5°	1143.5	1143.7	1143.2	1142.1	1140.9	1139.8	1138.6
145°	1204.1	1204.4	1203.9	1202.8	1201.7	1200.5	1199.4
147.5°	1257.6	1258.3	1258.0	1256.9	1255.8	1254.7	1253.6
150°	1291.5	1292.4	1292.4	1291.5	1290.6	1289.8	1288.9
152.5°	1325.4	1326.5	1326.5	1325.4	1324.3	1323.3	1322.2
155°	1368.6	1369.9	1370.3	1369.4	1368.6	1367.7	1366.8
157.5°	1408.5	1410.5	1410.7	1409.4	1408.0	1406.6	1405.2
160°	1431.7	1433.4	1433.7	1432.5	1431.4	1430.3	1429.1
162.5°	1453.2	1455.1	1455.4	1454.1	1452.7	1451.3	1449.8
165°	1480.6	1482.6	1482.9	1481.4	1480.1	1478.6	1477.1
167.5°	1503.2	1505.2	1505.5	1504.0	1502.4	1501.0	1499.4
170°	1515.6	1517.7	1517.8	1516.0	1514.3	1512.6	1510.9
172.5°	1525.0	1527.0	1527.2	1525.4	1523.7	1522.0	1520.3
175°	1535.1	1537.1	1537.3	1535.5	1533.8	1532.1	1530.3
177.5°	1539.2	1540.6	1540.6	1539.2	1537.8	1536.4	1535.0
180°	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2	1538.2

(END OF REPORT)