

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331559-930

Luminaire Tested: **S122DIW-S865D435U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331559-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D435U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER  
UPLIGHT 435 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 4275.0 lumens  
Efficiency: N/A  
Efficacy: 92.5 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Direct


Input Watts (W): 46.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	97	93	90	96	92	88	85	81	79	76	72	70	68	63	62	61	56
2	93	85	79	73	87	80	75	70	71	67	63	63	60	57	56	53	51	47
3	84	75	67	61	79	71	64	58	63	58	53	56	52	48	49	46	43	40
4	77	66	58	52	73	63	55	50	56	50	45	50	45	41	44	41	37	34
5	71	59	51	45	67	56	48	43	50	44	39	45	40	36	40	36	33	30
6	66	53	45	39	62	50	43	37	45	39	34	41	36	32	36	32	29	26
7	61	48	40	34	57	46	38	33	41	35	30	37	32	28	33	29	26	23
8	56	44	36	30	53	42	34	29	38	32	27	34	29	25	30	26	23	21
9	53	40	32	27	50	38	31	26	35	29	24	31	26	23	28	24	21	19
10	49	37	29	24	46	35	28	24	32	26	22	29	24	21	26	22	19	17

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	105.8	2.5
10°-20°	297.7	7.0
20°-30°	437.6	10.2
30°-40°	508.3	11.9
40°-50°	507.7	11.9
50°-60°	442.8	10.4
60°-70°	327.4	7.7
70°-80°	185.4	4.3
80°-90°	51.0	1.2
90°-100°	16.1	0.4
100°-110°	58.9	1.4
110°-120°	157.5	3.7
120°-130°	259.9	6.1
130°-140°	276.4	6.5
140°-150°	256.9	6.0
150°-160°	206.6	4.8
160°-170°	133.1	3.1
170°-180°	45.8	1.1
0°-30°	841.1	19.7
0°-40°	1349.3	31.6
0°-60°	2299.8	53.8
0°-90°	2863.7	67.0
90°-120°	232.4	5.4
90°-150°	1025.8	24.0
90°-180°	1411.0	33.0
0°-180°	4275.0	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	0	4	7	9	9	3
95°	23	12	14	15	15	28
105°	106	110	21	25	26	113
115°	200	206	215	61	28	197
125°	283	288	294	297	298	252
135°	351	356	359	362	362	271
145°	407	407	412	414	413	254
155°	448	445	449	451	448	206
165°	472	470	471	473	471	133
175°	483	480	481	483	480	46
180°	482	482	482	482	482	



TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.4	15.2	15.0	14.8	14.6	14.3	14.0	13.8	13.5	13.0
90°	0.3	1.2	2.0	2.9	3.8	4.5	5.1	5.7	6.4	6.9	7.3
92.5°	7.0	6.9	6.8	6.8	6.8	6.8	7.2	7.5	7.7	8.1	8.3
95°	22.7	20.1	17.5	15.0	12.4	11.4	12.0	12.5	13.0	13.6	13.9
97.5°	44.9	37.7	30.6	23.3	16.1	13.2	14.4	15.7	17.0	18.2	18.5
100°	61.7	51.0	40.4	29.8	19.2	14.6	15.9	17.2	18.5	19.9	20.5
102.5°	80.1	77.9	75.6	73.4	71.1	64.5	53.5	42.5	31.5	20.4	21.2
105°	105.9	108.3	110.6	112.9	115.2	105.8	84.7	63.5	42.4	21.3	22.1
107.5°	135.4	137.3	139.2	141.0	142.9	131.2	105.8	80.5	55.1	29.8	28.9
110°	154.3	156.0	157.6	159.2	160.9	150.5	128.1	105.7	83.3	61.0	53.2



TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	172.2	173.7	175.1	176.5	178.0	175.9	170.4	164.9	159.3	153.8	125.6
115°	200.4	201.7	203.0	204.3	205.6	207.2	209.2	211.2	213.0	215.0	179.1
117.5°	225.5	227.0	228.4	229.9	231.4	232.8	234.2	235.5	236.8	238.1	229.5
120°	243.9	245.1	246.2	247.4	248.6	249.9	251.3	252.7	254.0	255.4	256.3
122.5°	259.5	260.7	262.0	263.2	264.4	265.8	267.3	268.8	270.4	271.9	272.5
125°	283.3	284.3	285.4	286.3	287.3	288.5	290.1	291.6	293.0	294.5	295.0
127.5°	304.8	306.0	307.0	308.2	309.3	310.4	311.5	312.6	313.7	314.8	315.6
130°	318.5	319.8	321.0	322.2	323.4	324.5	325.4	326.2	327.1	327.9	328.7
132.5°	332.5	333.5	334.5	335.6	336.6	337.6	338.4	339.3	340.1	341.0	341.8
135°	350.6	351.8	353.0	354.2	355.6	356.4	357.2	357.9	358.6	359.3	360.0
137.5°	368.9	369.7	370.6	371.5	372.3	373.2	374.0	374.8	375.5	376.3	377.1
140°	380.9	381.5	382.1	382.7	383.4	384.1	385.0	385.8	386.6	387.5	388.2
142.5°	390.9	391.5	392.0	392.6	393.1	394.0	394.8	395.8	396.8	397.8	398.4
145°	406.7	406.6	406.5	406.4	406.3	407.0	408.3	409.6	410.9	412.2	412.8
147.5°	420.4	420.1	419.8	419.6	419.2	419.7	421.0	422.3	423.6	424.9	425.3
150°	429.3	428.8	428.2	427.7	427.1	427.5	428.8	430.0	431.2	432.4	432.9
152.5°	436.8	436.3	435.6	435.0	434.4	434.7	435.9	437.1	438.2	439.4	439.9
155°	447.8	447.1	446.4	445.7	445.0	445.2	446.1	446.9	447.9	448.8	449.3
157.5°	456.3	455.8	455.2	454.6	454.0	454.0	454.7	455.3	456.0	456.6	457.1
160°	461.4	460.9	460.5	460.0	459.5	459.5	460.0	460.5	460.9	461.4	461.9
162.5°	465.9	465.4	464.9	464.5	464.0	464.0	464.3	464.7	465.1	465.5	466.1
165°	471.8	471.4	470.9	470.4	469.9	469.9	470.1	470.3	470.6	470.8	471.3
167.5°	476.3	475.8	475.4	474.9	474.4	474.3	474.5	474.7	475.0	475.2	475.7
170°	478.8	478.3	477.8	477.4	477.0	476.8	477.0	477.1	477.3	477.4	477.9
172.5°	480.5	480.0	479.6	479.1	478.6	478.5	478.6	478.7	478.9	479.1	479.6
175°	482.7	482.1	481.5	481.0	480.5	480.3	480.5	480.6	480.7	480.9	481.4
177.5°	483.0	482.6	482.1	481.7	481.3	481.0	481.1	481.2	481.3	481.3	481.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6



TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	12.5	12.0	11.5	11.2	11.0	10.8	10.7	10.5
90°	7.7	8.2	8.5	8.8	9.0	9.1	9.3	9.4
92.5°	8.5	8.7	8.9	9.0	9.1	9.2	9.3	9.4
95°	14.3	14.8	15.2	15.3	15.2	15.2	15.1	15.0
97.5°	18.8	19.2	19.4	19.6	19.7	19.8	19.9	20.0
100°	21.1	21.7	22.3	22.7	22.9	23.1	23.2	23.3
102.5°	22.0	22.8	23.6	24.1	24.4	24.6	24.8	25.0
105°	23.0	23.8	24.7	25.3	25.5	25.8	26.2	26.5
107.5°	28.0	27.1	26.3	26.0	26.3	26.7	26.9	27.2
110°	45.5	37.7	30.0	26.3	26.6	26.9	27.2	27.6





TEST NUMBER: P331559-930

CATALOG NUMBER: S122DIW-S865D435U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	97.3	69.1	40.8	26.8	27.1	27.3	27.6	27.8
115°	143.3	107.5	71.6	50.9	45.3	39.7	34.2	28.5
117.5°	220.8	212.1	203.4	190.0	171.6	153.3	135.0	116.7
120°	257.3	258.2	259.2	254.4	243.9	233.5	223.0	212.5
122.5°	273.0	273.5	274.1	273.4	271.3	269.3	267.3	265.2
125°	295.5	296.1	296.6	297.0	297.3	297.5	297.7	297.9
127.5°	316.4	317.2	318.0	318.4	318.5	318.5	318.5	318.5
130°	329.6	330.4	331.3	331.7	331.7	331.6	331.5	331.4
132.5°	342.5	343.2	343.9	344.2	344.1	344.1	344.1	344.0
135°	360.9	361.6	362.4	362.6	362.6	362.4	362.2	362.1
137.5°	377.9	378.6	379.4	379.6	379.4	379.1	378.9	378.5
140°	388.9	389.6	390.3	390.4	390.0	389.6	389.3	388.9
142.5°	399.1	399.7	400.4	400.5	400.1	399.7	399.3	398.9
145°	413.4	413.8	414.4	414.5	414.1	413.7	413.4	412.9
147.5°	425.7	426.2	426.6	426.6	426.2	425.9	425.6	425.3
150°	433.4	433.8	434.3	434.4	434.0	433.6	433.2	432.8
152.5°	440.3	440.8	441.3	441.2	440.8	440.3	439.7	439.2
155°	449.8	450.2	450.7	450.6	450.0	449.4	448.7	448.2
157.5°	457.7	458.2	458.8	458.7	458.1	457.5	456.9	456.3
160°	462.3	462.8	463.3	463.2	462.7	462.1	461.5	461.1
162.5°	466.6	467.2	467.7	467.6	466.9	466.3	465.6	465.0
165°	471.9	472.4	473.0	473.0	472.4	471.9	471.3	470.8
167.5°	476.3	476.8	477.4	477.3	476.5	475.9	475.2	474.5
170°	478.5	479.1	479.6	479.5	478.8	478.1	477.4	476.7
172.5°	480.1	480.7	481.3	481.2	480.5	479.8	479.1	478.4
175°	482.0	482.5	483.1	483.0	482.2	481.4	480.6	479.9
177.5°	482.2	482.6	483.1	483.0	482.4	481.8	481.3	480.8
180°	481.6	481.6	481.6	481.6	481.6	481.6	481.6	481.6

(END OF REPORT)