

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331847-935

Luminaire Tested: **S122RDIW-S1005D435U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331847-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4490.5 lumens
Efficiency: N/A
Efficacy: 85.7 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	111	111	111	111	105	105	105	105	93	93	93	82	82	82	72	72	72	67
1	102	98	94	91	96	93	89	86	82	80	78	73	71	69	64	63	62	58
2	94	86	80	75	88	82	76	72	73	69	65	65	62	59	57	55	53	49
3	86	77	69	64	81	72	66	61	65	60	56	58	54	51	51	48	46	42
4	79	68	60	54	74	65	58	52	58	53	48	52	48	44	46	43	40	37
5	73	61	53	47	68	58	51	45	52	47	42	47	42	39	42	38	35	33
6	67	55	47	41	63	53	45	40	48	42	37	43	38	34	38	35	31	29
7	62	50	42	37	59	48	41	36	43	37	33	39	34	31	35	31	28	26
8	58	46	38	33	55	44	37	32	40	34	30	36	31	28	33	29	26	23
9	54	42	35	30	51	40	33	29	37	31	27	33	29	25	30	26	23	21
10	51	39	32	27	48	37	31	26	34	28	24	31	26	23	28	24	21	19

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	23541	23541	23541
5°	23631	23246	23376
10°	23451	22866	22673
15°	23181	22188	21549
20°	22807	21220	20155
25°	22425	20122	18805
30°	21895	18990	17074
35°	21378	17763	15554
40°	20858	16493	13793
45°	20247	15066	12202
50°	19623	13622	10638
55°	18978	12073	9137
60°	18235	10440	7585
65°	17391	8772	6907
70°	16386	7227	6354
75°	15147	6588	5926
80°	13371	5895	5393
85°	10504	4650	4650



TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	136.5	3.0
10°-20°	374.7	8.3
20°-30°	526.2	11.7
30°-40°	573.8	12.8
40°-50°	527.6	11.7
50°-60°	414.4	9.2
60°-70°	270.2	6.0
70°-80°	139.3	3.1
80°-90°	37.4	0.8
90°-100°	17.0	0.4
100°-110°	62.2	1.4
110°-120°	166.3	3.7
120°-130°	274.5	6.1
130°-140°	291.9	6.5
140°-150°	271.3	6.0
150°-160°	218.2	4.9
160°-170°	140.6	3.1
170°-180°	48.4	1.1
0°-30°	1037.4	23.1
0°-40°	1611.3	35.9
0°-60°	2553.2	56.9
0°-90°	3000.1	66.8
90°-120°	245.5	5.5
90°-150°	1083.3	24.1
90°-180°	1490.0	33.2
0°-180°	4490.5	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1458	1458	1458	1458	1458	
5°	1458	1451	1434	1445	1442	138
15°	1387	1371	1327	1303	1289	390
25°	1259	1214	1130	1077	1056	579
35°	1085	1015	901	821	789	678
45°	887	796	660	570	534	684
55°	674	569	429	353	325	602
65°	455	348	230	187	181	451
75°	243	153	106	97	95	257
85°	57	30	25	25	25	67
90°	0	4	7	9	10	3
95°	24	13	14	16	16	29
105°	112	117	22	26	28	120
115°	212	218	227	65	30	208
125°	299	304	311	313	315	267
135°	370	376	379	383	382	286
145°	430	429	435	438	436	269
155°	473	470	474	476	473	218
165°	498	496	497	500	497	141
175°	510	507	508	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1463.4	1462.2	1460.9	1459.8	1458.6	1456.7	1454.1	1451.6	1449.1	1446.5	1448.8
5°	1458.0	1456.6	1455.1	1453.6	1452.2	1449.6	1445.7	1441.9	1438.1	1434.3	1436.9
7.5°	1443.0	1441.2	1439.4	1437.5	1435.7	1432.6	1428.1	1423.7	1419.3	1414.8	1415.6
10°	1430.4	1428.3	1426.2	1424.2	1422.1	1418.2	1412.3	1406.4	1400.6	1394.7	1393.9
12.5°	1414.5	1412.0	1409.5	1407.0	1404.5	1399.4	1391.9	1384.4	1376.9	1369.4	1367.8
15°	1386.8	1383.5	1380.4	1377.1	1373.9	1367.3	1357.4	1347.4	1337.4	1327.4	1321.9
17.5°	1352.7	1347.8	1342.9	1338.0	1333.1	1324.2	1311.4	1298.6	1285.8	1273.1	1266.4
20°	1327.4	1321.5	1315.7	1309.8	1304.0	1293.7	1279.0	1264.4	1249.7	1235.0	1227.7
22.5°	1299.9	1293.4	1286.9	1280.3	1273.7	1262.1	1245.6	1229.1	1212.5	1196.0	1186.5
25°	1258.8	1249.4	1240.0	1230.6	1221.2	1206.9	1187.6	1168.2	1148.8	1129.5	1117.5
27.5°	1209.2	1199.0	1188.8	1178.6	1168.4	1152.4	1130.6	1108.7	1086.9	1065.1	1051.1
30°	1174.4	1163.2	1152.1	1140.9	1129.8	1112.5	1089.0	1065.6	1042.2	1018.6	1003.7
32.5°	1140.6	1127.6	1114.6	1101.6	1088.5	1070.1	1046.1	1022.2	998.2	974.3	957.3
35°	1084.6	1069.7	1054.7	1039.7	1024.8	1004.4	978.6	952.9	927.0	901.2	882.8
37.5°	1028.7	1012.3	995.8	979.4	963.0	941.1	913.5	886.1	858.5	831.0	810.7
40°	989.6	972.1	954.4	936.9	919.3	896.2	867.8	839.4	810.9	782.5	761.6
42.5°	949.5	931.0	912.5	893.9	875.4	851.4	822.1	792.6	763.3	733.9	712.4
45°	886.7	867.0	847.4	827.8	808.1	782.9	752.1	721.3	690.5	659.8	638.9
47.5°	825.4	804.7	783.9	763.0	742.2	715.9	684.2	652.3	620.5	588.8	568.1
50°	781.2	760.3	739.5	718.7	697.8	671.3	639.1	606.8	574.5	542.3	522.1
52.5°	737.9	716.1	694.4	672.6	650.8	624.2	592.6	561.1	529.5	498.0	478.5
55°	674.2	651.4	628.5	605.6	582.8	555.5	523.8	492.1	460.5	428.9	411.2
57.5°	609.1	585.7	562.1	538.7	515.2	488.3	457.9	427.4	397.0	366.5	350.4
60°	564.7	541.3	517.8	494.4	470.9	444.1	413.9	383.7	353.4	323.3	308.3
62.5°	521.5	498.0	474.6	451.1	427.7	401.5	372.7	343.9	315.1	286.4	272.1
65°	455.2	431.4	407.8	384.0	360.2	335.2	308.8	282.4	256.0	229.6	219.6
67.5°	391.3	367.8	344.2	320.6	297.0	273.4	249.7	225.9	202.2	178.4	173.8
70°	347.1	324.2	301.3	278.4	255.5	234.0	213.8	193.6	173.3	153.1	150.2
72.5°	304.8	282.8	261.0	239.0	217.1	197.9	181.8	165.5	149.2	133.0	130.5
75°	242.8	222.2	201.7	181.2	160.7	145.4	135.4	125.5	115.5	105.6	103.5
77.5°	181.8	163.8	145.9	127.9	109.8	98.4	93.6	88.8	83.9	79.2	78.0
80°	143.8	128.9	113.9	98.9	84.0	75.1	72.2	69.2	66.3	63.4	62.2
82.5°	109.0	97.3	85.7	74.0	62.3	55.4	53.5	51.5	49.5	47.5	46.8
85°	56.7	50.5	44.4	38.2	32.1	28.6	27.7	26.9	25.9	25.1	25.1
87.5°	17.0	15.2	13.6	11.9	10.2	9.4	9.6	9.6	9.8	9.9	9.7
90°	0.3	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7
92.5°	7.4	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8
95°	23.9	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7
97.5°	47.4	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5
100°	65.2	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6
102.5°	84.6	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4
105°	111.8	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3
107.5°	143.0	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5
110°	163.0	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2



TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.8	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6
115°	211.6	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2
117.5°	238.2	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4
120°	257.6	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7
122.5°	274.1	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7
125°	299.2	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5
127.5°	321.9	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3
130°	336.4	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2
132.5°	351.1	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9
135°	370.2	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2
137.5°	389.6	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2
140°	402.3	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9
142.5°	412.8	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8
145°	429.5	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9
147.5°	443.9	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2
150°	453.4	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2
152.5°	461.3	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5
155°	472.9	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5
157.5°	481.9	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8
160°	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8
162.5°	492.0	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2
165°	498.3	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7
167.5°	503.0	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4
170°	505.7	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7
172.5°	507.4	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5
175°	509.7	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4
177.5°	510.1	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0	1458.0
2.5°	1451.1	1453.5	1455.9	1456.7	1456.3	1455.9	1455.3	1454.9
5°	1439.6	1442.3	1444.8	1445.7	1444.8	1444.0	1443.1	1442.3
7.5°	1416.3	1417.0	1417.8	1417.5	1415.9	1414.4	1412.9	1411.4
10°	1392.9	1392.1	1391.2	1389.9	1388.1	1386.4	1384.6	1382.9
12.5°	1366.2	1364.6	1363.0	1360.8	1357.9	1355.0	1352.0	1349.1
15°	1316.3	1310.7	1305.1	1300.9	1298.0	1295.0	1292.1	1289.2
17.5°	1259.8	1253.2	1246.6	1240.7	1235.7	1230.6	1225.5	1220.6
20°	1220.4	1213.1	1205.7	1198.9	1192.4	1185.9	1179.5	1173.0
22.5°	1177.2	1167.7	1158.2	1151.1	1146.3	1141.5	1136.7	1131.9
25°	1105.4	1093.5	1081.4	1073.2	1068.8	1064.4	1060.0	1055.6
27.5°	1037.1	1023.0	1009.0	998.5	991.5	984.6	977.6	970.6
30°	988.8	973.8	958.8	947.4	939.5	931.6	923.7	915.8
32.5°	940.2	923.2	906.0	893.8	886.4	878.9	871.4	864.0
35°	864.3	845.8	827.3	814.9	808.4	801.9	795.5	789.1
37.5°	790.3	770.0	749.6	735.7	728.4	721.0	713.6	706.2
40°	740.8	720.0	699.2	685.0	677.3	669.7	662.1	654.4
42.5°	690.9	669.3	647.8	633.4	625.9	618.5	611.2	603.8
45°	618.1	597.3	576.4	562.6	555.5	548.5	541.4	534.4
47.5°	547.3	526.7	505.9	492.4	486.0	479.7	473.2	466.8
50°	501.9	481.6	461.4	448.2	442.0	435.8	429.7	423.5
52.5°	458.9	439.4	419.9	407.3	401.6	395.9	390.2	384.5
55°	393.6	376.1	358.4	346.9	341.3	335.7	330.2	324.6
57.5°	334.3	318.1	302.0	291.6	287.0	282.2	277.6	272.9
60°	293.3	278.4	263.5	253.7	248.9	244.3	239.5	234.9
62.5°	257.9	243.6	229.4	220.8	218.0	215.2	212.3	209.6
65°	209.7	199.7	189.7	184.3	183.4	182.5	181.7	180.8
67.5°	169.3	164.7	160.1	157.3	156.4	155.5	154.5	153.6
70°	147.2	144.3	141.4	139.3	138.1	136.9	135.8	134.6
72.5°	128.1	125.6	123.1	121.6	120.9	120.2	119.4	118.7
75°	101.4	99.4	97.4	96.2	95.9	95.6	95.3	95.0
77.5°	76.8	75.7	74.5	73.6	73.2	72.8	72.2	71.8
80°	61.0	59.8	58.6	58.0	58.0	58.0	58.0	58.0
82.5°	46.1	45.4	44.7	44.3	44.3	44.3	44.3	44.3
85°	25.1	25.1	25.1	25.1	25.1	25.1	25.1	25.1
87.5°	9.6	9.5	9.3	9.2	9.3	9.3	9.4	9.4
90°	8.2	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.0	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.2	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	19.9	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.3	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	23.2	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	24.3	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	29.6	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	48.0	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331847-935

CATALOG NUMBER: S122RDIW-S1005D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	102.8	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	151.4	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	233.2	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	271.7	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.3	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.1	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.2	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	348.1	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	361.7	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.1	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.1	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	410.7	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	421.5	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	436.5	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	449.6	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	457.7	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.0	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.0	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.4	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.2	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	492.8	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.0	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.3	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.0	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.0	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.2	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)