

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331849-935

Luminaire Tested: **S122RDIW-S1005D710U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331849-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D710U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5724.9 lumens
Efficiency: N/A
Efficacy: 95.7 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	3.1
10°-20°	501.6	8.8
20°-30°	646.3	11.3
30°-40°	614.2	10.7
40°-50°	526.2	9.2
50°-60°	400.7	7.0
60°-70°	253.3	4.4
70°-80°	126.5	2.2
80°-90°	35.0	0.6
90°-100°	27.8	0.5
100°-110°	101.9	1.8
110°-120°	272.4	4.8
120°-130°	449.6	7.9
130°-140°	478.2	8.4
140°-150°	444.4	7.8
150°-160°	357.3	6.2
160°-170°	230.3	4.0
170°-180°	79.3	1.4
0°-30°	1327.9	23.2
0°-40°	1942.1	33.9
0°-60°	2869.0	50.1
0°-90°	3283.7	57.4
90°-120°	402.1	7.0
90°-150°	1774.3	31.0
90°-180°	2441.0	42.6
0°-180°	5724.9	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	16	1	16	1	16	8
95°	26	39	26	39	26	24
105°	46	183	46	183	46	48
115°	49	347	49	347	49	124
125°	515	490	515	490	515	446
135°	626	606	626	606	626	483
145°	714	703	714	703	714	447
155°	775	775	775	775	775	358
165°	814	816	814	816	814	230
175°	830	835	830	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	11.7	12.1	12.1	12.1	12.1	11.9	11.8	12.1	11.5	11.9	11.2
90°	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4	12.7	12.1	11.0
92.5°	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7	14.3	13.9	13.4
95°	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9	24.2	23.5	22.6
97.5°	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5	32.0	31.4	29.3
100°	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5	35.4	34.4	32.1
102.5°	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1	36.7	35.3	54.3
105°	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7	38.2	36.8	73.4
107.5°	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5	49.9	51.5	95.3
110°	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7	92.1	105.5	144.2



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3	217.2	266.0	275.6
115°	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9	309.9	371.9	368.5
117.5°	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9	396.9	411.9	409.6
120°	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1	443.4	441.8	439.4
122.5°	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2	471.2	470.3	467.6
125°	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2	510.2	509.3	506.8
127.5°	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3	545.9	544.5	542.6
130°	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2	568.7	567.2	565.7
132.5°	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4	591.1	589.9	588.4
135°	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1	622.8	621.5	620.3
137.5°	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6	652.3	651.0	649.6
140°	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7	671.5	670.3	668.7
142.5°	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3	689.2	688.1	686.4
145°	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9	714.0	713.1	710.8
147.5°	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4	735.7	734.9	732.7
150°	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6	748.8	748.0	745.9
152.5°	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6	760.9	760.1	758.0
155°	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9	777.1	776.4	774.7
157.5°	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7	790.7	789.8	788.7
160°	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6	798.8	798.1	797.2
162.5°	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1	806.2	805.3	804.6
165°	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3	813.9
167.5°	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8	822.9	821.9	821.6
170°	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7	826.7	825.8	825.5
172.5°	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5	829.6	828.6	828.4
175°	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7	832.8	831.8	831.6
177.5°	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1	833.3	832.5	832.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	10.9	11.3	11.0	10.2	10.5	10.8	13.1	15.4	13.6	12.3	11.5
90°	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6	2.1	3.5	5.0
92.5°	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1	12.1	11.9	11.8
95°	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2	34.8	30.3	25.9
97.5°	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7	65.3	52.9	40.4
100°	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7	88.3	70.0	51.7
102.5°	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5	134.7	130.7	126.8
105°	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2	187.3	191.3	195.3
107.5°	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2	237.5	240.7	243.9
110°	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0	269.8	272.7	275.4



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9	300.4	302.9	305.3
115°	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6	348.9	351.1	353.4
117.5°	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1	392.6	395.2	397.7
120°	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9	424.0	425.9	427.9
122.5°	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9	451.1	453.1	455.3
125°	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0	491.8	493.5	495.2
127.5°	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3	529.2	531.2	533.0
130°	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9	553.0	555.2	557.3
132.5°	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1	576.9	578.7	580.5
135°	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4	608.5	610.6	612.8
137.5°	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1	639.6	641.1	642.6
140°	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8	659.9	660.9	662.0
142.5°	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1	677.1	678.1	679.1
145°	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4	703.3	703.2	703.0
147.5°	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1	726.7	726.2	725.7
150°	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6	741.7	740.7	739.8
152.5°	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6	754.6	753.5	752.4
155°	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6	773.4	772.1	770.9
157.5°	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4	788.3	787.3	786.3
160°	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	797.2	796.4	795.7
162.5°	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7	804.9	804.2	803.3
165°	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1	815.3	814.5	813.7
167.5°	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8	823.0	822.3	821.4
170°	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2	827.3	826.6	825.8
172.5°	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0	830.3	829.5	828.6
175°	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8	833.9	832.9	832.0
177.5°	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4	834.7	833.9	833.2
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	11.4	11.0	10.2	10.4	10.7	10.3	10.5	10.1	10.2	10.3	9.9
90°	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4	14.0	14.7	15.2
92.5°	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7	15.1	15.4	15.7
95°	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9	25.5	26.2	26.4
97.5°	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5	33.1	33.6	33.9
100°	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5	37.5	38.7	39.3
102.5°	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1	39.5	40.9	41.8
105°	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7	41.2	42.6	43.7
107.5°	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5	47.0	45.5	45.0
110°	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7	65.3	51.9	45.5



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3	119.5	70.6	46.4
115°	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9	185.8	123.8	88.0
117.5°	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9	366.9	351.9	328.6
120°	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1	446.6	448.2	440.0
122.5°	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2	473.1	474.2	472.9
125°	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2	512.1	513.1	513.8
127.5°	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3	548.6	550.0	550.7
130°	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2	571.6	573.1	573.8
132.5°	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4	593.7	594.9	595.5
135°	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1	625.4	626.8	627.3
137.5°	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6	654.9	656.3	656.7
140°	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7	673.9	675.1	675.4
142.5°	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3	691.4	692.5	692.7
145°	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9	715.8	716.8	717.0
147.5°	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4	737.1	737.8	737.9
150°	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6	750.4	751.2	751.3
152.5°	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6	762.5	763.3	763.3
155°	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9	778.8	779.5	779.4
157.5°	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7	792.6	793.5	793.4
160°	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6	800.5	801.2	801.2
162.5°	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1	808.0	808.9	808.8
165°	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2	817.1	818.0	818.0
167.5°	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8	824.8	825.6	825.5
170°	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7	828.5	829.5	829.4
172.5°	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5	831.5	832.4	832.2
175°	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7	834.6	835.5	835.3
177.5°	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1	834.7	835.5	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	10.0	9.5	10.1	9.6	10.1	9.5	10.0	9.9	10.3	10.2	10.1
90°	15.5	15.8	16.0	16.3	16.0	15.8	15.5	15.2	14.7	14.0	13.4
92.5°	15.8	15.9	16.1	16.3	16.1	15.9	15.8	15.7	15.4	15.1	14.7
95°	26.3	26.2	26.1	25.9	26.1	26.2	26.3	26.4	26.2	25.5	24.9
97.5°	34.1	34.3	34.4	34.6	34.4	34.3	34.1	33.9	33.6	33.1	32.5
100°	39.6	39.9	40.1	40.4	40.1	39.9	39.6	39.3	38.7	37.5	36.5
102.5°	42.2	42.5	42.9	43.3	42.9	42.5	42.2	41.8	40.9	39.5	38.1
105°	44.2	44.8	45.3	45.8	45.3	44.8	44.2	43.7	42.6	41.2	39.7
107.5°	45.5	46.1	46.6	47.1	46.6	46.1	45.5	45.0	45.5	47.0	48.5
110°	46.0	46.6	47.1	47.6	47.1	46.6	46.0	45.5	51.9	65.3	78.7



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	46.8	47.3	47.7	48.1	47.7	47.3	46.8	46.4	70.6	119.5	168.3
115°	78.4	68.7	59.1	49.4	59.1	68.7	78.4	88.0	123.8	185.8	247.9
117.5°	296.9	265.2	233.5	201.8	233.5	265.2	296.9	328.6	351.9	366.9	381.9
120°	421.9	403.8	385.7	367.6	385.7	403.8	421.9	440.0	448.2	446.6	445.1
122.5°	469.3	465.8	462.4	458.8	462.4	465.8	469.3	472.9	474.2	473.1	472.2
125°	514.1	514.5	515.0	515.3	515.0	514.5	514.1	513.8	513.1	512.1	511.2
127.5°	550.8	550.9	551.0	551.0	551.0	550.9	550.8	550.7	550.0	548.6	547.3
130°	573.6	573.5	573.3	573.3	573.3	573.5	573.6	573.8	573.1	571.6	570.2
132.5°	595.3	595.2	595.0	595.0	595.0	595.2	595.3	595.5	594.9	593.7	592.4
135°	627.1	626.8	626.5	626.3	626.5	626.8	627.1	627.3	626.8	625.4	624.1
137.5°	656.2	655.7	655.3	654.8	655.3	655.7	656.2	656.7	656.3	654.9	653.6
140°	674.7	674.0	673.3	672.7	673.3	674.0	674.7	675.4	675.1	673.9	672.7
142.5°	692.1	691.4	690.7	690.0	690.7	691.4	692.1	692.7	692.5	691.4	690.3
145°	716.3	715.6	714.9	714.3	714.9	715.6	716.3	717.0	716.8	715.8	714.9
147.5°	737.3	736.8	736.2	735.6	736.2	736.8	737.3	737.9	737.8	737.1	736.4
150°	750.6	749.9	749.2	748.6	749.2	749.9	750.6	751.3	751.2	750.4	749.6
152.5°	762.3	761.5	760.6	759.7	760.6	761.5	762.3	763.3	763.3	762.5	761.6
155°	778.3	777.3	776.2	775.2	776.2	777.3	778.3	779.4	779.5	778.8	777.9
157.5°	792.4	791.3	790.3	789.2	790.3	791.3	792.4	793.4	793.5	792.6	791.7
160°	800.2	799.3	798.4	797.5	798.4	799.3	800.2	801.2	801.2	800.5	799.6
162.5°	807.6	806.5	805.3	804.2	805.3	806.5	807.6	808.8	808.9	808.0	807.1
165°	817.1	816.2	815.3	814.3	815.3	816.2	817.1	818.0	818.0	817.1	816.2
167.5°	824.3	823.1	821.9	820.7	821.9	823.1	824.3	825.5	825.6	824.8	823.8
170°	828.2	827.0	825.8	824.6	825.8	827.0	828.2	829.4	829.5	828.5	827.7
172.5°	831.0	829.8	828.6	827.4	828.6	829.8	831.0	832.2	832.4	831.5	830.5
175°	834.0	832.7	831.3	830.0	831.3	832.7	834.0	835.3	835.5	834.6	833.7
177.5°	834.5	833.4	832.5	831.6	832.5	833.4	834.5	835.4	835.5	834.7	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	10.5	10.3	10.7	10.4	10.2	11.0	11.4	11.5	12.3	13.6	15.4
90°	12.7	12.1	11.0	9.9	8.9	7.7	6.5	5.0	3.5	2.1	0.6
92.5°	14.3	13.9	13.4	12.9	12.4	11.9	11.6	11.8	11.9	12.1	12.1
95°	24.2	23.5	22.6	21.6	20.7	19.7	21.5	25.9	30.3	34.8	39.2
97.5°	32.0	31.4	29.3	27.1	25.0	22.8	27.9	40.4	52.9	65.3	77.7
100°	35.4	34.4	32.1	29.8	27.6	25.2	33.3	51.7	70.0	88.3	106.7
102.5°	36.7	35.3	54.3	73.4	92.5	111.5	123.0	126.8	130.7	134.7	138.5
105°	38.2	36.8	73.4	109.9	146.5	183.0	199.3	195.3	191.3	187.3	183.2
107.5°	49.9	51.5	95.3	139.2	183.0	226.9	247.2	243.9	240.7	237.5	234.2
110°	92.1	105.5	144.2	182.9	221.6	260.3	278.3	275.4	272.7	269.8	267.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	217.2	266.0	275.6	285.2	294.7	304.3	307.8	305.3	302.9	300.4	297.9
115°	309.9	371.9	368.5	365.2	361.9	358.5	355.7	353.4	351.1	348.9	346.6
117.5°	396.9	411.9	409.6	407.3	405.0	402.7	400.3	397.7	395.2	392.6	390.1
120°	443.4	441.8	439.4	437.0	434.5	432.1	430.0	427.9	425.9	424.0	421.9
122.5°	471.2	470.3	467.6	465.0	462.4	459.8	457.4	455.3	453.1	451.1	448.9
125°	510.2	509.3	506.8	504.2	501.7	499.1	497.0	495.2	493.5	491.8	490.0
127.5°	545.9	544.5	542.6	540.7	538.8	536.9	535.0	533.0	531.2	529.2	527.3
130°	568.7	567.2	565.7	564.2	562.7	561.3	559.5	557.3	555.2	553.0	550.9
132.5°	591.1	589.9	588.4	586.9	585.4	583.9	582.3	580.5	578.7	576.9	575.1
135°	622.8	621.5	620.3	619.1	617.9	616.6	614.9	612.8	610.6	608.5	606.4
137.5°	652.3	651.0	649.6	648.2	646.9	645.5	644.0	642.6	641.1	639.6	638.1
140°	671.5	670.3	668.7	667.3	665.8	664.3	663.1	662.0	660.9	659.9	658.8
142.5°	689.2	688.1	686.4	684.8	683.0	681.3	680.0	679.1	678.1	677.1	676.1
145°	714.0	713.1	710.8	708.5	706.2	704.0	702.8	703.0	703.2	703.3	703.4
147.5°	735.7	734.9	732.7	730.5	728.2	726.0	725.1	725.7	726.2	726.7	727.1
150°	748.8	748.0	745.9	743.7	741.6	739.4	738.8	739.8	740.7	741.7	742.6
152.5°	760.9	760.1	758.0	756.0	754.0	751.9	751.4	752.4	753.5	754.6	755.6
155°	777.1	776.4	774.7	773.1	771.5	769.9	769.7	770.9	772.1	773.4	774.6
157.5°	790.7	789.8	788.7	787.6	786.4	785.3	785.3	786.3	787.3	788.3	789.4
160°	798.8	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1
162.5°	806.2	805.3	804.6	803.9	803.1	802.5	802.5	803.3	804.2	804.9	805.7
165°	815.3	814.3	813.9	813.5	813.1	812.7	812.9	813.7	814.5	815.3	816.1
167.5°	822.9	821.9	821.6	821.1	820.8	820.4	820.6	821.4	822.3	823.0	823.8
170°	826.7	825.8	825.5	825.3	824.9	824.7	824.9	825.8	826.6	827.3	828.2
172.5°	829.6	828.6	828.4	828.1	827.9	827.6	827.9	828.6	829.5	830.3	831.0
175°	832.8	831.8	831.6	831.3	831.0	830.7	831.0	832.0	832.9	833.9	834.8
177.5°	833.3	832.5	832.4	832.3	832.2	832.1	832.4	833.2	833.9	834.7	835.4
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.1	10.8	10.5	10.2	11.0	11.3	10.9	11.2	11.9	11.5	12.1
90°	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7	13.4
92.5°	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3	14.7
95°	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2	24.9
97.5°	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0	32.5
100°	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4	36.5
102.5°	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7	38.1
105°	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2	39.7
107.5°	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9	48.5
110°	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1	78.7



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2	168.3
115°	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9	247.9
117.5°	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9	381.9
120°	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4	445.1
122.5°	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2	472.2
125°	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2	511.2
127.5°	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9	547.3
130°	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7	570.2
132.5°	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1	592.4
135°	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8	624.1
137.5°	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3	653.6
140°	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5	672.7
142.5°	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2	690.3
145°	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0	714.9
147.5°	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7	736.4
150°	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8	749.6
152.5°	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9	761.6
155°	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1	777.9
157.5°	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7	791.7
160°	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8	799.6
162.5°	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2	807.1
165°	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3	816.2
167.5°	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9	823.8
170°	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7	827.7
172.5°	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6	830.5
175°	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8	833.7
177.5°	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3	834.1
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	11.8	11.9	12.1	12.1	12.1	12.1	11.7
90°	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331849-935

CATALOG NUMBER: S122RDIW-S1005D710U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)