

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331565-930

Luminaire Tested: **S122DIW-S865D710U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331565-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122DIW-S865D710U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 865 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5176.0 lumens
Efficiency: N/A
Efficacy: 96.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 1.16 / 1.3
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 53.6
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20									20									20									20									
RC	80									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0													
RCR																																					
0	108	108	108	108	101	101	101	101	86	86	86	73	73	73	61	61	61	55																			
1	99	95	91	87	92	88	85	82	76	73	71	64	63	61	54	53	52	47																			
2	90	83	76	71	83	77	72	67	66	62	59	57	54	51	47	45	43	39																			
3	82	73	65	59	76	68	61	56	59	54	49	50	46	43	42	39	37	33																			
4	75	64	56	50	70	60	53	47	52	47	42	45	40	37	38	34	32	28																			
5	69	57	49	43	64	54	46	41	47	41	36	40	36	32	34	31	28	25																			
6	64	51	43	37	59	48	41	36	42	36	32	36	32	28	31	27	24	22																			
7	59	47	38	33	55	44	36	31	38	32	28	33	28	25	28	25	22	19																			
8	55	42	34	29	51	40	33	28	35	29	25	30	26	22	26	22	20	17																			
9	51	39	31	26	47	36	29	25	32	26	22	28	23	20	24	20	18	16																			
10	48	35	28	23	44	33	27	22	29	24	20	26	21	18	22	19	16	14																			

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	18166	18166	18166
5°	18235	17973	18078
10°	18126	17790	17879
15°	17904	17560	17541
20°	17584	17213	17194
25°	17268	16787	16787
30°	16861	16397	16257
35°	16484	15928	15693
40°	16008	15460	15163
45°	15536	14995	14625
50°	15028	14511	13996
55°	14494	13948	13430
60°	13905	13275	12788
65°	13268	12607	12027
70°	12463	11797	11235
75°	11335	10861	10593
80°	10060	9754	9252
85°	8225	7818	7003



TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	105.8	2.0
10°-20°	297.7	5.8
20°-30°	437.6	8.5
30°-40°	508.3	9.8
40°-50°	507.7	9.8
50°-60°	442.8	8.6
60°-70°	327.4	6.3
70°-80°	185.4	3.6
80°-90°	51.8	1.0
90°-100°	26.3	0.5
100°-110°	96.5	1.9
110°-120°	257.9	5.0
120°-130°	425.7	8.2
130°-140°	452.8	8.7
140°-150°	420.8	8.1
150°-160°	338.4	6.5
160°-170°	218.0	4.2
170°-180°	75.1	1.4
0°-30°	841.1	16.2
0°-40°	1349.3	26.1
0°-60°	2299.8	44.4
0°-90°	2864.4	55.3
90°-120°	380.7	7.4
90°-150°	1680.1	32.5
90°-180°	2312.0	44.7
0°-180°	5176.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1125	1125	1125	1125	1125	
5°	1125	1120	1109	1117	1115	107
15°	1071	1064	1050	1054	1049	301
25°	969	960	942	944	942	446
35°	836	825	808	802	796	522
45°	680	672	657	645	640	525
55°	515	508	496	483	477	460
65°	347	341	330	320	315	343
75°	182	179	174	168	170	194
85°	44	43	42	39	38	51
90°	1	7	11	14	15	4
95°	37	20	22	25	24	45
105°	174	181	35	41	43	185
115°	328	338	352	100	47	323
125°	464	472	482	486	488	414
135°	574	583	588	594	593	443
145°	666	666	675	679	676	416
155°	733	729	735	738	734	338
165°	773	770	771	775	771	218
175°	790	787	788	791	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1130.3	1129.4	1128.4	1127.5	1126.5	1124.9	1122.8	1120.7	1118.6	1116.5	1118.4
5°	1125.1	1124.1	1123.2	1122.3	1121.3	1119.5	1116.9	1114.2	1111.6	1108.9	1110.8
7.5°	1115.2	1113.7	1112.2	1110.7	1109.2	1107.1	1104.4	1101.7	1099.0	1096.3	1098.3
10°	1105.6	1104.0	1102.3	1100.6	1098.9	1096.7	1093.7	1090.9	1088.0	1085.1	1087.0
12.5°	1092.7	1091.2	1089.7	1088.2	1086.7	1084.5	1081.7	1078.7	1075.9	1073.0	1074.3
15°	1071.1	1069.6	1068.1	1066.7	1065.3	1063.0	1059.9	1056.7	1053.6	1050.5	1051.4
17.5°	1043.3	1041.9	1040.5	1039.0	1037.5	1035.3	1032.1	1028.9	1025.7	1022.5	1023.7
20°	1023.4	1022.0	1020.6	1019.1	1017.7	1015.3	1011.9	1008.5	1005.2	1001.8	1002.5
22.5°	1003.6	1001.5	999.5	997.4	995.5	992.9	989.7	986.5	983.3	980.2	980.3
25°	969.3	967.4	965.5	963.6	961.6	958.6	954.6	950.5	946.4	942.3	942.8
27.5°	930.4	928.7	926.9	925.2	923.5	921.0	917.8	914.5	911.3	908.1	907.4
30°	904.4	902.5	900.6	898.7	896.7	894.0	890.4	886.8	883.1	879.5	878.8
32.5°	876.8	875.2	873.7	872.1	870.6	867.9	864.1	860.3	856.6	852.7	851.4
35°	836.3	833.9	831.4	829.1	826.6	823.5	819.7	815.9	812.0	808.1	806.7
37.5°	790.6	788.5	786.4	784.2	782.2	779.2	775.3	771.5	767.6	763.8	762.0
40°	759.5	757.6	755.6	753.7	751.8	748.9	745.0	741.2	737.4	733.5	731.3
42.5°	729.2	727.2	725.3	723.4	721.5	718.6	714.8	710.9	707.0	703.2	700.8
45°	680.4	678.8	677.1	675.5	673.8	671.1	667.5	663.9	660.3	656.7	654.0
47.5°	632.0	630.5	628.8	627.3	625.7	623.0	619.2	615.5	611.7	608.0	605.2
50°	598.3	597.0	595.9	594.7	593.5	591.2	587.8	584.4	581.1	577.7	574.4
52.5°	565.4	563.8	562.2	560.6	559.1	556.7	553.5	550.3	547.1	544.0	541.2
55°	514.9	513.6	512.1	510.6	509.2	507.0	504.2	501.2	498.4	495.5	492.6
57.5°	464.3	463.2	462.0	460.9	459.7	457.5	454.4	451.2	448.0	444.8	442.1
60°	430.6	429.6	428.7	427.7	426.7	424.6	421.2	417.8	414.5	411.1	408.5
62.5°	397.7	396.2	394.6	393.1	391.5	389.5	386.9	384.3	381.6	379.1	376.7
65°	347.3	345.8	344.4	342.9	341.5	339.6	337.2	334.8	332.4	330.0	327.8
67.5°	296.0	294.8	293.7	292.5	291.4	289.8	287.6	285.4	283.2	281.0	279.4
70°	264.0	263.0	262.0	261.1	260.2	258.5	256.4	254.2	252.1	249.9	248.3
72.5°	231.1	230.2	229.2	228.2	227.2	226.1	224.7	223.3	221.8	220.5	218.8
75°	181.7	181.2	180.8	180.3	179.9	179.0	177.8	176.6	175.4	174.1	172.8
77.5°	137.6	136.8	136.0	135.2	134.4	133.7	133.2	132.7	132.2	131.8	131.0
80°	108.2	107.9	107.7	107.5	107.2	106.9	106.4	105.9	105.4	104.9	104.2
82.5°	80.5	80.5	80.4	80.3	80.3	80.1	79.8	79.6	79.2	79.0	78.0
85°	44.4	44.1	43.9	43.6	43.4	43.1	42.9	42.6	42.4	42.2	41.5
87.5°	15.7	15.6	15.5	15.4	15.2	15.2	14.9	14.8	14.6	14.4	13.9
90°	0.6	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1
92.5°	11.5	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5
95°	37.1	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9
97.5°	73.6	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3
100°	101.0	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5
102.5°	131.2	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7
105°	173.5	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2
107.5°	221.8	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3
110°	252.8	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2



TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.1	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7
115°	328.2	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4
117.5°	369.4	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9
120°	399.5	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9
122.5°	425.1	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2
125°	464.0	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1
127.5°	499.3	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9
130°	521.6	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5
132.5°	544.5	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7
135°	574.2	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7
137.5°	604.2	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7
140°	623.9	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9
142.5°	640.3	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6
145°	666.1	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1
147.5°	688.5	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7
150°	703.2	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1
152.5°	715.5	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5
155°	733.4	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9
157.5°	747.5	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8
160°	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4
162.5°	763.0	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4
165°	772.8	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0
167.5°	780.1	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2
170°	784.2	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9
172.5°	786.9	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5
175°	790.5	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6
177.5°	791.1	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1	1125.1
2.5°	1120.3	1122.3	1124.1	1124.9	1124.5	1124.1	1123.8	1123.4
5°	1112.7	1114.7	1116.6	1117.3	1116.9	1116.4	1115.9	1115.4
7.5°	1100.2	1102.1	1104.1	1104.7	1104.2	1103.7	1103.2	1102.6
10°	1088.9	1090.9	1092.8	1093.4	1092.7	1091.9	1091.2	1090.5
12.5°	1075.7	1077.0	1078.4	1078.8	1078.2	1077.7	1077.2	1076.7
15°	1052.4	1053.4	1054.3	1054.2	1053.0	1051.8	1050.6	1049.4
17.5°	1024.7	1025.9	1027.0	1027.0	1025.8	1024.7	1023.5	1022.4
20°	1003.2	1004.0	1004.7	1004.5	1003.6	1002.7	1001.7	1000.7
22.5°	980.5	980.6	980.7	980.6	979.9	979.3	978.8	978.2
25°	943.3	943.7	944.2	944.2	943.7	943.3	942.8	942.3
27.5°	906.7	906.0	905.2	904.3	903.1	902.0	900.8	899.7
30°	878.1	877.4	876.7	875.8	874.9	873.9	872.9	872.0
32.5°	850.1	848.8	847.5	846.4	845.5	844.5	843.5	842.5
35°	805.3	803.8	802.4	801.0	799.9	798.7	797.4	796.2
37.5°	760.3	758.5	756.7	755.2	754.1	752.9	751.8	750.6
40°	729.2	727.0	724.9	723.3	722.4	721.4	720.4	719.4
42.5°	698.5	696.1	693.8	691.9	690.6	689.3	687.9	686.6
45°	651.4	648.7	646.1	644.3	643.4	642.4	641.4	640.5
47.5°	602.4	599.7	596.9	594.8	593.4	592.0	590.6	589.2
50°	571.0	567.6	564.3	562.0	560.8	559.5	558.4	557.2
52.5°	538.3	535.6	532.8	530.6	529.0	527.4	525.9	524.2
55°	489.8	486.8	484.0	481.9	480.7	479.5	478.3	477.1
57.5°	439.2	436.3	433.5	431.6	430.7	429.8	428.9	428.0
60°	405.9	403.2	400.6	398.8	398.1	397.4	396.6	396.0
62.5°	374.1	371.7	369.2	367.6	366.6	365.7	364.8	363.9
65°	325.6	323.5	321.3	319.6	318.5	317.2	316.0	314.8
67.5°	277.7	276.0	274.3	273.0	272.1	271.1	270.1	269.1
70°	246.5	244.8	243.2	241.8	240.9	239.9	239.0	238.0
72.5°	217.1	215.4	213.8	212.5	211.7	211.0	210.2	209.5
75°	171.3	169.8	168.4	168.0	168.4	168.9	169.3	169.8
77.5°	130.4	129.6	128.9	128.2	127.5	126.9	126.2	125.5
80°	103.5	102.8	102.1	101.4	100.9	100.5	100.0	99.5
82.5°	77.1	76.2	75.3	74.8	74.7	74.6	74.5	74.4
85°	40.8	40.0	39.3	38.8	38.6	38.3	38.1	37.8
87.5°	13.5	13.0	12.6	12.3	12.1	12.0	11.9	11.7
90°	12.7	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	13.9	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	23.6	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	30.8	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	34.6	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	36.1	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	37.6	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	45.9	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	74.5	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331565-930

CATALOG NUMBER: S122DIW-S865D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.4	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	234.7	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	361.7	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	421.4	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	447.1	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.0	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	518.2	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	539.9	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	560.9	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	591.0	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	618.9	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	637.0	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	653.6	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	676.9	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	697.3	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	709.8	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	721.2	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	736.6	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	749.7	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	757.2	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	764.3	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	780.1	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	783.7	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	786.4	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	789.5	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	789.8	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)