

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331853-935

Luminaire Tested: **S122RDIW-S1005D970U935-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331853-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D970U935-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6616.5 lumens
Efficiency: N/A
Efficacy: 98.2 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	98	94	91	88	91	87	84	81	74	72	70		62	60	59		50	49	49	43
2	90	83	78	73	83	77	72	68	66	62	59		55	53	50		45	44	42	38
3	83	74	67	62	76	69	63	58	59	54	51		50	46	44		41	39	37	33
4	76	66	59	53	70	62	55	50	53	48	44		45	41	38		37	35	33	29
5	70	59	52	46	65	55	49	44	48	43	39		41	37	34		34	31	29	26
6	65	54	46	40	60	50	43	38	43	38	34		37	33	30		31	28	26	23
7	61	49	41	36	56	46	39	34	40	34	31		34	30	27		29	26	24	21
8	56	45	37	32	52	42	35	31	36	31	27		31	27	24		27	24	21	19
9	53	41	34	29	49	38	32	28	34	28	25		29	25	22		25	22	20	17
10	49	38	31	26	46	35	29	25	31	26	23		27	23	20		23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	30658	30658	30658	30658
5°	34240	30851	27353	30851
10°	37990	30634	23710	30634
15°	39858	30186	18683	30186
20°	34553	29520	16167	29520
25°	22661	28609	14434	28609
30°	15252	27505	13064	27505
35°	12354	26112	11783	26112
40°	10985	24601	10903	24601
45°	9944	22825	9732	22825
50°	9048	21064	9018	21064
55°	8507	19111	8397	19111
60°	7114	17321	7030	17321
65°	5998	15729	6804	15729
70°	5542	14049	6420	14049
75°	5190	12227	5926	12227
80°	4788	10060	5272	10060
85°	4409	7947	4650	7947



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	180.0	2.7
10°-20°	501.6	7.6
20°-30°	646.3	9.8
30°-40°	614.2	9.3
40°-50°	526.2	8.0
50°-60°	400.7	6.1
60°-70°	253.3	3.8
70°-80°	126.5	1.9
80°-90°	35.7	0.5
90°-100°	37.9	0.6
100°-110°	139.1	2.1
110°-120°	371.8	5.6
120°-130°	613.7	9.3
130°-140°	652.7	9.9
140°-150°	606.6	9.2
150°-160°	487.7	7.4
160°-170°	314.3	4.8
170°-180°	108.2	1.6
0°-30°	1327.9	20.1
0°-40°	1942.1	29.4
0°-60°	2869.0	43.4
0°-90°	3284.5	49.6
90°-120°	548.8	8.3
90°-150°	2421.8	36.6
90°-180°	3332.0	50.4
0°-180°	6616.5	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1899	1899	1899	1899	1899	
5°	2113	1904	1688	1904	2113	209
15°	2384	1806	1118	1806	2384	643
25°	1272	1606	810	1606	1272	604
35°	627	1325	598	1325	627	401
45°	436	1000	426	1000	436	337
55°	302	679	298	679	302	265
65°	157	412	178	412	157	160
75°	83	196	95	196	83	88
85°	24	43	25	43	24	26
90°	22	1	22	1	22	11
95°	35	54	35	54	35	33
105°	62	250	62	250	62	65
115°	68	473	68	473	68	169
125°	703	669	703	669	703	609
135°	855	828	855	828	855	659
145°	975	960	975	960	975	610
155°	1058	1057	1058	1057	1058	488
165°	1112	1114	1112	1114	1112	314
175°	1133	1139	1133	1139	1133	108
180°	1137	1137	1137	1137	1137	



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1975.9	1977.5	1979.1	1975.4	1975.4	1972.2	1965.4	1960.1	1945.3	1943.2	1943.2
5°	2112.6	2111.3	2113.9	2105.4	2093.5	2090.9	2078.4	2061.8	2044.7	2025.6	2021.6
7.5°	2248.6	2246.6	2241.3	2239.9	2230.8	2210.8	2190.6	2169.1	2140.6	2112.8	2098.8
10°	2317.2	2339.0	2325.7	2302.7	2307.3	2276.3	2259.8	2231.5	2207.7	2166.1	2156.9
12.5°	2384.7	2393.3	2389.1	2376.0	2370.1	2348.5	2326.2	2301.6	2257.8	2220.4	2188.0
15°	2384.5	2397.0	2400.3	2396.3	2399.7	2398.3	2386.4	2366.0	2327.7	2286.8	2251.2
17.5°	2208.5	2217.2	2238.8	2253.4	2271.9	2311.0	2330.2	2337.8	2332.1	2308.8	2283.6
20°	2011.0	1996.5	2057.2	2088.3	2114.6	2180.6	2237.3	2259.1	2294.0	2293.4	2286.8
22.5°	1731.3	1734.7	1792.3	1829.1	1906.2	1972.1	2036.8	2118.7	2186.4	2231.1	2257.3
25°	1272.0	1297.2	1354.5	1404.7	1490.5	1613.2	1724.7	1854.0	1976.1	2072.4	2164.1
27.5°	955.4	957.3	1002.7	1049.0	1100.0	1200.6	1340.9	1495.4	1669.4	1813.0	1978.1
30°	818.1	814.2	833.3	861.7	905.3	983.1	1088.6	1240.4	1413.9	1630.3	1823.0
32.5°	721.0	721.3	735.6	756.6	792.8	845.3	917.7	1040.9	1204.9	1417.6	1643.6
35°	626.8	626.1	636.7	651.9	667.0	700.7	750.2	814.9	927.6	1126.3	1357.2
37.5°	559.2	562.1	567.3	576.8	593.6	612.3	642.0	685.4	765.8	883.2	1077.3
40°	521.2	522.5	529.8	537.7	547.6	562.1	586.5	621.6	680.3	774.0	915.8
42.5°	486.4	487.8	492.8	500.2	508.1	522.5	542.8	573.0	620.6	693.7	810.7
45°	435.5	435.5	440.1	443.4	451.9	465.1	481.6	506.7	539.7	593.8	671.7
47.5°	387.7	387.8	390.9	396.6	401.9	412.2	428.4	448.9	472.9	514.8	581.3
50°	360.2	360.9	362.9	367.5	370.8	380.0	392.6	410.4	435.5	467.8	523.2
52.5°	338.1	337.7	340.2	342.2	344.4	351.0	360.4	376.1	398.5	426.6	472.5
55°	302.2	299.5	303.5	306.8	308.8	311.4	316.7	326.6	345.7	369.5	403.8
57.5°	257.4	256.2	259.1	262.1	268.3	275.4	279.9	286.2	296.1	313.1	347.2
60°	220.3	220.3	226.3	228.3	235.6	244.8	254.0	259.3	269.2	280.4	305.5
62.5°	187.6	188.2	191.0	193.0	197.0	208.4	221.3	232.9	242.3	253.0	269.6
65°	157.0	158.3	158.3	159.6	162.3	165.0	170.2	179.4	196.0	211.1	223.7
67.5°	133.3	133.7	134.1	135.3	136.0	139.0	141.0	145.2	149.0	163.3	178.9
70°	117.4	119.4	118.7	120.1	120.7	122.1	124.7	126.7	132.6	136.0	145.2
72.5°	102.6	104.1	104.0	104.8	106.5	106.8	108.8	110.8	114.7	117.4	122.4
75°	83.2	82.5	83.2	84.5	85.2	85.8	85.8	88.4	90.4	93.0	96.3
77.5°	64.1	64.8	64.7	64.8	64.9	66.1	66.0	67.2	69.1	70.4	72.1
80°	51.5	52.1	51.5	52.1	52.8	53.5	52.8	53.5	55.4	56.7	56.7
82.5°	39.9	40.0	40.4	40.6	40.6	40.8	41.7	41.8	43.3	43.0	43.6
85°	23.8	23.1	23.1	23.1	23.8	24.5	23.8	23.8	24.5	24.5	24.5
87.5°	12.9	13.3	13.3	13.2	13.1	13.0	12.8	13.2	12.5	12.8	12.0
90°	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3	17.4	16.4	15.0
92.5°	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1	19.5	19.1	18.3
95°	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9	33.0	32.1	30.8
97.5°	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4	43.7	43.0	40.0
100°	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9	48.4	46.9	43.8
102.5°	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0	50.1	48.2	44.2
105°	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2	52.2	50.2	46.1
107.5°	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1	68.2	70.3	66.1
110°	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4	125.7	144.0	146.8



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7	296.4	363.2	376.2
115°	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3	422.9	507.6	503.1
117.5°	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2	541.7	562.2	559.1
120°	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4	605.3	603.0	599.8
122.5°	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5	643.2	641.9	638.3
125°	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8	696.5	695.2	691.7
127.5°	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0	745.1	743.2	740.6
130°	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2	776.2	774.2	772.1
132.5°	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6	806.8	805.1	803.1
135°	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9	850.1	848.3	846.5
137.5°	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1	890.4	888.6	886.7
140°	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2	916.5	914.9	912.8
142.5°	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2	940.7	939.2	936.9
145°	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9	974.6	973.3	970.2
147.5°	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1	1004.2	1003.2	1000.1
150°	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2	1022.1	1021.0	1018.0
152.5°	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7	1038.5	1037.4	1034.7
155°	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9	1060.8	1059.6	1057.5
157.5°	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6	1079.3	1078.1	1076.5
160°	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5	1090.4	1089.3	1088.2
162.5°	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6	1100.4	1099.2	1098.2
165°	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5	1110.9
167.5°	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4	1123.1	1121.9	1121.4
170°	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7	1128.4	1127.1	1126.8
172.5°	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6	1132.4	1131.1	1130.7
175°	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9	1136.6	1135.3	1135.0
177.5°	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4	1137.4	1136.3	1136.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1944.3	1940.0	1936.4	1926.8	1922.1	1911.5	1910.0	1909.4	1895.7	1882.5	1878.8
5°	2011.0	2000.4	1984.7	1966.2	1947.1	1927.3	1914.1	1903.5	1877.1	1852.0	1837.5
7.5°	2078.4	2055.6	2028.3	1993.4	1964.2	1931.5	1907.2	1885.4	1848.0	1812.1	1787.9
10°	2128.5	2091.5	2055.2	2007.1	1969.5	1932.5	1898.2	1868.5	1826.3	1778.8	1745.2
12.5°	2159.6	2119.0	2069.0	2021.9	1973.2	1926.2	1880.3	1842.1	1792.5	1743.4	1703.5
15°	2201.7	2158.2	2097.5	2030.2	1967.5	1906.2	1853.4	1805.9	1741.2	1682.5	1633.7
17.5°	2236.2	2176.3	2111.1	2033.3	1960.7	1882.7	1814.7	1754.0	1682.0	1611.2	1553.7
20°	2247.2	2187.9	2112.6	2034.8	1949.0	1857.3	1784.1	1718.1	1640.9	1563.7	1497.7
22.5°	2240.4	2194.2	2110.6	2017.4	1929.5	1833.6	1750.8	1674.3	1588.6	1509.8	1433.3
25°	2193.8	2178.0	2098.8	1997.2	1896.9	1785.4	1689.7	1605.9	1508.3	1423.8	1340.7
27.5°	2085.2	2119.4	2070.3	1962.0	1850.5	1731.0	1623.5	1528.1	1426.8	1331.7	1248.9
30°	1980.7	2059.2	2038.1	1937.8	1813.1	1695.7	1574.9	1475.3	1367.1	1269.5	1187.7
32.5°	1837.6	1967.4	1988.0	1904.0	1775.1	1646.1	1519.5	1420.4	1307.4	1204.5	1124.8
35°	1609.9	1803.9	1892.9	1839.5	1710.2	1571.0	1440.3	1324.8	1211.3	1109.7	1030.6
37.5°	1338.2	1602.4	1750.8	1754.6	1635.9	1491.2	1348.8	1234.2	1118.1	1018.3	932.7
40°	1161.9	1448.2	1641.6	1684.5	1584.2	1427.8	1283.9	1167.2	1053.7	956.1	857.7
42.5°	1003.6	1288.8	1526.5	1601.0	1521.4	1366.1	1221.7	1099.6	989.3	896.9	796.5
45°	811.6	1060.9	1322.8	1456.1	1412.0	1268.1	1115.7	999.6	896.0	816.1	719.8
47.5°	684.6	860.4	1113.9	1294.1	1293.3	1162.0	1012.1	900.9	804.8	730.0	652.0
50°	612.3	765.3	979.8	1184.3	1201.4	1091.3	948.7	838.6	748.9	670.4	607.7
52.5°	547.3	673.5	866.3	1062.4	1111.2	1015.8	877.5	775.8	688.7	616.5	562.8
55°	462.5	560.2	706.6	890.0	964.0	896.6	774.0	678.9	608.3	547.6	501.4
57.5°	391.2	464.5	582.0	729.7	815.8	773.4	672.2	595.0	534.6	479.7	443.2
60°	346.4	406.4	506.1	629.5	724.4	694.7	608.3	536.4	484.9	437.5	403.1
62.5°	304.2	355.8	441.2	541.3	628.4	616.1	545.5	485.2	440.1	396.8	367.7
65°	244.8	282.4	349.0	427.6	497.5	503.4	452.6	411.7	371.4	337.2	311.4
67.5°	194.9	219.5	266.4	332.5	385.0	403.6	372.6	341.4	309.4	282.9	260.6
70°	164.3	184.1	218.3	271.8	320.0	339.8	322.0	297.6	269.8	248.1	228.9
72.5°	133.1	152.4	177.7	217.0	258.2	279.7	273.5	255.9	233.4	215.3	197.3
75°	100.3	106.2	123.4	149.8	182.1	200.6	205.2	196.0	178.1	164.3	153.7
77.5°	74.1	77.7	85.9	99.8	120.9	137.3	144.1	143.0	130.8	122.7	112.8
80°	59.4	61.4	65.3	71.3	87.1	103.6	108.2	108.2	99.6	96.3	86.4
82.5°	45.1	46.6	49.0	52.3	59.7	74.0	79.2	80.2	74.8	70.4	62.7
85°	25.7	25.1	26.4	28.4	29.7	33.7	41.6	42.9	41.6	36.2	34.3
87.5°	11.7	11.9	11.6	10.8	10.8	11.0	13.3	15.5	13.8	12.6	12.0
90°	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9	2.8	4.8	6.9
92.5°	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6	16.4	16.3	16.1
95°	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5	47.4	41.4	35.4
97.5°	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2	89.1	72.2	55.1
100°	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6	120.5	95.5	70.5
102.5°	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1	183.7	178.5	173.1
105°	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1	255.6	261.1	266.6
107.5°	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7	324.2	328.6	332.9
110°	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5	368.3	372.1	376.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6	410.0	413.4	416.8
115°	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0	476.1	479.3	482.4
117.5°	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4	536.0	539.4	542.9
120°	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9	578.7	581.3	584.1
122.5°	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8	615.6	618.5	621.4
125°	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8	671.2	673.6	676.0
127.5°	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7	722.4	725.0	727.6
130°	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0	754.9	757.9	760.7
132.5°	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9	787.4	789.9	792.3
135°	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7	830.6	833.5	836.5
137.5°	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9	873.0	875.0	877.1
140°	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2	900.7	902.2	903.6
142.5°	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9	924.2	925.6	926.9
145°	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1	959.9	959.8	959.6
147.5°	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6	991.8	991.1	990.4
150°	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6	1012.3	1011.0	1009.8
152.5°	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4	1029.9	1028.5	1027.1
155°	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2	1055.5	1053.9	1052.2
157.5°	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5	1076.1	1074.6	1073.2
160°	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1088.2	1087.1	1086.0
162.5°	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8	1098.7	1097.6	1096.5
165°	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0	1112.8	1111.7	1110.7
167.5°	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5	1123.3	1122.3	1121.2
170°	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4	1129.3	1128.3	1127.1
172.5°	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4	1133.2	1132.1	1131.1
175°	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4	1138.2	1136.9	1135.7
177.5°	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3	1139.3	1138.2	1137.2
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1872.0	1868.3	1861.4	1850.8	1844.5	1833.4	1826.0	1830.2	1831.3	1830.2	1829.2
5°	1821.7	1807.8	1788.7	1770.2	1753.1	1734.6	1724.1	1719.4	1710.2	1704.9	1702.3
7.5°	1760.8	1737.0	1709.9	1677.7	1650.4	1621.8	1607.1	1599.8	1581.0	1570.7	1561.7
10°	1715.5	1677.8	1650.8	1608.6	1582.9	1545.2	1519.5	1520.2	1494.4	1479.9	1469.4
12.5°	1665.3	1624.0	1579.0	1541.0	1505.3	1475.1	1444.0	1431.5	1404.2	1390.2	1361.7
15°	1582.2	1534.0	1486.5	1435.0	1398.8	1351.9	1307.1	1252.3	1208.1	1169.8	1159.3
17.5°	1491.4	1431.8	1384.1	1323.7	1261.5	1182.8	1130.8	1099.0	1072.3	1052.1	1037.1
20°	1429.1	1368.4	1317.6	1226.6	1142.7	1089.3	1051.0	1026.7	998.9	977.1	965.3
22.5°	1363.7	1300.3	1231.1	1129.5	1064.1	1021.2	987.1	959.1	940.3	923.3	912.5
25°	1270.7	1201.4	1087.4	1017.4	964.6	919.7	896.0	878.8	859.0	835.9	825.4
27.5°	1172.6	1062.4	980.4	928.4	878.0	848.9	827.5	801.9	784.2	773.8	762.8
30°	1099.2	989.0	925.1	868.3	832.7	800.3	775.2	760.8	743.6	725.7	718.5
32.5°	1017.4	929.4	868.1	820.8	784.6	757.1	737.3	713.8	701.4	690.4	675.2
35°	915.8	849.1	793.1	754.8	720.5	698.1	674.9	661.1	638.7	629.5	623.5
37.5°	829.7	772.0	730.1	689.7	662.5	637.7	623.6	601.6	591.9	579.0	566.5
40°	781.2	724.4	684.2	651.2	620.9	602.4	584.5	566.8	552.2	546.3	531.2
42.5°	731.6	685.4	645.1	609.0	588.7	569.1	546.6	533.5	518.5	508.9	499.5
45°	663.1	622.2	587.9	558.2	535.7	515.3	500.8	479.0	470.5	451.3	443.4
47.5°	603.0	564.9	532.2	503.9	482.1	468.7	447.5	430.4	416.7	405.0	394.9
50°	560.2	528.5	496.8	471.7	451.9	432.8	411.0	402.4	381.3	375.4	369.5
52.5°	521.1	491.0	462.0	437.5	417.7	399.1	379.9	368.7	354.5	348.5	344.1
55°	466.5	437.5	409.7	388.0	368.2	349.0	337.2	323.3	316.7	312.1	306.8
57.5°	411.6	385.5	364.2	342.2	322.3	307.0	293.3	285.0	278.2	272.1	265.8
60°	376.8	351.6	332.5	312.1	291.6	279.1	268.5	258.6	250.7	241.5	238.8
62.5°	339.8	317.9	300.3	280.4	262.6	251.2	241.1	231.7	222.2	208.8	205.1
65°	289.0	271.8	253.4	236.9	221.0	209.8	195.3	184.8	180.8	179.4	178.8
67.5°	243.1	226.9	211.0	194.1	179.7	169.3	162.0	160.3	157.6	156.8	154.9
70°	212.5	197.3	181.4	165.6	151.8	149.8	147.1	144.5	141.2	139.9	138.5
72.5°	185.0	169.3	153.4	140.8	134.8	132.3	129.8	127.1	124.8	123.6	122.7
75°	141.9	127.3	116.8	112.2	108.8	106.9	102.9	100.9	99.6	97.6	96.9
77.5°	102.1	93.9	89.1	86.2	82.7	80.6	78.4	76.4	75.0	74.6	73.5
80°	77.8	73.9	70.6	66.6	65.3	62.7	62.0	60.0	60.7	58.7	58.7
82.5°	60.4	55.4	52.7	50.8	49.5	47.4	46.8	45.8	45.9	44.4	44.4
85°	31.0	29.7	28.4	27.0	27.0	25.1	25.7	25.1	25.1	23.8	23.1
87.5°	11.8	11.6	10.8	11.2	11.5	11.2	11.4	11.0	11.2	11.5	11.0
90°	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3	19.2	20.1	20.8
92.5°	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1	20.5	21.0	21.4
95°	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9	34.9	35.7	36.1
97.5°	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4	45.1	45.9	46.3
100°	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9	51.3	52.8	53.6
102.5°	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0	53.9	55.8	57.0
105°	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2	56.2	58.2	59.6
107.5°	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1	64.1	62.1	61.4
110°	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4	89.1	70.9	62.1



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7	163.1	96.3	63.3
115°	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3	253.7	169.0	120.1
117.5°	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2	500.8	480.4	448.5
120°	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4	609.6	611.8	600.5
122.5°	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5	645.8	647.1	645.4
125°	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8	699.0	700.3	701.2
127.5°	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0	748.8	750.7	751.7
130°	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2	780.2	782.2	783.2
132.5°	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6	810.3	812.0	812.8
135°	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9	853.7	855.5	856.3
137.5°	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1	893.9	895.7	896.3
140°	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2	919.8	921.4	921.8
142.5°	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2	943.7	945.2	945.5
145°	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9	977.1	978.4	978.6
147.5°	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1	1006.1	1007.0	1007.1
150°	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2	1024.2	1025.4	1025.5
152.5°	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7	1040.7	1041.8	1041.8
155°	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9	1062.9	1064.0	1063.9
157.5°	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6	1081.8	1083.1	1083.0
160°	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5	1092.5	1093.6	1093.6
162.5°	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6	1102.9	1104.1	1104.0
165°	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6
167.5°	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4	1125.7	1127.0	1126.8
170°	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7	1130.9	1132.2	1132.0
172.5°	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6	1134.9	1136.2	1136.0
175°	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9	1139.2	1140.5	1140.2
177.5°	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4	1139.4	1140.4	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1823.4	1824.5	1822.9	1823.9	1822.9	1824.5	1823.4	1829.2	1830.2	1831.3	1830.2
5°	1698.9	1691.0	1689.7	1687.7	1689.7	1691.0	1698.9	1702.3	1704.9	1710.2	1719.4
7.5°	1550.4	1549.2	1545.9	1541.3	1545.9	1549.2	1550.4	1561.7	1570.7	1581.0	1599.8
10°	1454.8	1451.6	1450.9	1446.2	1450.9	1451.6	1454.8	1469.4	1479.9	1494.4	1520.2
12.5°	1342.9	1321.7	1319.5	1307.9	1319.5	1321.7	1342.9	1361.7	1390.2	1404.2	1431.5
15°	1143.4	1139.4	1126.3	1117.7	1126.3	1139.4	1143.4	1159.3	1169.8	1208.1	1252.3
17.5°	1029.4	1016.5	1012.4	1010.6	1012.4	1016.5	1029.4	1037.1	1052.1	1072.3	1099.0
20°	956.1	944.2	942.2	940.9	942.2	944.2	956.1	965.3	977.1	998.9	1026.7
22.5°	905.3	892.9	887.8	883.8	887.8	892.9	905.3	912.5	923.3	940.3	959.1
25°	818.8	814.2	811.6	810.2	811.6	814.2	818.8	825.4	835.9	859.0	878.8
27.5°	751.1	741.0	739.0	735.6	739.0	741.0	751.1	762.8	773.8	784.2	801.9
30°	712.6	709.3	704.6	700.7	704.6	709.3	712.6	718.5	725.7	743.6	760.8
32.5°	667.2	664.4	660.3	658.5	660.3	664.4	667.2	675.2	690.4	701.4	713.8
35°	616.9	607.7	603.7	597.8	603.7	607.7	616.9	623.5	629.5	638.7	661.1
37.5°	563.7	558.9	553.3	555.3	553.3	558.9	563.7	566.5	579.0	591.9	601.6
40°	522.5	519.3	518.0	517.3	518.0	519.3	522.5	531.2	546.3	552.2	566.8
42.5°	489.8	480.7	477.3	477.2	477.3	480.7	489.8	499.5	508.9	518.5	533.5
45°	440.1	431.5	425.6	426.2	425.6	431.5	440.1	443.4	451.3	470.5	479.0
47.5°	389.2	388.9	385.2	386.3	385.2	388.9	389.2	394.9	405.0	416.7	430.4
50°	364.9	360.9	358.3	359.0	358.3	360.9	364.9	369.5	375.4	381.3	402.4
52.5°	341.6	338.2	336.1	338.9	336.1	338.2	341.6	344.1	348.5	354.5	368.7
55°	303.5	299.5	298.9	298.3	298.9	299.5	303.5	306.8	312.1	316.7	323.3
57.5°	260.9	258.2	254.3	252.5	254.3	258.2	260.9	265.8	272.1	278.2	285.0
60°	230.2	225.0	218.3	217.7	218.3	225.0	230.2	238.8	241.5	250.7	258.6
62.5°	202.2	201.2	199.9	199.8	199.9	201.2	202.2	205.1	208.8	222.2	231.7
65°	177.5	176.8	177.5	178.1	177.5	176.8	177.5	178.8	179.4	180.8	184.8
67.5°	154.6	153.4	152.3	152.8	152.3	153.4	154.6	154.9	156.8	157.6	160.3
70°	137.2	136.6	136.0	136.0	136.0	136.6	137.2	138.5	139.9	141.2	144.5
72.5°	120.4	120.2	119.6	119.0	119.6	120.2	120.4	122.7	123.6	124.8	127.1
75°	96.3	95.0	95.0	95.0	95.0	95.0	96.3	96.9	97.6	99.6	100.9
77.5°	73.4	72.7	72.1	71.5	72.1	72.7	73.4	73.5	74.6	75.0	76.4
80°	58.0	57.4	56.7	56.7	56.7	57.4	58.0	58.7	58.7	60.7	60.0
82.5°	44.3	43.7	43.6	43.0	43.6	43.7	44.3	44.4	44.4	45.9	45.8
85°	23.8	24.5	23.8	25.1	23.8	24.5	23.8	23.1	23.8	25.1	25.1
87.5°	11.1	10.6	11.2	10.8	11.2	10.6	11.1	11.0	11.5	11.2	11.0
90°	21.1	21.4	21.9	22.2	21.9	21.4	21.1	20.8	20.1	19.2	18.3
92.5°	21.5	21.8	22.0	22.2	22.0	21.8	21.5	21.4	21.0	20.5	20.1
95°	35.9	35.7	35.6	35.4	35.6	35.7	35.9	36.1	35.7	34.9	33.9
97.5°	46.6	46.8	47.0	47.2	47.0	46.8	46.6	46.3	45.9	45.1	44.4
100°	54.0	54.4	54.8	55.1	54.8	54.4	54.0	53.6	52.8	51.3	49.9
102.5°	57.5	58.0	58.5	59.1	58.5	58.0	57.5	57.0	55.8	53.9	52.0
105°	60.4	61.0	61.8	62.5	61.8	61.0	60.4	59.6	58.2	56.2	54.2
107.5°	62.2	62.9	63.6	64.3	63.6	62.9	62.2	61.4	62.1	64.1	66.1
110°	62.8	63.5	64.2	65.0	64.2	63.5	62.8	62.1	70.9	89.1	107.4



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	63.9	64.5	65.1	65.7	65.1	64.5	63.9	63.3	96.3	163.1	229.7
115°	106.9	93.8	80.6	67.5	80.6	93.8	106.9	120.1	169.0	253.7	338.3
117.5°	405.2	362.0	318.7	275.4	318.7	362.0	405.2	448.5	480.4	500.8	521.2
120°	575.9	551.2	526.5	501.9	526.5	551.2	575.9	600.5	611.8	609.6	607.4
122.5°	640.6	635.8	631.0	626.3	631.0	635.8	640.6	645.4	647.1	645.8	644.5
125°	701.8	702.3	702.8	703.4	702.8	702.3	701.8	701.2	700.3	699.0	697.8
127.5°	751.8	751.9	752.0	752.1	752.0	751.9	751.8	751.7	750.7	748.8	747.0
130°	782.9	782.7	782.6	782.4	782.6	782.7	782.9	783.2	782.2	780.2	778.2
132.5°	812.5	812.4	812.2	812.0	812.2	812.4	812.5	812.8	812.0	810.3	808.6
135°	855.9	855.5	855.1	854.8	855.1	855.5	855.9	856.3	855.5	853.7	851.9
137.5°	895.7	895.0	894.4	893.8	894.4	895.0	895.7	896.3	895.7	893.9	892.1
140°	920.9	920.0	919.0	918.2	919.0	920.0	920.9	921.8	921.4	919.8	918.2
142.5°	944.6	943.7	942.8	941.8	942.8	943.7	944.6	945.5	945.2	943.7	942.2
145°	977.7	976.7	975.9	974.9	975.9	976.7	977.7	978.6	978.4	977.1	975.9
147.5°	1006.3	1005.6	1004.8	1004.0	1004.8	1005.6	1006.3	1007.1	1007.0	1006.1	1005.1
150°	1024.6	1023.6	1022.7	1021.8	1022.7	1023.6	1024.6	1025.5	1025.4	1024.2	1023.2
152.5°	1040.6	1039.4	1038.2	1037.0	1038.2	1039.4	1040.6	1041.8	1041.8	1040.7	1039.7
155°	1062.4	1060.9	1059.5	1058.0	1059.5	1060.9	1062.4	1063.9	1064.0	1062.9	1061.9
157.5°	1081.5	1080.1	1078.7	1077.3	1078.7	1080.1	1081.5	1083.0	1083.1	1081.8	1080.6
160°	1092.3	1091.0	1089.8	1088.5	1089.8	1091.0	1092.3	1093.6	1093.6	1092.5	1091.5
162.5°	1102.3	1100.8	1099.2	1097.7	1099.2	1100.8	1102.3	1104.0	1104.1	1102.9	1101.6
165°	1115.3	1114.0	1112.8	1111.5	1112.8	1114.0	1115.3	1116.6	1116.6	1115.3	1114.0
167.5°	1125.2	1123.5	1121.9	1120.2	1121.9	1123.5	1125.2	1126.8	1127.0	1125.7	1124.4
170°	1130.4	1128.8	1127.1	1125.5	1127.1	1128.8	1130.4	1132.0	1132.2	1130.9	1129.7
172.5°	1134.4	1132.7	1131.1	1129.5	1131.1	1132.7	1134.4	1136.0	1136.2	1134.9	1133.6
175°	1138.3	1136.5	1134.7	1132.9	1134.7	1136.5	1138.3	1140.2	1140.5	1139.2	1137.9
177.5°	1138.9	1137.6	1136.3	1135.1	1136.3	1137.6	1138.9	1140.3	1140.4	1139.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1826.0	1833.4	1844.5	1850.8	1861.4	1868.3	1872.0	1878.8	1882.5	1895.7	1909.4
5°	1724.1	1734.6	1753.1	1770.2	1788.7	1807.8	1821.7	1837.5	1852.0	1877.1	1903.5
7.5°	1607.1	1621.8	1650.4	1677.7	1709.9	1737.0	1760.8	1787.9	1812.1	1848.0	1885.4
10°	1519.5	1545.2	1582.9	1608.6	1650.8	1677.8	1715.5	1745.2	1778.8	1826.3	1868.5
12.5°	1444.0	1475.1	1505.3	1541.0	1579.0	1624.0	1665.3	1703.5	1743.4	1792.5	1842.1
15°	1307.1	1351.9	1398.8	1435.0	1486.5	1534.0	1582.2	1633.7	1682.5	1741.2	1805.9
17.5°	1130.8	1182.8	1261.5	1323.7	1384.1	1431.8	1491.4	1553.7	1611.2	1682.0	1754.0
20°	1051.0	1089.3	1142.7	1226.6	1317.6	1368.4	1429.1	1497.7	1563.7	1640.9	1718.1
22.5°	987.1	1021.2	1064.1	1129.5	1231.1	1300.3	1363.7	1433.3	1509.8	1588.6	1674.3
25°	896.0	919.7	964.6	1017.4	1087.4	1201.4	1270.7	1340.7	1423.8	1508.3	1605.9
27.5°	827.5	848.9	878.0	928.4	980.4	1062.4	1172.6	1248.9	1331.7	1426.8	1528.1
30°	775.2	800.3	832.7	868.3	925.1	989.0	1099.2	1187.7	1269.5	1367.1	1475.3
32.5°	737.3	757.1	784.6	820.8	868.1	929.4	1017.4	1124.8	1204.5	1307.4	1420.4
35°	674.9	698.1	720.5	754.8	793.1	849.1	915.8	1030.6	1109.7	1211.3	1324.8
37.5°	623.6	637.7	662.5	689.7	730.1	772.0	829.7	932.7	1018.3	1118.1	1234.2
40°	584.5	602.4	620.9	651.2	684.2	724.4	781.2	857.7	956.1	1053.7	1167.2
42.5°	546.6	569.1	588.7	609.0	645.1	685.4	731.6	796.5	896.9	989.3	1099.6
45°	500.8	515.3	535.7	558.2	587.9	622.2	663.1	719.8	816.1	896.0	999.6
47.5°	447.5	468.7	482.1	503.9	532.2	564.9	603.0	652.0	730.0	804.8	900.9
50°	411.0	432.8	451.9	471.7	496.8	528.5	560.2	607.7	670.4	748.9	838.6
52.5°	379.9	399.1	417.7	437.5	462.0	491.0	521.1	562.8	616.5	688.7	775.8
55°	337.2	349.0	368.2	388.0	409.7	437.5	466.5	501.4	547.6	608.3	678.9
57.5°	293.3	307.0	322.3	342.2	364.2	385.5	411.6	443.2	479.7	534.6	595.0
60°	268.5	279.1	291.6	312.1	332.5	351.6	376.8	403.1	437.5	484.9	536.4
62.5°	241.1	251.2	262.6	280.4	300.3	317.9	339.8	367.7	396.8	440.1	485.2
65°	195.3	209.8	221.0	236.9	253.4	271.8	289.0	311.4	337.2	371.4	411.7
67.5°	162.0	169.3	179.7	194.1	211.0	226.9	243.1	260.6	282.9	309.4	341.4
70°	147.1	149.8	151.8	165.6	181.4	197.3	212.5	228.9	248.1	269.8	297.6
72.5°	129.8	132.3	134.8	140.8	153.4	169.3	185.0	197.3	215.3	233.4	255.9
75°	102.9	106.9	108.8	112.2	116.8	127.3	141.9	153.7	164.3	178.1	196.0
77.5°	78.4	80.6	82.7	86.2	89.1	93.9	102.1	112.8	122.7	130.8	143.0
80°	62.0	62.7	65.3	66.6	70.6	73.9	77.8	86.4	96.3	99.6	108.2
82.5°	46.8	47.4	49.5	50.8	52.7	55.4	60.4	62.7	70.4	74.8	80.2
85°	25.7	25.1	27.0	27.0	28.4	29.7	31.0	34.3	36.2	41.6	42.9
87.5°	11.4	11.2	11.5	11.2	10.8	11.6	11.8	12.0	12.6	13.8	15.5
90°	17.4	16.4	15.0	13.5	12.1	10.6	8.9	6.9	4.8	2.8	0.9
92.5°	19.5	19.1	18.3	17.7	16.9	16.2	15.9	16.1	16.3	16.4	16.6
95°	33.0	32.1	30.8	29.5	28.2	26.9	29.4	35.4	41.4	47.4	53.5
97.5°	43.7	43.0	40.0	37.0	34.1	31.1	38.1	55.1	72.2	89.1	106.2
100°	48.4	46.9	43.8	40.6	37.5	34.4	45.5	70.5	95.5	120.5	145.6
102.5°	50.1	48.2	74.2	100.2	126.2	152.2	167.8	173.1	178.5	183.7	189.1
105°	52.2	50.2	100.1	150.0	199.9	249.9	272.1	266.6	261.1	255.6	250.1
107.5°	68.2	70.3	130.1	189.9	249.9	309.7	337.4	332.9	328.6	324.2	319.7
110°	125.7	144.0	196.8	249.7	302.5	355.3	379.8	376.0	372.1	368.3	364.5



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	296.4	363.2	376.2	389.3	402.3	415.3	420.2	416.8	413.4	410.0	406.6
115°	422.9	507.6	503.1	498.4	493.9	489.3	485.5	482.4	479.3	476.1	473.0
117.5°	541.7	562.2	559.1	555.9	552.8	549.7	546.4	542.9	539.4	536.0	532.4
120°	605.3	603.0	599.8	596.5	593.1	589.9	586.9	584.1	581.3	578.7	575.9
122.5°	643.2	641.9	638.3	634.7	631.1	627.6	624.3	621.4	618.5	615.6	612.8
125°	696.5	695.2	691.7	688.3	684.8	681.3	678.4	676.0	673.6	671.2	668.8
127.5°	745.1	743.2	740.6	738.0	735.5	732.9	730.2	727.6	725.0	722.4	719.7
130°	776.2	774.2	772.1	770.2	768.1	766.1	763.6	760.7	757.9	754.9	752.0
132.5°	806.8	805.1	803.1	801.1	799.1	797.0	794.8	792.3	789.9	787.4	784.9
135°	850.1	848.3	846.5	844.9	843.3	841.6	839.4	836.5	833.5	830.6	827.7
137.5°	890.4	888.6	886.7	884.8	883.0	881.1	879.1	877.1	875.0	873.0	870.9
140°	916.5	914.9	912.8	910.9	908.8	906.8	905.1	903.6	902.2	900.7	899.2
142.5°	940.7	939.2	936.9	934.6	932.3	930.0	928.2	926.9	925.6	924.2	922.9
145°	974.6	973.3	970.2	967.1	964.0	960.9	959.4	959.6	959.8	959.9	960.1
147.5°	1004.2	1003.2	1000.1	997.0	994.0	990.9	989.7	990.4	991.1	991.8	992.6
150°	1022.1	1021.0	1018.0	1015.1	1012.2	1009.3	1008.5	1009.8	1011.0	1012.3	1013.6
152.5°	1038.5	1037.4	1034.7	1031.9	1029.1	1026.3	1025.6	1027.1	1028.5	1029.9	1031.4
155°	1060.8	1059.6	1057.5	1055.2	1053.1	1050.9	1050.6	1052.2	1053.9	1055.5	1057.2
157.5°	1079.3	1078.1	1076.5	1075.0	1073.5	1071.9	1071.9	1073.2	1074.6	1076.1	1077.5
160°	1090.4	1089.3	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3
162.5°	1100.4	1099.2	1098.2	1097.3	1096.3	1095.4	1095.5	1096.5	1097.6	1098.7	1099.8
165°	1112.8	1111.5	1110.9	1110.3	1109.8	1109.3	1109.6	1110.7	1111.7	1112.8	1114.0
167.5°	1123.1	1121.9	1121.4	1120.8	1120.3	1119.8	1120.1	1121.2	1122.3	1123.3	1124.5
170°	1128.4	1127.1	1126.8	1126.4	1126.0	1125.7	1126.0	1127.1	1128.3	1129.3	1130.4
172.5°	1132.4	1131.1	1130.7	1130.3	1130.0	1129.6	1130.0	1131.1	1132.1	1133.2	1134.4
175°	1136.6	1135.3	1135.0	1134.6	1134.3	1133.9	1134.4	1135.7	1136.9	1138.2	1139.4
177.5°	1137.4	1136.3	1136.2	1136.0	1135.9	1135.7	1136.2	1137.2	1138.2	1139.3	1140.3
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1910.0	1911.5	1922.1	1926.8	1936.4	1940.0	1944.3	1943.2	1943.2	1945.3	1960.1
5°	1914.1	1927.3	1947.1	1966.2	1984.7	2000.4	2011.0	2021.6	2025.6	2044.7	2061.8
7.5°	1907.2	1931.5	1964.2	1993.4	2028.3	2055.6	2078.4	2098.8	2112.8	2140.6	2169.1
10°	1898.2	1932.5	1969.5	2007.1	2055.2	2091.5	2128.5	2156.9	2166.1	2207.7	2231.5
12.5°	1880.3	1926.2	1973.2	2021.9	2069.0	2119.0	2159.6	2188.0	2220.4	2257.8	2301.6
15°	1853.4	1906.2	1967.5	2030.2	2097.5	2158.2	2201.7	2251.2	2286.8	2327.7	2366.0
17.5°	1814.7	1882.7	1960.7	2033.3	2111.1	2176.3	2236.2	2283.6	2308.8	2332.1	2337.8
20°	1784.1	1857.3	1949.0	2034.8	2112.6	2187.9	2247.2	2286.8	2293.4	2294.0	2259.1
22.5°	1750.8	1833.6	1929.5	2017.4	2110.6	2194.2	2240.4	2257.3	2231.1	2186.4	2118.7
25°	1689.7	1785.4	1896.9	1997.2	2098.8	2178.0	2193.8	2164.1	2072.4	1976.1	1854.0
27.5°	1623.5	1731.0	1850.5	1962.0	2070.3	2119.4	2085.2	1978.1	1813.0	1669.4	1495.4
30°	1574.9	1695.7	1813.1	1937.8	2038.1	2059.2	1980.7	1823.0	1630.3	1413.9	1240.4
32.5°	1519.5	1646.1	1775.1	1904.0	1988.0	1967.4	1837.6	1643.6	1417.6	1204.9	1040.9
35°	1440.3	1571.0	1710.2	1839.5	1892.9	1803.9	1609.9	1357.2	1126.3	927.6	814.9
37.5°	1348.8	1491.2	1635.9	1754.6	1750.8	1602.4	1338.2	1077.3	883.2	765.8	685.4
40°	1283.9	1427.8	1584.2	1684.5	1641.6	1448.2	1161.9	915.8	774.0	680.3	621.6
42.5°	1221.7	1366.1	1521.4	1601.0	1526.5	1288.8	1003.6	810.7	693.7	620.6	573.0
45°	1115.7	1268.1	1412.0	1456.1	1322.8	1060.9	811.6	671.7	593.8	539.7	506.7
47.5°	1012.1	1162.0	1293.3	1294.1	1113.9	860.4	684.6	581.3	514.8	472.9	448.9
50°	948.7	1091.3	1201.4	1184.3	979.8	765.3	612.3	523.2	467.8	435.5	410.4
52.5°	877.5	1015.8	1111.2	1062.4	866.3	673.5	547.3	472.5	426.6	398.5	376.1
55°	774.0	896.6	964.0	890.0	706.6	560.2	462.5	403.8	369.5	345.7	326.6
57.5°	672.2	773.4	815.8	729.7	582.0	464.5	391.2	347.2	313.1	296.1	286.2
60°	608.3	694.7	724.4	629.5	506.1	406.4	346.4	305.5	280.4	269.2	259.3
62.5°	545.5	616.1	628.4	541.3	441.2	355.8	304.2	269.6	253.0	242.3	232.9
65°	452.6	503.4	497.5	427.6	349.0	282.4	244.8	223.7	211.1	196.0	179.4
67.5°	372.6	403.6	385.0	332.5	266.4	219.5	194.9	178.9	163.3	149.0	145.2
70°	322.0	339.8	320.0	271.8	218.3	184.1	164.3	145.2	136.0	132.6	126.7
72.5°	273.5	279.7	258.2	217.0	177.7	152.4	133.1	122.4	117.4	114.7	110.8
75°	205.2	200.6	182.1	149.8	123.4	106.2	100.3	96.3	93.0	90.4	88.4
77.5°	144.1	137.3	120.9	99.8	85.9	77.7	74.1	72.1	70.4	69.1	67.2
80°	108.2	103.6	87.1	71.3	65.3	61.4	59.4	56.7	56.7	55.4	53.5
82.5°	79.2	74.0	59.7	52.3	49.0	46.6	45.1	43.6	43.0	43.3	41.8
85°	41.6	33.7	29.7	28.4	26.4	25.1	25.7	24.5	24.5	24.5	23.8
87.5°	13.3	11.0	10.8	10.8	11.6	11.9	11.7	12.0	12.8	12.5	13.2
90°	2.8	4.8	6.9	8.9	10.6	12.1	13.5	15.0	16.4	17.4	18.3
92.5°	16.4	16.3	16.1	15.9	16.2	16.9	17.7	18.3	19.1	19.5	20.1
95°	47.4	41.4	35.4	29.4	26.9	28.2	29.5	30.8	32.1	33.0	33.9
97.5°	89.1	72.2	55.1	38.1	31.1	34.1	37.0	40.0	43.0	43.7	44.4
100°	120.5	95.5	70.5	45.5	34.4	37.5	40.6	43.8	46.9	48.4	49.9
102.5°	183.7	178.5	173.1	167.8	152.2	126.2	100.2	74.2	48.2	50.1	52.0
105°	255.6	261.1	266.6	272.1	249.9	199.9	150.0	100.1	50.2	52.2	54.2
107.5°	324.2	328.6	332.9	337.4	309.7	249.9	189.9	130.1	70.3	68.2	66.1
110°	368.3	372.1	376.0	379.8	355.3	302.5	249.7	196.8	144.0	125.7	107.4



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	410.0	413.4	416.8	420.2	415.3	402.3	389.3	376.2	363.2	296.4	229.7
115°	476.1	479.3	482.4	485.5	489.3	493.9	498.4	503.1	507.6	422.9	338.3
117.5°	536.0	539.4	542.9	546.4	549.7	552.8	555.9	559.1	562.2	541.7	521.2
120°	578.7	581.3	584.1	586.9	589.9	593.1	596.5	599.8	603.0	605.3	607.4
122.5°	615.6	618.5	621.4	624.3	627.6	631.1	634.7	638.3	641.9	643.2	644.5
125°	671.2	673.6	676.0	678.4	681.3	684.8	688.3	691.7	695.2	696.5	697.8
127.5°	722.4	725.0	727.6	730.2	732.9	735.5	738.0	740.6	743.2	745.1	747.0
130°	754.9	757.9	760.7	763.6	766.1	768.1	770.2	772.1	774.2	776.2	778.2
132.5°	787.4	789.9	792.3	794.8	797.0	799.1	801.1	803.1	805.1	806.8	808.6
135°	830.6	833.5	836.5	839.4	841.6	843.3	844.9	846.5	848.3	850.1	851.9
137.5°	873.0	875.0	877.1	879.1	881.1	883.0	884.8	886.7	888.6	890.4	892.1
140°	900.7	902.2	903.6	905.1	906.8	908.8	910.9	912.8	914.9	916.5	918.2
142.5°	924.2	925.6	926.9	928.2	930.0	932.3	934.6	936.9	939.2	940.7	942.2
145°	959.9	959.8	959.6	959.4	960.9	964.0	967.1	970.2	973.3	974.6	975.9
147.5°	991.8	991.1	990.4	989.7	990.9	994.0	997.0	1000.1	1003.2	1004.2	1005.1
150°	1012.3	1011.0	1009.8	1008.5	1009.3	1012.2	1015.1	1018.0	1021.0	1022.1	1023.2
152.5°	1029.9	1028.5	1027.1	1025.6	1026.3	1029.1	1031.9	1034.7	1037.4	1038.5	1039.7
155°	1055.5	1053.9	1052.2	1050.6	1050.9	1053.1	1055.2	1057.5	1059.6	1060.8	1061.9
157.5°	1076.1	1074.6	1073.2	1071.9	1071.9	1073.5	1075.0	1076.5	1078.1	1079.3	1080.6
160°	1088.2	1087.1	1086.0	1084.9	1084.9	1086.0	1087.1	1088.2	1089.3	1090.4	1091.5
162.5°	1098.7	1097.6	1096.5	1095.5	1095.4	1096.3	1097.3	1098.2	1099.2	1100.4	1101.6
165°	1112.8	1111.7	1110.7	1109.6	1109.3	1109.8	1110.3	1110.9	1111.5	1112.8	1114.0
167.5°	1123.3	1122.3	1121.2	1120.1	1119.8	1120.3	1120.8	1121.4	1121.9	1123.1	1124.4
170°	1129.3	1128.3	1127.1	1126.0	1125.7	1126.0	1126.4	1126.8	1127.1	1128.4	1129.7
172.5°	1133.2	1132.1	1131.1	1130.0	1129.6	1130.0	1130.3	1130.7	1131.1	1132.4	1133.6
175°	1138.2	1136.9	1135.7	1134.4	1133.9	1134.3	1134.6	1135.0	1135.3	1136.6	1137.9
177.5°	1139.3	1138.2	1137.2	1136.2	1135.7	1135.9	1136.0	1136.2	1136.3	1137.4	1138.4
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8	1898.8
2.5°	1965.4	1972.2	1975.4	1975.4	1979.1	1977.5	1975.9
5°	2078.4	2090.9	2093.5	2105.4	2113.9	2111.3	2112.6
7.5°	2190.6	2210.8	2230.8	2239.9	2241.3	2246.6	2248.6
10°	2259.8	2276.3	2307.3	2302.7	2325.7	2339.0	2317.2
12.5°	2326.2	2348.5	2370.1	2376.0	2389.1	2393.3	2384.7
15°	2386.4	2398.3	2399.7	2396.3	2400.3	2397.0	2384.5
17.5°	2330.2	2311.0	2271.9	2253.4	2238.8	2217.2	2208.5
20°	2237.3	2180.6	2114.6	2088.3	2057.2	1996.5	2011.0
22.5°	2036.8	1972.1	1906.2	1829.1	1792.3	1734.7	1731.3
25°	1724.7	1613.2	1490.5	1404.7	1354.5	1297.2	1272.0
27.5°	1340.9	1200.6	1100.0	1049.0	1002.7	957.3	955.4
30°	1088.6	983.1	905.3	861.7	833.3	814.2	818.1
32.5°	917.7	845.3	792.8	756.6	735.6	721.3	721.0
35°	750.2	700.7	667.0	651.9	636.7	626.1	626.8
37.5°	642.0	612.3	593.6	576.8	567.3	562.1	559.2
40°	586.5	562.1	547.6	537.7	529.8	522.5	521.2
42.5°	542.8	522.5	508.1	500.2	492.8	487.8	486.4
45°	481.6	465.1	451.9	443.4	440.1	435.5	435.5
47.5°	428.4	412.2	401.9	396.6	390.9	387.8	387.7
50°	392.6	380.0	370.8	367.5	362.9	360.9	360.2
52.5°	360.4	351.0	344.4	342.2	340.2	337.7	338.1
55°	316.7	311.4	308.8	306.8	303.5	299.5	302.2
57.5°	279.9	275.4	268.3	262.1	259.1	256.2	257.4
60°	254.0	244.8	235.6	228.3	226.3	220.3	220.3
62.5°	221.3	208.4	197.0	193.0	191.0	188.2	187.6
65°	170.2	165.0	162.3	159.6	158.3	158.3	157.0
67.5°	141.0	139.0	136.0	135.3	134.1	133.7	133.3
70°	124.7	122.1	120.7	120.1	118.7	119.4	117.4
72.5°	108.8	106.8	106.5	104.8	104.0	104.1	102.6
75°	85.8	85.8	85.2	84.5	83.2	82.5	83.2
77.5°	66.0	66.1	64.9	64.8	64.7	64.8	64.1
80°	52.8	53.5	52.8	52.1	51.5	52.1	51.5
82.5°	41.7	40.8	40.6	40.6	40.4	40.0	39.9
85°	23.8	24.5	23.8	23.1	23.1	23.1	23.8
87.5°	12.8	13.0	13.1	13.2	13.3	13.3	12.9
90°	19.2	20.1	20.8	21.1	21.4	21.9	22.2
92.5°	20.5	21.0	21.4	21.5	21.8	22.0	22.2
95°	34.9	35.7	36.1	35.9	35.7	35.6	35.4
97.5°	45.1	45.9	46.3	46.6	46.8	47.0	47.2
100°	51.3	52.8	53.6	54.0	54.4	54.8	55.1
102.5°	53.9	55.8	57.0	57.5	58.0	58.5	59.1
105°	56.2	58.2	59.6	60.4	61.0	61.8	62.5
107.5°	64.1	62.1	61.4	62.2	62.9	63.6	64.3
110°	89.1	70.9	62.1	62.8	63.5	64.2	65.0



TEST NUMBER: P331853-935

CATALOG NUMBER: S122RDIW-S1005D970U935-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	163.1	96.3	63.3	63.9	64.5	65.1	65.7
115°	253.7	169.0	120.1	106.9	93.8	80.6	67.5
117.5°	500.8	480.4	448.5	405.2	362.0	318.7	275.4
120°	609.6	611.8	600.5	575.9	551.2	526.5	501.9
122.5°	645.8	647.1	645.4	640.6	635.8	631.0	626.3
125°	699.0	700.3	701.2	701.8	702.3	702.8	703.4
127.5°	748.8	750.7	751.7	751.8	751.9	752.0	752.1
130°	780.2	782.2	783.2	782.9	782.7	782.6	782.4
132.5°	810.3	812.0	812.8	812.5	812.4	812.2	812.0
135°	853.7	855.5	856.3	855.9	855.5	855.1	854.8
137.5°	893.9	895.7	896.3	895.7	895.0	894.4	893.8
140°	919.8	921.4	921.8	920.9	920.0	919.0	918.2
142.5°	943.7	945.2	945.5	944.6	943.7	942.8	941.8
145°	977.1	978.4	978.6	977.7	976.7	975.9	974.9
147.5°	1006.1	1007.0	1007.1	1006.3	1005.6	1004.8	1004.0
150°	1024.2	1025.4	1025.5	1024.6	1023.6	1022.7	1021.8
152.5°	1040.7	1041.8	1041.8	1040.6	1039.4	1038.2	1037.0
155°	1062.9	1064.0	1063.9	1062.4	1060.9	1059.5	1058.0
157.5°	1081.8	1083.1	1083.0	1081.5	1080.1	1078.7	1077.3
160°	1092.5	1093.6	1093.6	1092.3	1091.0	1089.8	1088.5
162.5°	1102.9	1104.1	1104.0	1102.3	1100.8	1099.2	1097.7
165°	1115.3	1116.6	1116.6	1115.3	1114.0	1112.8	1111.5
167.5°	1125.7	1127.0	1126.8	1125.2	1123.5	1121.9	1120.2
170°	1130.9	1132.2	1132.0	1130.4	1128.8	1127.1	1125.5
172.5°	1134.9	1136.2	1136.0	1134.4	1132.7	1131.1	1129.5
175°	1139.2	1140.5	1140.2	1138.3	1136.5	1134.7	1132.9
177.5°	1139.4	1140.4	1140.3	1138.9	1137.6	1136.3	1135.1
180°	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0	1137.0

(END OF REPORT)