

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331567-930

Luminaire Tested: **S122DIW-S865D970U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331567-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122DIW-S865D970U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 865 LUMENS PER FOOT, ASYMMETRIC DIFFUSER  
UPLIGHT 970 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 6263.3 lumens  
Efficiency: N/A  
Efficacy: 102.3 lumens/watt  
Spacing Criteria (0/90/45): 1.08 / 1.16 / 1.23  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 61.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20									20									20									20									20									
RC	80									70									50									30									10									0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0																			
RCR																																														
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50																												
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43																												
2	90	83	77	72	83	77	71	67	65	61	58	54	52	49	45	43	41	37																												
3	82	73	66	60	76	68	62	57	58	53	49	49	45	42	40	38	36	32																												
4	75	65	57	52	69	60	54	48	52	47	43	44	40	37	36	33	31	27																												
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24																												
6	64	52	44	39	59	49	42	37	42	37	33	36	32	28	30	27	24	22																												
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19																												
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17																												
9	51	40	32	27	48	37	30	26	32	27	23	28	24	21	23	20	18	16																												
10	48	36	29	25	45	34	28	23	30	25	21	26	22	19	22	19	16	14																												

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	22727	22727	22727	22727
5°	25480	22875	20272	22875
10°	29198	22689	17544	22689
15°	32301	22272	15499	22272
20°	31809	21825	14129	21825
25°	28682	21232	13261	21232
30°	23702	20282	12629	20282
35°	17274	19291	12177	19291
40°	13797	18120	11927	18120
45°	12056	16762	11586	16762
50°	11333	15450	11359	15450
55°	10446	14117	11054	14117
60°	9571	12700	10585	12700
65°	8722	11427	10128	11427
70°	7917	10192	9451	10192
75°	7018	8808	8372	8808
80°	6034	7290	6741	7290
85°	5409	5409	4001	5409



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	134.1	2.1
10°-20°	389.7	6.2
20°-30°	565.6	9.0
30°-40°	596.9	9.5
40°-50°	528.5	8.4
50°-60°	421.7	6.7
60°-70°	286.7	4.6
70°-80°	147.0	2.3
80°-90°	38.1	0.6
90°-100°	35.9	0.6
100°-110°	131.7	2.1
110°-120°	352.0	5.6
120°-130°	581.1	9.3
130°-140°	618.0	9.9
140°-150°	574.4	9.2
150°-160°	461.8	7.4
160°-170°	297.6	4.8
170°-180°	102.4	1.6
0°-30°	1089.4	17.4
0°-40°	1686.3	26.9
0°-60°	2636.5	42.1
0°-90°	3108.2	49.6
90°-120°	519.7	8.3
90°-150°	2293.2	36.6
90°-180°	3155.0	50.4
0°-180°	6263.3	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1408	1408	1408	1408	1408	
5°	1572	1411	1251	1411	1572	157
15°	1932	1332	927	1332	1932	533
25°	1610	1192	744	1192	1610	728
35°	876	979	618	979	876	570
45°	528	734	507	734	528	415
55°	371	502	393	502	371	333
65°	228	299	265	299	228	227
75°	112	141	134	141	112	120
85°	29	29	22	29	29	33
90°	21	1	21	1	21	11
95°	34	51	34	51	34	31
105°	59	237	59	237	59	62
115°	64	448	64	448	64	160
125°	666	633	666	633	666	576
135°	809	784	809	784	809	624
145°	923	909	923	909	923	577
155°	1002	1001	1002	1001	1002	462
165°	1052	1055	1052	1055	1052	297
175°	1073	1079	1073	1079	1073	102
180°	1077	1077	1077	1077	1077	



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1472.6	1473.0	1473.9	1467.0	1466.1	1466.1	1460.0	1454.8	1448.8	1440.6	1441.4
5°	1572.1	1578.1	1580.2	1573.8	1564.0	1562.9	1553.7	1538.6	1524.5	1513.1	1505.0
7.5°	1690.9	1693.3	1688.0	1679.4	1672.2	1659.2	1642.1	1625.4	1601.9	1580.4	1564.3
10°	1780.9	1784.2	1775.0	1762.5	1752.2	1737.1	1712.2	1686.8	1656.0	1626.2	1602.4
12.5°	1849.3	1857.3	1845.5	1843.9	1826.3	1805.5	1775.9	1763.0	1719.6	1678.1	1652.6
15°	1932.4	1931.9	1933.0	1922.6	1909.7	1906.4	1875.1	1841.0	1779.9	1755.5	1713.4
17.5°	1908.4	1916.6	1920.4	1920.3	1919.9	1917.9	1907.9	1886.4	1855.7	1816.2	1767.5
20°	1851.3	1862.1	1863.7	1876.2	1883.2	1892.4	1896.1	1890.2	1871.3	1838.3	1796.1
22.5°	1763.0	1766.0	1771.1	1790.5	1805.7	1828.8	1840.8	1860.8	1853.5	1837.4	1802.1
25°	1610.0	1604.6	1623.5	1633.2	1668.4	1705.2	1731.7	1760.9	1786.9	1802.5	1792.3
27.5°	1426.3	1418.1	1446.5	1472.3	1500.9	1540.8	1582.1	1630.8	1671.4	1722.2	1739.6
30°	1271.3	1276.2	1303.3	1330.8	1374.1	1430.4	1476.9	1530.5	1588.4	1645.1	1684.7
32.5°	1104.2	1123.0	1140.1	1182.3	1220.5	1283.2	1351.4	1418.4	1490.5	1555.1	1616.2
35°	876.4	898.1	921.9	952.7	1006.2	1068.4	1135.0	1225.3	1323.8	1412.0	1484.5
37.5°	737.7	734.3	747.9	770.1	813.5	863.7	940.4	1029.6	1145.5	1249.1	1351.4
40°	654.6	652.4	662.2	682.7	715.8	752.5	819.6	898.1	1005.7	1132.3	1254.0
42.5°	597.5	598.8	604.1	618.6	641.3	671.6	721.8	788.6	887.1	1006.3	1137.2
45°	528.0	531.8	537.8	544.8	557.7	582.6	610.7	658.4	736.3	835.8	964.6
47.5°	478.0	478.1	484.2	490.3	498.1	512.1	535.0	564.9	619.9	700.9	811.6
50°	451.2	447.4	451.8	456.6	464.7	474.4	489.6	517.7	554.5	620.0	712.5
52.5°	418.3	418.4	422.3	424.1	431.4	441.2	454.9	474.4	507.8	559.0	635.0
55°	371.1	373.8	376.0	379.2	385.7	392.7	403.6	416.5	442.5	480.9	537.2
57.5°	326.8	327.6	329.8	336.0	340.1	346.6	356.9	368.6	385.5	413.9	456.2
60°	296.4	296.4	300.8	303.5	308.9	315.4	323.5	334.8	350.0	373.2	407.4
62.5°	268.8	268.3	270.0	274.5	278.6	284.7	292.8	302.4	316.7	337.4	365.4
65°	228.3	227.2	230.5	231.5	235.9	241.8	248.3	258.6	269.9	285.1	310.0
67.5°	189.3	190.6	192.4	194.4	196.8	203.1	207.4	214.7	224.3	236.8	253.7
70°	167.7	167.7	167.7	169.3	172.6	175.9	180.2	186.1	195.3	206.1	221.3
72.5°	143.5	145.2	146.9	145.9	150.1	152.1	157.2	160.5	169.3	176.3	189.6
75°	112.5	112.5	112.5	115.2	116.8	118.5	121.7	125.0	129.3	137.9	145.0
77.5°	84.0	83.7	84.3	85.0	86.7	88.6	89.6	92.5	96.5	100.5	106.5
80°	64.9	66.0	66.5	67.6	67.6	68.7	69.2	73.1	75.7	78.4	82.3
82.5°	50.2	50.4	50.5	50.7	51.2	51.9	53.2	54.5	55.4	57.6	60.6
85°	29.2	28.7	28.7	29.8	29.2	29.2	30.3	31.4	31.4	31.9	33.5
87.5°	15.5	15.4	15.7	15.2	15.2	15.5	15.3	14.7	15.0	15.2	15.4
90°	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3	16.5	15.6	14.2
92.5°	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0	18.5	18.1	17.4
95°	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1	31.2	30.4	29.2
97.5°	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1	41.3	40.7	37.8
100°	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2	45.8	44.4	41.5
102.5°	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2	47.5	45.7	40.3
105°	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4	49.4	47.5	44.8
107.5°	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6	64.6	66.5	123.2
110°	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7	119.0	136.3	186.4



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5	280.7	343.9	356.2
115°	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3	400.5	480.7	476.4
117.5°	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6	513.0	532.4	529.5
120°	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2	573.2	571.0	567.9
122.5°	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3	609.0	607.8	604.4
125°	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7	659.5	658.3	655.0
127.5°	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4	705.6	703.8	701.3
130°	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9	735.0	733.1	731.2
132.5°	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6	764.0	762.4	760.4
135°	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7	804.9	803.2	801.6
137.5°	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7	843.1	841.4	839.6
140°	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4	867.9	866.3	864.4
142.5°	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2	890.8	889.3	887.2
145°	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1	922.8	921.6	918.7
147.5°	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8	950.9	950.0	947.1
150°	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9	967.8	966.8	964.0
152.5°	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5	983.4	982.4	979.7
155°	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5	1004.4	1003.4	1001.4
157.5°	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2	1022.1	1020.8	1019.4
160°	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6	1032.5	1031.4	1030.5
162.5°	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2	1042.0	1040.8	1039.9
165°	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5	1052.0
167.5°	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7	1063.5	1062.3	1061.8
170°	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8	1068.5	1067.3	1067.0
172.5°	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4	1072.3	1071.1	1070.7
175°	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5	1076.3	1075.1	1074.7
177.5°	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0	1077.0	1076.0	1075.9
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1444.5	1441.0	1438.8	1431.0	1424.1	1417.2	1415.0	1415.8	1406.4	1397.3	1393.3
5°	1500.7	1489.9	1479.6	1465.0	1447.7	1428.7	1419.0	1411.4	1392.5	1372.0	1360.1
7.5°	1551.1	1535.6	1515.9	1488.4	1463.1	1433.4	1414.5	1397.7	1370.0	1341.0	1323.2
10°	1581.8	1560.7	1535.3	1501.8	1471.0	1434.7	1409.2	1383.9	1351.4	1316.8	1295.1
12.5°	1608.3	1579.8	1554.8	1511.7	1475.3	1430.0	1399.8	1363.9	1329.8	1288.7	1267.5
15°	1671.1	1618.6	1571.0	1522.3	1477.4	1414.1	1380.6	1332.4	1287.5	1236.7	1212.4
17.5°	1719.7	1660.8	1585.8	1523.9	1471.5	1401.4	1352.2	1294.5	1241.4	1183.2	1150.1
20°	1747.4	1679.8	1599.1	1525.6	1462.8	1382.7	1329.2	1270.2	1208.0	1142.6	1106.9
22.5°	1763.8	1692.7	1613.0	1519.1	1445.5	1367.6	1300.2	1235.6	1172.6	1101.9	1064.5
25°	1769.0	1704.1	1619.8	1513.7	1423.9	1335.7	1254.6	1191.8	1115.5	1049.5	994.9
27.5°	1743.3	1696.7	1615.6	1503.5	1398.9	1295.8	1205.3	1134.2	1053.8	982.1	927.2
30°	1711.7	1684.7	1605.7	1493.1	1379.0	1268.1	1168.6	1087.9	1007.9	935.4	879.1
32.5°	1662.8	1656.9	1587.5	1478.4	1357.8	1233.1	1130.0	1048.6	959.9	888.6	834.9
35°	1566.7	1592.7	1548.8	1445.5	1317.8	1183.2	1071.7	978.7	886.7	818.5	768.2
37.5°	1437.9	1502.4	1490.9	1397.3	1264.0	1128.9	1005.8	908.6	820.9	752.1	702.7
40°	1349.2	1431.4	1443.3	1360.6	1225.9	1086.9	956.5	859.7	774.1	711.4	661.6
42.5°	1254.0	1350.1	1382.7	1316.5	1184.3	1042.7	912.3	812.0	727.4	666.4	622.2
45°	1094.5	1221.6	1280.5	1242.7	1115.0	970.0	835.8	734.1	657.3	600.0	565.9
47.5°	945.2	1084.1	1163.4	1150.1	1037.8	894.2	761.6	664.0	589.2	543.5	513.0
50°	839.6	982.4	1078.2	1082.6	982.4	840.2	707.1	615.1	546.4	503.7	478.7
52.5°	747.9	884.2	988.6	1011.5	920.6	783.9	658.2	566.6	506.1	466.8	444.6
55°	628.1	743.3	859.1	901.3	828.3	698.4	582.1	501.5	444.7	417.7	398.2
57.5°	522.2	618.2	725.1	771.8	726.8	615.6	506.5	436.6	390.4	366.8	351.9
60°	466.4	542.1	637.3	693.0	654.0	555.1	459.8	393.3	355.5	334.4	320.2
62.5°	414.4	481.5	562.0	612.9	591.7	498.4	413.1	354.3	321.6	301.9	291.7
65°	341.9	394.9	457.1	504.2	490.2	419.2	349.5	299.1	273.2	257.5	249.4
67.5°	281.5	319.8	363.0	404.2	392.9	342.7	286.6	247.4	228.1	214.6	209.7
70°	243.4	272.6	311.0	344.1	334.8	293.8	249.4	215.9	199.1	187.8	182.9
72.5°	207.1	231.1	260.4	287.4	281.2	247.0	210.0	184.7	171.8	161.3	157.4
75°	156.4	174.7	192.6	210.4	208.8	182.3	160.7	141.2	130.9	122.8	121.2
77.5°	115.4	125.7	137.9	148.5	145.5	130.4	113.4	102.2	94.7	89.3	88.4
80°	88.2	94.2	102.8	110.4	106.6	100.1	86.6	78.4	73.1	67.6	65.5
82.5°	63.9	69.9	75.1	79.2	76.3	70.2	61.9	56.3	53.2	49.4	48.6
85°	33.5	36.8	39.0	40.0	39.0	35.1	31.4	29.2	26.5	24.9	24.4
87.5°	15.6	15.2	15.0	15.5	13.9	13.5	11.3	9.7	9.6	9.5	9.0
90°	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7	15.6	15.4	15.2
95°	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6	44.9	39.2	33.5
97.5°	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5	84.4	68.3	52.2
100°	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9	114.1	90.4	66.8
102.5°	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0	174.0	169.0	164.0
105°	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8	242.1	247.2	252.4
107.5°	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7	307.0	311.1	315.3
110°	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1	348.8	352.4	356.0





TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0	388.2	391.4	394.7
115°	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9	450.9	453.9	456.8
117.5°	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2	507.5	510.8	514.0
120°	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4	548.0	550.5	553.1
122.5°	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2	582.9	585.7	588.4
125°	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3	635.6	637.9	640.1
127.5°	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5	684.0	686.5	689.0
130°	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1	714.9	717.6	720.3
132.5°	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2	745.6	748.0	750.2
135°	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7	786.5	789.3	792.1
137.5°	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7	826.6	828.6	830.5
140°	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5	852.9	854.3	855.7
142.5°	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9	875.1	876.4	877.7
145°	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1	909.0	908.8	908.7
147.5°	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9	939.1	938.5	937.8
150°	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8	958.5	957.3	956.2
152.5°	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6	975.3	973.9	972.6
155°	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1	999.5	997.9	996.4
157.5°	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3	1019.0	1017.6	1016.3
160°	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1030.5	1029.4	1028.3
162.5°	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5	1040.4	1039.3	1038.3
165°	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8	1053.8	1052.7	1051.7
167.5°	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8	1063.7	1062.7	1061.7
170°	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4	1069.3	1068.4	1067.3
172.5°	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2	1073.1	1072.0	1071.1
175°	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0	1077.7	1076.5	1075.4
177.5°	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8	1078.8	1077.8	1076.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1389.0	1386.4	1377.4	1372.6	1364.8	1357.5	1352.7	1354.9	1356.6	1355.7	1354.5
5°	1349.2	1339.0	1323.2	1309.7	1300.0	1282.1	1274.6	1270.8	1267.5	1263.7	1260.0
7.5°	1301.9	1285.6	1263.1	1243.8	1225.6	1203.5	1190.8	1183.2	1175.5	1166.9	1159.4
10°	1268.1	1245.4	1221.6	1194.5	1172.9	1152.8	1135.0	1123.1	1112.3	1102.0	1094.5
12.5°	1232.6	1206.4	1177.0	1140.0	1116.1	1087.5	1084.8	1063.8	1046.9	1040.6	1031.7
15°	1176.2	1139.3	1102.0	1058.2	1039.3	1013.3	997.0	980.8	966.2	955.9	953.2
17.5°	1112.0	1064.4	1027.2	995.7	964.7	938.1	923.2	910.2	898.1	884.4	882.6
20°	1063.1	1021.9	981.4	953.7	921.9	894.8	876.4	863.4	853.1	845.1	838.0
22.5°	1016.8	971.8	934.6	904.4	872.9	851.1	836.6	824.0	815.5	806.5	799.9
25°	942.4	907.3	866.7	832.6	806.6	792.6	780.6	769.8	764.4	758.5	750.9
27.5°	877.3	838.3	800.4	774.0	751.1	738.7	730.3	722.8	717.8	714.3	710.0
30°	831.5	792.0	762.2	736.3	717.4	704.9	699.5	695.2	689.3	687.1	684.9
32.5°	787.3	751.8	726.4	703.8	685.7	677.7	672.7	668.8	664.1	661.9	657.6
35°	725.0	695.2	670.3	657.9	643.3	636.2	632.4	627.0	622.6	620.5	620.0
37.5°	666.2	640.3	623.9	608.0	601.8	597.5	592.3	588.6	587.3	586.9	586.4
40°	628.1	607.0	592.4	579.4	576.7	570.2	565.9	562.6	562.6	563.2	562.6
42.5°	593.5	574.5	561.7	550.4	547.2	543.4	539.1	538.8	539.7	541.5	539.7
45°	541.0	527.5	518.3	512.8	506.9	503.1	502.6	504.2	504.8	505.3	506.9
47.5°	492.8	483.7	475.4	469.4	466.8	466.2	465.5	468.4	471.0	472.0	474.4
50°	464.1	453.9	446.9	443.0	440.9	439.9	440.9	444.2	446.3	449.0	450.6
52.5°	432.1	424.9	420.0	417.1	416.2	416.9	417.1	420.8	424.3	425.2	426.0
55°	387.9	382.5	381.4	376.5	378.7	378.1	380.8	383.0	386.3	389.6	390.0
57.5°	343.7	339.4	336.5	337.0	337.6	340.0	342.3	346.0	349.5	352.9	353.3
60°	314.3	312.2	310.5	310.5	311.6	314.9	317.6	321.3	323.5	325.7	327.3
62.5°	287.5	285.4	283.7	284.5	287.4	289.3	292.4	294.5	296.7	298.8	299.6
65°	245.1	244.0	245.6	246.7	247.2	250.0	253.7	255.4	257.5	258.6	262.4
67.5°	206.0	206.2	206.0	207.5	210.7	211.3	214.9	218.7	219.1	221.2	223.6
70°	179.6	180.7	181.8	182.9	185.6	186.6	189.3	190.9	193.1	194.8	196.4
72.5°	155.4	155.6	156.7	156.5	158.7	161.1	163.4	165.0	167.1	169.3	170.8
75°	119.5	119.5	120.7	121.2	123.9	126.6	126.0	127.1	129.3	131.4	132.6
77.5°	87.3	86.1	87.3	87.9	88.7	91.0	91.4	92.9	95.4	94.7	95.9
80°	66.5	64.9	66.5	67.1	67.1	69.8	69.8	70.8	72.5	70.8	72.5
82.5°	47.5	46.7	47.9	48.0	48.9	49.0	49.9	50.1	51.7	51.0	51.7
85°	23.8	23.2	23.8	23.2	23.8	24.4	24.4	23.8	23.8	24.9	23.2
87.5°	9.0	9.0	8.8	9.0	8.9	8.7	8.5	8.6	8.8	8.2	8.2
90°	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3	18.2	19.1	19.6
92.5°	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0	19.4	19.9	20.2
95°	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1	33.0	33.8	34.2
97.5°	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1	42.7	43.5	43.9
100°	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2	48.6	50.0	50.8
102.5°	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2	51.0	52.8	54.0
105°	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4	53.2	55.1	56.4
107.5°	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6	60.7	58.8	58.1
110°	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7	84.4	67.1	58.8



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5	154.4	91.2	59.9
115°	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3	240.2	160.0	113.7
117.5°	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6	474.3	454.9	424.7
120°	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2	577.2	579.4	568.7
122.5°	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3	611.6	612.8	611.1
125°	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7	661.9	663.2	664.0
127.5°	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4	709.1	710.9	711.8
130°	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9	738.8	740.7	741.6
132.5°	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6	767.3	768.9	769.6
135°	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7	808.4	810.1	810.8
137.5°	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7	846.4	848.2	848.7
140°	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4	871.0	872.5	872.9
142.5°	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2	893.6	895.0	895.3
145°	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1	925.3	926.4	926.7
147.5°	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8	952.7	953.6	953.7
150°	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9	969.9	970.9	971.0
152.5°	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5	985.5	986.5	986.5
155°	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5	1006.5	1007.5	1007.4
157.5°	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2	1024.4	1025.6	1025.5
160°	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6	1034.5	1035.6	1035.5
162.5°	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2	1044.3	1045.5	1045.4
165°	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4
167.5°	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7	1065.9	1067.1	1067.0
170°	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8	1070.9	1072.1	1072.0
172.5°	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4	1074.6	1075.9	1075.7
175°	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5	1078.7	1079.9	1079.7
177.5°	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0	1078.9	1079.9	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1350.1	1349.2	1349.2	1345.3	1349.2	1349.2	1350.1	1354.5	1355.7	1356.6	1354.9
5°	1252.4	1250.8	1248.1	1250.8	1248.1	1250.8	1252.4	1260.0	1263.7	1267.5	1270.8
7.5°	1155.8	1149.2	1148.3	1141.9	1148.3	1149.2	1155.8	1159.4	1166.9	1175.5	1183.2
10°	1085.2	1080.9	1080.4	1070.1	1080.4	1080.9	1085.2	1094.5	1102.0	1112.3	1123.1
12.5°	1031.6	1021.2	1023.2	1017.2	1023.2	1021.2	1031.6	1031.7	1040.6	1046.9	1063.8
15°	938.7	938.7	936.5	927.2	936.5	938.7	938.7	953.2	955.9	966.2	980.8
17.5°	871.9	870.7	865.6	868.2	865.6	870.7	871.9	882.6	884.4	898.1	910.2
20°	832.0	828.8	822.3	822.3	822.3	828.8	832.0	838.0	845.1	853.1	863.4
22.5°	794.4	794.2	787.3	789.4	787.3	794.2	794.4	799.9	806.5	815.5	824.0
25°	750.3	746.0	742.8	744.4	742.8	746.0	750.3	750.9	758.5	764.4	769.8
27.5°	708.6	706.2	706.0	701.6	706.0	706.2	708.6	710.0	714.3	717.8	722.8
30°	684.4	679.0	680.0	677.4	680.0	679.0	684.4	684.9	687.1	689.3	695.2
32.5°	656.6	654.7	653.6	651.3	653.6	654.7	656.6	657.6	661.9	664.1	668.8
35°	618.9	619.5	616.7	617.8	616.7	619.5	618.9	620.0	620.5	622.6	627.0
37.5°	585.9	587.6	586.4	586.7	586.4	587.6	585.9	586.4	586.9	587.3	588.6
40°	564.3	564.3	564.3	565.9	564.3	564.3	564.3	562.6	563.2	562.6	562.6
42.5°	543.5	542.6	541.8	541.6	541.8	542.6	543.5	539.7	541.5	539.7	538.8
45°	508.0	509.6	510.1	507.4	510.1	509.6	508.0	506.9	505.3	504.8	504.2
47.5°	475.9	476.1	475.9	478.3	475.9	476.1	475.9	474.4	472.0	471.0	468.4
50°	453.4	452.2	453.4	452.2	453.4	452.2	453.4	450.6	449.0	446.3	444.2
52.5°	429.6	429.7	429.1	428.9	429.1	429.7	429.6	426.0	425.2	424.3	420.8
55°	392.2	393.3	392.7	392.7	392.7	393.3	392.2	390.0	389.6	386.3	383.0
57.5°	353.6	354.6	355.3	352.9	355.3	354.6	353.6	353.3	352.9	349.5	346.0
60°	326.8	329.5	328.9	327.8	328.9	329.5	326.8	327.3	325.7	323.5	321.3
62.5°	302.1	303.0	303.0	302.7	303.0	303.0	302.1	299.6	298.8	296.7	294.5
65°	264.0	265.1	263.4	265.1	263.4	265.1	264.0	262.4	258.6	257.5	255.4
67.5°	223.0	223.3	224.5	225.3	224.5	223.3	223.0	223.6	221.2	219.1	218.7
70°	197.5	196.9	198.5	200.2	198.5	196.9	197.5	196.4	194.8	193.1	190.9
72.5°	170.6	171.8	171.3	172.4	171.3	171.8	170.6	170.8	169.3	167.1	165.0
75°	131.4	133.1	132.6	134.2	132.6	133.1	131.4	132.6	131.4	129.3	127.1
77.5°	95.0	95.2	95.0	95.9	95.0	95.2	95.0	95.9	94.7	95.4	92.9
80°	72.5	71.4	70.4	72.5	70.4	71.4	72.5	72.5	70.8	72.5	70.8
82.5°	50.4	51.0	50.0	50.0	50.0	51.0	50.4	51.7	51.0	51.7	50.1
85°	23.2	22.7	21.6	21.6	21.6	22.7	23.2	23.2	24.9	23.8	23.8
87.5°	8.3	8.0	8.1	7.7	8.1	8.0	8.3	8.2	8.2	8.8	8.6
90°	20.0	20.3	20.7	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3
92.5°	20.4	20.6	20.8	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0
95°	34.0	33.8	33.7	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1
97.5°	44.1	44.3	44.5	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1
100°	51.1	51.5	51.9	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2
102.5°	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2
105°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4
107.5°	58.9	59.5	60.3	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6
110°	59.4	60.2	60.8	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	60.5	61.1	61.6	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5
115°	101.3	88.8	76.3	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3
117.5°	383.7	342.8	301.8	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6
120°	545.4	522.0	498.6	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2
122.5°	606.6	602.1	597.5	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3
125°	664.6	665.0	665.5	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7
127.5°	711.9	712.0	712.1	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4
130°	741.4	741.2	741.0	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9
132.5°	769.4	769.2	769.1	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6
135°	810.5	810.1	809.8	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7
137.5°	848.2	847.5	846.9	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7
140°	872.0	871.1	870.3	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4
142.5°	894.5	893.6	892.8	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2
145°	925.8	924.9	924.1	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1
147.5°	952.9	952.2	951.5	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8
150°	970.2	969.3	968.4	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9
152.5°	985.4	984.2	983.1	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5
155°	1006.0	1004.6	1003.2	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5
157.5°	1024.1	1022.8	1021.4	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2
160°	1034.3	1033.1	1031.9	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6
162.5°	1043.8	1042.4	1040.9	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2
165°	1056.1	1054.9	1053.7	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9
167.5°	1065.4	1063.9	1062.3	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7
170°	1070.4	1068.9	1067.3	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8
172.5°	1074.2	1072.6	1071.1	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4
175°	1077.9	1076.2	1074.5	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5
177.5°	1078.5	1077.3	1076.0	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1352.7	1357.5	1364.8	1372.6	1377.4	1386.4	1389.0	1393.3	1397.3	1406.4	1415.8
5°	1274.6	1282.1	1300.0	1309.7	1323.2	1339.0	1349.2	1360.1	1372.0	1392.5	1411.4
7.5°	1190.8	1203.5	1225.6	1243.8	1263.1	1285.6	1301.9	1323.2	1341.0	1370.0	1397.7
10°	1135.0	1152.8	1172.9	1194.5	1221.6	1245.4	1268.1	1295.1	1316.8	1351.4	1383.9
12.5°	1084.8	1087.5	1116.1	1140.0	1177.0	1206.4	1232.6	1267.5	1288.7	1329.8	1363.9
15°	997.0	1013.3	1039.3	1058.2	1102.0	1139.3	1176.2	1212.4	1236.7	1287.5	1332.4
17.5°	923.2	938.1	964.7	995.7	1027.2	1064.4	1112.0	1150.1	1183.2	1241.4	1294.5
20°	876.4	894.8	921.9	953.7	981.4	1021.9	1063.1	1106.9	1142.6	1208.0	1270.2
22.5°	836.6	851.1	872.9	904.4	934.6	971.8	1016.8	1064.5	1101.9	1172.6	1235.6
25°	780.6	792.6	806.6	832.6	866.7	907.3	942.4	994.9	1049.5	1115.5	1191.8
27.5°	730.3	738.7	751.1	774.0	800.4	838.3	877.3	927.2	982.1	1053.8	1134.2
30°	699.5	704.9	717.4	736.3	762.2	792.0	831.5	879.1	935.4	1007.9	1087.9
32.5°	672.7	677.7	685.7	703.8	726.4	751.8	787.3	834.9	888.6	959.9	1048.6
35°	632.4	636.2	643.3	657.9	670.3	695.2	725.0	768.2	818.5	886.7	978.7
37.5°	592.3	597.5	601.8	608.0	623.9	640.3	666.2	702.7	752.1	820.9	908.6
40°	565.9	570.2	576.7	579.4	592.4	607.0	628.1	661.6	711.4	774.1	859.7
42.5°	539.1	543.4	547.2	550.4	561.7	574.5	593.5	622.2	666.4	727.4	812.0
45°	502.6	503.1	506.9	512.8	518.3	527.5	541.0	565.9	600.0	657.3	734.1
47.5°	465.5	466.2	466.8	469.4	475.4	483.7	492.8	513.0	543.5	589.2	664.0
50°	440.9	439.9	440.9	443.0	446.9	453.9	464.1	478.7	503.7	546.4	615.1
52.5°	417.1	416.9	416.2	417.1	420.0	424.9	432.1	444.6	466.8	506.1	566.6
55°	380.8	378.1	378.7	376.5	381.4	382.5	387.9	398.2	417.7	444.7	501.5
57.5°	342.3	340.0	337.6	337.0	336.5	339.4	343.7	351.9	366.8	390.4	436.6
60°	317.6	314.9	311.6	310.5	310.5	312.2	314.3	320.2	334.4	355.5	393.3
62.5°	292.4	289.3	287.4	284.5	283.7	285.4	287.5	291.7	301.9	321.6	354.3
65°	253.7	250.0	247.2	246.7	245.6	244.0	245.1	249.4	257.5	273.2	299.1
67.5°	214.9	211.3	210.7	207.5	206.0	206.2	206.0	209.7	214.6	228.1	247.4
70°	189.3	186.6	185.6	182.9	181.8	180.7	179.6	182.9	187.8	199.1	215.9
72.5°	163.4	161.1	158.7	156.5	156.7	155.6	155.4	157.4	161.3	171.8	184.7
75°	126.0	126.6	123.9	121.2	120.7	119.5	119.5	121.2	122.8	130.9	141.2
77.5°	91.4	91.0	88.7	87.9	87.3	86.1	87.3	88.4	89.3	94.7	102.2
80°	69.8	69.8	67.1	67.1	66.5	64.9	66.5	65.5	67.6	73.1	78.4
82.5°	49.9	49.0	48.9	48.0	47.9	46.7	47.5	48.6	49.4	53.2	56.3
85°	24.4	24.4	23.8	23.2	23.8	23.2	23.8	24.4	24.9	26.5	29.2
87.5°	8.5	8.7	8.9	9.0	8.8	9.0	9.0	9.0	9.5	9.6	9.7
90°	16.5	15.6	14.2	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8
92.5°	18.5	18.1	17.4	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7
95°	31.2	30.4	29.2	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6
97.5°	41.3	40.7	37.8	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5
100°	45.8	44.4	41.5	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9
102.5°	47.5	45.7	70.3	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0
105°	49.4	47.5	94.8	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8
107.5°	64.6	66.5	123.2	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7
110°	119.0	136.3	186.4	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.7	343.9	356.2	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0
115°	400.5	480.7	476.4	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9
117.5°	513.0	532.4	529.5	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2
120°	573.2	571.0	567.9	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4
122.5°	609.0	607.8	604.4	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2
125°	659.5	658.3	655.0	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3
127.5°	705.6	703.8	701.3	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5
130°	735.0	733.1	731.2	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1
132.5°	764.0	762.4	760.4	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2
135°	804.9	803.2	801.6	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7
137.5°	843.1	841.4	839.6	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7
140°	867.9	866.3	864.4	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5
142.5°	890.8	889.3	887.2	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9
145°	922.8	921.6	918.7	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1
147.5°	950.9	950.0	947.1	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9
150°	967.8	966.8	964.0	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8
152.5°	983.4	982.4	979.7	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6
155°	1004.4	1003.4	1001.4	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1
157.5°	1022.1	1020.8	1019.4	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3
160°	1032.5	1031.4	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4
162.5°	1042.0	1040.8	1039.9	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5
165°	1053.7	1052.5	1052.0	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8
167.5°	1063.5	1062.3	1061.8	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8
170°	1068.5	1067.3	1067.0	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4
172.5°	1072.3	1071.1	1070.7	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2
175°	1076.3	1075.1	1074.7	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0
177.5°	1077.0	1076.0	1075.9	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1415.0	1417.2	1424.1	1431.0	1438.8	1441.0	1444.5	1441.4	1440.6	1448.8	1454.8
5°	1419.0	1428.7	1447.7	1465.0	1479.6	1489.9	1500.7	1505.0	1513.1	1524.5	1538.6
7.5°	1414.5	1433.4	1463.1	1488.4	1515.9	1535.6	1551.1	1564.3	1580.4	1601.9	1625.4
10°	1409.2	1434.7	1471.0	1501.8	1535.3	1560.7	1581.8	1602.4	1626.2	1656.0	1686.8
12.5°	1399.8	1430.0	1475.3	1511.7	1554.8	1579.8	1608.3	1652.6	1678.1	1719.6	1763.0
15°	1380.6	1414.1	1477.4	1522.3	1571.0	1618.6	1671.1	1713.4	1755.5	1779.9	1841.0
17.5°	1352.2	1401.4	1471.5	1523.9	1585.8	1660.8	1719.7	1767.5	1816.2	1855.7	1886.4
20°	1329.2	1382.7	1462.8	1525.6	1599.1	1679.8	1747.4	1796.1	1838.3	1871.3	1890.2
22.5°	1300.2	1367.6	1445.5	1519.1	1613.0	1692.7	1763.8	1802.1	1837.4	1853.5	1860.8
25°	1254.6	1335.7	1423.9	1513.7	1619.8	1704.1	1769.0	1792.3	1802.5	1786.9	1760.9
27.5°	1205.3	1295.8	1398.9	1503.5	1615.6	1696.7	1743.3	1739.6	1722.2	1671.4	1630.8
30°	1168.6	1268.1	1379.0	1493.1	1605.7	1684.7	1711.7	1684.7	1645.1	1588.4	1530.5
32.5°	1130.0	1233.1	1357.8	1478.4	1587.5	1656.9	1662.8	1616.2	1555.1	1490.5	1418.4
35°	1071.7	1183.2	1317.8	1445.5	1548.8	1592.7	1566.7	1484.5	1412.0	1323.8	1225.3
37.5°	1005.8	1128.9	1264.0	1397.3	1490.9	1502.4	1437.9	1351.4	1249.1	1145.5	1029.6
40°	956.5	1086.9	1225.9	1360.6	1443.3	1431.4	1349.2	1254.0	1132.3	1005.7	898.1
42.5°	912.3	1042.7	1184.3	1316.5	1382.7	1350.1	1254.0	1137.2	1006.3	887.1	788.6
45°	835.8	970.0	1115.0	1242.7	1280.5	1221.6	1094.5	964.6	835.8	736.3	658.4
47.5°	761.6	894.2	1037.8	1150.1	1163.4	1084.1	945.2	811.6	700.9	619.9	564.9
50°	707.1	840.2	982.4	1082.6	1078.2	982.4	839.6	712.5	620.0	554.5	517.7
52.5°	658.2	783.9	920.6	1011.5	988.6	884.2	747.9	635.0	559.0	507.8	474.4
55°	582.1	698.4	828.3	901.3	859.1	743.3	628.1	537.2	480.9	442.5	416.5
57.5°	506.5	615.6	726.8	771.8	725.1	618.2	522.2	456.2	413.9	385.5	368.6
60°	459.8	555.1	654.0	693.0	637.3	542.1	466.4	407.4	373.2	350.0	334.8
62.5°	413.1	498.4	591.7	612.9	562.0	481.5	414.4	365.4	337.4	316.7	302.4
65°	349.5	419.2	490.2	504.2	457.1	394.9	341.9	310.0	285.1	269.9	258.6
67.5°	286.6	342.7	392.9	404.2	363.0	319.8	281.5	253.7	236.8	224.3	214.7
70°	249.4	293.8	334.8	344.1	311.0	272.6	243.4	221.3	206.1	195.3	186.1
72.5°	210.0	247.0	281.2	287.4	260.4	231.1	207.1	189.6	176.3	169.3	160.5
75°	160.7	182.3	208.8	210.4	192.6	174.7	156.4	145.0	137.9	129.3	125.0
77.5°	113.4	130.4	145.5	148.5	137.9	125.7	115.4	106.5	100.5	96.5	92.5
80°	86.6	100.1	106.6	110.4	102.8	94.2	88.2	82.3	78.4	75.7	73.1
82.5°	61.9	70.2	76.3	79.2	75.1	69.9	63.9	60.6	57.6	55.4	54.5
85°	31.4	35.1	39.0	40.0	39.0	36.8	33.5	33.5	31.9	31.4	31.4
87.5°	11.3	13.5	13.9	15.5	15.0	15.2	15.6	15.4	15.2	15.0	14.7
90°	2.7	4.6	6.5	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3
92.5°	15.6	15.4	15.2	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0
95°	44.9	39.2	33.5	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1
97.5°	84.4	68.3	52.2	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1
100°	114.1	90.4	66.8	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2
102.5°	174.0	169.0	164.0	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2
105°	242.1	247.2	252.4	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4
107.5°	307.0	311.1	315.3	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6
110°	348.8	352.4	356.0	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7





TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	388.2	391.4	394.7	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5
115°	450.9	453.9	456.8	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3
117.5°	507.5	510.8	514.0	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6
120°	548.0	550.5	553.1	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2
122.5°	582.9	585.7	588.4	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3
125°	635.6	637.9	640.1	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7
127.5°	684.0	686.5	689.0	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4
130°	714.9	717.6	720.3	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9
132.5°	745.6	748.0	750.2	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6
135°	786.5	789.3	792.1	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7
137.5°	826.6	828.6	830.5	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7
140°	852.9	854.3	855.7	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4
142.5°	875.1	876.4	877.7	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2
145°	909.0	908.8	908.7	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1
147.5°	939.1	938.5	937.8	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8
150°	958.5	957.3	956.2	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9
152.5°	975.3	973.9	972.6	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5
155°	999.5	997.9	996.4	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5
157.5°	1019.0	1017.6	1016.3	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2
160°	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6
162.5°	1040.4	1039.3	1038.3	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2
165°	1053.8	1052.7	1051.7	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9
167.5°	1063.7	1062.7	1061.7	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7
170°	1069.3	1068.4	1067.3	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8
172.5°	1073.1	1072.0	1071.1	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4
175°	1077.7	1076.5	1075.4	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5
177.5°	1078.8	1077.8	1076.8	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6	1407.6
2.5°	1460.0	1466.1	1466.1	1467.0	1473.9	1473.0	1472.6
5°	1553.7	1562.9	1564.0	1573.8	1580.2	1578.1	1572.1
7.5°	1642.1	1659.2	1672.2	1679.4	1688.0	1693.3	1690.9
10°	1712.2	1737.1	1752.2	1762.5	1775.0	1784.2	1780.9
12.5°	1775.9	1805.5	1826.3	1843.9	1845.5	1857.3	1849.3
15°	1875.1	1906.4	1909.7	1922.6	1933.0	1931.9	1932.4
17.5°	1907.9	1917.9	1919.9	1920.3	1920.4	1916.6	1908.4
20°	1896.1	1892.4	1883.2	1876.2	1863.7	1862.1	1851.3
22.5°	1840.8	1828.8	1805.7	1790.5	1771.1	1766.0	1763.0
25°	1731.7	1705.2	1668.4	1633.2	1623.5	1604.6	1610.0
27.5°	1582.1	1540.8	1500.9	1472.3	1446.5	1418.1	1426.3
30°	1476.9	1430.4	1374.1	1330.8	1303.3	1276.2	1271.3
32.5°	1351.4	1283.2	1220.5	1182.3	1140.1	1123.0	1104.2
35°	1135.0	1068.4	1006.2	952.7	921.9	898.1	876.4
37.5°	940.4	863.7	813.5	770.1	747.9	734.3	737.7
40°	819.6	752.5	715.8	682.7	662.2	652.4	654.6
42.5°	721.8	671.6	641.3	618.6	604.1	598.8	597.5
45°	610.7	582.6	557.7	544.8	537.8	531.8	528.0
47.5°	535.0	512.1	498.1	490.3	484.2	478.1	478.0
50°	489.6	474.4	464.7	456.6	451.8	447.4	451.2
52.5°	454.9	441.2	431.4	424.1	422.3	418.4	418.3
55°	403.6	392.7	385.7	379.2	376.0	373.8	371.1
57.5°	356.9	346.6	340.1	336.0	329.8	327.6	326.8
60°	323.5	315.4	308.9	303.5	300.8	296.4	296.4
62.5°	292.8	284.7	278.6	274.5	270.0	268.3	268.8
65°	248.3	241.8	235.9	231.5	230.5	227.2	228.3
67.5°	207.4	203.1	196.8	194.4	192.4	190.6	189.3
70°	180.2	175.9	172.6	169.3	167.7	167.7	167.7
72.5°	157.2	152.1	150.1	145.9	146.9	145.2	143.5
75°	121.7	118.5	116.8	115.2	112.5	112.5	112.5
77.5°	89.6	88.6	86.7	85.0	84.3	83.7	84.0
80°	69.2	68.7	67.6	67.6	66.5	66.0	64.9
82.5°	53.2	51.9	51.2	50.7	50.5	50.4	50.2
85°	30.3	29.2	29.2	29.8	28.7	28.7	29.2
87.5°	15.3	15.5	15.2	15.2	15.7	15.4	15.5
90°	18.2	19.1	19.6	20.0	20.3	20.7	21.0
92.5°	19.4	19.9	20.2	20.4	20.6	20.8	21.0
95°	33.0	33.8	34.2	34.0	33.8	33.7	33.5
97.5°	42.7	43.5	43.9	44.1	44.3	44.5	44.7
100°	48.6	50.0	50.8	51.1	51.5	51.9	52.2
102.5°	51.0	52.8	54.0	54.5	55.0	55.4	55.9
105°	53.2	55.1	56.4	57.2	57.8	58.5	59.2
107.5°	60.7	58.8	58.1	58.9	59.5	60.3	60.9
110°	84.4	67.1	58.8	59.4	60.2	60.8	61.6



TEST NUMBER: P331567-930

CATALOG NUMBER: S122DIW-S865D970U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	154.4	91.2	59.9	60.5	61.1	61.6	62.2
115°	240.2	160.0	113.7	101.3	88.8	76.3	63.9
117.5°	474.3	454.9	424.7	383.7	342.8	301.8	260.8
120°	577.2	579.4	568.7	545.4	522.0	498.6	475.2
122.5°	611.6	612.8	611.1	606.6	602.1	597.5	593.0
125°	661.9	663.2	664.0	664.6	665.0	665.5	666.1
127.5°	709.1	710.9	711.8	711.9	712.0	712.1	712.2
130°	738.8	740.7	741.6	741.4	741.2	741.0	740.9
132.5°	767.3	768.9	769.6	769.4	769.2	769.1	768.9
135°	808.4	810.1	810.8	810.5	810.1	809.8	809.4
137.5°	846.4	848.2	848.7	848.2	847.5	846.9	846.4
140°	871.0	872.5	872.9	872.0	871.1	870.3	869.4
142.5°	893.6	895.0	895.3	894.5	893.6	892.8	891.9
145°	925.3	926.4	926.7	925.8	924.9	924.1	923.2
147.5°	952.7	953.6	953.7	952.9	952.2	951.5	950.7
150°	969.9	970.9	971.0	970.2	969.3	968.4	967.6
152.5°	985.5	986.5	986.5	985.4	984.2	983.1	981.9
155°	1006.5	1007.5	1007.4	1006.0	1004.6	1003.2	1001.8
157.5°	1024.4	1025.6	1025.5	1024.1	1022.8	1021.4	1020.1
160°	1034.5	1035.6	1035.5	1034.3	1033.1	1031.9	1030.7
162.5°	1044.3	1045.5	1045.4	1043.8	1042.4	1040.9	1039.4
165°	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5
167.5°	1065.9	1067.1	1067.0	1065.4	1063.9	1062.3	1060.8
170°	1070.9	1072.1	1072.0	1070.4	1068.9	1067.3	1065.8
172.5°	1074.6	1075.9	1075.7	1074.2	1072.6	1071.1	1069.5
175°	1078.7	1079.9	1079.7	1077.9	1076.2	1074.5	1072.8
177.5°	1078.9	1079.9	1079.8	1078.5	1077.3	1076.0	1074.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6

(END OF REPORT)