

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331857-930

Luminaire Tested: **S122RDIW-S1005D1240U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331857-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1240U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 7150.1 lumens  
Efficiency: N/A  
Efficacy: 93.8 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	106	106	106	106	97	97	97	97	80	80	80	64	64	64	50	50	50	44
1	97	93	89	86	89	85	82	79	71	69	67	58	56	55	45	44	44	38
2	89	82	76	71	81	75	70	66	63	59	56	51	49	47	41	39	38	33
3	82	73	66	60	74	67	61	56	56	52	48	46	43	41	37	35	33	29
4	75	65	57	52	68	60	53	48	50	46	42	42	38	35	33	31	29	25
5	69	58	51	45	63	54	47	42	45	40	37	38	34	31	30	28	26	23
6	64	52	45	39	58	49	42	37	41	36	32	34	31	28	28	25	23	20
7	59	48	40	35	54	44	38	33	38	33	29	32	28	25	26	23	21	18
8	55	43	36	31	51	40	34	29	35	29	26	29	25	22	24	21	19	17
9	51	40	33	28	47	37	31	26	32	27	23	27	23	20	22	19	17	15
10	48	37	30	25	44	34	28	24	29	25	21	25	21	19	21	18	16	14

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	29032	29032	29032	29032
5°	32423	29214	25901	29214
10°	35974	29009	22453	29009
15°	37742	28583	17690	28583
20°	32720	27953	15309	27953
25°	21458	27091	13668	27091
30°	14443	26045	12370	26045
35°	11698	24727	11158	24727
40°	10404	23294	10323	23294
45°	9417	21614	9216	21614
50°	8568	19947	8538	19947
55°	8056	18097	7949	18097
60°	6736	16401	6659	16401
65°	5681	14896	6445	14896
70°	5249	13303	6076	13303
75°	4916	11578	5608	11578
80°	4537	9530	4993	9530
85°	4168	7521	4390	7521



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.4	2.4
10°-20°	474.9	6.6
20°-30°	612.0	8.6
30°-40°	581.6	8.1
40°-50°	498.2	7.0
50°-60°	379.4	5.3
60°-70°	239.9	3.4
70°-80°	119.8	1.7
80°-90°	34.6	0.5
90°-100°	46.0	0.6
100°-110°	168.6	2.4
110°-120°	450.7	6.3
120°-130°	744.0	10.4
130°-140°	791.2	11.1
140°-150°	735.4	10.3
150°-160°	591.2	8.3
160°-170°	381.0	5.3
170°-180°	131.1	1.8
0°-30°	1257.4	17.6
0°-40°	1839.0	25.7
0°-60°	2716.7	38.0
0°-90°	3110.9	43.5
90°-120°	665.3	9.3
90°-150°	2935.8	41.1
90°-180°	4039.0	56.5
0°-180°	7150.1	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1798	1798	1798	1798	1798	
5°	2000	1802	1598	1802	2000	197
15°	2258	1710	1058	1710	2258	609
25°	1204	1521	767	1521	1204	572
35°	594	1254	566	1254	594	380
45°	412	947	404	947	412	319
55°	286	643	282	643	286	251
65°	149	390	169	390	149	151
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	27	1	27	1	27	13
95°	43	65	43	65	43	40
105°	76	303	76	303	76	79
115°	82	574	82	574	82	205
125°	853	811	853	811	853	738
135°	1036	1003	1036	1003	1036	799
145°	1182	1164	1182	1164	1182	739
155°	1282	1282	1282	1282	1282	592
165°	1347	1350	1347	1350	1347	380
175°	1373	1381	1373	1381	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1871.0	1872.6	1874.0	1870.5	1870.5	1867.5	1861.1	1856.0	1842.1	1840.0	1840.0
5°	2000.5	1999.3	2001.7	1993.7	1982.4	1979.9	1968.1	1952.4	1936.2	1918.1	1914.3
7.5°	2129.2	2127.4	2122.3	2121.0	2112.4	2093.4	2074.4	2054.0	2027.0	2000.7	1987.4
10°	2194.2	2214.8	2202.3	2180.4	2184.8	2155.5	2139.8	2113.0	2090.5	2051.1	2042.4
12.5°	2258.1	2266.3	2262.3	2249.9	2244.3	2223.9	2202.8	2179.5	2138.0	2102.6	2071.8
15°	2257.9	2269.8	2272.9	2269.1	2272.3	2271.0	2259.8	2240.4	2204.2	2165.4	2131.7
17.5°	2091.2	2099.5	2119.9	2133.8	2151.3	2188.3	2206.5	2213.7	2208.3	2186.2	2162.4
20°	1904.3	1890.5	1948.0	1977.4	2002.4	2064.8	2118.6	2139.2	2172.3	2171.7	2165.4
22.5°	1639.4	1642.7	1697.1	1732.0	1805.0	1867.4	1928.7	2006.3	2070.4	2112.7	2137.5
25°	1204.5	1228.3	1282.6	1330.2	1411.4	1527.5	1633.1	1755.6	1871.2	1962.4	2049.3
27.5°	904.7	906.4	949.5	993.4	1041.6	1136.9	1269.7	1416.0	1580.8	1716.8	1873.2
30°	774.7	770.9	789.0	816.0	857.2	930.9	1030.9	1174.6	1338.9	1543.8	1726.2
32.5°	682.7	683.0	696.6	716.5	750.7	800.5	868.9	985.6	1140.9	1342.4	1556.3
35°	593.5	592.9	602.9	617.3	631.6	663.5	710.4	771.6	878.4	1066.5	1285.2
37.5°	529.5	532.3	537.2	546.2	562.1	579.8	607.9	649.0	725.1	836.3	1020.1
40°	493.6	494.8	501.7	509.2	518.5	532.3	555.4	588.6	644.2	732.9	867.2
42.5°	460.6	461.9	466.7	473.7	481.1	494.8	514.0	542.6	587.7	656.9	767.7
45°	412.4	412.4	416.7	419.9	428.0	440.4	456.1	479.8	511.0	562.3	636.0
47.5°	367.1	367.2	370.1	375.5	380.6	390.4	405.7	425.1	447.8	487.5	550.4
50°	341.1	341.8	343.6	348.0	351.1	359.9	371.8	388.6	412.4	443.0	495.5
52.5°	320.2	319.8	322.1	324.0	326.1	332.4	341.3	356.1	377.3	404.0	447.4
55°	286.2	283.6	287.4	290.5	292.4	294.9	299.9	309.2	327.3	349.8	382.4
57.5°	243.7	242.6	245.3	248.2	254.0	260.8	265.1	271.0	280.4	296.5	328.7
60°	208.6	208.6	214.3	216.1	223.1	231.8	240.5	245.6	254.9	265.5	289.3
62.5°	177.7	178.2	180.8	182.7	186.5	197.3	209.5	220.5	229.4	239.5	255.3
65°	148.7	149.9	149.9	151.2	153.7	156.2	161.2	169.9	185.6	199.9	211.8
67.5°	126.2	126.6	126.9	128.2	128.8	131.6	133.5	137.5	141.0	154.7	169.4
70°	111.2	113.1	112.4	113.7	114.3	115.6	118.1	119.9	125.6	128.7	137.5
72.5°	97.2	98.6	98.5	99.2	100.9	101.1	103.1	104.9	108.6	111.2	115.9
75°	78.8	78.1	78.8	80.0	80.6	81.2	81.2	83.7	85.6	88.1	91.2
77.5°	60.7	61.4	61.2	61.4	61.5	62.6	62.5	63.6	65.5	66.7	68.2
80°	48.8	49.3	48.8	49.3	50.0	50.6	50.0	50.6	52.5	53.7	53.7
82.5°	37.7	37.8	38.2	38.4	38.5	38.6	39.5	39.6	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.2	22.5	22.5	23.2	23.2	23.2
87.5°	13.4	13.8	13.7	13.6	13.5	13.4	13.1	13.5	12.7	13.0	12.1
90°	26.9	26.5	26.0	25.6	25.2	24.4	23.2	22.2	21.0	20.0	18.2
92.5°	26.9	26.7	26.4	26.1	25.8	25.4	24.9	24.3	23.7	23.2	22.3
95°	42.9	43.1	43.3	43.5	43.8	43.3	42.2	41.1	40.0	38.9	37.3
97.5°	57.2	57.0	56.7	56.4	56.2	55.6	54.7	53.8	52.9	52.1	48.5
100°	66.9	66.4	66.0	65.5	65.1	63.9	62.1	60.4	58.6	56.8	53.1
102.5°	71.6	71.0	70.4	69.7	69.1	67.7	65.4	63.0	60.7	58.5	89.9
105°	75.8	74.9	74.0	73.1	72.2	70.6	68.2	65.7	63.3	60.8	121.3
107.5°	78.0	77.1	76.2	75.3	74.4	75.3	77.7	80.2	82.7	85.2	157.8
110°	78.8	77.9	77.0	76.1	75.3	85.9	108.0	130.2	152.4	174.6	238.6



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.6	78.8	78.2	77.5	76.7	116.8	197.7	278.5	359.4	440.2	456.1
115°	81.8	97.8	113.7	129.6	145.6	204.9	307.5	410.1	512.7	615.4	609.8
117.5°	333.9	386.4	438.8	491.2	543.6	582.3	607.1	631.9	656.7	681.6	677.8
120°	608.4	638.3	668.2	698.1	728.1	741.7	739.0	736.4	733.7	731.0	727.1
122.5°	759.1	765.0	770.8	776.6	782.4	784.5	782.9	781.3	779.7	778.1	773.8
125°	852.7	852.1	851.4	850.7	850.0	849.0	847.4	845.9	844.3	842.8	838.5
127.5°	911.7	911.6	911.5	911.3	911.3	910.0	907.8	905.5	903.3	901.0	897.8
130°	948.4	948.7	948.9	949.1	949.3	948.2	945.8	943.4	940.9	938.5	936.0
132.5°	984.4	984.6	984.8	985.0	985.2	984.3	982.2	980.2	978.0	976.0	973.5
135°	1036.2	1036.7	1037.1	1037.5	1038.0	1037.1	1034.9	1032.7	1030.5	1028.3	1026.2
137.5°	1083.5	1084.3	1085.0	1085.7	1086.5	1085.8	1083.6	1081.4	1079.3	1077.1	1074.8
140°	1113.0	1114.1	1115.2	1116.3	1117.4	1117.0	1115.0	1113.0	1111.0	1109.1	1106.6
142.5°	1141.7	1142.8	1143.9	1145.1	1146.1	1145.8	1144.0	1142.2	1140.4	1138.6	1135.7
145°	1181.9	1182.9	1184.1	1185.1	1186.3	1186.0	1184.5	1182.9	1181.4	1179.8	1176.1
147.5°	1217.2	1218.1	1219.0	1219.9	1220.8	1220.7	1219.6	1218.5	1217.3	1216.1	1212.4
150°	1238.7	1239.7	1240.9	1242.0	1243.1	1243.0	1241.7	1240.3	1239.0	1237.7	1234.1
152.5°	1257.0	1258.5	1260.0	1261.4	1262.9	1263.0	1261.6	1260.3	1259.0	1257.6	1254.3
155°	1282.5	1284.3	1286.1	1287.8	1289.6	1289.9	1288.6	1287.2	1285.9	1284.6	1281.9
157.5°	1305.9	1307.7	1309.4	1311.1	1312.8	1313.0	1311.4	1309.9	1308.4	1306.9	1305.0
160°	1319.5	1321.0	1322.6	1324.1	1325.7	1325.8	1324.5	1323.1	1321.8	1320.5	1319.2
162.5°	1330.6	1332.5	1334.4	1336.4	1338.2	1338.5	1336.9	1335.5	1333.9	1332.4	1331.3
165°	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4	1346.7
167.5°	1358.0	1359.9	1362.0	1363.9	1366.0	1366.1	1364.6	1363.0	1361.5	1359.9	1359.3
170°	1364.3	1366.4	1368.3	1370.4	1372.3	1372.6	1371.0	1369.5	1367.9	1366.4	1365.9
172.5°	1369.1	1371.1	1373.1	1375.1	1377.1	1377.3	1375.7	1374.2	1372.6	1371.1	1370.7
175°	1373.3	1375.5	1377.8	1380.0	1382.2	1382.5	1381.0	1379.4	1377.9	1376.3	1375.9
177.5°	1375.9	1377.5	1379.1	1380.7	1382.3	1382.5	1381.2	1380.0	1378.8	1377.5	1377.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1841.1	1837.0	1833.6	1824.6	1820.1	1810.0	1808.6	1808.1	1795.1	1782.6	1779.1
5°	1904.3	1894.3	1879.3	1861.8	1843.7	1825.0	1812.5	1802.5	1777.4	1753.7	1740.0
7.5°	1968.1	1946.5	1920.7	1887.6	1859.9	1829.0	1806.0	1785.3	1749.9	1715.9	1693.0
10°	2015.5	1980.5	1946.1	1900.5	1864.9	1829.9	1797.5	1769.4	1729.3	1684.4	1652.5
12.5°	2045.0	2006.5	1959.2	1914.6	1868.4	1824.0	1780.5	1744.3	1697.4	1650.9	1613.1
15°	2084.9	2043.6	1986.2	1922.4	1863.0	1805.0	1755.0	1710.0	1648.8	1593.2	1546.9
17.5°	2117.5	2060.8	1999.0	1925.3	1856.6	1782.7	1718.4	1660.9	1592.8	1525.7	1471.2
20°	2127.9	2071.8	2000.5	1926.8	1845.6	1758.8	1689.4	1626.9	1553.8	1480.7	1418.2
22.5°	2121.5	2077.7	1998.5	1910.3	1827.1	1736.3	1657.9	1585.4	1504.3	1429.7	1357.2
25°	2077.4	2062.4	1987.4	1891.2	1796.2	1690.6	1600.0	1520.7	1428.2	1348.3	1269.5
27.5°	1974.5	2006.9	1960.4	1857.9	1752.3	1639.2	1537.3	1447.0	1351.0	1261.0	1182.6
30°	1875.6	1949.9	1929.9	1834.9	1716.9	1605.7	1491.3	1397.0	1294.5	1202.1	1124.6
32.5°	1740.1	1863.0	1882.4	1803.0	1680.9	1558.7	1438.8	1345.0	1238.0	1140.6	1065.1
35°	1524.4	1708.1	1792.4	1741.9	1619.4	1487.6	1363.8	1254.5	1147.0	1050.8	975.9
37.5°	1267.1	1517.4	1657.9	1661.5	1549.1	1412.0	1277.2	1168.7	1058.7	964.3	883.2
40°	1100.2	1371.3	1554.4	1595.1	1500.1	1352.0	1215.8	1105.2	997.8	905.3	812.2
42.5°	950.3	1220.4	1445.4	1516.0	1440.6	1293.6	1156.8	1041.2	936.8	849.3	754.2
45°	768.5	1004.6	1252.6	1378.8	1337.0	1200.8	1056.5	946.6	848.4	772.8	681.6
47.5°	648.2	814.7	1054.8	1225.4	1224.7	1100.3	958.4	853.0	762.1	691.2	617.4
50°	579.8	724.7	927.8	1121.4	1137.7	1033.4	898.4	794.1	709.1	634.8	575.4
52.5°	518.3	637.7	820.4	1006.0	1052.2	961.9	831.0	734.6	652.2	583.8	533.0
55°	438.0	530.4	669.1	842.8	912.8	849.1	732.9	642.9	576.0	518.5	474.8
57.5°	370.5	439.9	551.1	691.0	772.5	732.4	636.5	563.5	506.2	454.2	419.7
60°	328.0	384.8	479.2	596.1	686.0	657.9	576.0	507.9	459.2	414.3	381.7
62.5°	288.0	336.9	417.8	512.6	595.0	583.4	516.6	459.4	416.7	375.8	348.2
65°	231.8	267.4	330.5	404.9	471.1	476.7	428.6	389.9	351.7	319.3	294.9
67.5°	184.6	207.8	252.3	314.9	364.5	382.2	352.9	323.3	293.0	267.9	246.8
70°	155.6	174.3	206.8	257.4	303.0	321.7	304.9	281.8	255.5	234.9	216.8
72.5°	126.0	144.3	168.3	205.5	244.5	264.8	258.9	242.3	221.0	203.9	186.8
75°	95.0	100.6	116.8	141.9	172.4	190.0	194.3	185.6	168.7	155.6	145.5
77.5°	70.2	73.6	81.4	94.5	114.5	130.0	136.5	135.4	123.8	116.2	106.8
80°	56.3	58.1	61.9	67.5	82.5	98.1	102.5	102.5	94.3	91.2	81.9
82.5°	42.7	44.1	46.4	49.5	56.5	70.1	75.0	76.0	70.8	66.7	59.4
85°	24.4	23.7	25.0	26.9	28.1	31.9	39.4	40.6	39.4	34.3	32.4
87.5°	11.7	11.9	11.6	10.7	10.7	10.7	12.7	14.7	13.2	12.1	11.7
90°	16.4	14.6	12.9	10.8	8.3	5.9	3.4	1.0	3.4	5.9	8.3
92.5°	21.4	20.5	19.6	19.2	19.5	19.7	19.9	20.1	19.9	19.7	19.5
95°	35.8	34.2	32.7	35.5	42.9	50.2	57.5	64.8	57.5	50.2	42.9
97.5°	44.8	41.3	37.7	46.2	66.9	87.4	108.0	128.7	108.0	87.4	66.9
100°	49.3	45.6	41.7	55.1	85.4	115.8	146.2	176.5	146.2	115.8	85.4
102.5°	121.5	153.0	184.5	203.5	209.9	216.3	222.7	229.2	222.7	216.3	209.9
105°	181.8	242.4	302.9	329.8	323.1	316.5	309.8	303.2	309.8	316.5	323.1
107.5°	230.3	302.9	375.4	409.0	403.7	398.3	392.9	387.6	392.9	398.3	403.7
110°	302.6	366.7	430.7	460.4	455.8	451.1	446.5	441.8	446.5	451.1	455.8





TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	471.9	487.7	503.5	509.4	505.2	501.1	497.0	492.8	497.0	501.1	505.2
115°	604.3	598.8	593.2	588.6	584.7	581.0	577.2	573.5	577.2	581.0	584.7
117.5°	673.9	670.1	666.3	662.3	658.1	653.9	649.7	645.5	649.7	653.9	658.1
120°	723.1	719.1	715.1	711.4	708.1	704.7	701.5	698.1	701.5	704.7	708.1
122.5°	769.4	765.1	760.8	756.8	753.3	749.8	746.3	742.8	746.3	749.8	753.3
125°	834.3	830.1	825.9	822.3	819.5	816.6	813.7	810.8	813.7	816.6	819.5
127.5°	894.7	891.5	888.4	885.3	882.1	878.8	875.6	872.5	875.6	878.8	882.1
130°	933.6	931.2	928.7	925.8	922.2	918.7	915.1	911.6	915.1	918.7	922.2
132.5°	971.1	968.7	966.2	963.5	960.5	957.5	954.5	951.5	954.5	957.5	960.5
135°	1024.3	1022.2	1020.3	1017.5	1013.9	1010.4	1006.8	1003.3	1006.8	1010.4	1013.9
137.5°	1072.6	1070.3	1068.0	1065.7	1063.2	1060.7	1058.3	1055.7	1058.3	1060.7	1063.2
140°	1104.2	1101.7	1099.3	1097.1	1095.4	1093.6	1091.8	1090.1	1091.8	1093.6	1095.4
142.5°	1132.9	1130.2	1127.4	1125.2	1123.6	1122.0	1120.4	1118.8	1120.4	1122.0	1123.6
145°	1172.3	1168.6	1164.7	1163.0	1163.2	1163.4	1163.7	1163.8	1163.7	1163.4	1163.2
147.5°	1208.7	1204.9	1201.3	1199.8	1200.6	1201.5	1202.3	1203.1	1202.3	1201.5	1200.6
150°	1230.6	1227.0	1223.5	1222.5	1224.0	1225.6	1227.2	1228.7	1227.2	1225.6	1224.0
152.5°	1250.9	1247.5	1244.1	1243.3	1245.0	1246.8	1248.5	1250.3	1248.5	1246.8	1245.0
155°	1279.2	1276.6	1273.9	1273.6	1275.5	1277.6	1279.5	1281.6	1279.5	1277.6	1275.5
157.5°	1303.2	1301.3	1299.4	1299.3	1301.1	1302.7	1304.4	1306.1	1304.4	1302.7	1301.1
160°	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1319.2	1317.8	1316.5
162.5°	1330.1	1328.9	1327.8	1327.9	1329.3	1330.6	1331.9	1333.3	1331.9	1330.6	1329.3
165°	1346.1	1345.4	1344.8	1345.1	1346.4	1347.7	1349.1	1350.4	1349.1	1347.7	1346.4
167.5°	1358.7	1358.1	1357.5	1357.8	1359.2	1360.5	1361.8	1363.2	1361.8	1360.5	1359.2
170°	1365.5	1365.0	1364.6	1365.0	1366.4	1367.7	1369.0	1370.4	1369.0	1367.7	1366.4
172.5°	1370.2	1369.8	1369.4	1369.8	1371.1	1372.5	1373.8	1375.1	1373.8	1372.5	1371.1
175°	1375.4	1375.0	1374.5	1375.1	1376.6	1378.2	1379.7	1381.3	1379.7	1378.2	1376.6
177.5°	1377.1	1377.0	1376.8	1377.3	1378.6	1379.8	1381.0	1382.3	1381.0	1379.8	1378.6
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1772.6	1769.1	1762.6	1752.6	1746.6	1736.1	1729.1	1733.1	1734.1	1733.1	1732.1
5°	1725.0	1711.9	1693.8	1676.3	1660.0	1642.5	1632.6	1628.2	1619.4	1614.4	1611.9
7.5°	1667.4	1644.8	1619.2	1588.7	1562.8	1535.7	1521.8	1514.9	1497.1	1487.4	1478.8
10°	1624.4	1588.8	1563.2	1523.2	1498.8	1463.2	1438.8	1439.5	1415.1	1401.3	1391.4
12.5°	1577.0	1537.8	1495.2	1459.2	1425.4	1396.8	1367.3	1355.5	1329.7	1316.4	1289.4
15°	1498.2	1452.6	1407.6	1358.9	1324.5	1280.2	1237.7	1185.9	1143.9	1107.7	1097.7
17.5°	1412.3	1355.8	1310.7	1253.4	1194.6	1120.0	1070.7	1040.6	1015.4	996.3	982.0
20°	1353.2	1295.8	1247.7	1161.5	1082.1	1031.5	995.2	972.2	945.9	925.3	914.0
22.5°	1291.3	1231.3	1165.7	1069.5	1007.6	967.0	934.7	908.2	890.4	874.3	864.1
25°	1203.3	1137.7	1029.6	963.4	913.4	870.9	848.4	832.2	813.4	791.6	781.6
27.5°	1110.4	1006.0	928.4	879.1	831.4	803.8	783.6	759.4	742.6	732.7	722.4
30°	1040.9	936.5	876.0	822.2	788.5	757.8	734.1	720.4	704.1	687.2	680.4
32.5°	963.4	880.0	822.0	777.2	743.0	716.9	698.1	675.9	664.1	653.8	639.4
35°	867.2	804.0	751.0	714.8	682.2	661.0	639.1	626.0	604.8	596.1	590.4
37.5°	785.7	731.0	691.4	653.1	627.4	603.9	590.5	569.6	560.4	548.3	536.5
40°	739.7	686.0	647.9	616.6	587.9	570.4	553.5	536.7	522.9	517.3	503.0
42.5°	692.8	649.0	610.9	576.7	557.4	538.9	517.6	505.2	491.0	481.8	473.0
45°	627.9	589.1	556.7	528.6	507.3	488.0	474.2	453.6	445.5	427.4	419.9
47.5°	571.0	534.9	503.9	477.2	456.5	443.8	423.7	407.6	394.6	383.5	373.9
50°	530.4	500.4	470.4	446.7	428.0	409.9	389.2	381.1	361.1	355.5	349.8
52.5°	493.4	465.0	437.5	414.3	395.5	377.9	359.7	349.1	335.7	330.0	325.9
55°	441.7	414.3	388.0	367.4	348.6	330.5	319.3	306.1	299.9	295.5	290.5
57.5°	389.7	365.0	344.9	324.0	305.2	290.7	277.8	269.9	263.4	257.6	251.7
60°	356.8	333.0	314.9	295.5	276.1	264.2	254.3	244.9	237.4	228.7	226.2
62.5°	321.7	301.0	284.4	265.5	248.7	237.8	228.3	219.4	210.4	197.7	194.2
65°	273.6	257.4	239.9	224.3	209.3	198.7	184.9	175.0	171.2	169.9	169.3
67.5°	230.2	214.8	199.8	183.8	170.2	160.3	153.4	151.8	149.2	148.5	146.7
70°	201.2	186.8	171.8	156.8	143.7	141.9	139.3	136.8	133.7	132.5	131.2
72.5°	175.2	160.3	145.3	133.3	127.7	125.3	122.9	120.3	118.2	117.0	116.2
75°	134.4	120.6	110.6	106.2	103.1	101.2	97.4	95.6	94.3	92.5	91.8
77.5°	96.7	88.9	84.4	81.6	78.4	76.3	74.2	72.3	71.0	70.6	69.6
80°	73.7	70.0	66.9	63.1	61.9	59.4	58.7	56.8	57.5	55.6	55.6
82.5°	57.2	52.5	49.9	48.1	46.9	44.8	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.1	26.9	25.6	25.6	23.7	24.4	23.7	23.7	22.5	21.9
87.5°	11.7	11.6	10.9	11.3	11.7	11.5	11.7	11.4	11.7	11.9	11.5
90°	10.8	12.9	14.6	16.4	18.2	20.0	21.0	22.2	23.2	24.4	25.2
92.5°	19.2	19.6	20.5	21.4	22.3	23.2	23.7	24.3	24.9	25.4	25.8
95°	35.5	32.7	34.2	35.8	37.3	38.9	40.0	41.1	42.2	43.3	43.8
97.5°	46.2	37.7	41.3	44.8	48.5	52.1	52.9	53.8	54.7	55.6	56.2
100°	55.1	41.7	45.6	49.3	53.1	56.8	58.6	60.4	62.1	63.9	65.1
102.5°	203.5	184.5	153.0	121.5	89.9	58.5	60.7	63.0	65.4	67.7	69.1
105°	329.8	302.9	242.4	181.8	121.3	60.8	63.3	65.7	68.2	70.6	72.2
107.5°	409.0	375.4	302.9	230.3	157.8	85.2	82.7	80.2	77.7	75.3	74.4
110°	460.4	430.7	366.7	302.6	238.6	174.6	152.4	130.2	108.0	85.9	75.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	509.4	503.5	487.7	471.9	456.1	440.2	359.4	278.5	197.7	116.8	76.7
115°	588.6	593.2	598.8	604.3	609.8	615.4	512.7	410.1	307.5	204.9	145.6
117.5°	662.3	666.3	670.1	673.9	677.8	681.6	656.7	631.9	607.1	582.3	543.6
120°	711.4	715.1	719.1	723.1	727.1	731.0	733.7	736.4	739.0	741.7	728.1
122.5°	756.8	760.8	765.1	769.4	773.8	778.1	779.7	781.3	782.9	784.5	782.4
125°	822.3	825.9	830.1	834.3	838.5	842.8	844.3	845.9	847.4	849.0	850.0
127.5°	885.3	888.4	891.5	894.7	897.8	901.0	903.3	905.5	907.8	910.0	911.3
130°	925.8	928.7	931.2	933.6	936.0	938.5	940.9	943.4	945.8	948.2	949.3
132.5°	963.5	966.2	968.7	971.1	973.5	976.0	978.0	980.2	982.2	984.3	985.2
135°	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5	1032.7	1034.9	1037.1	1038.0
137.5°	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3	1081.4	1083.6	1085.8	1086.5
140°	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0	1113.0	1115.0	1117.0	1117.4
142.5°	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4	1142.2	1144.0	1145.8	1146.1
145°	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4	1182.9	1184.5	1186.0	1186.3
147.5°	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3	1218.5	1219.6	1220.7	1220.8
150°	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0	1240.3	1241.7	1243.0	1243.1
152.5°	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0	1260.3	1261.6	1263.0	1262.9
155°	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9	1287.2	1288.6	1289.9	1289.6
157.5°	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4	1309.9	1311.4	1313.0	1312.8
160°	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8	1323.1	1324.5	1325.8	1325.7
162.5°	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9	1335.5	1336.9	1338.5	1338.2
165°	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6
167.5°	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5	1363.0	1364.6	1366.1	1366.0
170°	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9	1369.5	1371.0	1372.6	1372.3
172.5°	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6	1374.2	1375.7	1377.3	1377.1
175°	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9	1379.4	1381.0	1382.5	1382.2
177.5°	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8	1380.0	1381.2	1382.5	1382.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1726.6	1727.6	1726.2	1727.1	1726.2	1727.6	1726.6	1732.1	1733.1	1734.1	1733.1
5°	1608.7	1601.2	1600.0	1598.1	1600.0	1601.2	1608.7	1611.9	1614.4	1619.4	1628.2
7.5°	1468.1	1467.0	1463.9	1459.5	1463.9	1467.0	1468.1	1478.8	1487.4	1497.1	1514.9
10°	1377.6	1374.5	1373.9	1369.5	1373.9	1374.5	1377.6	1391.4	1401.3	1415.1	1439.5
12.5°	1271.6	1251.6	1249.4	1238.5	1249.4	1251.6	1271.6	1289.4	1316.4	1329.7	1355.5
15°	1082.7	1079.0	1066.5	1058.3	1066.5	1079.0	1082.7	1097.7	1107.7	1143.9	1185.9
17.5°	974.8	962.5	958.6	956.9	958.6	962.5	974.8	982.0	996.3	1015.4	1040.6
20°	905.3	894.1	892.2	891.0	892.2	894.1	905.3	914.0	925.3	945.9	972.2
22.5°	857.3	845.5	840.7	836.9	840.7	845.5	857.3	864.1	874.3	890.4	908.2
25°	775.3	770.9	768.5	767.2	768.5	770.9	775.3	781.6	791.6	813.4	832.2
27.5°	711.3	701.6	699.8	696.5	699.8	701.6	711.3	722.4	732.7	742.6	759.4
30°	674.7	671.6	667.2	663.5	667.2	671.6	674.7	680.4	687.2	704.1	720.4
32.5°	631.8	629.2	625.3	623.5	625.3	629.2	631.8	639.4	653.8	664.1	675.9
35°	584.2	575.4	571.7	566.1	571.7	575.4	584.2	590.4	596.1	604.8	626.0
37.5°	533.8	529.2	523.9	525.8	523.9	529.2	533.8	536.5	548.3	560.4	569.6
40°	494.8	491.7	490.5	489.8	490.5	491.7	494.8	503.0	517.3	522.9	536.7
42.5°	463.8	455.2	451.9	451.8	451.9	455.2	463.8	473.0	481.8	491.0	505.2
45°	416.7	408.6	403.0	403.6	403.0	408.6	416.7	419.9	427.4	445.5	453.6
47.5°	368.5	368.3	364.8	365.8	364.8	368.3	368.5	373.9	383.5	394.6	407.6
50°	345.5	341.8	339.2	339.9	339.2	341.8	345.5	349.8	355.5	361.1	381.1
52.5°	323.5	320.2	318.3	320.9	318.3	320.2	323.5	325.9	330.0	335.7	349.1
55°	287.4	283.6	283.0	282.4	283.0	283.6	287.4	290.5	295.5	299.9	306.1
57.5°	247.0	244.5	240.8	239.1	240.8	244.5	247.0	251.7	257.6	263.4	269.9
60°	218.0	213.0	206.8	206.2	206.8	213.0	218.0	226.2	228.7	237.4	244.9
62.5°	191.5	190.5	189.3	189.1	189.3	190.5	191.5	194.2	197.7	210.4	219.4
65°	168.0	167.5	168.0	168.7	168.0	167.5	168.0	169.3	169.9	171.2	175.0
67.5°	146.4	145.3	144.2	144.7	144.2	145.3	146.4	146.7	148.5	149.2	151.8
70°	130.0	129.3	128.7	128.7	128.7	129.3	130.0	131.2	132.5	133.7	136.8
72.5°	114.0	113.8	113.2	112.7	113.2	113.8	114.0	116.2	117.0	118.2	120.3
75°	91.2	89.9	89.9	89.9	89.9	89.9	91.2	91.8	92.5	94.3	95.6
77.5°	69.5	68.8	68.2	67.8	68.2	68.8	69.5	69.6	70.6	71.0	72.3
80°	55.0	54.4	53.7	53.7	53.7	54.4	55.0	55.6	55.6	57.5	56.8
82.5°	42.0	41.3	41.3	40.8	41.3	41.3	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.2	22.5	23.7	22.5	23.2	22.5	21.9	22.5	23.7	23.7
87.5°	11.6	11.2	11.8	11.4	11.8	11.2	11.6	11.5	11.9	11.7	11.4
90°	25.6	26.0	26.5	26.9	26.5	26.0	25.6	25.2	24.4	23.2	22.2
92.5°	26.1	26.4	26.7	26.9	26.7	26.4	26.1	25.8	25.4	24.9	24.3
95°	43.5	43.3	43.1	42.9	43.1	43.3	43.5	43.8	43.3	42.2	41.1
97.5°	56.4	56.7	57.0	57.2	57.0	56.7	56.4	56.2	55.6	54.7	53.8
100°	65.5	66.0	66.4	66.9	66.4	66.0	65.5	65.1	63.9	62.1	60.4
102.5°	69.7	70.4	71.0	71.6	71.0	70.4	69.7	69.1	67.7	65.4	63.0
105°	73.1	74.0	74.9	75.8	74.9	74.0	73.1	72.2	70.6	68.2	65.7
107.5°	75.3	76.2	77.1	78.0	77.1	76.2	75.3	74.4	75.3	77.7	80.2
110°	76.1	77.0	77.9	78.8	77.9	77.0	76.1	75.3	85.9	108.0	130.2



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	77.5	78.2	78.8	79.6	78.8	78.2	77.5	76.7	116.8	197.7	278.5
115°	129.6	113.7	97.8	81.8	97.8	113.7	129.6	145.6	204.9	307.5	410.1
117.5°	491.2	438.8	386.4	333.9	386.4	438.8	491.2	543.6	582.3	607.1	631.9
120°	698.1	668.2	638.3	608.4	638.3	668.2	698.1	728.1	741.7	739.0	736.4
122.5°	776.6	770.8	765.0	759.1	765.0	770.8	776.6	782.4	784.5	782.9	781.3
125°	850.7	851.4	852.1	852.7	852.1	851.4	850.7	850.0	849.0	847.4	845.9
127.5°	911.3	911.5	911.6	911.7	911.6	911.5	911.3	911.3	910.0	907.8	905.5
130°	949.1	948.9	948.7	948.4	948.7	948.9	949.1	949.3	948.2	945.8	943.4
132.5°	985.0	984.8	984.6	984.4	984.6	984.8	985.0	985.2	984.3	982.2	980.2
135°	1037.5	1037.1	1036.7	1036.2	1036.7	1037.1	1037.5	1038.0	1037.1	1034.9	1032.7
137.5°	1085.7	1085.0	1084.3	1083.5	1084.3	1085.0	1085.7	1086.5	1085.8	1083.6	1081.4
140°	1116.3	1115.2	1114.1	1113.0	1114.1	1115.2	1116.3	1117.4	1117.0	1115.0	1113.0
142.5°	1145.1	1143.9	1142.8	1141.7	1142.8	1143.9	1145.1	1146.1	1145.8	1144.0	1142.2
145°	1185.1	1184.1	1182.9	1181.9	1182.9	1184.1	1185.1	1186.3	1186.0	1184.5	1182.9
147.5°	1219.9	1219.0	1218.1	1217.2	1218.1	1219.0	1219.9	1220.8	1220.7	1219.6	1218.5
150°	1242.0	1240.9	1239.7	1238.7	1239.7	1240.9	1242.0	1243.1	1243.0	1241.7	1240.3
152.5°	1261.4	1260.0	1258.5	1257.0	1258.5	1260.0	1261.4	1262.9	1263.0	1261.6	1260.3
155°	1287.8	1286.1	1284.3	1282.5	1284.3	1286.1	1287.8	1289.6	1289.9	1288.6	1287.2
157.5°	1311.1	1309.4	1307.7	1305.9	1307.7	1309.4	1311.1	1312.8	1313.0	1311.4	1309.9
160°	1324.1	1322.6	1321.0	1319.5	1321.0	1322.6	1324.1	1325.7	1325.8	1324.5	1323.1
162.5°	1336.4	1334.4	1332.5	1330.6	1332.5	1334.4	1336.4	1338.2	1338.5	1336.9	1335.5
165°	1352.0	1350.5	1348.9	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5
167.5°	1363.9	1362.0	1359.9	1358.0	1359.9	1362.0	1363.9	1366.0	1366.1	1364.6	1363.0
170°	1370.4	1368.3	1366.4	1364.3	1366.4	1368.3	1370.4	1372.3	1372.6	1371.0	1369.5
172.5°	1375.1	1373.1	1371.1	1369.1	1371.1	1373.1	1375.1	1377.1	1377.3	1375.7	1374.2
175°	1380.0	1377.8	1375.5	1373.3	1375.5	1377.8	1380.0	1382.2	1382.5	1381.0	1379.4
177.5°	1380.7	1379.1	1377.5	1375.9	1377.5	1379.1	1380.7	1382.3	1382.5	1381.2	1380.0
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1729.1	1736.1	1746.6	1752.6	1762.6	1769.1	1772.6	1779.1	1782.6	1795.1	1808.1
5°	1632.6	1642.5	1660.0	1676.3	1693.8	1711.9	1725.0	1740.0	1753.7	1777.4	1802.5
7.5°	1521.8	1535.7	1562.8	1588.7	1619.2	1644.8	1667.4	1693.0	1715.9	1749.9	1785.3
10°	1438.8	1463.2	1498.8	1523.2	1563.2	1588.8	1624.4	1652.5	1684.4	1729.3	1769.4
12.5°	1367.3	1396.8	1425.4	1459.2	1495.2	1537.8	1577.0	1613.1	1650.9	1697.4	1744.3
15°	1237.7	1280.2	1324.5	1358.9	1407.6	1452.6	1498.2	1546.9	1593.2	1648.8	1710.0
17.5°	1070.7	1120.0	1194.6	1253.4	1310.7	1355.8	1412.3	1471.2	1525.7	1592.8	1660.9
20°	995.2	1031.5	1082.1	1161.5	1247.7	1295.8	1353.2	1418.2	1480.7	1553.8	1626.9
22.5°	934.7	967.0	1007.6	1069.5	1165.7	1231.3	1291.3	1357.2	1429.7	1504.3	1585.4
25°	848.4	870.9	913.4	963.4	1029.6	1137.7	1203.3	1269.5	1348.3	1428.2	1520.7
27.5°	783.6	803.8	831.4	879.1	928.4	1006.0	1110.4	1182.6	1261.0	1351.0	1447.0
30°	734.1	757.8	788.5	822.2	876.0	936.5	1040.9	1124.6	1202.1	1294.5	1397.0
32.5°	698.1	716.9	743.0	777.2	822.0	880.0	963.4	1065.1	1140.6	1238.0	1345.0
35°	639.1	661.0	682.2	714.8	751.0	804.0	867.2	975.9	1050.8	1147.0	1254.5
37.5°	590.5	603.9	627.4	653.1	691.4	731.0	785.7	883.2	964.3	1058.7	1168.7
40°	553.5	570.4	587.9	616.6	647.9	686.0	739.7	812.2	905.3	997.8	1105.2
42.5°	517.6	538.9	557.4	576.7	610.9	649.0	692.8	754.2	849.3	936.8	1041.2
45°	474.2	488.0	507.3	528.6	556.7	589.1	627.9	681.6	772.8	848.4	946.6
47.5°	423.7	443.8	456.5	477.2	503.9	534.9	571.0	617.4	691.2	762.1	853.0
50°	389.2	409.9	428.0	446.7	470.4	500.4	530.4	575.4	634.8	709.1	794.1
52.5°	359.7	377.9	395.5	414.3	437.5	465.0	493.4	533.0	583.8	652.2	734.6
55°	319.3	330.5	348.6	367.4	388.0	414.3	441.7	474.8	518.5	576.0	642.9
57.5°	277.8	290.7	305.2	324.0	344.9	365.0	389.7	419.7	454.2	506.2	563.5
60°	254.3	264.2	276.1	295.5	314.9	333.0	356.8	381.7	414.3	459.2	507.9
62.5°	228.3	237.8	248.7	265.5	284.4	301.0	321.7	348.2	375.8	416.7	459.4
65°	184.9	198.7	209.3	224.3	239.9	257.4	273.6	294.9	319.3	351.7	389.9
67.5°	153.4	160.3	170.2	183.8	199.8	214.8	230.2	246.8	267.9	293.0	323.3
70°	139.3	141.9	143.7	156.8	171.8	186.8	201.2	216.8	234.9	255.5	281.8
72.5°	122.9	125.3	127.7	133.3	145.3	160.3	175.2	186.8	203.9	221.0	242.3
75°	97.4	101.2	103.1	106.2	110.6	120.6	134.4	145.5	155.6	168.7	185.6
77.5°	74.2	76.3	78.4	81.6	84.4	88.9	96.7	106.8	116.2	123.8	135.4
80°	58.7	59.4	61.9	63.1	66.9	70.0	73.7	81.9	91.2	94.3	102.5
82.5°	44.3	44.8	46.9	48.1	49.9	52.5	57.2	59.4	66.7	70.8	76.0
85°	24.4	23.7	25.6	25.6	26.9	28.1	29.4	32.4	34.3	39.4	40.6
87.5°	11.7	11.5	11.7	11.3	10.9	11.6	11.7	11.7	12.1	13.2	14.7
90°	21.0	20.0	18.2	16.4	14.6	12.9	10.8	8.3	5.9	3.4	1.0
92.5°	23.7	23.2	22.3	21.4	20.5	19.6	19.2	19.5	19.7	19.9	20.1
95°	40.0	38.9	37.3	35.8	34.2	32.7	35.5	42.9	50.2	57.5	64.8
97.5°	52.9	52.1	48.5	44.8	41.3	37.7	46.2	66.9	87.4	108.0	128.7
100°	58.6	56.8	53.1	49.3	45.6	41.7	55.1	85.4	115.8	146.2	176.5
102.5°	60.7	58.5	89.9	121.5	153.0	184.5	203.5	209.9	216.3	222.7	229.2
105°	63.3	60.8	121.3	181.8	242.4	302.9	329.8	323.1	316.5	309.8	303.2
107.5°	82.7	85.2	157.8	230.3	302.9	375.4	409.0	403.7	398.3	392.9	387.6
110°	152.4	174.6	238.6	302.6	366.7	430.7	460.4	455.8	451.1	446.5	441.8



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	359.4	440.2	456.1	471.9	487.7	503.5	509.4	505.2	501.1	497.0	492.8
115°	512.7	615.4	609.8	604.3	598.8	593.2	588.6	584.7	581.0	577.2	573.5
117.5°	656.7	681.6	677.8	673.9	670.1	666.3	662.3	658.1	653.9	649.7	645.5
120°	733.7	731.0	727.1	723.1	719.1	715.1	711.4	708.1	704.7	701.5	698.1
122.5°	779.7	778.1	773.8	769.4	765.1	760.8	756.8	753.3	749.8	746.3	742.8
125°	844.3	842.8	838.5	834.3	830.1	825.9	822.3	819.5	816.6	813.7	810.8
127.5°	903.3	901.0	897.8	894.7	891.5	888.4	885.3	882.1	878.8	875.6	872.5
130°	940.9	938.5	936.0	933.6	931.2	928.7	925.8	922.2	918.7	915.1	911.6
132.5°	978.0	976.0	973.5	971.1	968.7	966.2	963.5	960.5	957.5	954.5	951.5
135°	1030.5	1028.3	1026.2	1024.3	1022.2	1020.3	1017.5	1013.9	1010.4	1006.8	1003.3
137.5°	1079.3	1077.1	1074.8	1072.6	1070.3	1068.0	1065.7	1063.2	1060.7	1058.3	1055.7
140°	1111.0	1109.1	1106.6	1104.2	1101.7	1099.3	1097.1	1095.4	1093.6	1091.8	1090.1
142.5°	1140.4	1138.6	1135.7	1132.9	1130.2	1127.4	1125.2	1123.6	1122.0	1120.4	1118.8
145°	1181.4	1179.8	1176.1	1172.3	1168.6	1164.7	1163.0	1163.2	1163.4	1163.7	1163.8
147.5°	1217.3	1216.1	1212.4	1208.7	1204.9	1201.3	1199.8	1200.6	1201.5	1202.3	1203.1
150°	1239.0	1237.7	1234.1	1230.6	1227.0	1223.5	1222.5	1224.0	1225.6	1227.2	1228.7
152.5°	1259.0	1257.6	1254.3	1250.9	1247.5	1244.1	1243.3	1245.0	1246.8	1248.5	1250.3
155°	1285.9	1284.6	1281.9	1279.2	1276.6	1273.9	1273.6	1275.5	1277.6	1279.5	1281.6
157.5°	1308.4	1306.9	1305.0	1303.2	1301.3	1299.4	1299.3	1301.1	1302.7	1304.4	1306.1
160°	1321.8	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5
162.5°	1333.9	1332.4	1331.3	1330.1	1328.9	1327.8	1327.9	1329.3	1330.6	1331.9	1333.3
165°	1348.9	1347.4	1346.7	1346.1	1345.4	1344.8	1345.1	1346.4	1347.7	1349.1	1350.4
167.5°	1361.5	1359.9	1359.3	1358.7	1358.1	1357.5	1357.8	1359.2	1360.5	1361.8	1363.2
170°	1367.9	1366.4	1365.9	1365.5	1365.0	1364.6	1365.0	1366.4	1367.7	1369.0	1370.4
172.5°	1372.6	1371.1	1370.7	1370.2	1369.8	1369.4	1369.8	1371.1	1372.5	1373.8	1375.1
175°	1377.9	1376.3	1375.9	1375.4	1375.0	1374.5	1375.1	1376.6	1378.2	1379.7	1381.3
177.5°	1378.8	1377.5	1377.3	1377.1	1377.0	1376.8	1377.3	1378.6	1379.8	1381.0	1382.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1808.6	1810.0	1820.1	1824.6	1833.6	1837.0	1841.1	1840.0	1840.0	1842.1	1856.0
5°	1812.5	1825.0	1843.7	1861.8	1879.3	1894.3	1904.3	1914.3	1918.1	1936.2	1952.4
7.5°	1806.0	1829.0	1859.9	1887.6	1920.7	1946.5	1968.1	1987.4	2000.7	2027.0	2054.0
10°	1797.5	1829.9	1864.9	1900.5	1946.1	1980.5	2015.5	2042.4	2051.1	2090.5	2113.0
12.5°	1780.5	1824.0	1868.4	1914.6	1959.2	2006.5	2045.0	2071.8	2102.6	2138.0	2179.5
15°	1755.0	1805.0	1863.0	1922.4	1986.2	2043.6	2084.9	2131.7	2165.4	2204.2	2240.4
17.5°	1718.4	1782.7	1856.6	1925.3	1999.0	2060.8	2117.5	2162.4	2186.2	2208.3	2213.7
20°	1689.4	1758.8	1845.6	1926.8	2000.5	2071.8	2127.9	2165.4	2171.7	2172.3	2139.2
22.5°	1657.9	1736.3	1827.1	1910.3	1998.5	2077.7	2121.5	2137.5	2112.7	2070.4	2006.3
25°	1600.0	1690.6	1796.2	1891.2	1987.4	2062.4	2077.4	2049.3	1962.4	1871.2	1755.6
27.5°	1537.3	1639.2	1752.3	1857.9	1960.4	2006.9	1974.5	1873.2	1716.8	1580.8	1416.0
30°	1491.3	1605.7	1716.9	1834.9	1929.9	1949.9	1875.6	1726.2	1543.8	1338.9	1174.6
32.5°	1438.8	1558.7	1680.9	1803.0	1882.4	1863.0	1740.1	1556.3	1342.4	1140.9	985.6
35°	1363.8	1487.6	1619.4	1741.9	1792.4	1708.1	1524.4	1285.2	1066.5	878.4	771.6
37.5°	1277.2	1412.0	1549.1	1661.5	1657.9	1517.4	1267.1	1020.1	836.3	725.1	649.0
40°	1215.8	1352.0	1500.1	1595.1	1554.4	1371.3	1100.2	867.2	732.9	644.2	588.6
42.5°	1156.8	1293.6	1440.6	1516.0	1445.4	1220.4	950.3	767.7	656.9	587.7	542.6
45°	1056.5	1200.8	1337.0	1378.8	1252.6	1004.6	768.5	636.0	562.3	511.0	479.8
47.5°	958.4	1100.3	1224.7	1225.4	1054.8	814.7	648.2	550.4	487.5	447.8	425.1
50°	898.4	1033.4	1137.7	1121.4	927.8	724.7	579.8	495.5	443.0	412.4	388.6
52.5°	831.0	961.9	1052.2	1006.0	820.4	637.7	518.3	447.4	404.0	377.3	356.1
55°	732.9	849.1	912.8	842.8	669.1	530.4	438.0	382.4	349.8	327.3	309.2
57.5°	636.5	732.4	772.5	691.0	551.1	439.9	370.5	328.7	296.5	280.4	271.0
60°	576.0	657.9	686.0	596.1	479.2	384.8	328.0	289.3	265.5	254.9	245.6
62.5°	516.6	583.4	595.0	512.6	417.8	336.9	288.0	255.3	239.5	229.4	220.5
65°	428.6	476.7	471.1	404.9	330.5	267.4	231.8	211.8	199.9	185.6	169.9
67.5°	352.9	382.2	364.5	314.9	252.3	207.8	184.6	169.4	154.7	141.0	137.5
70°	304.9	321.7	303.0	257.4	206.8	174.3	155.6	137.5	128.7	125.6	119.9
72.5°	258.9	264.8	244.5	205.5	168.3	144.3	126.0	115.9	111.2	108.6	104.9
75°	194.3	190.0	172.4	141.9	116.8	100.6	95.0	91.2	88.1	85.6	83.7
77.5°	136.5	130.0	114.5	94.5	81.4	73.6	70.2	68.2	66.7	65.5	63.6
80°	102.5	98.1	82.5	67.5	61.9	58.1	56.3	53.7	53.7	52.5	50.6
82.5°	75.0	70.1	56.5	49.5	46.4	44.1	42.7	41.3	40.8	41.0	39.6
85°	39.4	31.9	28.1	26.9	25.0	23.7	24.4	23.2	23.2	23.2	22.5
87.5°	12.7	10.7	10.7	10.7	11.6	11.9	11.7	12.1	13.0	12.7	13.5
90°	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0	22.2
92.5°	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7	24.3
95°	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0	41.1
97.5°	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9	53.8
100°	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6	60.4
102.5°	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7	63.0
105°	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3	65.7
107.5°	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7	80.2
110°	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4	130.2





TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4	278.5
115°	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7	410.1
117.5°	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7	631.9
120°	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7	736.4
122.5°	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7	781.3
125°	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3	845.9
127.5°	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3	905.5
130°	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9	943.4
132.5°	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0	980.2
135°	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5	1032.7
137.5°	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3	1081.4
140°	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0	1113.0
142.5°	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4	1142.2
145°	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4	1182.9
147.5°	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3	1218.5
150°	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0	1240.3
152.5°	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0	1260.3
155°	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9	1287.2
157.5°	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4	1309.9
160°	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8	1323.1
162.5°	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9	1335.5
165°	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9	1350.5
167.5°	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5	1363.0
170°	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9	1369.5
172.5°	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6	1374.2
175°	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9	1379.4
177.5°	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8	1380.0
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1861.1	1867.5	1870.5	1870.5	1874.0	1872.6	1871.0
5°	1968.1	1979.9	1982.4	1993.7	2001.7	1999.3	2000.5
7.5°	2074.4	2093.4	2112.4	2121.0	2122.3	2127.4	2129.2
10°	2139.8	2155.5	2184.8	2180.4	2202.3	2214.8	2194.2
12.5°	2202.8	2223.9	2244.3	2249.9	2262.3	2266.3	2258.1
15°	2259.8	2271.0	2272.3	2269.1	2272.9	2269.8	2257.9
17.5°	2206.5	2188.3	2151.3	2133.8	2119.9	2099.5	2091.2
20°	2118.6	2064.8	2002.4	1977.4	1948.0	1890.5	1904.3
22.5°	1928.7	1867.4	1805.0	1732.0	1697.1	1642.7	1639.4
25°	1633.1	1527.5	1411.4	1330.2	1282.6	1228.3	1204.5
27.5°	1269.7	1136.9	1041.6	993.4	949.5	906.4	904.7
30°	1030.9	930.9	857.2	816.0	789.0	770.9	774.7
32.5°	868.9	800.5	750.7	716.5	696.6	683.0	682.7
35°	710.4	663.5	631.6	617.3	602.9	592.9	593.5
37.5°	607.9	579.8	562.1	546.2	537.2	532.3	529.5
40°	555.4	532.3	518.5	509.2	501.7	494.8	493.6
42.5°	514.0	494.8	481.1	473.7	466.7	461.9	460.6
45°	456.1	440.4	428.0	419.9	416.7	412.4	412.4
47.5°	405.7	390.4	380.6	375.5	370.1	367.2	367.1
50°	371.8	359.9	351.1	348.0	343.6	341.8	341.1
52.5°	341.3	332.4	326.1	324.0	322.1	319.8	320.2
55°	299.9	294.9	292.4	290.5	287.4	283.6	286.2
57.5°	265.1	260.8	254.0	248.2	245.3	242.6	243.7
60°	240.5	231.8	223.1	216.1	214.3	208.6	208.6
62.5°	209.5	197.3	186.5	182.7	180.8	178.2	177.7
65°	161.2	156.2	153.7	151.2	149.9	149.9	148.7
67.5°	133.5	131.6	128.8	128.2	126.9	126.6	126.2
70°	118.1	115.6	114.3	113.7	112.4	113.1	111.2
72.5°	103.1	101.1	100.9	99.2	98.5	98.6	97.2
75°	81.2	81.2	80.6	80.0	78.8	78.1	78.8
77.5°	62.5	62.6	61.5	61.4	61.2	61.4	60.7
80°	50.0	50.6	50.0	49.3	48.8	49.3	48.8
82.5°	39.5	38.6	38.5	38.4	38.2	37.8	37.7
85°	22.5	23.2	22.5	21.9	21.9	21.9	22.5
87.5°	13.1	13.4	13.5	13.6	13.7	13.8	13.4
90°	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	108.0	85.9	75.3	76.1	77.0	77.9	78.8



TEST NUMBER: P331857-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)