

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331859-930

Luminaire Tested: **S122RDIW-S1005D1240U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331859-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D1240U930-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 6882.2 lumens  
Efficiency: N/A  
Efficacy: 90.3 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: General Diffuse


Input Watts (W): 76.2  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	105	105	105	105	96	96	96	96	79	79	79	63	63	63	48	48	48	41				
1	96	92	88	85	88	84	81	78	69	67	65	56	54	53	43	42	41	36				
2	88	81	75	70	80	74	69	65	61	58	55	49	47	45	38	37	35	30				
3	80	71	64	59	73	65	59	55	54	50	46	44	41	38	34	32	31	26				
4	74	63	56	50	67	58	52	47	48	44	40	39	36	33	31	29	27	23				
5	68	57	49	43	62	52	45	40	44	38	35	36	32	29	28	26	24	20				
6	63	51	43	37	57	47	40	35	39	34	30	32	28	26	26	23	21	18				
7	58	46	38	33	53	42	36	31	36	31	27	29	26	23	24	21	19	16				
8	54	42	34	29	49	39	32	27	33	28	24	27	23	20	22	19	17	14				
9	50	38	31	26	46	35	29	25	30	25	21	25	21	18	20	17	15	13				
10	47	35	28	23	43	33	26	22	28	23	19	23	19	17	19	16	14	12				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	129.2	1.9
10°-20°	354.8	5.2
20°-30°	498.3	7.2
30°-40°	543.4	7.9
40°-50°	499.6	7.3
50°-60°	392.4	5.7
60°-70°	255.8	3.7
70°-80°	131.9	1.9
80°-90°	37.6	0.5
90°-100°	46.0	0.7
100°-110°	168.6	2.4
110°-120°	450.7	6.5
120°-130°	744.0	10.8
130°-140°	791.2	11.5
140°-150°	735.4	10.7
150°-160°	591.2	8.6
160°-170°	381.0	5.5
170°-180°	131.1	1.9
0°-30°	982.4	14.3
0°-40°	1525.7	22.2
0°-60°	2417.7	35.1
0°-90°	2843.1	41.3
90°-120°	665.3	9.7
90°-150°	2935.8	42.7
90°-180°	4039.0	58.7
0°-180°	6882.2	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	1	12	20	25	27	5
95°	65	34	39	44	43	79
105°	303	316	61	71	76	324
115°	574	591	615	175	82	564
125°	811	824	843	850	853	723
135°	1003	1019	1028	1038	1036	775
145°	1164	1164	1180	1186	1182	728
155°	1282	1274	1285	1290	1282	590
165°	1350	1345	1347	1354	1347	381
175°	1381	1375	1376	1382	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.2	14.9	13.6	12.3	11.0	10.6	10.9	11.3	11.7	12.0	12.0
90°	1.0	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0
92.5°	20.1	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7
95°	64.8	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0
97.5°	128.7	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9
100°	176.5	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6
102.5°	229.2	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7
105°	303.2	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3
107.5°	387.6	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7
110°	441.8	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4



TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	492.8	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4
115°	573.5	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7
117.5°	645.5	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7
120°	698.1	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7
122.5°	742.8	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7
125°	810.8	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3
127.5°	872.5	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3
130°	911.6	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9
132.5°	951.5	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0
135°	1003.3	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5
137.5°	1055.7	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3
140°	1090.1	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0
142.5°	1118.8	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4
145°	1163.8	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4
147.5°	1203.1	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3
150°	1228.7	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0
152.5°	1250.3	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0
155°	1281.6	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9
157.5°	1306.1	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4
160°	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8
162.5°	1333.3	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9
165°	1350.4	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9
167.5°	1363.2	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5
170°	1370.4	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9
172.5°	1375.1	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6
175°	1381.3	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9
177.5°	1382.3	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	12.0	12.0	12.0	12.1	12.1	12.2	12.3	12.4
90°	22.2	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.3	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	41.1	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	53.8	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	60.4	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	63.0	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	65.7	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	80.2	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	130.2	108.0	85.9	75.3	76.1	77.0	77.9	78.8





TEST NUMBER: P331859-930

CATALOG NUMBER: S122RDIW-S1005D1240U930-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	278.5	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	410.1	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	631.9	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	736.4	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	781.3	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	845.9	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	905.5	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	943.4	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	980.2	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1032.7	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1081.4	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1113.0	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1142.2	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1182.9	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1218.5	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1240.3	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1260.3	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1287.2	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1309.9	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1323.1	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1335.5	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1363.0	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1369.5	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1374.2	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1379.4	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1380.0	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)