

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331779-935

Luminaire Tested: **S122RDIW-S290D1240U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331779-935  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D1240U935-4F0-1E-UDD-F  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED  
HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**

Lumens per Lamp: N/A  
Luminaire Lumens: 5158.1 lumens  
Efficiency: N/A  
Efficacy: 110.7 lumens/watt  
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16  
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')  
CIE Type: Semi-Indirect


Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (A<sub>in</sub>): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

### Luminous Intensity Polar Plot





TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	99	99	99	99	87	87	87	87	65	65	65	45	45	45	26	26	26	17
1	91	87	83	80	80	76	73	71	57	55	53	39	38	37	23	23	22	15
2	83	76	70	65	72	67	62	58	50	47	44	35	33	31	21	20	19	13
3	75	67	60	54	66	59	53	49	44	41	37	31	29	27	18	17	16	11
4	69	59	52	46	60	52	46	41	39	35	32	28	25	23	17	15	14	10
5	63	52	45	39	55	46	40	35	35	31	27	25	22	20	15	13	12	8
6	58	47	39	34	51	42	35	30	32	27	24	22	19	17	14	12	11	7
7	54	42	35	29	47	37	31	27	29	24	21	20	17	15	12	11	10	7
8	50	38	31	26	44	34	28	23	26	21	18	18	16	13	11	10	9	6
9	46	35	28	23	40	31	25	21	24	19	16	17	14	12	10	9	8	5
10	43	32	25	20	38	28	22	18	22	17	15	15	13	11	10	8	7	5

**AVERAGE LUMINANCE (cd/sqm):**

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	40.5	0.8
10°-20°	111.1	2.2
20°-30°	156.0	3.0
30°-40°	170.1	3.3
40°-50°	156.4	3.0
50°-60°	122.8	2.4
60°-70°	80.1	1.6
70°-80°	41.3	0.8
80°-90°	14.3	0.3
90°-100°	48.6	0.9
100°-110°	178.1	3.5
110°-120°	476.0	9.2
120°-130°	785.7	15.2
130°-140°	835.5	16.2
140°-150°	776.6	15.1
150°-160°	624.4	12.1
160°-170°	402.3	7.8
170°-180°	138.5	2.7
0°-30°	307.5	6.0
0°-40°	477.6	9.3
0°-60°	756.8	14.7
0°-90°	892.5	17.3
90°-120°	702.6	13.6
90°-150°	3100.4	60.1
90°-180°	4266.0	82.7
0°-180°	5158.1	100.0

**CANDELA DISTRIBUTION:**

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	1	12	21	26	28	4
95°	68	36	41	46	45	84
105°	320	334	64	75	80	342
115°	606	624	650	185	86	596
125°	856	870	890	897	900	763
135°	1060	1076	1086	1096	1094	818
145°	1229	1229	1246	1253	1248	768
155°	1353	1345	1357	1362	1354	623
165°	1426	1420	1423	1429	1423	403
175°	1459	1452	1454	1460	1450	139
180°	1456	1456	1456	1456	1456	



TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.3	5.2	5.2	5.1	5.1	5.3	5.6	5.9	6.4	6.7	6.9
90°	1.0	3.6	6.2	8.8	11.4	13.6	15.4	17.3	19.2	21.1	22.2
92.5°	21.3	21.0	20.8	20.6	20.3	20.7	21.6	22.6	23.5	24.5	25.1
95°	68.4	60.7	53.0	45.3	37.5	34.5	36.2	37.8	39.4	41.1	42.3
97.5°	135.9	114.1	92.3	70.6	48.8	39.8	43.6	47.4	51.2	55.0	55.9
100°	186.4	154.4	122.3	90.2	58.2	44.1	48.1	52.1	56.1	60.0	61.9
102.5°	242.0	235.2	228.4	221.7	214.9	194.8	161.5	128.3	95.0	61.7	64.1
105°	320.2	327.2	334.2	341.2	348.3	319.9	256.0	192.0	128.1	64.2	66.8
107.5°	409.3	414.9	420.6	426.3	432.0	396.5	319.9	243.2	166.6	90.0	87.3
110°	466.6	471.5	476.4	481.3	486.2	454.9	387.3	319.6	251.9	184.3	160.9



TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	520.5	524.9	529.2	533.6	538.0	531.8	515.1	498.3	481.6	464.9	379.5
115°	605.6	609.6	613.5	617.5	621.6	626.5	632.3	638.2	644.0	649.9	541.5
117.5°	681.7	686.1	690.5	695.0	699.5	703.7	707.7	711.7	715.7	719.8	693.5
120°	737.3	740.8	744.2	747.8	751.3	755.2	759.4	763.6	767.8	772.0	774.8
122.5°	784.5	788.2	791.9	795.6	799.3	803.4	808.0	812.5	817.2	821.7	823.4
125°	856.3	859.3	862.4	865.4	868.4	872.2	876.7	881.1	885.5	890.0	891.7
127.5°	921.4	924.7	928.1	931.5	934.9	938.2	941.5	944.9	948.1	951.5	953.9
130°	962.7	966.4	970.2	973.9	977.7	980.8	983.3	985.9	988.5	991.1	993.7
132.5°	1004.8	1008.0	1011.2	1014.3	1017.5	1020.4	1023.0	1025.5	1028.1	1030.7	1032.9
135°	1059.5	1063.2	1067.0	1070.7	1074.5	1077.5	1079.5	1081.7	1083.7	1085.9	1088.2
137.5°	1114.9	1117.6	1120.2	1122.8	1125.4	1127.9	1130.3	1132.7	1135.1	1137.5	1139.8
140°	1151.2	1153.1	1154.9	1156.8	1158.6	1160.9	1163.5	1166.1	1168.6	1171.2	1173.3
142.5°	1181.6	1183.2	1184.9	1186.5	1188.3	1190.6	1193.5	1196.4	1199.4	1202.4	1204.3
145°	1229.1	1228.9	1228.6	1228.4	1228.2	1230.0	1234.1	1238.0	1242.0	1246.0	1247.6
147.5°	1270.6	1269.7	1268.9	1267.9	1267.0	1268.6	1272.5	1276.4	1280.4	1284.3	1285.6
150°	1297.6	1296.0	1294.3	1292.6	1291.0	1292.1	1295.8	1299.6	1303.3	1307.1	1308.5
152.5°	1320.3	1318.5	1316.6	1314.8	1313.0	1313.9	1317.4	1321.0	1324.6	1328.1	1329.6
155°	1353.4	1351.3	1349.2	1347.0	1345.0	1345.3	1348.2	1350.9	1353.8	1356.6	1358.0
157.5°	1379.3	1377.5	1375.7	1374.0	1372.2	1372.3	1374.2	1376.2	1378.2	1380.2	1381.7
160°	1394.5	1393.1	1391.6	1390.3	1388.9	1388.9	1390.3	1391.6	1393.1	1394.5	1395.9
162.5°	1408.0	1406.5	1405.2	1403.8	1402.3	1402.2	1403.4	1404.6	1405.9	1407.1	1408.7
165°	1426.1	1424.7	1423.2	1421.9	1420.5	1420.1	1420.8	1421.5	1422.2	1422.9	1424.5
167.5°	1439.6	1438.1	1436.8	1435.4	1433.9	1433.6	1434.3	1434.9	1435.5	1436.1	1437.8
170°	1447.2	1445.7	1444.3	1442.9	1441.5	1441.1	1441.5	1442.0	1442.4	1442.9	1444.6
172.5°	1452.2	1450.8	1449.4	1447.9	1446.6	1446.1	1446.6	1447.0	1447.5	1447.9	1449.6
175°	1458.7	1457.1	1455.4	1453.8	1452.2	1451.6	1452.1	1452.5	1453.0	1453.5	1455.1
177.5°	1459.7	1458.4	1457.2	1455.9	1454.5	1454.0	1454.1	1454.3	1454.5	1454.7	1456.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5



TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	7.1	7.2	7.4	7.5	7.6	7.7	7.7	7.8
90°	23.4	24.5	25.7	26.6	27.0	27.5	28.0	28.4
92.5°	25.7	26.3	26.9	27.3	27.6	27.9	28.2	28.4
95°	43.4	44.6	45.7	46.2	46.0	45.7	45.5	45.3
97.5°	56.8	57.8	58.7	59.3	59.6	59.9	60.2	60.4
100°	63.8	65.6	67.5	68.7	69.1	69.7	70.1	70.6
102.5°	66.6	69.1	71.5	73.0	73.6	74.3	75.0	75.6
105°	69.4	72.0	74.6	76.3	77.2	78.2	79.1	80.1
107.5°	84.7	82.1	79.5	78.6	79.6	80.5	81.5	82.4
110°	137.5	114.1	90.7	79.5	80.4	81.4	82.3	83.2





TEST NUMBER: P331779-935

CATALOG NUMBER: S122RDIW-S290D1240U935-4F0-1E-UDD-F

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	294.1	208.8	123.4	81.0	81.8	82.6	83.3	84.0
115°	433.1	324.8	216.4	153.8	136.9	120.1	103.2	86.4
117.5°	667.4	641.1	614.9	574.1	518.8	463.4	408.0	352.6
120°	777.7	780.4	783.3	768.9	737.3	705.7	674.1	642.5
122.5°	825.1	826.8	828.5	826.2	820.1	814.0	807.9	801.7
125°	893.3	894.9	896.6	897.7	898.4	899.1	899.8	900.5
127.5°	956.2	958.6	961.0	962.3	962.4	962.6	962.7	962.9
130°	996.3	998.8	1001.3	1002.5	1002.3	1002.1	1001.9	1001.6
132.5°	1035.1	1037.2	1039.5	1040.4	1040.3	1040.0	1039.7	1039.6
135°	1090.5	1092.9	1095.3	1096.1	1095.7	1095.3	1094.8	1094.3
137.5°	1142.0	1144.4	1146.7	1147.4	1146.6	1145.8	1145.0	1144.2
140°	1175.4	1177.5	1179.7	1180.1	1178.9	1177.8	1176.6	1175.4
142.5°	1206.2	1208.2	1210.0	1210.4	1209.3	1208.1	1206.9	1205.7
145°	1249.2	1250.9	1252.5	1252.8	1251.5	1250.4	1249.2	1248.1
147.5°	1286.8	1288.0	1289.2	1289.3	1288.3	1287.3	1286.3	1285.4
150°	1309.8	1311.3	1312.7	1312.8	1311.6	1310.4	1309.2	1308.1
152.5°	1330.9	1332.3	1333.8	1333.7	1332.1	1330.6	1329.0	1327.5
155°	1359.3	1360.8	1362.2	1361.9	1360.0	1358.2	1356.3	1354.4
157.5°	1383.4	1384.9	1386.6	1386.4	1384.6	1382.8	1381.0	1379.1
160°	1397.3	1398.7	1400.1	1400.0	1398.4	1396.7	1395.1	1393.4
162.5°	1410.3	1411.9	1413.5	1413.2	1411.3	1409.2	1407.2	1405.2
165°	1426.2	1427.8	1429.4	1429.4	1427.8	1426.2	1424.5	1422.9
167.5°	1439.4	1441.1	1442.7	1442.5	1440.4	1438.3	1436.1	1434.1
170°	1446.2	1447.9	1449.5	1449.2	1447.2	1445.0	1442.9	1440.8
172.5°	1451.2	1452.9	1454.5	1454.3	1452.2	1450.1	1447.9	1445.9
175°	1456.7	1458.4	1460.0	1459.7	1457.3	1455.0	1452.6	1450.3
177.5°	1457.3	1458.6	1460.0	1459.7	1458.1	1456.4	1454.7	1453.0
180°	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5	1455.5

(END OF REPORT)