

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331848-930

Luminaire Tested: **S122RDIW-S1005D435U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331848-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D435U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4065.4 lumens
Efficiency: N/A
Efficacy: 77.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Direct


Input Watts (W): 52.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	112	112	112	112	106	106	106	106	94	94	94	84	84	84	74	74	74	70
1	103	99	95	92	97	94	90	87	84	81	79	75	73	71	67	65	64	60
2	94	87	81	76	89	83	77	73	74	70	67	67	63	61	60	57	55	52
3	86	77	70	64	82	73	67	62	66	61	57	60	56	52	53	50	48	44
4	80	69	61	55	75	66	58	53	59	54	49	54	49	45	48	45	42	39
5	73	62	54	48	69	59	52	46	54	48	43	49	44	40	44	40	37	34
6	68	56	48	42	64	53	46	41	49	42	38	44	39	35	40	36	33	30
7	63	51	43	37	60	49	41	36	44	38	34	40	35	32	37	33	29	27
8	59	46	39	33	56	44	37	32	41	35	30	37	32	28	34	30	27	24
9	55	43	35	30	52	41	34	29	38	32	27	34	29	26	31	27	24	22
10	51	39	32	27	49	38	31	26	35	29	25	32	27	24	29	25	22	20

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	3.2
10°-20°	354.8	8.7
20°-30°	498.3	12.3
30°-40°	543.4	13.4
40°-50°	499.6	12.3
50°-60°	392.4	9.7
60°-70°	255.8	6.3
70°-80°	131.9	3.2
80°-90°	36.0	0.9
90°-100°	27.7	0.7
100°-110°	86.1	2.1
110°-120°	147.2	3.6
120°-130°	193.6	4.8
130°-140°	217.3	5.3
140°-150°	213.1	5.2
150°-160°	178.7	4.4
160°-170°	118.6	2.9
170°-180°	41.4	1.0
0°-30°	982.4	24.2
0°-40°	1525.7	37.5
0°-60°	2417.7	59.5
0°-90°	2841.4	69.9
90°-120°	261.1	6.4
90°-150°	885.2	21.8
90°-180°	1224.0	30.1
0°-180°	4065.4	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	0	5	13	12	13	3
95°	19	23	24	24	23	22
105°	79	80	81	82	82	84
115°	148	150	149	149	148	146
125°	215	218	217	216	216	192
135°	278	282	283	282	281	215
145°	338	340	342	343	341	211
155°	386	387	388	390	389	178
165°	420	420	420	422	420	118
175°	437	436	435	437	436	41
180°	438	438	438	438	438	



TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.1	14.5	12.9	11.3	9.8	9.1	9.5	9.9	10.2	10.6	10.4
90°	0.4	1.4	2.4	3.3	4.3	5.7	7.5	9.3	11.1	13.0	12.8
92.5°	6.6	7.3	8.0	8.7	9.5	10.0	10.4	10.9	11.3	11.7	11.7
95°	19.2	20.1	20.9	21.7	22.5	23.0	23.2	23.3	23.5	23.6	23.6
97.5°	35.1	35.8	36.5	37.3	38.0	38.5	38.8	39.1	39.5	39.7	39.7
100°	46.9	47.5	48.2	48.9	49.6	50.0	50.2	50.5	50.7	51.0	51.0
102.5°	59.4	59.8	60.3	60.9	61.4	61.9	62.1	62.5	62.8	63.1	63.2
105°	79.4	79.7	79.9	80.1	80.4	80.6	80.8	81.0	81.1	81.3	81.4
107.5°	99.6	100.0	100.4	100.8	101.1	101.3	101.3	101.3	101.3	101.3	101.3
110°	112.7	113.2	113.7	114.1	114.6	114.9	114.9	114.9	114.9	114.9	114.9



TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	126.9	127.3	127.8	128.3	128.8	129.1	129.0	128.9	128.8	128.7	128.6
115°	147.7	148.2	148.7	149.2	149.7	149.9	149.7	149.5	149.4	149.2	149.1
117.5°	168.6	169.3	169.9	170.6	171.2	171.3	170.9	170.4	169.9	169.5	169.3
120°	182.5	183.1	183.8	184.4	185.1	185.1	184.4	183.8	183.1	182.5	182.5
122.5°	195.2	196.0	196.7	197.5	198.4	198.5	198.0	197.5	197.1	196.7	196.5
125°	215.0	215.7	216.5	217.2	217.9	218.2	217.9	217.7	217.4	217.2	217.0
127.5°	234.2	235.2	236.1	237.1	238.0	238.3	238.1	237.7	237.4	237.2	236.8
130°	246.4	247.4	248.5	249.6	250.6	251.1	250.9	250.8	250.6	250.5	250.3
132.5°	260.0	260.8	261.7	262.6	263.4	263.9	263.9	264.0	264.0	264.0	263.7
135°	278.2	279.1	280.0	280.9	281.8	282.3	282.4	282.6	282.7	282.9	282.8
137.5°	297.3	298.0	298.7	299.5	300.2	300.7	300.9	301.2	301.3	301.6	301.5
140°	308.8	309.6	310.3	311.0	311.8	312.3	312.7	313.2	313.6	314.0	314.0
142.5°	320.7	321.4	322.1	322.9	323.6	324.1	324.3	324.7	324.9	325.2	325.3
145°	337.6	338.2	338.8	339.3	339.9	340.5	341.0	341.4	341.9	342.4	342.5
147.5°	352.8	353.4	354.2	354.8	355.6	356.0	356.4	356.7	357.0	357.3	357.5
150°	363.1	363.6	364.1	364.6	365.1	365.5	365.8	366.2	366.5	366.8	367.0
152.5°	372.3	372.8	373.2	373.7	374.2	374.7	375.0	375.4	375.9	376.3	376.6
155°	386.0	386.2	386.5	386.8	387.0	387.3	387.5	387.8	388.0	388.2	388.7
157.5°	397.8	397.9	398.1	398.3	398.4	398.5	398.7	398.8	399.0	399.2	399.7
160°	404.9	405.0	405.2	405.4	405.5	405.6	405.7	405.8	405.9	405.9	406.4
162.5°	411.3	411.4	411.4	411.4	411.5	411.6	411.6	411.7	411.8	411.9	412.4
165°	420.0	419.9	419.8	419.7	419.6	419.6	419.6	419.6	419.6	419.6	420.2
167.5°	427.2	427.0	426.7	426.5	426.2	426.1	426.1	426.1	426.1	426.1	426.6
170°	431.0	430.8	430.6	430.3	430.1	429.9	429.8	429.7	429.7	429.6	430.2
172.5°	433.7	433.5	433.3	433.0	432.8	432.6	432.5	432.4	432.4	432.3	432.8
175°	437.0	436.8	436.5	436.3	436.0	435.8	435.6	435.5	435.3	435.1	435.7
177.5°	438.3	438.1	437.9	437.7	437.5	437.3	437.2	437.1	436.9	436.8	437.2
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7



TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	10.1	9.8	9.5	9.5	9.5	9.5	9.5	9.5
90°	12.6	12.5	12.3	12.2	12.3	12.4	12.5	12.6
92.5°	11.8	11.8	11.9	11.9	11.9	11.9	12.0	12.0
95°	23.6	23.6	23.6	23.6	23.4	23.2	23.1	22.9
97.5°	39.7	39.7	39.7	39.7	39.7	39.7	39.7	39.7
100°	51.0	51.0	51.0	51.0	50.9	50.8	50.7	50.6
102.5°	63.2	63.3	63.3	63.3	63.3	63.2	63.1	63.0
105°	81.6	81.8	81.9	82.0	82.0	82.0	82.0	82.0
107.5°	101.4	101.5	101.6	101.4	101.0	100.6	100.3	99.9
110°	114.9	114.9	114.9	114.7	114.5	114.2	114.0	113.7



TEST NUMBER: P331848-930

CATALOG NUMBER: S122RDIW-S1005D435U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	128.4	128.2	128.0	127.8	127.6	127.4	127.3	127.1
115°	149.0	149.0	148.9	148.7	148.5	148.2	148.0	147.7
117.5°	169.1	168.8	168.7	168.4	168.2	168.0	167.7	167.5
120°	182.5	182.5	182.5	182.4	182.1	181.9	181.6	181.4
122.5°	196.2	196.1	195.8	195.7	195.5	195.3	195.1	194.9
125°	216.7	216.5	216.2	216.1	216.0	215.9	215.8	215.7
127.5°	236.5	236.3	235.9	235.7	235.4	235.1	234.9	234.6
130°	250.1	250.0	249.8	249.6	249.2	248.9	248.6	248.3
132.5°	263.3	262.9	262.6	262.3	262.0	261.7	261.5	261.2
135°	282.7	282.7	282.6	282.4	282.2	281.9	281.7	281.4
137.5°	301.4	301.3	301.3	301.1	300.8	300.4	300.1	299.8
140°	314.0	314.0	314.0	313.8	313.5	313.2	312.8	312.5
142.5°	325.3	325.4	325.5	325.3	325.0	324.7	324.3	324.0
145°	342.6	342.7	342.8	342.6	342.3	341.9	341.6	341.3
147.5°	357.7	357.9	358.1	358.0	357.7	357.3	357.0	356.8
150°	367.3	367.5	367.8	367.8	367.5	367.3	367.0	366.8
152.5°	376.8	377.2	377.5	377.5	377.2	376.8	376.6	376.3
155°	389.1	389.5	389.9	390.0	389.7	389.5	389.2	389.0
157.5°	400.2	400.8	401.4	401.5	401.0	400.6	400.3	399.9
160°	406.9	407.4	407.9	408.0	407.6	407.3	407.0	406.7
162.5°	412.9	413.5	414.1	414.2	413.8	413.4	412.9	412.6
165°	420.8	421.3	421.9	422.0	421.6	421.2	420.8	420.4
167.5°	427.2	427.8	428.4	428.4	428.0	427.5	427.1	426.7
170°	430.7	431.3	431.9	431.9	431.5	431.0	430.5	430.0
172.5°	433.4	434.0	434.6	434.6	434.1	433.6	433.1	432.6
175°	436.3	436.8	437.4	437.5	437.0	436.5	436.0	435.5
177.5°	437.7	438.0	438.4	438.4	438.0	437.7	437.2	436.8
180°	437.7	437.7	437.7	437.7	437.7	437.7	437.7	437.7

(END OF REPORT)