

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331771-935

Luminaire Tested: **S122RDIW-S290D710U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331771-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3332.1 lumens
Efficiency: N/A
Efficacy: 109.6 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	55	51	48	41	38	37	28	26	25	20
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	20	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	8
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6978	6978	6978
5°	7005	6891	6929
10°	6951	6779	6720
15°	6870	6578	6387
20°	6761	6290	5976
25°	6649	5964	5574
30°	6490	5630	5062
35°	6337	5267	4610
40°	6182	4890	4089
45°	6003	4464	3617
50°	5815	4037	3152
55°	5624	3578	2711
60°	5406	3094	2251
65°	5154	2598	2048
70°	4858	2143	1884
75°	4492	1953	1759
80°	3961	1748	1599
85°	3112	1371	1371



TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	40.5	1.2
10°-20°	111.1	3.3
20°-30°	156.0	4.7
30°-40°	170.1	5.1
40°-50°	156.4	4.7
50°-60°	122.8	3.7
60°-70°	80.1	2.4
70°-80°	41.3	1.2
80°-90°	12.8	0.4
90°-100°	27.8	0.8
100°-110°	101.9	3.1
110°-120°	272.4	8.2
120°-130°	449.6	13.5
130°-140°	478.2	14.4
140°-150°	444.4	13.3
150°-160°	357.3	10.7
160°-170°	230.3	6.9
170°-180°	79.3	2.4
0°-30°	307.5	9.2
0°-40°	477.6	14.3
0°-60°	756.8	22.7
0°-90°	891.0	26.7
90°-120°	402.1	12.1
90°-150°	1774.3	53.2
90°-180°	2441.0	73.3
0°-180°	3332.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	432	432	432	432	432	
5°	432	430	425	428	428	41
15°	411	406	394	386	382	116
25°	373	360	335	319	313	172
35°	322	301	267	243	234	201
45°	263	236	196	169	158	203
55°	200	169	127	104	96	179
65°	135	103	68	55	54	134
75°	72	45	31	29	28	76
85°	17	9	7	7	7	20
90°	1	7	12	15	16	3
95°	39	21	24	26	26	48
105°	183	191	37	43	46	196
115°	347	357	372	106	49	341
125°	490	498	509	513	515	437
135°	606	616	622	627	626	468
145°	703	703	713	717	714	440
155°	775	770	776	779	775	357
165°	816	813	814	818	814	230
175°	835	831	832	835	830	79
180°	833	833	833	833	833	



TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	433.8	433.4	433.1	432.7	432.4	431.8	431.0	430.3	429.6	428.8	429.5
5°	432.2	431.8	431.4	430.9	430.5	429.6	428.5	427.4	426.3	425.2	425.9
7.5°	427.7	427.2	426.6	426.1	425.6	424.6	423.4	422.0	420.7	419.4	419.6
10°	424.0	423.4	422.8	422.1	421.5	420.3	418.6	416.9	415.2	413.5	413.2
12.5°	419.3	418.5	417.8	417.1	416.3	414.8	412.6	410.4	408.1	405.9	405.4
15°	411.0	410.1	409.1	408.2	407.3	405.3	402.3	399.4	396.4	393.5	391.8
17.5°	401.0	399.5	398.0	396.6	395.1	392.5	388.7	385.0	381.2	377.4	375.4
20°	393.5	391.8	390.0	388.2	386.5	383.5	379.1	374.8	370.5	366.1	363.9
22.5°	385.4	383.4	381.4	379.5	377.5	374.1	369.2	364.3	359.5	354.6	351.7
25°	373.2	370.3	367.6	364.8	362.1	357.7	352.0	346.3	340.5	334.8	331.2
27.5°	358.4	355.4	352.4	349.4	346.3	341.6	335.1	328.6	322.2	315.7	311.6
30°	348.1	344.8	341.5	338.2	334.9	329.8	322.8	315.9	308.9	302.0	297.6
32.5°	338.1	334.2	330.4	326.5	322.6	317.2	310.1	303.0	295.9	288.8	283.8
35°	321.5	317.1	312.6	308.2	303.8	297.7	290.1	282.4	274.8	267.2	261.7
37.5°	305.0	300.1	295.2	290.3	285.4	279.0	270.8	262.6	254.5	246.3	240.3
40°	293.3	288.2	282.9	277.7	272.5	265.7	257.3	248.8	240.4	232.0	225.8
42.5°	281.5	276.0	270.4	265.0	259.5	252.4	243.7	235.0	226.3	217.6	211.2
45°	262.9	257.0	251.2	245.4	239.5	232.0	222.9	213.8	204.7	195.5	189.4
47.5°	244.7	238.5	232.4	226.2	220.0	212.2	202.8	193.4	183.9	174.5	168.4
50°	231.5	225.4	219.2	213.0	206.9	199.0	189.4	179.9	170.3	160.7	154.7
52.5°	218.7	212.2	205.9	199.4	193.0	185.0	175.6	166.3	157.0	147.6	141.8
55°	199.8	193.1	186.3	179.5	172.7	164.7	155.2	145.9	136.5	127.1	121.9
57.5°	180.6	173.6	166.6	159.7	152.7	144.7	135.7	126.7	117.7	108.7	103.8
60°	167.4	160.5	153.5	146.5	139.6	131.6	122.7	113.7	104.8	95.8	91.4
62.5°	154.5	147.7	140.7	133.7	126.7	119.0	110.5	101.9	93.4	84.9	80.7
65°	134.9	127.9	120.9	113.8	106.8	99.4	91.5	83.7	75.9	68.0	65.1
67.5°	116.0	109.0	102.0	95.1	88.1	81.0	74.0	67.0	59.9	52.9	51.5
70°	102.9	96.1	89.3	82.6	75.8	69.4	63.4	57.3	51.4	45.4	44.5
72.5°	90.3	83.9	77.3	70.9	64.3	58.7	53.9	49.1	44.3	39.4	38.7
75°	72.0	65.9	59.8	53.7	47.6	43.1	40.1	37.2	34.3	31.3	30.7
77.5°	53.9	48.6	43.2	37.9	32.5	29.2	27.7	26.3	24.9	23.5	23.2
80°	42.6	38.2	33.8	29.4	24.9	22.2	21.4	20.5	19.6	18.8	18.4
82.5°	32.3	28.8	25.4	22.0	18.5	16.4	15.8	15.2	14.6	14.1	13.9
85°	16.8	15.0	13.2	11.4	9.6	8.4	8.2	7.9	7.7	7.4	7.4
87.5°	5.2	4.9	4.6	4.3	4.0	4.0	4.3	4.5	4.7	4.9	5.0
90°	0.6	2.1	3.5	5.0	6.5	7.7	8.9	9.9	11.0	12.1	12.7
92.5°	12.1	12.1	11.9	11.8	11.6	11.9	12.4	12.9	13.4	13.9	14.3
95°	39.2	34.8	30.3	25.9	21.5	19.7	20.7	21.6	22.6	23.5	24.2
97.5°	77.7	65.3	52.9	40.4	27.9	22.8	25.0	27.1	29.3	31.4	32.0
100°	106.7	88.3	70.0	51.7	33.3	25.2	27.6	29.8	32.1	34.4	35.4
102.5°	138.5	134.7	130.7	126.8	123.0	111.5	92.5	73.4	54.3	35.3	36.7
105°	183.2	187.3	191.3	195.3	199.3	183.0	146.5	109.9	73.4	36.8	38.2
107.5°	234.2	237.5	240.7	243.9	247.2	226.9	183.0	139.2	95.3	51.5	49.9
110°	267.0	269.8	272.7	275.4	278.3	260.3	221.6	182.9	144.2	105.5	92.1



TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	297.9	300.4	302.9	305.3	307.8	304.3	294.7	285.2	275.6	266.0	217.2
115°	346.6	348.9	351.1	353.4	355.7	358.5	361.9	365.2	368.5	371.9	309.9
117.5°	390.1	392.6	395.2	397.7	400.3	402.7	405.0	407.3	409.6	411.9	396.9
120°	421.9	424.0	425.9	427.9	430.0	432.1	434.5	437.0	439.4	441.8	443.4
122.5°	448.9	451.1	453.1	455.3	457.4	459.8	462.4	465.0	467.6	470.3	471.2
125°	490.0	491.8	493.5	495.2	497.0	499.1	501.7	504.2	506.8	509.3	510.2
127.5°	527.3	529.2	531.2	533.0	535.0	536.9	538.8	540.7	542.6	544.5	545.9
130°	550.9	553.0	555.2	557.3	559.5	561.3	562.7	564.2	565.7	567.2	568.7
132.5°	575.1	576.9	578.7	580.5	582.3	583.9	585.4	586.9	588.4	589.9	591.1
135°	606.4	608.5	610.6	612.8	614.9	616.6	617.9	619.1	620.3	621.5	622.8
137.5°	638.1	639.6	641.1	642.6	644.0	645.5	646.9	648.2	649.6	651.0	652.3
140°	658.8	659.9	660.9	662.0	663.1	664.3	665.8	667.3	668.7	670.3	671.5
142.5°	676.1	677.1	678.1	679.1	680.0	681.3	683.0	684.8	686.4	688.1	689.2
145°	703.4	703.3	703.2	703.0	702.8	704.0	706.2	708.5	710.8	713.1	714.0
147.5°	727.1	726.7	726.2	725.7	725.1	726.0	728.2	730.5	732.7	734.9	735.7
150°	742.6	741.7	740.7	739.8	738.8	739.4	741.6	743.7	745.9	748.0	748.8
152.5°	755.6	754.6	753.5	752.4	751.4	751.9	754.0	756.0	758.0	760.1	760.9
155°	774.6	773.4	772.1	770.9	769.7	769.9	771.5	773.1	774.7	776.4	777.1
157.5°	789.4	788.3	787.3	786.3	785.3	785.3	786.4	787.6	788.7	789.8	790.7
160°	798.1	797.2	796.4	795.7	794.8	794.8	795.7	796.4	797.2	798.1	798.8
162.5°	805.7	804.9	804.2	803.3	802.5	802.5	803.1	803.9	804.6	805.3	806.2
165°	816.1	815.3	814.5	813.7	812.9	812.7	813.1	813.5	813.9	814.3	815.3
167.5°	823.8	823.0	822.3	821.4	820.6	820.4	820.8	821.1	821.6	821.9	822.9
170°	828.2	827.3	826.6	825.8	824.9	824.7	824.9	825.3	825.5	825.8	826.7
172.5°	831.0	830.3	829.5	828.6	827.9	827.6	827.9	828.1	828.4	828.6	829.6
175°	834.8	833.9	832.9	832.0	831.0	830.7	831.0	831.3	831.6	831.8	832.8
177.5°	835.4	834.7	833.9	833.2	832.4	832.1	832.2	832.3	832.4	832.5	833.3
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0



TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	432.2	432.2	432.2	432.2	432.2	432.2	432.2	432.2
2.5°	430.2	430.8	431.5	431.8	431.7	431.5	431.4	431.3
5°	426.7	427.5	428.3	428.5	428.3	428.0	427.7	427.5
7.5°	419.8	420.1	420.3	420.2	419.7	419.2	418.8	418.4
10°	412.9	412.7	412.4	412.0	411.5	411.0	410.4	409.9
12.5°	405.0	404.5	404.1	403.4	402.5	401.7	400.8	399.9
15°	390.2	388.5	386.8	385.6	384.8	383.8	383.0	382.1
17.5°	373.4	371.4	369.5	367.8	366.3	364.8	363.3	361.8
20°	361.8	359.6	357.4	355.3	353.4	351.5	349.7	347.8
22.5°	349.0	346.1	343.4	341.2	339.8	338.4	336.9	335.5
25°	327.7	324.1	320.6	318.1	316.8	315.5	314.2	312.9
27.5°	307.4	303.2	299.1	296.0	293.9	291.9	289.8	287.7
30°	293.1	288.7	284.2	280.9	278.4	276.1	273.8	271.5
32.5°	278.7	273.6	268.5	264.9	262.8	260.5	258.3	256.1
35°	256.2	250.7	245.2	241.5	239.6	237.7	235.8	233.9
37.5°	234.3	228.3	222.2	218.1	215.9	213.7	211.5	209.3
40°	219.6	213.4	207.2	203.0	200.8	198.5	196.2	194.0
42.5°	204.7	198.4	192.0	187.8	185.5	183.4	181.2	179.0
45°	183.2	177.0	170.9	166.8	164.7	162.6	160.5	158.4
47.5°	162.2	156.1	150.0	145.9	144.0	142.2	140.3	138.4
50°	148.8	142.8	136.7	132.9	131.0	129.2	127.3	125.5
52.5°	136.0	130.3	124.5	120.7	119.1	117.4	115.6	114.0
55°	116.7	111.5	106.2	102.8	101.2	99.5	97.9	96.3
57.5°	99.1	94.3	89.5	86.4	85.1	83.7	82.3	80.8
60°	87.0	82.6	78.1	75.2	73.8	72.4	71.0	69.7
62.5°	76.5	72.2	68.0	65.4	64.6	63.8	62.9	62.1
65°	62.2	59.2	56.2	54.6	54.3	54.1	53.8	53.6
67.5°	50.2	48.8	47.4	46.7	46.3	46.1	45.8	45.5
70°	43.7	42.8	41.9	41.3	40.9	40.6	40.2	39.9
72.5°	38.0	37.2	36.5	36.1	35.8	35.6	35.4	35.2
75°	30.0	29.4	28.8	28.5	28.4	28.3	28.2	28.2
77.5°	22.7	22.4	22.0	21.9	21.7	21.5	21.4	21.3
80°	18.1	17.7	17.4	17.2	17.2	17.2	17.2	17.2
82.5°	13.7	13.4	13.3	13.2	13.2	13.2	13.2	13.2
85°	7.4	7.4	7.4	7.4	7.4	7.4	7.4	7.4
87.5°	5.1	5.1	5.2	5.3	5.3	5.3	5.4	5.4
90°	13.4	14.0	14.7	15.2	15.5	15.8	16.0	16.3
92.5°	14.7	15.1	15.4	15.7	15.8	15.9	16.1	16.3
95°	24.9	25.5	26.2	26.4	26.3	26.2	26.1	25.9
97.5°	32.5	33.1	33.6	33.9	34.1	34.3	34.4	34.6
100°	36.5	37.5	38.7	39.3	39.6	39.9	40.1	40.4
102.5°	38.1	39.5	40.9	41.8	42.2	42.5	42.9	43.3
105°	39.7	41.2	42.6	43.7	44.2	44.8	45.3	45.8
107.5°	48.5	47.0	45.5	45.0	45.5	46.1	46.6	47.1
110°	78.7	65.3	51.9	45.5	46.0	46.6	47.1	47.6



TEST NUMBER: P331771-935

CATALOG NUMBER: S122RDIW-S290D710U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	168.3	119.5	70.6	46.4	46.8	47.3	47.7	48.1
115°	247.9	185.8	123.8	88.0	78.4	68.7	59.1	49.4
117.5°	381.9	366.9	351.9	328.6	296.9	265.2	233.5	201.8
120°	445.1	446.6	448.2	440.0	421.9	403.8	385.7	367.6
122.5°	472.2	473.1	474.2	472.9	469.3	465.8	462.4	458.8
125°	511.2	512.1	513.1	513.8	514.1	514.5	515.0	515.3
127.5°	547.3	548.6	550.0	550.7	550.8	550.9	551.0	551.0
130°	570.2	571.6	573.1	573.8	573.6	573.5	573.3	573.3
132.5°	592.4	593.7	594.9	595.5	595.3	595.2	595.0	595.0
135°	624.1	625.4	626.8	627.3	627.1	626.8	626.5	626.3
137.5°	653.6	654.9	656.3	656.7	656.2	655.7	655.3	654.8
140°	672.7	673.9	675.1	675.4	674.7	674.0	673.3	672.7
142.5°	690.3	691.4	692.5	692.7	692.1	691.4	690.7	690.0
145°	714.9	715.8	716.8	717.0	716.3	715.6	714.9	714.3
147.5°	736.4	737.1	737.8	737.9	737.3	736.8	736.2	735.6
150°	749.6	750.4	751.2	751.3	750.6	749.9	749.2	748.6
152.5°	761.6	762.5	763.3	763.3	762.3	761.5	760.6	759.7
155°	777.9	778.8	779.5	779.4	778.3	777.3	776.2	775.2
157.5°	791.7	792.6	793.5	793.4	792.4	791.3	790.3	789.2
160°	799.6	800.5	801.2	801.2	800.2	799.3	798.4	797.5
162.5°	807.1	808.0	808.9	808.8	807.6	806.5	805.3	804.2
165°	816.2	817.1	818.0	818.0	817.1	816.2	815.3	814.3
167.5°	823.8	824.8	825.6	825.5	824.3	823.1	821.9	820.7
170°	827.7	828.5	829.5	829.4	828.2	827.0	825.8	824.6
172.5°	830.5	831.5	832.4	832.2	831.0	829.8	828.6	827.4
175°	833.7	834.6	835.5	835.3	834.0	832.7	831.3	830.0
177.5°	834.1	834.7	835.5	835.4	834.5	833.4	832.5	831.6
180°	833.0	833.0	833.0	833.0	833.0	833.0	833.0	833.0

(END OF REPORT)