

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331849-930

Luminaire Tested: **S122RDIW-S1005D710U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331849-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S1005D710U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 710 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 5421.0 lumens  
Efficiency: N/A  
Efficacy: 90.7 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: General Diffuse  
  
Input Watts (W): 59.8  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot





TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	109	109	109	109	101	101	101	101	87	87	87	75	75	75	63	63	63	57				
1	100	96	93	89	93	90	87	84	78	76	74	67	65	64	57	56	55	50				
2	92	85	79	75	86	80	75	70	69	66	62	60	57	55	51	49	48	43				
3	85	76	69	63	79	71	65	60	62	58	54	54	51	48	46	44	42	38				
4	78	68	60	55	73	64	57	52	56	51	47	49	45	42	42	39	37	34				
5	72	61	53	48	67	57	51	45	51	45	41	44	40	37	38	35	33	30				
6	67	55	47	42	62	52	45	40	46	41	36	41	36	33	35	32	29	27				
7	62	50	43	37	58	48	41	36	42	37	33	37	33	30	33	29	27	24				
8	58	46	39	33	54	44	37	32	39	33	29	34	30	27	30	27	24	22				
9	54	42	35	30	51	40	34	29	36	31	27	32	28	24	28	25	22	20				
10	51	39	32	27	48	37	31	26	33	28	24	30	25	22	26	23	20	19				

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	29032	29032	29032	29032
5°	32423	29214	25901	29214
10°	35974	29009	22453	29009
15°	37742	28583	17690	28583
20°	32720	27953	15309	27953
25°	21458	27091	13668	27091
30°	14443	26045	12370	26045
35°	11698	24727	11158	24727
40°	10404	23294	10323	23294
45°	9417	21614	9216	21614
50°	8568	19947	8538	19947
55°	8056	18097	7949	18097
60°	6736	16401	6659	16401
65°	5681	14896	6445	14896
70°	5249	13303	6076	13303
75°	4916	11578	5608	11578
80°	4537	9530	4993	9530
85°	4168	7521	4390	7521



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	170.4	3.1
10°-20°	474.9	8.8
20°-30°	612.0	11.3
30°-40°	581.6	10.7
40°-50°	498.2	9.2
50°-60°	379.4	7.0
60°-70°	239.9	4.4
70°-80°	119.8	2.2
80°-90°	33.1	0.6
90°-100°	26.3	0.5
100°-110°	96.5	1.8
110°-120°	257.9	4.8
120°-130°	425.7	7.9
130°-140°	452.8	8.4
140°-150°	420.8	7.8
150°-160°	338.4	6.2
160°-170°	218.0	4.0
170°-180°	75.1	1.4
0°-30°	1257.4	23.2
0°-40°	1839.0	33.9
0°-60°	2716.7	50.1
0°-90°	3109.4	57.4
90°-120°	380.7	7.0
90°-150°	1680.1	31.0
90°-180°	2312.0	42.6
0°-180°	5421.0	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	1798	1798	1798	1798	1798	
5°	2000	1802	1598	1802	2000	197
15°	2258	1710	1058	1710	2258	609
25°	1204	1521	767	1521	1204	572
35°	594	1254	566	1254	594	380
45°	412	947	404	947	412	319
55°	286	643	282	643	286	251
65°	149	390	169	390	149	151
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	15	1	15	1	15	8
95°	24	37	24	37	24	23
105°	43	174	43	174	43	45
115°	47	328	47	328	47	117
125°	488	464	488	464	488	422
135°	593	574	593	574	593	457
145°	676	666	676	666	676	423
155°	734	733	734	733	734	339
165°	771	773	771	773	771	218
175°	786	790	786	790	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1871.0	1872.6	1874.0	1870.5	1870.5	1867.5	1861.1	1856.0	1842.1	1840.0	1840.0
5°	2000.5	1999.3	2001.7	1993.7	1982.4	1979.9	1968.1	1952.4	1936.2	1918.1	1914.3
7.5°	2129.2	2127.4	2122.3	2121.0	2112.4	2093.4	2074.4	2054.0	2027.0	2000.7	1987.4
10°	2194.2	2214.8	2202.3	2180.4	2184.8	2155.5	2139.8	2113.0	2090.5	2051.1	2042.4
12.5°	2258.1	2266.3	2262.3	2249.9	2244.3	2223.9	2202.8	2179.5	2138.0	2102.6	2071.8
15°	2257.9	2269.8	2272.9	2269.1	2272.3	2271.0	2259.8	2240.4	2204.2	2165.4	2131.7
17.5°	2091.2	2099.5	2119.9	2133.8	2151.3	2188.3	2206.5	2213.7	2208.3	2186.2	2162.4
20°	1904.3	1890.5	1948.0	1977.4	2002.4	2064.8	2118.6	2139.2	2172.3	2171.7	2165.4
22.5°	1639.4	1642.7	1697.1	1732.0	1805.0	1867.4	1928.7	2006.3	2070.4	2112.7	2137.5
25°	1204.5	1228.3	1282.6	1330.2	1411.4	1527.5	1633.1	1755.6	1871.2	1962.4	2049.3
27.5°	904.7	906.4	949.5	993.4	1041.6	1136.9	1269.7	1416.0	1580.8	1716.8	1873.2
30°	774.7	770.9	789.0	816.0	857.2	930.9	1030.9	1174.6	1338.9	1543.8	1726.2
32.5°	682.7	683.0	696.6	716.5	750.7	800.5	868.9	985.6	1140.9	1342.4	1556.3
35°	593.5	592.9	602.9	617.3	631.6	663.5	710.4	771.6	878.4	1066.5	1285.2
37.5°	529.5	532.3	537.2	546.2	562.1	579.8	607.9	649.0	725.1	836.3	1020.1
40°	493.6	494.8	501.7	509.2	518.5	532.3	555.4	588.6	644.2	732.9	867.2
42.5°	460.6	461.9	466.7	473.7	481.1	494.8	514.0	542.6	587.7	656.9	767.7
45°	412.4	412.4	416.7	419.9	428.0	440.4	456.1	479.8	511.0	562.3	636.0
47.5°	367.1	367.2	370.1	375.5	380.6	390.4	405.7	425.1	447.8	487.5	550.4
50°	341.1	341.8	343.6	348.0	351.1	359.9	371.8	388.6	412.4	443.0	495.5
52.5°	320.2	319.8	322.1	324.0	326.1	332.4	341.3	356.1	377.3	404.0	447.4
55°	286.2	283.6	287.4	290.5	292.4	294.9	299.9	309.2	327.3	349.8	382.4
57.5°	243.7	242.6	245.3	248.2	254.0	260.8	265.1	271.0	280.4	296.5	328.7
60°	208.6	208.6	214.3	216.1	223.1	231.8	240.5	245.6	254.9	265.5	289.3
62.5°	177.7	178.2	180.8	182.7	186.5	197.3	209.5	220.5	229.4	239.5	255.3
65°	148.7	149.9	149.9	151.2	153.7	156.2	161.2	169.9	185.6	199.9	211.8
67.5°	126.2	126.6	126.9	128.2	128.8	131.6	133.5	137.5	141.0	154.7	169.4
70°	111.2	113.1	112.4	113.7	114.3	115.6	118.1	119.9	125.6	128.7	137.5
72.5°	97.2	98.6	98.5	99.2	100.9	101.1	103.1	104.9	108.6	111.2	115.9
75°	78.8	78.1	78.8	80.0	80.6	81.2	81.2	83.7	85.6	88.1	91.2
77.5°	60.7	61.4	61.2	61.4	61.5	62.6	62.5	63.6	65.5	66.7	68.2
80°	48.8	49.3	48.8	49.3	50.0	50.6	50.0	50.6	52.5	53.7	53.7
82.5°	37.7	37.8	38.2	38.4	38.5	38.6	39.5	39.6	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.2	22.5	22.5	23.2	23.2	23.2
87.5°	11.1	11.5	11.5	11.4	11.4	11.3	11.2	11.5	10.9	11.3	10.6
90°	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7	12.1	11.4	10.4
92.5°	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9	13.5	13.2	12.7
95°	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6	22.9	22.3	21.4
97.5°	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8	30.3	29.8	27.7
100°	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6	33.5	32.5	30.4
102.5°	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1	34.7	33.4	31.4
105°	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6	36.2	34.8	32.5
107.5°	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9	47.3	48.8	49.3
110°	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5	87.2	99.9	136.6



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4	205.7	251.9	261.0
115°	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7	293.4	352.1	348.9
117.5°	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7	375.9	390.0	387.8
120°	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4	419.9	418.3	416.0
122.5°	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1	446.2	445.3	442.8
125°	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0	483.1	482.2	479.9
127.5°	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2	516.9	515.6	513.8
130°	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9	538.5	537.1	535.7
132.5°	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9	559.7	558.6	557.2
135°	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0	589.7	588.5	587.3
137.5°	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9	617.7	616.4	615.1
140°	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0	635.9	634.7	633.2
142.5°	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6	652.6	651.6	650.0
145°	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9	676.1	675.2	673.0
147.5°	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3	696.7	695.9	693.8
150°	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8	709.1	708.3	706.3
152.5°	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2	720.5	719.7	717.8
155°	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6	735.9	735.2	733.6
157.5°	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7	748.8	747.9	746.8
160°	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2	756.4	755.7	754.9
162.5°	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3	763.4	762.5	761.9
165°	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1	770.7
167.5°	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1	779.2	778.3	778.0
170°	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7	782.9	782.0	781.7
172.5°	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4	785.5	784.6	784.4
175°	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5	788.6	787.7	787.4
177.5°	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8	789.0	788.3	788.2
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1841.1	1837.0	1833.6	1824.6	1820.1	1810.0	1808.6	1808.1	1795.1	1782.6	1779.1
5°	1904.3	1894.3	1879.3	1861.8	1843.7	1825.0	1812.5	1802.5	1777.4	1753.7	1740.0
7.5°	1968.1	1946.5	1920.7	1887.6	1859.9	1829.0	1806.0	1785.3	1749.9	1715.9	1693.0
10°	2015.5	1980.5	1946.1	1900.5	1864.9	1829.9	1797.5	1769.4	1729.3	1684.4	1652.5
12.5°	2045.0	2006.5	1959.2	1914.6	1868.4	1824.0	1780.5	1744.3	1697.4	1650.9	1613.1
15°	2084.9	2043.6	1986.2	1922.4	1863.0	1805.0	1755.0	1710.0	1648.8	1593.2	1546.9
17.5°	2117.5	2060.8	1999.0	1925.3	1856.6	1782.7	1718.4	1660.9	1592.8	1525.7	1471.2
20°	2127.9	2071.8	2000.5	1926.8	1845.6	1758.8	1689.4	1626.9	1553.8	1480.7	1418.2
22.5°	2121.5	2077.7	1998.5	1910.3	1827.1	1736.3	1657.9	1585.4	1504.3	1429.7	1357.2
25°	2077.4	2062.4	1987.4	1891.2	1796.2	1690.6	1600.0	1520.7	1428.2	1348.3	1269.5
27.5°	1974.5	2006.9	1960.4	1857.9	1752.3	1639.2	1537.3	1447.0	1351.0	1261.0	1182.6
30°	1875.6	1949.9	1929.9	1834.9	1716.9	1605.7	1491.3	1397.0	1294.5	1202.1	1124.6
32.5°	1740.1	1863.0	1882.4	1803.0	1680.9	1558.7	1438.8	1345.0	1238.0	1140.6	1065.1
35°	1524.4	1708.1	1792.4	1741.9	1619.4	1487.6	1363.8	1254.5	1147.0	1050.8	975.9
37.5°	1267.1	1517.4	1657.9	1661.5	1549.1	1412.0	1277.2	1168.7	1058.7	964.3	883.2
40°	1100.2	1371.3	1554.4	1595.1	1500.1	1352.0	1215.8	1105.2	997.8	905.3	812.2
42.5°	950.3	1220.4	1445.4	1516.0	1440.6	1293.6	1156.8	1041.2	936.8	849.3	754.2
45°	768.5	1004.6	1252.6	1378.8	1337.0	1200.8	1056.5	946.6	848.4	772.8	681.6
47.5°	648.2	814.7	1054.8	1225.4	1224.7	1100.3	958.4	853.0	762.1	691.2	617.4
50°	579.8	724.7	927.8	1121.4	1137.7	1033.4	898.4	794.1	709.1	634.8	575.4
52.5°	518.3	637.7	820.4	1006.0	1052.2	961.9	831.0	734.6	652.2	583.8	533.0
55°	438.0	530.4	669.1	842.8	912.8	849.1	732.9	642.9	576.0	518.5	474.8
57.5°	370.5	439.9	551.1	691.0	772.5	732.4	636.5	563.5	506.2	454.2	419.7
60°	328.0	384.8	479.2	596.1	686.0	657.9	576.0	507.9	459.2	414.3	381.7
62.5°	288.0	336.9	417.8	512.6	595.0	583.4	516.6	459.4	416.7	375.8	348.2
65°	231.8	267.4	330.5	404.9	471.1	476.7	428.6	389.9	351.7	319.3	294.9
67.5°	184.6	207.8	252.3	314.9	364.5	382.2	352.9	323.3	293.0	267.9	246.8
70°	155.6	174.3	206.8	257.4	303.0	321.7	304.9	281.8	255.5	234.9	216.8
72.5°	126.0	144.3	168.3	205.5	244.5	264.8	258.9	242.3	221.0	203.9	186.8
75°	95.0	100.6	116.8	141.9	172.4	190.0	194.3	185.6	168.7	155.6	145.5
77.5°	70.2	73.6	81.4	94.5	114.5	130.0	136.5	135.4	123.8	116.2	106.8
80°	56.3	58.1	61.9	67.5	82.5	98.1	102.5	102.5	94.3	91.2	81.9
82.5°	42.7	44.1	46.4	49.5	56.5	70.1	75.0	76.0	70.8	66.7	59.4
85°	24.4	23.7	25.0	26.9	28.1	31.9	39.4	40.6	39.4	34.3	32.4
87.5°	10.4	10.7	10.4	9.7	9.9	10.2	12.4	14.6	12.9	11.7	10.9
90°	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6	2.0	3.3	4.7
92.5°	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5	11.4	11.3	11.2
95°	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1	32.9	28.7	24.5
97.5°	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6	61.8	50.1	38.2
100°	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0	83.6	66.3	48.9
102.5°	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2	127.5	123.8	120.1
105°	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5	177.3	181.2	184.9
107.5°	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8	224.9	228.0	231.0
110°	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8	255.5	258.2	260.8





TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1	284.5	286.8	289.1
115°	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2	330.4	332.5	334.7
117.5°	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4	371.8	374.2	376.6
120°	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5	401.5	403.3	405.2
122.5°	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1	427.1	429.1	431.1
125°	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0	465.7	467.3	469.0
127.5°	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3	501.1	503.0	504.8
130°	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6	523.7	525.7	527.7
132.5°	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5	546.3	548.0	549.7
135°	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2	576.2	578.2	580.2
137.5°	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2	605.6	607.1	608.5
140°	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9	624.8	625.8	626.9
142.5°	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3	641.2	642.1	643.0
145°	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1	665.9	665.9	665.7
147.5°	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5	688.1	687.6	687.1
150°	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2	702.3	701.4	700.5
152.5°	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5	714.5	713.5	712.5
155°	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4	732.3	731.2	730.0
157.5°	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5	746.5	745.5	744.5
160°	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	754.9	754.2	753.4
162.5°	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0	762.2	761.5	760.7
165°	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8	772.0	771.3	770.5
167.5°	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1	779.3	778.6	777.8
170°	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2	783.4	782.7	782.0
172.5°	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9	786.2	785.5	784.6
175°	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5	789.6	788.7	787.8
177.5°	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1	790.4	789.6	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1772.6	1769.1	1762.6	1752.6	1746.6	1736.1	1729.1	1733.1	1734.1	1733.1	1732.1
5°	1725.0	1711.9	1693.8	1676.3	1660.0	1642.5	1632.6	1628.2	1619.4	1614.4	1611.9
7.5°	1667.4	1644.8	1619.2	1588.7	1562.8	1535.7	1521.8	1514.9	1497.1	1487.4	1478.8
10°	1624.4	1588.8	1563.2	1523.2	1498.8	1463.2	1438.8	1439.5	1415.1	1401.3	1391.4
12.5°	1577.0	1537.8	1495.2	1459.2	1425.4	1396.8	1367.3	1355.5	1329.7	1316.4	1289.4
15°	1498.2	1452.6	1407.6	1358.9	1324.5	1280.2	1237.7	1185.9	1143.9	1107.7	1097.7
17.5°	1412.3	1355.8	1310.7	1253.4	1194.6	1120.0	1070.7	1040.6	1015.4	996.3	982.0
20°	1353.2	1295.8	1247.7	1161.5	1082.1	1031.5	995.2	972.2	945.9	925.3	914.0
22.5°	1291.3	1231.3	1165.7	1069.5	1007.6	967.0	934.7	908.2	890.4	874.3	864.1
25°	1203.3	1137.7	1029.6	963.4	913.4	870.9	848.4	832.2	813.4	791.6	781.6
27.5°	1110.4	1006.0	928.4	879.1	831.4	803.8	783.6	759.4	742.6	732.7	722.4
30°	1040.9	936.5	876.0	822.2	788.5	757.8	734.1	720.4	704.1	687.2	680.4
32.5°	963.4	880.0	822.0	777.2	743.0	716.9	698.1	675.9	664.1	653.8	639.4
35°	867.2	804.0	751.0	714.8	682.2	661.0	639.1	626.0	604.8	596.1	590.4
37.5°	785.7	731.0	691.4	653.1	627.4	603.9	590.5	569.6	560.4	548.3	536.5
40°	739.7	686.0	647.9	616.6	587.9	570.4	553.5	536.7	522.9	517.3	503.0
42.5°	692.8	649.0	610.9	576.7	557.4	538.9	517.6	505.2	491.0	481.8	473.0
45°	627.9	589.1	556.7	528.6	507.3	488.0	474.2	453.6	445.5	427.4	419.9
47.5°	571.0	534.9	503.9	477.2	456.5	443.8	423.7	407.6	394.6	383.5	373.9
50°	530.4	500.4	470.4	446.7	428.0	409.9	389.2	381.1	361.1	355.5	349.8
52.5°	493.4	465.0	437.5	414.3	395.5	377.9	359.7	349.1	335.7	330.0	325.9
55°	441.7	414.3	388.0	367.4	348.6	330.5	319.3	306.1	299.9	295.5	290.5
57.5°	389.7	365.0	344.9	324.0	305.2	290.7	277.8	269.9	263.4	257.6	251.7
60°	356.8	333.0	314.9	295.5	276.1	264.2	254.3	244.9	237.4	228.7	226.2
62.5°	321.7	301.0	284.4	265.5	248.7	237.8	228.3	219.4	210.4	197.7	194.2
65°	273.6	257.4	239.9	224.3	209.3	198.7	184.9	175.0	171.2	169.9	169.3
67.5°	230.2	214.8	199.8	183.8	170.2	160.3	153.4	151.8	149.2	148.5	146.7
70°	201.2	186.8	171.8	156.8	143.7	141.9	139.3	136.8	133.7	132.5	131.2
72.5°	175.2	160.3	145.3	133.3	127.7	125.3	122.9	120.3	118.2	117.0	116.2
75°	134.4	120.6	110.6	106.2	103.1	101.2	97.4	95.6	94.3	92.5	91.8
77.5°	96.7	88.9	84.4	81.6	78.4	76.3	74.2	72.3	71.0	70.6	69.6
80°	73.7	70.0	66.9	63.1	61.9	59.4	58.7	56.8	57.5	55.6	55.6
82.5°	57.2	52.5	49.9	48.1	46.9	44.8	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.1	26.9	25.6	25.6	23.7	24.4	23.7	23.7	22.5	21.9
87.5°	10.8	10.4	9.7	9.9	10.1	9.8	9.9	9.5	9.6	9.8	9.4
90°	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7	13.3	13.9	14.4
92.5°	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9	14.3	14.6	14.8
95°	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6	24.1	24.8	25.0
97.5°	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8	31.3	31.8	32.1
100°	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6	35.5	36.6	37.3
102.5°	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1	37.4	38.7	39.5
105°	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6	39.0	40.4	41.3
107.5°	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9	44.5	43.0	42.6
110°	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5	61.8	49.2	43.0



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4	113.2	66.9	43.9
115°	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7	175.9	117.2	83.3
117.5°	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7	347.4	333.2	311.1
120°	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4	422.9	424.4	416.6
122.5°	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1	448.0	449.0	447.8
125°	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0	484.9	485.8	486.5
127.5°	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2	519.5	520.8	521.5
130°	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9	541.3	542.7	543.3
132.5°	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9	562.1	563.3	563.9
135°	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0	592.2	593.5	594.0
137.5°	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9	620.1	621.4	621.8
140°	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0	638.1	639.3	639.5
142.5°	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6	654.7	655.7	655.9
145°	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9	677.8	678.7	678.9
147.5°	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3	698.0	698.6	698.7
150°	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8	710.6	711.3	711.4
152.5°	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2	722.0	722.8	722.8
155°	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6	737.4	738.2	738.0
157.5°	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7	750.5	751.4	751.3
160°	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2	758.0	758.7	758.6
162.5°	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3	765.1	766.0	765.9
165°	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9	773.7	774.6	774.6
167.5°	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1	781.0	781.8	781.7
170°	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7	784.6	785.5	785.4
172.5°	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4	787.3	788.2	788.1
175°	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5	790.3	791.2	791.0
177.5°	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8	790.4	791.2	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1726.6	1727.6	1726.2	1727.1	1726.2	1727.6	1726.6	1732.1	1733.1	1734.1	1733.1
5°	1608.7	1601.2	1600.0	1598.1	1600.0	1601.2	1608.7	1611.9	1614.4	1619.4	1628.2
7.5°	1468.1	1467.0	1463.9	1459.5	1463.9	1467.0	1468.1	1478.8	1487.4	1497.1	1514.9
10°	1377.6	1374.5	1373.9	1369.5	1373.9	1374.5	1377.6	1391.4	1401.3	1415.1	1439.5
12.5°	1271.6	1251.6	1249.4	1238.5	1249.4	1251.6	1271.6	1289.4	1316.4	1329.7	1355.5
15°	1082.7	1079.0	1066.5	1058.3	1066.5	1079.0	1082.7	1097.7	1107.7	1143.9	1185.9
17.5°	974.8	962.5	958.6	956.9	958.6	962.5	974.8	982.0	996.3	1015.4	1040.6
20°	905.3	894.1	892.2	891.0	892.2	894.1	905.3	914.0	925.3	945.9	972.2
22.5°	857.3	845.5	840.7	836.9	840.7	845.5	857.3	864.1	874.3	890.4	908.2
25°	775.3	770.9	768.5	767.2	768.5	770.9	775.3	781.6	791.6	813.4	832.2
27.5°	711.3	701.6	699.8	696.5	699.8	701.6	711.3	722.4	732.7	742.6	759.4
30°	674.7	671.6	667.2	663.5	667.2	671.6	674.7	680.4	687.2	704.1	720.4
32.5°	631.8	629.2	625.3	623.5	625.3	629.2	631.8	639.4	653.8	664.1	675.9
35°	584.2	575.4	571.7	566.1	571.7	575.4	584.2	590.4	596.1	604.8	626.0
37.5°	533.8	529.2	523.9	525.8	523.9	529.2	533.8	536.5	548.3	560.4	569.6
40°	494.8	491.7	490.5	489.8	490.5	491.7	494.8	503.0	517.3	522.9	536.7
42.5°	463.8	455.2	451.9	451.8	451.9	455.2	463.8	473.0	481.8	491.0	505.2
45°	416.7	408.6	403.0	403.6	403.0	408.6	416.7	419.9	427.4	445.5	453.6
47.5°	368.5	368.3	364.8	365.8	364.8	368.3	368.5	373.9	383.5	394.6	407.6
50°	345.5	341.8	339.2	339.9	339.2	341.8	345.5	349.8	355.5	361.1	381.1
52.5°	323.5	320.2	318.3	320.9	318.3	320.2	323.5	325.9	330.0	335.7	349.1
55°	287.4	283.6	283.0	282.4	283.0	283.6	287.4	290.5	295.5	299.9	306.1
57.5°	247.0	244.5	240.8	239.1	240.8	244.5	247.0	251.7	257.6	263.4	269.9
60°	218.0	213.0	206.8	206.2	206.8	213.0	218.0	226.2	228.7	237.4	244.9
62.5°	191.5	190.5	189.3	189.1	189.3	190.5	191.5	194.2	197.7	210.4	219.4
65°	168.0	167.5	168.0	168.7	168.0	167.5	168.0	169.3	169.9	171.2	175.0
67.5°	146.4	145.3	144.2	144.7	144.2	145.3	146.4	146.7	148.5	149.2	151.8
70°	130.0	129.3	128.7	128.7	128.7	129.3	130.0	131.2	132.5	133.7	136.8
72.5°	114.0	113.8	113.2	112.7	113.2	113.8	114.0	116.2	117.0	118.2	120.3
75°	91.2	89.9	89.9	89.9	89.9	89.9	91.2	91.8	92.5	94.3	95.6
77.5°	69.5	68.8	68.2	67.8	68.2	68.8	69.5	69.6	70.6	71.0	72.3
80°	55.0	54.4	53.7	53.7	53.7	54.4	55.0	55.6	55.6	57.5	56.8
82.5°	42.0	41.3	41.3	40.8	41.3	41.3	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.2	22.5	23.7	22.5	23.2	22.5	21.9	22.5	23.7	23.7
87.5°	9.5	9.0	9.5	9.0	9.5	9.0	9.5	9.4	9.8	9.6	9.5
90°	14.7	14.9	15.2	15.4	15.2	14.9	14.7	14.4	13.9	13.3	12.7
92.5°	14.9	15.1	15.2	15.4	15.2	15.1	14.9	14.8	14.6	14.3	13.9
95°	24.9	24.8	24.7	24.5	24.7	24.8	24.9	25.0	24.8	24.1	23.6
97.5°	32.3	32.4	32.6	32.8	32.6	32.4	32.3	32.1	31.8	31.3	30.8
100°	37.5	37.7	38.0	38.2	38.0	37.7	37.5	37.3	36.6	35.5	34.6
102.5°	39.9	40.3	40.6	41.0	40.6	40.3	39.9	39.5	38.7	37.4	36.1
105°	41.8	42.4	42.9	43.4	42.9	42.4	41.8	41.3	40.4	39.0	37.6
107.5°	43.1	43.6	44.1	44.6	44.1	43.6	43.1	42.6	43.0	44.5	45.9
110°	43.5	44.1	44.6	45.1	44.6	44.1	43.5	43.0	49.2	61.8	74.5



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	44.4	44.8	45.2	45.6	45.2	44.8	44.4	43.9	66.9	113.2	159.4
115°	74.2	65.1	55.9	46.8	55.9	65.1	74.2	83.3	117.2	175.9	234.7
117.5°	281.1	251.1	221.1	191.1	221.1	251.1	281.1	311.1	333.2	347.4	361.7
120°	399.5	382.4	365.3	348.1	365.3	382.4	399.5	416.6	424.4	422.9	421.4
122.5°	444.4	441.1	437.8	434.5	437.8	441.1	444.4	447.8	449.0	448.0	447.1
125°	486.8	487.2	487.6	488.0	487.6	487.2	486.8	486.5	485.8	484.9	484.0
127.5°	521.5	521.6	521.7	521.8	521.7	521.6	521.5	521.5	520.8	519.5	518.2
130°	543.2	543.1	542.9	542.8	542.9	543.1	543.2	543.3	542.7	541.3	539.9
132.5°	563.7	563.6	563.5	563.4	563.5	563.6	563.7	563.9	563.3	562.1	560.9
135°	593.8	593.5	593.3	593.0	593.3	593.5	593.8	594.0	593.5	592.2	591.0
137.5°	621.3	620.9	620.5	620.0	620.5	620.9	621.3	621.8	621.4	620.1	618.9
140°	638.9	638.2	637.6	637.0	637.6	638.2	638.9	639.5	639.3	638.1	637.0
142.5°	655.3	654.7	654.0	653.4	654.0	654.7	655.3	655.9	655.7	654.7	653.6
145°	678.2	677.6	676.9	676.4	676.9	677.6	678.2	678.9	678.7	677.8	676.9
147.5°	698.1	697.7	697.1	696.5	697.1	697.7	698.1	698.7	698.6	698.0	697.3
150°	710.8	710.1	709.5	708.9	709.5	710.1	710.8	711.4	711.3	710.6	709.8
152.5°	721.9	721.1	720.2	719.3	720.2	721.1	721.9	722.8	722.8	722.0	721.2
155°	737.0	736.1	735.0	734.0	735.0	736.1	737.0	738.0	738.2	737.4	736.6
157.5°	750.3	749.3	748.4	747.3	748.4	749.3	750.3	751.3	751.4	750.5	749.7
160°	757.7	756.8	756.0	755.1	756.0	756.8	757.7	758.6	758.7	758.0	757.2
162.5°	764.8	763.7	762.5	761.5	762.5	763.7	764.8	765.9	766.0	765.1	764.3
165°	773.7	772.9	772.0	771.1	772.0	772.9	773.7	774.6	774.6	773.7	772.9
167.5°	780.6	779.4	778.3	777.1	778.3	779.4	780.6	781.7	781.8	781.0	780.1
170°	784.2	783.1	782.0	780.8	782.0	783.1	784.2	785.4	785.5	784.6	783.7
172.5°	786.9	785.8	784.6	783.5	784.6	785.8	786.9	788.1	788.2	787.3	786.4
175°	789.7	788.5	787.2	785.9	787.2	788.5	789.7	791.0	791.2	790.3	789.5
177.5°	790.2	789.2	788.3	787.4	788.3	789.2	790.2	791.1	791.2	790.4	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1729.1	1736.1	1746.6	1752.6	1762.6	1769.1	1772.6	1779.1	1782.6	1795.1	1808.1
5°	1632.6	1642.5	1660.0	1676.3	1693.8	1711.9	1725.0	1740.0	1753.7	1777.4	1802.5
7.5°	1521.8	1535.7	1562.8	1588.7	1619.2	1644.8	1667.4	1693.0	1715.9	1749.9	1785.3
10°	1438.8	1463.2	1498.8	1523.2	1563.2	1588.8	1624.4	1652.5	1684.4	1729.3	1769.4
12.5°	1367.3	1396.8	1425.4	1459.2	1495.2	1537.8	1577.0	1613.1	1650.9	1697.4	1744.3
15°	1237.7	1280.2	1324.5	1358.9	1407.6	1452.6	1498.2	1546.9	1593.2	1648.8	1710.0
17.5°	1070.7	1120.0	1194.6	1253.4	1310.7	1355.8	1412.3	1471.2	1525.7	1592.8	1660.9
20°	995.2	1031.5	1082.1	1161.5	1247.7	1295.8	1353.2	1418.2	1480.7	1553.8	1626.9
22.5°	934.7	967.0	1007.6	1069.5	1165.7	1231.3	1291.3	1357.2	1429.7	1504.3	1585.4
25°	848.4	870.9	913.4	963.4	1029.6	1137.7	1203.3	1269.5	1348.3	1428.2	1520.7
27.5°	783.6	803.8	831.4	879.1	928.4	1006.0	1110.4	1182.6	1261.0	1351.0	1447.0
30°	734.1	757.8	788.5	822.2	876.0	936.5	1040.9	1124.6	1202.1	1294.5	1397.0
32.5°	698.1	716.9	743.0	777.2	822.0	880.0	963.4	1065.1	1140.6	1238.0	1345.0
35°	639.1	661.0	682.2	714.8	751.0	804.0	867.2	975.9	1050.8	1147.0	1254.5
37.5°	590.5	603.9	627.4	653.1	691.4	731.0	785.7	883.2	964.3	1058.7	1168.7
40°	553.5	570.4	587.9	616.6	647.9	686.0	739.7	812.2	905.3	997.8	1105.2
42.5°	517.6	538.9	557.4	576.7	610.9	649.0	692.8	754.2	849.3	936.8	1041.2
45°	474.2	488.0	507.3	528.6	556.7	589.1	627.9	681.6	772.8	848.4	946.6
47.5°	423.7	443.8	456.5	477.2	503.9	534.9	571.0	617.4	691.2	762.1	853.0
50°	389.2	409.9	428.0	446.7	470.4	500.4	530.4	575.4	634.8	709.1	794.1
52.5°	359.7	377.9	395.5	414.3	437.5	465.0	493.4	533.0	583.8	652.2	734.6
55°	319.3	330.5	348.6	367.4	388.0	414.3	441.7	474.8	518.5	576.0	642.9
57.5°	277.8	290.7	305.2	324.0	344.9	365.0	389.7	419.7	454.2	506.2	563.5
60°	254.3	264.2	276.1	295.5	314.9	333.0	356.8	381.7	414.3	459.2	507.9
62.5°	228.3	237.8	248.7	265.5	284.4	301.0	321.7	348.2	375.8	416.7	459.4
65°	184.9	198.7	209.3	224.3	239.9	257.4	273.6	294.9	319.3	351.7	389.9
67.5°	153.4	160.3	170.2	183.8	199.8	214.8	230.2	246.8	267.9	293.0	323.3
70°	139.3	141.9	143.7	156.8	171.8	186.8	201.2	216.8	234.9	255.5	281.8
72.5°	122.9	125.3	127.7	133.3	145.3	160.3	175.2	186.8	203.9	221.0	242.3
75°	97.4	101.2	103.1	106.2	110.6	120.6	134.4	145.5	155.6	168.7	185.6
77.5°	74.2	76.3	78.4	81.6	84.4	88.9	96.7	106.8	116.2	123.8	135.4
80°	58.7	59.4	61.9	63.1	66.9	70.0	73.7	81.9	91.2	94.3	102.5
82.5°	44.3	44.8	46.9	48.1	49.9	52.5	57.2	59.4	66.7	70.8	76.0
85°	24.4	23.7	25.6	25.6	26.9	28.1	29.4	32.4	34.3	39.4	40.6
87.5°	9.9	9.8	10.1	9.9	9.7	10.4	10.8	10.9	11.7	12.9	14.6
90°	12.1	11.4	10.4	9.4	8.4	7.3	6.1	4.7	3.3	2.0	0.6
92.5°	13.5	13.2	12.7	12.2	11.7	11.3	11.0	11.2	11.3	11.4	11.5
95°	22.9	22.3	21.4	20.5	19.6	18.7	20.4	24.5	28.7	32.9	37.1
97.5°	30.3	29.8	27.7	25.7	23.6	21.6	26.4	38.2	50.1	61.8	73.6
100°	33.5	32.5	30.4	28.2	26.1	23.9	31.6	48.9	66.3	83.6	101.0
102.5°	34.7	33.4	51.4	69.5	87.6	105.6	116.4	120.1	123.8	127.5	131.2
105°	36.2	34.8	69.5	104.0	138.7	173.3	188.7	184.9	181.2	177.3	173.5
107.5°	47.3	48.8	90.3	131.8	173.3	214.8	234.1	231.0	228.0	224.9	221.8
110°	87.2	99.9	136.6	173.2	209.9	246.5	263.5	260.8	258.2	255.5	252.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	205.7	251.9	261.0	270.0	279.1	288.1	291.5	289.1	286.8	284.5	282.1
115°	293.4	352.1	348.9	345.8	342.7	339.5	336.8	334.7	332.5	330.4	328.2
117.5°	375.9	390.0	387.8	385.7	383.5	381.3	379.0	376.6	374.2	371.8	369.4
120°	419.9	418.3	416.0	413.8	411.5	409.2	407.2	405.2	403.3	401.5	399.5
122.5°	446.2	445.3	442.8	440.3	437.8	435.4	433.1	431.1	429.1	427.1	425.1
125°	483.1	482.2	479.9	477.4	475.1	472.6	470.6	469.0	467.3	465.7	464.0
127.5°	516.9	515.6	513.8	512.0	510.2	508.4	506.6	504.8	503.0	501.1	499.3
130°	538.5	537.1	535.7	534.3	532.9	531.5	529.8	527.7	525.7	523.7	521.6
132.5°	559.7	558.6	557.2	555.7	554.3	552.9	551.4	549.7	548.0	546.3	544.5
135°	589.7	588.5	587.3	586.2	585.1	583.9	582.3	580.2	578.2	576.2	574.2
137.5°	617.7	616.4	615.1	613.8	612.5	611.2	609.8	608.5	607.1	605.6	604.2
140°	635.9	634.7	633.2	631.9	630.5	629.1	627.9	626.9	625.8	624.8	623.9
142.5°	652.6	651.6	650.0	648.4	646.8	645.1	643.9	643.0	642.1	641.2	640.3
145°	676.1	675.2	673.0	670.9	668.7	666.6	665.5	665.7	665.9	665.9	666.1
147.5°	696.7	695.9	693.8	691.7	689.6	687.5	686.6	687.1	687.6	688.1	688.5
150°	709.1	708.3	706.3	704.3	702.2	700.2	699.6	700.5	701.4	702.3	703.2
152.5°	720.5	719.7	717.8	715.8	714.0	712.0	711.5	712.5	713.5	714.5	715.5
155°	735.9	735.2	733.6	732.1	730.6	729.0	728.9	730.0	731.2	732.3	733.4
157.5°	748.8	747.9	746.8	745.8	744.7	743.6	743.6	744.5	745.5	746.5	747.5
160°	756.4	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7
162.5°	763.4	762.5	761.9	761.2	760.5	759.9	759.9	760.7	761.5	762.2	763.0
165°	772.0	771.1	770.7	770.3	770.0	769.6	769.7	770.5	771.3	772.0	772.8
167.5°	779.2	778.3	778.0	777.6	777.2	776.9	777.1	777.8	778.6	779.3	780.1
170°	782.9	782.0	781.7	781.5	781.1	780.9	781.1	782.0	782.7	783.4	784.2
172.5°	785.5	784.6	784.4	784.2	783.9	783.7	783.9	784.6	785.5	786.2	786.9
175°	788.6	787.7	787.4	787.2	786.8	786.6	786.9	787.8	788.7	789.6	790.5
177.5°	789.0	788.3	788.2	788.1	788.0	787.9	788.2	789.0	789.6	790.4	791.1
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1808.6	1810.0	1820.1	1824.6	1833.6	1837.0	1841.1	1840.0	1840.0	1842.1	1856.0
5°	1812.5	1825.0	1843.7	1861.8	1879.3	1894.3	1904.3	1914.3	1918.1	1936.2	1952.4
7.5°	1806.0	1829.0	1859.9	1887.6	1920.7	1946.5	1968.1	1987.4	2000.7	2027.0	2054.0
10°	1797.5	1829.9	1864.9	1900.5	1946.1	1980.5	2015.5	2042.4	2051.1	2090.5	2113.0
12.5°	1780.5	1824.0	1868.4	1914.6	1959.2	2006.5	2045.0	2071.8	2102.6	2138.0	2179.5
15°	1755.0	1805.0	1863.0	1922.4	1986.2	2043.6	2084.9	2131.7	2165.4	2204.2	2240.4
17.5°	1718.4	1782.7	1856.6	1925.3	1999.0	2060.8	2117.5	2162.4	2186.2	2208.3	2213.7
20°	1689.4	1758.8	1845.6	1926.8	2000.5	2071.8	2127.9	2165.4	2171.7	2172.3	2139.2
22.5°	1657.9	1736.3	1827.1	1910.3	1998.5	2077.7	2121.5	2137.5	2112.7	2070.4	2006.3
25°	1600.0	1690.6	1796.2	1891.2	1987.4	2062.4	2077.4	2049.3	1962.4	1871.2	1755.6
27.5°	1537.3	1639.2	1752.3	1857.9	1960.4	2006.9	1974.5	1873.2	1716.8	1580.8	1416.0
30°	1491.3	1605.7	1716.9	1834.9	1929.9	1949.9	1875.6	1726.2	1543.8	1338.9	1174.6
32.5°	1438.8	1558.7	1680.9	1803.0	1882.4	1863.0	1740.1	1556.3	1342.4	1140.9	985.6
35°	1363.8	1487.6	1619.4	1741.9	1792.4	1708.1	1524.4	1285.2	1066.5	878.4	771.6
37.5°	1277.2	1412.0	1549.1	1661.5	1657.9	1517.4	1267.1	1020.1	836.3	725.1	649.0
40°	1215.8	1352.0	1500.1	1595.1	1554.4	1371.3	1100.2	867.2	732.9	644.2	588.6
42.5°	1156.8	1293.6	1440.6	1516.0	1445.4	1220.4	950.3	767.7	656.9	587.7	542.6
45°	1056.5	1200.8	1337.0	1378.8	1252.6	1004.6	768.5	636.0	562.3	511.0	479.8
47.5°	958.4	1100.3	1224.7	1225.4	1054.8	814.7	648.2	550.4	487.5	447.8	425.1
50°	898.4	1033.4	1137.7	1121.4	927.8	724.7	579.8	495.5	443.0	412.4	388.6
52.5°	831.0	961.9	1052.2	1006.0	820.4	637.7	518.3	447.4	404.0	377.3	356.1
55°	732.9	849.1	912.8	842.8	669.1	530.4	438.0	382.4	349.8	327.3	309.2
57.5°	636.5	732.4	772.5	691.0	551.1	439.9	370.5	328.7	296.5	280.4	271.0
60°	576.0	657.9	686.0	596.1	479.2	384.8	328.0	289.3	265.5	254.9	245.6
62.5°	516.6	583.4	595.0	512.6	417.8	336.9	288.0	255.3	239.5	229.4	220.5
65°	428.6	476.7	471.1	404.9	330.5	267.4	231.8	211.8	199.9	185.6	169.9
67.5°	352.9	382.2	364.5	314.9	252.3	207.8	184.6	169.4	154.7	141.0	137.5
70°	304.9	321.7	303.0	257.4	206.8	174.3	155.6	137.5	128.7	125.6	119.9
72.5°	258.9	264.8	244.5	205.5	168.3	144.3	126.0	115.9	111.2	108.6	104.9
75°	194.3	190.0	172.4	141.9	116.8	100.6	95.0	91.2	88.1	85.6	83.7
77.5°	136.5	130.0	114.5	94.5	81.4	73.6	70.2	68.2	66.7	65.5	63.6
80°	102.5	98.1	82.5	67.5	61.9	58.1	56.3	53.7	53.7	52.5	50.6
82.5°	75.0	70.1	56.5	49.5	46.4	44.1	42.7	41.3	40.8	41.0	39.6
85°	39.4	31.9	28.1	26.9	25.0	23.7	24.4	23.2	23.2	23.2	22.5
87.5°	12.4	10.2	9.9	9.7	10.4	10.7	10.4	10.6	11.3	10.9	11.5
90°	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1	12.7
92.5°	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5	13.9
95°	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9	23.6
97.5°	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3	30.8
100°	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5	34.6
102.5°	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7	36.1
105°	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2	37.6
107.5°	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3	45.9
110°	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2	74.5





TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7	159.4
115°	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4	234.7
117.5°	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9	361.7
120°	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9	421.4
122.5°	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2	447.1
125°	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1	484.0
127.5°	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9	518.2
130°	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5	539.9
132.5°	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7	560.9
135°	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7	591.0
137.5°	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7	618.9
140°	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9	637.0
142.5°	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6	653.6
145°	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1	676.9
147.5°	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7	697.3
150°	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1	709.8
152.5°	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5	721.2
155°	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9	736.6
157.5°	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8	749.7
160°	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4	757.2
162.5°	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4	764.3
165°	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0	772.9
167.5°	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2	780.1
170°	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9	783.7
172.5°	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5	786.4
175°	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6	789.5
177.5°	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0	789.8
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1861.1	1867.5	1870.5	1870.5	1874.0	1872.6	1871.0
5°	1968.1	1979.9	1982.4	1993.7	2001.7	1999.3	2000.5
7.5°	2074.4	2093.4	2112.4	2121.0	2122.3	2127.4	2129.2
10°	2139.8	2155.5	2184.8	2180.4	2202.3	2214.8	2194.2
12.5°	2202.8	2223.9	2244.3	2249.9	2262.3	2266.3	2258.1
15°	2259.8	2271.0	2272.3	2269.1	2272.9	2269.8	2257.9
17.5°	2206.5	2188.3	2151.3	2133.8	2119.9	2099.5	2091.2
20°	2118.6	2064.8	2002.4	1977.4	1948.0	1890.5	1904.3
22.5°	1928.7	1867.4	1805.0	1732.0	1697.1	1642.7	1639.4
25°	1633.1	1527.5	1411.4	1330.2	1282.6	1228.3	1204.5
27.5°	1269.7	1136.9	1041.6	993.4	949.5	906.4	904.7
30°	1030.9	930.9	857.2	816.0	789.0	770.9	774.7
32.5°	868.9	800.5	750.7	716.5	696.6	683.0	682.7
35°	710.4	663.5	631.6	617.3	602.9	592.9	593.5
37.5°	607.9	579.8	562.1	546.2	537.2	532.3	529.5
40°	555.4	532.3	518.5	509.2	501.7	494.8	493.6
42.5°	514.0	494.8	481.1	473.7	466.7	461.9	460.6
45°	456.1	440.4	428.0	419.9	416.7	412.4	412.4
47.5°	405.7	390.4	380.6	375.5	370.1	367.2	367.1
50°	371.8	359.9	351.1	348.0	343.6	341.8	341.1
52.5°	341.3	332.4	326.1	324.0	322.1	319.8	320.2
55°	299.9	294.9	292.4	290.5	287.4	283.6	286.2
57.5°	265.1	260.8	254.0	248.2	245.3	242.6	243.7
60°	240.5	231.8	223.1	216.1	214.3	208.6	208.6
62.5°	209.5	197.3	186.5	182.7	180.8	178.2	177.7
65°	161.2	156.2	153.7	151.2	149.9	149.9	148.7
67.5°	133.5	131.6	128.8	128.2	126.9	126.6	126.2
70°	118.1	115.6	114.3	113.7	112.4	113.1	111.2
72.5°	103.1	101.1	100.9	99.2	98.5	98.6	97.2
75°	81.2	81.2	80.6	80.0	78.8	78.1	78.8
77.5°	62.5	62.6	61.5	61.4	61.2	61.4	60.7
80°	50.0	50.6	50.0	49.3	48.8	49.3	48.8
82.5°	39.5	38.6	38.5	38.4	38.2	37.8	37.7
85°	22.5	23.2	22.5	21.9	21.9	21.9	22.5
87.5°	11.2	11.3	11.4	11.4	11.5	11.5	11.1
90°	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331849-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)