

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331852-930

Luminaire Tested: **S122RDIW-S1005D710U930-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331852-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D710U930-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 4847.2 lumens
Efficiency: N/A
Efficacy: 81.1 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 59.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	109	109	109	109	102	102	102	102	88	88	88	76	76	76	64	64	64	59
1	100	96	92	89	93	90	87	84	78	76	74	67	66	64	57	56	55	50
2	92	85	79	74	85	79	74	70	69	65	62	60	57	54	51	49	47	43
3	84	75	68	62	78	70	64	59	62	57	53	53	50	47	46	43	41	37
4	77	67	59	53	72	63	56	50	55	50	45	48	44	41	41	38	36	32
5	71	60	52	46	66	56	49	44	50	44	40	43	39	36	38	34	32	29
6	66	54	46	40	61	51	44	38	45	39	35	39	35	31	34	31	28	25
7	61	49	41	36	57	46	39	34	41	35	31	36	32	28	32	28	25	23
8	57	45	37	32	53	42	35	30	38	32	28	33	29	25	29	25	23	21
9	53	41	33	28	50	39	32	27	35	29	25	31	26	23	27	23	21	19
10	50	38	30	26	46	36	29	25	32	27	23	28	24	21	25	22	19	17

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	22291	22291	22291
5°	22376	22013	22135
10°	22207	21653	21469
15°	21951	21010	20404
20°	21596	20094	19086
25°	21235	19053	17808
30°	20734	17984	16168
35°	20243	16821	14728
40°	19751	15616	13061
45°	19173	14266	11556
50°	18580	12901	10073
55°	17973	11431	8653
60°	17270	9884	7182
65°	16466	8306	6541
70°	15512	6845	6014
75°	14342	6238	5608
80°	12664	5579	5114
85°	9948	4390	4390



TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	129.2	2.7
10°-20°	354.8	7.3
20°-30°	498.3	10.3
30°-40°	543.4	11.2
40°-50°	499.6	10.3
50°-60°	392.4	8.1
60°-70°	255.8	5.3
70°-80°	131.9	2.7
80°-90°	37.1	0.8
90°-100°	45.4	0.9
100°-110°	141.1	2.9
110°-120°	241.2	5.0
120°-130°	317.1	6.5
130°-140°	356.0	7.3
140°-150°	349.0	7.2
150°-160°	292.8	6.0
160°-170°	194.2	4.0
170°-180°	67.9	1.4
0°-30°	982.4	20.3
0°-40°	1525.7	31.5
0°-60°	2417.7	49.9
0°-90°	2842.5	58.6
90°-120°	427.7	8.8
90°-150°	1449.8	29.9
90°-180°	2005.0	41.4
0°-180°	4847.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	1381	1381	1381	1381	1381	
5°	1381	1374	1358	1369	1366	131
15°	1313	1298	1257	1234	1221	370
25°	1192	1150	1070	1020	1000	548
35°	1027	961	853	778	747	642
45°	840	753	625	539	506	648
55°	638	539	406	334	307	570
65°	431	329	217	177	171	427
75°	230	145	100	92	90	243
85°	54	29	24	24	24	63
90°	1	8	21	20	20	4
95°	32	37	39	39	38	36
105°	130	132	133	134	134	137
115°	242	245	244	244	242	239
125°	352	357	356	354	353	315
135°	456	462	463	463	461	352
145°	553	557	561	561	559	345
155°	632	634	636	639	637	291
165°	688	687	687	691	688	194
175°	716	714	713	716	713	68
180°	717	717	717	717	717	



TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1385.7	1384.5	1383.4	1382.3	1381.2	1379.4	1377.0	1374.6	1372.1	1369.7	1371.9
5°	1380.6	1379.2	1377.9	1376.5	1375.1	1372.6	1369.0	1365.4	1361.8	1358.2	1360.7
7.5°	1366.4	1364.7	1363.0	1361.2	1359.5	1356.6	1352.3	1348.1	1343.9	1339.7	1340.4
10°	1354.5	1352.5	1350.5	1348.6	1346.6	1342.9	1337.3	1331.8	1326.2	1320.7	1319.9
12.5°	1339.5	1337.0	1334.6	1332.3	1329.9	1325.1	1318.0	1310.9	1303.8	1296.7	1295.2
15°	1313.2	1310.1	1307.1	1304.0	1301.0	1294.7	1285.3	1275.9	1266.4	1256.9	1251.7
17.5°	1280.9	1276.3	1271.6	1267.0	1262.3	1253.9	1241.8	1229.7	1217.6	1205.5	1199.2
20°	1256.9	1251.4	1245.9	1240.3	1234.8	1225.1	1211.1	1197.3	1183.4	1169.5	1162.5
22.5°	1230.9	1224.7	1218.5	1212.4	1206.1	1195.1	1179.5	1163.8	1148.2	1132.5	1123.6
25°	1192.0	1183.1	1174.2	1165.3	1156.4	1142.9	1124.5	1106.2	1087.9	1069.5	1058.2
27.5°	1145.0	1135.4	1125.7	1116.1	1106.4	1091.2	1070.6	1049.9	1029.2	1008.6	995.3
30°	1112.1	1101.5	1091.0	1080.4	1069.8	1053.4	1031.2	1009.0	986.8	964.6	950.4
32.5°	1080.0	1067.7	1055.4	1043.1	1030.7	1013.3	990.6	967.9	945.3	922.6	906.4
35°	1027.0	1012.9	998.7	984.6	970.5	951.1	926.7	902.3	877.8	853.4	835.9
37.5°	974.1	958.5	943.0	927.4	911.9	891.1	865.0	839.0	812.9	786.9	767.7
40°	937.1	920.5	903.8	887.1	870.5	848.6	821.7	794.8	767.8	740.9	721.2
42.5°	899.1	881.6	864.1	846.4	828.9	806.2	778.4	750.6	722.8	695.0	674.6
45°	839.7	821.0	802.4	783.8	765.2	741.4	712.2	683.1	653.9	624.8	605.0
47.5°	781.6	762.0	742.2	722.5	702.8	677.9	647.8	617.7	587.6	557.5	537.9
50°	739.7	720.0	700.3	680.5	660.8	635.7	605.2	574.6	544.0	513.6	494.4
52.5°	698.7	678.1	657.5	636.9	616.3	591.1	561.2	531.3	501.4	471.6	453.1
55°	638.5	616.9	595.2	573.5	551.9	526.0	496.0	466.0	436.1	406.1	389.4
57.5°	576.7	554.6	532.3	510.1	487.9	462.4	433.6	404.7	375.9	347.1	331.8
60°	534.8	512.6	490.3	468.1	445.9	420.5	391.9	363.3	334.7	306.1	292.0
62.5°	493.8	471.6	449.4	427.1	405.0	380.2	352.9	325.6	298.4	271.2	257.6
65°	431.0	408.5	386.1	363.6	341.1	317.4	292.4	267.4	242.4	217.4	208.0
67.5°	370.6	348.3	326.0	303.6	281.3	258.9	236.4	213.9	191.4	168.9	164.6
70°	328.6	307.0	285.3	263.7	242.0	221.6	202.4	183.3	164.1	145.0	142.2
72.5°	288.6	267.8	247.1	226.3	205.5	187.4	172.1	156.7	141.3	126.0	123.6
75°	229.9	210.4	191.0	171.6	152.1	137.7	128.2	118.9	109.4	100.0	98.0
77.5°	172.2	155.2	138.1	121.1	104.0	93.2	88.6	84.1	79.5	75.0	73.9
80°	136.2	122.1	107.9	93.7	79.6	71.1	68.3	65.6	62.8	60.0	58.9
82.5°	103.2	92.1	81.1	70.0	59.0	52.5	50.6	48.8	46.9	45.0	44.4
85°	53.7	47.9	42.1	36.2	30.4	27.1	26.3	25.4	24.5	23.7	23.7
87.5°	16.1	14.7	13.2	11.7	10.3	9.9	10.4	11.1	11.7	12.2	12.0
90°	0.6	2.2	3.8	5.5	7.1	9.4	12.3	15.2	18.2	21.2	20.9
92.5°	10.8	12.0	13.1	14.3	15.5	16.5	17.1	17.9	18.5	19.2	19.3
95°	31.5	32.8	34.2	35.5	36.9	37.7	37.9	38.2	38.5	38.7	38.7
97.5°	57.5	58.6	59.8	61.0	62.2	63.0	63.6	64.1	64.6	65.1	65.1
100°	76.8	77.9	79.0	80.1	81.1	81.9	82.3	82.7	83.1	83.5	83.5
102.5°	97.2	98.0	98.9	99.7	100.6	101.3	101.8	102.3	102.8	103.3	103.5
105°	130.0	130.4	130.9	131.3	131.7	132.0	132.3	132.6	132.8	133.1	133.4
107.5°	163.2	163.8	164.4	165.0	165.6	165.9	165.9	165.9	165.9	165.9	166.0
110°	184.5	185.3	186.1	186.9	187.8	188.2	188.2	188.2	188.2	188.2	188.2



TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	207.7	208.6	209.4	210.2	211.0	211.3	211.2	211.1	211.0	210.9	210.6
115°	242.0	242.8	243.6	244.4	245.2	245.5	245.2	244.9	244.7	244.4	244.3
117.5°	276.1	277.2	278.3	279.3	280.4	280.5	279.8	279.1	278.3	277.6	277.3
120°	298.9	299.9	301.0	302.1	303.1	303.1	302.1	301.0	299.9	298.9	298.9
122.5°	319.7	321.0	322.3	323.5	324.8	325.1	324.3	323.6	322.9	322.1	321.8
125°	352.1	353.4	354.5	355.7	356.9	357.3	356.9	356.5	356.1	355.7	355.3
127.5°	383.7	385.2	386.8	388.2	389.8	390.4	389.9	389.4	388.9	388.4	387.9
130°	403.5	405.3	407.0	408.8	410.5	411.2	411.0	410.7	410.4	410.2	409.9
132.5°	425.8	427.2	428.7	430.1	431.5	432.3	432.3	432.4	432.4	432.4	431.9
135°	455.6	457.1	458.5	460.0	461.5	462.4	462.6	462.9	463.2	463.4	463.3
137.5°	486.9	488.1	489.3	490.6	491.7	492.5	492.8	493.3	493.6	493.9	493.8
140°	505.8	507.0	508.2	509.4	510.6	511.5	512.3	512.9	513.6	514.2	514.2
142.5°	525.1	526.4	527.6	528.8	529.9	530.8	531.2	531.7	532.1	532.6	532.7
145°	552.9	553.9	554.8	555.8	556.8	557.6	558.4	559.2	560.0	560.8	560.9
147.5°	577.8	578.9	580.0	581.1	582.3	583.1	583.7	584.2	584.7	585.3	585.5
150°	594.7	595.5	596.3	597.1	597.9	598.6	599.2	599.7	600.2	600.8	601.2
152.5°	609.7	610.5	611.3	612.1	612.9	613.7	614.3	615.0	615.6	616.3	616.8
155°	632.2	632.6	633.0	633.4	633.8	634.2	634.6	635.0	635.4	635.9	636.5
157.5°	651.4	651.8	652.0	652.2	652.6	652.8	653.1	653.3	653.5	653.8	654.7
160°	663.1	663.3	663.6	663.9	664.1	664.4	664.5	664.6	664.7	664.9	665.7
162.5°	673.7	673.8	673.8	673.8	673.9	674.0	674.2	674.3	674.4	674.6	675.5
165°	687.9	687.7	687.6	687.5	687.4	687.3	687.3	687.3	687.3	687.3	688.2
167.5°	699.8	699.4	699.0	698.5	698.1	697.9	697.9	697.8	697.8	697.8	698.7
170°	706.0	705.6	705.2	704.8	704.4	704.2	704.0	703.8	703.8	703.6	704.6
172.5°	710.4	710.0	709.6	709.1	708.7	708.5	708.3	708.3	708.1	707.9	708.9
175°	715.7	715.3	714.9	714.5	714.1	713.8	713.5	713.2	713.0	712.7	713.6
177.5°	717.9	717.5	717.2	716.9	716.6	716.3	716.1	715.9	715.7	715.4	716.1
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9



TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6	1380.6
2.5°	1374.1	1376.3	1378.6	1379.4	1379.0	1378.6	1378.1	1377.7
5°	1363.2	1365.7	1368.2	1369.0	1368.2	1367.3	1366.5	1365.7
7.5°	1341.1	1341.8	1342.6	1342.2	1340.8	1339.3	1337.9	1336.4
10°	1319.0	1318.2	1317.4	1316.1	1314.4	1312.8	1311.1	1309.5
12.5°	1293.7	1292.2	1290.7	1288.6	1285.8	1283.0	1280.3	1277.5
15°	1246.4	1241.1	1235.8	1231.8	1229.1	1226.3	1223.5	1220.7
17.5°	1192.9	1186.7	1180.4	1174.8	1170.1	1165.3	1160.5	1155.8
20°	1155.6	1148.7	1141.7	1135.2	1129.1	1123.0	1116.9	1110.8
22.5°	1114.7	1105.7	1096.7	1090.0	1085.5	1080.9	1076.4	1071.8
25°	1046.8	1035.4	1024.0	1016.3	1012.0	1007.9	1003.7	999.6
27.5°	982.0	968.7	955.4	945.5	938.9	932.3	925.7	919.1
30°	936.3	922.1	907.9	897.2	889.7	882.2	874.7	867.2
32.5°	890.3	874.2	857.9	846.4	839.4	832.3	825.2	818.2
35°	818.4	801.0	783.4	771.6	765.5	759.4	753.3	747.2
37.5°	748.4	729.1	709.8	696.7	689.7	682.7	675.7	668.7
40°	701.5	681.8	662.1	648.7	641.4	634.1	627.0	619.7
42.5°	654.2	633.8	613.4	599.7	592.7	585.7	578.8	571.8
45°	585.3	565.6	545.8	532.7	526.0	519.3	512.7	506.1
47.5°	518.3	498.7	479.1	466.3	460.2	454.2	448.1	442.1
50°	475.2	456.1	436.9	424.4	418.6	412.7	406.9	401.0
52.5°	434.6	416.0	397.6	385.6	380.3	374.9	369.5	364.1
55°	372.8	356.1	339.4	328.5	323.2	317.9	312.7	307.4
57.5°	316.6	301.3	286.0	276.1	271.7	267.3	262.9	258.4
60°	277.8	263.7	249.5	240.2	235.7	231.3	226.8	222.4
62.5°	244.2	230.6	217.2	209.0	206.4	203.7	201.1	198.4
65°	198.5	189.1	179.6	174.5	173.7	172.8	172.0	171.2
67.5°	160.3	156.0	151.6	149.0	148.1	147.2	146.3	145.4
70°	139.4	136.6	133.9	131.9	130.8	129.6	128.6	127.4
72.5°	121.3	119.0	116.6	115.1	114.5	113.8	113.1	112.4
75°	96.0	94.2	92.2	91.1	90.8	90.5	90.3	89.9
77.5°	72.7	71.7	70.5	69.7	69.3	68.9	68.4	68.0
80°	57.7	56.7	55.5	55.0	55.0	55.0	55.0	55.0
82.5°	43.6	43.0	42.3	42.0	42.0	42.0	42.0	42.0
85°	23.7	23.7	23.7	23.7	23.7	23.7	23.7	23.7
87.5°	11.7	11.4	11.1	11.0	11.0	11.1	11.1	11.1
90°	20.6	20.4	20.1	20.1	20.1	20.3	20.5	20.5
92.5°	19.3	19.4	19.5	19.5	19.5	19.6	19.6	19.6
95°	38.7	38.7	38.7	38.6	38.3	38.1	37.7	37.5
97.5°	65.1	65.1	65.1	65.1	65.1	65.1	65.0	65.0
100°	83.5	83.5	83.5	83.4	83.3	83.2	83.0	82.9
102.5°	103.5	103.6	103.8	103.8	103.6	103.5	103.4	103.2
105°	133.6	133.9	134.2	134.3	134.3	134.3	134.3	134.3
107.5°	166.1	166.2	166.3	166.1	165.4	164.9	164.2	163.6
110°	188.2	188.2	188.2	187.9	187.5	187.1	186.7	186.4



TEST NUMBER: P331852-930

CATALOG NUMBER: S122RDIW-S1005D710U930-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	210.3	209.9	209.6	209.3	209.0	208.7	208.4	208.1
115°	244.2	244.0	243.9	243.6	243.2	242.8	242.4	242.0
117.5°	277.0	276.6	276.3	275.9	275.5	275.1	274.7	274.3
120°	298.9	298.9	298.9	298.6	298.2	297.8	297.4	297.0
122.5°	321.5	321.1	320.8	320.5	320.2	319.9	319.6	319.4
125°	354.9	354.5	354.1	353.8	353.8	353.6	353.4	353.4
127.5°	387.4	386.9	386.5	386.0	385.6	385.1	384.7	384.3
130°	409.7	409.4	409.1	408.7	408.1	407.6	407.1	406.6
132.5°	431.3	430.6	430.1	429.6	429.2	428.7	428.3	427.9
135°	463.2	463.0	462.9	462.6	462.2	461.8	461.4	461.0
137.5°	493.7	493.6	493.5	493.2	492.6	492.1	491.5	491.0
140°	514.2	514.2	514.2	514.0	513.5	512.9	512.3	511.8
142.5°	532.9	533.0	533.0	532.9	532.3	531.7	531.2	530.7
145°	561.1	561.3	561.3	561.2	560.6	560.1	559.5	559.1
147.5°	585.9	586.1	586.4	586.4	585.9	585.3	584.8	584.3
150°	601.5	601.9	602.3	602.3	601.9	601.5	601.2	600.8
152.5°	617.3	617.8	618.3	618.3	617.8	617.3	616.8	616.3
155°	637.2	637.9	638.5	638.7	638.3	637.9	637.5	637.1
157.5°	655.6	656.5	657.4	657.5	656.9	656.2	655.6	654.9
160°	666.5	667.3	668.1	668.2	667.7	667.2	666.7	666.1
162.5°	676.4	677.4	678.2	678.3	677.7	677.1	676.5	675.8
165°	689.2	690.1	691.0	691.2	690.5	689.8	689.2	688.5
167.5°	699.7	700.6	701.6	701.6	701.0	700.3	699.6	698.9
170°	705.5	706.5	707.4	707.4	706.6	705.8	705.0	704.2
172.5°	709.9	710.8	711.8	711.8	711.0	710.2	709.4	708.6
175°	714.5	715.5	716.5	716.5	715.7	714.9	714.1	713.3
177.5°	716.7	717.4	718.0	718.0	717.4	716.7	716.1	715.4
180°	716.9	716.9	716.9	716.9	716.9	716.9	716.9	716.9

(END OF REPORT)