

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331798-935

Luminaire Tested: **S122RDIW-S485D1240U935-4F0-1E-UDD-A1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331798-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U935-4F0-1E-UDD-A1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5303.7 lumens
Efficiency: N/A
Efficacy: 98.6 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

Luminous Intensity Polar Plot





TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20					20					20					20					20	
RC	80					70					50					30					10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	50	30	10	0	
RCR																						
0	102	102	102	102	92	92	92	92	72	72	72	54	54	54	38	38	38	30				
1	94	90	86	83	84	81	78	75	64	62	60	48	47	46	34	34	33	26				
2	86	79	73	68	77	71	66	62	57	53	50	43	41	39	31	29	28	23				
3	79	70	63	58	70	63	57	53	50	46	43	39	36	34	28	26	25	20				
4	72	62	55	49	65	56	50	45	45	41	37	35	32	29	25	23	22	18				
5	66	55	48	42	59	50	44	39	40	36	32	31	28	26	23	21	19	16				
6	61	50	42	37	55	45	39	34	37	32	28	28	25	23	21	19	17	14				
7	57	45	38	32	51	41	34	30	33	29	25	26	23	20	19	17	16	13				
8	53	41	34	29	47	37	31	27	30	26	22	24	21	18	18	16	14	12				
9	49	37	30	26	44	34	28	24	28	23	20	22	19	16	17	14	13	11				
10	46	34	27	23	41	31	25	21	26	21	18	20	17	15	15	13	12	10				

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	14941	14941	14941	14941
5°	16686	15034	13331	15034
10°	18513	14929	11555	14929
15°	19423	14710	9105	14710
20°	16838	14385	7878	14385
25°	11043	13942	7035	13942
30°	7433	13403	6367	13403
35°	6022	12727	5742	12727
40°	5354	11989	5313	11989
45°	4845	11125	4743	11125
50°	4411	10263	4393	10263
55°	4144	9315	4090	9315
60°	3468	8441	3426	8441
65°	2923	7664	3316	7664
70°	2705	6845	3125	6845
75°	2533	5958	2888	5958
80°	2334	4900	2566	4900
85°	2130	3872	2260	3872



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	87.7	1.7
10°-20°	244.4	4.6
20°-30°	315.0	5.9
30°-40°	299.3	5.6
40°-50°	256.4	4.8
50°-60°	195.3	3.7
60°-70°	123.4	2.3
70°-80°	61.6	1.2
80°-90°	21.3	0.4
90°-100°	83.8	1.6
100°-110°	260.4	4.9
110°-120°	445.0	8.4
120°-130°	585.3	11.0
130°-140°	656.9	12.4
140°-150°	644.1	12.1
150°-160°	540.2	10.2
160°-170°	358.3	6.8
170°-180°	125.2	2.4
0°-30°	647.1	12.2
0°-40°	946.4	17.8
0°-60°	1398.1	26.4
0°-90°	1604.5	30.3
90°-120°	789.2	14.9
90°-150°	2675.4	50.4
90°-180°	3699.0	69.7
0°-180°	5303.7	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	925	925	925	925	925	
5°	1030	928	822	928	1030	102
15°	1162	880	545	880	1162	313
25°	620	783	395	783	620	294
35°	306	646	291	646	306	195
45°	212	487	208	487	212	164
55°	147	331	145	331	147	129
65°	76	201	87	201	76	78
75°	41	96	46	96	41	43
85°	12	21	12	21	12	13
90°	38	1	38	1	38	17
95°	69	58	69	58	69	77
105°	248	240	248	240	248	261
115°	447	447	447	447	447	441
125°	652	650	652	650	652	581
135°	851	841	851	841	851	655
145°	1032	1020	1032	1020	1032	644
155°	1176	1167	1176	1167	1176	541
165°	1270	1269	1270	1269	1270	358
175°	1316	1321	1316	1321	1316	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	962.9	963.7	964.5	962.7	962.7	961.1	957.8	955.2	948.0	946.9	946.9
5°	1029.5	1028.9	1030.2	1026.0	1020.2	1018.9	1012.8	1004.8	996.4	987.1	985.2
7.5°	1095.8	1094.8	1092.3	1091.5	1087.1	1077.4	1067.6	1057.0	1043.2	1029.6	1022.8
10°	1129.2	1139.8	1133.4	1122.1	1124.4	1109.3	1101.2	1087.4	1075.8	1055.6	1051.1
12.5°	1162.1	1166.3	1164.2	1157.9	1155.0	1144.5	1133.7	1121.6	1100.3	1082.1	1066.3
15°	1162.0	1168.1	1169.8	1167.8	1169.4	1168.7	1163.0	1153.0	1134.4	1114.4	1097.1
17.5°	1076.2	1080.5	1091.0	1098.1	1107.2	1126.2	1135.6	1139.3	1136.4	1125.1	1112.8
20°	980.0	972.9	1002.5	1017.6	1030.5	1062.6	1090.3	1100.9	1117.9	1117.7	1114.4
22.5°	843.7	845.3	873.4	891.3	928.9	961.0	992.6	1032.5	1065.5	1087.3	1100.0
25°	619.9	632.1	660.1	684.5	726.3	786.2	840.5	903.5	962.9	1010.0	1054.6
27.5°	465.5	466.5	488.6	511.3	536.1	585.0	653.5	728.8	813.6	883.5	964.0
30°	398.7	396.7	406.1	419.9	441.2	479.1	530.5	604.5	689.1	794.5	888.4
32.5°	351.4	351.5	358.5	368.8	386.3	411.9	447.2	507.2	587.2	690.9	800.9
35°	305.5	305.1	310.3	317.7	325.0	341.5	365.6	397.1	452.1	548.9	661.4
37.5°	272.5	274.0	276.5	281.1	289.2	298.3	312.9	334.0	373.2	430.4	525.0
40°	254.0	254.7	258.2	262.1	266.9	274.0	285.9	302.9	331.5	377.1	446.3
42.5°	237.0	237.6	240.2	243.7	247.5	254.7	264.5	279.2	302.5	338.0	395.1
45°	212.2	212.2	214.5	216.0	220.2	226.7	234.7	246.9	263.0	289.4	327.4
47.5°	188.9	189.0	190.5	193.2	195.9	200.9	208.8	218.8	230.5	250.9	283.3
50°	175.6	175.9	176.8	179.1	180.7	185.2	191.3	200.0	212.2	228.0	254.9
52.5°	164.7	164.5	165.7	166.8	167.8	171.1	175.6	183.3	194.2	207.9	230.3
55°	147.2	145.9	147.9	149.5	150.5	151.8	154.3	159.2	168.5	180.0	196.7
57.5°	125.4	124.8	126.2	127.7	130.7	134.2	136.4	139.5	144.3	152.6	169.2
60°	107.4	107.4	110.3	111.2	114.8	119.2	123.8	126.4	131.2	136.6	148.9
62.5°	91.4	91.7	93.1	94.0	96.0	101.5	107.9	113.5	118.0	123.3	131.4
65°	76.5	77.1	77.1	77.8	79.1	80.4	82.9	87.5	95.5	102.9	109.0
67.5°	64.9	65.2	65.3	66.0	66.3	67.7	68.7	70.8	72.6	79.6	87.2
70°	57.3	58.2	57.9	58.5	58.8	59.5	60.8	61.7	64.7	66.2	70.8
72.5°	50.0	50.7	50.7	51.1	51.9	52.0	53.0	54.0	55.9	57.3	59.7
75°	40.6	40.2	40.6	41.2	41.5	41.8	41.8	43.0	44.1	45.4	46.9
77.5°	31.3	31.6	31.5	31.6	31.6	32.2	32.1	32.7	33.7	34.4	35.1
80°	25.1	25.4	25.1	25.4	25.7	26.0	25.7	26.0	27.0	27.6	27.6
82.5°	19.5	19.5	19.7	19.7	19.8	19.9	20.3	20.4	21.1	20.9	21.2
85°	11.5	11.3	11.3	11.3	11.5	11.9	11.5	11.5	11.9	11.9	11.9
87.5°	11.7	11.9	11.9	11.8	11.8	11.8	11.9	12.2	12.1	12.5	11.1
90°	38.0	37.7	37.5	37.2	36.9	37.1	37.6	38.1	38.6	39.1	33.6
92.5°	36.2	36.2	36.1	36.0	36.0	35.9	35.8	35.7	35.6	35.5	34.2
95°	69.2	69.7	70.2	70.7	71.2	71.5	71.5	71.5	71.5	71.5	70.9
97.5°	119.9	119.9	120.0	120.0	120.1	120.1	120.1	120.1	120.1	120.1	119.2
100°	152.9	153.2	153.4	153.7	153.9	154.0	154.0	154.0	154.0	154.0	153.3
102.5°	190.5	190.7	191.0	191.2	191.5	191.5	191.3	191.1	190.9	190.7	189.8
105°	247.9	247.9	247.9	247.9	247.9	247.6	247.1	246.6	246.1	245.6	245.1
107.5°	301.9	303.0	304.2	305.3	306.4	306.9	306.7	306.5	306.3	306.1	306.1
110°	343.9	344.6	345.3	346.1	346.8	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	384.0	384.6	385.1	385.6	386.2	386.8	387.4	388.0	388.6	389.2	389.3
115°	446.6	447.3	448.1	448.8	449.5	450.0	450.3	450.6	450.8	451.0	451.5
117.5°	506.2	507.0	507.6	508.4	509.2	509.8	510.4	511.0	511.6	512.2	513.6
120°	548.2	548.9	549.7	550.4	551.1	551.5	551.5	551.5	551.5	551.5	553.5
122.5°	589.3	589.8	590.3	590.9	591.4	592.0	592.6	593.2	593.7	594.3	595.7
125°	651.9	652.2	652.5	652.7	653.0	653.5	654.2	655.0	655.7	656.4	657.2
127.5°	709.1	710.0	710.8	711.5	712.3	713.2	714.0	715.0	715.8	716.7	717.6
130°	750.2	751.2	752.3	753.2	754.2	754.9	755.4	756.0	756.4	756.9	757.4
132.5°	789.5	790.3	791.1	791.9	792.7	793.7	794.7	795.8	796.9	798.0	797.9
135°	850.7	851.4	852.2	852.9	853.7	854.2	854.5	854.7	854.9	855.1	854.7
137.5°	906.1	907.1	908.1	909.0	910.1	910.7	910.9	911.0	911.3	911.5	910.8
140°	944.5	945.5	946.5	947.4	948.5	948.9	948.9	948.9	948.9	948.9	947.7
142.5°	979.3	980.3	981.3	982.3	983.3	983.7	983.5	983.3	983.1	982.9	982.1
145°	1031.6	1032.6	1033.5	1034.6	1035.5	1035.9	1035.7	1035.4	1035.2	1034.9	1033.5
147.5°	1078.2	1079.2	1080.1	1081.1	1082.0	1082.2	1081.7	1081.1	1080.6	1080.0	1079.0
150°	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6	1107.6
152.5°	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2	1136.0
155°	1175.6	1176.3	1177.1	1177.8	1178.5	1178.3	1177.1	1175.9	1174.6	1173.4	1172.6
157.5°	1208.6	1209.8	1211.0	1212.2	1213.4	1213.1	1211.4	1209.8	1208.1	1206.4	1205.9
160°	1229.2	1230.2	1231.1	1232.2	1233.1	1232.9	1231.4	1229.9	1228.4	1226.9	1226.7
162.5°	1247.1	1248.2	1249.4	1250.6	1251.8	1251.5	1249.8	1248.2	1246.5	1244.8	1244.6
165°	1270.5	1271.7	1273.0	1274.2	1275.4	1275.2	1273.4	1271.7	1270.0	1268.3	1268.3
167.5°	1289.7	1291.0	1292.3	1293.6	1294.9	1294.6	1292.9	1291.2	1289.4	1287.6	1287.7
170°	1299.5	1301.0	1302.5	1304.0	1305.4	1305.4	1303.6	1301.8	1300.1	1298.4	1298.6
172.5°	1307.5	1309.1	1310.5	1312.0	1313.5	1313.4	1311.6	1309.9	1308.2	1306.4	1306.7
175°	1316.2	1317.8	1319.2	1320.7	1322.2	1322.1	1320.3	1318.6	1316.9	1315.1	1315.6
177.5°	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3	1320.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	947.4	945.5	943.7	939.0	936.7	931.5	930.7	930.5	923.9	917.4	915.6
5°	980.0	974.9	967.2	958.1	948.8	939.2	932.7	927.6	914.7	902.5	895.4
7.5°	1012.8	1001.8	988.4	971.4	957.2	941.2	929.4	918.8	900.5	883.0	871.2
10°	1037.2	1019.3	1001.6	978.1	959.8	941.8	925.1	910.6	890.0	866.9	850.4
12.5°	1052.4	1032.6	1008.2	985.3	961.6	938.7	916.3	897.7	873.6	849.6	830.1
15°	1073.0	1051.7	1022.2	989.4	958.8	928.9	903.2	880.0	848.5	819.9	796.1
17.5°	1089.8	1060.5	1028.7	990.8	955.5	917.5	884.3	854.7	819.7	785.1	757.2
20°	1095.1	1066.2	1029.5	991.6	949.8	905.1	869.4	837.2	799.6	762.0	729.9
22.5°	1091.7	1069.3	1028.5	983.1	940.3	893.5	853.3	815.9	774.2	735.8	698.5
25°	1069.1	1061.4	1022.8	973.3	924.4	870.0	823.5	782.6	735.0	693.9	653.3
27.5°	1016.2	1032.9	1008.9	956.1	901.8	843.5	791.2	744.7	695.3	648.9	608.6
30°	965.3	1003.5	993.2	944.3	883.6	826.3	767.5	718.9	666.2	618.6	578.8
32.5°	895.5	958.7	968.8	927.9	865.0	802.1	740.5	692.2	637.1	586.9	548.1
35°	784.5	879.1	922.5	896.4	833.4	765.6	701.9	645.7	590.3	540.8	502.2
37.5°	652.1	780.8	853.3	855.1	797.2	726.7	657.4	601.5	544.8	496.3	454.5
40°	566.2	705.8	800.0	820.9	772.0	695.8	625.7	568.8	513.5	465.9	418.0
42.5°	489.0	628.1	743.9	780.2	741.4	665.7	595.4	535.9	482.1	437.0	388.1
45°	395.5	517.0	644.6	709.6	688.1	617.9	543.7	487.2	436.6	397.7	350.8
47.5°	333.6	419.3	542.8	630.7	630.3	566.3	493.3	439.0	392.2	355.8	317.7
50°	298.3	373.0	477.5	577.1	585.5	531.8	462.4	408.6	365.0	326.7	296.1
52.5°	266.7	328.2	422.1	517.7	541.5	495.0	427.7	378.1	335.6	300.4	274.2
55°	225.4	272.9	344.4	433.8	469.8	437.0	377.1	330.9	296.4	266.9	244.4
57.5°	190.6	226.4	283.6	355.6	397.5	376.9	327.6	290.0	260.5	233.8	216.0
60°	168.8	198.0	246.6	306.8	353.0	338.5	296.4	261.4	236.3	213.2	196.5
62.5°	148.3	173.4	215.0	263.8	306.3	300.2	265.9	236.4	214.5	193.4	179.3
65°	119.2	137.6	170.0	208.4	242.5	245.3	220.6	200.6	181.0	164.3	151.8
67.5°	95.0	106.9	129.8	162.0	187.6	196.7	181.6	166.3	150.8	137.8	127.0
70°	80.1	89.7	106.4	132.5	155.9	165.6	156.9	145.0	131.5	120.9	111.6
72.5°	64.9	74.3	86.6	105.7	125.9	136.3	133.3	124.7	113.7	105.0	96.2
75°	48.9	51.7	60.1	73.0	88.8	97.7	100.0	95.5	86.8	80.1	74.9
77.5°	36.2	37.9	41.8	48.6	58.9	66.9	70.3	69.7	63.7	59.8	55.0
80°	28.9	29.9	31.9	34.7	42.4	50.5	52.7	52.7	48.6	46.9	42.1
82.5°	22.0	22.7	23.8	25.5	29.1	36.1	38.6	39.1	36.4	34.4	30.6
85°	12.6	12.2	12.8	13.9	14.5	16.4	20.2	20.9	20.2	17.7	16.7
87.5°	10.0	9.2	8.1	7.0	6.6	6.3	7.0	7.7	7.2	7.1	7.1
90°	28.2	22.7	17.2	13.0	10.1	7.1	4.1	1.1	4.1	7.1	10.1
92.5°	32.9	31.6	30.3	28.6	26.4	24.3	22.0	19.9	22.0	24.3	26.4
95°	70.4	70.0	69.5	68.0	65.5	63.0	60.5	58.0	60.5	63.0	65.5
97.5°	118.2	117.3	116.3	114.8	112.6	110.5	108.2	106.1	108.2	110.5	112.6
100°	152.6	151.8	151.1	149.7	147.7	145.8	143.8	141.8	143.8	145.8	147.7
102.5°	188.8	187.9	186.9	185.6	184.1	182.4	180.9	179.3	180.9	182.4	184.1
105°	244.6	244.1	243.7	243.0	242.3	241.5	240.7	240.0	240.7	241.5	242.3
107.5°	306.1	306.1	306.1	305.6	304.4	303.4	302.3	301.2	302.3	303.4	304.4
110°	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5	342.0	343.5	345.0



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	389.6	389.8	389.9	389.3	387.9	386.3	384.9	383.4	384.9	386.3	387.9
115°	452.0	452.5	453.0	452.5	451.0	449.5	448.1	446.6	448.1	449.5	451.0
117.5°	515.0	516.3	517.8	517.5	515.5	513.5	511.5	509.5	511.5	513.5	515.5
120°	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	553.5	555.5	557.5
122.5°	597.2	598.6	599.9	599.4	597.0	594.7	592.3	589.9	592.3	594.7	597.0
125°	658.0	658.7	659.4	658.7	656.4	654.2	651.9	649.7	651.9	654.2	656.4
127.5°	718.5	719.5	720.3	719.4	716.5	713.7	710.8	708.0	710.8	713.7	716.5
130°	757.9	758.5	758.9	757.5	754.3	751.1	747.9	744.7	747.9	751.1	754.3
132.5°	797.8	797.7	797.6	796.3	793.6	791.0	788.3	785.7	788.3	791.0	793.6
135°	854.2	853.7	853.2	851.6	848.9	846.1	843.3	840.7	843.3	846.1	848.9
137.5°	910.2	909.5	908.9	907.4	905.2	902.9	900.7	898.5	900.7	902.9	905.2
140°	946.5	945.2	944.0	942.3	940.0	937.8	935.6	933.3	935.6	937.8	940.0
142.5°	981.2	980.3	979.5	978.0	975.8	973.5	971.3	969.1	971.3	973.5	975.8
145°	1031.9	1030.4	1029.0	1027.3	1025.6	1023.9	1022.2	1020.4	1022.2	1023.9	1025.6
147.5°	1078.1	1077.0	1076.1	1074.5	1072.5	1070.3	1068.2	1066.2	1068.2	1070.3	1072.5
150°	1106.6	1105.6	1104.7	1103.4	1101.9	1100.4	1098.9	1097.4	1098.9	1100.4	1101.9
152.5°	1134.8	1133.6	1132.4	1131.1	1129.5	1128.1	1126.6	1125.2	1126.6	1128.1	1129.5
155°	1171.8	1171.1	1170.4	1169.7	1168.9	1168.1	1167.4	1166.7	1167.4	1168.1	1168.9
157.5°	1205.5	1205.1	1204.6	1204.1	1203.7	1203.2	1202.6	1202.1	1202.6	1203.2	1203.7
160°	1226.4	1226.2	1226.0	1225.5	1225.1	1224.6	1224.1	1223.6	1224.1	1224.6	1225.1
162.5°	1244.3	1244.1	1243.8	1243.6	1243.5	1243.5	1243.4	1243.2	1243.4	1243.5	1243.5
165°	1268.3	1268.3	1268.3	1268.3	1268.6	1268.9	1269.1	1269.4	1269.1	1268.9	1268.6
167.5°	1287.8	1287.8	1287.9	1288.2	1289.0	1289.8	1290.5	1291.2	1290.5	1289.8	1289.0
170°	1298.9	1299.2	1299.4	1299.9	1300.6	1301.4	1302.1	1302.9	1302.1	1301.4	1300.6
172.5°	1306.9	1307.2	1307.4	1307.9	1308.6	1309.4	1310.2	1310.9	1310.2	1309.4	1308.6
175°	1316.1	1316.6	1317.2	1317.8	1318.4	1319.2	1320.0	1320.7	1320.0	1319.2	1318.4
177.5°	1321.0	1321.5	1321.9	1322.3	1322.9	1323.5	1324.1	1324.7	1324.1	1323.5	1322.9
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	912.2	910.4	907.1	902.0	898.9	893.5	889.8	891.9	892.4	891.9	891.4
5°	887.8	881.0	871.7	862.6	854.3	845.3	840.2	837.9	833.4	830.9	829.6
7.5°	858.1	846.4	833.3	817.6	804.3	790.3	783.2	779.6	770.4	765.4	761.0
10°	835.9	817.6	804.4	783.9	771.4	753.0	740.5	740.8	728.2	721.2	716.0
12.5°	811.6	791.4	769.5	751.0	733.6	718.8	703.7	697.6	684.2	677.4	663.6
15°	771.0	747.5	724.4	699.3	681.7	658.8	637.0	610.3	588.8	570.1	564.9
17.5°	726.8	697.8	674.5	645.1	614.8	576.4	551.0	535.5	522.5	512.7	505.4
20°	696.5	666.8	642.1	597.7	556.9	530.8	512.2	500.3	486.8	476.2	470.4
22.5°	664.5	633.7	599.9	550.4	518.6	497.7	481.0	467.4	458.2	450.0	444.7
25°	619.2	585.5	529.9	495.8	470.1	448.2	436.6	428.3	418.6	407.3	402.3
27.5°	571.4	517.7	477.8	452.5	427.9	413.7	403.3	390.8	382.2	377.1	371.8
30°	535.6	482.0	450.8	423.1	405.8	390.0	377.8	370.7	362.4	353.7	350.2
32.5°	495.8	452.9	423.0	400.0	382.4	368.9	359.3	347.8	341.8	336.5	329.1
35°	446.3	413.8	386.5	367.8	351.1	340.2	328.9	322.2	311.3	306.8	303.8
37.5°	404.3	376.2	355.8	336.1	322.9	310.8	303.9	293.2	288.4	282.1	276.0
40°	380.6	353.0	333.5	317.4	302.6	293.5	284.9	276.2	269.1	266.2	258.8
42.5°	356.5	334.0	314.4	296.8	286.9	277.3	266.4	260.0	252.6	248.0	243.4
45°	323.1	303.2	286.5	272.0	261.1	251.2	244.0	233.4	229.3	219.9	216.0
47.5°	293.8	275.3	259.3	245.6	234.9	228.4	218.1	209.7	203.1	197.3	192.4
50°	272.9	257.5	242.1	229.9	220.2	210.9	200.4	196.1	185.8	183.0	180.0
52.5°	253.9	239.3	225.2	213.2	203.5	194.5	185.1	179.7	172.7	169.8	167.7
55°	227.3	213.2	199.7	189.1	179.4	170.0	164.3	157.6	154.3	152.1	149.5
57.5°	200.5	187.9	177.5	166.8	157.0	149.6	142.9	138.9	135.5	132.6	129.5
60°	183.6	171.3	162.0	152.1	142.2	136.0	130.9	126.1	122.2	117.7	116.4
62.5°	165.6	154.9	146.4	136.6	127.9	122.3	117.5	113.0	108.3	101.8	100.0
65°	140.9	132.5	123.5	115.5	107.7	102.3	95.1	90.1	88.1	87.5	87.1
67.5°	118.5	110.6	102.8	94.6	87.6	82.5	78.9	78.1	76.8	76.4	75.5
70°	103.5	96.2	88.4	80.7	74.0	73.0	71.7	70.4	68.8	68.2	67.5
72.5°	90.1	82.5	74.8	68.6	65.7	64.5	63.2	61.9	60.9	60.2	59.8
75°	69.1	62.1	56.9	54.7	53.0	52.1	50.2	49.2	48.6	47.6	47.3
77.5°	49.8	45.8	43.4	42.0	40.3	39.3	38.2	37.2	36.5	36.3	35.8
80°	38.0	36.0	34.4	32.5	31.9	30.6	30.2	29.3	29.6	28.6	28.6
82.5°	29.4	27.0	25.7	24.8	24.1	23.1	22.7	22.3	22.4	21.7	21.7
85°	15.2	14.5	13.9	13.2	13.2	12.2	12.6	12.2	12.2	11.5	11.3
87.5°	7.5	8.1	8.7	9.7	10.8	11.7	11.5	11.2	11.1	11.0	10.8
90°	13.0	17.2	22.7	28.2	33.6	39.1	38.6	38.1	37.6	37.1	36.9
92.5°	28.6	30.3	31.6	32.9	34.2	35.5	35.6	35.7	35.8	35.9	36.0
95°	68.0	69.5	70.0	70.4	70.9	71.5	71.5	71.5	71.5	71.5	71.2
97.5°	114.8	116.3	117.3	118.2	119.2	120.1	120.1	120.1	120.1	120.1	120.1
100°	149.7	151.1	151.8	152.6	153.3	154.0	154.0	154.0	154.0	154.0	153.9
102.5°	185.6	186.9	187.9	188.8	189.8	190.7	190.9	191.1	191.3	191.5	191.5
105°	243.0	243.7	244.1	244.6	245.1	245.6	246.1	246.6	247.1	247.6	247.9
107.5°	305.6	306.1	306.1	306.1	306.1	306.1	306.3	306.5	306.7	306.9	306.4
110°	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	347.2	346.8



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	389.3	389.9	389.8	389.6	389.3	389.2	388.6	388.0	387.4	386.8	386.2
115°	452.5	453.0	452.5	452.0	451.5	451.0	450.8	450.6	450.3	450.0	449.5
117.5°	517.5	517.8	516.3	515.0	513.6	512.2	511.6	511.0	510.4	509.8	509.2
120°	559.5	559.5	557.5	555.5	553.5	551.5	551.5	551.5	551.5	551.5	551.1
122.5°	599.4	599.9	598.6	597.2	595.7	594.3	593.7	593.2	592.6	592.0	591.4
125°	658.7	659.4	658.7	658.0	657.2	656.4	655.7	655.0	654.2	653.5	653.0
127.5°	719.4	720.3	719.5	718.5	717.6	716.7	715.8	715.0	714.0	713.2	712.3
130°	757.5	758.9	758.5	757.9	757.4	756.9	756.4	756.0	755.4	754.9	754.2
132.5°	796.3	797.6	797.7	797.8	797.9	798.0	796.9	795.8	794.7	793.7	792.7
135°	851.6	853.2	853.7	854.2	854.7	855.1	854.9	854.7	854.5	854.2	853.7
137.5°	907.4	908.9	909.5	910.2	910.8	911.5	911.3	911.0	910.9	910.7	910.1
140°	942.3	944.0	945.2	946.5	947.7	948.9	948.9	948.9	948.9	948.9	948.5
142.5°	978.0	979.5	980.3	981.2	982.1	982.9	983.1	983.3	983.5	983.7	983.3
145°	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2	1035.4	1035.7	1035.9	1035.5
147.5°	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6	1081.1	1081.7	1082.2	1082.0
150°	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6
152.5°	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9
155°	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6	1175.9	1177.1	1178.3	1178.5
157.5°	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1	1209.8	1211.4	1213.1	1213.4
160°	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4	1229.9	1231.4	1232.9	1233.1
162.5°	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5	1248.2	1249.8	1251.5	1251.8
165°	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0	1271.7	1273.4	1275.2	1275.4
167.5°	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4	1291.2	1292.9	1294.6	1294.9
170°	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1	1301.8	1303.6	1305.4	1305.4
172.5°	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2	1309.9	1311.6	1313.4	1313.5
175°	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9	1318.6	1320.3	1322.1	1322.2
177.5°	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	888.6	889.1	888.3	888.8	888.3	889.1	888.6	891.4	891.9	892.4	891.9
5°	827.9	824.1	823.5	822.5	823.5	824.1	827.9	829.6	830.9	833.4	837.9
7.5°	755.5	754.9	753.4	751.1	753.4	754.9	755.5	761.0	765.4	770.4	779.6
10°	708.9	707.4	707.1	704.8	707.1	707.4	708.9	716.0	721.2	728.2	740.8
12.5°	654.4	644.1	643.0	637.4	643.0	644.1	654.4	663.6	677.4	684.2	697.6
15°	557.2	555.3	548.9	544.7	548.9	555.3	557.2	564.9	570.1	588.8	610.3
17.5°	501.6	495.3	493.4	492.5	493.4	495.3	501.6	505.4	512.7	522.5	535.5
20°	465.9	460.1	459.2	458.5	459.2	460.1	465.9	470.4	476.2	486.8	500.3
22.5°	441.2	435.1	432.7	430.8	432.7	435.1	441.2	444.7	450.0	458.2	467.4
25°	399.0	396.7	395.5	394.9	395.5	396.7	399.0	402.3	407.3	418.6	428.3
27.5°	366.0	361.1	360.1	358.4	360.1	361.1	366.0	371.8	377.1	382.2	390.8
30°	347.2	345.6	343.4	341.5	343.4	345.6	347.2	350.2	353.7	362.4	370.7
32.5°	325.1	323.8	321.8	320.9	321.8	323.8	325.1	329.1	336.5	341.8	347.8
35°	300.7	296.1	294.2	291.3	294.2	296.1	300.7	303.8	306.8	311.3	322.2
37.5°	274.7	272.3	269.7	270.6	269.7	272.3	274.7	276.0	282.1	288.4	293.2
40°	254.7	253.0	252.4	252.1	252.4	253.0	254.7	258.8	266.2	269.1	276.2
42.5°	238.7	234.3	232.6	232.6	232.6	234.3	238.7	243.4	248.0	252.6	260.0
45°	214.5	210.3	207.4	207.7	207.4	210.3	214.5	216.0	219.9	229.3	233.4
47.5°	189.7	189.5	187.7	188.3	187.7	189.5	189.7	192.4	197.3	203.1	209.7
50°	177.8	175.9	174.6	174.9	174.6	175.9	177.8	180.0	183.0	185.8	196.1
52.5°	166.5	164.8	163.8	165.1	163.8	164.8	166.5	167.7	169.8	172.7	179.7
55°	147.9	145.9	145.7	145.3	145.7	145.9	147.9	149.5	152.1	154.3	157.6
57.5°	127.2	125.9	123.9	123.1	123.9	125.9	127.2	129.5	132.6	135.5	138.9
60°	112.2	109.6	106.4	106.1	106.4	109.6	112.2	116.4	117.7	122.2	126.1
62.5°	98.6	98.1	97.5	97.4	97.5	98.1	98.6	100.0	101.8	108.3	113.0
65°	86.5	86.2	86.5	86.8	86.5	86.2	86.5	87.1	87.5	88.1	90.1
67.5°	75.3	74.8	74.2	74.5	74.2	74.8	75.3	75.5	76.4	76.8	78.1
70°	66.9	66.6	66.2	66.2	66.2	66.6	66.9	67.5	68.2	68.8	70.4
72.5°	58.6	58.5	58.3	58.0	58.3	58.5	58.6	59.8	60.2	60.9	61.9
75°	46.9	46.3	46.3	46.3	46.3	46.3	46.9	47.3	47.6	48.6	49.2
77.5°	35.7	35.5	35.1	34.9	35.1	35.5	35.7	35.8	36.3	36.5	37.2
80°	28.3	28.0	27.6	27.6	27.6	28.0	28.3	28.6	28.6	29.6	29.3
82.5°	21.6	21.3	21.2	20.9	21.2	21.3	21.6	21.7	21.7	22.4	22.3
85°	11.5	11.9	11.5	12.2	11.5	11.9	11.5	11.3	11.5	12.2	12.2
87.5°	10.8	10.6	10.8	10.7	10.8	10.6	10.8	10.8	11.0	11.1	11.2
90°	37.2	37.5	37.7	38.0	37.7	37.5	37.2	36.9	37.1	37.6	38.1
92.5°	36.0	36.1	36.2	36.2	36.2	36.1	36.0	36.0	35.9	35.8	35.7
95°	70.7	70.2	69.7	69.2	69.7	70.2	70.7	71.2	71.5	71.5	71.5
97.5°	120.0	120.0	119.9	119.9	119.9	120.0	120.0	120.1	120.1	120.1	120.1
100°	153.7	153.4	153.2	152.9	153.2	153.4	153.7	153.9	154.0	154.0	154.0
102.5°	191.2	191.0	190.7	190.5	190.7	191.0	191.2	191.5	191.5	191.3	191.1
105°	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.9	247.6	247.1	246.6
107.5°	305.3	304.2	303.0	301.9	303.0	304.2	305.3	306.4	306.9	306.7	306.5
110°	346.1	345.3	344.6	343.9	344.6	345.3	346.1	346.8	347.2	347.2	347.2



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	385.6	385.1	384.6	384.0	384.6	385.1	385.6	386.2	386.8	387.4	388.0
115°	448.8	448.1	447.3	446.6	447.3	448.1	448.8	449.5	450.0	450.3	450.6
117.5°	508.4	507.6	507.0	506.2	507.0	507.6	508.4	509.2	509.8	510.4	511.0
120°	550.4	549.7	548.9	548.2	548.9	549.7	550.4	551.1	551.5	551.5	551.5
122.5°	590.9	590.3	589.8	589.3	589.8	590.3	590.9	591.4	592.0	592.6	593.2
125°	652.7	652.5	652.2	651.9	652.2	652.5	652.7	653.0	653.5	654.2	655.0
127.5°	711.5	710.8	710.0	709.1	710.0	710.8	711.5	712.3	713.2	714.0	715.0
130°	753.2	752.3	751.2	750.2	751.2	752.3	753.2	754.2	754.9	755.4	756.0
132.5°	791.9	791.1	790.3	789.5	790.3	791.1	791.9	792.7	793.7	794.7	795.8
135°	852.9	852.2	851.4	850.7	851.4	852.2	852.9	853.7	854.2	854.5	854.7
137.5°	909.0	908.1	907.1	906.1	907.1	908.1	909.0	910.1	910.7	910.9	911.0
140°	947.4	946.5	945.5	944.5	945.5	946.5	947.4	948.5	948.9	948.9	948.9
142.5°	982.3	981.3	980.3	979.3	980.3	981.3	982.3	983.3	983.7	983.5	983.3
145°	1034.6	1033.5	1032.6	1031.6	1032.6	1033.5	1034.6	1035.5	1035.9	1035.7	1035.4
147.5°	1081.1	1080.1	1079.2	1078.2	1079.2	1080.1	1081.1	1082.0	1082.2	1081.7	1081.1
150°	1110.9	1110.1	1109.3	1108.6	1109.3	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1
152.5°	1140.0	1139.1	1138.2	1137.2	1138.2	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1
155°	1177.8	1177.1	1176.3	1175.6	1176.3	1177.1	1177.8	1178.5	1178.3	1177.1	1175.9
157.5°	1212.2	1211.0	1209.8	1208.6	1209.8	1211.0	1212.2	1213.4	1213.1	1211.4	1209.8
160°	1232.2	1231.1	1230.2	1229.2	1230.2	1231.1	1232.2	1233.1	1232.9	1231.4	1229.9
162.5°	1250.6	1249.4	1248.2	1247.1	1248.2	1249.4	1250.6	1251.8	1251.5	1249.8	1248.2
165°	1274.2	1273.0	1271.7	1270.5	1271.7	1273.0	1274.2	1275.4	1275.2	1273.4	1271.7
167.5°	1293.6	1292.3	1291.0	1289.7	1291.0	1292.3	1293.6	1294.9	1294.6	1292.9	1291.2
170°	1304.0	1302.5	1301.0	1299.5	1301.0	1302.5	1304.0	1305.4	1305.4	1303.6	1301.8
172.5°	1312.0	1310.5	1309.1	1307.5	1309.1	1310.5	1312.0	1313.5	1313.4	1311.6	1309.9
175°	1320.7	1319.2	1317.8	1316.2	1317.8	1319.2	1320.7	1322.2	1322.1	1320.3	1318.6
177.5°	1323.9	1322.7	1321.5	1320.3	1321.5	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	889.8	893.5	898.9	902.0	907.1	910.4	912.2	915.6	917.4	923.9	930.5
5°	840.2	845.3	854.3	862.6	871.7	881.0	887.8	895.4	902.5	914.7	927.6
7.5°	783.2	790.3	804.3	817.6	833.3	846.4	858.1	871.2	883.0	900.5	918.8
10°	740.5	753.0	771.4	783.9	804.4	817.6	835.9	850.4	866.9	890.0	910.6
12.5°	703.7	718.8	733.6	751.0	769.5	791.4	811.6	830.1	849.6	873.6	897.7
15°	637.0	658.8	681.7	699.3	724.4	747.5	771.0	796.1	819.9	848.5	880.0
17.5°	551.0	576.4	614.8	645.1	674.5	697.8	726.8	757.2	785.1	819.7	854.7
20°	512.2	530.8	556.9	597.7	642.1	666.8	696.5	729.9	762.0	799.6	837.2
22.5°	481.0	497.7	518.6	550.4	599.9	633.7	664.5	698.5	735.8	774.2	815.9
25°	436.6	448.2	470.1	495.8	529.9	585.5	619.2	653.3	693.9	735.0	782.6
27.5°	403.3	413.7	427.9	452.5	477.8	517.7	571.4	608.6	648.9	695.3	744.7
30°	377.8	390.0	405.8	423.1	450.8	482.0	535.6	578.8	618.6	666.2	718.9
32.5°	359.3	368.9	382.4	400.0	423.0	452.9	495.8	548.1	586.9	637.1	692.2
35°	328.9	340.2	351.1	367.8	386.5	413.8	446.3	502.2	540.8	590.3	645.7
37.5°	303.9	310.8	322.9	336.1	355.8	376.2	404.3	454.5	496.3	544.8	601.5
40°	284.9	293.5	302.6	317.4	333.5	353.0	380.6	418.0	465.9	513.5	568.8
42.5°	266.4	277.3	286.9	296.8	314.4	334.0	356.5	388.1	437.0	482.1	535.9
45°	244.0	251.2	261.1	272.0	286.5	303.2	323.1	350.8	397.7	436.6	487.2
47.5°	218.1	228.4	234.9	245.6	259.3	275.3	293.8	317.7	355.8	392.2	439.0
50°	200.4	210.9	220.2	229.9	242.1	257.5	272.9	296.1	326.7	365.0	408.6
52.5°	185.1	194.5	203.5	213.2	225.2	239.3	253.9	274.2	300.4	335.6	378.1
55°	164.3	170.0	179.4	189.1	199.7	213.2	227.3	244.4	266.9	296.4	330.9
57.5°	142.9	149.6	157.0	166.8	177.5	187.9	200.5	216.0	233.8	260.5	290.0
60°	130.9	136.0	142.2	152.1	162.0	171.3	183.6	196.5	213.2	236.3	261.4
62.5°	117.5	122.3	127.9	136.6	146.4	154.9	165.6	179.3	193.4	214.5	236.4
65°	95.1	102.3	107.7	115.5	123.5	132.5	140.9	151.8	164.3	181.0	200.6
67.5°	78.9	82.5	87.6	94.6	102.8	110.6	118.5	127.0	137.8	150.8	166.3
70°	71.7	73.0	74.0	80.7	88.4	96.2	103.5	111.6	120.9	131.5	145.0
72.5°	63.2	64.5	65.7	68.6	74.8	82.5	90.1	96.2	105.0	113.7	124.7
75°	50.2	52.1	53.0	54.7	56.9	62.1	69.1	74.9	80.1	86.8	95.5
77.5°	38.2	39.3	40.3	42.0	43.4	45.8	49.8	55.0	59.8	63.7	69.7
80°	30.2	30.6	31.9	32.5	34.4	36.0	38.0	42.1	46.9	48.6	52.7
82.5°	22.7	23.1	24.1	24.8	25.7	27.0	29.4	30.6	34.4	36.4	39.1
85°	12.6	12.2	13.2	13.2	13.9	14.5	15.2	16.7	17.7	20.2	20.9
87.5°	11.5	11.7	10.8	9.7	8.7	8.1	7.5	7.1	7.1	7.2	7.7
90°	38.6	39.1	33.6	28.2	22.7	17.2	13.0	10.1	7.1	4.1	1.1
92.5°	35.6	35.5	34.2	32.9	31.6	30.3	28.6	26.4	24.3	22.0	19.9
95°	71.5	71.5	70.9	70.4	70.0	69.5	68.0	65.5	63.0	60.5	58.0
97.5°	120.1	120.1	119.2	118.2	117.3	116.3	114.8	112.6	110.5	108.2	106.1
100°	154.0	154.0	153.3	152.6	151.8	151.1	149.7	147.7	145.8	143.8	141.8
102.5°	190.9	190.7	189.8	188.8	187.9	186.9	185.6	184.1	182.4	180.9	179.3
105°	246.1	245.6	245.1	244.6	244.1	243.7	243.0	242.3	241.5	240.7	240.0
107.5°	306.3	306.1	306.1	306.1	306.1	306.1	305.6	304.4	303.4	302.3	301.2
110°	347.2	347.2	347.2	347.2	347.2	347.2	346.5	345.0	343.5	342.0	340.5



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	388.6	389.2	389.3	389.6	389.8	389.9	389.3	387.9	386.3	384.9	383.4
115°	450.8	451.0	451.5	452.0	452.5	453.0	452.5	451.0	449.5	448.1	446.6
117.5°	511.6	512.2	513.6	515.0	516.3	517.8	517.5	515.5	513.5	511.5	509.5
120°	551.5	551.5	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5
122.5°	593.7	594.3	595.7	597.2	598.6	599.9	599.4	597.0	594.7	592.3	589.9
125°	655.7	656.4	657.2	658.0	658.7	659.4	658.7	656.4	654.2	651.9	649.7
127.5°	715.8	716.7	717.6	718.5	719.5	720.3	719.4	716.5	713.7	710.8	708.0
130°	756.4	756.9	757.4	757.9	758.5	758.9	757.5	754.3	751.1	747.9	744.7
132.5°	796.9	798.0	797.9	797.8	797.7	797.6	796.3	793.6	791.0	788.3	785.7
135°	854.9	855.1	854.7	854.2	853.7	853.2	851.6	848.9	846.1	843.3	840.7
137.5°	911.3	911.5	910.8	910.2	909.5	908.9	907.4	905.2	902.9	900.7	898.5
140°	948.9	948.9	947.7	946.5	945.2	944.0	942.3	940.0	937.8	935.6	933.3
142.5°	983.1	982.9	982.1	981.2	980.3	979.5	978.0	975.8	973.5	971.3	969.1
145°	1035.2	1034.9	1033.5	1031.9	1030.4	1029.0	1027.3	1025.6	1023.9	1022.2	1020.4
147.5°	1080.6	1080.0	1079.0	1078.1	1077.0	1076.1	1074.5	1072.5	1070.3	1068.2	1066.2
150°	1109.3	1108.6	1107.6	1106.6	1105.6	1104.7	1103.4	1101.9	1100.4	1098.9	1097.4
152.5°	1138.2	1137.2	1136.0	1134.8	1133.6	1132.4	1131.1	1129.5	1128.1	1126.6	1125.2
155°	1174.6	1173.4	1172.6	1171.8	1171.1	1170.4	1169.7	1168.9	1168.1	1167.4	1166.7
157.5°	1208.1	1206.4	1205.9	1205.5	1205.1	1204.6	1204.1	1203.7	1203.2	1202.6	1202.1
160°	1228.4	1226.9	1226.7	1226.4	1226.2	1226.0	1225.5	1225.1	1224.6	1224.1	1223.6
162.5°	1246.5	1244.8	1244.6	1244.3	1244.1	1243.8	1243.6	1243.5	1243.5	1243.4	1243.2
165°	1270.0	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1268.6	1268.9	1269.1	1269.4
167.5°	1289.4	1287.6	1287.7	1287.8	1287.8	1287.9	1288.2	1289.0	1289.8	1290.5	1291.2
170°	1300.1	1298.4	1298.6	1298.9	1299.2	1299.4	1299.9	1300.6	1301.4	1302.1	1302.9
172.5°	1308.2	1306.4	1306.7	1306.9	1307.2	1307.4	1307.9	1308.6	1309.4	1310.2	1310.9
175°	1316.9	1315.1	1315.6	1316.1	1316.6	1317.2	1317.8	1318.4	1319.2	1320.0	1320.7
177.5°	1321.5	1320.3	1320.7	1321.0	1321.5	1321.9	1322.3	1322.9	1323.5	1324.1	1324.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	930.7	931.5	936.7	939.0	943.7	945.5	947.4	946.9	946.9	948.0	955.2
5°	932.7	939.2	948.8	958.1	967.2	974.9	980.0	985.2	987.1	996.4	1004.8
7.5°	929.4	941.2	957.2	971.4	988.4	1001.8	1012.8	1022.8	1029.6	1043.2	1057.0
10°	925.1	941.8	959.8	978.1	1001.6	1019.3	1037.2	1051.1	1055.6	1075.8	1087.4
12.5°	916.3	938.7	961.6	985.3	1008.2	1032.6	1052.4	1066.3	1082.1	1100.3	1121.6
15°	903.2	928.9	958.8	989.4	1022.2	1051.7	1073.0	1097.1	1114.4	1134.4	1153.0
17.5°	884.3	917.5	955.5	990.8	1028.7	1060.5	1089.8	1112.8	1125.1	1136.4	1139.3
20°	869.4	905.1	949.8	991.6	1029.5	1066.2	1095.1	1114.4	1117.7	1117.9	1100.9
22.5°	853.3	893.5	940.3	983.1	1028.5	1069.3	1091.7	1100.0	1087.3	1065.5	1032.5
25°	823.5	870.0	924.4	973.3	1022.8	1061.4	1069.1	1054.6	1010.0	962.9	903.5
27.5°	791.2	843.5	901.8	956.1	1008.9	1032.9	1016.2	964.0	883.5	813.6	728.8
30°	767.5	826.3	883.6	944.3	993.2	1003.5	965.3	888.4	794.5	689.1	604.5
32.5°	740.5	802.1	865.0	927.9	968.8	958.7	895.5	800.9	690.9	587.2	507.2
35°	701.9	765.6	833.4	896.4	922.5	879.1	784.5	661.4	548.9	452.1	397.1
37.5°	657.4	726.7	797.2	855.1	853.3	780.8	652.1	525.0	430.4	373.2	334.0
40°	625.7	695.8	772.0	820.9	800.0	705.8	566.2	446.3	377.1	331.5	302.9
42.5°	595.4	665.7	741.4	780.2	743.9	628.1	489.0	395.1	338.0	302.5	279.2
45°	543.7	617.9	688.1	709.6	644.6	517.0	395.5	327.4	289.4	263.0	246.9
47.5°	493.3	566.3	630.3	630.7	542.8	419.3	333.6	283.3	250.9	230.5	218.8
50°	462.4	531.8	585.5	577.1	477.5	373.0	298.3	254.9	228.0	212.2	200.0
52.5°	427.7	495.0	541.5	517.7	422.1	328.2	266.7	230.3	207.9	194.2	183.3
55°	377.1	437.0	469.8	433.8	344.4	272.9	225.4	196.7	180.0	168.5	159.2
57.5°	327.6	376.9	397.5	355.6	283.6	226.4	190.6	169.2	152.6	144.3	139.5
60°	296.4	338.5	353.0	306.8	246.6	198.0	168.8	148.9	136.6	131.2	126.4
62.5°	265.9	300.2	306.3	263.8	215.0	173.4	148.3	131.4	123.3	118.0	113.5
65°	220.6	245.3	242.5	208.4	170.0	137.6	119.2	109.0	102.9	95.5	87.5
67.5°	181.6	196.7	187.6	162.0	129.8	106.9	95.0	87.2	79.6	72.6	70.8
70°	156.9	165.6	155.9	132.5	106.4	89.7	80.1	70.8	66.2	64.7	61.7
72.5°	133.3	136.3	125.9	105.7	86.6	74.3	64.9	59.7	57.3	55.9	54.0
75°	100.0	97.7	88.8	73.0	60.1	51.7	48.9	46.9	45.4	44.1	43.0
77.5°	70.3	66.9	58.9	48.6	41.8	37.9	36.2	35.1	34.4	33.7	32.7
80°	52.7	50.5	42.4	34.7	31.9	29.9	28.9	27.6	27.6	27.0	26.0
82.5°	38.6	36.1	29.1	25.5	23.8	22.7	22.0	21.2	20.9	21.1	20.4
85°	20.2	16.4	14.5	13.9	12.8	12.2	12.6	11.9	11.9	11.9	11.5
87.5°	7.0	6.3	6.6	7.0	8.1	9.2	10.0	11.1	12.5	12.1	12.2
90°	4.1	7.1	10.1	13.0	17.2	22.7	28.2	33.6	39.1	38.6	38.1
92.5°	22.0	24.3	26.4	28.6	30.3	31.6	32.9	34.2	35.5	35.6	35.7
95°	60.5	63.0	65.5	68.0	69.5	70.0	70.4	70.9	71.5	71.5	71.5
97.5°	108.2	110.5	112.6	114.8	116.3	117.3	118.2	119.2	120.1	120.1	120.1
100°	143.8	145.8	147.7	149.7	151.1	151.8	152.6	153.3	154.0	154.0	154.0
102.5°	180.9	182.4	184.1	185.6	186.9	187.9	188.8	189.8	190.7	190.9	191.1
105°	240.7	241.5	242.3	243.0	243.7	244.1	244.6	245.1	245.6	246.1	246.6
107.5°	302.3	303.4	304.4	305.6	306.1	306.1	306.1	306.1	306.1	306.3	306.5
110°	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	384.9	386.3	387.9	389.3	389.9	389.8	389.6	389.3	389.2	388.6	388.0
115°	448.1	449.5	451.0	452.5	453.0	452.5	452.0	451.5	451.0	450.8	450.6
117.5°	511.5	513.5	515.5	517.5	517.8	516.3	515.0	513.6	512.2	511.6	511.0
120°	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	551.5	551.5
122.5°	592.3	594.7	597.0	599.4	599.9	598.6	597.2	595.7	594.3	593.7	593.2
125°	651.9	654.2	656.4	658.7	659.4	658.7	658.0	657.2	656.4	655.7	655.0
127.5°	710.8	713.7	716.5	719.4	720.3	719.5	718.5	717.6	716.7	715.8	715.0
130°	747.9	751.1	754.3	757.5	758.9	758.5	757.9	757.4	756.9	756.4	756.0
132.5°	788.3	791.0	793.6	796.3	797.6	797.7	797.8	797.9	798.0	796.9	795.8
135°	843.3	846.1	848.9	851.6	853.2	853.7	854.2	854.7	855.1	854.9	854.7
137.5°	900.7	902.9	905.2	907.4	908.9	909.5	910.2	910.8	911.5	911.3	911.0
140°	935.6	937.8	940.0	942.3	944.0	945.2	946.5	947.7	948.9	948.9	948.9
142.5°	971.3	973.5	975.8	978.0	979.5	980.3	981.2	982.1	982.9	983.1	983.3
145°	1022.2	1023.9	1025.6	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2	1035.4
147.5°	1068.2	1070.3	1072.5	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6	1081.1
150°	1098.9	1100.4	1101.9	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3	1110.1
152.5°	1126.6	1128.1	1129.5	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2	1139.1
155°	1167.4	1168.1	1168.9	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6	1175.9
157.5°	1202.6	1203.2	1203.7	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1	1209.8
160°	1224.1	1224.6	1225.1	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4	1229.9
162.5°	1243.4	1243.5	1243.5	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5	1248.2
165°	1269.1	1268.9	1268.6	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0	1271.7
167.5°	1290.5	1289.8	1289.0	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4	1291.2
170°	1302.1	1301.4	1300.6	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1	1301.8
172.5°	1310.2	1309.4	1308.6	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2	1309.9
175°	1320.0	1319.2	1318.4	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9	1318.6
177.5°	1324.1	1323.5	1322.9	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5	1322.7
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	925.4	925.4	925.4	925.4	925.4	925.4	925.4
2.5°	957.8	961.1	962.7	962.7	964.5	963.7	962.9
5°	1012.8	1018.9	1020.2	1026.0	1030.2	1028.9	1029.5
7.5°	1067.6	1077.4	1087.1	1091.5	1092.3	1094.8	1095.8
10°	1101.2	1109.3	1124.4	1122.1	1133.4	1139.8	1129.2
12.5°	1133.7	1144.5	1155.0	1157.9	1164.2	1166.3	1162.1
15°	1163.0	1168.7	1169.4	1167.8	1169.8	1168.1	1162.0
17.5°	1135.6	1126.2	1107.2	1098.1	1091.0	1080.5	1076.2
20°	1090.3	1062.6	1030.5	1017.6	1002.5	972.9	980.0
22.5°	992.6	961.0	928.9	891.3	873.4	845.3	843.7
25°	840.5	786.2	726.3	684.5	660.1	632.1	619.9
27.5°	653.5	585.0	536.1	511.3	488.6	466.5	465.5
30°	530.5	479.1	441.2	419.9	406.1	396.7	398.7
32.5°	447.2	411.9	386.3	368.8	358.5	351.5	351.4
35°	365.6	341.5	325.0	317.7	310.3	305.1	305.5
37.5°	312.9	298.3	289.2	281.1	276.5	274.0	272.5
40°	285.9	274.0	266.9	262.1	258.2	254.7	254.0
42.5°	264.5	254.7	247.5	243.7	240.2	237.6	237.0
45°	234.7	226.7	220.2	216.0	214.5	212.2	212.2
47.5°	208.8	200.9	195.9	193.2	190.5	189.0	188.9
50°	191.3	185.2	180.7	179.1	176.8	175.9	175.6
52.5°	175.6	171.1	167.8	166.8	165.7	164.5	164.7
55°	154.3	151.8	150.5	149.5	147.9	145.9	147.2
57.5°	136.4	134.2	130.7	127.7	126.2	124.8	125.4
60°	123.8	119.2	114.8	111.2	110.3	107.4	107.4
62.5°	107.9	101.5	96.0	94.0	93.1	91.7	91.4
65°	82.9	80.4	79.1	77.8	77.1	77.1	76.5
67.5°	68.7	67.7	66.3	66.0	65.3	65.2	64.9
70°	60.8	59.5	58.8	58.5	57.9	58.2	57.3
72.5°	53.0	52.0	51.9	51.1	50.7	50.7	50.0
75°	41.8	41.8	41.5	41.2	40.6	40.2	40.6
77.5°	32.1	32.2	31.6	31.6	31.5	31.6	31.3
80°	25.7	26.0	25.7	25.4	25.1	25.4	25.1
82.5°	20.3	19.9	19.8	19.7	19.7	19.5	19.5
85°	11.5	11.9	11.5	11.3	11.3	11.3	11.5
87.5°	11.9	11.8	11.8	11.8	11.9	11.9	11.7
90°	37.6	37.1	36.9	37.2	37.5	37.7	38.0
92.5°	35.8	35.9	36.0	36.0	36.1	36.2	36.2
95°	71.5	71.5	71.2	70.7	70.2	69.7	69.2
97.5°	120.1	120.1	120.1	120.0	120.0	119.9	119.9
100°	154.0	154.0	153.9	153.7	153.4	153.2	152.9
102.5°	191.3	191.5	191.5	191.2	191.0	190.7	190.5
105°	247.1	247.6	247.9	247.9	247.9	247.9	247.9
107.5°	306.7	306.9	306.4	305.3	304.2	303.0	301.9
110°	347.2	347.2	346.8	346.1	345.3	344.6	343.9



TEST NUMBER: P331798-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-A1

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	387.4	386.8	386.2	385.6	385.1	384.6	384.0
115°	450.3	450.0	449.5	448.8	448.1	447.3	446.6
117.5°	510.4	509.8	509.2	508.4	507.6	507.0	506.2
120°	551.5	551.5	551.1	550.4	549.7	548.9	548.2
122.5°	592.6	592.0	591.4	590.9	590.3	589.8	589.3
125°	654.2	653.5	653.0	652.7	652.5	652.2	651.9
127.5°	714.0	713.2	712.3	711.5	710.8	710.0	709.1
130°	755.4	754.9	754.2	753.2	752.3	751.2	750.2
132.5°	794.7	793.7	792.7	791.9	791.1	790.3	789.5
135°	854.5	854.2	853.7	852.9	852.2	851.4	850.7
137.5°	910.9	910.7	910.1	909.0	908.1	907.1	906.1
140°	948.9	948.9	948.5	947.4	946.5	945.5	944.5
142.5°	983.5	983.7	983.3	982.3	981.3	980.3	979.3
145°	1035.7	1035.9	1035.5	1034.6	1033.5	1032.6	1031.6
147.5°	1081.7	1082.2	1082.0	1081.1	1080.1	1079.2	1078.2
150°	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6
152.5°	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2
155°	1177.1	1178.3	1178.5	1177.8	1177.1	1176.3	1175.6
157.5°	1211.4	1213.1	1213.4	1212.2	1211.0	1209.8	1208.6
160°	1231.4	1232.9	1233.1	1232.2	1231.1	1230.2	1229.2
162.5°	1249.8	1251.5	1251.8	1250.6	1249.4	1248.2	1247.1
165°	1273.4	1275.2	1275.4	1274.2	1273.0	1271.7	1270.5
167.5°	1292.9	1294.6	1294.9	1293.6	1292.3	1291.0	1289.7
170°	1303.6	1305.4	1305.4	1304.0	1302.5	1301.0	1299.5
172.5°	1311.6	1313.4	1313.5	1312.0	1310.5	1309.1	1307.5
175°	1320.3	1322.1	1322.2	1320.7	1319.2	1317.8	1316.2
177.5°	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)