

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331853-930

Luminaire Tested: **S122RDIW-S1005D970U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331853-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S1005D970U930-4F0-1E-UDD-A
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 1005 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING
UPLIGHT 970 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6265.3 lumens
Efficiency: N/A
Efficacy: 93.0 lumens/watt
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 67.4
Input Voltage (V): 120
Input Current (Ain): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

Luminous Intensity Polar Plot





TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20			
RC	80				70				50				30				10	0		
RW	70	50	30	10	70	50	30	10	50	30	10		50	30	10		50	30	10	0
RCR																				
0	107	107	107	107	99	99	99	99	83	83	83		69	69	69		56	56	56	50
1	98	94	91	88	91	87	84	81	74	72	70		62	60	59		50	49	49	43
2	90	83	78	73	83	77	72	68	66	62	59		55	53	50		45	44	42	38
3	83	74	67	62	76	69	63	58	59	54	51		50	46	44		41	39	37	33
4	76	66	59	53	70	62	55	50	53	48	44		45	41	38		37	35	33	29
5	70	59	52	46	65	55	49	44	48	43	39		41	37	34		34	31	29	26
6	65	54	46	40	60	50	43	38	43	38	34		37	33	30		31	28	26	23
7	61	49	41	36	56	46	39	34	40	34	31		34	30	27		29	26	24	21
8	56	45	37	32	52	42	35	31	36	31	27		31	27	24		27	24	21	19
9	53	41	34	29	49	38	32	28	34	28	25		29	25	22		25	22	20	17
10	49	38	31	26	46	35	29	25	31	26	23		27	23	20		23	20	18	16

AVERAGE LUMINANCE (cd/sqm):

	0°	90°	180°	270°
0°	29032	29032	29032	29032
5°	32423	29214	25901	29214
10°	35974	29009	22453	29009
15°	37742	28583	17690	28583
20°	32720	27953	15309	27953
25°	21458	27091	13668	27091
30°	14443	26045	12370	26045
35°	11698	24727	11158	24727
40°	10404	23294	10323	23294
45°	9417	21614	9216	21614
50°	8568	19947	8538	19947
55°	8056	18097	7949	18097
60°	6736	16401	6659	16401
65°	5681	14896	6445	14896
70°	5249	13303	6076	13303
75°	4916	11578	5608	11578
80°	4537	9530	4993	9530
85°	4168	7521	4390	7521



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	170.4	2.7
10°-20°	474.9	7.6
20°-30°	612.0	9.8
30°-40°	581.6	9.3
40°-50°	498.2	8.0
50°-60°	379.4	6.1
60°-70°	239.9	3.8
70°-80°	119.8	1.9
80°-90°	33.8	0.5
90°-100°	35.9	0.6
100°-110°	131.7	2.1
110°-120°	352.0	5.6
120°-130°	581.1	9.3
130°-140°	618.0	9.9
140°-150°	574.4	9.2
150°-160°	461.8	7.4
160°-170°	297.6	4.8
170°-180°	102.4	1.6
0°-30°	1257.4	20.1
0°-40°	1839.0	29.4
0°-60°	2716.7	43.4
0°-90°	3110.2	49.6
90°-120°	519.7	8.3
90°-150°	2293.2	36.6
90°-180°	3155.0	50.4
0°-180°	6265.3	100.0

CANDELA DISTRIBUTION:

	0°	90°	180°	270°	360°	Flux
0°	1798	1798	1798	1798	1798	
5°	2000	1802	1598	1802	2000	197
15°	2258	1710	1058	1710	2258	609
25°	1204	1521	767	1521	1204	572
35°	594	1254	566	1254	594	380
45°	412	947	404	947	412	319
55°	286	643	282	643	286	251
65°	149	390	169	390	149	151
75°	79	186	90	186	79	84
85°	22	41	24	41	22	25
90°	21	1	21	1	21	10
95°	34	51	34	51	34	31
105°	59	237	59	237	59	62
115°	64	448	64	448	64	160
125°	666	633	666	633	666	576
135°	809	784	809	784	809	624
145°	923	909	923	909	923	577
155°	1002	1001	1002	1001	1002	462
165°	1052	1055	1052	1055	1052	297
175°	1073	1079	1073	1079	1073	102
180°	1077	1077	1077	1077	1077	



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1871.0	1872.6	1874.0	1870.5	1870.5	1867.5	1861.1	1856.0	1842.1	1840.0	1840.0
5°	2000.5	1999.3	2001.7	1993.7	1982.4	1979.9	1968.1	1952.4	1936.2	1918.1	1914.3
7.5°	2129.2	2127.4	2122.3	2121.0	2112.4	2093.4	2074.4	2054.0	2027.0	2000.7	1987.4
10°	2194.2	2214.8	2202.3	2180.4	2184.8	2155.5	2139.8	2113.0	2090.5	2051.1	2042.4
12.5°	2258.1	2266.3	2262.3	2249.9	2244.3	2223.9	2202.8	2179.5	2138.0	2102.6	2071.8
15°	2257.9	2269.8	2272.9	2269.1	2272.3	2271.0	2259.8	2240.4	2204.2	2165.4	2131.7
17.5°	2091.2	2099.5	2119.9	2133.8	2151.3	2188.3	2206.5	2213.7	2208.3	2186.2	2162.4
20°	1904.3	1890.5	1948.0	1977.4	2002.4	2064.8	2118.6	2139.2	2172.3	2171.7	2165.4
22.5°	1639.4	1642.7	1697.1	1732.0	1805.0	1867.4	1928.7	2006.3	2070.4	2112.7	2137.5
25°	1204.5	1228.3	1282.6	1330.2	1411.4	1527.5	1633.1	1755.6	1871.2	1962.4	2049.3
27.5°	904.7	906.4	949.5	993.4	1041.6	1136.9	1269.7	1416.0	1580.8	1716.8	1873.2
30°	774.7	770.9	789.0	816.0	857.2	930.9	1030.9	1174.6	1338.9	1543.8	1726.2
32.5°	682.7	683.0	696.6	716.5	750.7	800.5	868.9	985.6	1140.9	1342.4	1556.3
35°	593.5	592.9	602.9	617.3	631.6	663.5	710.4	771.6	878.4	1066.5	1285.2
37.5°	529.5	532.3	537.2	546.2	562.1	579.8	607.9	649.0	725.1	836.3	1020.1
40°	493.6	494.8	501.7	509.2	518.5	532.3	555.4	588.6	644.2	732.9	867.2
42.5°	460.6	461.9	466.7	473.7	481.1	494.8	514.0	542.6	587.7	656.9	767.7
45°	412.4	412.4	416.7	419.9	428.0	440.4	456.1	479.8	511.0	562.3	636.0
47.5°	367.1	367.2	370.1	375.5	380.6	390.4	405.7	425.1	447.8	487.5	550.4
50°	341.1	341.8	343.6	348.0	351.1	359.9	371.8	388.6	412.4	443.0	495.5
52.5°	320.2	319.8	322.1	324.0	326.1	332.4	341.3	356.1	377.3	404.0	447.4
55°	286.2	283.6	287.4	290.5	292.4	294.9	299.9	309.2	327.3	349.8	382.4
57.5°	243.7	242.6	245.3	248.2	254.0	260.8	265.1	271.0	280.4	296.5	328.7
60°	208.6	208.6	214.3	216.1	223.1	231.8	240.5	245.6	254.9	265.5	289.3
62.5°	177.7	178.2	180.8	182.7	186.5	197.3	209.5	220.5	229.4	239.5	255.3
65°	148.7	149.9	149.9	151.2	153.7	156.2	161.2	169.9	185.6	199.9	211.8
67.5°	126.2	126.6	126.9	128.2	128.8	131.6	133.5	137.5	141.0	154.7	169.4
70°	111.2	113.1	112.4	113.7	114.3	115.6	118.1	119.9	125.6	128.7	137.5
72.5°	97.2	98.6	98.5	99.2	100.9	101.1	103.1	104.9	108.6	111.2	115.9
75°	78.8	78.1	78.8	80.0	80.6	81.2	81.2	83.7	85.6	88.1	91.2
77.5°	60.7	61.4	61.2	61.4	61.5	62.6	62.5	63.6	65.5	66.7	68.2
80°	48.8	49.3	48.8	49.3	50.0	50.6	50.0	50.6	52.5	53.7	53.7
82.5°	37.7	37.8	38.2	38.4	38.5	38.6	39.5	39.6	41.0	40.8	41.3
85°	22.5	21.9	21.9	21.9	22.5	23.2	22.5	22.5	23.2	23.2	23.2
87.5°	12.2	12.6	12.6	12.5	12.4	12.3	12.1	12.5	11.8	12.1	11.3
90°	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3	16.5	15.6	14.2
92.5°	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0	18.5	18.1	17.4
95°	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1	31.2	30.4	29.2
97.5°	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1	41.3	40.7	37.8
100°	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2	45.8	44.4	41.5
102.5°	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2	47.5	45.7	40.3
105°	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4	49.4	47.5	44.8
107.5°	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6	64.6	66.5	123.2
110°	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7	119.0	136.3	186.4



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5	280.7	343.9	356.2
115°	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3	400.5	480.7	476.4
117.5°	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6	513.0	532.4	529.5
120°	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2	573.2	571.0	567.9
122.5°	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3	609.0	607.8	604.4
125°	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7	659.5	658.3	655.0
127.5°	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4	705.6	703.8	701.3
130°	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9	735.0	733.1	731.2
132.5°	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6	764.0	762.4	760.4
135°	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7	804.9	803.2	801.6
137.5°	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7	843.1	841.4	839.6
140°	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4	867.9	866.3	864.4
142.5°	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2	890.8	889.3	887.2
145°	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1	922.8	921.6	918.7
147.5°	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8	950.9	950.0	947.1
150°	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9	967.8	966.8	964.0
152.5°	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5	983.4	982.4	979.7
155°	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5	1004.4	1003.4	1001.4
157.5°	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2	1022.1	1020.8	1019.4
160°	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6	1032.5	1031.4	1030.5
162.5°	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2	1042.0	1040.8	1039.9
165°	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5	1052.0
167.5°	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7	1063.5	1062.3	1061.8
170°	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8	1068.5	1067.3	1067.0
172.5°	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4	1072.3	1071.1	1070.7
175°	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5	1076.3	1075.1	1074.7
177.5°	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0	1077.0	1076.0	1075.9
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1841.1	1837.0	1833.6	1824.6	1820.1	1810.0	1808.6	1808.1	1795.1	1782.6	1779.1
5°	1904.3	1894.3	1879.3	1861.8	1843.7	1825.0	1812.5	1802.5	1777.4	1753.7	1740.0
7.5°	1968.1	1946.5	1920.7	1887.6	1859.9	1829.0	1806.0	1785.3	1749.9	1715.9	1693.0
10°	2015.5	1980.5	1946.1	1900.5	1864.9	1829.9	1797.5	1769.4	1729.3	1684.4	1652.5
12.5°	2045.0	2006.5	1959.2	1914.6	1868.4	1824.0	1780.5	1744.3	1697.4	1650.9	1613.1
15°	2084.9	2043.6	1986.2	1922.4	1863.0	1805.0	1755.0	1710.0	1648.8	1593.2	1546.9
17.5°	2117.5	2060.8	1999.0	1925.3	1856.6	1782.7	1718.4	1660.9	1592.8	1525.7	1471.2
20°	2127.9	2071.8	2000.5	1926.8	1845.6	1758.8	1689.4	1626.9	1553.8	1480.7	1418.2
22.5°	2121.5	2077.7	1998.5	1910.3	1827.1	1736.3	1657.9	1585.4	1504.3	1429.7	1357.2
25°	2077.4	2062.4	1987.4	1891.2	1796.2	1690.6	1600.0	1520.7	1428.2	1348.3	1269.5
27.5°	1974.5	2006.9	1960.4	1857.9	1752.3	1639.2	1537.3	1447.0	1351.0	1261.0	1182.6
30°	1875.6	1949.9	1929.9	1834.9	1716.9	1605.7	1491.3	1397.0	1294.5	1202.1	1124.6
32.5°	1740.1	1863.0	1882.4	1803.0	1680.9	1558.7	1438.8	1345.0	1238.0	1140.6	1065.1
35°	1524.4	1708.1	1792.4	1741.9	1619.4	1487.6	1363.8	1254.5	1147.0	1050.8	975.9
37.5°	1267.1	1517.4	1657.9	1661.5	1549.1	1412.0	1277.2	1168.7	1058.7	964.3	883.2
40°	1100.2	1371.3	1554.4	1595.1	1500.1	1352.0	1215.8	1105.2	997.8	905.3	812.2
42.5°	950.3	1220.4	1445.4	1516.0	1440.6	1293.6	1156.8	1041.2	936.8	849.3	754.2
45°	768.5	1004.6	1252.6	1378.8	1337.0	1200.8	1056.5	946.6	848.4	772.8	681.6
47.5°	648.2	814.7	1054.8	1225.4	1224.7	1100.3	958.4	853.0	762.1	691.2	617.4
50°	579.8	724.7	927.8	1121.4	1137.7	1033.4	898.4	794.1	709.1	634.8	575.4
52.5°	518.3	637.7	820.4	1006.0	1052.2	961.9	831.0	734.6	652.2	583.8	533.0
55°	438.0	530.4	669.1	842.8	912.8	849.1	732.9	642.9	576.0	518.5	474.8
57.5°	370.5	439.9	551.1	691.0	772.5	732.4	636.5	563.5	506.2	454.2	419.7
60°	328.0	384.8	479.2	596.1	686.0	657.9	576.0	507.9	459.2	414.3	381.7
62.5°	288.0	336.9	417.8	512.6	595.0	583.4	516.6	459.4	416.7	375.8	348.2
65°	231.8	267.4	330.5	404.9	471.1	476.7	428.6	389.9	351.7	319.3	294.9
67.5°	184.6	207.8	252.3	314.9	364.5	382.2	352.9	323.3	293.0	267.9	246.8
70°	155.6	174.3	206.8	257.4	303.0	321.7	304.9	281.8	255.5	234.9	216.8
72.5°	126.0	144.3	168.3	205.5	244.5	264.8	258.9	242.3	221.0	203.9	186.8
75°	95.0	100.6	116.8	141.9	172.4	190.0	194.3	185.6	168.7	155.6	145.5
77.5°	70.2	73.6	81.4	94.5	114.5	130.0	136.5	135.4	123.8	116.2	106.8
80°	56.3	58.1	61.9	67.5	82.5	98.1	102.5	102.5	94.3	91.2	81.9
82.5°	42.7	44.1	46.4	49.5	56.5	70.1	75.0	76.0	70.8	66.7	59.4
85°	24.4	23.7	25.0	26.9	28.1	31.9	39.4	40.6	39.4	34.3	32.4
87.5°	11.1	11.3	11.0	10.2	10.3	10.4	12.6	14.7	13.0	11.9	11.3
90°	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8	2.7	4.6	6.5
92.5°	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7	15.6	15.4	15.2
95°	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6	44.9	39.2	33.5
97.5°	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5	84.4	68.3	52.2
100°	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9	114.1	90.4	66.8
102.5°	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0	174.0	169.0	164.0
105°	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8	242.1	247.2	252.4
107.5°	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7	307.0	311.1	315.3
110°	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1	348.8	352.4	356.0



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0	388.2	391.4	394.7
115°	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9	450.9	453.9	456.8
117.5°	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2	507.5	510.8	514.0
120°	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4	548.0	550.5	553.1
122.5°	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2	582.9	585.7	588.4
125°	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3	635.6	637.9	640.1
127.5°	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5	684.0	686.5	689.0
130°	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1	714.9	717.6	720.3
132.5°	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2	745.6	748.0	750.2
135°	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7	786.5	789.3	792.1
137.5°	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7	826.6	828.6	830.5
140°	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5	852.9	854.3	855.7
142.5°	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9	875.1	876.4	877.7
145°	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1	909.0	908.8	908.7
147.5°	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9	939.1	938.5	937.8
150°	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8	958.5	957.3	956.2
152.5°	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6	975.3	973.9	972.6
155°	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1	999.5	997.9	996.4
157.5°	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3	1019.0	1017.6	1016.3
160°	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1030.5	1029.4	1028.3
162.5°	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5	1040.4	1039.3	1038.3
165°	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8	1053.8	1052.7	1051.7
167.5°	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8	1063.7	1062.7	1061.7
170°	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4	1069.3	1068.4	1067.3
172.5°	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2	1073.1	1072.0	1071.1
175°	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0	1077.7	1076.5	1075.4
177.5°	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8	1078.8	1077.8	1076.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1772.6	1769.1	1762.6	1752.6	1746.6	1736.1	1729.1	1733.1	1734.1	1733.1	1732.1
5°	1725.0	1711.9	1693.8	1676.3	1660.0	1642.5	1632.6	1628.2	1619.4	1614.4	1611.9
7.5°	1667.4	1644.8	1619.2	1588.7	1562.8	1535.7	1521.8	1514.9	1497.1	1487.4	1478.8
10°	1624.4	1588.8	1563.2	1523.2	1498.8	1463.2	1438.8	1439.5	1415.1	1401.3	1391.4
12.5°	1577.0	1537.8	1495.2	1459.2	1425.4	1396.8	1367.3	1355.5	1329.7	1316.4	1289.4
15°	1498.2	1452.6	1407.6	1358.9	1324.5	1280.2	1237.7	1185.9	1143.9	1107.7	1097.7
17.5°	1412.3	1355.8	1310.7	1253.4	1194.6	1120.0	1070.7	1040.6	1015.4	996.3	982.0
20°	1353.2	1295.8	1247.7	1161.5	1082.1	1031.5	995.2	972.2	945.9	925.3	914.0
22.5°	1291.3	1231.3	1165.7	1069.5	1007.6	967.0	934.7	908.2	890.4	874.3	864.1
25°	1203.3	1137.7	1029.6	963.4	913.4	870.9	848.4	832.2	813.4	791.6	781.6
27.5°	1110.4	1006.0	928.4	879.1	831.4	803.8	783.6	759.4	742.6	732.7	722.4
30°	1040.9	936.5	876.0	822.2	788.5	757.8	734.1	720.4	704.1	687.2	680.4
32.5°	963.4	880.0	822.0	777.2	743.0	716.9	698.1	675.9	664.1	653.8	639.4
35°	867.2	804.0	751.0	714.8	682.2	661.0	639.1	626.0	604.8	596.1	590.4
37.5°	785.7	731.0	691.4	653.1	627.4	603.9	590.5	569.6	560.4	548.3	536.5
40°	739.7	686.0	647.9	616.6	587.9	570.4	553.5	536.7	522.9	517.3	503.0
42.5°	692.8	649.0	610.9	576.7	557.4	538.9	517.6	505.2	491.0	481.8	473.0
45°	627.9	589.1	556.7	528.6	507.3	488.0	474.2	453.6	445.5	427.4	419.9
47.5°	571.0	534.9	503.9	477.2	456.5	443.8	423.7	407.6	394.6	383.5	373.9
50°	530.4	500.4	470.4	446.7	428.0	409.9	389.2	381.1	361.1	355.5	349.8
52.5°	493.4	465.0	437.5	414.3	395.5	377.9	359.7	349.1	335.7	330.0	325.9
55°	441.7	414.3	388.0	367.4	348.6	330.5	319.3	306.1	299.9	295.5	290.5
57.5°	389.7	365.0	344.9	324.0	305.2	290.7	277.8	269.9	263.4	257.6	251.7
60°	356.8	333.0	314.9	295.5	276.1	264.2	254.3	244.9	237.4	228.7	226.2
62.5°	321.7	301.0	284.4	265.5	248.7	237.8	228.3	219.4	210.4	197.7	194.2
65°	273.6	257.4	239.9	224.3	209.3	198.7	184.9	175.0	171.2	169.9	169.3
67.5°	230.2	214.8	199.8	183.8	170.2	160.3	153.4	151.8	149.2	148.5	146.7
70°	201.2	186.8	171.8	156.8	143.7	141.9	139.3	136.8	133.7	132.5	131.2
72.5°	175.2	160.3	145.3	133.3	127.7	125.3	122.9	120.3	118.2	117.0	116.2
75°	134.4	120.6	110.6	106.2	103.1	101.2	97.4	95.6	94.3	92.5	91.8
77.5°	96.7	88.9	84.4	81.6	78.4	76.3	74.2	72.3	71.0	70.6	69.6
80°	73.7	70.0	66.9	63.1	61.9	59.4	58.7	56.8	57.5	55.6	55.6
82.5°	57.2	52.5	49.9	48.1	46.9	44.8	44.3	43.4	43.5	42.1	42.1
85°	29.4	28.1	26.9	25.6	25.6	23.7	24.4	23.7	23.7	22.5	21.9
87.5°	11.2	11.0	10.3	10.6	10.8	10.6	10.8	10.4	10.6	10.8	10.4
90°	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3	18.2	19.1	19.6
92.5°	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0	19.4	19.9	20.2
95°	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1	33.0	33.8	34.2
97.5°	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1	42.7	43.5	43.9
100°	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2	48.6	50.0	50.8
102.5°	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2	51.0	52.8	54.0
105°	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4	53.2	55.1	56.4
107.5°	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6	60.7	58.8	58.1
110°	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7	84.4	67.1	58.8



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5	154.4	91.2	59.9
115°	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3	240.2	160.0	113.7
117.5°	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6	474.3	454.9	424.7
120°	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2	577.2	579.4	568.7
122.5°	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3	611.6	612.8	611.1
125°	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7	661.9	663.2	664.0
127.5°	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4	709.1	710.9	711.8
130°	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9	738.8	740.7	741.6
132.5°	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6	767.3	768.9	769.6
135°	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7	808.4	810.1	810.8
137.5°	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7	846.4	848.2	848.7
140°	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4	871.0	872.5	872.9
142.5°	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2	893.6	895.0	895.3
145°	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1	925.3	926.4	926.7
147.5°	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8	952.7	953.6	953.7
150°	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9	969.9	970.9	971.0
152.5°	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5	985.5	986.5	986.5
155°	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5	1006.5	1007.5	1007.4
157.5°	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2	1024.4	1025.6	1025.5
160°	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6	1034.5	1035.6	1035.5
162.5°	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2	1044.3	1045.5	1045.4
165°	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4
167.5°	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7	1065.9	1067.1	1067.0
170°	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8	1070.9	1072.1	1072.0
172.5°	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4	1074.6	1075.9	1075.7
175°	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5	1078.7	1079.9	1079.7
177.5°	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0	1078.9	1079.9	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1726.6	1727.6	1726.2	1727.1	1726.2	1727.6	1726.6	1732.1	1733.1	1734.1	1733.1
5°	1608.7	1601.2	1600.0	1598.1	1600.0	1601.2	1608.7	1611.9	1614.4	1619.4	1628.2
7.5°	1468.1	1467.0	1463.9	1459.5	1463.9	1467.0	1468.1	1478.8	1487.4	1497.1	1514.9
10°	1377.6	1374.5	1373.9	1369.5	1373.9	1374.5	1377.6	1391.4	1401.3	1415.1	1439.5
12.5°	1271.6	1251.6	1249.4	1238.5	1249.4	1251.6	1271.6	1289.4	1316.4	1329.7	1355.5
15°	1082.7	1079.0	1066.5	1058.3	1066.5	1079.0	1082.7	1097.7	1107.7	1143.9	1185.9
17.5°	974.8	962.5	958.6	956.9	958.6	962.5	974.8	982.0	996.3	1015.4	1040.6
20°	905.3	894.1	892.2	891.0	892.2	894.1	905.3	914.0	925.3	945.9	972.2
22.5°	857.3	845.5	840.7	836.9	840.7	845.5	857.3	864.1	874.3	890.4	908.2
25°	775.3	770.9	768.5	767.2	768.5	770.9	775.3	781.6	791.6	813.4	832.2
27.5°	711.3	701.6	699.8	696.5	699.8	701.6	711.3	722.4	732.7	742.6	759.4
30°	674.7	671.6	667.2	663.5	667.2	671.6	674.7	680.4	687.2	704.1	720.4
32.5°	631.8	629.2	625.3	623.5	625.3	629.2	631.8	639.4	653.8	664.1	675.9
35°	584.2	575.4	571.7	566.1	571.7	575.4	584.2	590.4	596.1	604.8	626.0
37.5°	533.8	529.2	523.9	525.8	523.9	529.2	533.8	536.5	548.3	560.4	569.6
40°	494.8	491.7	490.5	489.8	490.5	491.7	494.8	503.0	517.3	522.9	536.7
42.5°	463.8	455.2	451.9	451.8	451.9	455.2	463.8	473.0	481.8	491.0	505.2
45°	416.7	408.6	403.0	403.6	403.0	408.6	416.7	419.9	427.4	445.5	453.6
47.5°	368.5	368.3	364.8	365.8	364.8	368.3	368.5	373.9	383.5	394.6	407.6
50°	345.5	341.8	339.2	339.9	339.2	341.8	345.5	349.8	355.5	361.1	381.1
52.5°	323.5	320.2	318.3	320.9	318.3	320.2	323.5	325.9	330.0	335.7	349.1
55°	287.4	283.6	283.0	282.4	283.0	283.6	287.4	290.5	295.5	299.9	306.1
57.5°	247.0	244.5	240.8	239.1	240.8	244.5	247.0	251.7	257.6	263.4	269.9
60°	218.0	213.0	206.8	206.2	206.8	213.0	218.0	226.2	228.7	237.4	244.9
62.5°	191.5	190.5	189.3	189.1	189.3	190.5	191.5	194.2	197.7	210.4	219.4
65°	168.0	167.5	168.0	168.7	168.0	167.5	168.0	169.3	169.9	171.2	175.0
67.5°	146.4	145.3	144.2	144.7	144.2	145.3	146.4	146.7	148.5	149.2	151.8
70°	130.0	129.3	128.7	128.7	128.7	129.3	130.0	131.2	132.5	133.7	136.8
72.5°	114.0	113.8	113.2	112.7	113.2	113.8	114.0	116.2	117.0	118.2	120.3
75°	91.2	89.9	89.9	89.9	89.9	89.9	91.2	91.8	92.5	94.3	95.6
77.5°	69.5	68.8	68.2	67.8	68.2	68.8	69.5	69.6	70.6	71.0	72.3
80°	55.0	54.4	53.7	53.7	53.7	54.4	55.0	55.6	55.6	57.5	56.8
82.5°	42.0	41.3	41.3	40.8	41.3	41.3	42.0	42.1	42.1	43.5	43.4
85°	22.5	23.2	22.5	23.7	22.5	23.2	22.5	21.9	22.5	23.7	23.7
87.5°	10.5	10.0	10.6	10.2	10.6	10.0	10.5	10.4	10.8	10.6	10.4
90°	20.0	20.3	20.7	21.0	20.7	20.3	20.0	19.6	19.1	18.2	17.3
92.5°	20.4	20.6	20.8	21.0	20.8	20.6	20.4	20.2	19.9	19.4	19.0
95°	34.0	33.8	33.7	33.5	33.7	33.8	34.0	34.2	33.8	33.0	32.1
97.5°	44.1	44.3	44.5	44.7	44.5	44.3	44.1	43.9	43.5	42.7	42.1
100°	51.1	51.5	51.9	52.2	51.9	51.5	51.1	50.8	50.0	48.6	47.2
102.5°	54.5	55.0	55.4	55.9	55.4	55.0	54.5	54.0	52.8	51.0	49.2
105°	57.2	57.8	58.5	59.2	58.5	57.8	57.2	56.4	55.1	53.2	51.4
107.5°	58.9	59.5	60.3	60.9	60.3	59.5	58.9	58.1	58.8	60.7	62.6
110°	59.4	60.2	60.8	61.6	60.8	60.2	59.4	58.8	67.1	84.4	101.7



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	60.5	61.1	61.6	62.2	61.6	61.1	60.5	59.9	91.2	154.4	217.5
115°	101.3	88.8	76.3	63.9	76.3	88.8	101.3	113.7	160.0	240.2	320.3
117.5°	383.7	342.8	301.8	260.8	301.8	342.8	383.7	424.7	454.9	474.3	493.6
120°	545.4	522.0	498.6	475.2	498.6	522.0	545.4	568.7	579.4	577.2	575.2
122.5°	606.6	602.1	597.5	593.0	597.5	602.1	606.6	611.1	612.8	611.6	610.3
125°	664.6	665.0	665.5	666.1	665.5	665.0	664.6	664.0	663.2	661.9	660.7
127.5°	711.9	712.0	712.1	712.2	712.1	712.0	711.9	711.8	710.9	709.1	707.4
130°	741.4	741.2	741.0	740.9	741.0	741.2	741.4	741.6	740.7	738.8	736.9
132.5°	769.4	769.2	769.1	768.9	769.1	769.2	769.4	769.6	768.9	767.3	765.6
135°	810.5	810.1	809.8	809.4	809.8	810.1	810.5	810.8	810.1	808.4	806.7
137.5°	848.2	847.5	846.9	846.4	846.9	847.5	848.2	848.7	848.2	846.4	844.7
140°	872.0	871.1	870.3	869.4	870.3	871.1	872.0	872.9	872.5	871.0	869.4
142.5°	894.5	893.6	892.8	891.9	892.8	893.6	894.5	895.3	895.0	893.6	892.2
145°	925.8	924.9	924.1	923.2	924.1	924.9	925.8	926.7	926.4	925.3	924.1
147.5°	952.9	952.2	951.5	950.7	951.5	952.2	952.9	953.7	953.6	952.7	951.8
150°	970.2	969.3	968.4	967.6	968.4	969.3	970.2	971.0	970.9	969.9	968.9
152.5°	985.4	984.2	983.1	981.9	983.1	984.2	985.4	986.5	986.5	985.5	984.5
155°	1006.0	1004.6	1003.2	1001.8	1003.2	1004.6	1006.0	1007.4	1007.5	1006.5	1005.5
157.5°	1024.1	1022.8	1021.4	1020.1	1021.4	1022.8	1024.1	1025.5	1025.6	1024.4	1023.2
160°	1034.3	1033.1	1031.9	1030.7	1031.9	1033.1	1034.3	1035.5	1035.6	1034.5	1033.6
162.5°	1043.8	1042.4	1040.9	1039.4	1040.9	1042.4	1043.8	1045.4	1045.5	1044.3	1043.2
165°	1056.1	1054.9	1053.7	1052.5	1053.7	1054.9	1056.1	1057.4	1057.4	1056.1	1054.9
167.5°	1065.4	1063.9	1062.3	1060.8	1062.3	1063.9	1065.4	1067.0	1067.1	1065.9	1064.7
170°	1070.4	1068.9	1067.3	1065.8	1067.3	1068.9	1070.4	1072.0	1072.1	1070.9	1069.8
172.5°	1074.2	1072.6	1071.1	1069.5	1071.1	1072.6	1074.2	1075.7	1075.9	1074.6	1073.4
175°	1077.9	1076.2	1074.5	1072.8	1074.5	1076.2	1077.9	1079.7	1079.9	1078.7	1077.5
177.5°	1078.5	1077.3	1076.0	1074.8	1076.0	1077.3	1078.5	1079.8	1079.9	1078.9	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1729.1	1736.1	1746.6	1752.6	1762.6	1769.1	1772.6	1779.1	1782.6	1795.1	1808.1
5°	1632.6	1642.5	1660.0	1676.3	1693.8	1711.9	1725.0	1740.0	1753.7	1777.4	1802.5
7.5°	1521.8	1535.7	1562.8	1588.7	1619.2	1644.8	1667.4	1693.0	1715.9	1749.9	1785.3
10°	1438.8	1463.2	1498.8	1523.2	1563.2	1588.8	1624.4	1652.5	1684.4	1729.3	1769.4
12.5°	1367.3	1396.8	1425.4	1459.2	1495.2	1537.8	1577.0	1613.1	1650.9	1697.4	1744.3
15°	1237.7	1280.2	1324.5	1358.9	1407.6	1452.6	1498.2	1546.9	1593.2	1648.8	1710.0
17.5°	1070.7	1120.0	1194.6	1253.4	1310.7	1355.8	1412.3	1471.2	1525.7	1592.8	1660.9
20°	995.2	1031.5	1082.1	1161.5	1247.7	1295.8	1353.2	1418.2	1480.7	1553.8	1626.9
22.5°	934.7	967.0	1007.6	1069.5	1165.7	1231.3	1291.3	1357.2	1429.7	1504.3	1585.4
25°	848.4	870.9	913.4	963.4	1029.6	1137.7	1203.3	1269.5	1348.3	1428.2	1520.7
27.5°	783.6	803.8	831.4	879.1	928.4	1006.0	1110.4	1182.6	1261.0	1351.0	1447.0
30°	734.1	757.8	788.5	822.2	876.0	936.5	1040.9	1124.6	1202.1	1294.5	1397.0
32.5°	698.1	716.9	743.0	777.2	822.0	880.0	963.4	1065.1	1140.6	1238.0	1345.0
35°	639.1	661.0	682.2	714.8	751.0	804.0	867.2	975.9	1050.8	1147.0	1254.5
37.5°	590.5	603.9	627.4	653.1	691.4	731.0	785.7	883.2	964.3	1058.7	1168.7
40°	553.5	570.4	587.9	616.6	647.9	686.0	739.7	812.2	905.3	997.8	1105.2
42.5°	517.6	538.9	557.4	576.7	610.9	649.0	692.8	754.2	849.3	936.8	1041.2
45°	474.2	488.0	507.3	528.6	556.7	589.1	627.9	681.6	772.8	848.4	946.6
47.5°	423.7	443.8	456.5	477.2	503.9	534.9	571.0	617.4	691.2	762.1	853.0
50°	389.2	409.9	428.0	446.7	470.4	500.4	530.4	575.4	634.8	709.1	794.1
52.5°	359.7	377.9	395.5	414.3	437.5	465.0	493.4	533.0	583.8	652.2	734.6
55°	319.3	330.5	348.6	367.4	388.0	414.3	441.7	474.8	518.5	576.0	642.9
57.5°	277.8	290.7	305.2	324.0	344.9	365.0	389.7	419.7	454.2	506.2	563.5
60°	254.3	264.2	276.1	295.5	314.9	333.0	356.8	381.7	414.3	459.2	507.9
62.5°	228.3	237.8	248.7	265.5	284.4	301.0	321.7	348.2	375.8	416.7	459.4
65°	184.9	198.7	209.3	224.3	239.9	257.4	273.6	294.9	319.3	351.7	389.9
67.5°	153.4	160.3	170.2	183.8	199.8	214.8	230.2	246.8	267.9	293.0	323.3
70°	139.3	141.9	143.7	156.8	171.8	186.8	201.2	216.8	234.9	255.5	281.8
72.5°	122.9	125.3	127.7	133.3	145.3	160.3	175.2	186.8	203.9	221.0	242.3
75°	97.4	101.2	103.1	106.2	110.6	120.6	134.4	145.5	155.6	168.7	185.6
77.5°	74.2	76.3	78.4	81.6	84.4	88.9	96.7	106.8	116.2	123.8	135.4
80°	58.7	59.4	61.9	63.1	66.9	70.0	73.7	81.9	91.2	94.3	102.5
82.5°	44.3	44.8	46.9	48.1	49.9	52.5	57.2	59.4	66.7	70.8	76.0
85°	24.4	23.7	25.6	25.6	26.9	28.1	29.4	32.4	34.3	39.4	40.6
87.5°	10.8	10.6	10.8	10.6	10.3	11.0	11.2	11.3	11.9	13.0	14.7
90°	16.5	15.6	14.2	12.8	11.4	10.0	8.4	6.5	4.6	2.7	0.8
92.5°	18.5	18.1	17.4	16.7	16.0	15.3	15.1	15.2	15.4	15.6	15.7
95°	31.2	30.4	29.2	28.0	26.7	25.5	27.8	33.5	39.2	44.9	50.6
97.5°	41.3	40.7	37.8	35.1	32.3	29.4	36.1	52.2	68.3	84.4	100.5
100°	45.8	44.4	41.5	38.5	35.5	32.6	43.0	66.8	90.4	114.1	137.9
102.5°	47.5	45.7	70.3	94.9	119.5	144.1	158.9	164.0	169.0	174.0	179.0
105°	49.4	47.5	94.8	142.0	189.3	236.6	257.6	252.4	247.2	242.1	236.8
107.5°	64.6	66.5	123.2	179.9	236.6	293.3	319.5	315.3	311.1	307.0	302.7
110°	119.0	136.3	186.4	236.4	286.4	336.5	359.6	356.0	352.4	348.8	345.1



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	280.7	343.9	356.2	368.6	381.0	393.3	397.9	394.7	391.4	388.2	385.0
115°	400.5	480.7	476.4	472.0	467.7	463.3	459.7	456.8	453.9	450.9	447.9
117.5°	513.0	532.4	529.5	526.4	523.5	520.5	517.4	514.0	510.8	507.5	504.2
120°	573.2	571.0	567.9	564.8	561.7	558.6	555.7	553.1	550.5	548.0	545.4
122.5°	609.0	607.8	604.4	601.0	597.6	594.3	591.2	588.4	585.7	582.9	580.2
125°	659.5	658.3	655.0	651.8	648.4	645.1	642.4	640.1	637.9	635.6	633.3
127.5°	705.6	703.8	701.3	698.9	696.4	694.0	691.5	689.0	686.5	684.0	681.5
130°	735.0	733.1	731.2	729.3	727.3	725.5	723.1	720.3	717.6	714.9	712.1
132.5°	764.0	762.4	760.4	758.6	756.7	754.7	752.6	750.2	748.0	745.6	743.2
135°	804.9	803.2	801.6	800.1	798.5	797.0	794.8	792.1	789.3	786.5	783.7
137.5°	843.1	841.4	839.6	837.8	836.1	834.3	832.4	830.5	828.6	826.6	824.7
140°	867.9	866.3	864.4	862.5	860.5	858.7	857.0	855.7	854.3	852.9	851.5
142.5°	890.8	889.3	887.2	885.0	882.8	880.6	878.9	877.7	876.4	875.1	873.9
145°	922.8	921.6	918.7	915.7	912.8	909.9	908.5	908.7	908.8	909.0	909.1
147.5°	950.9	950.0	947.1	944.1	941.3	938.3	937.2	937.8	938.5	939.1	939.9
150°	967.8	966.8	964.0	961.2	958.5	955.7	955.0	956.2	957.3	958.5	959.8
152.5°	983.4	982.4	979.7	977.1	974.4	971.8	971.2	972.6	973.9	975.3	976.6
155°	1004.4	1003.4	1001.4	999.2	997.2	995.1	994.8	996.4	997.9	999.5	1001.1
157.5°	1022.1	1020.8	1019.4	1018.0	1016.5	1015.0	1015.0	1016.3	1017.6	1019.0	1020.3
160°	1032.5	1031.4	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4
162.5°	1042.0	1040.8	1039.9	1039.0	1038.1	1037.2	1037.3	1038.3	1039.3	1040.4	1041.5
165°	1053.7	1052.5	1052.0	1051.4	1050.9	1050.4	1050.7	1051.7	1052.7	1053.8	1054.8
167.5°	1063.5	1062.3	1061.8	1061.4	1060.9	1060.4	1060.6	1061.7	1062.7	1063.7	1064.8
170°	1068.5	1067.3	1067.0	1066.6	1066.2	1065.9	1066.2	1067.3	1068.4	1069.3	1070.4
172.5°	1072.3	1071.1	1070.7	1070.3	1070.0	1069.7	1070.0	1071.1	1072.0	1073.1	1074.2
175°	1076.3	1075.1	1074.7	1074.4	1074.1	1073.7	1074.2	1075.4	1076.5	1077.7	1079.0
177.5°	1077.0	1076.0	1075.9	1075.7	1075.6	1075.5	1075.9	1076.8	1077.8	1078.8	1079.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1808.6	1810.0	1820.1	1824.6	1833.6	1837.0	1841.1	1840.0	1840.0	1842.1	1856.0
5°	1812.5	1825.0	1843.7	1861.8	1879.3	1894.3	1904.3	1914.3	1918.1	1936.2	1952.4
7.5°	1806.0	1829.0	1859.9	1887.6	1920.7	1946.5	1968.1	1987.4	2000.7	2027.0	2054.0
10°	1797.5	1829.9	1864.9	1900.5	1946.1	1980.5	2015.5	2042.4	2051.1	2090.5	2113.0
12.5°	1780.5	1824.0	1868.4	1914.6	1959.2	2006.5	2045.0	2071.8	2102.6	2138.0	2179.5
15°	1755.0	1805.0	1863.0	1922.4	1986.2	2043.6	2084.9	2131.7	2165.4	2204.2	2240.4
17.5°	1718.4	1782.7	1856.6	1925.3	1999.0	2060.8	2117.5	2162.4	2186.2	2208.3	2213.7
20°	1689.4	1758.8	1845.6	1926.8	2000.5	2071.8	2127.9	2165.4	2171.7	2172.3	2139.2
22.5°	1657.9	1736.3	1827.1	1910.3	1998.5	2077.7	2121.5	2137.5	2112.7	2070.4	2006.3
25°	1600.0	1690.6	1796.2	1891.2	1987.4	2062.4	2077.4	2049.3	1962.4	1871.2	1755.6
27.5°	1537.3	1639.2	1752.3	1857.9	1960.4	2006.9	1974.5	1873.2	1716.8	1580.8	1416.0
30°	1491.3	1605.7	1716.9	1834.9	1929.9	1949.9	1875.6	1726.2	1543.8	1338.9	1174.6
32.5°	1438.8	1558.7	1680.9	1803.0	1882.4	1863.0	1740.1	1556.3	1342.4	1140.9	985.6
35°	1363.8	1487.6	1619.4	1741.9	1792.4	1708.1	1524.4	1285.2	1066.5	878.4	771.6
37.5°	1277.2	1412.0	1549.1	1661.5	1657.9	1517.4	1267.1	1020.1	836.3	725.1	649.0
40°	1215.8	1352.0	1500.1	1595.1	1554.4	1371.3	1100.2	867.2	732.9	644.2	588.6
42.5°	1156.8	1293.6	1440.6	1516.0	1445.4	1220.4	950.3	767.7	656.9	587.7	542.6
45°	1056.5	1200.8	1337.0	1378.8	1252.6	1004.6	768.5	636.0	562.3	511.0	479.8
47.5°	958.4	1100.3	1224.7	1225.4	1054.8	814.7	648.2	550.4	487.5	447.8	425.1
50°	898.4	1033.4	1137.7	1121.4	927.8	724.7	579.8	495.5	443.0	412.4	388.6
52.5°	831.0	961.9	1052.2	1006.0	820.4	637.7	518.3	447.4	404.0	377.3	356.1
55°	732.9	849.1	912.8	842.8	669.1	530.4	438.0	382.4	349.8	327.3	309.2
57.5°	636.5	732.4	772.5	691.0	551.1	439.9	370.5	328.7	296.5	280.4	271.0
60°	576.0	657.9	686.0	596.1	479.2	384.8	328.0	289.3	265.5	254.9	245.6
62.5°	516.6	583.4	595.0	512.6	417.8	336.9	288.0	255.3	239.5	229.4	220.5
65°	428.6	476.7	471.1	404.9	330.5	267.4	231.8	211.8	199.9	185.6	169.9
67.5°	352.9	382.2	364.5	314.9	252.3	207.8	184.6	169.4	154.7	141.0	137.5
70°	304.9	321.7	303.0	257.4	206.8	174.3	155.6	137.5	128.7	125.6	119.9
72.5°	258.9	264.8	244.5	205.5	168.3	144.3	126.0	115.9	111.2	108.6	104.9
75°	194.3	190.0	172.4	141.9	116.8	100.6	95.0	91.2	88.1	85.6	83.7
77.5°	136.5	130.0	114.5	94.5	81.4	73.6	70.2	68.2	66.7	65.5	63.6
80°	102.5	98.1	82.5	67.5	61.9	58.1	56.3	53.7	53.7	52.5	50.6
82.5°	75.0	70.1	56.5	49.5	46.4	44.1	42.7	41.3	40.8	41.0	39.6
85°	39.4	31.9	28.1	26.9	25.0	23.7	24.4	23.2	23.2	23.2	22.5
87.5°	12.6	10.4	10.3	10.2	11.0	11.3	11.1	11.3	12.1	11.8	12.5
90°	2.7	4.6	6.5	8.4	10.0	11.4	12.8	14.2	15.6	16.5	17.3
92.5°	15.6	15.4	15.2	15.1	15.3	16.0	16.7	17.4	18.1	18.5	19.0
95°	44.9	39.2	33.5	27.8	25.5	26.7	28.0	29.2	30.4	31.2	32.1
97.5°	84.4	68.3	52.2	36.1	29.4	32.3	35.1	37.8	40.7	41.3	42.1
100°	114.1	90.4	66.8	43.0	32.6	35.5	38.5	41.5	44.4	45.8	47.2
102.5°	174.0	169.0	164.0	158.9	144.1	119.5	94.9	70.3	45.7	47.5	49.2
105°	242.1	247.2	252.4	257.6	236.6	189.3	142.0	94.8	47.5	49.4	51.4
107.5°	307.0	311.1	315.3	319.5	293.3	236.6	179.9	123.2	66.5	64.6	62.6
110°	348.8	352.4	356.0	359.6	336.5	286.4	236.4	186.4	136.3	119.0	101.7



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	388.2	391.4	394.7	397.9	393.3	381.0	368.6	356.2	343.9	280.7	217.5
115°	450.9	453.9	456.8	459.7	463.3	467.7	472.0	476.4	480.7	400.5	320.3
117.5°	507.5	510.8	514.0	517.4	520.5	523.5	526.4	529.5	532.4	513.0	493.6
120°	548.0	550.5	553.1	555.7	558.6	561.7	564.8	567.9	571.0	573.2	575.2
122.5°	582.9	585.7	588.4	591.2	594.3	597.6	601.0	604.4	607.8	609.0	610.3
125°	635.6	637.9	640.1	642.4	645.1	648.4	651.8	655.0	658.3	659.5	660.7
127.5°	684.0	686.5	689.0	691.5	694.0	696.4	698.9	701.3	703.8	705.6	707.4
130°	714.9	717.6	720.3	723.1	725.5	727.3	729.3	731.2	733.1	735.0	736.9
132.5°	745.6	748.0	750.2	752.6	754.7	756.7	758.6	760.4	762.4	764.0	765.6
135°	786.5	789.3	792.1	794.8	797.0	798.5	800.1	801.6	803.2	804.9	806.7
137.5°	826.6	828.6	830.5	832.4	834.3	836.1	837.8	839.6	841.4	843.1	844.7
140°	852.9	854.3	855.7	857.0	858.7	860.5	862.5	864.4	866.3	867.9	869.4
142.5°	875.1	876.4	877.7	878.9	880.6	882.8	885.0	887.2	889.3	890.8	892.2
145°	909.0	908.8	908.7	908.5	909.9	912.8	915.7	918.7	921.6	922.8	924.1
147.5°	939.1	938.5	937.8	937.2	938.3	941.3	944.1	947.1	950.0	950.9	951.8
150°	958.5	957.3	956.2	955.0	955.7	958.5	961.2	964.0	966.8	967.8	968.9
152.5°	975.3	973.9	972.6	971.2	971.8	974.4	977.1	979.7	982.4	983.4	984.5
155°	999.5	997.9	996.4	994.8	995.1	997.2	999.2	1001.4	1003.4	1004.4	1005.5
157.5°	1019.0	1017.6	1016.3	1015.0	1015.0	1016.5	1018.0	1019.4	1020.8	1022.1	1023.2
160°	1030.5	1029.4	1028.3	1027.3	1027.3	1028.3	1029.4	1030.5	1031.4	1032.5	1033.6
162.5°	1040.4	1039.3	1038.3	1037.3	1037.2	1038.1	1039.0	1039.9	1040.8	1042.0	1043.2
165°	1053.8	1052.7	1051.7	1050.7	1050.4	1050.9	1051.4	1052.0	1052.5	1053.7	1054.9
167.5°	1063.7	1062.7	1061.7	1060.6	1060.4	1060.9	1061.4	1061.8	1062.3	1063.5	1064.7
170°	1069.3	1068.4	1067.3	1066.2	1065.9	1066.2	1066.6	1067.0	1067.3	1068.5	1069.8
172.5°	1073.1	1072.0	1071.1	1070.0	1069.7	1070.0	1070.3	1070.7	1071.1	1072.3	1073.4
175°	1077.7	1076.5	1075.4	1074.2	1073.7	1074.1	1074.4	1074.7	1075.1	1076.3	1077.5
177.5°	1078.8	1077.8	1076.8	1075.9	1075.5	1075.6	1075.7	1075.9	1076.0	1077.0	1078.0
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
0°	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1	1798.1
2.5°	1861.1	1867.5	1870.5	1870.5	1874.0	1872.6	1871.0
5°	1968.1	1979.9	1982.4	1993.7	2001.7	1999.3	2000.5
7.5°	2074.4	2093.4	2112.4	2121.0	2122.3	2127.4	2129.2
10°	2139.8	2155.5	2184.8	2180.4	2202.3	2214.8	2194.2
12.5°	2202.8	2223.9	2244.3	2249.9	2262.3	2266.3	2258.1
15°	2259.8	2271.0	2272.3	2269.1	2272.9	2269.8	2257.9
17.5°	2206.5	2188.3	2151.3	2133.8	2119.9	2099.5	2091.2
20°	2118.6	2064.8	2002.4	1977.4	1948.0	1890.5	1904.3
22.5°	1928.7	1867.4	1805.0	1732.0	1697.1	1642.7	1639.4
25°	1633.1	1527.5	1411.4	1330.2	1282.6	1228.3	1204.5
27.5°	1269.7	1136.9	1041.6	993.4	949.5	906.4	904.7
30°	1030.9	930.9	857.2	816.0	789.0	770.9	774.7
32.5°	868.9	800.5	750.7	716.5	696.6	683.0	682.7
35°	710.4	663.5	631.6	617.3	602.9	592.9	593.5
37.5°	607.9	579.8	562.1	546.2	537.2	532.3	529.5
40°	555.4	532.3	518.5	509.2	501.7	494.8	493.6
42.5°	514.0	494.8	481.1	473.7	466.7	461.9	460.6
45°	456.1	440.4	428.0	419.9	416.7	412.4	412.4
47.5°	405.7	390.4	380.6	375.5	370.1	367.2	367.1
50°	371.8	359.9	351.1	348.0	343.6	341.8	341.1
52.5°	341.3	332.4	326.1	324.0	322.1	319.8	320.2
55°	299.9	294.9	292.4	290.5	287.4	283.6	286.2
57.5°	265.1	260.8	254.0	248.2	245.3	242.6	243.7
60°	240.5	231.8	223.1	216.1	214.3	208.6	208.6
62.5°	209.5	197.3	186.5	182.7	180.8	178.2	177.7
65°	161.2	156.2	153.7	151.2	149.9	149.9	148.7
67.5°	133.5	131.6	128.8	128.2	126.9	126.6	126.2
70°	118.1	115.6	114.3	113.7	112.4	113.1	111.2
72.5°	103.1	101.1	100.9	99.2	98.5	98.6	97.2
75°	81.2	81.2	80.6	80.0	78.8	78.1	78.8
77.5°	62.5	62.6	61.5	61.4	61.2	61.4	60.7
80°	50.0	50.6	50.0	49.3	48.8	49.3	48.8
82.5°	39.5	38.6	38.5	38.4	38.2	37.8	37.7
85°	22.5	23.2	22.5	21.9	21.9	21.9	22.5
87.5°	12.1	12.3	12.4	12.5	12.6	12.6	12.2
90°	18.2	19.1	19.6	20.0	20.3	20.7	21.0
92.5°	19.4	19.9	20.2	20.4	20.6	20.8	21.0
95°	33.0	33.8	34.2	34.0	33.8	33.7	33.5
97.5°	42.7	43.5	43.9	44.1	44.3	44.5	44.7
100°	48.6	50.0	50.8	51.1	51.5	51.9	52.2
102.5°	51.0	52.8	54.0	54.5	55.0	55.4	55.9
105°	53.2	55.1	56.4	57.2	57.8	58.5	59.2
107.5°	60.7	58.8	58.1	58.9	59.5	60.3	60.9
110°	84.4	67.1	58.8	59.4	60.2	60.8	61.6



TEST NUMBER: P331853-930

CATALOG NUMBER: S122RDIW-S1005D970U930-4F0-1E-UDD-A

CANDELA DISTRIBUTION (continued):

	330°	335°	340°	345°	350°	355°	360°
112.5°	154.4	91.2	59.9	60.5	61.1	61.6	62.2
115°	240.2	160.0	113.7	101.3	88.8	76.3	63.9
117.5°	474.3	454.9	424.7	383.7	342.8	301.8	260.8
120°	577.2	579.4	568.7	545.4	522.0	498.6	475.2
122.5°	611.6	612.8	611.1	606.6	602.1	597.5	593.0
125°	661.9	663.2	664.0	664.6	665.0	665.5	666.1
127.5°	709.1	710.9	711.8	711.9	712.0	712.1	712.2
130°	738.8	740.7	741.6	741.4	741.2	741.0	740.9
132.5°	767.3	768.9	769.6	769.4	769.2	769.1	768.9
135°	808.4	810.1	810.8	810.5	810.1	809.8	809.4
137.5°	846.4	848.2	848.7	848.2	847.5	846.9	846.4
140°	871.0	872.5	872.9	872.0	871.1	870.3	869.4
142.5°	893.6	895.0	895.3	894.5	893.6	892.8	891.9
145°	925.3	926.4	926.7	925.8	924.9	924.1	923.2
147.5°	952.7	953.6	953.7	952.9	952.2	951.5	950.7
150°	969.9	970.9	971.0	970.2	969.3	968.4	967.6
152.5°	985.5	986.5	986.5	985.4	984.2	983.1	981.9
155°	1006.5	1007.5	1007.4	1006.0	1004.6	1003.2	1001.8
157.5°	1024.4	1025.6	1025.5	1024.1	1022.8	1021.4	1020.1
160°	1034.5	1035.6	1035.5	1034.3	1033.1	1031.9	1030.7
162.5°	1044.3	1045.5	1045.4	1043.8	1042.4	1040.9	1039.4
165°	1056.1	1057.4	1057.4	1056.1	1054.9	1053.7	1052.5
167.5°	1065.9	1067.1	1067.0	1065.4	1063.9	1062.3	1060.8
170°	1070.9	1072.1	1072.0	1070.4	1068.9	1067.3	1065.8
172.5°	1074.6	1075.9	1075.7	1074.2	1072.6	1071.1	1069.5
175°	1078.7	1079.9	1079.7	1077.9	1076.2	1074.5	1072.8
177.5°	1078.9	1079.9	1079.8	1078.5	1077.3	1076.0	1074.8
180°	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6	1076.6

(END OF REPORT)