

Scaled data based on original data using  
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State  
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331777-930

Luminaire Tested: **S122RDIW-S290D1240U930-4F0-1E-UDD-A**

Issue Date: 3/3/2020

**Test Information**

Test Method: LM-79-08  
Report Number: P331777-930  
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,  
Test Lab: INNOVATION CENTER  
Issue Date: 3/3/2020  
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)  
Product Line: NEO-RAY  
Catalog Number: S122RDIW-S290D1240U930-4F0-1E-UDD-A  
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE  
DOWNLIGHT 290 LUMENS PER FOOT, ASYMMETRIC DIFFUSER, REGRESSED HOUSING  
UPLIGHT 1240 LUMENS PER FOOT, NO LENS  
Light Source: -  
Ballast/Driver: ELECTRONIC DRIVER

**Summary**


Lumens per Lamp: N/A  
Luminaire Lumens: 4963.7 lumens  
Efficiency: N/A  
Efficacy: 106.5 lumens/watt  
Spacing Criteria (0/90/45): 0.86 / 1.16 / 1.02  
Luminous Opening: Rectangular (W 4' x L: 0.17' x H: 0')  
CIE Type: Semi-Indirect  
  
Input Watts (W): 46.6  
Input Voltage (V): 120  
Input Current (Ain): NR  
Voltage Rise (V): NR  
Power Factor: NR  
Total Harmonic Distortion (THDi): NR  
Frequency (hertz): 60  
Stabilization Time: NR  
Operation Time: NR  
Ambient Temperature (°C): NR  
Test Distance: 25 FT



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

### Luminous Intensity Polar Plot



— 0°-180°    - - 45°-225°    - - - 90°-270°    - - - 135°-315°



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:**

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	100	100	100	100	88	88	88	88	66	66	66	46	46	46	27	27	27	19
1	91	87	83	80	80	77	74	71	58	56	54	41	39	38	24	24	23	16
2	83	76	71	66	73	68	63	59	51	48	45	36	34	33	22	21	20	14
3	76	67	60	55	67	60	54	49	45	42	38	32	30	28	20	19	18	12
4	69	60	52	47	61	53	47	42	40	36	33	29	26	24	18	16	15	11
5	64	53	46	40	56	47	41	36	36	32	28	26	23	21	16	15	14	10
6	59	47	40	35	52	42	36	31	32	28	25	23	21	18	15	13	12	9
7	54	43	35	30	48	38	32	27	29	25	22	21	18	16	14	12	11	8
8	50	39	32	27	44	35	28	24	27	22	19	19	17	15	12	11	10	7
9	47	35	28	24	41	32	26	21	25	20	17	18	15	13	12	10	9	7
10	43	32	26	21	38	29	23	19	23	18	15	16	14	12	11	9	8	6

**AVERAGE LUMINANCE (cd/sqm):**

	0°	90°	180°	270°
0°	8606	8606	8606	8606
5°	9611	8660	7679	8660
10°	10663	8599	6655	8599
15°	11188	8473	5244	8473
20°	9699	8285	4538	8285
25°	6360	8031	4051	8031
30°	4282	7720	3667	7720
35°	3467	7330	3307	7330
40°	3084	6905	3060	6905
45°	2790	6405	2731	6405
50°	2539	5913	2532	5913
55°	2387	5362	2356	5362
60°	1999	4863	1973	4863
65°	1685	4413	1910	4413
70°	1553	3942	1803	3942
75°	1454	3431	1666	3431
80°	1339	2827	1478	2827
85°	1241	2242	1297	2242



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**ZONAL LUMENS:**

Zone	Lumens	% Fixture
0°-10°	50.5	1.0
10°-20°	140.8	2.8
20°-30°	181.4	3.7
30°-40°	172.4	3.5
40°-50°	147.7	3.0
50°-60°	112.5	2.3
60°-70°	71.1	1.4
70°-80°	35.5	0.7
80°-90°	12.6	0.3
90°-100°	46.0	0.9
100°-110°	168.6	3.4
110°-120°	450.7	9.1
120°-130°	744.0	15.0
130°-140°	791.2	15.9
140°-150°	735.4	14.8
150°-160°	591.2	11.9
160°-170°	381.0	7.7
170°-180°	131.1	2.6
0°-30°	372.7	7.5
0°-40°	545.1	11.0
0°-60°	805.3	16.2
0°-90°	924.5	18.6
90°-120°	665.3	13.4
90°-150°	2935.8	59.1
90°-180°	4039.0	81.4
0°-180°	4963.7	100.0

**CANDELA DISTRIBUTION:**

	0°	90°	180°	270°	360°	Flux
0°	533	533	533	533	533	
5°	593	534	474	534	593	59
15°	669	507	314	507	669	181
25°	357	451	227	451	357	169
35°	176	372	168	372	176	113
45°	122	280	120	280	122	95
55°	85	190	84	190	85	74
65°	44	116	50	116	44	45
75°	23	55	27	55	23	25
85°	7	12	7	12	7	8
90°	27	1	27	1	27	12
95°	43	65	43	65	43	40
105°	76	303	76	303	76	79
115°	82	574	82	574	82	205
125°	853	811	853	811	853	738
135°	1036	1003	1036	1003	1036	799
145°	1182	1164	1182	1164	1182	739
155°	1282	1282	1282	1282	1282	592
165°	1347	1350	1347	1350	1347	380
175°	1373	1381	1373	1381	1373	131
180°	1378	1378	1378	1378	1378	



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (FULL):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	554.6	555.1	555.5	554.5	554.5	553.6	551.6	550.2	546.0	545.4	545.4
5°	593.0	592.6	593.4	590.9	587.7	586.9	583.3	578.7	573.9	568.6	567.4
7.5°	631.1	630.6	629.1	628.7	626.1	620.5	614.9	608.9	600.9	593.0	589.1
10°	650.4	656.6	652.8	646.4	647.6	639.0	634.3	626.3	619.6	608.0	605.4
12.5°	669.4	671.8	670.6	666.9	665.3	659.3	653.0	646.0	633.7	623.3	614.2
15°	669.3	672.8	673.8	672.6	673.5	673.2	669.8	664.1	653.4	641.9	631.9
17.5°	619.9	622.3	628.4	632.5	637.7	648.7	654.1	656.2	654.6	648.0	641.0
20°	564.5	560.4	577.5	586.1	593.5	612.0	628.0	634.1	643.9	643.8	641.9
22.5°	485.9	486.9	503.0	513.4	535.0	553.6	571.7	594.7	613.7	626.2	633.6
25°	357.0	364.1	380.2	394.3	418.3	452.8	484.1	520.4	554.6	581.7	607.5
27.5°	268.2	268.7	281.4	294.5	308.8	337.0	376.4	419.7	468.6	508.9	555.2
30°	229.7	228.5	233.9	241.9	254.1	276.0	305.6	348.1	396.9	457.6	511.7
32.5°	202.4	202.4	206.5	212.4	222.5	237.3	257.6	292.2	338.2	397.9	461.3
35°	175.9	175.8	178.7	183.0	187.2	196.7	210.6	228.7	260.4	316.1	380.9
37.5°	156.9	157.8	159.2	161.9	166.6	171.9	180.2	192.4	214.9	247.9	302.4
40°	146.3	146.7	148.7	150.9	153.7	157.8	164.6	174.5	190.9	217.2	257.1
42.5°	136.6	136.9	138.4	140.4	142.6	146.7	152.4	160.9	174.2	194.7	227.6
45°	122.2	122.2	123.5	124.4	126.9	130.5	135.2	142.3	151.5	166.6	188.5
47.5°	108.8	108.8	109.7	111.3	112.8	115.7	120.3	126.0	132.7	144.5	163.1
50°	101.1	101.3	101.8	103.1	104.1	106.6	110.2	115.2	122.2	131.3	146.8
52.5°	94.9	94.8	95.5	96.0	96.7	98.5	101.2	105.6	111.9	119.8	132.6
55°	84.8	84.1	85.2	86.1	86.7	87.4	88.9	91.6	97.0	103.7	113.3
57.5°	72.2	71.9	72.7	73.5	75.3	77.3	78.6	80.3	83.1	87.9	97.4
60°	61.9	61.9	63.5	64.1	66.1	68.7	71.3	72.8	75.6	78.7	85.8
62.5°	52.7	52.8	53.6	54.1	55.3	58.5	62.1	65.4	68.0	71.0	75.7
65°	44.1	44.4	44.4	44.8	45.6	46.3	47.8	50.4	55.0	59.3	62.8
67.5°	37.4	37.5	37.7	38.0	38.2	39.0	39.6	40.8	41.8	45.8	50.2
70°	32.9	33.5	33.3	33.7	33.9	34.2	35.0	35.5	37.3	38.2	40.8
72.5°	28.8	29.2	29.2	29.4	29.9	30.0	30.6	31.1	32.2	32.9	34.4
75°	23.3	23.2	23.3	23.7	23.9	24.1	24.1	24.8	25.4	26.1	27.1
77.5°	18.0	18.2	18.2	18.2	18.3	18.6	18.5	18.8	19.4	19.8	20.2
80°	14.4	14.6	14.4	14.6	14.8	15.0	14.8	15.0	15.6	15.9	15.9
82.5°	11.2	11.3	11.3	11.3	11.4	11.4	11.7	11.7	12.1	12.1	12.2
85°	6.7	6.5	6.5	6.5	6.7	6.8	6.7	6.7	6.8	6.8	6.8
87.5°	7.7	7.8	7.7	7.7	7.6	7.4	7.2	7.1	6.8	6.7	6.1
90°	26.9	26.5	26.0	25.6	25.2	24.4	23.2	22.2	21.0	20.0	18.2
92.5°	26.9	26.7	26.4	26.1	25.8	25.4	24.9	24.3	23.7	23.2	22.3
95°	42.9	43.1	43.3	43.5	43.8	43.3	42.2	41.1	40.0	38.9	37.3
97.5°	57.2	57.0	56.7	56.4	56.2	55.6	54.7	53.8	52.9	52.1	48.5
100°	66.9	66.4	66.0	65.5	65.1	63.9	62.1	60.4	58.6	56.8	53.1
102.5°	71.6	71.0	70.4	69.7	69.1	67.7	65.4	63.0	60.7	58.5	89.9
105°	75.8	74.9	74.0	73.1	72.2	70.6	68.2	65.7	63.3	60.8	121.3
107.5°	78.0	77.1	76.2	75.3	74.4	75.3	77.7	80.2	82.7	85.2	157.8
110°	78.8	77.9	77.0	76.1	75.3	85.9	108.0	130.2	152.4	174.6	238.6



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	79.6	78.8	78.2	77.5	76.7	116.8	197.7	278.5	359.4	440.2	456.1
115°	81.8	97.8	113.7	129.6	145.6	204.9	307.5	410.1	512.7	615.4	609.8
117.5°	333.9	386.4	438.8	491.2	543.6	582.3	607.1	631.9	656.7	681.6	677.8
120°	608.4	638.3	668.2	698.1	728.1	741.7	739.0	736.4	733.7	731.0	727.1
122.5°	759.1	765.0	770.8	776.6	782.4	784.5	782.9	781.3	779.7	778.1	773.8
125°	852.7	852.1	851.4	850.7	850.0	849.0	847.4	845.9	844.3	842.8	838.5
127.5°	911.7	911.6	911.5	911.3	911.3	910.0	907.8	905.5	903.3	901.0	897.8
130°	948.4	948.7	948.9	949.1	949.3	948.2	945.8	943.4	940.9	938.5	936.0
132.5°	984.4	984.6	984.8	985.0	985.2	984.3	982.2	980.2	978.0	976.0	973.5
135°	1036.2	1036.7	1037.1	1037.5	1038.0	1037.1	1034.9	1032.7	1030.5	1028.3	1026.2
137.5°	1083.5	1084.3	1085.0	1085.7	1086.5	1085.8	1083.6	1081.4	1079.3	1077.1	1074.8
140°	1113.0	1114.1	1115.2	1116.3	1117.4	1117.0	1115.0	1113.0	1111.0	1109.1	1106.6
142.5°	1141.7	1142.8	1143.9	1145.1	1146.1	1145.8	1144.0	1142.2	1140.4	1138.6	1135.7
145°	1181.9	1182.9	1184.1	1185.1	1186.3	1186.0	1184.5	1182.9	1181.4	1179.8	1176.1
147.5°	1217.2	1218.1	1219.0	1219.9	1220.8	1220.7	1219.6	1218.5	1217.3	1216.1	1212.4
150°	1238.7	1239.7	1240.9	1242.0	1243.1	1243.0	1241.7	1240.3	1239.0	1237.7	1234.1
152.5°	1257.0	1258.5	1260.0	1261.4	1262.9	1263.0	1261.6	1260.3	1259.0	1257.6	1254.3
155°	1282.5	1284.3	1286.1	1287.8	1289.6	1289.9	1288.6	1287.2	1285.9	1284.6	1281.9
157.5°	1305.9	1307.7	1309.4	1311.1	1312.8	1313.0	1311.4	1309.9	1308.4	1306.9	1305.0
160°	1319.5	1321.0	1322.6	1324.1	1325.7	1325.8	1324.5	1323.1	1321.8	1320.5	1319.2
162.5°	1330.6	1332.5	1334.4	1336.4	1338.2	1338.5	1336.9	1335.5	1333.9	1332.4	1331.3
165°	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4	1346.7
167.5°	1358.0	1359.9	1362.0	1363.9	1366.0	1366.1	1364.6	1363.0	1361.5	1359.9	1359.3
170°	1364.3	1366.4	1368.3	1370.4	1372.3	1372.6	1371.0	1369.5	1367.9	1366.4	1365.9
172.5°	1369.1	1371.1	1373.1	1375.1	1377.1	1377.3	1375.7	1374.2	1372.6	1371.1	1370.7
175°	1373.3	1375.5	1377.8	1380.0	1382.2	1382.5	1381.0	1379.4	1377.9	1376.3	1375.9
177.5°	1375.9	1377.5	1379.1	1380.7	1382.3	1382.5	1381.2	1380.0	1378.8	1377.5	1377.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	545.8	544.5	543.5	540.9	539.5	536.5	536.1	536.0	532.1	528.4	527.3
5°	564.5	561.5	557.1	551.9	546.5	541.0	537.3	534.3	526.8	519.8	515.8
7.5°	583.3	577.0	569.3	559.5	551.3	542.2	535.3	529.2	518.7	508.6	501.8
10°	597.5	587.1	576.9	563.4	552.8	542.4	532.8	524.5	512.7	499.3	489.8
12.5°	606.2	594.8	580.7	567.5	553.8	540.6	527.7	517.1	503.1	489.3	478.2
15°	618.0	605.8	588.7	569.8	552.3	535.0	520.2	506.9	488.8	472.2	458.5
17.5°	627.7	610.8	592.6	570.7	550.3	528.5	509.4	492.4	472.1	452.2	436.1
20°	630.8	614.1	593.0	571.1	547.1	521.3	500.8	482.2	460.6	438.9	420.4
22.5°	628.8	615.9	592.4	566.2	541.6	514.7	491.5	469.9	445.9	423.8	402.4
25°	615.8	611.3	589.1	560.6	532.5	501.2	474.3	450.8	423.4	399.7	376.3
27.5°	585.3	594.9	581.1	550.7	519.4	485.9	455.7	428.9	400.5	373.8	350.6
30°	556.0	578.0	572.1	543.9	508.9	476.0	442.1	414.1	383.8	356.3	333.4
32.5°	515.8	552.2	558.0	534.4	498.2	462.0	426.5	398.7	367.0	338.1	315.7
35°	451.8	506.3	531.3	516.3	480.0	440.9	404.3	371.9	340.0	311.5	289.3
37.5°	375.6	449.8	491.5	492.5	459.2	418.6	378.6	346.4	313.8	285.8	261.8
40°	326.1	406.5	460.8	472.8	444.7	400.8	360.4	327.6	295.8	268.3	240.8
42.5°	281.7	361.7	428.4	449.4	427.1	383.4	342.9	308.7	277.7	251.8	223.6
45°	227.8	297.8	371.3	408.7	396.3	356.0	313.2	280.5	251.5	229.1	202.0
47.5°	192.2	241.5	312.7	363.2	363.1	326.2	284.1	252.9	225.9	204.9	183.0
50°	171.9	214.8	275.0	332.4	337.2	306.3	266.3	235.4	210.2	188.2	170.6
52.5°	153.6	189.1	243.1	298.2	311.9	285.1	246.3	217.8	193.3	173.0	158.0
55°	129.8	157.3	198.4	249.8	270.6	251.7	217.2	190.5	170.7	153.7	140.7
57.5°	109.8	130.4	163.4	204.8	228.9	217.1	188.7	167.0	150.0	134.6	124.4
60°	97.3	114.1	142.0	176.7	203.3	195.0	170.7	150.6	136.2	122.8	113.2
62.5°	85.4	99.9	123.8	152.0	176.3	172.9	153.1	136.2	123.5	111.4	103.2
65°	68.7	79.2	98.0	120.0	139.7	141.3	127.0	115.5	104.3	94.7	87.4
67.5°	54.7	61.6	74.8	93.4	108.0	113.3	104.6	95.8	86.8	79.4	73.1
70°	46.1	51.7	61.3	76.3	89.8	95.4	90.3	83.5	75.7	69.6	64.2
72.5°	37.3	42.8	49.9	60.9	72.5	78.5	76.7	71.8	65.6	60.4	55.4
75°	28.1	29.8	34.7	42.1	51.1	56.3	57.6	55.0	50.0	46.1	43.1
77.5°	20.8	21.9	24.1	28.0	33.9	38.6	40.4	40.1	36.7	34.5	31.6
80°	16.6	17.2	18.3	20.0	24.5	29.1	30.4	30.4	28.0	27.1	24.3
82.5°	12.6	13.0	13.8	14.7	16.7	20.8	22.3	22.5	21.0	19.8	17.6
85°	7.3	7.0	7.4	8.0	8.3	9.5	11.7	12.1	11.7	10.2	9.6
87.5°	5.8	5.6	5.2	4.6	4.3	4.0	4.2	4.5	4.4	4.4	4.6
90°	16.4	14.6	12.9	10.8	8.3	5.9	3.4	1.0	3.4	5.9	8.3
92.5°	21.4	20.5	19.6	19.2	19.5	19.7	19.9	20.1	19.9	19.7	19.5
95°	35.8	34.2	32.7	35.5	42.9	50.2	57.5	64.8	57.5	50.2	42.9
97.5°	44.8	41.3	37.7	46.2	66.9	87.4	108.0	128.7	108.0	87.4	66.9
100°	49.3	45.6	41.7	55.1	85.4	115.8	146.2	176.5	146.2	115.8	85.4
102.5°	121.5	153.0	184.5	203.5	209.9	216.3	222.7	229.2	222.7	216.3	209.9
105°	181.8	242.4	302.9	329.8	323.1	316.5	309.8	303.2	309.8	316.5	323.1
107.5°	230.3	302.9	375.4	409.0	403.7	398.3	392.9	387.6	392.9	398.3	403.7
110°	302.6	366.7	430.7	460.4	455.8	451.1	446.5	441.8	446.5	451.1	455.8





TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	55°	60°	65°	70°	75°	80°	85°	90°	95°	100°	105°
112.5°	471.9	487.7	503.5	509.4	505.2	501.1	497.0	492.8	497.0	501.1	505.2
115°	604.3	598.8	593.2	588.6	584.7	581.0	577.2	573.5	577.2	581.0	584.7
117.5°	673.9	670.1	666.3	662.3	658.1	653.9	649.7	645.5	649.7	653.9	658.1
120°	723.1	719.1	715.1	711.4	708.1	704.7	701.5	698.1	701.5	704.7	708.1
122.5°	769.4	765.1	760.8	756.8	753.3	749.8	746.3	742.8	746.3	749.8	753.3
125°	834.3	830.1	825.9	822.3	819.5	816.6	813.7	810.8	813.7	816.6	819.5
127.5°	894.7	891.5	888.4	885.3	882.1	878.8	875.6	872.5	875.6	878.8	882.1
130°	933.6	931.2	928.7	925.8	922.2	918.7	915.1	911.6	915.1	918.7	922.2
132.5°	971.1	968.7	966.2	963.5	960.5	957.5	954.5	951.5	954.5	957.5	960.5
135°	1024.3	1022.2	1020.3	1017.5	1013.9	1010.4	1006.8	1003.3	1006.8	1010.4	1013.9
137.5°	1072.6	1070.3	1068.0	1065.7	1063.2	1060.7	1058.3	1055.7	1058.3	1060.7	1063.2
140°	1104.2	1101.7	1099.3	1097.1	1095.4	1093.6	1091.8	1090.1	1091.8	1093.6	1095.4
142.5°	1132.9	1130.2	1127.4	1125.2	1123.6	1122.0	1120.4	1118.8	1120.4	1122.0	1123.6
145°	1172.3	1168.6	1164.7	1163.0	1163.2	1163.4	1163.7	1163.8	1163.7	1163.4	1163.2
147.5°	1208.7	1204.9	1201.3	1199.8	1200.6	1201.5	1202.3	1203.1	1202.3	1201.5	1200.6
150°	1230.6	1227.0	1223.5	1222.5	1224.0	1225.6	1227.2	1228.7	1227.2	1225.6	1224.0
152.5°	1250.9	1247.5	1244.1	1243.3	1245.0	1246.8	1248.5	1250.3	1248.5	1246.8	1245.0
155°	1279.2	1276.6	1273.9	1273.6	1275.5	1277.6	1279.5	1281.6	1279.5	1277.6	1275.5
157.5°	1303.2	1301.3	1299.4	1299.3	1301.1	1302.7	1304.4	1306.1	1304.4	1302.7	1301.1
160°	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1319.2	1317.8	1316.5
162.5°	1330.1	1328.9	1327.8	1327.9	1329.3	1330.6	1331.9	1333.3	1331.9	1330.6	1329.3
165°	1346.1	1345.4	1344.8	1345.1	1346.4	1347.7	1349.1	1350.4	1349.1	1347.7	1346.4
167.5°	1358.7	1358.1	1357.5	1357.8	1359.2	1360.5	1361.8	1363.2	1361.8	1360.5	1359.2
170°	1365.5	1365.0	1364.6	1365.0	1366.4	1367.7	1369.0	1370.4	1369.0	1367.7	1366.4
172.5°	1370.2	1369.8	1369.4	1369.8	1371.1	1372.5	1373.8	1375.1	1373.8	1372.5	1371.1
175°	1375.4	1375.0	1374.5	1375.1	1376.6	1378.2	1379.7	1381.3	1379.7	1378.2	1376.6
177.5°	1377.1	1377.0	1376.8	1377.3	1378.6	1379.8	1381.0	1382.3	1381.0	1379.8	1378.6
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	525.5	524.4	522.4	519.5	517.7	514.6	512.6	513.7	514.0	513.7	513.5
5°	511.4	507.4	502.1	496.8	492.0	486.9	483.9	482.7	480.0	478.6	477.8
7.5°	494.2	487.5	480.0	470.9	463.3	455.2	451.1	449.1	443.8	440.9	438.4
10°	481.5	470.9	463.3	451.5	444.3	433.7	426.5	426.7	419.5	415.4	412.5
12.5°	467.4	455.8	443.2	432.5	422.5	414.0	405.3	401.8	394.1	390.2	382.2
15°	444.1	430.6	417.3	402.8	392.6	379.4	366.9	351.5	339.1	328.3	325.4
17.5°	418.7	401.9	388.5	371.5	354.1	332.0	317.4	308.4	301.0	295.3	291.1
20°	401.1	384.1	369.8	344.3	320.7	305.7	295.1	288.1	280.4	274.3	270.9
22.5°	382.8	365.0	345.5	317.0	298.6	286.7	277.1	269.2	263.9	259.2	256.1
25°	356.7	337.2	305.2	285.6	270.8	258.1	251.5	246.7	241.2	234.6	231.7
27.5°	329.1	298.2	275.2	260.6	246.5	238.3	232.3	225.1	220.1	217.2	214.1
30°	308.5	277.6	259.7	243.7	233.7	224.6	217.6	213.5	208.7	203.7	201.7
32.5°	285.6	260.9	243.6	230.4	220.2	212.5	206.9	200.3	196.9	193.8	189.6
35°	257.1	238.3	222.6	211.9	202.2	195.9	189.5	185.6	179.3	176.7	175.0
37.5°	232.9	216.7	205.0	193.6	186.0	179.0	175.0	168.8	166.2	162.5	159.0
40°	219.2	203.3	192.1	182.8	174.2	169.1	164.1	159.1	155.0	153.4	149.1
42.5°	205.4	192.4	181.1	171.0	165.3	159.7	153.4	149.8	145.5	142.8	140.2
45°	186.1	174.6	165.0	156.7	150.3	144.6	140.6	134.4	132.1	126.7	124.4
47.5°	169.3	158.6	149.4	141.5	135.3	131.6	125.6	120.8	117.0	113.7	110.8
50°	157.3	148.3	139.4	132.4	126.9	121.5	115.4	113.0	107.0	105.3	103.7
52.5°	146.3	137.8	129.7	122.8	117.2	112.0	106.6	103.5	99.5	97.8	96.6
55°	130.9	122.8	115.0	108.9	103.4	98.0	94.7	90.7	88.9	87.6	86.1
57.5°	115.5	108.2	102.2	96.0	90.4	86.2	82.3	80.0	78.1	76.4	74.6
60°	105.7	98.7	93.4	87.6	81.9	78.4	75.4	72.6	70.4	67.8	67.0
62.5°	95.4	89.2	84.3	78.7	73.7	70.5	67.7	65.1	62.4	58.6	57.6
65°	81.1	76.3	71.1	66.4	62.0	58.9	54.8	51.9	50.7	50.4	50.2
67.5°	68.2	63.7	59.2	54.5	50.5	47.5	45.4	45.0	44.2	44.0	43.5
70°	59.6	55.4	51.0	46.5	42.6	42.1	41.3	40.5	39.6	39.3	38.9
72.5°	51.9	47.5	43.0	39.5	37.8	37.2	36.4	35.6	35.1	34.7	34.5
75°	39.8	35.7	32.8	31.5	30.6	30.0	28.9	28.4	28.0	27.4	27.2
77.5°	28.7	26.3	25.0	24.2	23.2	22.7	22.0	21.4	21.0	21.0	20.6
80°	21.9	20.7	19.8	18.7	18.3	17.6	17.4	16.9	17.0	16.5	16.5
82.5°	17.0	15.6	14.8	14.3	13.9	13.3	13.1	12.9	12.9	12.5	12.5
85°	8.7	8.3	8.0	7.6	7.6	7.0	7.3	7.0	7.0	6.7	6.5
87.5°	5.0	5.2	5.3	5.6	6.0	6.2	6.4	6.5	6.8	6.9	6.9
90°	10.8	12.9	14.6	16.4	18.2	20.0	21.0	22.2	23.2	24.4	25.2
92.5°	19.2	19.6	20.5	21.4	22.3	23.2	23.7	24.3	24.9	25.4	25.8
95°	35.5	32.7	34.2	35.8	37.3	38.9	40.0	41.1	42.2	43.3	43.8
97.5°	46.2	37.7	41.3	44.8	48.5	52.1	52.9	53.8	54.7	55.6	56.2
100°	55.1	41.7	45.6	49.3	53.1	56.8	58.6	60.4	62.1	63.9	65.1
102.5°	203.5	184.5	153.0	121.5	89.9	58.5	60.7	63.0	65.4	67.7	69.1
105°	329.8	302.9	242.4	181.8	121.3	60.8	63.3	65.7	68.2	70.6	72.2
107.5°	409.0	375.4	302.9	230.3	157.8	85.2	82.7	80.2	77.7	75.3	74.4
110°	460.4	430.7	366.7	302.6	238.6	174.6	152.4	130.2	108.0	85.9	75.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	110°	115°	120°	125°	130°	135°	140°	145°	150°	155°	160°
112.5°	509.4	503.5	487.7	471.9	456.1	440.2	359.4	278.5	197.7	116.8	76.7
115°	588.6	593.2	598.8	604.3	609.8	615.4	512.7	410.1	307.5	204.9	145.6
117.5°	662.3	666.3	670.1	673.9	677.8	681.6	656.7	631.9	607.1	582.3	543.6
120°	711.4	715.1	719.1	723.1	727.1	731.0	733.7	736.4	739.0	741.7	728.1
122.5°	756.8	760.8	765.1	769.4	773.8	778.1	779.7	781.3	782.9	784.5	782.4
125°	822.3	825.9	830.1	834.3	838.5	842.8	844.3	845.9	847.4	849.0	850.0
127.5°	885.3	888.4	891.5	894.7	897.8	901.0	903.3	905.5	907.8	910.0	911.3
130°	925.8	928.7	931.2	933.6	936.0	938.5	940.9	943.4	945.8	948.2	949.3
132.5°	963.5	966.2	968.7	971.1	973.5	976.0	978.0	980.2	982.2	984.3	985.2
135°	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5	1032.7	1034.9	1037.1	1038.0
137.5°	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3	1081.4	1083.6	1085.8	1086.5
140°	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0	1113.0	1115.0	1117.0	1117.4
142.5°	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4	1142.2	1144.0	1145.8	1146.1
145°	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4	1182.9	1184.5	1186.0	1186.3
147.5°	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3	1218.5	1219.6	1220.7	1220.8
150°	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0	1240.3	1241.7	1243.0	1243.1
152.5°	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0	1260.3	1261.6	1263.0	1262.9
155°	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9	1287.2	1288.6	1289.9	1289.6
157.5°	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4	1309.9	1311.4	1313.0	1312.8
160°	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8	1323.1	1324.5	1325.8	1325.7
162.5°	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9	1335.5	1336.9	1338.5	1338.2
165°	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6
167.5°	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5	1363.0	1364.6	1366.1	1366.0
170°	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9	1369.5	1371.0	1372.6	1372.3
172.5°	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6	1374.2	1375.7	1377.3	1377.1
175°	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9	1379.4	1381.0	1382.5	1382.2
177.5°	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8	1380.0	1381.2	1382.5	1382.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	511.8	512.1	511.7	511.9	511.7	512.1	511.8	513.5	513.7	514.0	513.7
5°	476.9	474.7	474.3	473.8	474.3	474.7	476.9	477.8	478.6	480.0	482.7
7.5°	435.2	434.9	433.9	432.6	433.9	434.9	435.2	438.4	440.9	443.8	449.1
10°	408.4	407.4	407.2	405.9	407.2	407.4	408.4	412.5	415.4	419.5	426.7
12.5°	376.9	371.0	370.4	367.1	370.4	371.0	376.9	382.2	390.2	394.1	401.8
15°	321.0	319.8	316.1	313.7	316.1	319.8	321.0	325.4	328.3	339.1	351.5
17.5°	288.9	285.3	284.1	283.6	284.1	285.3	288.9	291.1	295.3	301.0	308.4
20°	268.3	265.1	264.5	264.1	264.5	265.1	268.3	270.9	274.3	280.4	288.1
22.5°	254.1	250.6	249.2	248.1	249.2	250.6	254.1	256.1	259.2	263.9	269.2
25°	229.8	228.5	227.8	227.4	227.8	228.5	229.8	231.7	234.6	241.2	246.7
27.5°	210.8	208.0	207.4	206.4	207.4	208.0	210.8	214.1	217.2	220.1	225.1
30°	200.0	199.1	197.8	196.7	197.8	199.1	200.0	201.7	203.7	208.7	213.5
32.5°	187.3	186.5	185.3	184.8	185.3	186.5	187.3	189.6	193.8	196.9	200.3
35°	173.2	170.6	169.4	167.8	169.4	170.6	173.2	175.0	176.7	179.3	185.6
37.5°	158.2	156.9	155.3	155.9	155.3	156.9	158.2	159.0	162.5	166.2	168.8
40°	146.7	145.8	145.4	145.2	145.4	145.8	146.7	149.1	153.4	155.0	159.1
42.5°	137.5	134.9	134.0	134.0	134.0	134.9	137.5	140.2	142.8	145.5	149.8
45°	123.5	121.2	119.4	119.6	119.4	121.2	123.5	124.4	126.7	132.1	134.4
47.5°	109.3	109.2	108.1	108.4	108.1	109.2	109.3	110.8	113.7	117.0	120.8
50°	102.4	101.3	100.5	100.8	100.5	101.3	102.4	103.7	105.3	107.0	113.0
52.5°	95.9	94.9	94.3	95.1	94.3	94.9	95.9	96.6	97.8	99.5	103.5
55°	85.2	84.1	83.9	83.7	83.9	84.1	85.2	86.1	87.6	88.9	90.7
57.5°	73.2	72.5	71.3	70.9	71.3	72.5	73.2	74.6	76.4	78.1	80.0
60°	64.7	63.2	61.3	61.1	61.3	63.2	64.7	67.0	67.8	70.4	72.6
62.5°	56.7	56.5	56.1	56.1	56.1	56.5	56.7	57.6	58.6	62.4	65.1
65°	49.8	49.7	49.8	50.0	49.8	49.7	49.8	50.2	50.4	50.7	51.9
67.5°	43.4	43.0	42.7	42.9	42.7	43.0	43.4	43.5	44.0	44.2	45.0
70°	38.5	38.3	38.2	38.2	38.2	38.3	38.5	38.9	39.3	39.6	40.5
72.5°	33.8	33.8	33.6	33.4	33.6	33.8	33.8	34.5	34.7	35.1	35.6
75°	27.1	26.7	26.7	26.7	26.7	26.7	27.1	27.2	27.4	28.0	28.4
77.5°	20.6	20.4	20.2	20.1	20.2	20.4	20.6	20.6	21.0	21.0	21.4
80°	16.3	16.1	15.9	15.9	15.9	16.1	16.3	16.5	16.5	17.0	16.9
82.5°	12.5	12.2	12.2	12.1	12.2	12.2	12.5	12.5	12.5	12.9	12.9
85°	6.7	6.8	6.7	7.0	6.7	6.8	6.7	6.5	6.7	7.0	7.0
87.5°	7.0	7.0	7.3	7.2	7.3	7.0	7.0	6.9	6.9	6.8	6.5
90°	25.6	26.0	26.5	26.9	26.5	26.0	25.6	25.2	24.4	23.2	22.2
92.5°	26.1	26.4	26.7	26.9	26.7	26.4	26.1	25.8	25.4	24.9	24.3
95°	43.5	43.3	43.1	42.9	43.1	43.3	43.5	43.8	43.3	42.2	41.1
97.5°	56.4	56.7	57.0	57.2	57.0	56.7	56.4	56.2	55.6	54.7	53.8
100°	65.5	66.0	66.4	66.9	66.4	66.0	65.5	65.1	63.9	62.1	60.4
102.5°	69.7	70.4	71.0	71.6	71.0	70.4	69.7	69.1	67.7	65.4	63.0
105°	73.1	74.0	74.9	75.8	74.9	74.0	73.1	72.2	70.6	68.2	65.7
107.5°	75.3	76.2	77.1	78.0	77.1	76.2	75.3	74.4	75.3	77.7	80.2
110°	76.1	77.0	77.9	78.8	77.9	77.0	76.1	75.3	85.9	108.0	130.2



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	165°	170°	175°	180°	185°	190°	195°	200°	205°	210°	215°
112.5°	77.5	78.2	78.8	79.6	78.8	78.2	77.5	76.7	116.8	197.7	278.5
115°	129.6	113.7	97.8	81.8	97.8	113.7	129.6	145.6	204.9	307.5	410.1
117.5°	491.2	438.8	386.4	333.9	386.4	438.8	491.2	543.6	582.3	607.1	631.9
120°	698.1	668.2	638.3	608.4	638.3	668.2	698.1	728.1	741.7	739.0	736.4
122.5°	776.6	770.8	765.0	759.1	765.0	770.8	776.6	782.4	784.5	782.9	781.3
125°	850.7	851.4	852.1	852.7	852.1	851.4	850.7	850.0	849.0	847.4	845.9
127.5°	911.3	911.5	911.6	911.7	911.6	911.5	911.3	911.3	910.0	907.8	905.5
130°	949.1	948.9	948.7	948.4	948.7	948.9	949.1	949.3	948.2	945.8	943.4
132.5°	985.0	984.8	984.6	984.4	984.6	984.8	985.0	985.2	984.3	982.2	980.2
135°	1037.5	1037.1	1036.7	1036.2	1036.7	1037.1	1037.5	1038.0	1037.1	1034.9	1032.7
137.5°	1085.7	1085.0	1084.3	1083.5	1084.3	1085.0	1085.7	1086.5	1085.8	1083.6	1081.4
140°	1116.3	1115.2	1114.1	1113.0	1114.1	1115.2	1116.3	1117.4	1117.0	1115.0	1113.0
142.5°	1145.1	1143.9	1142.8	1141.7	1142.8	1143.9	1145.1	1146.1	1145.8	1144.0	1142.2
145°	1185.1	1184.1	1182.9	1181.9	1182.9	1184.1	1185.1	1186.3	1186.0	1184.5	1182.9
147.5°	1219.9	1219.0	1218.1	1217.2	1218.1	1219.0	1219.9	1220.8	1220.7	1219.6	1218.5
150°	1242.0	1240.9	1239.7	1238.7	1239.7	1240.9	1242.0	1243.1	1243.0	1241.7	1240.3
152.5°	1261.4	1260.0	1258.5	1257.0	1258.5	1260.0	1261.4	1262.9	1263.0	1261.6	1260.3
155°	1287.8	1286.1	1284.3	1282.5	1284.3	1286.1	1287.8	1289.6	1289.9	1288.6	1287.2
157.5°	1311.1	1309.4	1307.7	1305.9	1307.7	1309.4	1311.1	1312.8	1313.0	1311.4	1309.9
160°	1324.1	1322.6	1321.0	1319.5	1321.0	1322.6	1324.1	1325.7	1325.8	1324.5	1323.1
162.5°	1336.4	1334.4	1332.5	1330.6	1332.5	1334.4	1336.4	1338.2	1338.5	1336.9	1335.5
165°	1352.0	1350.5	1348.9	1347.4	1348.9	1350.5	1352.0	1353.6	1353.6	1352.0	1350.5
167.5°	1363.9	1362.0	1359.9	1358.0	1359.9	1362.0	1363.9	1366.0	1366.1	1364.6	1363.0
170°	1370.4	1368.3	1366.4	1364.3	1366.4	1368.3	1370.4	1372.3	1372.6	1371.0	1369.5
172.5°	1375.1	1373.1	1371.1	1369.1	1371.1	1373.1	1375.1	1377.1	1377.3	1375.7	1374.2
175°	1380.0	1377.8	1375.5	1373.3	1375.5	1377.8	1380.0	1382.2	1382.5	1381.0	1379.4
177.5°	1380.7	1379.1	1377.5	1375.9	1377.5	1379.1	1380.7	1382.3	1382.5	1381.2	1380.0
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	512.6	514.6	517.7	519.5	522.4	524.4	525.5	527.3	528.4	532.1	536.0
5°	483.9	486.9	492.0	496.8	502.1	507.4	511.4	515.8	519.8	526.8	534.3
7.5°	451.1	455.2	463.3	470.9	480.0	487.5	494.2	501.8	508.6	518.7	529.2
10°	426.5	433.7	444.3	451.5	463.3	470.9	481.5	489.8	499.3	512.7	524.5
12.5°	405.3	414.0	422.5	432.5	443.2	455.8	467.4	478.2	489.3	503.1	517.1
15°	366.9	379.4	392.6	402.8	417.3	430.6	444.1	458.5	472.2	488.8	506.9
17.5°	317.4	332.0	354.1	371.5	388.5	401.9	418.7	436.1	452.2	472.1	492.4
20°	295.1	305.7	320.7	344.3	369.8	384.1	401.1	420.4	438.9	460.6	482.2
22.5°	277.1	286.7	298.6	317.0	345.5	365.0	382.8	402.4	423.8	445.9	469.9
25°	251.5	258.1	270.8	285.6	305.2	337.2	356.7	376.3	399.7	423.4	450.8
27.5°	232.3	238.3	246.5	260.6	275.2	298.2	329.1	350.6	373.8	400.5	428.9
30°	217.6	224.6	233.7	243.7	259.7	277.6	308.5	333.4	356.3	383.8	414.1
32.5°	206.9	212.5	220.2	230.4	243.6	260.9	285.6	315.7	338.1	367.0	398.7
35°	189.5	195.9	202.2	211.9	222.6	238.3	257.1	289.3	311.5	340.0	371.9
37.5°	175.0	179.0	186.0	193.6	205.0	216.7	232.9	261.8	285.8	313.8	346.4
40°	164.1	169.1	174.2	182.8	192.1	203.3	219.2	240.8	268.3	295.8	327.6
42.5°	153.4	159.7	165.3	171.0	181.1	192.4	205.4	223.6	251.8	277.7	308.7
45°	140.6	144.6	150.3	156.7	165.0	174.6	186.1	202.0	229.1	251.5	280.5
47.5°	125.6	131.6	135.3	141.5	149.4	158.6	169.3	183.0	204.9	225.9	252.9
50°	115.4	121.5	126.9	132.4	139.4	148.3	157.3	170.6	188.2	210.2	235.4
52.5°	106.6	112.0	117.2	122.8	129.7	137.8	146.3	158.0	173.0	193.3	217.8
55°	94.7	98.0	103.4	108.9	115.0	122.8	130.9	140.7	153.7	170.7	190.5
57.5°	82.3	86.2	90.4	96.0	102.2	108.2	115.5	124.4	134.6	150.0	167.0
60°	75.4	78.4	81.9	87.6	93.4	98.7	105.7	113.2	122.8	136.2	150.6
62.5°	67.7	70.5	73.7	78.7	84.3	89.2	95.4	103.2	111.4	123.5	136.2
65°	54.8	58.9	62.0	66.4	71.1	76.3	81.1	87.4	94.7	104.3	115.5
67.5°	45.4	47.5	50.5	54.5	59.2	63.7	68.2	73.1	79.4	86.8	95.8
70°	41.3	42.1	42.6	46.5	51.0	55.4	59.6	64.2	69.6	75.7	83.5
72.5°	36.4	37.2	37.8	39.5	43.0	47.5	51.9	55.4	60.4	65.6	71.8
75°	28.9	30.0	30.6	31.5	32.8	35.7	39.8	43.1	46.1	50.0	55.0
77.5°	22.0	22.7	23.2	24.2	25.0	26.3	28.7	31.6	34.5	36.7	40.1
80°	17.4	17.6	18.3	18.7	19.8	20.7	21.9	24.3	27.1	28.0	30.4
82.5°	13.1	13.3	13.9	14.3	14.8	15.6	17.0	17.6	19.8	21.0	22.5
85°	7.3	7.0	7.6	7.6	8.0	8.3	8.7	9.6	10.2	11.7	12.1
87.5°	6.4	6.2	6.0	5.6	5.3	5.2	5.0	4.6	4.4	4.4	4.5
90°	21.0	20.0	18.2	16.4	14.6	12.9	10.8	8.3	5.9	3.4	1.0
92.5°	23.7	23.2	22.3	21.4	20.5	19.6	19.2	19.5	19.7	19.9	20.1
95°	40.0	38.9	37.3	35.8	34.2	32.7	35.5	42.9	50.2	57.5	64.8
97.5°	52.9	52.1	48.5	44.8	41.3	37.7	46.2	66.9	87.4	108.0	128.7
100°	58.6	56.8	53.1	49.3	45.6	41.7	55.1	85.4	115.8	146.2	176.5
102.5°	60.7	58.5	89.9	121.5	153.0	184.5	203.5	209.9	216.3	222.7	229.2
105°	63.3	60.8	121.3	181.8	242.4	302.9	329.8	323.1	316.5	309.8	303.2
107.5°	82.7	85.2	157.8	230.3	302.9	375.4	409.0	403.7	398.3	392.9	387.6
110°	152.4	174.6	238.6	302.6	366.7	430.7	460.4	455.8	451.1	446.5	441.8



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	220°	225°	230°	235°	240°	245°	250°	255°	260°	265°	270°
112.5°	359.4	440.2	456.1	471.9	487.7	503.5	509.4	505.2	501.1	497.0	492.8
115°	512.7	615.4	609.8	604.3	598.8	593.2	588.6	584.7	581.0	577.2	573.5
117.5°	656.7	681.6	677.8	673.9	670.1	666.3	662.3	658.1	653.9	649.7	645.5
120°	733.7	731.0	727.1	723.1	719.1	715.1	711.4	708.1	704.7	701.5	698.1
122.5°	779.7	778.1	773.8	769.4	765.1	760.8	756.8	753.3	749.8	746.3	742.8
125°	844.3	842.8	838.5	834.3	830.1	825.9	822.3	819.5	816.6	813.7	810.8
127.5°	903.3	901.0	897.8	894.7	891.5	888.4	885.3	882.1	878.8	875.6	872.5
130°	940.9	938.5	936.0	933.6	931.2	928.7	925.8	922.2	918.7	915.1	911.6
132.5°	978.0	976.0	973.5	971.1	968.7	966.2	963.5	960.5	957.5	954.5	951.5
135°	1030.5	1028.3	1026.2	1024.3	1022.2	1020.3	1017.5	1013.9	1010.4	1006.8	1003.3
137.5°	1079.3	1077.1	1074.8	1072.6	1070.3	1068.0	1065.7	1063.2	1060.7	1058.3	1055.7
140°	1111.0	1109.1	1106.6	1104.2	1101.7	1099.3	1097.1	1095.4	1093.6	1091.8	1090.1
142.5°	1140.4	1138.6	1135.7	1132.9	1130.2	1127.4	1125.2	1123.6	1122.0	1120.4	1118.8
145°	1181.4	1179.8	1176.1	1172.3	1168.6	1164.7	1163.0	1163.2	1163.4	1163.7	1163.8
147.5°	1217.3	1216.1	1212.4	1208.7	1204.9	1201.3	1199.8	1200.6	1201.5	1202.3	1203.1
150°	1239.0	1237.7	1234.1	1230.6	1227.0	1223.5	1222.5	1224.0	1225.6	1227.2	1228.7
152.5°	1259.0	1257.6	1254.3	1250.9	1247.5	1244.1	1243.3	1245.0	1246.8	1248.5	1250.3
155°	1285.9	1284.6	1281.9	1279.2	1276.6	1273.9	1273.6	1275.5	1277.6	1279.5	1281.6
157.5°	1308.4	1306.9	1305.0	1303.2	1301.3	1299.4	1299.3	1301.1	1302.7	1304.4	1306.1
160°	1321.8	1320.5	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5
162.5°	1333.9	1332.4	1331.3	1330.1	1328.9	1327.8	1327.9	1329.3	1330.6	1331.9	1333.3
165°	1348.9	1347.4	1346.7	1346.1	1345.4	1344.8	1345.1	1346.4	1347.7	1349.1	1350.4
167.5°	1361.5	1359.9	1359.3	1358.7	1358.1	1357.5	1357.8	1359.2	1360.5	1361.8	1363.2
170°	1367.9	1366.4	1365.9	1365.5	1365.0	1364.6	1365.0	1366.4	1367.7	1369.0	1370.4
172.5°	1372.6	1371.1	1370.7	1370.2	1369.8	1369.4	1369.8	1371.1	1372.5	1373.8	1375.1
175°	1377.9	1376.3	1375.9	1375.4	1375.0	1374.5	1375.1	1376.6	1378.2	1379.7	1381.3
177.5°	1378.8	1377.5	1377.3	1377.1	1377.0	1376.8	1377.3	1378.6	1379.8	1381.0	1382.3
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	536.1	536.5	539.5	540.9	543.5	544.5	545.8	545.4	545.4	546.0	550.2
5°	537.3	541.0	546.5	551.9	557.1	561.5	564.5	567.4	568.6	573.9	578.7
7.5°	535.3	542.2	551.3	559.5	569.3	577.0	583.3	589.1	593.0	600.9	608.9
10°	532.8	542.4	552.8	563.4	576.9	587.1	597.5	605.4	608.0	619.6	626.3
12.5°	527.7	540.6	553.8	567.5	580.7	594.8	606.2	614.2	623.3	633.7	646.0
15°	520.2	535.0	552.3	569.8	588.7	605.8	618.0	631.9	641.9	653.4	664.1
17.5°	509.4	528.5	550.3	570.7	592.6	610.8	627.7	641.0	648.0	654.6	656.2
20°	500.8	521.3	547.1	571.1	593.0	614.1	630.8	641.9	643.8	643.9	634.1
22.5°	491.5	514.7	541.6	566.2	592.4	615.9	628.8	633.6	626.2	613.7	594.7
25°	474.3	501.2	532.5	560.6	589.1	611.3	615.8	607.5	581.7	554.6	520.4
27.5°	455.7	485.9	519.4	550.7	581.1	594.9	585.3	555.2	508.9	468.6	419.7
30°	442.1	476.0	508.9	543.9	572.1	578.0	556.0	511.7	457.6	396.9	348.1
32.5°	426.5	462.0	498.2	534.4	558.0	552.2	515.8	461.3	397.9	338.2	292.2
35°	404.3	440.9	480.0	516.3	531.3	506.3	451.8	380.9	316.1	260.4	228.7
37.5°	378.6	418.6	459.2	492.5	491.5	449.8	375.6	302.4	247.9	214.9	192.4
40°	360.4	400.8	444.7	472.8	460.8	406.5	326.1	257.1	217.2	190.9	174.5
42.5°	342.9	383.4	427.1	449.4	428.4	361.7	281.7	227.6	194.7	174.2	160.9
45°	313.2	356.0	396.3	408.7	371.3	297.8	227.8	188.5	166.6	151.5	142.3
47.5°	284.1	326.2	363.1	363.2	312.7	241.5	192.2	163.1	144.5	132.7	126.0
50°	266.3	306.3	337.2	332.4	275.0	214.8	171.9	146.8	131.3	122.2	115.2
52.5°	246.3	285.1	311.9	298.2	243.1	189.1	153.6	132.6	119.8	111.9	105.6
55°	217.2	251.7	270.6	249.8	198.4	157.3	129.8	113.3	103.7	97.0	91.6
57.5°	188.7	217.1	228.9	204.8	163.4	130.4	109.8	97.4	87.9	83.1	80.3
60°	170.7	195.0	203.3	176.7	142.0	114.1	97.3	85.8	78.7	75.6	72.8
62.5°	153.1	172.9	176.3	152.0	123.8	99.9	85.4	75.7	71.0	68.0	65.4
65°	127.0	141.3	139.7	120.0	98.0	79.2	68.7	62.8	59.3	55.0	50.4
67.5°	104.6	113.3	108.0	93.4	74.8	61.6	54.7	50.2	45.8	41.8	40.8
70°	90.3	95.4	89.8	76.3	61.3	51.7	46.1	40.8	38.2	37.3	35.5
72.5°	76.7	78.5	72.5	60.9	49.9	42.8	37.3	34.4	32.9	32.2	31.1
75°	57.6	56.3	51.1	42.1	34.7	29.8	28.1	27.1	26.1	25.4	24.8
77.5°	40.4	38.6	33.9	28.0	24.1	21.9	20.8	20.2	19.8	19.4	18.8
80°	30.4	29.1	24.5	20.0	18.3	17.2	16.6	15.9	15.9	15.6	15.0
82.5°	22.3	20.8	16.7	14.7	13.8	13.0	12.6	12.2	12.1	12.1	11.7
85°	11.7	9.5	8.3	8.0	7.4	7.0	7.3	6.8	6.8	6.8	6.7
87.5°	4.2	4.0	4.3	4.6	5.2	5.6	5.8	6.1	6.7	6.8	7.1
90°	3.4	5.9	8.3	10.8	12.9	14.6	16.4	18.2	20.0	21.0	22.2
92.5°	19.9	19.7	19.5	19.2	19.6	20.5	21.4	22.3	23.2	23.7	24.3
95°	57.5	50.2	42.9	35.5	32.7	34.2	35.8	37.3	38.9	40.0	41.1
97.5°	108.0	87.4	66.9	46.2	37.7	41.3	44.8	48.5	52.1	52.9	53.8
100°	146.2	115.8	85.4	55.1	41.7	45.6	49.3	53.1	56.8	58.6	60.4
102.5°	222.7	216.3	209.9	203.5	184.5	153.0	121.5	89.9	58.5	60.7	63.0
105°	309.8	316.5	323.1	329.8	302.9	242.4	181.8	121.3	60.8	63.3	65.7
107.5°	392.9	398.3	403.7	409.0	375.4	302.9	230.3	157.8	85.2	82.7	80.2
110°	446.5	451.1	455.8	460.4	430.7	366.7	302.6	238.6	174.6	152.4	130.2





TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	275°	280°	285°	290°	295°	300°	305°	310°	315°	320°	325°
112.5°	497.0	501.1	505.2	509.4	503.5	487.7	471.9	456.1	440.2	359.4	278.5
115°	577.2	581.0	584.7	588.6	593.2	598.8	604.3	609.8	615.4	512.7	410.1
117.5°	649.7	653.9	658.1	662.3	666.3	670.1	673.9	677.8	681.6	656.7	631.9
120°	701.5	704.7	708.1	711.4	715.1	719.1	723.1	727.1	731.0	733.7	736.4
122.5°	746.3	749.8	753.3	756.8	760.8	765.1	769.4	773.8	778.1	779.7	781.3
125°	813.7	816.6	819.5	822.3	825.9	830.1	834.3	838.5	842.8	844.3	845.9
127.5°	875.6	878.8	882.1	885.3	888.4	891.5	894.7	897.8	901.0	903.3	905.5
130°	915.1	918.7	922.2	925.8	928.7	931.2	933.6	936.0	938.5	940.9	943.4
132.5°	954.5	957.5	960.5	963.5	966.2	968.7	971.1	973.5	976.0	978.0	980.2
135°	1006.8	1010.4	1013.9	1017.5	1020.3	1022.2	1024.3	1026.2	1028.3	1030.5	1032.7
137.5°	1058.3	1060.7	1063.2	1065.7	1068.0	1070.3	1072.6	1074.8	1077.1	1079.3	1081.4
140°	1091.8	1093.6	1095.4	1097.1	1099.3	1101.7	1104.2	1106.6	1109.1	1111.0	1113.0
142.5°	1120.4	1122.0	1123.6	1125.2	1127.4	1130.2	1132.9	1135.7	1138.6	1140.4	1142.2
145°	1163.7	1163.4	1163.2	1163.0	1164.7	1168.6	1172.3	1176.1	1179.8	1181.4	1182.9
147.5°	1202.3	1201.5	1200.6	1199.8	1201.3	1204.9	1208.7	1212.4	1216.1	1217.3	1218.5
150°	1227.2	1225.6	1224.0	1222.5	1223.5	1227.0	1230.6	1234.1	1237.7	1239.0	1240.3
152.5°	1248.5	1246.8	1245.0	1243.3	1244.1	1247.5	1250.9	1254.3	1257.6	1259.0	1260.3
155°	1279.5	1277.6	1275.5	1273.6	1273.9	1276.6	1279.2	1281.9	1284.6	1285.9	1287.2
157.5°	1304.4	1302.7	1301.1	1299.3	1299.4	1301.3	1303.2	1305.0	1306.9	1308.4	1309.9
160°	1319.2	1317.8	1316.5	1315.2	1315.2	1316.5	1317.8	1319.2	1320.5	1321.8	1323.1
162.5°	1331.9	1330.6	1329.3	1327.9	1327.8	1328.9	1330.1	1331.3	1332.4	1333.9	1335.5
165°	1349.1	1347.7	1346.4	1345.1	1344.8	1345.4	1346.1	1346.7	1347.4	1348.9	1350.5
167.5°	1361.8	1360.5	1359.2	1357.8	1357.5	1358.1	1358.7	1359.3	1359.9	1361.5	1363.0
170°	1369.0	1367.7	1366.4	1365.0	1364.6	1365.0	1365.5	1365.9	1366.4	1367.9	1369.5
172.5°	1373.8	1372.5	1371.1	1369.8	1369.4	1369.8	1370.2	1370.7	1371.1	1372.6	1374.2
175°	1379.7	1378.2	1376.6	1375.1	1374.5	1375.0	1375.4	1375.9	1376.3	1377.9	1379.4
177.5°	1381.0	1379.8	1378.6	1377.3	1376.8	1377.0	1377.1	1377.3	1377.5	1378.8	1380.0
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
0°	533.0	533.0	533.0	533.0	533.0	533.0	533.0
2.5°	551.6	553.6	554.5	554.5	555.5	555.1	554.6
5°	583.3	586.9	587.7	590.9	593.4	592.6	593.0
7.5°	614.9	620.5	626.1	628.7	629.1	630.6	631.1
10°	634.3	639.0	647.6	646.4	652.8	656.6	650.4
12.5°	653.0	659.3	665.3	666.9	670.6	671.8	669.4
15°	669.8	673.2	673.5	672.6	673.8	672.8	669.3
17.5°	654.1	648.7	637.7	632.5	628.4	622.3	619.9
20°	628.0	612.0	593.5	586.1	577.5	560.4	564.5
22.5°	571.7	553.6	535.0	513.4	503.0	486.9	485.9
25°	484.1	452.8	418.3	394.3	380.2	364.1	357.0
27.5°	376.4	337.0	308.8	294.5	281.4	268.7	268.2
30°	305.6	276.0	254.1	241.9	233.9	228.5	229.7
32.5°	257.6	237.3	222.5	212.4	206.5	202.4	202.4
35°	210.6	196.7	187.2	183.0	178.7	175.8	175.9
37.5°	180.2	171.9	166.6	161.9	159.2	157.8	156.9
40°	164.6	157.8	153.7	150.9	148.7	146.7	146.3
42.5°	152.4	146.7	142.6	140.4	138.4	136.9	136.6
45°	135.2	130.5	126.9	124.4	123.5	122.2	122.2
47.5°	120.3	115.7	112.8	111.3	109.7	108.8	108.8
50°	110.2	106.6	104.1	103.1	101.8	101.3	101.1
52.5°	101.2	98.5	96.7	96.0	95.5	94.8	94.9
55°	88.9	87.4	86.7	86.1	85.2	84.1	84.8
57.5°	78.6	77.3	75.3	73.5	72.7	71.9	72.2
60°	71.3	68.7	66.1	64.1	63.5	61.9	61.9
62.5°	62.1	58.5	55.3	54.1	53.6	52.8	52.7
65°	47.8	46.3	45.6	44.8	44.4	44.4	44.1
67.5°	39.6	39.0	38.2	38.0	37.7	37.5	37.4
70°	35.0	34.2	33.9	33.7	33.3	33.5	32.9
72.5°	30.6	30.0	29.9	29.4	29.2	29.2	28.8
75°	24.1	24.1	23.9	23.7	23.3	23.2	23.3
77.5°	18.5	18.6	18.3	18.2	18.2	18.2	18.0
80°	14.8	15.0	14.8	14.6	14.4	14.6	14.4
82.5°	11.7	11.4	11.4	11.3	11.3	11.3	11.2
85°	6.7	6.8	6.7	6.5	6.5	6.5	6.7
87.5°	7.2	7.4	7.6	7.7	7.7	7.8	7.7
90°	23.2	24.4	25.2	25.6	26.0	26.5	26.9
92.5°	24.9	25.4	25.8	26.1	26.4	26.7	26.9
95°	42.2	43.3	43.8	43.5	43.3	43.1	42.9
97.5°	54.7	55.6	56.2	56.4	56.7	57.0	57.2
100°	62.1	63.9	65.1	65.5	66.0	66.4	66.9
102.5°	65.4	67.7	69.1	69.7	70.4	71.0	71.6
105°	68.2	70.6	72.2	73.1	74.0	74.9	75.8
107.5°	77.7	75.3	74.4	75.3	76.2	77.1	78.0
110°	108.0	85.9	75.3	76.1	77.0	77.9	78.8



TEST NUMBER: P331777-930

CATALOG NUMBER: S122RDIW-S290D1240U930-4F0-1E-UDD-A

**CANDELA DISTRIBUTION (continued):**

	330°	335°	340°	345°	350°	355°	360°
112.5°	197.7	116.8	76.7	77.5	78.2	78.8	79.6
115°	307.5	204.9	145.6	129.6	113.7	97.8	81.8
117.5°	607.1	582.3	543.6	491.2	438.8	386.4	333.9
120°	739.0	741.7	728.1	698.1	668.2	638.3	608.4
122.5°	782.9	784.5	782.4	776.6	770.8	765.0	759.1
125°	847.4	849.0	850.0	850.7	851.4	852.1	852.7
127.5°	907.8	910.0	911.3	911.3	911.5	911.6	911.7
130°	945.8	948.2	949.3	949.1	948.9	948.7	948.4
132.5°	982.2	984.3	985.2	985.0	984.8	984.6	984.4
135°	1034.9	1037.1	1038.0	1037.5	1037.1	1036.7	1036.2
137.5°	1083.6	1085.8	1086.5	1085.7	1085.0	1084.3	1083.5
140°	1115.0	1117.0	1117.4	1116.3	1115.2	1114.1	1113.0
142.5°	1144.0	1145.8	1146.1	1145.1	1143.9	1142.8	1141.7
145°	1184.5	1186.0	1186.3	1185.1	1184.1	1182.9	1181.9
147.5°	1219.6	1220.7	1220.8	1219.9	1219.0	1218.1	1217.2
150°	1241.7	1243.0	1243.1	1242.0	1240.9	1239.7	1238.7
152.5°	1261.6	1263.0	1262.9	1261.4	1260.0	1258.5	1257.0
155°	1288.6	1289.9	1289.6	1287.8	1286.1	1284.3	1282.5
157.5°	1311.4	1313.0	1312.8	1311.1	1309.4	1307.7	1305.9
160°	1324.5	1325.8	1325.7	1324.1	1322.6	1321.0	1319.5
162.5°	1336.9	1338.5	1338.2	1336.4	1334.4	1332.5	1330.6
165°	1352.0	1353.6	1353.6	1352.0	1350.5	1348.9	1347.4
167.5°	1364.6	1366.1	1366.0	1363.9	1362.0	1359.9	1358.0
170°	1371.0	1372.6	1372.3	1370.4	1368.3	1366.4	1364.3
172.5°	1375.7	1377.3	1377.1	1375.1	1373.1	1371.1	1369.1
175°	1381.0	1382.5	1382.2	1380.0	1377.8	1375.5	1373.3
177.5°	1381.2	1382.5	1382.3	1380.7	1379.1	1377.5	1375.9
180°	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3	1378.3

(END OF REPORT)