

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331800-935

Luminaire Tested: **S122RDIW-S485D1240U935-4F0-1E-UDD-F1**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331800-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-8,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1240U935-4F0-1E-UDD-F1
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1240 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 5165.9 lumens
Efficiency: N/A
Efficacy: 96.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 53.8
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

Luminous Intensity Polar Plot





TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20
RC	80				70				50				30				10
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10
RCR																	
0	102	102	102	102	91	91	91	91	71	71	71	53	53	53	36	36	36
1	93	89	85	82	83	80	77	74	63	61	59	47	46	45	32	32	31
2	85	78	72	67	76	70	65	61	55	52	49	42	39	38	29	28	27
3	78	69	62	56	69	62	56	51	49	45	42	37	34	32	26	24	23
4	71	61	53	48	63	55	49	44	44	39	36	33	30	28	23	21	20
5	65	54	47	41	58	49	42	37	39	34	31	30	27	24	21	19	17
6	60	49	41	35	54	44	37	33	35	30	27	27	24	21	19	17	16
7	56	44	36	31	50	40	33	29	32	27	24	24	21	19	18	15	14
8	51	40	32	27	46	36	30	25	29	24	21	22	19	17	16	14	12
9	48	36	29	24	43	33	27	22	27	22	19	21	17	15	15	13	11
10	45	33	26	22	40	30	24	20	24	20	17	19	16	13	14	12	10

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.3
10°-20°	182.6	3.5
20°-30°	256.4	5.0
30°-40°	279.6	5.4
40°-50°	257.1	5.0
50°-60°	201.9	3.9
60°-70°	131.7	2.5
70°-80°	67.9	1.3
80°-90°	22.9	0.4
90°-100°	83.8	1.6
100°-110°	260.4	5.0
110°-120°	445.0	8.6
120°-130°	585.3	11.3
130°-140°	656.9	12.7
140°-150°	644.1	12.5
150°-160°	540.2	10.5
160°-170°	358.3	6.9
170°-180°	125.2	2.4
0°-30°	505.6	9.8
0°-40°	785.2	15.2
0°-60°	1244.3	24.1
0°-90°	1466.7	28.4
90°-120°	789.2	15.3
90°-150°	2675.4	51.8
90°-180°	3699.0	71.6
0°-180°	5165.9	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	15	39	37	38	4
95°	58	69	72	71	69	67
105°	240	243	246	248	248	253
115°	447	453	451	450	447	442
125°	650	659	656	653	652	580
135°	841	852	855	854	851	649
145°	1020	1028	1035	1036	1032	637
155°	1167	1170	1173	1178	1176	537
165°	1269	1268	1268	1275	1270	358
175°	1321	1318	1315	1322	1316	125
180°	1323	1323	1323	1323	1323	



TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.4	8.1	7.8	7.5	7.1	7.6	8.7	9.7	10.8	12.0	11.7
90°	1.1	4.1	7.1	10.1	13.0	17.2	22.7	28.2	33.6	39.1	38.6
92.5°	19.9	22.0	24.3	26.4	28.6	30.3	31.6	32.9	34.2	35.5	35.6
95°	58.0	60.5	63.0	65.5	68.0	69.5	70.0	70.4	70.9	71.5	71.5
97.5°	106.1	108.2	110.5	112.6	114.8	116.3	117.3	118.2	119.2	120.1	120.1
100°	141.8	143.8	145.8	147.7	149.7	151.1	151.8	152.6	153.3	154.0	154.0
102.5°	179.3	180.9	182.4	184.1	185.6	186.9	187.9	188.8	189.8	190.7	190.9
105°	240.0	240.7	241.5	242.3	243.0	243.7	244.1	244.6	245.1	245.6	246.1
107.5°	301.2	302.3	303.4	304.4	305.6	306.1	306.1	306.1	306.1	306.1	306.3
110°	340.5	342.0	343.5	345.0	346.5	347.2	347.2	347.2	347.2	347.2	347.2



TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	383.4	384.9	386.3	387.9	389.3	389.9	389.8	389.6	389.3	389.2	388.6
115°	446.6	448.1	449.5	451.0	452.5	453.0	452.5	452.0	451.5	451.0	450.8
117.5°	509.5	511.5	513.5	515.5	517.5	517.8	516.3	515.0	513.6	512.2	511.6
120°	551.5	553.5	555.5	557.5	559.5	559.5	557.5	555.5	553.5	551.5	551.5
122.5°	589.9	592.3	594.7	597.0	599.4	599.9	598.6	597.2	595.7	594.3	593.7
125°	649.7	651.9	654.2	656.4	658.7	659.4	658.7	658.0	657.2	656.4	655.7
127.5°	708.0	710.8	713.7	716.5	719.4	720.3	719.5	718.5	717.6	716.7	715.8
130°	744.7	747.9	751.1	754.3	757.5	758.9	758.5	757.9	757.4	756.9	756.4
132.5°	785.7	788.3	791.0	793.6	796.3	797.6	797.7	797.8	797.9	798.0	796.9
135°	840.7	843.3	846.1	848.9	851.6	853.2	853.7	854.2	854.7	855.1	854.9
137.5°	898.5	900.7	902.9	905.2	907.4	908.9	909.5	910.2	910.8	911.5	911.3
140°	933.3	935.6	937.8	940.0	942.3	944.0	945.2	946.5	947.7	948.9	948.9
142.5°	969.1	971.3	973.5	975.8	978.0	979.5	980.3	981.2	982.1	982.9	983.1
145°	1020.4	1022.2	1023.9	1025.6	1027.3	1029.0	1030.4	1031.9	1033.5	1034.9	1035.2
147.5°	1066.2	1068.2	1070.3	1072.5	1074.5	1076.1	1077.0	1078.1	1079.0	1080.0	1080.6
150°	1097.4	1098.9	1100.4	1101.9	1103.4	1104.7	1105.6	1106.6	1107.6	1108.6	1109.3
152.5°	1125.2	1126.6	1128.1	1129.5	1131.1	1132.4	1133.6	1134.8	1136.0	1137.2	1138.2
155°	1166.7	1167.4	1168.1	1168.9	1169.7	1170.4	1171.1	1171.8	1172.6	1173.4	1174.6
157.5°	1202.1	1202.6	1203.2	1203.7	1204.1	1204.6	1205.1	1205.5	1205.9	1206.4	1208.1
160°	1223.6	1224.1	1224.6	1225.1	1225.5	1226.0	1226.2	1226.4	1226.7	1226.9	1228.4
162.5°	1243.2	1243.4	1243.5	1243.5	1243.6	1243.8	1244.1	1244.3	1244.6	1244.8	1246.5
165°	1269.4	1269.1	1268.9	1268.6	1268.3	1268.3	1268.3	1268.3	1268.3	1268.3	1270.0
167.5°	1291.2	1290.5	1289.8	1289.0	1288.2	1287.9	1287.8	1287.8	1287.7	1287.6	1289.4
170°	1302.9	1302.1	1301.4	1300.6	1299.9	1299.4	1299.2	1298.9	1298.6	1298.4	1300.1
172.5°	1310.9	1310.2	1309.4	1308.6	1307.9	1307.4	1307.2	1306.9	1306.7	1306.4	1308.2
175°	1320.7	1320.0	1319.2	1318.4	1317.8	1317.2	1316.6	1316.1	1315.6	1315.1	1316.9
177.5°	1324.7	1324.1	1323.5	1322.9	1322.3	1321.9	1321.5	1321.0	1320.7	1320.3	1321.5
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9



TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	11.5	11.3	11.1	11.0	11.0	11.1	11.1	11.2
90°	38.1	37.6	37.1	36.9	37.2	37.5	37.7	38.0
92.5°	35.7	35.8	35.9	36.0	36.0	36.1	36.2	36.2
95°	71.5	71.5	71.5	71.2	70.7	70.2	69.7	69.2
97.5°	120.1	120.1	120.1	120.1	120.0	120.0	119.9	119.9
100°	154.0	154.0	154.0	153.9	153.7	153.4	153.2	152.9
102.5°	191.1	191.3	191.5	191.5	191.2	191.0	190.7	190.5
105°	246.6	247.1	247.6	247.9	247.9	247.9	247.9	247.9
107.5°	306.5	306.7	306.9	306.4	305.3	304.2	303.0	301.9
110°	347.2	347.2	347.2	346.8	346.1	345.3	344.6	343.9



TEST NUMBER: P331800-935

CATALOG NUMBER: S122RDIW-S485D1240U935-4F0-1E-UDD-F1

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	388.0	387.4	386.8	386.2	385.6	385.1	384.6	384.0
115°	450.6	450.3	450.0	449.5	448.8	448.1	447.3	446.6
117.5°	511.0	510.4	509.8	509.2	508.4	507.6	507.0	506.2
120°	551.5	551.5	551.5	551.1	550.4	549.7	548.9	548.2
122.5°	593.2	592.6	592.0	591.4	590.9	590.3	589.8	589.3
125°	655.0	654.2	653.5	653.0	652.7	652.5	652.2	651.9
127.5°	715.0	714.0	713.2	712.3	711.5	710.8	710.0	709.1
130°	756.0	755.4	754.9	754.2	753.2	752.3	751.2	750.2
132.5°	795.8	794.7	793.7	792.7	791.9	791.1	790.3	789.5
135°	854.7	854.5	854.2	853.7	852.9	852.2	851.4	850.7
137.5°	911.0	910.9	910.7	910.1	909.0	908.1	907.1	906.1
140°	948.9	948.9	948.9	948.5	947.4	946.5	945.5	944.5
142.5°	983.3	983.5	983.7	983.3	982.3	981.3	980.3	979.3
145°	1035.4	1035.7	1035.9	1035.5	1034.6	1033.5	1032.6	1031.6
147.5°	1081.1	1081.7	1082.2	1082.0	1081.1	1080.1	1079.2	1078.2
150°	1110.1	1110.9	1111.6	1111.6	1110.9	1110.1	1109.3	1108.6
152.5°	1139.1	1140.0	1140.9	1140.9	1140.0	1139.1	1138.2	1137.2
155°	1175.9	1177.1	1178.3	1178.5	1177.8	1177.1	1176.3	1175.6
157.5°	1209.8	1211.4	1213.1	1213.4	1212.2	1211.0	1209.8	1208.6
160°	1229.9	1231.4	1232.9	1233.1	1232.2	1231.1	1230.2	1229.2
162.5°	1248.2	1249.8	1251.5	1251.8	1250.6	1249.4	1248.2	1247.1
165°	1271.7	1273.4	1275.2	1275.4	1274.2	1273.0	1271.7	1270.5
167.5°	1291.2	1292.9	1294.6	1294.9	1293.6	1292.3	1291.0	1289.7
170°	1301.8	1303.6	1305.4	1305.4	1304.0	1302.5	1301.0	1299.5
172.5°	1309.9	1311.6	1313.4	1313.5	1312.0	1310.5	1309.1	1307.5
175°	1318.6	1320.3	1322.1	1322.2	1320.7	1319.2	1317.8	1316.2
177.5°	1322.7	1323.9	1325.0	1325.0	1323.9	1322.7	1321.5	1320.3
180°	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9	1322.9

(END OF REPORT)