

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331803-935

Luminaire Tested: **S122RDIW-S485D1440U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331803-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D1440U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 1440 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 6425.0 lumens
Efficiency: N/A
Efficacy: 106.0 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 60.6
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	101	101	101	101	89	89	89	89	68	68	68	49	49	49	31	31	31	23
1	92	88	84	81	81	78	75	72	60	58	56	43	42	41	28	27	27	20
2	84	77	71	66	74	68	64	60	53	50	47	38	36	34	25	24	23	17
3	77	68	61	55	68	60	55	50	47	43	39	34	31	29	22	21	20	14
4	70	60	53	47	62	54	47	42	41	37	34	30	27	25	20	18	17	13
5	64	53	46	40	57	48	41	36	37	33	29	27	24	22	18	16	15	11
6	59	48	40	35	52	43	36	31	33	29	25	25	22	19	16	15	13	10
7	55	43	35	30	48	39	32	28	30	26	22	22	19	17	15	13	12	9
8	50	39	32	27	45	35	29	24	27	23	20	20	17	15	14	12	11	8
9	47	35	28	24	42	32	26	22	25	21	17	19	16	13	13	11	10	7
10	44	32	26	21	39	29	23	19	23	19	16	17	14	12	12	10	9	7

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	1.0
10°-20°	182.6	2.8
20°-30°	256.4	4.0
30°-40°	279.6	4.4
40°-50°	257.1	4.0
50°-60°	201.9	3.1
60°-70°	131.7	2.0
70°-80°	67.9	1.1
80°-90°	21.8	0.3
90°-100°	56.5	0.9
100°-110°	207.0	3.2
110°-120°	553.4	8.6
120°-130°	913.5	14.2
130°-140°	971.4	15.1
140°-150°	902.9	14.1
150°-160°	726.0	11.3
160°-170°	467.8	7.3
170°-180°	161.0	2.5
0°-30°	505.6	7.9
0°-40°	785.2	12.2
0°-60°	1244.3	19.4
0°-90°	1465.6	22.8
90°-120°	816.8	12.7
90°-150°	3604.6	56.1
90°-180°	4959.0	77.2
0°-180°	6425.0	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	1	14	24	30	33	5
95°	80	42	48	53	53	97
105°	372	388	75	88	93	398
115°	704	725	756	215	100	693
125°	996	1012	1035	1043	1047	887
135°	1232	1251	1262	1274	1272	951
145°	1429	1429	1449	1456	1451	893
155°	1574	1564	1577	1584	1575	725
165°	1658	1651	1654	1662	1654	468
175°	1696	1688	1690	1697	1686	161
180°	1692	1692	1692	1692	1692	



TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.4	8.2	7.8	7.5	7.2	7.2	7.7	8.2	8.6	9.0	9.2
90°	1.2	4.2	7.2	10.2	13.2	15.8	18.0	20.1	22.3	24.5	25.8
92.5°	24.7	24.5	24.2	23.9	23.7	24.0	25.1	26.3	27.3	28.4	29.1
95°	79.6	70.6	61.6	52.7	43.7	40.1	42.0	43.9	45.9	47.8	49.1
97.5°	158.0	132.7	107.4	82.1	56.7	46.3	50.7	55.1	59.5	63.9	65.0
100°	216.7	179.4	142.2	104.9	67.6	51.3	55.9	60.5	65.2	69.8	72.0
102.5°	281.4	273.5	265.6	257.7	249.9	226.5	187.9	149.1	110.5	71.7	74.6
105°	372.3	380.4	388.6	396.7	404.9	371.9	297.6	223.3	149.0	74.7	77.7
107.5°	475.9	482.4	489.0	495.6	502.2	461.0	371.9	282.8	193.6	104.6	101.5
110°	542.5	548.2	553.9	559.6	565.3	528.8	450.2	371.6	292.9	214.3	187.1



TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	605.2	610.2	615.3	620.4	625.4	618.2	598.8	579.4	559.9	540.5	441.3
115°	704.1	708.8	713.3	718.0	722.6	728.3	735.1	741.9	748.7	755.5	629.6
117.5°	792.6	797.7	802.9	808.0	813.2	818.1	822.8	827.5	832.2	836.9	806.4
120°	857.2	861.3	865.3	869.4	873.5	878.0	882.9	887.8	892.7	897.6	900.9
122.5°	912.1	916.4	920.7	925.0	929.3	934.1	939.4	944.7	950.0	955.4	957.3
125°	995.6	999.1	1002.6	1006.2	1009.7	1014.1	1019.3	1024.4	1029.6	1034.7	1036.6
127.5°	1071.3	1075.1	1079.1	1083.0	1086.9	1090.8	1094.7	1098.5	1102.4	1106.3	1109.1
130°	1119.2	1123.6	1127.9	1132.3	1136.7	1140.3	1143.3	1146.3	1149.3	1152.3	1155.3
132.5°	1168.2	1171.9	1175.6	1179.3	1183.0	1186.4	1189.4	1192.3	1195.3	1198.3	1200.9
135°	1231.9	1236.2	1240.6	1244.9	1249.3	1252.7	1255.2	1257.6	1260.1	1262.5	1265.2
137.5°	1296.3	1299.3	1302.4	1305.4	1308.5	1311.4	1314.1	1317.0	1319.7	1322.5	1325.2
140°	1338.4	1340.6	1342.8	1345.0	1347.1	1349.7	1352.7	1355.7	1358.7	1361.7	1364.2
142.5°	1373.7	1375.6	1377.6	1379.6	1381.6	1384.2	1387.7	1391.1	1394.5	1397.9	1400.2
145°	1429.1	1428.7	1428.5	1428.2	1428.0	1430.1	1434.8	1439.4	1444.0	1448.6	1450.5
147.5°	1477.3	1476.3	1475.2	1474.2	1473.2	1474.9	1479.5	1484.1	1488.7	1493.2	1494.6
150°	1508.6	1506.8	1504.9	1503.0	1501.0	1502.3	1506.6	1511.0	1515.3	1519.7	1521.3
152.5°	1535.1	1533.0	1530.9	1528.7	1526.6	1527.6	1531.7	1535.9	1540.0	1544.1	1545.8
155°	1573.6	1571.1	1568.7	1566.2	1563.7	1564.2	1567.5	1570.7	1574.0	1577.2	1578.8
157.5°	1603.7	1601.6	1599.6	1597.5	1595.4	1595.5	1597.8	1600.1	1602.3	1604.6	1606.5
160°	1621.3	1619.6	1618.1	1616.4	1614.8	1614.8	1616.4	1618.1	1619.6	1621.3	1622.9
162.5°	1636.9	1635.4	1633.7	1632.1	1630.5	1630.3	1631.8	1633.1	1634.6	1636.0	1637.9
165°	1658.0	1656.4	1654.8	1653.1	1651.5	1651.1	1651.9	1652.7	1653.6	1654.3	1656.3
167.5°	1673.7	1672.1	1670.4	1668.8	1667.2	1666.7	1667.5	1668.3	1669.0	1669.8	1671.7
170°	1682.6	1680.9	1679.3	1677.7	1676.0	1675.4	1676.0	1676.5	1677.1	1677.7	1679.6
172.5°	1688.4	1686.8	1685.1	1683.5	1681.9	1681.4	1681.9	1682.4	1683.0	1683.5	1685.4
175°	1696.0	1694.1	1692.2	1690.3	1688.4	1687.7	1688.2	1688.8	1689.4	1689.9	1691.8
177.5°	1697.2	1695.7	1694.2	1692.6	1691.1	1690.5	1690.7	1690.9	1691.1	1691.3	1692.9
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3



TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	9.3	9.5	9.6	9.8	9.9	10.0	10.1	10.2
90°	27.2	28.6	30.0	30.9	31.4	31.9	32.5	33.1
92.5°	29.8	30.6	31.3	31.8	32.1	32.4	32.7	33.1
95°	50.5	51.8	53.2	53.7	53.5	53.2	53.0	52.7
97.5°	66.1	67.2	68.3	69.0	69.3	69.7	70.0	70.3
100°	74.1	76.4	78.5	79.9	80.4	80.9	81.5	82.1
102.5°	77.4	80.2	83.1	84.9	85.7	86.4	87.1	87.9
105°	80.7	83.7	86.7	88.7	89.8	90.9	92.0	93.1
107.5°	98.5	95.4	92.4	91.4	92.5	93.6	94.7	95.7
110°	159.9	132.7	105.5	92.4	93.5	94.5	95.7	96.8



TEST NUMBER: P331803-935

CATALOG NUMBER: S122RDIW-S485D1440U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	342.0	242.7	143.4	94.2	95.1	96.0	96.9	97.7
115°	503.6	377.5	251.6	178.7	159.2	139.6	120.0	100.4
117.5°	775.9	745.5	715.0	667.5	603.1	538.7	474.3	410.0
120°	904.1	907.4	910.7	893.9	857.2	820.4	783.7	747.0
122.5°	959.3	961.3	963.2	960.6	953.5	946.4	939.3	932.1
125°	1038.5	1040.4	1042.3	1043.7	1044.6	1045.3	1046.2	1047.0
127.5°	1111.8	1114.6	1117.3	1118.9	1119.0	1119.1	1119.3	1119.5
130°	1158.3	1161.3	1164.2	1165.6	1165.4	1165.1	1164.8	1164.5
132.5°	1203.4	1206.0	1208.6	1209.7	1209.4	1209.2	1208.9	1208.6
135°	1267.9	1270.7	1273.4	1274.5	1273.9	1273.4	1272.8	1272.3
137.5°	1327.8	1330.5	1333.2	1334.0	1333.1	1332.2	1331.3	1330.3
140°	1366.6	1369.1	1371.5	1372.0	1370.7	1369.3	1368.0	1366.6
142.5°	1402.4	1404.6	1406.9	1407.3	1405.9	1404.5	1403.3	1401.9
145°	1452.4	1454.3	1456.3	1456.6	1455.2	1453.8	1452.4	1451.1
147.5°	1496.1	1497.5	1498.9	1499.0	1497.9	1496.8	1495.6	1494.4
150°	1522.9	1524.6	1526.2	1526.3	1525.0	1523.6	1522.2	1520.9
152.5°	1547.4	1549.0	1550.7	1550.6	1548.8	1547.0	1545.2	1543.4
155°	1580.5	1582.1	1583.7	1583.5	1581.3	1579.2	1576.9	1574.8
157.5°	1608.3	1610.2	1612.1	1611.9	1609.8	1607.7	1605.5	1603.4
160°	1624.5	1626.2	1627.8	1627.7	1625.8	1623.8	1622.0	1620.1
162.5°	1639.7	1641.6	1643.4	1643.1	1640.8	1638.5	1636.2	1633.8
165°	1658.2	1660.1	1662.0	1662.0	1660.1	1658.2	1656.3	1654.3
167.5°	1673.6	1675.5	1677.4	1677.1	1674.7	1672.2	1669.8	1667.3
170°	1681.4	1683.3	1685.2	1685.0	1682.6	1680.1	1677.7	1675.2
172.5°	1687.3	1689.2	1691.1	1690.8	1688.4	1685.9	1683.5	1681.0
175°	1693.7	1695.6	1697.5	1697.1	1694.4	1691.6	1688.9	1686.2
177.5°	1694.4	1695.9	1697.5	1697.2	1695.2	1693.3	1691.3	1689.4
180°	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3	1692.3

(END OF REPORT)