

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331771-930

Luminaire Tested: **S122RDIW-S290D710U930-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331771-930
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S290D710U930-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 290 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 710 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 3155.2 lumens
Efficiency: N/A
Efficacy: 103.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: Semi-Indirect


Input Watts (W): 30.4
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	102	102	102	102	91	91	91	91	70	70	70	52	52	52	35	35	35	27
1	93	89	85	82	83	79	76	74	62	60	58	46	45	43	31	30	30	23
2	85	78	72	67	75	70	65	61	55	51	48	41	38	37	28	26	25	20
3	77	68	62	56	69	61	56	51	48	44	41	36	33	31	25	23	22	17
4	71	61	53	48	63	55	48	43	43	39	35	32	29	27	22	20	19	15
5	65	54	46	41	58	49	42	37	38	34	30	29	26	23	20	18	17	13
6	60	48	41	35	53	44	37	32	35	30	26	26	23	21	18	16	15	12
7	55	44	36	31	49	39	33	28	31	27	23	24	21	18	17	15	13	10
8	51	40	32	27	46	36	29	25	29	24	21	22	19	16	15	13	12	9
9	48	36	29	24	43	33	26	22	26	22	18	20	17	15	14	12	11	8
10	44	33	26	21	40	30	24	20	24	20	16	18	15	13	13	11	10	8

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	6608	6608	6608
5°	6634	6525	6561
10°	6583	6419	6365
15°	6506	6228	6048
20°	6402	5957	5658
25°	6296	5649	5279
30°	6145	5330	4793
35°	6000	4987	4366
40°	5855	4628	3872
45°	5683	4229	3425
50°	5506	3823	2987
55°	5326	3386	2567
60°	5118	2929	2131
65°	4883	2460	1937
70°	4598	2030	1780
75°	4255	1847	1666
80°	3756	1655	1516
85°	2946	1297	1297



TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	38.3	1.2
10°-20°	105.2	3.3
20°-30°	147.7	4.7
30°-40°	161.1	5.1
40°-50°	148.1	4.7
50°-60°	116.3	3.7
60°-70°	75.8	2.4
70°-80°	39.1	1.2
80°-90°	12.1	0.4
90°-100°	26.3	0.8
100°-110°	96.5	3.1
110°-120°	257.9	8.2
120°-130°	425.7	13.5
130°-140°	452.8	14.4
140°-150°	420.8	13.3
150°-160°	338.4	10.7
160°-170°	218.0	6.9
170°-180°	75.1	2.4
0°-30°	291.2	9.2
0°-40°	452.3	14.3
0°-60°	716.7	22.7
0°-90°	843.7	26.7
90°-120°	380.7	12.1
90°-150°	1680.1	53.2
90°-180°	2312.0	73.3
0°-180°	3155.2	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	409	409	409	409	409	
5°	409	407	403	406	405	39
15°	389	385	373	366	362	110
25°	353	341	317	302	296	162
35°	304	285	253	230	222	190
45°	249	223	185	160	150	192
55°	189	160	120	99	91	169
65°	128	98	64	52	51	127
75°	68	43	30	27	27	72
85°	16	8	7	7	7	19
90°	1	7	11	14	15	2
95°	37	20	22	25	24	45
105°	174	181	35	41	43	185
115°	328	338	352	100	47	323
125°	464	472	482	486	488	414
135°	574	583	588	594	593	443
145°	666	666	675	679	676	416
155°	733	729	735	738	734	338
165°	773	770	771	775	771	218
175°	790	787	788	791	786	75
180°	789	789	789	789	789	



TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	410.7	410.4	410.1	409.8	409.4	408.9	408.1	407.5	406.8	406.0	406.7
5°	409.3	408.9	408.5	408.1	407.6	406.8	405.8	404.7	403.7	402.6	403.3
7.5°	405.0	404.6	404.0	403.5	403.0	402.1	400.9	399.6	398.4	397.1	397.3
10°	401.5	400.9	400.3	399.7	399.2	398.0	396.4	394.8	393.1	391.5	391.3
12.5°	397.1	396.3	395.6	394.9	394.2	392.8	390.7	388.6	386.5	384.3	383.9
15°	389.2	388.3	387.4	386.5	385.6	383.8	381.0	378.2	375.4	372.6	371.0
17.5°	379.7	378.3	376.9	375.5	374.1	371.7	368.1	364.5	360.9	357.3	355.5
20°	372.6	371.0	369.3	367.6	366.0	363.1	359.0	354.9	350.8	346.7	344.6
22.5°	364.9	363.1	361.2	359.4	357.5	354.2	349.6	345.0	340.4	335.7	333.0
25°	353.4	350.7	348.1	345.4	342.8	338.8	333.3	327.9	322.5	317.1	313.6
27.5°	339.4	336.6	333.7	330.8	327.9	323.4	317.3	311.2	305.1	299.0	295.1
30°	329.6	326.5	323.3	320.2	317.2	312.3	305.7	299.1	292.5	285.9	281.8
32.5°	320.2	316.5	312.8	309.2	305.5	300.4	293.7	286.9	280.2	273.5	268.7
35°	304.4	300.3	296.0	291.9	287.6	281.9	274.7	267.4	260.2	253.0	247.8
37.5°	288.8	284.1	279.5	274.9	270.3	264.2	256.4	248.7	241.0	233.3	227.6
40°	277.8	272.9	267.9	262.9	258.0	251.6	243.6	235.6	227.6	219.6	213.8
42.5°	266.5	261.3	256.1	250.9	245.7	239.0	230.7	222.5	214.3	206.0	200.0
45°	248.9	243.4	237.8	232.4	226.8	219.7	211.1	202.4	193.8	185.2	179.4
47.5°	231.7	225.8	220.0	214.2	208.3	201.0	192.0	183.1	174.1	165.3	159.5
50°	219.2	213.4	207.6	201.7	195.9	188.4	179.4	170.3	161.3	152.2	146.5
52.5°	207.1	201.0	194.9	188.8	182.7	175.2	166.3	157.5	148.6	139.7	134.3
55°	189.2	182.9	176.4	170.0	163.5	156.0	147.0	138.1	129.2	120.3	115.4
57.5°	171.0	164.4	157.8	151.2	144.6	137.1	128.5	120.0	111.5	102.9	98.3
60°	158.5	152.0	145.4	138.8	132.2	124.7	116.2	107.7	99.2	90.7	86.5
62.5°	146.3	139.8	133.2	126.6	120.0	112.7	104.6	96.5	88.5	80.4	76.4
65°	127.8	121.1	114.5	107.8	101.1	94.1	86.7	79.2	71.8	64.4	61.6
67.5°	109.8	103.2	96.6	90.0	83.4	76.7	70.0	63.4	56.7	50.1	48.8
70°	97.4	91.0	84.5	78.2	71.7	65.7	60.0	54.3	48.7	43.0	42.2
72.5°	85.5	79.4	73.2	67.1	60.9	55.6	51.0	46.5	41.9	37.3	36.6
75°	68.2	62.4	56.7	50.9	45.1	40.8	38.0	35.2	32.4	29.6	29.0
77.5°	51.0	46.0	40.9	35.9	30.8	27.6	26.3	24.9	23.6	22.3	21.9
80°	40.4	36.2	32.0	27.8	23.6	21.0	20.2	19.4	18.6	17.8	17.4
82.5°	30.6	27.3	24.1	20.8	17.5	15.6	15.0	14.4	13.9	13.4	13.1
85°	15.9	14.2	12.5	10.8	9.0	8.0	7.7	7.5	7.3	7.0	7.0
87.5°	4.9	4.6	4.3	4.1	3.8	3.8	4.1	4.2	4.5	4.6	4.7
90°	0.6	2.0	3.3	4.7	6.1	7.3	8.4	9.4	10.4	11.4	12.1
92.5°	11.5	11.4	11.3	11.2	11.0	11.3	11.7	12.2	12.7	13.2	13.5
95°	37.1	32.9	28.7	24.5	20.4	18.7	19.6	20.5	21.4	22.3	22.9
97.5°	73.6	61.8	50.1	38.2	26.4	21.6	23.6	25.7	27.7	29.8	30.3
100°	101.0	83.6	66.3	48.9	31.6	23.9	26.1	28.2	30.4	32.5	33.5
102.5°	131.2	127.5	123.8	120.1	116.4	105.6	87.6	69.5	51.4	33.4	34.7
105°	173.5	177.3	181.2	184.9	188.7	173.3	138.7	104.0	69.5	34.8	36.2
107.5°	221.8	224.9	228.0	231.0	234.1	214.8	173.3	131.8	90.3	48.8	47.3
110°	252.8	255.5	258.2	260.8	263.5	246.5	209.9	173.2	136.6	99.9	87.2



TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	282.1	284.5	286.8	289.1	291.5	288.1	279.1	270.0	261.0	251.9	205.7
115°	328.2	330.4	332.5	334.7	336.8	339.5	342.7	345.8	348.9	352.1	293.4
117.5°	369.4	371.8	374.2	376.6	379.0	381.3	383.5	385.7	387.8	390.0	375.9
120°	399.5	401.5	403.3	405.2	407.2	409.2	411.5	413.8	416.0	418.3	419.9
122.5°	425.1	427.1	429.1	431.1	433.1	435.4	437.8	440.3	442.8	445.3	446.2
125°	464.0	465.7	467.3	469.0	470.6	472.6	475.1	477.4	479.9	482.2	483.1
127.5°	499.3	501.1	503.0	504.8	506.6	508.4	510.2	512.0	513.8	515.6	516.9
130°	521.6	523.7	525.7	527.7	529.8	531.5	532.9	534.3	535.7	537.1	538.5
132.5°	544.5	546.3	548.0	549.7	551.4	552.9	554.3	555.7	557.2	558.6	559.7
135°	574.2	576.2	578.2	580.2	582.3	583.9	585.1	586.2	587.3	588.5	589.7
137.5°	604.2	605.6	607.1	608.5	609.8	611.2	612.5	613.8	615.1	616.4	617.7
140°	623.9	624.8	625.8	626.9	627.9	629.1	630.5	631.9	633.2	634.7	635.9
142.5°	640.3	641.2	642.1	643.0	643.9	645.1	646.8	648.4	650.0	651.6	652.6
145°	666.1	665.9	665.9	665.7	665.5	666.6	668.7	670.9	673.0	675.2	676.1
147.5°	688.5	688.1	687.6	687.1	686.6	687.5	689.6	691.7	693.8	695.9	696.7
150°	703.2	702.3	701.4	700.5	699.6	700.2	702.2	704.3	706.3	708.3	709.1
152.5°	715.5	714.5	713.5	712.5	711.5	712.0	714.0	715.8	717.8	719.7	720.5
155°	733.4	732.3	731.2	730.0	728.9	729.0	730.6	732.1	733.6	735.2	735.9
157.5°	747.5	746.5	745.5	744.5	743.6	743.6	744.7	745.8	746.8	747.9	748.8
160°	755.7	754.9	754.2	753.4	752.6	752.6	753.4	754.2	754.9	755.7	756.4
162.5°	763.0	762.2	761.5	760.7	759.9	759.9	760.5	761.2	761.9	762.5	763.4
165°	772.8	772.0	771.3	770.5	769.7	769.6	770.0	770.3	770.7	771.1	772.0
167.5°	780.1	779.3	778.6	777.8	777.1	776.9	777.2	777.6	778.0	778.3	779.2
170°	784.2	783.4	782.7	782.0	781.1	780.9	781.1	781.5	781.7	782.0	782.9
172.5°	786.9	786.2	785.5	784.6	783.9	783.7	783.9	784.2	784.4	784.6	785.5
175°	790.5	789.6	788.7	787.8	786.9	786.6	786.8	787.2	787.4	787.7	788.6
177.5°	791.1	790.4	789.6	789.0	788.2	787.9	788.0	788.1	788.2	788.3	789.0
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8



TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	409.3	409.3	409.3	409.3	409.3	409.3	409.3	409.3
2.5°	407.3	408.0	408.6	408.9	408.8	408.6	408.5	408.4
5°	404.1	404.8	405.5	405.8	405.5	405.3	405.0	404.8
7.5°	397.5	397.8	397.9	397.9	397.5	397.0	396.6	396.2
10°	391.0	390.8	390.5	390.1	389.6	389.1	388.7	388.2
12.5°	383.5	383.0	382.6	382.0	381.2	380.3	379.5	378.7
15°	369.5	367.9	366.3	365.2	364.4	363.5	362.6	361.8
17.5°	353.6	351.7	349.9	348.3	346.8	345.4	344.0	342.6
20°	342.6	340.5	338.4	336.5	334.7	332.9	331.1	329.3
22.5°	330.4	327.8	325.1	323.1	321.7	320.4	319.0	317.7
25°	310.3	306.9	303.5	301.3	300.0	298.7	297.5	296.3
27.5°	291.1	287.1	283.2	280.3	278.3	276.4	274.4	272.5
30°	277.5	273.4	269.1	266.0	263.7	261.5	259.3	257.1
32.5°	263.9	259.1	254.3	250.9	248.8	246.7	244.6	242.6
35°	242.6	237.4	232.2	228.7	226.9	225.1	223.3	221.5
37.5°	221.8	216.1	210.4	206.5	204.5	202.4	200.3	198.2
40°	208.0	202.1	196.2	192.2	190.1	188.0	185.8	183.7
42.5°	193.9	187.8	181.8	177.8	175.7	173.7	171.5	169.5
45°	173.5	167.6	161.8	157.9	156.0	153.9	152.0	150.0
47.5°	153.6	147.8	142.0	138.2	136.4	134.6	132.8	131.0
50°	140.9	135.2	129.5	125.8	124.1	122.4	120.6	118.9
52.5°	128.8	123.4	117.9	114.3	112.8	111.1	109.5	107.9
55°	110.5	105.6	100.6	97.3	95.8	94.2	92.7	91.2
57.5°	93.8	89.3	84.8	81.9	80.6	79.2	77.9	76.6
60°	82.3	78.2	73.9	71.2	69.9	68.6	67.3	66.0
62.5°	72.4	68.4	64.4	62.0	61.1	60.4	59.6	58.8
65°	58.9	56.0	53.2	51.7	51.4	51.2	51.0	50.7
67.5°	47.5	46.2	44.9	44.2	43.9	43.6	43.4	43.1
70°	41.3	40.5	39.7	39.1	38.7	38.4	38.1	37.7
72.5°	36.0	35.2	34.6	34.2	33.9	33.8	33.5	33.3
75°	28.5	27.9	27.3	27.0	26.9	26.8	26.7	26.7
77.5°	21.5	21.2	20.9	20.7	20.5	20.4	20.3	20.1
80°	17.1	16.8	16.5	16.3	16.3	16.3	16.3	16.3
82.5°	13.0	12.7	12.6	12.5	12.5	12.5	12.5	12.5
85°	7.0	7.0	7.0	7.0	7.0	7.0	7.0	7.0
87.5°	4.8	4.8	4.9	5.0	5.0	5.1	5.1	5.1
90°	12.7	13.3	13.9	14.4	14.7	14.9	15.2	15.4
92.5°	13.9	14.3	14.6	14.8	14.9	15.1	15.2	15.4
95°	23.6	24.1	24.8	25.0	24.9	24.8	24.7	24.5
97.5°	30.8	31.3	31.8	32.1	32.3	32.4	32.6	32.8
100°	34.6	35.5	36.6	37.3	37.5	37.7	38.0	38.2
102.5°	36.1	37.4	38.7	39.5	39.9	40.3	40.6	41.0
105°	37.6	39.0	40.4	41.3	41.8	42.4	42.9	43.4
107.5°	45.9	44.5	43.0	42.6	43.1	43.6	44.1	44.6
110°	74.5	61.8	49.2	43.0	43.5	44.1	44.6	45.1



TEST NUMBER: P331771-930

CATALOG NUMBER: S122RDIW-S290D710U930-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	159.4	113.2	66.9	43.9	44.4	44.8	45.2	45.6
115°	234.7	175.9	117.2	83.3	74.2	65.1	55.9	46.8
117.5°	361.7	347.4	333.2	311.1	281.1	251.1	221.1	191.1
120°	421.4	422.9	424.4	416.6	399.5	382.4	365.3	348.1
122.5°	447.1	448.0	449.0	447.8	444.4	441.1	437.8	434.5
125°	484.0	484.9	485.8	486.5	486.8	487.2	487.6	488.0
127.5°	518.2	519.5	520.8	521.5	521.5	521.6	521.7	521.8
130°	539.9	541.3	542.7	543.3	543.2	543.1	542.9	542.8
132.5°	560.9	562.1	563.3	563.9	563.7	563.6	563.5	563.4
135°	591.0	592.2	593.5	594.0	593.8	593.5	593.3	593.0
137.5°	618.9	620.1	621.4	621.8	621.3	620.9	620.5	620.0
140°	637.0	638.1	639.3	639.5	638.9	638.2	637.6	637.0
142.5°	653.6	654.7	655.7	655.9	655.3	654.7	654.0	653.4
145°	676.9	677.8	678.7	678.9	678.2	677.6	676.9	676.4
147.5°	697.3	698.0	698.6	698.7	698.1	697.7	697.1	696.5
150°	709.8	710.6	711.3	711.4	710.8	710.1	709.5	708.9
152.5°	721.2	722.0	722.8	722.8	721.9	721.1	720.2	719.3
155°	736.6	737.4	738.2	738.0	737.0	736.1	735.0	734.0
157.5°	749.7	750.5	751.4	751.3	750.3	749.3	748.4	747.3
160°	757.2	758.0	758.7	758.6	757.7	756.8	756.0	755.1
162.5°	764.3	765.1	766.0	765.9	764.8	763.7	762.5	761.5
165°	772.9	773.7	774.6	774.6	773.7	772.9	772.0	771.1
167.5°	780.1	781.0	781.8	781.7	780.6	779.4	778.3	777.1
170°	783.7	784.6	785.5	785.4	784.2	783.1	782.0	780.8
172.5°	786.4	787.3	788.2	788.1	786.9	785.8	784.6	783.5
175°	789.5	790.3	791.2	791.0	789.7	788.5	787.2	785.9
177.5°	789.8	790.4	791.2	791.1	790.2	789.2	788.3	787.4
180°	788.8	788.8	788.8	788.8	788.8	788.8	788.8	788.8

(END OF REPORT)