

Scaled data based on original data using
LM-79-08 Approved Method: Electrical and Photometric Measurements of Solid-State
Lighting Products

Test Report Prepared for

Cooper Lighting Solutions

(formerly Eaton)

Brand: NEO-RAY

Report Number: P331787-935

Luminaire Tested: **S122RDIW-S485D435U935-4F0-1E-UDD-F**

Issue Date: 3/3/2020

Test Information

Test Method: LM-79-08
Report Number: P331787-935
REPORT IS SCALED FROM IESNA LM-79-08 TEST DATA (G3-1807-864-2,
Test Lab: INNOVATION CENTER
Issue Date: 3/3/2020
Manufacturer: COOPER LIGHTING SOLUTIONS (FORMERLY EATON)
Product Line: NEO-RAY
Catalog Number: S122RDIW-S485D435U935-4F0-1E-UDD-F
Description: DEFINE 2 DIRECT-INDIRECT WALL MOUNT LED LUMINAIRE
DOWNLIGHT 485 LUMENS PER FOOT, FLUSH SATIN WHITE DIFFUSER, REGRESSED
HOUSING
UPLIGHT 435 LUMENS PER FOOT, NO LENS
Light Source: -
Ballast/Driver: ELECTRONIC DRIVER

Summary

Lumens per Lamp: N/A
Luminaire Lumens: 2953.1 lumens
Efficiency: N/A
Efficacy: 97.8 lumens/watt
Spacing Criteria (0/90/45): 1.2 / 0.99 / 1.16
Luminous Opening: Rectangular (W 0.17' x L: 4' x H: 0')
CIE Type: General Diffuse


Input Watts (W): 30.2
Input Voltage (V): 120
Input Current (A_{in}): NR
Voltage Rise (V): NR
Power Factor: NR
Total Harmonic Distortion (THDi): NR
Frequency (hertz): 60
Stabilization Time: NR
Operation Time: NR
Ambient Temperature (°C): NR
Test Distance: 25 FT



TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

Luminous Intensity Polar Plot





TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

COEFFICIENT OF UTILIZATION - ZONAL CAVITY METHOD:

RF	20				20				20				20				20	
RC	80				70				50				30				10	0
RW	70	50	30	10	70	50	30	10	50	30	10	50	30	10	50	30	10	0
RCR																		
0	107	107	107	107	99	99	99	99	83	83	83	69	69	69	56	56	56	50
1	98	94	90	87	90	87	84	81	74	71	69	61	60	58	50	49	48	43
2	90	83	77	72	83	76	71	67	65	61	58	54	52	49	45	43	41	36
3	82	73	66	60	76	68	62	57	58	53	49	48	45	42	40	38	36	31
4	75	65	57	51	69	60	54	48	52	47	42	44	40	37	36	33	31	27
5	69	58	50	44	64	54	47	42	46	41	37	39	35	32	33	30	27	24
6	64	52	44	39	59	49	42	37	42	37	32	36	32	28	30	27	24	21
7	59	47	40	34	55	44	37	32	38	33	29	33	28	25	27	24	22	19
8	55	43	36	30	51	40	34	29	35	30	26	30	26	23	25	22	20	17
9	51	39	32	27	48	37	30	26	32	27	23	28	23	20	23	20	18	16
10	48	36	29	25	44	34	28	23	30	25	21	26	22	19	22	19	16	14

AVERAGE LUMINANCE (cd/sqm):

	0°	45°	90°
0°	11472	11472	11472
5°	11515	11329	11391
10°	11429	11144	11049
15°	11296	10813	10502
20°	11115	10340	9821
25°	10929	9805	9164
30°	10670	9257	8321
35°	10419	8657	7579
40°	10163	8037	6721
45°	9866	7341	5948
50°	9560	6636	5184
55°	9250	5883	4453
60°	8887	5089	3694
65°	8478	4271	3366
70°	7983	3522	3097
75°	7380	3206	2888
80°	6518	2864	2631
85°	5113	2260	2260



TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

ZONAL LUMENS:

Zone	Lumens	% Fixture
0°-10°	66.5	2.3
10°-20°	182.6	6.2
20°-30°	256.4	8.7
30°-40°	279.6	9.5
40°-50°	257.1	8.7
50°-60°	201.9	6.8
60°-70°	131.7	4.5
70°-80°	67.9	2.3
80°-90°	18.9	0.6
90°-100°	17.0	0.6
100°-110°	62.2	2.1
110°-120°	166.3	5.6
120°-130°	274.5	9.3
130°-140°	291.9	9.9
140°-150°	271.3	9.2
150°-160°	218.2	7.4
160°-170°	140.6	4.8
170°-180°	48.4	1.6
0°-30°	505.6	17.1
0°-40°	785.2	26.6
0°-60°	1244.3	42.1
0°-90°	1462.7	49.5
90°-120°	245.5	8.3
90°-150°	1083.3	36.7
90°-180°	1490.0	50.5
0°-180°	2953.1	100.0

CANDELA DISTRIBUTION:

	0°	22.5°	45°	67.5°	90°	Flux
0°	710	710	710	710	710	
5°	710	707	699	704	703	67
15°	676	668	647	635	628	190
25°	614	592	550	525	514	282
35°	529	494	439	400	384	331
45°	432	388	322	278	260	334
55°	329	277	209	172	158	293
65°	222	169	112	91	88	220
75°	118	75	51	47	46	125
85°	28	15	12	12	12	33
90°	0	4	7	9	10	2
95°	24	13	14	16	16	29
105°	112	117	22	26	28	120
115°	212	218	227	65	30	208
125°	299	304	311	313	315	267
135°	370	376	379	383	382	286
145°	430	429	435	438	436	269
155°	473	470	474	476	473	218
165°	498	496	497	500	497	141
175°	510	507	508	510	507	48
180°	509	509	509	509	509	



TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (FULL):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	713.1	712.6	712.0	711.4	710.8	709.9	708.7	707.4	706.1	704.9	706.0
5°	710.5	709.8	709.1	708.4	707.7	706.4	704.6	702.7	700.9	699.0	700.3
7.5°	703.2	702.3	701.5	700.5	699.6	698.1	695.9	693.8	691.6	689.5	689.8
10°	697.1	696.0	695.0	694.1	693.0	691.1	688.3	685.4	682.5	679.7	679.2
12.5°	689.3	688.1	686.8	685.6	684.4	682.0	678.3	674.7	671.0	667.4	666.6
15°	675.8	674.2	672.7	671.1	669.5	666.3	661.4	656.6	651.8	646.9	644.2
17.5°	659.3	656.9	654.4	652.0	649.6	645.3	639.1	632.8	626.6	620.4	617.2
20°	646.9	644.0	641.2	638.3	635.4	630.4	623.3	616.1	609.0	601.8	598.3
22.5°	633.5	630.3	627.1	623.9	620.7	615.1	607.0	598.9	590.9	582.8	578.2
25°	613.5	608.9	604.3	599.7	595.1	588.1	578.7	569.3	559.8	550.4	544.6
27.5°	589.3	584.3	579.3	574.4	569.4	561.5	551.0	540.3	529.7	519.0	512.2
30°	572.3	566.9	561.5	556.0	550.6	542.2	530.7	519.3	507.8	496.5	489.1
32.5°	555.9	549.5	543.1	536.8	530.5	521.4	509.8	498.1	486.5	474.8	466.5
35°	528.6	521.2	514.0	506.7	499.4	489.5	476.9	464.3	451.8	439.2	430.2
37.5°	501.3	493.3	485.3	477.3	469.3	458.6	445.2	431.8	418.4	405.0	395.0
40°	482.2	473.7	465.1	456.6	448.0	436.8	422.9	409.1	395.2	381.3	371.2
42.5°	462.7	453.7	444.6	435.7	426.6	414.9	400.6	386.2	372.0	357.7	347.2
45°	432.1	422.6	412.9	403.4	393.8	381.5	366.5	351.5	336.5	321.5	311.3
47.5°	402.3	392.1	382.0	371.9	361.7	348.9	333.4	317.9	302.4	286.9	276.8
50°	380.6	370.5	360.4	350.3	340.1	327.2	311.4	295.8	280.0	264.2	254.4
52.5°	359.6	349.0	338.4	327.8	317.2	304.2	288.8	273.5	258.0	242.7	233.2
55°	328.6	317.5	306.3	295.2	284.0	270.7	255.3	239.9	224.4	209.0	200.4
57.5°	296.8	285.4	274.0	262.5	251.1	238.0	223.2	208.3	193.5	178.7	170.7
60°	275.2	263.8	252.4	240.9	229.5	216.5	201.7	187.0	172.3	157.6	150.2
62.5°	254.1	242.7	231.3	219.8	208.4	195.7	181.7	167.6	153.6	139.6	132.6
65°	221.9	210.3	198.7	187.1	175.6	163.3	150.5	137.6	124.8	111.8	107.0
67.5°	190.7	179.3	167.7	156.3	144.7	133.2	121.7	110.1	98.5	87.0	84.7
70°	169.1	158.0	146.8	135.7	124.5	114.0	104.2	94.3	84.5	74.6	73.2
72.5°	148.5	137.8	127.2	116.5	105.8	96.5	88.6	80.7	72.8	64.8	63.6
75°	118.3	108.3	98.3	88.3	78.3	70.9	66.0	61.1	56.3	51.4	50.5
77.5°	88.6	79.8	71.0	62.3	53.6	48.0	45.6	43.3	40.9	38.6	38.0
80°	70.1	62.8	55.5	48.2	40.9	36.6	35.1	33.8	32.3	30.8	30.3
82.5°	53.1	47.4	41.8	36.1	30.4	27.0	26.1	25.1	24.1	23.2	22.8
85°	27.6	24.6	21.6	18.7	15.7	13.9	13.5	13.1	12.7	12.2	12.2
87.5°	8.3	7.6	6.8	6.1	5.3	5.1	5.2	5.3	5.4	5.6	5.6
90°	0.3	1.3	2.2	3.1	4.0	4.7	5.4	6.0	6.7	7.3	7.7
92.5°	7.4	7.3	7.2	7.1	7.1	7.2	7.6	7.9	8.2	8.5	8.8
95°	23.9	21.2	18.5	15.8	13.1	12.1	12.7	13.2	13.8	14.4	14.7
97.5°	47.4	39.9	32.3	24.6	17.0	13.9	15.2	16.5	17.9	19.2	19.5
100°	65.2	53.9	42.7	31.5	20.3	15.4	16.8	18.2	19.5	21.0	21.6
102.5°	84.6	82.2	79.8	77.5	75.1	68.1	56.5	44.9	33.2	21.5	22.4
105°	111.8	114.3	116.8	119.2	121.7	111.8	89.5	67.1	44.8	22.5	23.3
107.5°	143.0	145.0	147.0	149.0	150.9	138.5	111.8	85.0	58.2	31.4	30.5
110°	163.0	164.7	166.4	168.2	169.9	158.9	135.3	111.7	88.0	64.4	56.2



TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	0°	5°	10°	15°	20°	25°	30°	35°	40°	45°	50°
112.5°	181.8	183.4	184.9	186.4	188.0	185.8	179.9	174.1	168.2	162.5	132.6
115°	211.6	213.0	214.4	215.8	217.1	218.9	220.9	223.0	225.0	227.0	189.2
117.5°	238.2	239.7	241.3	242.8	244.4	245.9	247.3	248.7	250.1	251.5	242.4
120°	257.6	258.8	260.0	261.3	262.5	263.9	265.4	266.8	268.3	269.8	270.7
122.5°	274.1	275.3	276.6	277.9	279.2	280.7	282.3	283.9	285.5	287.1	287.7
125°	299.2	300.2	301.4	302.4	303.4	304.7	306.3	307.9	309.4	311.0	311.5
127.5°	321.9	323.1	324.3	325.5	326.7	327.8	329.0	330.1	331.3	332.4	333.3
130°	336.4	337.7	339.0	340.3	341.6	342.7	343.6	344.5	345.4	346.3	347.2
132.5°	351.1	352.1	353.3	354.4	355.5	356.5	357.4	358.3	359.2	360.2	360.9
135°	370.2	371.5	372.8	374.1	375.5	376.4	377.2	378.0	378.7	379.4	380.2
137.5°	389.6	390.5	391.4	392.4	393.2	394.1	394.9	395.8	396.6	397.4	398.2
140°	402.3	402.9	403.6	404.2	404.8	405.6	406.6	407.4	408.3	409.2	409.9
142.5°	412.8	413.5	414.0	414.6	415.2	416.0	417.0	418.0	419.0	420.1	420.8
145°	429.5	429.4	429.3	429.2	429.1	429.8	431.2	432.6	433.9	435.3	435.9
147.5°	443.9	443.7	443.3	443.1	442.7	443.2	444.6	446.0	447.4	448.8	449.2
150°	453.4	452.8	452.2	451.7	451.1	451.4	452.8	454.1	455.4	456.7	457.2
152.5°	461.3	460.7	460.0	459.4	458.7	459.1	460.3	461.6	462.8	464.1	464.5
155°	472.9	472.2	471.4	470.7	469.9	470.1	471.1	472.0	473.0	474.0	474.5
157.5°	481.9	481.3	480.7	480.1	479.5	479.5	480.2	480.9	481.6	482.2	482.8
160°	487.2	486.7	486.3	485.8	485.3	485.3	485.8	486.3	486.7	487.2	487.8
162.5°	492.0	491.5	490.9	490.5	490.0	490.0	490.3	490.8	491.2	491.6	492.2
165°	498.3	497.8	497.3	496.8	496.3	496.2	496.5	496.7	497.0	497.1	497.7
167.5°	503.0	502.5	502.0	501.5	501.0	500.9	501.1	501.4	501.6	501.8	502.4
170°	505.7	505.1	504.6	504.2	503.7	503.5	503.7	503.9	504.0	504.2	504.7
172.5°	507.4	507.0	506.4	505.9	505.4	505.3	505.4	505.6	505.8	505.9	506.5
175°	509.7	509.1	508.5	508.0	507.4	507.2	507.4	507.6	507.6	507.8	508.4
177.5°	510.1	509.6	509.1	508.7	508.2	508.0	508.1	508.2	508.2	508.2	508.8
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6



TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
0°	710.5	710.5	710.5	710.5	710.5	710.5	710.5	710.5
2.5°	707.1	708.3	709.5	709.9	709.7	709.5	709.2	709.0
5°	701.5	702.8	704.1	704.6	704.1	703.7	703.3	702.8
7.5°	690.2	690.5	691.0	690.8	690.0	689.2	688.5	687.8
10°	678.8	678.4	678.0	677.3	676.5	675.6	674.8	673.9
12.5°	665.8	665.0	664.3	663.1	661.7	660.3	658.8	657.5
15°	641.4	638.8	636.0	634.0	632.5	631.1	629.6	628.3
17.5°	613.9	610.7	607.4	604.6	602.2	599.7	597.3	594.8
20°	594.7	591.2	587.5	584.2	581.1	577.9	574.8	571.6
22.5°	573.6	569.0	564.5	560.9	558.6	556.3	554.0	551.6
25°	538.7	532.9	527.0	523.0	520.8	518.7	516.6	514.4
27.5°	505.4	498.5	491.7	486.6	483.2	479.8	476.4	473.0
30°	481.8	474.6	467.3	461.7	457.8	454.0	450.1	446.3
32.5°	458.1	449.9	441.5	435.6	432.0	428.3	424.6	421.0
35°	421.2	412.2	403.2	397.1	394.0	390.8	387.7	384.5
37.5°	385.1	375.2	365.3	358.5	355.0	351.4	347.8	344.1
40°	361.0	350.9	340.7	333.8	330.1	326.4	322.6	318.9
42.5°	336.7	326.1	315.7	308.7	305.1	301.4	297.8	294.2
45°	301.2	291.1	280.9	274.1	270.7	267.3	263.8	260.5
47.5°	266.7	256.7	246.6	240.0	236.9	233.8	230.6	227.5
50°	244.5	234.7	224.8	218.4	215.4	212.4	209.4	206.4
52.5°	223.6	214.1	204.6	198.5	195.7	193.0	190.1	187.4
55°	191.8	183.2	174.7	169.0	166.3	163.6	160.9	158.2
57.5°	162.9	155.1	147.2	142.2	139.8	137.6	135.3	132.9
60°	142.9	135.7	128.4	123.6	121.3	119.0	116.8	114.4
62.5°	125.6	118.7	111.8	107.6	106.2	104.9	103.5	102.1
65°	102.2	97.3	92.5	89.8	89.4	88.9	88.5	88.1
67.5°	82.5	80.2	78.0	76.7	76.2	75.8	75.3	74.8
70°	71.7	70.3	68.9	67.8	67.3	66.7	66.1	65.6
72.5°	62.4	61.2	60.0	59.2	58.9	58.5	58.2	57.9
75°	49.4	48.5	47.4	46.8	46.8	46.6	46.4	46.3
77.5°	37.5	36.9	36.3	35.9	35.6	35.5	35.2	35.0
80°	29.7	29.2	28.6	28.3	28.3	28.3	28.3	28.3
82.5°	22.5	22.1	21.8	21.6	21.6	21.6	21.6	21.6
85°	12.2	12.2	12.2	12.2	12.2	12.2	12.2	12.2
87.5°	5.5	5.5	5.4	5.4	5.5	5.5	5.6	5.6
90°	8.2	8.6	9.0	9.3	9.5	9.6	9.8	9.9
92.5°	9.0	9.2	9.4	9.6	9.6	9.7	9.8	9.9
95°	15.2	15.6	16.0	16.2	16.1	16.0	15.9	15.8
97.5°	19.9	20.2	20.5	20.8	20.8	20.9	21.0	21.1
100°	22.3	22.9	23.6	24.0	24.2	24.4	24.5	24.6
102.5°	23.2	24.1	25.0	25.5	25.7	26.0	26.2	26.4
105°	24.3	25.1	26.1	26.7	26.9	27.3	27.6	28.0
107.5°	29.6	28.7	27.7	27.5	27.8	28.2	28.4	28.8
110°	48.0	39.9	31.7	27.7	28.1	28.4	28.8	29.1



TEST NUMBER: P331787-935

CATALOG NUMBER: S122RDIW-S485D435U935-4F0-1E-UDD-F

CANDELA DISTRIBUTION (continued):

	55°	60°	65°	70°	75°	80°	85°	90°
112.5°	102.8	72.9	43.1	28.3	28.6	28.8	29.1	29.4
115°	151.4	113.5	75.6	53.7	47.9	41.9	36.1	30.1
117.5°	233.2	224.0	214.8	200.6	181.2	161.9	142.6	123.2
120°	271.7	272.7	273.7	268.6	257.6	246.6	235.5	224.5
122.5°	288.3	288.9	289.5	288.7	286.5	284.4	282.2	280.1
125°	312.1	312.7	313.2	313.7	313.9	314.2	314.4	314.6
127.5°	334.2	334.9	335.8	336.2	336.3	336.3	336.4	336.4
130°	348.1	349.0	349.9	350.3	350.3	350.2	350.1	350.0
132.5°	361.7	362.4	363.2	363.5	363.4	363.3	363.3	363.3
135°	381.1	381.9	382.7	383.0	382.9	382.7	382.5	382.4
137.5°	399.1	399.8	400.6	400.9	400.6	400.4	400.1	399.8
140°	410.7	411.5	412.2	412.3	411.9	411.5	411.1	410.7
142.5°	421.5	422.1	422.8	422.9	422.5	422.1	421.7	421.3
145°	436.5	437.0	437.6	437.7	437.3	436.9	436.5	436.1
147.5°	449.6	450.0	450.5	450.5	450.1	449.8	449.4	449.1
150°	457.7	458.1	458.7	458.7	458.3	457.9	457.4	457.1
152.5°	465.0	465.5	466.1	466.0	465.5	464.9	464.3	463.8
155°	475.0	475.4	476.0	475.9	475.2	474.6	473.9	473.3
157.5°	483.4	483.9	484.5	484.4	483.8	483.1	482.5	481.9
160°	488.2	488.7	489.2	489.1	488.6	488.0	487.4	486.9
162.5°	492.8	493.4	493.9	493.8	493.1	492.4	491.7	491.0
165°	498.3	498.9	499.5	499.5	498.9	498.3	497.7	497.1
167.5°	503.0	503.5	504.1	504.0	503.3	502.6	501.8	501.1
170°	505.3	505.9	506.4	506.4	505.7	504.9	504.2	503.4
172.5°	507.0	507.6	508.2	508.2	507.4	506.7	505.9	505.2
175°	509.0	509.5	510.1	510.1	509.2	508.4	507.6	506.8
177.5°	509.2	509.6	510.1	510.1	509.5	508.9	508.2	507.7
180°	508.6	508.6	508.6	508.6	508.6	508.6	508.6	508.6

(END OF REPORT)